

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930914

Luminaire Tested: DFN2DS-SQ3F0-040DS930-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930914
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-040DS930-RLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2771.0 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 38.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930914

CATALOG NUMBER: DFN2DS-SQ3F0-040DS930-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930914

CATALOG NUMBER: DFN2DS-SQ3F0-040DS930-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1544	1544	1544
5°	1550	1524	1533
10°	1538	1499	1487
15°	1520	1455	1413
20°	1496	1392	1322
25°	1471	1319	1233
30°	1436	1245	1120
35°	1402	1165	1020
40°	1368	1082	905
45°	1328	988	800
50°	1287	893	698
55°	1245	792	599
60°	1196	685	498
65°	1141	575	453
70°	1074	474	416
75°	993	432	389
80°	876	385	354
85°	689	304	304

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1328 cd/sqm

TEST NUMBER: P930914

CATALOG NUMBER: DFN2DS-SQ3F0-040DS930-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	4.6
10°-20°	346.7	12.5
20°-30°	486.7	17.6
30°-40°	530.5	19.1
40°-50°	487.6	17.6
50°-60°	382.9	13.8
60°-70°	249.3	9.0
70°-80°	128.3	4.6
80°-90°	32.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	959.6	34.6
0°-40°	1490.1	53.8
0°-60°	2360.7	85.2
0°-90°	2771.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2771.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1347	1347	1347	1347	1347	
5°	1347	1341	1325	1336	1333	128
15°	1282	1268	1227	1204	1191	361
25°	1163	1124	1044	994	975	535
35°	1002	940	833	756	729	627
45°	819	738	610	523	494	633
55°	623	528	396	323	300	557
65°	421	322	212	171	167	417
75°	224	139	98	89	88	237
85°	52	27	23	23	23	63
90°	0	0	0	0	0	

TEST NUMBER: P930914

CATALOG NUMBER: DFN2DS-SQ3F0-040DS930-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1347.4	1347.4	1347.4	1347.4	1347.4
2.5°	1353.5	1347.4	1333.9	1346.2	1343.7
5°	1347.4	1341.2	1325.4	1336.4	1332.8
7.5°	1336.4	1329.1	1312.1	1316.8	1310.8
10°	1321.8	1313.2	1288.8	1285.1	1277.9
12.5°	1303.5	1292.5	1259.5	1252.2	1238.8
15°	1281.5	1268.1	1226.7	1203.5	1191.4
17.5°	1255.9	1236.4	1185.1	1158.4	1138.8
20°	1226.7	1202.2	1141.2	1110.8	1083.9
22.5°	1195.0	1166.9	1096.1	1054.7	1036.5
25°	1163.2	1124.2	1043.7	993.8	975.4
27.5°	1125.5	1083.9	995.0	937.7	909.5
30°	1085.3	1038.8	941.2	879.1	846.2
32.5°	1046.2	990.1	890.1	817.0	786.4
35°	1002.4	940.1	832.8	756.0	729.1
37.5°	959.7	892.5	779.1	695.0	664.6
40°	914.5	841.4	723.1	636.5	604.8
42.5°	868.1	790.1	667.0	576.7	546.3
45°	819.4	737.7	609.7	523.1	493.8
47.5°	773.1	686.6	554.9	468.2	441.4
50°	721.8	635.3	501.1	417.0	391.4
52.5°	671.8	580.4	450.0	369.4	346.3
55°	623.1	528.0	396.3	323.1	300.0
57.5°	573.1	475.6	348.7	280.4	261.0
60°	521.8	424.3	298.7	236.6	217.1
62.5°	472.0	374.4	256.0	197.6	187.9
65°	420.7	321.8	212.1	170.7	167.0
67.5°	372.0	273.1	170.7	150.0	146.3
70°	320.7	225.6	141.4	129.3	124.3
72.5°	272.0	181.7	118.3	108.6	106.1
75°	224.3	139.0	97.6	89.0	87.9
77.5°	176.9	98.7	76.9	72.0	69.4
80°	132.8	70.7	58.4	53.7	53.7
82.5°	92.7	47.6	40.3	37.7	37.7
85°	52.4	26.8	23.1	23.1	23.1
87.5°	19.6	9.7	9.7	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930914

CATALOG NUMBER: DFN2DS-SQ3F0-040DS930-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.74	14.27	13.11	14.58	14.89	8.70	10.22	9.07	10.54	10.85
	3H	14.51	15.87	14.89	16.20	16.56	9.97	11.33	10.35	11.66	12.02
	4H	15.18	16.46	15.58	16.80	17.18	10.47	11.75	10.87	12.10	12.48
	6H	15.66	16.85	16.08	17.21	17.61	10.85	12.03	11.26	12.40	12.79
	8H	15.83	16.96	16.26	17.35	17.75	10.98	12.10	11.40	12.49	12.89
	12H	15.93	17.01	16.36	17.39	17.82	11.06	12.13	11.49	12.52	12.95
4H	2H	12.85	14.13	13.25	14.48	14.86	9.40	10.68	9.80	11.03	11.41
	3H	14.78	15.84	15.19	16.24	16.64	10.84	11.91	11.25	12.31	12.71
	4H	15.53	16.49	15.96	16.90	17.34	11.44	12.40	11.87	12.81	13.25
	6H	16.12	16.95	16.58	17.40	17.86	11.93	12.76	12.39	13.21	13.66
	8H	16.34	17.11	16.80	17.56	18.03	12.09	12.87	12.56	13.31	13.78
	12H	16.49	17.18	16.97	17.66	18.13	12.21	12.90	12.69	13.38	13.85
8H	4H	15.55	16.33	16.02	16.78	17.24	11.80	12.57	12.26	13.02	13.49
	6H	16.19	16.83	16.69	17.33	17.80	12.38	13.03	12.88	13.52	13.99
	8H	16.44	17.02	16.96	17.53	18.02	12.60	13.18	13.12	13.69	14.18
	12H	16.65	17.16	17.16	17.65	18.21	12.78	13.29	13.29	13.78	14.35
12H	4H	15.54	16.23	16.02	16.71	17.18	11.84	12.53	12.32	13.01	13.48
	6H	16.17	16.75	16.69	17.26	17.75	12.45	13.02	12.96	13.53	14.02
	8H	16.46	16.97	16.97	17.46	18.02	12.72	13.23	13.23	13.72	14.29