

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331366-927

Luminaire Tested: **S122DIP-S675D1080U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331366-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S675D1080U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5734.9 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331366-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331366-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41					41			
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	42	41	35					35			
2	88	81	75	70	80	74	69	65	61	57	54	49	46	44	38	36	35	30					30			
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26					26			
4	74	63	56	50	67	58	51	46	48	43	40	39	36	33	31	28	26	22					22			
5	68	57	49	43	61	52	45	40	43	38	34	35	32	29	28	25	23	20					20			
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18					18			
7	58	46	38	33	53	42	36	31	36	30	27	29	25	22	23	20	18	16					16			
8	54	42	34	29	49	39	32	27	32	27	24	27	23	20	21	19	17	14					14			
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13					13			
10	47	35	28	23	43	32	26	22	27	23	19	23	19	16	18	16	14	12					12			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16990	16990	16990	16990
5°	19047	17099	15152	17099
10°	21827	16959	13114	16959
15°	24145	16649	11587	16649
20°	23778	16314	10562	16314
25°	21440	15871	9912	15871
30°	17717	15163	9439	15163
35°	12912	14420	9102	14420
40°	10313	13544	8916	13544
45°	9012	12529	8661	12529
50°	8470	11549	8493	11549
55°	7809	10553	8265	10553
60°	7156	9494	7915	9494
65°	6518	8542	7568	8542
70°	5915	7619	7062	7619
75°	5246	6581	6257	6581
80°	4519	5449	5040	5449
85°	4057	4057	3001	4057



TEST NUMBER: P331366-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.2	1.7
10°-20°	291.3	5.1
20°-30°	422.8	7.4
30°-40°	446.2	7.8
40°-50°	395.0	6.9
50°-60°	315.3	5.5
60°-70°	214.3	3.7
70°-80°	109.9	1.9
80°-90°	29.4	0.5
90°-100°	38.8	0.7
100°-110°	142.4	2.5
110°-120°	380.6	6.6
120°-130°	628.2	11.0
130°-140°	668.1	11.6
140°-150°	620.9	10.8
150°-160°	499.2	8.7
160°-170°	321.7	5.6
170°-180°	110.7	1.9
0°-30°	814.3	14.2
0°-40°	1260.5	22.0
0°-60°	1970.8	34.4
0°-90°	2324.3	40.5
90°-120°	561.7	9.8
90°-150°	2478.9	43.2
90°-180°	3411.0	59.5
0°-180°	5734.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1052	1052	1052	1052	1052	
5°	1175	1055	935	1055	1175	117
15°	1444	996	693	996	1444	399
25°	1204	891	556	891	1204	544
35°	655	732	462	732	655	426
45°	395	549	379	549	395	310
55°	277	375	294	375	277	249
65°	171	224	198	224	171	170
75°	84	106	100	106	84	90
85°	22	22	16	22	22	25
90°	23	1	23	1	23	11
95°	36	55	36	55	36	34
105°	64	256	64	256	64	67
115°	69	484	69	484	69	173
125°	720	685	720	685	720	623
135°	875	847	875	847	875	674
145°	998	983	998	983	998	624
155°	1083	1082	1083	1082	1083	500
165°	1138	1140	1138	1140	1138	321
175°	1160	1166	1160	1166	1160	110
180°	1164	1164	1164	1164	1164	



TEST NUMBER: P331366-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1100.7	1101.1	1101.8	1096.5	1095.9	1095.9	1091.4	1087.5	1083.0	1076.8	1077.4
5°	1175.2	1179.6	1181.2	1176.4	1169.1	1168.3	1161.4	1150.1	1139.6	1131.1	1125.1
7.5°	1264.0	1265.7	1261.8	1255.4	1250.0	1240.3	1227.5	1215.0	1197.4	1181.3	1169.3
10°	1331.3	1333.7	1326.8	1317.6	1309.9	1298.5	1279.9	1260.9	1237.9	1215.6	1197.8
12.5°	1382.4	1388.4	1379.6	1378.3	1365.2	1349.6	1327.5	1317.9	1285.4	1254.4	1235.3
15°	1444.5	1444.1	1444.9	1437.3	1427.5	1425.1	1401.6	1376.2	1330.5	1312.2	1280.7
17.5°	1426.6	1432.7	1435.5	1435.4	1435.2	1433.7	1426.2	1410.1	1387.2	1357.6	1321.2
20°	1383.9	1391.9	1393.1	1402.5	1407.7	1414.6	1417.4	1412.9	1398.8	1374.1	1342.6
22.5°	1317.9	1320.1	1323.9	1338.4	1349.8	1367.0	1376.0	1391.0	1385.5	1373.5	1347.1
25°	1203.5	1199.4	1213.6	1220.8	1247.1	1274.6	1294.5	1316.3	1335.7	1347.4	1339.7
27.5°	1066.1	1060.1	1081.2	1100.6	1122.0	1151.8	1182.6	1219.1	1249.4	1287.4	1300.4
30°	950.3	953.9	974.2	994.8	1027.1	1069.2	1104.0	1144.1	1187.3	1229.8	1259.3
32.5°	825.5	839.5	852.2	883.8	912.3	959.3	1010.2	1060.3	1114.2	1162.4	1208.2
35°	655.1	671.3	689.1	712.2	752.2	798.7	848.4	915.9	989.6	1055.5	1109.7
37.5°	551.4	548.8	559.0	575.7	608.2	645.6	702.9	769.7	856.3	933.7	1010.2
40°	489.3	487.7	495.0	510.3	535.0	562.5	612.7	671.3	751.8	846.4	937.4
42.5°	446.6	447.6	451.6	462.5	479.3	502.0	539.6	589.5	663.1	752.3	850.0
45°	394.7	397.5	402.0	407.3	416.9	435.5	456.5	492.2	550.4	624.8	721.0
47.5°	357.4	357.4	361.9	366.5	372.3	382.8	400.0	422.2	463.3	523.9	606.7
50°	337.2	334.5	337.7	341.3	347.4	354.7	366.0	387.0	414.5	463.4	532.6
52.5°	312.7	312.8	315.7	317.0	322.5	329.7	340.1	354.7	379.5	417.8	474.7
55°	277.4	279.4	281.1	283.4	288.4	293.6	301.7	311.4	330.8	359.5	401.6
57.5°	244.2	244.9	246.5	251.1	254.2	259.0	266.7	275.5	288.2	309.4	341.0
60°	221.6	221.6	224.8	226.9	230.9	235.8	241.9	250.3	261.7	279.0	304.5
62.5°	200.9	200.6	201.8	205.2	208.3	212.8	218.9	226.1	236.7	252.2	273.1
65°	170.6	169.8	172.3	173.1	176.3	180.8	185.6	193.3	201.8	213.1	231.7
67.5°	141.6	142.5	143.8	145.4	147.1	151.8	155.0	160.5	167.6	177.1	189.6
70°	125.3	125.3	125.3	126.6	129.0	131.4	134.7	139.1	146.0	154.1	165.4
72.5°	107.3	108.5	109.8	109.1	112.2	113.6	117.5	120.0	126.6	131.7	141.8
75°	84.1	84.1	84.1	86.1	87.4	88.6	91.0	93.4	96.6	103.1	108.4
77.5°	62.7	62.6	63.0	63.5	64.8	66.2	66.9	69.2	72.2	75.1	79.6
80°	48.6	49.4	49.7	50.5	50.5	51.3	51.7	54.6	56.6	58.6	61.5
82.5°	37.5	37.7	37.8	37.9	38.3	38.7	39.8	40.7	41.4	43.1	45.3
85°	21.9	21.5	21.5	22.3	21.9	21.9	22.7	23.4	23.4	23.8	25.0
87.5°	13.0	12.9	13.2	12.8	12.7	12.8	12.7	12.1	12.3	12.4	12.4
90°	22.7	22.3	22.0	21.6	21.2	20.6	19.6	18.7	17.7	16.9	15.4
92.5°	22.7	22.5	22.3	22.1	21.9	21.5	21.0	20.5	20.0	19.6	18.8
95°	36.2	36.4	36.6	36.8	37.0	36.6	35.6	34.7	33.7	32.9	31.5
97.5°	48.3	48.1	47.9	47.7	47.5	47.0	46.2	45.5	44.7	44.0	41.0
100°	56.4	56.1	55.7	55.3	54.9	54.0	52.5	51.0	49.5	48.0	44.8
102.5°	60.4	60.0	59.4	58.9	58.4	57.1	55.2	53.2	51.3	49.4	46.0
105°	64.0	63.2	62.5	61.8	61.0	59.6	57.5	55.5	53.4	51.3	48.4
107.5°	65.8	65.1	64.3	63.6	62.9	63.5	65.6	67.7	69.8	71.9	73.2
110°	66.5	65.8	65.0	64.2	63.5	72.5	91.3	110.0	128.7	147.3	201.5



TEST NUMBER: P331366-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	67.2	66.6	66.0	65.4	64.8	98.6	166.9	235.2	303.5	371.7	385.1
115°	69.1	82.5	96.0	109.5	122.9	173.0	259.7	346.3	432.9	519.6	514.9
117.5°	281.9	326.2	370.5	414.8	459.1	491.7	512.6	533.6	554.5	575.5	572.3
120°	513.7	538.9	564.2	589.5	614.7	626.3	624.0	621.8	619.5	617.3	613.9
122.5°	641.0	645.9	650.9	655.8	660.6	662.4	661.1	659.7	658.4	657.0	653.4
125°	720.0	719.5	718.9	718.4	717.8	716.8	715.5	714.2	712.9	711.6	708.1
127.5°	769.8	769.8	769.7	769.5	769.4	768.4	766.5	764.6	762.7	760.8	758.1
130°	800.9	801.1	801.2	801.5	801.6	800.7	798.6	796.5	794.5	792.4	790.4
132.5°	831.2	831.4	831.6	831.7	831.9	831.2	829.4	827.6	825.9	824.1	822.0
135°	875.0	875.4	875.7	876.1	876.5	875.7	873.9	872.0	870.1	868.2	866.6
137.5°	914.9	915.5	916.2	916.8	917.4	916.8	915.0	913.1	911.3	909.5	907.6
140°	939.8	940.7	941.7	942.6	943.6	943.2	941.5	939.8	938.1	936.4	934.4
142.5°	964.1	965.0	965.9	966.9	967.8	967.5	966.0	964.4	962.9	961.4	959.0
145°	997.9	998.9	999.8	1000.8	1001.6	1001.5	1000.1	998.9	997.5	996.2	993.1
147.5°	1027.7	1028.5	1029.3	1030.1	1030.9	1030.8	1029.8	1028.8	1027.9	1026.9	1023.7
150°	1045.9	1046.9	1047.8	1048.7	1049.6	1049.6	1048.5	1047.3	1046.2	1045.0	1042.1
152.5°	1061.4	1062.6	1063.9	1065.1	1066.4	1066.4	1065.3	1064.1	1063.0	1061.9	1059.1
155°	1083.0	1084.5	1086.0	1087.4	1088.9	1089.2	1088.1	1086.9	1085.8	1084.7	1082.4
157.5°	1102.6	1104.1	1105.6	1107.1	1108.5	1108.6	1107.3	1106.0	1104.8	1103.5	1101.9
160°	1114.1	1115.5	1116.7	1118.1	1119.4	1119.4	1118.3	1117.2	1116.1	1115.0	1113.9
162.5°	1123.6	1125.1	1126.8	1128.4	1130.0	1130.2	1128.9	1127.6	1126.3	1125.1	1124.1
165°	1137.7	1139.0	1140.3	1141.6	1143.0	1143.0	1141.6	1140.3	1139.0	1137.7	1137.2
167.5°	1146.6	1148.3	1150.0	1151.7	1153.3	1153.6	1152.2	1151.0	1149.6	1148.3	1147.8
170°	1152.0	1153.7	1155.4	1157.1	1158.7	1159.0	1157.6	1156.3	1155.0	1153.7	1153.3
172.5°	1156.0	1157.8	1159.4	1161.1	1162.8	1163.0	1161.7	1160.4	1159.0	1157.8	1157.4
175°	1159.6	1161.5	1163.3	1165.2	1167.1	1167.4	1166.1	1164.7	1163.5	1162.1	1161.7
177.5°	1161.8	1163.2	1164.5	1165.9	1167.2	1167.4	1166.3	1165.2	1164.2	1163.2	1163.0
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8



TEST NUMBER: P331366-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1079.7	1077.1	1075.5	1069.7	1064.5	1059.4	1057.7	1058.4	1051.3	1044.5	1041.6
5°	1121.8	1113.7	1106.0	1095.1	1082.2	1068.0	1060.7	1055.0	1040.9	1025.6	1016.7
7.5°	1159.5	1148.0	1133.1	1112.5	1093.8	1071.5	1057.3	1044.8	1024.1	1002.4	989.1
10°	1182.5	1166.6	1147.6	1122.6	1099.5	1072.5	1053.4	1034.4	1010.2	984.3	968.1
12.5°	1202.2	1180.9	1162.2	1130.0	1102.8	1068.9	1046.3	1019.5	994.0	963.3	947.5
15°	1249.2	1210.0	1174.3	1138.0	1104.4	1057.1	1032.1	996.0	962.4	924.5	906.3
17.5°	1285.5	1241.4	1185.3	1139.1	1099.9	1047.6	1010.7	967.7	928.0	884.5	859.8
20°	1306.2	1255.6	1195.4	1140.4	1093.4	1033.6	993.6	949.5	903.0	854.1	827.4
22.5°	1318.5	1265.4	1205.8	1135.5	1080.5	1022.3	971.9	923.6	876.5	823.7	795.7
25°	1322.4	1273.8	1210.8	1131.5	1064.4	998.5	937.8	890.9	833.9	784.5	743.7
27.5°	1303.1	1268.4	1207.7	1123.9	1045.7	968.6	901.0	847.9	787.7	734.1	693.1
30°	1279.5	1259.3	1200.2	1116.1	1030.8	947.9	873.5	813.3	753.4	699.2	657.1
32.5°	1242.9	1238.6	1186.7	1105.1	1014.9	921.7	844.7	783.8	717.5	664.2	624.2
35°	1171.2	1190.6	1157.8	1080.5	985.1	884.4	801.1	731.6	662.8	611.9	574.3
37.5°	1074.9	1123.1	1114.5	1044.6	944.8	843.8	751.9	679.1	613.6	562.2	525.3
40°	1008.5	1070.0	1079.0	1017.1	916.4	812.5	714.9	642.6	578.7	531.8	494.6
42.5°	937.4	1009.2	1033.6	984.0	885.3	779.4	682.0	607.0	543.8	498.1	465.2
45°	818.1	913.1	957.2	928.9	833.5	725.1	624.8	548.7	491.3	448.5	423.0
47.5°	706.5	810.4	869.7	859.7	775.8	668.4	569.3	496.4	440.5	406.2	383.4
50°	627.6	734.4	806.0	809.2	734.4	628.0	528.5	459.8	408.4	376.5	357.9
52.5°	559.0	660.9	739.0	756.1	688.1	586.0	492.0	423.6	378.3	349.0	332.3
55°	469.5	555.6	642.1	673.8	619.1	522.0	435.1	374.9	332.4	312.2	297.6
57.5°	390.3	462.2	542.1	576.9	543.3	460.2	378.7	326.4	291.9	274.2	263.0
60°	348.6	405.2	476.3	518.0	488.9	414.9	343.7	294.0	265.7	249.9	239.4
62.5°	309.7	359.9	420.1	458.2	442.4	372.6	308.8	264.9	240.4	225.6	218.1
65°	255.6	295.2	341.7	376.9	366.4	313.4	261.3	223.6	204.2	192.5	186.4
67.5°	210.5	239.1	271.3	302.1	293.7	256.1	214.3	185.0	170.5	160.4	156.8
70°	182.0	203.8	232.5	257.2	250.3	219.6	186.4	161.4	148.9	140.3	136.7
72.5°	154.8	172.8	194.6	214.8	210.2	184.7	157.0	138.1	128.4	120.6	117.6
75°	116.8	130.6	143.9	157.3	156.1	136.3	120.1	105.5	97.8	91.8	90.5
77.5°	86.3	94.0	103.1	111.0	108.8	97.4	84.8	76.4	70.7	66.7	66.1
80°	65.9	70.3	76.8	82.5	79.7	74.8	64.7	58.6	54.6	50.5	49.0
82.5°	47.8	52.3	56.2	59.2	57.0	52.5	46.3	42.1	39.7	37.0	36.3
85°	25.0	27.5	29.2	29.9	29.2	26.3	23.4	21.9	19.8	18.6	18.2
87.5°	12.4	12.2	11.9	12.2	10.8	10.4	8.6	7.3	7.4	7.4	7.2
90°	13.9	12.4	10.9	9.1	7.1	5.0	2.9	0.9	2.9	5.0	7.1
92.5°	18.1	17.3	16.6	16.2	16.5	16.6	16.8	17.0	16.8	16.6	16.5
95°	30.3	28.9	27.6	30.0	36.2	42.4	48.6	54.7	48.6	42.4	36.2
97.5°	37.9	34.9	31.8	39.1	56.4	73.8	91.3	108.6	91.3	73.8	56.4
100°	41.7	38.4	35.3	46.5	72.2	97.8	123.4	149.1	123.4	97.8	72.2
102.5°	102.6	129.2	155.8	171.8	177.2	182.7	188.1	193.5	188.1	182.7	177.2
105°	153.5	204.6	255.7	278.5	272.8	267.2	261.7	256.0	261.7	267.2	272.8
107.5°	194.5	255.7	317.0	345.4	340.8	336.3	331.8	327.3	331.8	336.3	340.8
110°	255.6	309.6	363.7	388.8	384.8	381.0	377.0	373.0	377.0	381.0	384.8



TEST NUMBER: P331366-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	398.5	411.8	425.2	430.1	426.6	423.1	419.7	416.2	419.7	423.1	426.6
115°	510.2	505.6	500.9	496.9	493.8	490.6	487.4	484.3	487.4	490.6	493.8
117.5°	569.1	565.9	562.6	559.3	555.7	552.2	548.6	545.0	548.6	552.2	555.7
120°	610.5	607.2	603.8	600.7	597.9	595.1	592.3	589.5	592.3	595.1	597.9
122.5°	649.7	646.0	642.4	639.1	636.1	633.1	630.2	627.2	630.2	633.1	636.1
125°	704.5	700.9	697.4	694.3	692.0	689.5	687.1	684.7	687.1	689.5	692.0
127.5°	755.4	752.8	750.1	747.5	744.8	742.1	739.4	736.7	739.4	742.1	744.8
130°	788.3	786.2	784.2	781.6	778.7	775.7	772.7	769.7	772.7	775.7	778.7
132.5°	820.0	817.9	815.9	813.6	811.0	808.5	806.0	803.4	806.0	808.5	811.0
135°	864.8	863.2	861.5	859.1	856.2	853.2	850.2	847.2	850.2	853.2	856.2
137.5°	905.7	903.8	901.8	899.8	897.8	895.6	893.6	891.4	893.6	895.6	897.8
140°	932.3	930.3	928.2	926.5	925.0	923.4	921.9	920.4	921.9	923.4	925.0
142.5°	956.6	954.3	952.0	950.1	948.7	947.4	946.0	944.7	946.0	947.4	948.7
145°	989.8	986.7	983.5	982.0	982.2	982.4	982.5	982.8	982.5	982.4	982.2
147.5°	1020.6	1017.5	1014.3	1013.1	1013.8	1014.5	1015.3	1016.0	1015.3	1014.5	1013.8
150°	1039.1	1036.1	1033.1	1032.3	1033.6	1034.9	1036.2	1037.5	1036.2	1034.9	1033.6
152.5°	1056.2	1053.4	1050.5	1049.9	1051.3	1052.7	1054.2	1055.7	1054.2	1052.7	1051.3
155°	1080.1	1077.9	1075.7	1075.4	1077.1	1078.8	1080.5	1082.1	1080.5	1078.8	1077.1
157.5°	1100.3	1098.8	1097.3	1097.2	1098.6	1100.0	1101.5	1102.9	1101.5	1100.0	1098.6
160°	1112.7	1111.6	1110.5	1110.5	1111.6	1112.7	1113.9	1115.0	1113.9	1112.7	1111.6
162.5°	1123.2	1122.1	1121.2	1121.3	1122.4	1123.5	1124.7	1125.8	1124.7	1123.5	1122.4
165°	1136.6	1136.0	1135.4	1135.8	1136.9	1138.0	1139.1	1140.3	1139.1	1138.0	1136.9
167.5°	1147.2	1146.8	1146.2	1146.5	1147.6	1148.7	1149.9	1151.0	1149.9	1148.7	1147.6
170°	1152.9	1152.6	1152.2	1152.6	1153.7	1154.8	1156.0	1157.1	1156.0	1154.8	1153.7
172.5°	1157.0	1156.7	1156.3	1156.7	1157.8	1158.9	1160.0	1161.1	1160.0	1158.9	1157.8
175°	1161.4	1161.0	1160.6	1161.1	1162.4	1163.7	1165.1	1166.3	1165.1	1163.7	1162.4
177.5°	1162.8	1162.7	1162.5	1163.0	1164.0	1165.1	1166.2	1167.2	1166.2	1165.1	1164.0
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8



TEST NUMBER: P331366-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1038.3	1036.4	1029.6	1026.0	1020.2	1014.7	1011.1	1012.8	1014.1	1013.4	1012.4
5°	1008.5	1000.8	989.1	979.1	971.8	958.4	952.8	949.9	947.5	944.7	941.8
7.5°	973.1	961.0	944.2	929.8	916.2	899.6	890.2	884.5	878.7	872.3	866.6
10°	947.9	930.9	913.1	892.9	876.7	861.7	848.4	839.6	831.5	823.8	818.1
12.5°	921.4	901.8	879.8	852.2	834.3	812.9	810.9	795.2	782.6	777.8	771.2
15°	879.2	851.7	823.8	791.0	776.8	757.4	745.3	733.2	722.2	714.5	712.6
17.5°	831.2	795.6	767.9	744.3	721.1	701.2	690.1	680.3	671.4	661.1	659.7
20°	794.6	763.9	733.6	713.0	689.1	668.8	655.1	645.4	637.7	631.7	626.4
22.5°	760.0	726.4	698.6	676.0	652.5	636.2	625.3	616.0	609.6	602.9	597.9
25°	704.5	678.2	647.8	622.3	602.9	592.5	583.5	575.4	571.4	567.0	561.3
27.5°	655.8	626.6	598.3	578.5	561.5	552.2	545.8	540.3	536.5	533.9	530.8
30°	621.5	592.0	569.8	550.4	536.2	527.0	522.9	519.7	515.2	513.6	512.0
32.5°	588.6	562.0	543.0	526.1	512.6	506.5	502.8	499.9	496.5	494.8	491.5
35°	541.9	519.7	501.1	491.7	480.9	475.5	472.8	468.7	465.5	463.8	463.4
37.5°	498.0	478.6	466.4	454.5	449.9	446.6	442.8	440.0	439.0	438.8	438.4
40°	469.5	453.8	442.8	433.1	431.1	426.2	423.0	420.6	420.6	421.0	420.6
42.5°	443.6	429.4	419.9	411.5	409.1	406.2	402.9	402.7	403.5	404.8	403.5
45°	404.4	394.3	387.4	383.3	378.9	376.0	375.7	376.9	377.3	377.7	378.9
47.5°	368.3	361.6	355.4	350.9	349.0	348.5	348.0	350.1	352.0	352.8	354.7
50°	347.0	339.3	334.1	331.2	329.5	328.8	329.5	332.0	333.6	335.6	336.8
52.5°	323.1	317.6	313.9	311.8	311.2	311.6	311.8	314.6	317.1	317.8	318.5
55°	289.9	285.9	285.1	281.5	283.0	282.7	284.7	286.3	288.8	291.1	291.6
57.5°	257.0	253.7	251.5	251.8	252.3	254.1	255.8	258.6	261.3	263.8	264.0
60°	235.0	233.3	232.1	232.1	232.9	235.4	237.4	240.2	241.9	243.4	244.6
62.5°	214.9	213.3	212.1	212.7	214.8	216.3	218.6	220.1	221.7	223.4	223.9
65°	183.2	182.4	183.6	184.4	184.8	186.8	189.6	190.8	192.5	193.3	196.1
67.5°	154.0	154.2	154.0	155.1	157.5	158.0	160.7	163.4	163.7	165.3	167.2
70°	134.3	135.1	135.9	136.7	138.7	139.5	141.6	142.8	144.3	145.6	146.8
72.5°	116.1	116.3	117.1	116.9	118.7	120.4	122.2	123.3	124.9	126.5	127.7
75°	89.4	89.4	90.2	90.5	92.6	94.7	94.2	95.1	96.6	98.2	99.1
77.5°	65.3	64.4	65.3	65.7	66.3	68.0	68.4	69.5	71.3	70.7	71.7
80°	49.7	48.6	49.7	50.1	50.1	52.2	52.2	53.0	54.2	53.0	54.2
82.5°	35.5	34.9	35.8	35.9	36.5	36.6	37.3	37.5	38.7	38.1	38.7
85°	17.8	17.4	17.8	17.4	17.8	18.2	18.2	17.8	17.8	18.6	17.4
87.5°	7.3	7.4	7.3	7.6	7.6	7.6	7.4	7.6	7.8	7.4	7.4
90°	9.1	10.9	12.4	13.9	15.4	16.9	17.7	18.7	19.6	20.6	21.2
92.5°	16.2	16.6	17.3	18.1	18.8	19.6	20.0	20.5	21.0	21.5	21.9
95°	30.0	27.6	28.9	30.3	31.5	32.9	33.7	34.7	35.6	36.6	37.0
97.5°	39.1	31.8	34.9	37.9	41.0	44.0	44.7	45.5	46.2	47.0	47.5
100°	46.5	35.3	38.4	41.7	44.8	48.0	49.5	51.0	52.5	54.0	54.9
102.5°	171.8	155.8	129.2	102.6	76.0	49.4	51.3	53.2	55.2	57.1	58.4
105°	278.5	255.7	204.6	153.5	102.4	51.3	53.4	55.5	57.5	59.6	61.0
107.5°	345.4	317.0	255.7	194.5	133.2	71.9	69.8	67.7	65.6	63.5	62.9
110°	388.8	363.7	309.6	255.6	201.5	147.3	128.7	110.0	91.3	72.5	63.5



TEST NUMBER: P331366-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	430.1	425.2	411.8	398.5	385.1	371.7	303.5	235.2	166.9	98.6	64.8
115°	496.9	500.9	505.6	510.2	514.9	519.6	432.9	346.3	259.7	173.0	122.9
117.5°	559.3	562.6	565.9	569.1	572.3	575.5	554.5	533.6	512.6	491.7	459.1
120°	600.7	603.8	607.2	610.5	613.9	617.3	619.5	621.8	624.0	626.3	614.7
122.5°	639.1	642.4	646.0	649.7	653.4	657.0	658.4	659.7	661.1	662.4	660.6
125°	694.3	697.4	700.9	704.5	708.1	711.6	712.9	714.2	715.5	716.8	717.8
127.5°	747.5	750.1	752.8	755.4	758.1	760.8	762.7	764.6	766.5	768.4	769.4
130°	781.6	784.2	786.2	788.3	790.4	792.4	794.5	796.5	798.6	800.7	801.6
132.5°	813.6	815.9	817.9	820.0	822.0	824.1	825.9	827.6	829.4	831.2	831.9
135°	859.1	861.5	863.2	864.8	866.6	868.2	870.1	872.0	873.9	875.7	876.5
137.5°	899.8	901.8	903.8	905.7	907.6	909.5	911.3	913.1	915.0	916.8	917.4
140°	926.5	928.2	930.3	932.3	934.4	936.4	938.1	939.8	941.5	943.2	943.6
142.5°	950.1	952.0	954.3	956.6	959.0	961.4	962.9	964.4	966.0	967.5	967.8
145°	982.0	983.5	986.7	989.8	993.1	996.2	997.5	998.9	1000.1	1001.5	1001.6
147.5°	1013.1	1014.3	1017.5	1020.6	1023.7	1026.9	1027.9	1028.8	1029.8	1030.8	1030.9
150°	1032.3	1033.1	1036.1	1039.1	1042.1	1045.0	1046.2	1047.3	1048.5	1049.6	1049.6
152.5°	1049.9	1050.5	1053.4	1056.2	1059.1	1061.9	1063.0	1064.1	1065.3	1066.4	1066.4
155°	1075.4	1075.7	1077.9	1080.1	1082.4	1084.7	1085.8	1086.9	1088.1	1089.2	1088.9
157.5°	1097.2	1097.3	1098.8	1100.3	1101.9	1103.5	1104.8	1106.0	1107.3	1108.6	1108.5
160°	1110.5	1110.5	1111.6	1112.7	1113.9	1115.0	1116.1	1117.2	1118.3	1119.4	1119.4
162.5°	1121.3	1121.2	1122.1	1123.2	1124.1	1125.1	1126.3	1127.6	1128.9	1130.2	1130.0
165°	1135.8	1135.4	1136.0	1136.6	1137.2	1137.7	1139.0	1140.3	1141.6	1143.0	1143.0
167.5°	1146.5	1146.2	1146.8	1147.2	1147.8	1148.3	1149.6	1151.0	1152.2	1153.6	1153.3
170°	1152.6	1152.2	1152.6	1152.9	1153.3	1153.7	1155.0	1156.3	1157.6	1159.0	1158.7
172.5°	1156.7	1156.3	1156.7	1157.0	1157.4	1157.8	1159.0	1160.4	1161.7	1163.0	1162.8
175°	1161.1	1160.6	1161.0	1161.4	1161.7	1162.1	1163.5	1164.7	1166.1	1167.4	1167.1
177.5°	1163.0	1162.5	1162.7	1162.8	1163.0	1163.2	1164.2	1165.2	1166.3	1167.4	1167.2
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8



TEST NUMBER: P331366-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1009.2	1008.5	1008.5	1005.7	1008.5	1008.5	1009.2	1012.4	1013.4	1014.1	1012.8
5°	936.2	934.9	933.0	934.9	933.0	934.9	936.2	941.8	944.7	947.5	949.9
7.5°	864.0	859.1	858.4	853.6	858.4	859.1	864.0	866.6	872.3	878.7	884.5
10°	811.2	807.9	807.6	799.9	807.6	807.9	811.2	818.1	823.8	831.5	839.6
12.5°	771.1	763.3	764.9	760.4	764.9	763.3	771.1	771.2	777.8	782.6	795.2
15°	701.6	701.6	700.0	693.2	700.0	701.6	701.6	712.6	714.5	722.2	733.2
17.5°	651.7	650.9	647.1	649.0	647.1	650.9	651.7	659.7	661.1	671.4	680.3
20°	621.9	619.6	614.7	614.7	614.7	619.6	621.9	626.4	631.7	637.7	645.4
22.5°	593.8	593.7	588.5	590.1	588.5	593.7	593.8	597.9	602.9	609.6	616.0
25°	560.9	557.7	555.2	556.4	555.2	557.7	560.9	561.3	567.0	571.4	575.4
27.5°	529.7	527.9	527.8	524.4	527.8	527.9	529.7	530.8	533.9	536.5	540.3
30°	511.6	507.6	508.3	506.3	508.3	507.6	511.6	512.0	513.6	515.2	519.7
32.5°	490.8	489.4	488.6	486.9	488.6	489.4	490.8	491.5	494.8	496.5	499.9
35°	462.6	463.0	461.1	461.8	461.1	463.0	462.6	463.4	463.8	465.5	468.7
37.5°	438.0	439.3	438.3	438.6	438.3	439.3	438.0	438.4	438.8	439.0	440.0
40°	421.8	421.8	421.8	423.0	421.8	421.8	421.8	420.6	421.0	420.6	420.6
42.5°	406.2	405.6	405.0	404.9	405.0	405.6	406.2	403.5	404.8	403.5	402.7
45°	379.7	381.0	381.4	379.3	381.4	381.0	379.7	378.9	377.7	377.3	376.9
47.5°	355.7	355.8	355.7	357.5	355.7	355.8	355.7	354.7	352.8	352.0	350.1
50°	338.9	338.1	338.9	338.1	338.9	338.1	338.9	336.8	335.6	333.6	332.0
52.5°	321.1	321.2	320.8	320.6	320.8	321.2	321.1	318.5	317.8	317.1	314.6
55°	293.2	294.0	293.6	293.6	293.6	294.0	293.2	291.6	291.1	288.8	286.3
57.5°	264.4	265.1	265.6	263.8	265.6	265.1	264.4	264.0	263.8	261.3	258.6
60°	244.2	246.3	245.9	245.1	245.9	246.3	244.2	244.6	243.4	241.9	240.2
62.5°	225.9	226.6	226.5	226.3	226.5	226.6	225.9	223.9	223.4	221.7	220.1
65°	197.3	198.1	196.9	198.1	196.9	198.1	197.3	196.1	193.3	192.5	190.8
67.5°	166.7	166.9	167.9	168.4	167.9	166.9	166.7	167.2	165.3	163.7	163.4
70°	147.6	147.2	148.4	149.6	148.4	147.2	147.6	146.8	145.6	144.3	142.8
72.5°	127.5	128.4	128.0	128.9	128.0	128.4	127.5	127.7	126.5	124.9	123.3
75°	98.2	99.5	99.1	100.3	99.1	99.5	98.2	99.1	98.2	96.6	95.1
77.5°	71.0	71.1	71.0	71.7	71.0	71.1	71.0	71.7	70.7	71.3	69.5
80°	54.2	53.4	52.6	54.2	52.6	53.4	54.2	54.2	53.0	54.2	53.0
82.5°	37.7	38.2	37.4	37.4	37.4	38.2	37.7	38.7	38.1	38.7	37.5
85°	17.4	17.0	16.2	16.2	16.2	17.0	17.4	17.4	18.6	17.8	17.8
87.5°	7.5	7.3	7.4	7.1	7.4	7.3	7.5	7.4	7.4	7.8	7.6
90°	21.6	22.0	22.3	22.7	22.3	22.0	21.6	21.2	20.6	19.6	18.7
92.5°	22.1	22.3	22.5	22.7	22.5	22.3	22.1	21.9	21.5	21.0	20.5
95°	36.8	36.6	36.4	36.2	36.4	36.6	36.8	37.0	36.6	35.6	34.7
97.5°	47.7	47.9	48.1	48.3	48.1	47.9	47.7	47.5	47.0	46.2	45.5
100°	55.3	55.7	56.1	56.4	56.1	55.7	55.3	54.9	54.0	52.5	51.0
102.5°	58.9	59.4	60.0	60.4	60.0	59.4	58.9	58.4	57.1	55.2	53.2
105°	61.8	62.5	63.2	64.0	63.2	62.5	61.8	61.0	59.6	57.5	55.5
107.5°	63.6	64.3	65.1	65.8	65.1	64.3	63.6	62.9	63.5	65.6	67.7
110°	64.2	65.0	65.8	66.5	65.8	65.0	64.2	63.5	72.5	91.3	110.0



TEST NUMBER: P331366-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	65.4	66.0	66.6	67.2	66.6	66.0	65.4	64.8	98.6	166.9	235.2
115°	109.5	96.0	82.5	69.1	82.5	96.0	109.5	122.9	173.0	259.7	346.3
117.5°	414.8	370.5	326.2	281.9	326.2	370.5	414.8	459.1	491.7	512.6	533.6
120°	589.5	564.2	538.9	513.7	538.9	564.2	589.5	614.7	626.3	624.0	621.8
122.5°	655.8	650.9	645.9	641.0	645.9	650.9	655.8	660.6	662.4	661.1	659.7
125°	718.4	718.9	719.5	720.0	719.5	718.9	718.4	717.8	716.8	715.5	714.2
127.5°	769.5	769.7	769.8	769.8	769.8	769.7	769.5	769.4	768.4	766.5	764.6
130°	801.5	801.2	801.1	800.9	801.1	801.2	801.5	801.6	800.7	798.6	796.5
132.5°	831.7	831.6	831.4	831.2	831.4	831.6	831.7	831.9	831.2	829.4	827.6
135°	876.1	875.7	875.4	875.0	875.4	875.7	876.1	876.5	875.7	873.9	872.0
137.5°	916.8	916.2	915.5	914.9	915.5	916.2	916.8	917.4	916.8	915.0	913.1
140°	942.6	941.7	940.7	939.8	940.7	941.7	942.6	943.6	943.2	941.5	939.8
142.5°	966.9	965.9	965.0	964.1	965.0	965.9	966.9	967.8	967.5	966.0	964.4
145°	1000.8	999.8	998.9	997.9	998.9	999.8	1000.8	1001.6	1001.5	1000.1	998.9
147.5°	1030.1	1029.3	1028.5	1027.7	1028.5	1029.3	1030.1	1030.9	1030.8	1029.8	1028.8
150°	1048.7	1047.8	1046.9	1045.9	1046.9	1047.8	1048.7	1049.6	1049.6	1048.5	1047.3
152.5°	1065.1	1063.9	1062.6	1061.4	1062.6	1063.9	1065.1	1066.4	1066.4	1065.3	1064.1
155°	1087.4	1086.0	1084.5	1083.0	1084.5	1086.0	1087.4	1088.9	1089.2	1088.1	1086.9
157.5°	1107.1	1105.6	1104.1	1102.6	1104.1	1105.6	1107.1	1108.5	1108.6	1107.3	1106.0
160°	1118.1	1116.7	1115.5	1114.1	1115.5	1116.7	1118.1	1119.4	1119.4	1118.3	1117.2
162.5°	1128.4	1126.8	1125.1	1123.6	1125.1	1126.8	1128.4	1130.0	1130.2	1128.9	1127.6
165°	1141.6	1140.3	1139.0	1137.7	1139.0	1140.3	1141.6	1143.0	1143.0	1141.6	1140.3
167.5°	1151.7	1150.0	1148.3	1146.6	1148.3	1150.0	1151.7	1153.3	1153.6	1152.2	1151.0
170°	1157.1	1155.4	1153.7	1152.0	1153.7	1155.4	1157.1	1158.7	1159.0	1157.6	1156.3
172.5°	1161.1	1159.4	1157.8	1156.0	1157.8	1159.4	1161.1	1162.8	1163.0	1161.7	1160.4
175°	1165.2	1163.3	1161.5	1159.6	1161.5	1163.3	1165.2	1167.1	1167.4	1166.1	1164.7
177.5°	1165.9	1164.5	1163.2	1161.8	1163.2	1164.5	1165.9	1167.2	1167.4	1166.3	1165.2
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8



TEST NUMBER: P331366-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1011.1	1014.7	1020.2	1026.0	1029.6	1036.4	1038.3	1041.6	1044.5	1051.3	1058.4
5°	952.8	958.4	971.8	979.1	989.1	1000.8	1008.5	1016.7	1025.6	1040.9	1055.0
7.5°	890.2	899.6	916.2	929.8	944.2	961.0	973.1	989.1	1002.4	1024.1	1044.8
10°	848.4	861.7	876.7	892.9	913.1	930.9	947.9	968.1	984.3	1010.2	1034.4
12.5°	810.9	812.9	834.3	852.2	879.8	901.8	921.4	947.5	963.3	994.0	1019.5
15°	745.3	757.4	776.8	791.0	823.8	851.7	879.2	906.3	924.5	962.4	996.0
17.5°	690.1	701.2	721.1	744.3	767.9	795.6	831.2	859.8	884.5	928.0	967.7
20°	655.1	668.8	689.1	713.0	733.6	763.9	794.6	827.4	854.1	903.0	949.5
22.5°	625.3	636.2	652.5	676.0	698.6	726.4	760.0	795.7	823.7	876.5	923.6
25°	583.5	592.5	602.9	622.3	647.8	678.2	704.5	743.7	784.5	833.9	890.9
27.5°	545.8	552.2	561.5	578.5	598.3	626.6	655.8	693.1	734.1	787.7	847.9
30°	522.9	527.0	536.2	550.4	569.8	592.0	621.5	657.1	699.2	753.4	813.3
32.5°	502.8	506.5	512.6	526.1	543.0	562.0	588.6	624.2	664.2	717.5	783.8
35°	472.8	475.5	480.9	491.7	501.1	519.7	541.9	574.3	611.9	662.8	731.6
37.5°	442.8	446.6	449.9	454.5	466.4	478.6	498.0	525.3	562.2	613.6	679.1
40°	423.0	426.2	431.1	433.1	442.8	453.8	469.5	494.6	531.8	578.7	642.6
42.5°	402.9	406.2	409.1	411.5	419.9	429.4	443.6	465.2	498.1	543.8	607.0
45°	375.7	376.0	378.9	383.3	387.4	394.3	404.4	423.0	448.5	491.3	548.7
47.5°	348.0	348.5	349.0	350.9	355.4	361.6	368.3	383.4	406.2	440.5	496.4
50°	329.5	328.8	329.5	331.2	334.1	339.3	347.0	357.9	376.5	408.4	459.8
52.5°	311.8	311.6	311.2	311.8	313.9	317.6	323.1	332.3	349.0	378.3	423.6
55°	284.7	282.7	283.0	281.5	285.1	285.9	289.9	297.6	312.2	332.4	374.9
57.5°	255.8	254.1	252.3	251.8	251.5	253.7	257.0	263.0	274.2	291.9	326.4
60°	237.4	235.4	232.9	232.1	232.1	233.3	235.0	239.4	249.9	265.7	294.0
62.5°	218.6	216.3	214.8	212.7	212.1	213.3	214.9	218.1	225.6	240.4	264.9
65°	189.6	186.8	184.8	184.4	183.6	182.4	183.2	186.4	192.5	204.2	223.6
67.5°	160.7	158.0	157.5	155.1	154.0	154.2	154.0	156.8	160.4	170.5	185.0
70°	141.6	139.5	138.7	136.7	135.9	135.1	134.3	136.7	140.3	148.9	161.4
72.5°	122.2	120.4	118.7	116.9	117.1	116.3	116.1	117.6	120.6	128.4	138.1
75°	94.2	94.7	92.6	90.5	90.2	89.4	89.4	90.5	91.8	97.8	105.5
77.5°	68.4	68.0	66.3	65.7	65.3	64.4	65.3	66.1	66.7	70.7	76.4
80°	52.2	52.2	50.1	50.1	49.7	48.6	49.7	49.0	50.5	54.6	58.6
82.5°	37.3	36.6	36.5	35.9	35.8	34.9	35.5	36.3	37.0	39.7	42.1
85°	18.2	18.2	17.8	17.4	17.8	17.4	17.8	18.2	18.6	19.8	21.9
87.5°	7.4	7.6	7.6	7.6	7.3	7.4	7.3	7.2	7.4	7.4	7.3
90°	17.7	16.9	15.4	13.9	12.4	10.9	9.1	7.1	5.0	2.9	0.9
92.5°	20.0	19.6	18.8	18.1	17.3	16.6	16.2	16.5	16.6	16.8	17.0
95°	33.7	32.9	31.5	30.3	28.9	27.6	30.0	36.2	42.4	48.6	54.7
97.5°	44.7	44.0	41.0	37.9	34.9	31.8	39.1	56.4	73.8	91.3	108.6
100°	49.5	48.0	44.8	41.7	38.4	35.3	46.5	72.2	97.8	123.4	149.1
102.5°	51.3	49.4	76.0	102.6	129.2	155.8	171.8	177.2	182.7	188.1	193.5
105°	53.4	51.3	102.4	153.5	204.6	255.7	278.5	272.8	267.2	261.7	256.0
107.5°	69.8	71.9	133.2	194.5	255.7	317.0	345.4	340.8	336.3	331.8	327.3
110°	128.7	147.3	201.5	255.6	309.6	363.7	388.8	384.8	381.0	377.0	373.0



TEST NUMBER: P331366-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	303.5	371.7	385.1	398.5	411.8	425.2	430.1	426.6	423.1	419.7	416.2
115°	432.9	519.6	514.9	510.2	505.6	500.9	496.9	493.8	490.6	487.4	484.3
117.5°	554.5	575.5	572.3	569.1	565.9	562.6	559.3	555.7	552.2	548.6	545.0
120°	619.5	617.3	613.9	610.5	607.2	603.8	600.7	597.9	595.1	592.3	589.5
122.5°	658.4	657.0	653.4	649.7	646.0	642.4	639.1	636.1	633.1	630.2	627.2
125°	712.9	711.6	708.1	704.5	700.9	697.4	694.3	692.0	689.5	687.1	684.7
127.5°	762.7	760.8	758.1	755.4	752.8	750.1	747.5	744.8	742.1	739.4	736.7
130°	794.5	792.4	790.4	788.3	786.2	784.2	781.6	778.7	775.7	772.7	769.7
132.5°	825.9	824.1	822.0	820.0	817.9	815.9	813.6	811.0	808.5	806.0	803.4
135°	870.1	868.2	866.6	864.8	863.2	861.5	859.1	856.2	853.2	850.2	847.2
137.5°	911.3	909.5	907.6	905.7	903.8	901.8	899.8	897.8	895.6	893.6	891.4
140°	938.1	936.4	934.4	932.3	930.3	928.2	926.5	925.0	923.4	921.9	920.4
142.5°	962.9	961.4	959.0	956.6	954.3	952.0	950.1	948.7	947.4	946.0	944.7
145°	997.5	996.2	993.1	989.8	986.7	983.5	982.0	982.2	982.4	982.5	982.8
147.5°	1027.9	1026.9	1023.7	1020.6	1017.5	1014.3	1013.1	1013.8	1014.5	1015.3	1016.0
150°	1046.2	1045.0	1042.1	1039.1	1036.1	1033.1	1032.3	1033.6	1034.9	1036.2	1037.5
152.5°	1063.0	1061.9	1059.1	1056.2	1053.4	1050.5	1049.9	1051.3	1052.7	1054.2	1055.7
155°	1085.8	1084.7	1082.4	1080.1	1077.9	1075.7	1075.4	1077.1	1078.8	1080.5	1082.1
157.5°	1104.8	1103.5	1101.9	1100.3	1098.8	1097.3	1097.2	1098.6	1100.0	1101.5	1102.9
160°	1116.1	1115.0	1113.9	1112.7	1111.6	1110.5	1110.5	1111.6	1112.7	1113.9	1115.0
162.5°	1126.3	1125.1	1124.1	1123.2	1122.1	1121.2	1121.3	1122.4	1123.5	1124.7	1125.8
165°	1139.0	1137.7	1137.2	1136.6	1136.0	1135.4	1135.8	1136.9	1138.0	1139.1	1140.3
167.5°	1149.6	1148.3	1147.8	1147.2	1146.8	1146.2	1146.5	1147.6	1148.7	1149.9	1151.0
170°	1155.0	1153.7	1153.3	1152.9	1152.6	1152.2	1152.6	1153.7	1154.8	1156.0	1157.1
172.5°	1159.0	1157.8	1157.4	1157.0	1156.7	1156.3	1156.7	1157.8	1158.9	1160.0	1161.1
175°	1163.5	1162.1	1161.7	1161.4	1161.0	1160.6	1161.1	1162.4	1163.7	1165.1	1166.3
177.5°	1164.2	1163.2	1163.0	1162.8	1162.7	1162.5	1163.0	1164.0	1165.1	1166.2	1167.2
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8



TEST NUMBER: P331366-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1057.7	1059.4	1064.5	1069.7	1075.5	1077.1	1079.7	1077.4	1076.8	1083.0	1087.5
5°	1060.7	1068.0	1082.2	1095.1	1106.0	1113.7	1121.8	1125.1	1131.1	1139.6	1150.1
7.5°	1057.3	1071.5	1093.8	1112.5	1133.1	1148.0	1159.5	1169.3	1181.3	1197.4	1215.0
10°	1053.4	1072.5	1099.5	1122.6	1147.6	1166.6	1182.5	1197.8	1215.6	1237.9	1260.9
12.5°	1046.3	1068.9	1102.8	1130.0	1162.2	1180.9	1202.2	1235.3	1254.4	1285.4	1317.9
15°	1032.1	1057.1	1104.4	1138.0	1174.3	1210.0	1249.2	1280.7	1312.2	1330.5	1376.2
17.5°	1010.7	1047.6	1099.9	1139.1	1185.3	1241.4	1285.5	1321.2	1357.6	1387.2	1410.1
20°	993.6	1033.6	1093.4	1140.4	1195.4	1255.6	1306.2	1342.6	1374.1	1398.8	1412.9
22.5°	971.9	1022.3	1080.5	1135.5	1205.8	1265.4	1318.5	1347.1	1373.5	1385.5	1391.0
25°	937.8	998.5	1064.4	1131.5	1210.8	1273.8	1322.4	1339.7	1347.4	1335.7	1316.3
27.5°	901.0	968.6	1045.7	1123.9	1207.7	1268.4	1303.1	1300.4	1287.4	1249.4	1219.1
30°	873.5	947.9	1030.8	1116.1	1200.2	1259.3	1279.5	1259.3	1229.8	1187.3	1144.1
32.5°	844.7	921.7	1014.9	1105.1	1186.7	1238.6	1242.9	1208.2	1162.4	1114.2	1060.3
35°	801.1	884.4	985.1	1080.5	1157.8	1190.6	1171.2	1109.7	1055.5	989.6	915.9
37.5°	751.9	843.8	944.8	1044.6	1114.5	1123.1	1074.9	1010.2	933.7	856.3	769.7
40°	714.9	812.5	916.4	1017.1	1079.0	1070.0	1008.5	937.4	846.4	751.8	671.3
42.5°	682.0	779.4	885.3	984.0	1033.6	1009.2	937.4	850.0	752.3	663.1	589.5
45°	624.8	725.1	833.5	928.9	957.2	913.1	818.1	721.0	624.8	550.4	492.2
47.5°	569.3	668.4	775.8	859.7	869.7	810.4	706.5	606.7	523.9	463.3	422.2
50°	528.5	628.0	734.4	809.2	806.0	734.4	627.6	532.6	463.4	414.5	387.0
52.5°	492.0	586.0	688.1	756.1	739.0	660.9	559.0	474.7	417.8	379.5	354.7
55°	435.1	522.0	619.1	673.8	642.1	555.6	469.5	401.6	359.5	330.8	311.4
57.5°	378.7	460.2	543.3	576.9	542.1	462.2	390.3	341.0	309.4	288.2	275.5
60°	343.7	414.9	488.9	518.0	476.3	405.2	348.6	304.5	279.0	261.7	250.3
62.5°	308.8	372.6	442.4	458.2	420.1	359.9	309.7	273.1	252.2	236.7	226.1
65°	261.3	313.4	366.4	376.9	341.7	295.2	255.6	231.7	213.1	201.8	193.3
67.5°	214.3	256.1	293.7	302.1	271.3	239.1	210.5	189.6	177.1	167.6	160.5
70°	186.4	219.6	250.3	257.2	232.5	203.8	182.0	165.4	154.1	146.0	139.1
72.5°	157.0	184.7	210.2	214.8	194.6	172.8	154.8	141.8	131.7	126.6	120.0
75°	120.1	136.3	156.1	157.3	143.9	130.6	116.8	108.4	103.1	96.6	93.4
77.5°	84.8	97.4	108.8	111.0	103.1	94.0	86.3	79.6	75.1	72.2	69.2
80°	64.7	74.8	79.7	82.5	76.8	70.3	65.9	61.5	58.6	56.6	54.6
82.5°	46.3	52.5	57.0	59.2	56.2	52.3	47.8	45.3	43.1	41.4	40.7
85°	23.4	26.3	29.2	29.9	29.2	27.5	25.0	25.0	23.8	23.4	23.4
87.5°	8.6	10.4	10.8	12.2	11.9	12.2	12.4	12.4	12.4	12.3	12.1
90°	2.9	5.0	7.1	9.1	10.9	12.4	13.9	15.4	16.9	17.7	18.7
92.5°	16.8	16.6	16.5	16.2	16.6	17.3	18.1	18.8	19.6	20.0	20.5
95°	48.6	42.4	36.2	30.0	27.6	28.9	30.3	31.5	32.9	33.7	34.7
97.5°	91.3	73.8	56.4	39.1	31.8	34.9	37.9	41.0	44.0	44.7	45.5
100°	123.4	97.8	72.2	46.5	35.3	38.4	41.7	44.8	48.0	49.5	51.0
102.5°	188.1	182.7	177.2	171.8	155.8	129.2	102.6	76.0	49.4	51.3	53.2
105°	261.7	267.2	272.8	278.5	255.7	204.6	153.5	102.4	51.3	53.4	55.5
107.5°	331.8	336.3	340.8	345.4	317.0	255.7	194.5	133.2	71.9	69.8	67.7
110°	377.0	381.0	384.8	388.8	363.7	309.6	255.6	201.5	147.3	128.7	110.0



TEST NUMBER: P331366-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	419.7	423.1	426.6	430.1	425.2	411.8	398.5	385.1	371.7	303.5	235.2
115°	487.4	490.6	493.8	496.9	500.9	505.6	510.2	514.9	519.6	432.9	346.3
117.5°	548.6	552.2	555.7	559.3	562.6	565.9	569.1	572.3	575.5	554.5	533.6
120°	592.3	595.1	597.9	600.7	603.8	607.2	610.5	613.9	617.3	619.5	621.8
122.5°	630.2	633.1	636.1	639.1	642.4	646.0	649.7	653.4	657.0	658.4	659.7
125°	687.1	689.5	692.0	694.3	697.4	700.9	704.5	708.1	711.6	712.9	714.2
127.5°	739.4	742.1	744.8	747.5	750.1	752.8	755.4	758.1	760.8	762.7	764.6
130°	772.7	775.7	778.7	781.6	784.2	786.2	788.3	790.4	792.4	794.5	796.5
132.5°	806.0	808.5	811.0	813.6	815.9	817.9	820.0	822.0	824.1	825.9	827.6
135°	850.2	853.2	856.2	859.1	861.5	863.2	864.8	866.6	868.2	870.1	872.0
137.5°	893.6	895.6	897.8	899.8	901.8	903.8	905.7	907.6	909.5	911.3	913.1
140°	921.9	923.4	925.0	926.5	928.2	930.3	932.3	934.4	936.4	938.1	939.8
142.5°	946.0	947.4	948.7	950.1	952.0	954.3	956.6	959.0	961.4	962.9	964.4
145°	982.5	982.4	982.2	982.0	983.5	986.7	989.8	993.1	996.2	997.5	998.9
147.5°	1015.3	1014.5	1013.8	1013.1	1014.3	1017.5	1020.6	1023.7	1026.9	1027.9	1028.8
150°	1036.2	1034.9	1033.6	1032.3	1033.1	1036.1	1039.1	1042.1	1045.0	1046.2	1047.3
152.5°	1054.2	1052.7	1051.3	1049.9	1050.5	1053.4	1056.2	1059.1	1061.9	1063.0	1064.1
155°	1080.5	1078.8	1077.1	1075.4	1075.7	1077.9	1080.1	1082.4	1084.7	1085.8	1086.9
157.5°	1101.5	1100.0	1098.6	1097.2	1097.3	1098.8	1100.3	1101.9	1103.5	1104.8	1106.0
160°	1113.9	1112.7	1111.6	1110.5	1110.5	1111.6	1112.7	1113.9	1115.0	1116.1	1117.2
162.5°	1124.7	1123.5	1122.4	1121.3	1121.2	1122.1	1123.2	1124.1	1125.1	1126.3	1127.6
165°	1139.1	1138.0	1136.9	1135.8	1135.4	1136.0	1136.6	1137.2	1137.7	1139.0	1140.3
167.5°	1149.9	1148.7	1147.6	1146.5	1146.2	1146.8	1147.2	1147.8	1148.3	1149.6	1151.0
170°	1156.0	1154.8	1153.7	1152.6	1152.2	1152.6	1152.9	1153.3	1153.7	1155.0	1156.3
172.5°	1160.0	1158.9	1157.8	1156.7	1156.3	1156.7	1157.0	1157.4	1157.8	1159.0	1160.4
175°	1165.1	1163.7	1162.4	1161.1	1160.6	1161.0	1161.4	1161.7	1162.1	1163.5	1164.7
177.5°	1166.2	1165.1	1164.0	1163.0	1162.5	1162.7	1162.8	1163.0	1163.2	1164.2	1165.2
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8



TEST NUMBER: P331366-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1091.4	1095.9	1095.9	1096.5	1101.8	1101.1	1100.7
5°	1161.4	1168.3	1169.1	1176.4	1181.2	1179.6	1175.2
7.5°	1227.5	1240.3	1250.0	1255.4	1261.8	1265.7	1264.0
10°	1279.9	1298.5	1309.9	1317.6	1326.8	1333.7	1331.3
12.5°	1327.5	1349.6	1365.2	1378.3	1379.6	1388.4	1382.4
15°	1401.6	1425.1	1427.5	1437.3	1444.9	1444.1	1444.5
17.5°	1426.2	1433.7	1435.2	1435.4	1435.5	1432.7	1426.6
20°	1417.4	1414.6	1407.7	1402.5	1393.1	1391.9	1383.9
22.5°	1376.0	1367.0	1349.8	1338.4	1323.9	1320.1	1317.9
25°	1294.5	1274.6	1247.1	1220.8	1213.6	1199.4	1203.5
27.5°	1182.6	1151.8	1122.0	1100.6	1081.2	1060.1	1066.1
30°	1104.0	1069.2	1027.1	994.8	974.2	953.9	950.3
32.5°	1010.2	959.3	912.3	883.8	852.2	839.5	825.5
35°	848.4	798.7	752.2	712.2	689.1	671.3	655.1
37.5°	702.9	645.6	608.2	575.7	559.0	548.8	551.4
40°	612.7	562.5	535.0	510.3	495.0	487.7	489.3
42.5°	539.6	502.0	479.3	462.5	451.6	447.6	446.6
45°	456.5	435.5	416.9	407.3	402.0	397.5	394.7
47.5°	400.0	382.8	372.3	366.5	361.9	357.4	357.4
50°	366.0	354.7	347.4	341.3	337.7	334.5	337.2
52.5°	340.1	329.7	322.5	317.0	315.7	312.8	312.7
55°	301.7	293.6	288.4	283.4	281.1	279.4	277.4
57.5°	266.7	259.0	254.2	251.1	246.5	244.9	244.2
60°	241.9	235.8	230.9	226.9	224.8	221.6	221.6
62.5°	218.9	212.8	208.3	205.2	201.8	200.6	200.9
65°	185.6	180.8	176.3	173.1	172.3	169.8	170.6
67.5°	155.0	151.8	147.1	145.4	143.8	142.5	141.6
70°	134.7	131.4	129.0	126.6	125.3	125.3	125.3
72.5°	117.5	113.6	112.2	109.1	109.8	108.5	107.3
75°	91.0	88.6	87.4	86.1	84.1	84.1	84.1
77.5°	66.9	66.2	64.8	63.5	63.0	62.6	62.7
80°	51.7	51.3	50.5	50.5	49.7	49.4	48.6
82.5°	39.8	38.7	38.3	37.9	37.8	37.7	37.5
85°	22.7	21.9	21.9	22.3	21.5	21.5	21.9
87.5°	12.7	12.8	12.7	12.8	13.2	12.9	13.0
90°	19.6	20.6	21.2	21.6	22.0	22.3	22.7
92.5°	21.0	21.5	21.9	22.1	22.3	22.5	22.7
95°	35.6	36.6	37.0	36.8	36.6	36.4	36.2
97.5°	46.2	47.0	47.5	47.7	47.9	48.1	48.3
100°	52.5	54.0	54.9	55.3	55.7	56.1	56.4
102.5°	55.2	57.1	58.4	58.9	59.4	60.0	60.4
105°	57.5	59.6	61.0	61.8	62.5	63.2	64.0
107.5°	65.6	63.5	62.9	63.6	64.3	65.1	65.8
110°	91.3	72.5	63.5	64.2	65.0	65.8	66.5



TEST NUMBER: P331366-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	166.9	98.6	64.8	65.4	66.0	66.6	67.2
115°	259.7	173.0	122.9	109.5	96.0	82.5	69.1
117.5°	512.6	491.7	459.1	414.8	370.5	326.2	281.9
120°	624.0	626.3	614.7	589.5	564.2	538.9	513.7
122.5°	661.1	662.4	660.6	655.8	650.9	645.9	641.0
125°	715.5	716.8	717.8	718.4	718.9	719.5	720.0
127.5°	766.5	768.4	769.4	769.5	769.7	769.8	769.8
130°	798.6	800.7	801.6	801.5	801.2	801.1	800.9
132.5°	829.4	831.2	831.9	831.7	831.6	831.4	831.2
135°	873.9	875.7	876.5	876.1	875.7	875.4	875.0
137.5°	915.0	916.8	917.4	916.8	916.2	915.5	914.9
140°	941.5	943.2	943.6	942.6	941.7	940.7	939.8
142.5°	966.0	967.5	967.8	966.9	965.9	965.0	964.1
145°	1000.1	1001.5	1001.6	1000.8	999.8	998.9	997.9
147.5°	1029.8	1030.8	1030.9	1030.1	1029.3	1028.5	1027.7
150°	1048.5	1049.6	1049.6	1048.7	1047.8	1046.9	1045.9
152.5°	1065.3	1066.4	1066.4	1065.1	1063.9	1062.6	1061.4
155°	1088.1	1089.2	1088.9	1087.4	1086.0	1084.5	1083.0
157.5°	1107.3	1108.6	1108.5	1107.1	1105.6	1104.1	1102.6
160°	1118.3	1119.4	1119.4	1118.1	1116.7	1115.5	1114.1
162.5°	1128.9	1130.2	1130.0	1128.4	1126.8	1125.1	1123.6
165°	1141.6	1143.0	1143.0	1141.6	1140.3	1139.0	1137.7
167.5°	1152.2	1153.6	1153.3	1151.7	1150.0	1148.3	1146.6
170°	1157.6	1159.0	1158.7	1157.1	1155.4	1153.7	1152.0
172.5°	1161.7	1163.0	1162.8	1161.1	1159.4	1157.8	1156.0
175°	1166.1	1167.4	1167.1	1165.2	1163.3	1161.5	1159.6
177.5°	1166.3	1167.4	1167.2	1165.9	1164.5	1163.2	1161.8
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8

(END OF REPORT)