

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331369-927

Luminaire Tested: **S122DIP-S675D1080U927-4F0-1E-UDD-D**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331369-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S675D1080U927-4F0-1E-UDD-D
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5542.3 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: Semi-Indirect


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331369-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-D

Luminous Intensity Polar Plot





TEST NUMBER: P331369-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42
1	93	89	84	81	84	80	76	73	64	61	59	49	47	46	35	34	33
2	84	77	70	65	76	69	64	59	55	51	48	42	40	37	30	29	27
3	77	67	60	54	69	61	54	49	48	44	40	37	34	31	26	24	23
4	70	59	51	45	63	53	46	41	43	38	34	33	29	26	23	21	19
5	64	52	44	38	57	47	40	35	38	33	29	29	25	22	21	18	16
6	59	47	39	33	53	42	35	30	34	29	25	26	22	19	19	16	14
7	54	42	34	28	49	38	31	26	31	25	22	24	20	17	17	15	13
8	50	38	30	25	45	34	28	23	28	23	19	22	18	15	16	13	11
9	47	35	27	22	42	31	25	20	25	20	17	20	16	13	15	12	10
10	43	32	24	20	39	29	22	18	23	18	15	18	15	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9009	9009	9009
5°	9053	8672	8638
10°	8996	8417	8321
15°	8873	8146	7988
20°	8716	7854	7665
25°	8561	7573	7372
30°	8343	7286	7079
35°	8122	7007	6870
40°	7890	6771	6665
45°	7670	6558	6488
50°	7431	6366	6313
55°	7184	6161	6135
60°	6882	5948	5948
65°	6564	5697	5724
70°	6211	5427	5485
75°	5759	5163	5263
80°	5048	4895	5040
85°	4369	4658	4864



TEST NUMBER: P331369-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.9	1.0
10°-20°	151.6	2.7
20°-30°	229.8	4.1
30°-40°	279.8	5.0
40°-50°	301.1	5.4
50°-60°	292.4	5.3
60°-70°	255.3	4.6
70°-80°	196.5	3.5
80°-90°	134.8	2.4
90°-100°	129.7	2.3
100°-110°	208.7	3.8
110°-120°	424.4	7.7
120°-130°	652.6	11.8
130°-140°	678.3	12.2
140°-150°	622.7	11.2
150°-160°	499.2	9.0
160°-170°	321.7	5.8
170°-180°	110.7	2.0
0°-30°	434.3	7.8
0°-40°	714.1	12.9
0°-60°	1307.5	23.6
0°-90°	1894.1	34.2
90°-120°	762.8	13.8
90°-150°	2716.5	49.0
90°-180°	3648.0	65.8
0°-180°	5542.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	558	558	558	558	558	
5°	560	557	552	557	556	53
15°	534	535	535	542	542	150
25°	485	491	498	507	510	223
35°	418	432	447	464	471	261
45°	343	365	393	417	426	265
55°	263	293	334	362	374	235
65°	180	220	267	299	310	178
75°	100	145	196	230	242	105
85°	29	79	131	164	176	31
90°	9	65	124	159	172	8
95°	61	74	126	159	170	72
105°	260	296	121	157	171	278
115°	487	513	568	220	151	480
125°	686	699	739	766	777	612
135°	848	862	877	901	907	655
145°	983	983	996	1006	1007	615
155°	1082	1076	1085	1089	1083	498
165°	1140	1136	1138	1143	1138	322
175°	1166	1161	1162	1167	1160	111
180°	1164	1164	1164	1164	1164	



TEST NUMBER: P331369-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-D

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	558.0	558.0	558.0	558.0	558.0	558.0	558.0	558.0	558.0	558.0	558.0
2.5°	561.3	560.8	560.4	559.9	559.5	558.8	557.8	556.7	555.8	554.8	555.5
5°	559.6	559.0	558.6	558.0	557.5	556.7	555.6	554.5	553.4	552.3	553.4
7.5°	554.6	554.2	553.9	553.5	553.2	552.5	551.8	550.9	550.1	549.3	550.6
10°	550.7	550.3	550.0	549.6	549.3	548.8	548.3	547.8	547.2	546.7	548.1
12.5°	544.2	544.3	544.4	544.5	544.5	544.4	544.0	543.6	543.2	542.8	544.2
15°	533.8	534.1	534.5	534.8	535.2	535.4	535.4	535.4	535.4	535.4	536.9
17.5°	520.1	520.9	521.7	522.4	523.2	523.9	524.4	525.0	525.5	526.2	527.8
20°	511.1	512.0	512.9	513.8	514.7	515.5	516.2	517.0	517.7	518.4	520.4
22.5°	501.4	502.4	503.5	504.5	505.6	506.6	507.6	508.6	509.6	510.6	512.6
25°	485.2	486.5	487.7	489.0	490.3	491.7	493.3	495.0	496.5	498.1	500.3
27.5°	465.8	467.9	469.9	472.0	474.0	476.0	477.9	479.8	481.7	483.6	486.3
30°	452.9	455.2	457.6	459.9	462.2	464.5	466.9	469.2	471.6	473.9	476.7
32.5°	438.6	441.2	443.9	446.5	449.2	451.9	454.6	457.3	460.1	462.9	466.2
35°	418.1	421.1	424.2	427.2	430.3	433.6	437.0	440.4	443.8	447.2	451.1
37.5°	395.8	399.3	402.8	406.3	409.9	413.8	418.3	422.7	427.1	431.5	435.9
40°	380.9	384.8	388.8	392.8	396.7	401.1	406.0	410.8	415.7	420.5	425.2
42.5°	366.7	370.6	374.5	378.5	382.5	387.2	392.8	398.4	403.9	409.6	414.6
45°	342.9	347.8	352.6	357.4	362.3	367.9	374.1	380.5	386.7	393.0	398.6
47.5°	319.4	324.7	330.0	335.3	340.6	346.9	354.3	361.6	369.0	376.4	382.2
50°	303.2	308.9	314.4	320.0	325.5	332.4	340.5	348.6	356.6	364.7	370.8
52.5°	287.7	293.6	299.4	305.3	311.2	318.4	326.9	335.4	343.9	352.4	358.7
55°	262.8	269.3	275.8	282.3	288.7	296.6	305.9	315.3	324.6	334.0	340.5
57.5°	238.2	245.6	252.9	260.2	267.4	275.8	285.3	294.9	304.4	313.9	320.9
60°	220.8	228.5	236.2	244.0	251.7	260.7	270.9	281.1	291.4	301.7	308.5
62.5°	205.3	213.3	221.3	229.3	237.3	246.4	256.7	266.9	277.2	287.4	294.7
65°	179.5	188.3	197.2	206.0	214.8	224.4	235.0	245.7	256.3	266.9	274.3
67.5°	155.9	165.1	174.4	183.5	192.7	202.7	213.6	224.4	235.3	246.1	253.6
70°	139.1	148.5	157.8	167.2	176.5	186.7	197.9	209.0	220.1	231.3	239.0
72.5°	123.6	133.2	142.8	152.5	162.1	172.5	183.9	195.1	206.4	217.7	225.3
75°	99.5	109.6	119.6	129.7	139.7	150.5	162.0	173.5	185.0	196.5	204.2
77.5°	76.2	86.7	97.3	107.7	118.3	129.4	141.1	152.8	164.5	176.1	183.9
80°	60.7	71.6	82.5	93.6	104.5	115.8	127.5	139.2	150.8	162.6	170.1
82.5°	47.7	58.5	69.3	80.2	91.0	102.3	114.2	126.0	137.8	149.6	157.2
85°	29.2	40.2	51.4	62.5	73.7	85.0	96.5	108.0	119.5	131.0	138.6
87.5°	16.0	27.2	38.3	49.4	60.5	72.0	83.7	95.5	107.3	119.1	126.7
90°	9.0	21.4	33.9	46.3	58.9	71.6	84.6	97.6	110.6	123.6	131.7
92.5°	24.5	34.0	43.5	53.0	62.5	73.2	85.0	96.8	108.6	120.5	128.0
95°	61.2	63.5	65.8	68.0	70.3	77.5	89.6	101.6	113.8	125.9	133.6
97.5°	114.3	104.4	94.5	84.6	74.7	76.4	89.8	103.2	116.6	130.0	137.4
100°	154.7	135.7	116.8	97.8	78.7	75.9	89.1	102.3	115.7	128.9	137.0
102.5°	198.5	199.2	199.9	200.5	201.1	193.1	176.2	159.4	142.5	125.7	134.1
105°	260.1	270.8	281.7	292.6	303.3	287.9	246.1	204.4	162.6	120.9	129.3
107.5°	331.1	339.8	348.6	357.2	365.9	344.1	291.8	239.5	187.2	134.8	138.8
110°	376.3	383.8	391.3	398.9	406.4	387.5	342.2	297.0	251.7	206.4	193.5



TEST NUMBER: P331369-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	419.4	425.9	432.4	438.9	445.4	446.2	441.2	436.2	431.2	426.2	363.7
115°	487.4	492.6	497.8	503.0	508.1	517.1	529.8	542.6	555.3	568.1	486.9
117.5°	547.5	552.3	557.1	562.0	566.9	574.6	585.3	596.0	606.7	617.4	601.7
120°	591.9	595.4	599.0	602.5	606.0	613.1	623.6	634.1	644.8	655.3	662.6
122.5°	629.6	632.9	636.1	639.4	642.6	649.4	659.9	670.3	680.7	691.2	697.4
125°	686.3	688.7	691.1	693.6	696.0	701.9	711.1	720.5	729.8	739.1	745.3
127.5°	738.3	740.8	743.3	745.8	748.4	753.3	760.6	767.9	775.2	782.4	788.8
130°	771.3	774.1	777.0	779.7	782.6	786.9	792.7	798.6	804.4	810.2	816.6
132.5°	805.0	807.4	809.8	812.1	814.4	818.2	823.1	828.1	833.1	838.0	843.9
135°	848.0	851.0	854.0	857.0	860.0	863.2	866.6	870.1	873.6	877.1	882.8
137.5°	892.3	894.4	896.4	898.5	900.6	902.9	905.6	908.3	911.0	913.7	918.9
140°	921.2	922.6	923.9	925.2	926.5	928.4	930.8	933.2	935.6	938.0	942.6
142.5°	945.5	946.7	947.8	949.0	950.1	952.0	954.4	956.8	959.3	961.7	965.5
145°	982.8	982.5	982.4	982.2	982.0	983.5	986.7	989.8	993.1	996.2	998.6
147.5°	1016.0	1015.3	1014.5	1013.8	1013.1	1014.3	1017.5	1020.6	1023.7	1026.9	1028.0
150°	1037.5	1036.2	1034.9	1033.6	1032.3	1033.1	1036.1	1039.1	1042.1	1045.0	1046.2
152.5°	1055.7	1054.2	1052.7	1051.3	1049.9	1050.5	1053.4	1056.2	1059.1	1061.9	1063.0
155°	1082.1	1080.5	1078.8	1077.1	1075.4	1075.7	1077.9	1080.1	1082.4	1084.7	1085.8
157.5°	1102.9	1101.5	1100.0	1098.6	1097.2	1097.3	1098.8	1100.3	1101.9	1103.5	1104.8
160°	1115.0	1113.9	1112.7	1111.6	1110.5	1110.5	1111.6	1112.7	1113.9	1115.0	1116.1
162.5°	1125.8	1124.7	1123.5	1122.4	1121.3	1121.2	1122.1	1123.2	1124.1	1125.1	1126.3
165°	1140.3	1139.1	1138.0	1136.9	1135.8	1135.4	1136.0	1136.6	1137.2	1137.7	1139.0
167.5°	1151.0	1149.9	1148.7	1147.6	1146.5	1146.2	1146.8	1147.2	1147.8	1148.3	1149.6
170°	1157.1	1156.0	1154.8	1153.7	1152.6	1152.2	1152.6	1152.9	1153.3	1153.7	1155.0
172.5°	1161.1	1160.0	1158.9	1157.8	1156.7	1156.3	1156.7	1157.0	1157.4	1157.8	1159.0
175°	1166.3	1165.1	1163.7	1162.4	1161.1	1160.6	1161.0	1161.4	1161.7	1162.1	1163.5
177.5°	1167.2	1166.2	1165.1	1164.0	1163.0	1162.5	1162.7	1162.8	1163.0	1163.2	1164.2
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8



TEST NUMBER: P331369-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	558.0	558.0	558.0	558.0	558.0	558.0	558.0	558.0
2.5°	556.2	556.9	557.6	557.9	557.5	557.3	557.0	556.7
5°	554.5	555.6	556.7	557.1	556.9	556.7	556.6	556.3
7.5°	551.8	553.2	554.4	555.0	554.8	554.6	554.4	554.3
10°	549.5	551.0	552.5	553.0	552.9	552.7	552.5	552.3
12.5°	545.7	547.1	548.6	549.1	549.0	548.8	548.7	548.4
15°	538.6	540.2	541.9	542.6	542.4	542.2	542.0	541.9
17.5°	529.5	531.2	532.9	533.8	533.8	533.8	533.8	533.8
20°	522.4	524.3	526.2	527.3	527.3	527.3	527.3	527.3
22.5°	514.6	516.6	518.5	519.7	519.9	520.2	520.5	520.8
25°	502.5	504.6	506.8	508.1	508.7	509.2	509.8	510.3
27.5°	489.1	491.8	494.6	496.1	496.5	496.9	497.3	497.6
30°	479.7	482.5	485.4	487.1	487.7	488.2	488.7	489.3
32.5°	469.5	472.9	476.1	478.2	479.3	480.2	481.2	482.1
35°	455.1	459.1	463.0	465.6	466.9	468.2	469.4	470.6
37.5°	440.3	444.7	449.1	451.9	453.3	454.6	455.9	457.2
40°	429.8	434.5	439.2	442.4	443.9	445.6	447.2	448.9
42.5°	419.7	424.8	429.9	433.3	434.9	436.6	438.2	439.7
45°	404.2	409.7	415.3	419.0	420.8	422.6	424.4	426.2
47.5°	388.0	393.9	399.7	403.5	405.5	407.5	409.5	411.5
50°	376.9	383.0	389.2	393.2	395.2	397.2	399.1	401.1
52.5°	365.0	371.2	377.5	381.7	383.7	385.9	388.0	390.1
55°	346.9	353.4	359.9	364.2	366.6	368.9	371.3	373.6
57.5°	327.9	334.9	341.8	346.5	348.9	351.3	353.6	356.0
60°	315.3	322.1	329.0	333.7	336.1	338.7	341.2	343.7
62.5°	301.9	309.2	316.5	321.3	323.6	326.0	328.4	330.7
65°	281.6	289.0	296.4	301.2	303.6	305.9	308.2	310.5
67.5°	261.0	268.5	275.9	280.9	283.3	285.7	288.2	290.7
70°	246.8	254.4	262.2	267.1	269.3	271.5	273.6	275.8
72.5°	232.9	240.4	248.0	253.1	255.7	258.3	260.9	263.5
75°	212.0	219.7	227.4	232.4	234.8	237.1	239.5	241.8
77.5°	191.5	199.2	206.9	212.0	214.5	217.1	219.5	222.0
80°	177.6	185.2	192.7	197.8	200.3	202.8	205.3	207.9
82.5°	164.7	172.2	179.8	184.7	187.1	189.5	191.9	194.2
85°	146.1	153.7	161.2	166.2	168.7	171.3	173.8	176.3
87.5°	134.2	141.7	149.2	154.2	156.5	158.9	161.3	163.7
90°	139.8	148.0	156.1	161.4	164.0	166.4	169.0	171.5
92.5°	135.5	143.1	150.6	155.5	158.0	160.3	162.7	165.1
95°	141.4	149.2	156.9	161.8	163.7	165.7	167.7	169.7
97.5°	144.8	152.2	159.6	164.5	166.8	169.1	171.5	173.9
100°	145.1	153.3	161.4	166.7	169.1	171.4	173.7	176.1
102.5°	142.6	151.1	159.5	165.0	167.5	170.0	172.5	175.0
105°	137.6	146.0	154.3	159.9	162.6	165.3	168.0	170.7
107.5°	142.8	146.6	150.6	153.9	156.7	159.4	162.1	164.9
110°	180.5	167.5	154.6	149.4	152.2	154.9	157.6	160.3



TEST NUMBER: P331369-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	301.2	238.7	176.2	146.2	148.8	151.3	153.9	156.5
115°	405.6	324.3	243.1	196.7	185.2	173.7	162.2	150.8
117.5°	586.1	570.5	554.8	525.8	483.4	440.9	398.5	356.0
120°	669.9	677.2	684.4	676.4	653.1	629.8	606.5	583.3
122.5°	703.6	709.9	716.1	717.6	714.4	711.1	708.0	704.7
125°	751.4	757.6	763.7	767.9	770.1	772.3	774.4	776.7
127.5°	795.2	801.5	807.9	811.9	813.7	815.3	817.1	818.7
130°	823.0	829.3	835.8	839.6	840.7	842.0	843.3	844.5
132.5°	849.9	855.8	861.7	865.3	866.6	867.8	869.1	870.3
135°	888.4	894.1	899.7	903.1	904.1	905.2	906.3	907.3
137.5°	924.0	929.2	934.3	937.2	937.7	938.3	938.9	939.4
140°	947.2	951.7	956.3	958.6	958.8	958.9	959.1	959.3
142.5°	969.4	973.2	977.0	979.0	979.0	979.0	979.0	979.0
145°	1001.0	1003.4	1005.8	1006.9	1006.9	1006.9	1006.9	1006.8
147.5°	1029.1	1030.2	1031.3	1031.7	1031.3	1031.0	1030.7	1030.3
150°	1047.3	1048.5	1049.6	1049.6	1048.7	1047.8	1046.9	1045.9
152.5°	1064.1	1065.3	1066.4	1066.4	1065.1	1063.9	1062.6	1061.4
155°	1086.9	1088.1	1089.2	1088.9	1087.4	1086.0	1084.5	1083.0
157.5°	1106.0	1107.3	1108.6	1108.5	1107.1	1105.6	1104.1	1102.6
160°	1117.2	1118.3	1119.4	1119.4	1118.1	1116.7	1115.5	1114.1
162.5°	1127.6	1128.9	1130.2	1130.0	1128.4	1126.8	1125.1	1123.6
165°	1140.3	1141.6	1143.0	1143.0	1141.6	1140.3	1139.0	1137.7
167.5°	1151.0	1152.2	1153.6	1153.3	1151.7	1150.0	1148.3	1146.6
170°	1156.3	1157.6	1159.0	1158.7	1157.1	1155.4	1153.7	1152.0
172.5°	1160.4	1161.7	1163.0	1162.8	1161.1	1159.4	1157.8	1156.0
175°	1164.7	1166.1	1167.4	1167.1	1165.2	1163.3	1161.5	1159.6
177.5°	1165.2	1166.3	1167.4	1167.2	1165.9	1164.5	1163.2	1161.8
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8

(END OF REPORT)