

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331414-927

Luminaire Tested: **S122DIP-S865D1080U927-4F0-1E-UDD-D**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331414-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S865D1080U927-4F0-1E-UDD-D  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6180.6 lumens  
Efficiency: N/A  
Efficacy: 94.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42  
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')  
CIE Type: Semi-Indirect


Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331414-927

CATALOG NUMBER: S122DIP-S865D1080U927-4F0-1E-UDD-D

### Luminous Intensity Polar Plot





TEST NUMBER: P331414-927

CATALOG NUMBER: S122DIP-S865D1080U927-4F0-1E-UDD-D

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	94	90	85	81	85	81	78	74	66	64	61	52	50	49	39	38	37	31
2	85	77	71	65	77	70	65	60	57	53	50	45	42	40	34	32	30	25
3	78	68	60	54	70	62	55	50	50	45	41	40	36	33	30	27	25	21
4	71	60	51	45	64	54	47	42	44	39	35	35	31	28	26	24	21	17
5	65	53	45	38	58	48	41	35	39	34	30	31	27	24	24	21	18	15
6	59	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16	13
7	55	42	34	29	50	39	32	27	32	26	22	25	21	18	19	16	14	11
8	51	38	31	25	46	35	28	23	29	24	20	23	19	16	18	15	13	10
9	47	35	27	22	43	32	25	21	26	21	18	21	17	14	16	13	11	9
10	44	32	25	20	40	29	23	18	24	19	16	20	16	13	15	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11711	11711	11711
5°	11768	11274	11230
10°	11694	10940	10818
15°	11533	10587	10382
20°	11328	10209	9963
25°	11128	9845	9582
30°	10845	9471	9201
35°	10557	9109	8932
40°	10256	8801	8662
45°	9969	8526	8433
50°	9662	8276	8207
55°	9341	8008	7975
60°	8945	7730	7732
65°	8536	7405	7441
70°	8073	7053	7130
75°	7484	6710	6841
80°	6553	6361	6548
85°	5671	6056	6323



TEST NUMBER: P331414-927

CATALOG NUMBER: S122DIP-S865D1080U927-4F0-1E-UDD-D

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.7	1.1
10°-20°	197.1	3.2
20°-30°	298.7	4.8
30°-40°	363.8	5.9
40°-50°	391.3	6.3
50°-60°	380.0	6.1
60°-70°	331.8	5.4
70°-80°	255.5	4.1
80°-90°	174.3	2.8
90°-100°	156.9	2.5
100°-110°	228.6	3.7
110°-120°	437.5	7.1
120°-130°	660.0	10.7
130°-140°	681.4	11.0
140°-150°	623.3	10.1
150°-160°	499.2	8.1
160°-170°	321.7	5.2
170°-180°	110.7	1.8
0°-30°	564.5	9.1
0°-40°	928.2	15.0
0°-60°	1699.6	27.5
0°-90°	2461.2	39.8
90°-120°	823.1	13.3
90°-150°	2787.7	45.1
90°-180°	3719.0	60.2
0°-180°	6180.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	725	725	725	725	725	
5°	727	724	718	724	723	69
15°	694	696	696	705	704	195
25°	631	638	648	660	663	290
35°	543	562	581	604	612	340
45°	446	475	511	542	554	344
55°	342	380	434	471	486	305
65°	233	286	347	388	404	232
75°	129	189	255	299	314	137
85°	38	103	170	213	229	41
90°	11	82	156	200	216	10
95°	63	87	154	196	210	74
105°	261	304	142	186	203	280
115°	488	517	583	242	175	480
125°	687	700	747	780	794	612
135°	848	862	880	909	917	655
145°	983	983	996	1008	1010	615
155°	1082	1076	1085	1089	1083	498
165°	1140	1136	1138	1143	1138	322
175°	1166	1161	1162	1167	1160	111
180°	1164	1164	1164	1164	1164	



TEST NUMBER: P331414-927

CATALOG NUMBER: S122DIP-S865D1080U927-4F0-1E-UDD-D

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	725.3	725.3	725.3	725.3	725.3	725.3	725.3	725.3	725.3	725.3	725.3
2.5°	729.5	729.0	728.4	727.9	727.3	726.4	725.0	723.7	722.4	721.1	722.1
5°	727.4	726.7	726.0	725.3	724.6	723.6	722.2	720.7	719.4	718.0	719.4
7.5°	720.9	720.4	719.9	719.5	719.1	718.3	717.2	716.1	715.0	714.0	715.7
10°	715.9	715.4	714.9	714.5	714.0	713.4	712.7	712.0	711.3	710.6	712.5
12.5°	707.4	707.6	707.7	707.7	707.8	707.6	707.1	706.5	706.1	705.5	707.4
15°	693.8	694.3	694.7	695.2	695.6	695.9	695.9	695.9	695.9	695.9	698.0
17.5°	676.1	677.1	678.1	679.1	680.0	680.9	681.7	682.4	683.2	683.9	686.1
20°	664.3	665.5	666.7	667.9	669.0	670.1	671.0	671.9	672.9	673.8	676.4
22.5°	651.7	653.1	654.4	655.8	657.1	658.5	659.8	661.1	662.4	663.7	666.3
25°	630.7	632.3	634.0	635.6	637.2	639.1	641.2	643.3	645.4	647.5	650.3
27.5°	605.5	608.2	610.8	613.5	616.2	618.7	621.2	623.7	626.1	628.6	632.2
30°	588.7	591.7	594.8	597.8	600.8	603.9	606.9	609.9	613.0	616.0	619.7
32.5°	570.1	573.5	576.9	580.4	583.8	587.3	590.9	594.5	598.1	601.7	606.0
35°	543.4	547.4	551.4	555.4	559.4	563.6	568.0	572.4	576.9	581.3	586.5
37.5°	514.4	519.0	523.6	528.1	532.7	537.9	543.7	549.5	555.2	560.9	566.6
40°	495.1	500.3	505.4	510.6	515.6	521.4	527.7	534.0	540.3	546.6	552.7
42.5°	476.6	481.7	486.9	492.0	497.2	503.4	510.6	517.8	525.1	532.3	538.9
45°	445.7	452.0	458.3	464.6	471.0	478.2	486.3	494.6	502.7	510.9	518.1
47.5°	415.2	422.1	429.0	435.9	442.7	450.9	460.5	470.1	479.7	489.3	496.8
50°	394.2	401.4	408.7	415.9	423.2	432.1	442.5	453.0	463.6	474.1	482.0
52.5°	374.0	381.6	389.3	396.9	404.5	413.8	424.9	435.9	447.0	458.1	466.2
55°	341.7	350.1	358.5	366.9	375.3	385.6	397.7	409.9	422.0	434.1	442.5
57.5°	309.7	319.2	328.7	338.1	347.6	358.5	370.9	383.3	395.7	408.1	417.2
60°	287.0	297.0	307.0	317.1	327.2	338.8	352.1	365.4	378.7	392.1	401.0
62.5°	266.8	277.2	287.6	298.0	308.5	320.4	333.7	347.0	360.3	373.6	383.0
65°	233.4	244.8	256.3	267.7	279.2	291.8	305.5	319.3	333.1	346.9	356.5
67.5°	202.6	214.6	226.6	238.5	250.5	263.6	277.7	291.8	305.9	320.0	329.6
70°	180.8	193.0	205.1	217.2	229.4	242.7	257.2	271.6	286.1	300.6	310.7
72.5°	160.7	173.2	185.7	198.2	210.7	224.3	239.0	253.7	268.3	283.0	292.9
75°	129.3	142.4	155.4	168.6	181.6	195.7	210.6	225.5	240.5	255.4	265.5
77.5°	99.0	112.7	126.4	140.1	153.8	168.2	183.4	198.6	213.7	228.9	238.9
80°	78.8	93.1	107.3	121.6	135.9	150.5	165.7	180.9	196.1	211.3	221.1
82.5°	62.0	76.0	90.2	104.2	118.3	133.0	148.4	163.7	179.1	194.5	204.3
85°	37.9	52.4	66.8	81.3	95.8	110.5	125.4	140.4	155.3	170.3	180.1
87.5°	20.8	35.1	49.4	63.8	78.1	92.9	108.1	123.4	138.6	153.9	163.6
90°	11.3	26.9	42.5	58.1	73.8	89.8	106.2	122.7	139.2	155.6	165.9
92.5°	26.7	39.1	51.6	63.9	76.4	90.2	105.3	120.4	135.6	150.8	160.3
95°	63.1	68.0	72.7	77.6	82.4	92.4	107.7	123.1	138.4	153.8	163.5
97.5°	116.0	108.4	100.7	93.1	85.4	89.8	106.3	122.9	139.3	155.8	165.2
100°	156.4	139.4	122.4	105.4	88.4	88.1	104.3	120.6	136.9	153.1	163.3
102.5°	200.0	202.5	204.9	207.5	209.9	204.2	190.3	176.4	162.5	148.6	159.0
105°	261.3	273.6	286.1	298.4	310.9	297.5	258.6	219.7	180.7	141.8	152.0
107.5°	332.3	342.2	352.2	362.1	372.1	352.3	302.6	252.9	203.4	153.7	159.5
110°	377.2	385.9	394.5	403.1	411.7	394.7	352.0	309.3	266.7	224.1	212.9



TEST NUMBER: P331414-927

CATALOG NUMBER: S122DIP-S865D1080U927-4F0-1E-UDD-D

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	420.4	427.8	435.2	442.6	450.0	452.5	450.0	447.5	445.0	442.6	381.8
115°	488.5	494.2	499.9	505.6	511.4	521.9	537.1	552.3	567.4	582.7	503.0
117.5°	548.2	553.4	558.6	563.9	569.1	578.2	591.1	604.1	617.0	629.9	615.9
120°	592.6	596.4	600.2	603.9	607.6	615.8	628.5	641.3	653.9	666.7	675.5
122.5°	630.3	633.7	637.0	640.3	643.7	651.6	664.0	676.4	689.0	701.4	709.1
125°	686.7	689.2	691.7	694.0	696.5	703.2	714.2	725.2	736.3	747.3	754.9
127.5°	738.8	741.2	743.7	746.2	748.6	754.2	762.9	771.6	780.3	788.9	796.6
130°	771.8	774.6	777.3	780.1	782.8	787.7	794.6	801.6	808.6	815.6	823.2
132.5°	805.5	807.8	810.1	812.5	814.8	818.8	824.7	830.5	836.3	842.2	849.4
135°	848.2	851.2	854.2	857.2	860.2	863.7	867.8	871.7	875.8	879.8	886.5
137.5°	892.6	894.6	896.6	898.7	900.7	903.2	906.2	909.1	912.0	915.0	921.1
140°	921.5	922.7	924.0	925.3	926.5	928.4	931.0	933.5	936.0	938.6	944.0
142.5°	945.7	946.9	948.0	949.1	950.2	952.0	954.4	956.9	959.3	961.8	966.3
145°	982.8	982.5	982.4	982.2	982.0	983.5	986.7	989.8	993.1	996.2	998.9
147.5°	1016.0	1015.3	1014.5	1013.8	1013.1	1014.3	1017.5	1020.6	1023.7	1026.9	1028.0
150°	1037.5	1036.2	1034.9	1033.6	1032.3	1033.1	1036.1	1039.1	1042.1	1045.0	1046.2
152.5°	1055.7	1054.2	1052.7	1051.3	1049.9	1050.5	1053.4	1056.2	1059.1	1061.9	1063.0
155°	1082.1	1080.5	1078.8	1077.1	1075.4	1075.7	1077.9	1080.1	1082.4	1084.7	1085.8
157.5°	1102.9	1101.5	1100.0	1098.6	1097.2	1097.3	1098.8	1100.3	1101.9	1103.5	1104.8
160°	1115.0	1113.9	1112.7	1111.6	1110.5	1110.5	1111.6	1112.7	1113.9	1115.0	1116.1
162.5°	1125.8	1124.7	1123.5	1122.4	1121.3	1121.2	1122.1	1123.2	1124.1	1125.1	1126.3
165°	1140.3	1139.1	1138.0	1136.9	1135.8	1135.4	1136.0	1136.6	1137.2	1137.7	1139.0
167.5°	1151.0	1149.9	1148.7	1147.6	1146.5	1146.2	1146.8	1147.2	1147.8	1148.3	1149.6
170°	1157.1	1156.0	1154.8	1153.7	1152.6	1152.2	1152.6	1152.9	1153.3	1153.7	1155.0
172.5°	1161.1	1160.0	1158.9	1157.8	1156.7	1156.3	1156.7	1157.0	1157.4	1157.8	1159.0
175°	1166.3	1165.1	1163.7	1162.4	1161.1	1160.6	1161.0	1161.4	1161.7	1162.1	1163.5
177.5°	1167.2	1166.2	1165.1	1164.0	1163.0	1162.5	1162.7	1162.8	1163.0	1163.2	1164.2
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8



TEST NUMBER: P331414-927

CATALOG NUMBER: S122DIP-S865D1080U927-4F0-1E-UDD-D

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	725.3	725.3	725.3	725.3	725.3	725.3	725.3	725.3
2.5°	722.9	723.9	724.8	725.2	724.8	724.4	724.0	723.7
5°	720.7	722.2	723.6	724.1	723.9	723.7	723.4	723.2
7.5°	717.3	719.0	720.7	721.4	721.2	721.0	720.7	720.5
10°	714.3	716.2	718.1	718.9	718.7	718.4	718.2	718.0
12.5°	709.3	711.1	713.0	713.8	713.6	713.4	713.1	712.9
15°	700.1	702.2	704.3	705.2	705.0	704.7	704.5	704.3
17.5°	688.3	690.5	692.7	693.8	693.8	693.8	693.8	693.8
20°	679.0	681.5	684.0	685.4	685.4	685.4	685.4	685.4
22.5°	668.8	671.5	674.0	675.5	675.8	676.2	676.6	677.0
25°	653.2	655.9	658.8	660.5	661.2	661.9	662.6	663.3
27.5°	635.7	639.3	642.8	644.8	645.4	645.9	646.4	646.9
30°	623.4	627.2	631.0	633.2	633.8	634.5	635.3	636.0
32.5°	610.3	614.6	618.9	621.7	622.9	624.2	625.4	626.7
35°	591.6	596.8	601.9	605.2	606.9	608.6	610.1	611.8
37.5°	572.3	578.0	583.7	587.4	589.1	590.9	592.6	594.4
40°	558.7	564.8	570.9	575.0	577.1	579.2	581.3	583.4
42.5°	545.6	552.2	558.9	563.2	565.3	567.4	569.5	571.6
45°	525.4	532.6	539.9	544.6	547.0	549.3	551.7	554.0
47.5°	504.4	511.9	519.5	524.6	527.1	529.7	532.3	534.9
50°	490.0	497.9	505.9	511.1	513.7	516.3	518.8	521.4
52.5°	474.4	482.5	490.6	496.1	498.8	501.6	504.3	507.1
55°	451.0	459.4	467.8	473.5	476.5	479.6	482.6	485.6
57.5°	426.2	435.2	444.3	450.4	453.4	456.5	459.6	462.7
60°	409.9	418.7	427.6	433.6	437.0	440.2	443.5	446.8
62.5°	392.4	401.9	411.3	417.6	420.6	423.7	426.8	429.9
65°	366.1	375.7	385.2	391.5	394.5	397.6	400.6	403.6
67.5°	339.3	349.0	358.7	365.1	368.3	371.5	374.6	377.8
70°	320.8	330.7	340.8	347.2	350.1	352.8	355.7	358.5
72.5°	302.7	312.5	322.4	329.0	332.4	335.7	339.1	342.5
75°	275.5	285.6	295.6	302.1	305.2	308.2	311.2	314.3
77.5°	249.0	259.0	268.9	275.6	278.8	282.1	285.4	288.7
80°	230.9	240.7	250.6	257.1	260.3	263.6	266.9	270.1
82.5°	214.1	223.9	233.7	240.2	243.3	246.3	249.4	252.5
85°	189.9	199.7	209.5	216.1	219.4	222.6	225.9	229.2
87.5°	173.3	183.1	192.7	199.2	202.2	205.3	208.3	211.4
90°	176.2	186.4	196.7	203.4	206.6	209.8	212.9	216.2
92.5°	170.0	179.7	189.3	195.7	198.7	201.7	204.7	207.7
95°	173.3	183.2	193.0	199.2	201.8	204.5	207.1	209.7
97.5°	174.6	183.9	193.4	199.6	202.6	205.5	208.5	211.5
100°	173.4	183.5	193.7	200.2	203.2	206.1	209.1	212.0
102.5°	169.4	179.8	190.2	196.9	200.0	203.1	206.2	209.3
105°	162.2	172.5	182.7	189.5	192.8	196.1	199.5	202.7
107.5°	165.2	171.0	176.7	181.3	184.6	187.9	191.2	194.5
110°	201.6	190.4	179.2	175.2	178.5	181.8	185.1	188.5





TEST NUMBER: P331414-927

CATALOG NUMBER: S122DIP-S865D1080U927-4F0-1E-UDD-D

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	321.0	260.2	199.4	170.6	173.7	176.9	180.1	183.2
115°	423.4	343.7	264.1	218.9	207.9	197.0	186.2	175.2
117.5°	601.9	587.8	573.8	545.8	503.9	462.0	420.1	378.3
120°	684.3	693.1	701.8	694.9	672.2	649.5	626.8	604.1
122.5°	716.8	724.5	732.2	734.7	732.0	729.3	726.6	723.9
125°	762.6	770.2	777.8	782.9	785.6	788.3	790.9	793.6
127.5°	804.4	812.1	819.8	824.7	826.9	829.0	831.2	833.4
130°	830.9	838.5	846.2	850.9	852.5	854.3	856.0	857.6
132.5°	856.5	863.7	870.9	875.4	877.0	878.7	880.4	882.0
135°	893.3	900.2	906.9	911.0	912.5	914.0	915.5	917.0
137.5°	927.2	933.3	939.5	943.0	944.0	944.9	945.9	946.8
140°	949.4	954.8	960.2	963.2	963.6	964.1	964.6	965.0
142.5°	970.8	975.3	979.9	982.3	982.5	982.9	983.1	983.4
145°	1001.6	1004.3	1007.1	1008.5	1008.8	1009.0	1009.2	1009.5
147.5°	1029.2	1030.4	1031.5	1032.0	1031.7	1031.6	1031.3	1031.1
150°	1047.3	1048.5	1049.6	1049.6	1048.7	1047.8	1046.9	1045.9
152.5°	1064.1	1065.3	1066.4	1066.4	1065.1	1063.9	1062.6	1061.4
155°	1086.9	1088.1	1089.2	1088.9	1087.4	1086.0	1084.5	1083.0
157.5°	1106.0	1107.3	1108.6	1108.5	1107.1	1105.6	1104.1	1102.6
160°	1117.2	1118.3	1119.4	1119.4	1118.1	1116.7	1115.5	1114.1
162.5°	1127.6	1128.9	1130.2	1130.0	1128.4	1126.8	1125.1	1123.6
165°	1140.3	1141.6	1143.0	1143.0	1141.6	1140.3	1139.0	1137.7
167.5°	1151.0	1152.2	1153.6	1153.3	1151.7	1150.0	1148.3	1146.6
170°	1156.3	1157.6	1159.0	1158.7	1157.1	1155.4	1153.7	1152.0
172.5°	1160.4	1161.7	1163.0	1162.8	1161.1	1159.4	1157.8	1156.0
175°	1164.7	1166.1	1167.4	1167.1	1165.2	1163.3	1161.5	1159.6
177.5°	1165.2	1166.3	1167.4	1167.2	1165.9	1164.5	1163.2	1161.8
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8

(END OF REPORT)