

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331404-927

Luminaire Tested: **S122DIP-S865D925U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331404-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S865D925U927-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5882.1 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331404-927

CATALOG NUMBER: S122DIP-S865D925U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331404-927

CATALOG NUMBER: S122DIP-S865D925U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51	51	
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44	44	44	44	
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42	38	38	38	38	
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	39	37	33	33	33	33	
4	76	65	58	52	70	61	54	49	52	47	43	44	41	37	37	34	32	28	28	28	28	
5	70	58	51	45	64	55	48	42	47	42	37	40	36	33	34	31	28	25	25	25	25	
6	64	53	45	39	59	49	42	37	43	37	33	36	32	29	31	28	25	22	22	22	22	
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	20	20	20	20	
8	55	43	36	31	51	41	34	29	35	30	26	31	26	23	26	23	20	18	18	18	18	
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18	16	16	16	16	
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15	15	15	15	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	22083	22083	22083	22083
5°	24759	22227	19697	22227
10°	28370	22046	17046	22046
15°	31385	21641	15059	21641
20°	30907	21206	13728	21206
25°	27868	20630	12886	20630
30°	23029	19708	12269	19708
35°	16783	18743	11832	18743
40°	13405	17606	11590	17606
45°	11714	16287	11259	16287
50°	11012	15013	11037	15013
55°	10151	13717	10742	13717
60°	9300	12339	10285	12339
65°	8474	11106	9838	11106
70°	7695	9904	9182	9904
75°	6818	8559	8135	8559
80°	5867	7085	6546	7085
85°	5261	5261	3890	5261



TEST NUMBER: P331404-927

CATALOG NUMBER: S122DIP-S865D925U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.3	2.2
10°-20°	378.7	6.4
20°-30°	549.6	9.3
30°-40°	579.9	9.9
40°-50°	513.5	8.7
50°-60°	409.8	7.0
60°-70°	278.5	4.7
70°-80°	142.8	2.4
80°-90°	38.1	0.6
90°-100°	164.4	2.8
100°-110°	557.8	9.5
110°-120°	592.6	10.1
120°-130°	487.8	8.3
130°-140°	391.8	6.7
140°-150°	296.0	5.0
150°-160°	208.1	3.5
160°-170°	122.5	2.1
170°-180°	39.9	0.7
0°-30°	1058.5	18.0
0°-40°	1638.5	27.9
0°-60°	2561.8	43.6
0°-90°	3021.2	51.4
90°-120°	1314.8	22.4
90°-150°	2490.5	42.3
90°-180°	2861.0	48.6
0°-180°	5882.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1368	1368	1368	1368	1368	
5°	1528	1371	1215	1371	1528	153
15°	1878	1295	901	1295	1878	518
25°	1564	1158	723	1158	1564	707
35°	852	951	600	951	852	554
45°	513	713	493	713	513	403
55°	361	487	382	487	361	323
65°	222	291	258	291	222	221
75°	109	137	130	137	109	117
85°	28	28	21	28	28	32
90°	26	1	26	1	26	15
95°	90	28	90	28	90	117
105°	891	96	891	96	891	862
115°	1172	170	1172	170	1172	1148
125°	951	237	951	237	951	859
135°	788	278	788	278	788	612
145°	629	318	629	318	629	400
155°	529	361	529	361	529	247
165°	464	394	464	394	464	133
175°	418	410	418	410	418	41
180°	411	411	411	411	411	



TEST NUMBER: P331404-927

CATALOG NUMBER: S122DIP-S865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1430.8	1431.2	1432.1	1425.4	1424.5	1424.5	1418.6	1413.6	1407.7	1399.7	1400.6
5°	1527.6	1533.3	1535.4	1529.1	1519.6	1518.6	1509.7	1494.9	1481.3	1470.2	1462.4
7.5°	1643.0	1645.3	1640.1	1631.8	1624.8	1612.2	1595.5	1579.3	1556.5	1535.6	1520.0
10°	1730.4	1733.6	1724.7	1712.5	1702.6	1687.8	1663.7	1638.9	1609.0	1580.1	1557.0
12.5°	1796.9	1804.7	1793.2	1791.6	1774.5	1754.3	1725.5	1713.0	1670.9	1630.5	1605.8
15°	1877.6	1877.1	1878.2	1868.1	1855.5	1852.4	1821.9	1788.8	1729.4	1705.7	1664.8
17.5°	1854.3	1862.3	1866.0	1865.8	1865.5	1863.5	1853.8	1832.9	1803.1	1764.7	1717.4
20°	1798.8	1809.3	1810.8	1823.0	1829.8	1838.7	1842.4	1836.6	1818.2	1786.1	1745.2
22.5°	1713.0	1715.9	1720.9	1739.7	1754.5	1776.9	1788.6	1808.0	1800.9	1785.3	1751.0
25°	1564.3	1559.1	1577.5	1586.9	1621.1	1656.8	1682.6	1711.0	1736.2	1751.4	1741.5
27.5°	1385.8	1377.9	1405.5	1430.6	1458.3	1497.1	1537.2	1584.6	1624.1	1673.3	1690.3
30°	1235.2	1240.0	1266.3	1293.1	1335.1	1389.8	1435.0	1487.1	1543.3	1598.5	1636.9
32.5°	1072.9	1091.2	1107.8	1148.8	1185.9	1246.8	1313.0	1378.2	1448.3	1511.0	1570.4
35°	851.5	872.6	895.7	925.7	977.7	1038.2	1102.8	1190.6	1286.3	1372.0	1442.4
37.5°	716.8	713.4	726.7	748.3	790.4	839.2	913.7	1000.4	1113.0	1213.7	1313.0
40°	636.0	633.9	643.4	663.4	695.5	731.2	796.4	872.6	977.2	1100.2	1218.5
42.5°	580.5	581.8	587.0	601.1	623.1	652.5	701.3	766.2	862.0	977.8	1104.9
45°	513.0	516.7	522.5	529.3	541.9	566.1	593.4	639.7	715.4	812.1	937.2
47.5°	464.5	464.5	470.5	476.4	483.9	497.6	519.8	548.9	602.3	681.0	788.6
50°	438.4	434.7	438.9	443.6	451.5	461.0	475.7	503.0	538.8	602.4	692.3
52.5°	406.5	406.5	410.4	412.1	419.1	428.6	442.0	461.0	493.4	543.1	617.0
55°	360.6	363.2	365.4	368.4	374.8	381.6	392.1	404.7	430.0	467.3	522.0
57.5°	317.5	318.3	320.4	326.5	330.4	336.8	346.7	358.1	374.5	402.2	443.3
60°	288.0	288.0	292.2	294.9	300.2	306.4	314.3	325.3	340.1	362.7	395.9
62.5°	261.2	260.7	262.4	266.7	270.7	276.6	284.5	293.8	307.7	327.8	355.1
65°	221.8	220.8	223.9	225.0	229.2	235.0	241.3	251.3	262.3	277.0	301.2
67.5°	183.9	185.2	187.0	188.9	191.2	197.3	201.5	208.6	217.9	230.1	246.5
70°	163.0	163.0	163.0	164.5	167.7	170.9	175.1	180.9	189.7	200.3	215.0
72.5°	139.4	141.1	142.8	141.8	145.8	147.7	152.7	156.0	164.5	171.3	184.3
75°	109.3	109.3	109.3	111.9	113.5	115.1	118.3	121.4	125.6	134.0	140.9
77.5°	81.6	81.4	81.9	82.5	84.2	86.1	87.1	89.9	93.8	97.7	103.5
80°	63.1	64.2	64.6	65.7	65.7	66.8	67.3	71.0	73.6	76.2	79.9
82.5°	48.8	49.0	49.1	49.3	49.7	50.4	51.7	52.9	53.8	56.0	58.9
85°	28.4	27.9	27.9	28.9	28.4	28.4	29.5	30.5	30.5	31.0	32.6
87.5°	16.2	16.2	16.6	16.2	16.2	16.4	16.1	16.0	16.6	17.2	17.4
90°	26.1	26.1	26.1	26.1	26.1	25.3	23.7	25.3	26.1	26.9	26.1
92.5°	43.8	45.1	44.4	47.0	47.6	52.5	59.2	68.9	86.8	102.7	101.3
95°	90.2	89.4	91.7	98.1	108.3	125.7	158.9	207.2	271.2	309.9	274.3
97.5°	177.4	184.0	195.6	215.1	252.9	309.9	395.5	483.4	555.0	529.1	398.5
100°	283.0	297.3	320.2	354.2	419.9	515.5	623.8	721.8	738.5	624.6	430.1
102.5°	498.1	517.4	546.0	604.0	675.3	776.7	856.0	878.1	806.8	627.7	418.1
105°	891.0	902.1	936.1	985.1	1034.1	1060.3	1050.0	960.6	796.1	585.8	394.5
107.5°	1138.2	1152.9	1159.7	1162.4	1156.2	1117.9	1035.7	901.2	726.7	541.0	382.8
110°	1212.8	1213.6	1206.5	1191.4	1157.5	1092.7	991.4	849.9	683.1	519.4	380.3



TEST NUMBER: P331404-927

CATALOG NUMBER: S122DIP-S865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1211.6	1207.3	1193.8	1168.7	1121.4	1047.1	939.0	803.1	652.8	505.5	380.9
115°	1172.5	1165.4	1144.8	1108.4	1052.3	970.9	867.3	745.5	615.1	490.2	384.2
117.5°	1102.7	1096.8	1075.1	1036.6	979.5	903.0	809.1	702.2	591.4	482.8	389.9
120°	1057.9	1050.0	1027.0	989.8	934.5	862.5	778.8	680.7	578.8	478.3	393.7
122.5°	1011.1	1004.4	984.0	947.5	897.9	832.8	753.4	663.6	568.0	475.8	398.2
125°	951.1	944.8	925.0	895.0	849.1	789.8	720.3	638.8	552.6	471.2	404.8
127.5°	898.7	893.6	876.5	848.3	808.3	753.6	688.0	614.3	538.4	468.5	411.6
130°	868.9	862.5	846.8	819.9	781.2	729.0	666.5	598.5	528.9	467.2	416.7
132.5°	837.9	832.2	817.7	790.8	752.7	703.6	646.3	583.3	521.3	466.6	421.7
135°	788.2	785.1	770.9	744.7	710.7	666.5	614.3	562.1	510.7	465.6	427.7
137.5°	739.6	734.8	722.3	699.9	668.8	630.3	588.8	545.2	503.3	465.5	433.1
140°	706.0	701.3	689.4	668.8	643.6	608.8	572.4	534.5	498.9	464.9	435.6
142.5°	672.5	671.5	661.0	642.3	618.3	589.1	557.9	525.6	494.5	464.9	437.5
145°	629.3	626.9	619.1	605.6	586.6	563.7	539.2	513.1	488.6	463.3	439.6
147.5°	593.1	591.7	586.3	575.6	559.9	543.1	524.0	503.4	482.6	460.5	440.2
150°	571.6	570.8	566.1	556.6	544.7	530.5	513.9	496.5	477.5	458.6	439.6
152.5°	553.3	553.1	549.6	541.4	532.1	519.8	505.6	489.6	473.1	455.4	438.3
155°	528.9	530.5	527.4	521.8	513.1	504.4	492.6	479.9	464.9	449.9	436.4
157.5°	508.2	508.2	506.8	502.2	496.1	489.3	479.3	468.7	457.2	444.2	432.8
160°	495.0	495.0	494.2	490.2	484.7	479.1	470.4	461.7	451.5	440.4	430.9
162.5°	482.3	482.9	482.1	479.4	473.9	469.6	462.2	454.8	446.4	437.2	429.0
165°	464.1	464.9	464.9	461.7	458.6	455.4	449.9	444.3	438.0	430.9	425.3
167.5°	447.3	448.3	448.5	446.7	445.3	442.4	438.6	434.4	429.8	425.3	421.7
170°	437.2	438.8	439.6	437.2	436.4	434.8	431.7	429.3	425.3	422.2	419.9
172.5°	429.0	429.9	430.7	429.6	428.8	427.9	425.3	423.6	421.0	418.4	417.3
175°	418.3	419.9	420.6	419.9	419.9	419.1	418.3	417.5	415.1	414.3	413.5
177.5°	411.8	413.0	413.7	413.7	413.7	413.7	413.0	413.0	411.8	411.1	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331404-927

CATALOG NUMBER: S122DIP-S865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1403.5	1400.1	1398.0	1390.4	1383.7	1377.0	1374.9	1375.7	1366.5	1357.6	1353.8
5°	1458.2	1447.6	1437.7	1423.5	1406.7	1388.2	1378.8	1371.4	1353.0	1333.1	1321.5
7.5°	1507.1	1492.1	1472.9	1446.2	1421.7	1392.7	1374.4	1358.0	1331.2	1303.0	1285.7
10°	1537.0	1516.5	1491.8	1459.2	1429.3	1394.0	1369.3	1344.7	1313.0	1279.5	1258.4
12.5°	1562.7	1535.0	1510.7	1468.9	1433.5	1389.4	1360.1	1325.2	1292.0	1252.1	1231.5
15°	1623.7	1572.7	1526.5	1479.2	1435.5	1374.0	1341.5	1294.7	1251.0	1201.7	1178.0
17.5°	1671.0	1613.7	1540.8	1480.7	1429.7	1361.7	1313.8	1257.7	1206.2	1149.7	1117.5
20°	1697.9	1632.1	1553.8	1482.3	1421.3	1343.5	1291.5	1234.2	1173.8	1110.2	1075.5
22.5°	1713.8	1644.7	1567.3	1476.0	1404.5	1328.8	1263.4	1200.6	1139.3	1070.6	1034.3
25°	1718.9	1655.8	1573.8	1470.8	1383.5	1297.8	1219.0	1158.0	1083.9	1019.8	966.7
27.5°	1693.8	1648.6	1569.8	1460.9	1359.2	1259.0	1171.2	1102.1	1023.9	954.3	900.9
30°	1663.2	1636.9	1560.1	1450.8	1339.9	1232.2	1135.4	1057.1	979.3	908.9	854.2
32.5°	1615.7	1610.0	1542.5	1436.5	1319.3	1198.1	1098.0	1018.8	932.6	863.4	811.3
35°	1522.3	1547.5	1504.9	1404.5	1280.5	1149.6	1041.3	950.9	861.6	795.3	746.4
37.5°	1397.2	1459.8	1448.7	1357.7	1228.1	1096.9	977.3	882.8	797.6	730.8	682.8
40°	1311.0	1390.8	1402.4	1322.0	1191.1	1056.1	929.4	835.3	752.2	691.3	642.9
42.5°	1218.5	1311.8	1343.5	1279.1	1150.7	1013.1	886.5	789.0	706.8	647.5	604.6
45°	1063.4	1186.9	1244.2	1207.4	1083.4	942.5	812.1	713.3	638.7	583.0	549.9
47.5°	918.4	1053.4	1130.4	1117.5	1008.4	868.9	740.0	645.2	572.5	528.1	498.4
50°	815.8	954.6	1047.6	1051.9	954.6	816.3	687.1	597.7	530.9	489.4	465.2
52.5°	726.7	859.1	960.6	982.9	894.5	761.7	639.5	550.6	491.8	453.6	432.0
55°	610.3	722.2	834.7	875.8	804.8	678.6	565.6	487.3	432.1	405.8	386.9
57.5°	507.4	600.7	704.6	749.9	706.2	598.2	492.2	424.2	379.4	356.4	341.9
60°	453.1	526.7	619.2	673.4	635.5	539.3	446.8	382.1	345.4	324.9	311.2
62.5°	402.7	467.9	546.1	595.6	575.0	484.3	401.4	344.3	312.5	293.3	283.4
65°	332.2	383.7	444.2	489.9	476.3	407.3	339.6	290.7	265.5	250.2	242.3
67.5°	273.5	310.8	352.7	392.8	381.8	333.0	278.5	240.4	221.7	208.5	203.7
70°	236.5	264.9	302.2	334.3	325.3	285.4	242.3	209.8	193.5	182.4	177.7
72.5°	201.2	224.6	253.0	279.2	273.2	240.0	204.1	179.4	166.9	156.8	152.9
75°	151.9	169.8	187.1	204.5	202.9	177.1	156.1	137.2	127.2	119.3	117.7
77.5°	112.2	122.2	134.0	144.3	141.4	126.7	110.2	99.3	92.0	86.7	85.9
80°	85.7	91.5	99.9	107.3	103.5	97.3	84.1	76.2	71.0	65.7	63.6
82.5°	62.1	67.9	73.0	76.9	74.1	68.2	60.1	54.7	51.7	48.0	47.2
85°	32.6	35.7	37.9	38.9	37.9	34.1	30.5	28.4	25.7	24.2	23.7
87.5°	16.9	15.8	15.0	15.4	13.8	13.5	11.2	9.4	9.4	9.7	9.2
90°	21.3	15.8	11.9	9.5	7.9	6.3	3.2	0.8	3.2	6.3	7.9
92.5°	78.9	53.8	35.9	28.4	23.1	19.6	13.9	9.7	13.9	19.6	23.1
95°	182.6	113.8	77.5	58.5	45.9	38.7	30.8	27.6	30.8	38.7	45.9
97.5°	246.1	150.2	104.5	83.0	68.4	57.8	49.4	45.1	49.4	57.8	68.4
100°	259.4	162.9	121.0	98.9	83.0	70.3	63.2	60.8	63.2	70.3	83.0
102.5°	260.0	174.3	135.5	113.4	97.0	84.3	77.2	75.4	77.2	84.3	97.0
105°	264.0	193.7	156.5	134.4	117.0	105.1	99.7	96.5	99.7	105.1	117.0
107.5°	275.0	213.7	177.6	155.3	138.1	127.1	121.8	119.2	121.8	127.1	138.1
110°	283.8	226.9	192.1	169.2	152.6	142.3	137.6	134.4	137.6	142.3	152.6



TEST NUMBER: P331404-927

CATALOG NUMBER: S122DIP-S865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	293.3	239.6	206.0	182.4	166.5	156.9	151.5	148.3	151.5	156.9	166.5
115°	307.5	259.4	225.3	204.0	188.1	178.7	174.0	170.0	174.0	178.7	188.1
117.5°	322.7	277.5	246.1	223.9	208.7	200.3	195.6	192.4	195.6	200.3	208.7
120°	332.9	290.2	259.4	237.2	221.3	214.3	209.5	206.4	209.5	214.3	221.3
122.5°	341.7	302.1	273.2	250.5	234.6	226.9	222.1	219.7	222.1	226.9	234.6
125°	355.8	320.2	291.8	269.6	253.8	244.3	239.6	237.2	239.6	244.3	253.8
127.5°	368.9	337.0	309.3	286.5	271.3	260.9	254.3	251.1	254.3	260.9	271.3
130°	377.2	347.1	319.4	297.3	281.5	270.4	262.4	259.4	262.4	270.4	281.5
132.5°	385.3	355.9	329.5	307.4	291.0	279.2	270.7	266.9	270.7	279.2	291.0
135°	396.1	368.4	343.1	321.0	302.8	291.0	281.5	278.3	281.5	291.0	302.8
137.5°	404.3	378.6	353.6	333.0	315.0	302.3	292.9	289.1	292.9	302.3	315.0
140°	408.8	384.2	360.5	340.0	322.6	309.9	300.5	297.3	300.5	309.9	322.6
142.5°	412.6	388.6	365.6	346.3	329.5	316.9	308.0	305.5	308.0	316.9	329.5
145°	417.5	395.3	374.0	356.6	340.8	328.9	321.0	317.8	321.0	328.9	340.8
147.5°	420.2	400.7	380.6	365.1	352.0	341.0	333.5	331.1	333.5	341.0	352.0
150°	421.4	403.2	385.0	370.8	358.9	348.6	342.3	340.0	342.3	348.6	358.9
152.5°	422.0	405.8	389.4	376.5	365.3	356.2	349.9	348.8	349.9	356.2	365.3
155°	422.9	409.6	396.1	384.2	375.6	366.9	362.1	361.3	362.1	366.9	375.6
157.5°	422.9	412.3	400.8	390.9	383.9	376.4	372.6	371.8	372.6	376.4	383.9
160°	422.9	413.5	404.0	395.3	389.0	382.6	379.5	378.7	379.5	382.6	389.0
162.5°	422.3	414.2	405.9	399.1	393.4	388.3	385.2	385.6	385.2	388.3	393.4
165°	420.6	415.1	408.0	403.2	399.3	394.5	392.9	393.7	392.9	394.5	399.3
167.5°	419.5	414.9	409.7	406.7	403.9	400.8	399.4	400.4	399.4	400.8	403.9
170°	418.3	414.3	410.4	408.0	406.4	404.0	403.2	404.8	403.2	404.0	406.4
172.5°	416.4	413.7	411.0	409.2	408.3	405.9	406.4	407.3	406.4	405.9	408.3
175°	414.3	412.7	411.1	410.4	410.4	408.8	409.6	410.4	409.6	408.8	410.4
177.5°	413.0	411.8	411.1	411.1	411.1	409.9	410.5	411.8	410.5	409.9	411.1
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331404-927

CATALOG NUMBER: S122DIP-S865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1349.6	1347.1	1338.3	1333.7	1326.1	1319.0	1314.3	1316.4	1318.1	1317.2	1316.1
5°	1311.0	1301.0	1285.7	1272.6	1263.1	1245.8	1238.4	1234.8	1231.6	1227.9	1224.2
7.5°	1265.0	1249.2	1227.2	1208.6	1190.9	1169.3	1157.1	1149.7	1142.2	1133.9	1126.5
10°	1232.2	1210.1	1186.9	1160.6	1139.6	1120.1	1102.8	1091.2	1080.8	1070.7	1063.4
12.5°	1197.6	1172.2	1143.6	1107.6	1084.5	1056.7	1054.0	1033.6	1017.2	1011.1	1002.4
15°	1142.8	1107.0	1070.7	1028.2	1009.8	984.5	968.8	953.0	938.8	928.8	926.2
17.5°	1080.5	1034.2	998.1	967.5	937.3	911.5	897.0	884.4	872.7	859.4	857.5
20°	1032.9	992.9	953.5	926.7	895.7	869.4	851.5	838.9	828.9	821.1	814.2
22.5°	987.9	944.2	908.1	878.8	848.2	827.0	812.9	800.7	792.3	783.6	777.2
25°	915.7	881.5	842.1	809.0	783.7	770.1	758.5	748.0	742.8	737.0	729.6
27.5°	852.5	814.5	777.7	752.0	729.8	717.7	709.6	702.3	697.4	694.0	689.8
30°	807.9	769.5	740.6	715.4	697.0	684.9	679.7	675.5	669.7	667.6	665.5
32.5°	765.0	730.5	705.8	683.9	666.3	658.5	653.6	649.8	645.3	643.2	639.0
35°	704.4	675.5	651.3	639.2	625.0	618.1	614.5	609.3	605.0	602.9	602.4
37.5°	647.3	622.2	606.3	590.7	584.7	580.5	575.5	571.9	570.6	570.3	569.8
40°	610.3	589.8	575.6	563.0	560.3	554.1	549.9	546.7	546.7	547.2	546.7
42.5°	576.6	558.3	545.7	534.8	531.7	528.0	523.8	523.6	524.4	526.2	524.4
45°	525.6	512.5	503.6	498.3	492.5	488.9	488.3	489.9	490.4	491.0	492.5
47.5°	478.8	470.0	461.9	456.1	453.6	453.0	452.3	455.1	457.6	458.6	461.0
50°	451.0	441.0	434.2	430.5	428.4	427.4	428.4	431.6	433.6	436.3	437.8
52.5°	419.9	412.8	408.1	405.3	404.4	405.0	405.3	408.8	412.3	413.1	413.9
55°	376.9	371.6	370.6	365.8	368.0	367.4	370.0	372.2	375.3	378.5	379.0
57.5°	334.0	329.8	326.9	327.4	328.0	330.3	332.6	336.2	339.6	342.9	343.3
60°	305.4	303.3	301.7	301.7	302.8	305.9	308.6	312.2	314.3	316.5	318.0
62.5°	279.3	277.3	275.7	276.5	279.2	281.1	284.2	286.1	288.3	290.3	291.1
65°	238.1	237.1	238.7	239.7	240.2	242.9	246.5	248.1	250.2	251.3	254.9
67.5°	200.2	200.3	200.2	201.6	204.7	205.3	208.8	212.5	212.9	214.9	217.3
70°	174.5	175.5	176.7	177.7	180.3	181.3	183.9	185.5	187.7	189.3	190.8
72.5°	151.0	151.1	152.3	152.0	154.2	156.5	158.8	160.3	162.4	164.5	166.0
75°	116.1	116.1	117.2	117.7	120.4	123.0	122.5	123.5	125.6	127.7	128.8
77.5°	84.8	83.7	84.8	85.4	86.2	88.4	88.8	90.3	92.7	92.0	93.2
80°	64.6	63.1	64.6	65.2	65.2	67.8	67.8	68.8	70.4	68.8	70.4
82.5°	46.2	45.4	46.6	46.7	47.5	47.6	48.5	48.6	50.2	49.5	50.2
85°	23.1	22.6	23.1	22.6	23.1	23.7	23.7	23.1	23.1	24.2	22.6
87.5°	9.0	9.1	9.5	10.6	11.1	10.9	10.3	10.1	9.8	9.3	9.4
90°	9.5	11.9	15.8	21.3	26.1	26.9	26.1	25.3	23.7	25.3	26.1
92.5°	28.4	35.9	53.8	78.9	101.3	102.7	86.8	68.9	59.2	52.5	47.6
95°	58.5	77.5	113.8	182.6	274.3	309.9	271.2	207.2	158.9	125.7	108.3
97.5°	83.0	104.5	150.2	246.1	398.5	529.1	555.0	483.4	395.5	309.9	252.9
100°	98.9	121.0	162.9	259.4	430.1	624.6	738.5	721.8	623.8	515.5	419.9
102.5°	113.4	135.5	174.3	260.0	418.1	627.7	806.8	878.1	856.0	776.7	675.3
105°	134.4	156.5	193.7	264.0	394.5	585.8	796.1	960.6	1050.0	1060.3	1034.1
107.5°	155.3	177.6	213.7	275.0	382.8	541.0	726.7	901.2	1035.7	1117.9	1156.2
110°	169.2	192.1	226.9	283.8	380.3	519.4	683.1	849.9	991.4	1092.7	1157.5



TEST NUMBER: P331404-927

CATALOG NUMBER: S122DIP-S865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	182.4	206.0	239.6	293.3	380.9	505.5	652.8	803.1	939.0	1047.1	1121.4
115°	204.0	225.3	259.4	307.5	384.2	490.2	615.1	745.5	867.3	970.9	1052.3
117.5°	223.9	246.1	277.5	322.7	389.9	482.8	591.4	702.2	809.1	903.0	979.5
120°	237.2	259.4	290.2	332.9	393.7	478.3	578.8	680.7	778.8	862.5	934.5
122.5°	250.5	273.2	302.1	341.7	398.2	475.8	568.0	663.6	753.4	832.8	897.9
125°	269.6	291.8	320.2	355.8	404.8	471.2	552.6	638.8	720.3	789.8	849.1
127.5°	286.5	309.3	337.0	368.9	411.6	468.5	538.4	614.3	688.0	753.6	808.3
130°	297.3	319.4	347.1	377.2	416.7	467.2	528.9	598.5	666.5	729.0	781.2
132.5°	307.4	329.5	355.9	385.3	421.7	466.6	521.3	583.3	646.3	703.6	752.7
135°	321.0	343.1	368.4	396.1	427.7	465.6	510.7	562.1	614.3	666.5	710.7
137.5°	333.0	353.6	378.6	404.3	433.1	465.5	503.3	545.2	588.8	630.3	668.8
140°	340.0	360.5	384.2	408.8	435.6	464.9	498.9	534.5	572.4	608.8	643.6
142.5°	346.3	365.6	388.6	412.6	437.5	464.9	494.5	525.6	557.9	589.1	618.3
145°	356.6	374.0	395.3	417.5	439.6	463.3	488.6	513.1	539.2	563.7	586.6
147.5°	365.1	380.6	400.7	420.2	440.2	460.5	482.6	503.4	524.0	543.1	559.9
150°	370.8	385.0	403.2	421.4	439.6	458.6	477.5	496.5	513.9	530.5	544.7
152.5°	376.5	389.4	405.8	422.0	438.3	455.4	473.1	489.6	505.6	519.8	532.1
155°	384.2	396.1	409.6	422.9	436.4	449.9	464.9	479.9	492.6	504.4	513.1
157.5°	390.9	400.8	412.3	422.9	432.8	444.2	457.2	468.7	479.3	489.3	496.1
160°	395.3	404.0	413.5	422.9	430.9	440.4	451.5	461.7	470.4	479.1	484.7
162.5°	399.1	405.9	414.2	422.3	429.0	437.2	446.4	454.8	462.2	469.6	473.9
165°	403.2	408.0	415.1	420.6	425.3	430.9	438.0	444.3	449.9	455.4	458.6
167.5°	406.7	409.7	414.9	419.5	421.7	425.3	429.8	434.4	438.6	442.4	445.3
170°	408.0	410.4	414.3	418.3	419.9	422.2	425.3	429.3	431.7	434.8	436.4
172.5°	409.2	411.0	413.7	416.4	417.3	418.4	421.0	423.6	425.3	427.9	428.8
175°	410.4	411.1	412.7	414.3	413.5	414.3	415.1	417.5	418.3	419.1	419.9
177.5°	411.1	411.1	411.8	413.0	411.8	411.1	411.8	413.0	413.0	413.7	413.7
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331404-927

CATALOG NUMBER: S122DIP-S865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1311.8	1311.0	1311.0	1307.2	1311.0	1311.0	1311.8	1316.1	1317.2	1318.1	1316.4
5°	1216.9	1215.3	1212.7	1215.3	1212.7	1215.3	1216.9	1224.2	1227.9	1231.6	1234.8
7.5°	1123.0	1116.7	1115.7	1109.5	1115.7	1116.7	1123.0	1126.5	1133.9	1142.2	1149.7
10°	1054.5	1050.3	1049.7	1039.7	1049.7	1050.3	1054.5	1063.4	1070.7	1080.8	1091.2
12.5°	1002.3	992.2	994.2	988.4	994.2	992.2	1002.3	1002.4	1011.1	1017.2	1033.6
15°	912.0	912.0	909.9	900.9	909.9	912.0	912.0	926.2	928.8	938.8	953.0
17.5°	847.2	846.1	841.1	843.6	841.1	846.1	847.2	857.5	859.4	872.7	884.4
20°	808.4	805.3	799.0	799.0	799.0	805.3	808.4	814.2	821.1	828.9	838.9
22.5°	771.9	771.7	764.9	767.0	764.9	771.7	771.9	777.2	783.6	792.3	800.7
25°	729.0	724.8	721.8	723.3	721.8	724.8	729.0	729.6	737.0	742.8	748.0
27.5°	688.5	686.2	686.0	681.7	686.0	686.2	688.5	689.8	694.0	697.4	702.3
30°	665.0	659.7	660.8	658.1	660.8	659.7	665.0	665.5	667.6	669.7	675.5
32.5°	638.0	636.1	635.1	632.9	635.1	636.1	638.0	639.0	643.2	645.3	649.8
35°	601.3	601.9	599.2	600.3	599.2	601.9	601.3	602.4	602.9	605.0	609.3
37.5°	569.3	570.9	569.7	570.1	569.7	570.9	569.3	569.8	570.3	570.6	571.9
40°	548.3	548.3	548.3	549.9	548.3	548.3	548.3	546.7	547.2	546.7	546.7
42.5°	528.1	527.2	526.4	526.2	526.4	527.2	528.1	524.4	526.2	524.4	523.6
45°	493.6	495.2	495.7	493.1	495.7	495.2	493.6	492.5	491.0	490.4	489.9
47.5°	462.4	462.6	462.4	464.7	462.4	462.6	462.4	461.0	458.6	457.6	455.1
50°	440.5	439.4	440.5	439.4	440.5	439.4	440.5	437.8	436.3	433.6	431.6
52.5°	417.4	417.6	416.9	416.8	416.9	417.6	417.4	413.9	413.1	412.3	408.8
55°	381.1	382.1	381.6	381.6	381.6	382.1	381.1	379.0	378.5	375.3	372.2
57.5°	343.6	344.5	345.2	342.9	345.2	344.5	343.6	343.3	342.9	339.6	336.2
60°	317.5	320.1	319.6	318.5	319.6	320.1	317.5	318.0	316.5	314.3	312.2
62.5°	293.5	294.5	294.4	294.1	294.4	294.5	293.5	291.1	290.3	288.3	286.1
65°	256.5	257.5	256.0	257.5	256.0	257.5	256.5	254.9	251.3	250.2	248.1
67.5°	216.7	217.0	218.2	218.9	218.2	217.0	216.7	217.3	214.9	212.9	212.5
70°	191.9	191.3	192.9	194.5	192.9	191.3	191.9	190.8	189.3	187.7	185.5
72.5°	165.8	166.9	166.4	167.5	166.4	166.9	165.8	166.0	164.5	162.4	160.3
75°	127.7	129.3	128.8	130.4	128.8	129.3	127.7	128.8	127.7	125.6	123.5
77.5°	92.3	92.5	92.3	93.2	92.3	92.5	92.3	93.2	92.0	92.7	90.3
80°	70.4	69.4	68.4	70.4	68.4	69.4	70.4	70.4	68.8	70.4	68.8
82.5°	49.0	49.6	48.6	48.6	48.6	49.6	49.0	50.2	49.5	50.2	48.6
85°	22.6	22.1	21.0	21.0	21.0	22.1	22.6	22.6	24.2	23.1	23.1
87.5°	9.4	9.0	9.0	8.6	9.0	9.0	9.4	9.4	9.3	9.8	10.1
90°	26.1	26.1	26.1	26.1	26.1	26.1	26.1	26.1	25.3	23.7	25.3
92.5°	47.0	44.4	45.1	43.8	45.1	44.4	47.0	47.6	52.5	59.2	68.9
95°	98.1	91.7	89.4	90.2	89.4	91.7	98.1	108.3	125.7	158.9	207.2
97.5°	215.1	195.6	184.0	177.4	184.0	195.6	215.1	252.9	309.9	395.5	483.4
100°	354.2	320.2	297.3	283.0	297.3	320.2	354.2	419.9	515.5	623.8	721.8
102.5°	604.0	546.0	517.4	498.1	517.4	546.0	604.0	675.3	776.7	856.0	878.1
105°	985.1	936.1	902.1	891.0	902.1	936.1	985.1	1034.1	1060.3	1050.0	960.6
107.5°	1162.4	1159.7	1152.9	1138.2	1152.9	1159.7	1162.4	1156.2	1117.9	1035.7	901.2
110°	1191.4	1206.5	1213.6	1212.8	1213.6	1206.5	1191.4	1157.5	1092.7	991.4	849.9



TEST NUMBER: P331404-927

CATALOG NUMBER: S122DIP-S865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1168.7	1193.8	1207.3	1211.6	1207.3	1193.8	1168.7	1121.4	1047.1	939.0	803.1
115°	1108.4	1144.8	1165.4	1172.5	1165.4	1144.8	1108.4	1052.3	970.9	867.3	745.5
117.5°	1036.6	1075.1	1096.8	1102.7	1096.8	1075.1	1036.6	979.5	903.0	809.1	702.2
120°	989.8	1027.0	1050.0	1057.9	1050.0	1027.0	989.8	934.5	862.5	778.8	680.7
122.5°	947.5	984.0	1004.4	1011.1	1004.4	984.0	947.5	897.9	832.8	753.4	663.6
125°	895.0	925.0	944.8	951.1	944.8	925.0	895.0	849.1	789.8	720.3	638.8
127.5°	848.3	876.5	893.6	898.7	893.6	876.5	848.3	808.3	753.6	688.0	614.3
130°	819.9	846.8	862.5	868.9	862.5	846.8	819.9	781.2	729.0	666.5	598.5
132.5°	790.8	817.7	832.2	837.9	832.2	817.7	790.8	752.7	703.6	646.3	583.3
135°	744.7	770.9	785.1	788.2	785.1	770.9	744.7	710.7	666.5	614.3	562.1
137.5°	699.9	722.3	734.8	739.6	734.8	722.3	699.9	668.8	630.3	588.8	545.2
140°	668.8	689.4	701.3	706.0	701.3	689.4	668.8	643.6	608.8	572.4	534.5
142.5°	642.3	661.0	671.5	672.5	671.5	661.0	642.3	618.3	589.1	557.9	525.6
145°	605.6	619.1	626.9	629.3	626.9	619.1	605.6	586.6	563.7	539.2	513.1
147.5°	575.6	586.3	591.7	593.1	591.7	586.3	575.6	559.9	543.1	524.0	503.4
150°	556.6	566.1	570.8	571.6	570.8	566.1	556.6	544.7	530.5	513.9	496.5
152.5°	541.4	549.6	553.1	553.3	553.1	549.6	541.4	532.1	519.8	505.6	489.6
155°	521.8	527.4	530.5	528.9	530.5	527.4	521.8	513.1	504.4	492.6	479.9
157.5°	502.2	506.8	508.2	508.2	508.2	506.8	502.2	496.1	489.3	479.3	468.7
160°	490.2	494.2	495.0	495.0	495.0	494.2	490.2	484.7	479.1	470.4	461.7
162.5°	479.4	482.1	482.9	482.3	482.9	482.1	479.4	473.9	469.6	462.2	454.8
165°	461.7	464.9	464.9	464.1	464.9	464.9	461.7	458.6	455.4	449.9	444.3
167.5°	446.7	448.5	448.3	447.3	448.3	448.5	446.7	445.3	442.4	438.6	434.4
170°	437.2	439.6	438.8	437.2	438.8	439.6	437.2	436.4	434.8	431.7	429.3
172.5°	429.6	430.7	429.9	429.0	429.9	430.7	429.6	428.8	427.9	425.3	423.6
175°	419.9	420.6	419.9	418.3	419.9	420.6	419.9	419.9	419.1	418.3	417.5
177.5°	413.7	413.7	413.0	411.8	413.0	413.7	413.7	413.7	413.7	413.0	413.0
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331404-927

CATALOG NUMBER: S122DIP-S865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1314.3	1319.0	1326.1	1333.7	1338.3	1347.1	1349.6	1353.8	1357.6	1366.5	1375.7
5°	1238.4	1245.8	1263.1	1272.6	1285.7	1301.0	1311.0	1321.5	1333.1	1353.0	1371.4
7.5°	1157.1	1169.3	1190.9	1208.6	1227.2	1249.2	1265.0	1285.7	1303.0	1331.2	1358.0
10°	1102.8	1120.1	1139.6	1160.6	1186.9	1210.1	1232.2	1258.4	1279.5	1313.0	1344.7
12.5°	1054.0	1056.7	1084.5	1107.6	1143.6	1172.2	1197.6	1231.5	1252.1	1292.0	1325.2
15°	968.8	984.5	1009.8	1028.2	1070.7	1107.0	1142.8	1178.0	1201.7	1251.0	1294.7
17.5°	897.0	911.5	937.3	967.5	998.1	1034.2	1080.5	1117.5	1149.7	1206.2	1257.7
20°	851.5	869.4	895.7	926.7	953.5	992.9	1032.9	1075.5	1110.2	1173.8	1234.2
22.5°	812.9	827.0	848.2	878.8	908.1	944.2	987.9	1034.3	1070.6	1139.3	1200.6
25°	758.5	770.1	783.7	809.0	842.1	881.5	915.7	966.7	1019.8	1083.9	1158.0
27.5°	709.6	717.7	729.8	752.0	777.7	814.5	852.5	900.9	954.3	1023.9	1102.1
30°	679.7	684.9	697.0	715.4	740.6	769.5	807.9	854.2	908.9	979.3	1057.1
32.5°	653.6	658.5	666.3	683.9	705.8	730.5	765.0	811.3	863.4	932.6	1018.8
35°	614.5	618.1	625.0	639.2	651.3	675.5	704.4	746.4	795.3	861.6	950.9
37.5°	575.5	580.5	584.7	590.7	606.3	622.2	647.3	682.8	730.8	797.6	882.8
40°	549.9	554.1	560.3	563.0	575.6	589.8	610.3	642.9	691.3	752.2	835.3
42.5°	523.8	528.0	531.7	534.8	545.7	558.3	576.6	604.6	647.5	706.8	789.0
45°	488.3	488.9	492.5	498.3	503.6	512.5	525.6	549.9	583.0	638.7	713.3
47.5°	452.3	453.0	453.6	456.1	461.9	470.0	478.8	498.4	528.1	572.5	645.2
50°	428.4	427.4	428.4	430.5	434.2	441.0	451.0	465.2	489.4	530.9	597.7
52.5°	405.3	405.0	404.4	405.3	408.1	412.8	419.9	432.0	453.6	491.8	550.6
55°	370.0	367.4	368.0	365.8	370.6	371.6	376.9	386.9	405.8	432.1	487.3
57.5°	332.6	330.3	328.0	327.4	326.9	329.8	334.0	341.9	356.4	379.4	424.2
60°	308.6	305.9	302.8	301.7	301.7	303.3	305.4	311.2	324.9	345.4	382.1
62.5°	284.2	281.1	279.2	276.5	275.7	277.3	279.3	283.4	293.3	312.5	344.3
65°	246.5	242.9	240.2	239.7	238.7	237.1	238.1	242.3	250.2	265.5	290.7
67.5°	208.8	205.3	204.7	201.6	200.2	200.3	200.2	203.7	208.5	221.7	240.4
70°	183.9	181.3	180.3	177.7	176.7	175.5	174.5	177.7	182.4	193.5	209.8
72.5°	158.8	156.5	154.2	152.0	152.3	151.1	151.0	152.9	156.8	166.9	179.4
75°	122.5	123.0	120.4	117.7	117.2	116.1	116.1	117.7	119.3	127.2	137.2
77.5°	88.8	88.4	86.2	85.4	84.8	83.7	84.8	85.9	86.7	92.0	99.3
80°	67.8	67.8	65.2	65.2	64.6	63.1	64.6	63.6	65.7	71.0	76.2
82.5°	48.5	47.6	47.5	46.7	46.6	45.4	46.2	47.2	48.0	51.7	54.7
85°	23.7	23.7	23.1	22.6	23.1	22.6	23.1	23.7	24.2	25.7	28.4
87.5°	10.3	10.9	11.1	10.6	9.5	9.1	9.0	9.2	9.7	9.4	9.4
90°	26.1	26.9	26.1	21.3	15.8	11.9	9.5	7.9	6.3	3.2	0.8
92.5°	86.8	102.7	101.3	78.9	53.8	35.9	28.4	23.1	19.6	13.9	9.7
95°	271.2	309.9	274.3	182.6	113.8	77.5	58.5	45.9	38.7	30.8	27.6
97.5°	555.0	529.1	398.5	246.1	150.2	104.5	83.0	68.4	57.8	49.4	45.1
100°	738.5	624.6	430.1	259.4	162.9	121.0	98.9	83.0	70.3	63.2	60.8
102.5°	806.8	627.7	418.1	260.0	174.3	135.5	113.4	97.0	84.3	77.2	75.4
105°	796.1	585.8	394.5	264.0	193.7	156.5	134.4	117.0	105.1	99.7	96.5
107.5°	726.7	541.0	382.8	275.0	213.7	177.6	155.3	138.1	127.1	121.8	119.2
110°	683.1	519.4	380.3	283.8	226.9	192.1	169.2	152.6	142.3	137.6	134.4



TEST NUMBER: P331404-927

CATALOG NUMBER: S122DIP-S865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	652.8	505.5	380.9	293.3	239.6	206.0	182.4	166.5	156.9	151.5	148.3
115°	615.1	490.2	384.2	307.5	259.4	225.3	204.0	188.1	178.7	174.0	170.0
117.5°	591.4	482.8	389.9	322.7	277.5	246.1	223.9	208.7	200.3	195.6	192.4
120°	578.8	478.3	393.7	332.9	290.2	259.4	237.2	221.3	214.3	209.5	206.4
122.5°	568.0	475.8	398.2	341.7	302.1	273.2	250.5	234.6	226.9	222.1	219.7
125°	552.6	471.2	404.8	355.8	320.2	291.8	269.6	253.8	244.3	239.6	237.2
127.5°	538.4	468.5	411.6	368.9	337.0	309.3	286.5	271.3	260.9	254.3	251.1
130°	528.9	467.2	416.7	377.2	347.1	319.4	297.3	281.5	270.4	262.4	259.4
132.5°	521.3	466.6	421.7	385.3	355.9	329.5	307.4	291.0	279.2	270.7	266.9
135°	510.7	465.6	427.7	396.1	368.4	343.1	321.0	302.8	291.0	281.5	278.3
137.5°	503.3	465.5	433.1	404.3	378.6	353.6	333.0	315.0	302.3	292.9	289.1
140°	498.9	464.9	435.6	408.8	384.2	360.5	340.0	322.6	309.9	300.5	297.3
142.5°	494.5	464.9	437.5	412.6	388.6	365.6	346.3	329.5	316.9	308.0	305.5
145°	488.6	463.3	439.6	417.5	395.3	374.0	356.6	340.8	328.9	321.0	317.8
147.5°	482.6	460.5	440.2	420.2	400.7	380.6	365.1	352.0	341.0	333.5	331.1
150°	477.5	458.6	439.6	421.4	403.2	385.0	370.8	358.9	348.6	342.3	340.0
152.5°	473.1	455.4	438.3	422.0	405.8	389.4	376.5	365.3	356.2	349.9	348.8
155°	464.9	449.9	436.4	422.9	409.6	396.1	384.2	375.6	366.9	362.1	361.3
157.5°	457.2	444.2	432.8	422.9	412.3	400.8	390.9	383.9	376.4	372.6	371.8
160°	451.5	440.4	430.9	422.9	413.5	404.0	395.3	389.0	382.6	379.5	378.7
162.5°	446.4	437.2	429.0	422.3	414.2	405.9	399.1	393.4	388.3	385.2	385.6
165°	438.0	430.9	425.3	420.6	415.1	408.0	403.2	399.3	394.5	392.9	393.7
167.5°	429.8	425.3	421.7	419.5	414.9	409.7	406.7	403.9	400.8	399.4	400.4
170°	425.3	422.2	419.9	418.3	414.3	410.4	408.0	406.4	404.0	403.2	404.8
172.5°	421.0	418.4	417.3	416.4	413.7	411.0	409.2	408.3	405.9	406.4	407.3
175°	415.1	414.3	413.5	414.3	412.7	411.1	410.4	410.4	408.8	409.6	410.4
177.5°	411.8	411.1	411.8	413.0	411.8	411.1	411.1	411.1	409.9	410.5	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331404-927

CATALOG NUMBER: S122DIP-S865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1374.9	1377.0	1383.7	1390.4	1398.0	1400.1	1403.5	1400.6	1399.7	1407.7	1413.6
5°	1378.8	1388.2	1406.7	1423.5	1437.7	1447.6	1458.2	1462.4	1470.2	1481.3	1494.9
7.5°	1374.4	1392.7	1421.7	1446.2	1472.9	1492.1	1507.1	1520.0	1535.6	1556.5	1579.3
10°	1369.3	1394.0	1429.3	1459.2	1491.8	1516.5	1537.0	1557.0	1580.1	1609.0	1638.9
12.5°	1360.1	1389.4	1433.5	1468.9	1510.7	1535.0	1562.7	1605.8	1630.5	1670.9	1713.0
15°	1341.5	1374.0	1435.5	1479.2	1526.5	1572.7	1623.7	1664.8	1705.7	1729.4	1788.8
17.5°	1313.8	1361.7	1429.7	1480.7	1540.8	1613.7	1671.0	1717.4	1764.7	1803.1	1832.9
20°	1291.5	1343.5	1421.3	1482.3	1553.8	1632.1	1697.9	1745.2	1786.1	1818.2	1836.6
22.5°	1263.4	1328.8	1404.5	1476.0	1567.3	1644.7	1713.8	1751.0	1785.3	1800.9	1808.0
25°	1219.0	1297.8	1383.5	1470.8	1573.8	1655.8	1718.9	1741.5	1751.4	1736.2	1711.0
27.5°	1171.2	1259.0	1359.2	1460.9	1569.8	1648.6	1693.8	1690.3	1673.3	1624.1	1584.6
30°	1135.4	1232.2	1339.9	1450.8	1560.1	1636.9	1663.2	1636.9	1598.5	1543.3	1487.1
32.5°	1098.0	1198.1	1319.3	1436.5	1542.5	1610.0	1615.7	1570.4	1511.0	1448.3	1378.2
35°	1041.3	1149.6	1280.5	1404.5	1504.9	1547.5	1522.3	1442.4	1372.0	1286.3	1190.6
37.5°	977.3	1096.9	1228.1	1357.7	1448.7	1459.8	1397.2	1313.0	1213.7	1113.0	1000.4
40°	929.4	1056.1	1191.1	1322.0	1402.4	1390.8	1311.0	1218.5	1100.2	977.2	872.6
42.5°	886.5	1013.1	1150.7	1279.1	1343.5	1311.8	1218.5	1104.9	977.8	862.0	766.2
45°	812.1	942.5	1083.4	1207.4	1244.2	1186.9	1063.4	937.2	812.1	715.4	639.7
47.5°	740.0	868.9	1008.4	1117.5	1130.4	1053.4	918.4	788.6	681.0	602.3	548.9
50°	687.1	816.3	954.6	1051.9	1047.6	954.6	815.8	692.3	602.4	538.8	503.0
52.5°	639.5	761.7	894.5	982.9	960.6	859.1	726.7	617.0	543.1	493.4	461.0
55°	565.6	678.6	804.8	875.8	834.7	722.2	610.3	522.0	467.3	430.0	404.7
57.5°	492.2	598.2	706.2	749.9	704.6	600.7	507.4	443.3	402.2	374.5	358.1
60°	446.8	539.3	635.5	673.4	619.2	526.7	453.1	395.9	362.7	340.1	325.3
62.5°	401.4	484.3	575.0	595.6	546.1	467.9	402.7	355.1	327.8	307.7	293.8
65°	339.6	407.3	476.3	489.9	444.2	383.7	332.2	301.2	277.0	262.3	251.3
67.5°	278.5	333.0	381.8	392.8	352.7	310.8	273.5	246.5	230.1	217.9	208.6
70°	242.3	285.4	325.3	334.3	302.2	264.9	236.5	215.0	200.3	189.7	180.9
72.5°	204.1	240.0	273.2	279.2	253.0	224.6	201.2	184.3	171.3	164.5	156.0
75°	156.1	177.1	202.9	204.5	187.1	169.8	151.9	140.9	134.0	125.6	121.4
77.5°	110.2	126.7	141.4	144.3	134.0	122.2	112.2	103.5	97.7	93.8	89.9
80°	84.1	97.3	103.5	107.3	99.9	91.5	85.7	79.9	76.2	73.6	71.0
82.5°	60.1	68.2	74.1	76.9	73.0	67.9	62.1	58.9	56.0	53.8	52.9
85°	30.5	34.1	37.9	38.9	37.9	35.7	32.6	32.6	31.0	30.5	30.5
87.5°	11.2	13.5	13.8	15.4	15.0	15.8	16.9	17.4	17.2	16.6	16.0
90°	3.2	6.3	7.9	9.5	11.9	15.8	21.3	26.1	26.9	26.1	25.3
92.5°	13.9	19.6	23.1	28.4	35.9	53.8	78.9	101.3	102.7	86.8	68.9
95°	30.8	38.7	45.9	58.5	77.5	113.8	182.6	274.3	309.9	271.2	207.2
97.5°	49.4	57.8	68.4	83.0	104.5	150.2	246.1	398.5	529.1	555.0	483.4
100°	63.2	70.3	83.0	98.9	121.0	162.9	259.4	430.1	624.6	738.5	721.8
102.5°	77.2	84.3	97.0	113.4	135.5	174.3	260.0	418.1	627.7	806.8	878.1
105°	99.7	105.1	117.0	134.4	156.5	193.7	264.0	394.5	585.8	796.1	960.6
107.5°	121.8	127.1	138.1	155.3	177.6	213.7	275.0	382.8	541.0	726.7	901.2
110°	137.6	142.3	152.6	169.2	192.1	226.9	283.8	380.3	519.4	683.1	849.9



TEST NUMBER: P331404-927

CATALOG NUMBER: S122DIP-S865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	151.5	156.9	166.5	182.4	206.0	239.6	293.3	380.9	505.5	652.8	803.1
115°	174.0	178.7	188.1	204.0	225.3	259.4	307.5	384.2	490.2	615.1	745.5
117.5°	195.6	200.3	208.7	223.9	246.1	277.5	322.7	389.9	482.8	591.4	702.2
120°	209.5	214.3	221.3	237.2	259.4	290.2	332.9	393.7	478.3	578.8	680.7
122.5°	222.1	226.9	234.6	250.5	273.2	302.1	341.7	398.2	475.8	568.0	663.6
125°	239.6	244.3	253.8	269.6	291.8	320.2	355.8	404.8	471.2	552.6	638.8
127.5°	254.3	260.9	271.3	286.5	309.3	337.0	368.9	411.6	468.5	538.4	614.3
130°	262.4	270.4	281.5	297.3	319.4	347.1	377.2	416.7	467.2	528.9	598.5
132.5°	270.7	279.2	291.0	307.4	329.5	355.9	385.3	421.7	466.6	521.3	583.3
135°	281.5	291.0	302.8	321.0	343.1	368.4	396.1	427.7	465.6	510.7	562.1
137.5°	292.9	302.3	315.0	333.0	353.6	378.6	404.3	433.1	465.5	503.3	545.2
140°	300.5	309.9	322.6	340.0	360.5	384.2	408.8	435.6	464.9	498.9	534.5
142.5°	308.0	316.9	329.5	346.3	365.6	388.6	412.6	437.5	464.9	494.5	525.6
145°	321.0	328.9	340.8	356.6	374.0	395.3	417.5	439.6	463.3	488.6	513.1
147.5°	333.5	341.0	352.0	365.1	380.6	400.7	420.2	440.2	460.5	482.6	503.4
150°	342.3	348.6	358.9	370.8	385.0	403.2	421.4	439.6	458.6	477.5	496.5
152.5°	349.9	356.2	365.3	376.5	389.4	405.8	422.0	438.3	455.4	473.1	489.6
155°	362.1	366.9	375.6	384.2	396.1	409.6	422.9	436.4	449.9	464.9	479.9
157.5°	372.6	376.4	383.9	390.9	400.8	412.3	422.9	432.8	444.2	457.2	468.7
160°	379.5	382.6	389.0	395.3	404.0	413.5	422.9	430.9	440.4	451.5	461.7
162.5°	385.2	388.3	393.4	399.1	405.9	414.2	422.3	429.0	437.2	446.4	454.8
165°	392.9	394.5	399.3	403.2	408.0	415.1	420.6	425.3	430.9	438.0	444.3
167.5°	399.4	400.8	403.9	406.7	409.7	414.9	419.5	421.7	425.3	429.8	434.4
170°	403.2	404.0	406.4	408.0	410.4	414.3	418.3	419.9	422.2	425.3	429.3
172.5°	406.4	405.9	408.3	409.2	411.0	413.7	416.4	417.3	418.4	421.0	423.6
175°	409.6	408.8	410.4	410.4	411.1	412.7	414.3	413.5	414.3	415.1	417.5
177.5°	410.5	409.9	411.1	411.1	411.1	411.8	413.0	411.8	411.1	411.8	413.0
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331404-927

CATALOG NUMBER: S122DIP-S865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1418.6	1424.5	1424.5	1425.4	1432.1	1431.2	1430.8
5°	1509.7	1518.6	1519.6	1529.1	1535.4	1533.3	1527.6
7.5°	1595.5	1612.2	1624.8	1631.8	1640.1	1645.3	1643.0
10°	1663.7	1687.8	1702.6	1712.5	1724.7	1733.6	1730.4
12.5°	1725.5	1754.3	1774.5	1791.6	1793.2	1804.7	1796.9
15°	1821.9	1852.4	1855.5	1868.1	1878.2	1877.1	1877.6
17.5°	1853.8	1863.5	1865.5	1865.8	1866.0	1862.3	1854.3
20°	1842.4	1838.7	1829.8	1823.0	1810.8	1809.3	1798.8
22.5°	1788.6	1776.9	1754.5	1739.7	1720.9	1715.9	1713.0
25°	1682.6	1656.8	1621.1	1586.9	1577.5	1559.1	1564.3
27.5°	1537.2	1497.1	1458.3	1430.6	1405.5	1377.9	1385.8
30°	1435.0	1389.8	1335.1	1293.1	1266.3	1240.0	1235.2
32.5°	1313.0	1246.8	1185.9	1148.8	1107.8	1091.2	1072.9
35°	1102.8	1038.2	977.7	925.7	895.7	872.6	851.5
37.5°	913.7	839.2	790.4	748.3	726.7	713.4	716.8
40°	796.4	731.2	695.5	663.4	643.4	633.9	636.0
42.5°	701.3	652.5	623.1	601.1	587.0	581.8	580.5
45°	593.4	566.1	541.9	529.3	522.5	516.7	513.0
47.5°	519.8	497.6	483.9	476.4	470.5	464.5	464.5
50°	475.7	461.0	451.5	443.6	438.9	434.7	438.4
52.5°	442.0	428.6	419.1	412.1	410.4	406.5	406.5
55°	392.1	381.6	374.8	368.4	365.4	363.2	360.6
57.5°	346.7	336.8	330.4	326.5	320.4	318.3	317.5
60°	314.3	306.4	300.2	294.9	292.2	288.0	288.0
62.5°	284.5	276.6	270.7	266.7	262.4	260.7	261.2
65°	241.3	235.0	229.2	225.0	223.9	220.8	221.8
67.5°	201.5	197.3	191.2	188.9	187.0	185.2	183.9
70°	175.1	170.9	167.7	164.5	163.0	163.0	163.0
72.5°	152.7	147.7	145.8	141.8	142.8	141.1	139.4
75°	118.3	115.1	113.5	111.9	109.3	109.3	109.3
77.5°	87.1	86.1	84.2	82.5	81.9	81.4	81.6
80°	67.3	66.8	65.7	65.7	64.6	64.2	63.1
82.5°	51.7	50.4	49.7	49.3	49.1	49.0	48.8
85°	29.5	28.4	28.4	28.9	27.9	27.9	28.4
87.5°	16.1	16.4	16.2	16.2	16.6	16.2	16.2
90°	23.7	25.3	26.1	26.1	26.1	26.1	26.1
92.5°	59.2	52.5	47.6	47.0	44.4	45.1	43.8
95°	158.9	125.7	108.3	98.1	91.7	89.4	90.2
97.5°	395.5	309.9	252.9	215.1	195.6	184.0	177.4
100°	623.8	515.5	419.9	354.2	320.2	297.3	283.0
102.5°	856.0	776.7	675.3	604.0	546.0	517.4	498.1
105°	1050.0	1060.3	1034.1	985.1	936.1	902.1	891.0
107.5°	1035.7	1117.9	1156.2	1162.4	1159.7	1152.9	1138.2
110°	991.4	1092.7	1157.5	1191.4	1206.5	1213.6	1212.8



TEST NUMBER: P331404-927

CATALOG NUMBER: S122DIP-S865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	939.0	1047.1	1121.4	1168.7	1193.8	1207.3	1211.6
115°	867.3	970.9	1052.3	1108.4	1144.8	1165.4	1172.5
117.5°	809.1	903.0	979.5	1036.6	1075.1	1096.8	1102.7
120°	778.8	862.5	934.5	989.8	1027.0	1050.0	1057.9
122.5°	753.4	832.8	897.9	947.5	984.0	1004.4	1011.1
125°	720.3	789.8	849.1	895.0	925.0	944.8	951.1
127.5°	688.0	753.6	808.3	848.3	876.5	893.6	898.7
130°	666.5	729.0	781.2	819.9	846.8	862.5	868.9
132.5°	646.3	703.6	752.7	790.8	817.7	832.2	837.9
135°	614.3	666.5	710.7	744.7	770.9	785.1	788.2
137.5°	588.8	630.3	668.8	699.9	722.3	734.8	739.6
140°	572.4	608.8	643.6	668.8	689.4	701.3	706.0
142.5°	557.9	589.1	618.3	642.3	661.0	671.5	672.5
145°	539.2	563.7	586.6	605.6	619.1	626.9	629.3
147.5°	524.0	543.1	559.9	575.6	586.3	591.7	593.1
150°	513.9	530.5	544.7	556.6	566.1	570.8	571.6
152.5°	505.6	519.8	532.1	541.4	549.6	553.1	553.3
155°	492.6	504.4	513.1	521.8	527.4	530.5	528.9
157.5°	479.3	489.3	496.1	502.2	506.8	508.2	508.2
160°	470.4	479.1	484.7	490.2	494.2	495.0	495.0
162.5°	462.2	469.6	473.9	479.4	482.1	482.9	482.3
165°	449.9	455.4	458.6	461.7	464.9	464.9	464.1
167.5°	438.6	442.4	445.3	446.7	448.5	448.3	447.3
170°	431.7	434.8	436.4	437.2	439.6	438.8	437.2
172.5°	425.3	427.9	428.8	429.6	430.7	429.9	429.0
175°	418.3	419.1	419.9	419.9	420.6	419.9	418.3
177.5°	413.0	413.7	413.7	413.7	413.7	413.0	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1

(END OF REPORT)