

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930990

Luminaire Tested: DFN2DS-SQ3F0-080DS940-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930990
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-080DS940-RLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6065.6 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 82
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930990

CATALOG NUMBER: DFN2DS-SQ3F0-080DS940-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930990

CATALOG NUMBER: DFN2DS-SQ3F0-080DS940-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3379	3379	3379
5°	3392	3337	3355
10°	3366	3283	3254
15°	3328	3185	3093
20°	3274	3046	2893
25°	3219	2888	2699
30°	3143	2726	2451
35°	3069	2550	2232
40°	2994	2367	1980
45°	2906	2163	1751
50°	2817	1956	1527
55°	2724	1733	1312
60°	2618	1498	1089
65°	2497	1259	991
70°	2352	1037	912
75°	2174	945	851
80°	1919	845	775
85°	1508	667	667

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2906 cd/sqm

TEST NUMBER: P930990

CATALOG NUMBER: DFN2DS-SQ3F0-080DS940-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.4	4.6
10°-20°	758.8	12.5
20°-30°	1065.3	17.6
30°-40°	1161.3	19.1
40°-50°	1067.3	17.6
50°-60°	838.3	13.8
60°-70°	545.6	9.0
70°-80°	280.9	4.6
80°-90°	71.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2100.6	34.6
0°-40°	3261.8	53.8
0°-60°	5167.4	85.2
0°-90°	6065.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6065.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2949	2949	2949	2949	2949	
5°	2949	2936	2901	2925	2917	280
15°	2805	2776	2685	2634	2608	790
25°	2546	2461	2285	2175	2135	1171
35°	2194	2058	1823	1655	1596	1373
45°	1794	1615	1335	1145	1081	1385
55°	1364	1156	867	707	657	1219
65°	921	704	464	374	366	913
75°	491	304	214	195	192	519
85°	115	59	51	51	51	138
90°	0	0	0	0	0	

TEST NUMBER: P930990

CATALOG NUMBER: DFN2DS-SQ3F0-080DS940-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2949.3	2949.3	2949.3	2949.3	2949.3
2.5°	2962.6	2949.3	2919.9	2946.7	2941.4
5°	2949.3	2936.0	2901.1	2925.2	2917.3
7.5°	2925.2	2909.3	2872.0	2882.5	2869.1
10°	2893.2	2874.6	2821.3	2813.1	2797.2
12.5°	2853.3	2829.2	2757.0	2741.1	2711.7
15°	2805.2	2775.7	2685.1	2634.4	2607.8
17.5°	2749.1	2706.3	2594.2	2535.6	2492.8
20°	2685.1	2631.6	2498.2	2431.7	2372.7
22.5°	2615.7	2554.2	2399.4	2308.8	2268.8
25°	2546.3	2460.8	2284.7	2175.4	2135.2
27.5°	2463.6	2372.7	2177.9	2052.5	1991.0
30°	2375.6	2273.9	2060.4	1924.5	1852.2
32.5°	2290.0	2167.2	1948.6	1788.3	1721.5
35°	2194.1	2057.8	1823.1	1654.9	1596.0
37.5°	2100.6	1953.7	1705.6	1521.2	1454.7
40°	2001.8	1841.8	1582.7	1393.2	1323.8
42.5°	1900.4	1729.7	1460.0	1262.4	1195.8
45°	1793.6	1614.7	1334.6	1144.9	1080.9
47.5°	1692.3	1502.8	1214.5	1024.8	966.2
50°	1580.1	1390.7	1097.1	912.7	856.9
52.5°	1470.6	1270.3	984.9	808.8	758.1
55°	1363.8	1155.7	867.4	707.4	656.7
57.5°	1254.5	1041.0	763.5	614.0	571.1
60°	1142.3	928.8	653.8	517.9	475.2
62.5°	1033.0	819.5	560.4	432.4	411.2
65°	920.9	704.5	464.4	373.8	365.5
67.5°	814.1	597.8	373.8	328.2	320.3
70°	702.0	493.9	309.5	282.9	272.1
72.5°	595.2	397.6	258.9	237.6	232.2
75°	491.0	304.2	213.5	194.8	192.3
77.5°	387.1	216.0	168.2	157.4	152.1
80°	290.8	154.9	128.0	117.5	117.5
82.5°	202.8	104.2	88.0	82.7	82.7
85°	114.7	58.6	50.7	50.7	50.7
87.5°	42.7	21.2	21.2	18.7	18.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930990

CATALOG NUMBER: DFN2DS-SQ3F0-080DS940-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.47	16.99	15.83	17.30	17.62	11.43	12.95	11.79	13.26	13.58
	3H	17.23	18.60	17.61	18.92	19.29	12.69	14.06	13.07	14.38	14.75
	4H	17.90	19.18	18.30	19.53	19.90	13.19	14.47	13.59	14.82	15.20
	6H	18.39	19.57	18.80	19.94	20.33	13.57	14.76	13.99	15.12	15.52
	8H	18.55	19.68	18.98	20.07	20.47	13.70	14.83	14.13	15.21	15.62
	12H	18.65	19.73	19.08	20.11	20.54	13.78	14.86	14.21	15.24	15.67
4H	2H	15.57	16.85	15.97	17.20	17.58	12.12	13.40	12.52	13.75	14.13
	3H	17.50	18.57	17.91	18.97	19.37	13.56	14.63	13.98	15.03	15.43
	4H	18.25	19.21	18.68	19.62	20.06	14.16	15.12	14.60	15.54	15.97
	6H	18.84	19.68	19.30	20.12	20.58	14.65	15.48	15.11	15.93	16.39
	8H	19.06	19.84	19.52	20.28	20.75	14.81	15.59	15.28	16.04	16.50
	12H	19.21	19.91	19.69	20.38	20.86	14.93	15.63	15.41	16.10	16.58
8H	4H	18.28	19.05	18.74	19.50	19.97	14.52	15.30	14.98	15.74	16.21
	6H	18.91	19.56	19.41	20.05	20.52	15.10	15.75	15.60	16.24	16.72
	8H	19.16	19.74	19.68	20.25	20.74	15.33	15.90	15.84	16.41	16.90
	12H	19.37	19.88	19.88	20.37	20.93	15.50	16.01	16.01	16.51	17.07
12H	4H	18.26	18.96	18.74	19.43	19.90	14.56	15.26	15.04	15.73	16.21
	6H	18.89	19.47	19.41	19.98	20.47	15.17	15.75	15.68	16.25	16.74
	8H	19.18	19.69	19.69	20.18	20.75	15.44	15.95	15.95	16.44	17.01