

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331637-927

Luminaire Tested: **S122RDIP-S290D925U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331637-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S290D925U927-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3441.1 lumens  
Efficiency: N/A  
Efficacy: 92.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331637-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331637-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	27	20
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	25	24	23	18
3	77	68	61	56	68	61	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	53	47	62	54	47	43	42	37	34	31	28	26	20	19	18	13
5	64	53	46	40	57	48	41	37	37	33	29	28	25	22	19	17	15	12
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	17	15	14	10
7	55	43	36	30	49	39	32	28	30	26	22	23	20	17	15	14	12	9
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	12	11	8
9	47	36	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10	8
10	44	32	26	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6421	6421	6421
5°	6446	6340	6374
10°	6396	6237	6184
15°	6322	6051	5877
20°	6220	5787	5498
25°	6116	5489	5129
30°	5972	5179	4657
35°	5830	4845	4242
40°	5689	4498	3762
45°	5523	4108	3329
50°	5350	3715	2901
55°	5177	3291	2494
60°	4973	2848	2070
65°	4741	2392	1883
70°	4471	1969	1733
75°	4130	1797	1616
80°	3645	1609	1469
85°	2853	1260	1260



TEST NUMBER: P331637-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.2	1.1
10°-20°	102.2	3.0
20°-30°	143.5	4.2
30°-40°	156.5	4.5
40°-50°	143.9	4.2
50°-60°	113.0	3.3
60°-70°	73.7	2.1
70°-80°	38.0	1.1
80°-90°	13.6	0.4
90°-100°	59.4	1.7
100°-110°	184.4	5.4
110°-120°	315.1	9.2
120°-130°	414.4	12.0
130°-140°	465.2	13.5
140°-150°	456.1	13.3
150°-160°	382.5	11.1
160°-170°	253.7	7.4
170°-180°	88.7	2.6
0°-30°	282.9	8.2
0°-40°	439.4	12.8
0°-60°	696.4	20.2
0°-90°	821.6	23.9
90°-120°	558.9	16.2
90°-150°	1894.5	55.1
90°-180°	2620.0	76.1
0°-180°	3441.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	398	398	398	398	398	
5°	398	396	391	394	393	38
15°	378	374	362	355	352	106
25°	343	331	308	294	288	158
35°	296	277	246	224	215	185
45°	242	217	180	155	146	187
55°	184	155	117	96	89	164
65°	124	95	63	51	49	123
75°	66	42	29	26	26	70
85°	15	8	7	7	7	18
90°	1	11	28	26	27	3
95°	41	49	51	50	49	47
105°	170	172	174	175	176	180
115°	316	321	319	318	316	313
125°	460	467	465	463	462	411
135°	595	604	606	605	602	460
145°	722	728	733	733	730	451
155°	826	828	831	834	832	380
165°	899	898	898	903	900	253
175°	935	933	931	936	932	89
180°	937	937	937	937	937	



TEST NUMBER: P331637-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7
2.5°	399.1	398.8	398.5	398.2	397.8	397.3	396.6	395.9	395.2	394.5	395.1
5°	397.7	397.3	396.9	396.5	396.1	395.3	394.3	393.2	392.2	391.2	391.9
7.5°	393.6	393.1	392.5	392.1	391.6	390.7	389.5	388.2	387.1	385.9	386.0
10°	390.1	389.5	389.0	388.4	387.9	386.7	385.2	383.6	382.0	380.4	380.2
12.5°	385.8	385.1	384.4	383.7	383.0	381.7	379.6	377.6	375.5	373.4	373.0
15°	378.2	377.3	376.4	375.6	374.7	372.9	370.2	367.5	364.7	362.0	360.5
17.5°	368.9	367.6	366.2	364.9	363.5	361.2	357.7	354.2	350.7	347.2	345.4
20°	362.0	360.4	358.9	357.2	355.6	352.8	348.8	344.8	340.9	336.8	334.9
22.5°	354.6	352.8	350.9	349.2	347.4	344.2	339.7	335.2	330.7	326.2	323.6
25°	343.3	340.7	338.2	335.6	333.1	329.2	323.8	318.6	313.3	308.1	304.8
27.5°	329.8	327.0	324.2	321.5	318.6	314.3	308.3	302.4	296.4	290.5	286.7
30°	320.3	317.3	314.2	311.2	308.2	303.4	297.0	290.7	284.2	277.8	273.8
32.5°	311.1	307.5	304.0	300.4	296.8	291.8	285.3	278.8	272.3	265.7	261.1
35°	295.8	291.8	287.6	283.6	279.5	273.9	266.9	259.8	252.9	245.8	240.7
37.5°	280.6	276.1	271.6	267.1	262.6	256.7	249.1	241.6	234.2	226.6	221.1
40°	269.9	265.1	260.3	255.5	250.7	244.5	236.7	228.9	221.2	213.4	207.7
42.5°	259.0	253.9	248.8	243.8	238.8	232.2	224.2	216.2	208.2	200.2	194.3
45°	241.9	236.5	231.1	225.8	220.4	213.5	205.1	196.7	188.3	179.9	174.3
47.5°	225.1	219.4	213.8	208.1	202.4	195.3	186.6	177.9	169.2	160.6	155.0
50°	213.0	207.4	201.7	196.0	190.4	183.1	174.3	165.5	156.7	147.9	142.4
52.5°	201.2	195.3	189.4	183.5	177.5	170.2	161.6	153.0	144.4	135.8	130.5
55°	183.9	177.7	171.4	165.2	158.9	151.5	142.8	134.2	125.6	116.9	112.2
57.5°	166.1	159.7	153.3	146.9	140.5	133.2	124.8	116.6	108.3	100.0	95.5
60°	154.0	147.7	141.2	134.8	128.4	121.1	112.9	104.6	96.4	88.2	84.1
62.5°	142.2	135.9	129.4	123.0	116.6	109.5	101.6	93.8	86.0	78.1	74.2
65°	124.1	117.6	111.2	104.7	98.2	91.4	84.2	77.0	69.8	62.6	59.9
67.5°	106.7	100.3	93.9	87.5	81.0	74.5	68.0	61.6	55.1	48.6	47.4
70°	94.7	88.4	82.1	76.0	69.7	63.8	58.3	52.8	47.3	41.7	41.0
72.5°	83.1	77.2	71.1	65.2	59.2	54.0	49.6	45.2	40.7	36.3	35.6
75°	66.2	60.6	55.1	49.4	43.8	39.7	36.9	34.2	31.5	28.8	28.2
77.5°	49.6	44.7	39.8	34.9	29.9	26.9	25.5	24.2	22.9	21.6	21.3
80°	39.2	35.2	31.1	27.0	22.9	20.4	19.6	18.9	18.1	17.3	17.0
82.5°	29.7	26.5	23.4	20.2	17.0	15.1	14.6	14.0	13.5	13.0	12.8
85°	15.4	13.8	12.1	10.5	8.8	7.8	7.5	7.3	7.1	6.8	6.8
87.5°	4.8	4.7	4.6	4.5	4.4	4.8	5.5	6.3	7.1	7.8	7.7
90°	0.8	2.9	5.0	7.1	9.2	12.2	16.1	20.0	23.8	27.6	27.3
92.5°	14.1	15.6	17.2	18.7	20.3	21.5	22.4	23.3	24.2	25.1	25.2
95°	41.1	42.9	44.6	46.3	48.2	49.2	49.5	49.9	50.2	50.6	50.6
97.5°	75.1	76.7	78.2	79.8	81.3	82.4	83.1	83.7	84.4	85.1	85.1
100°	100.4	101.8	103.2	104.6	106.0	107.0	107.5	108.1	108.6	109.1	109.1
102.5°	127.0	128.1	129.2	130.3	131.4	132.4	133.0	133.7	134.4	135.1	135.1
105°	170.0	170.5	171.0	171.6	172.1	172.5	172.9	173.3	173.6	173.9	174.3
107.5°	213.3	214.0	214.8	215.6	216.4	216.7	216.7	216.7	216.7	216.7	216.9
110°	241.1	242.2	243.2	244.3	245.3	245.9	245.9	245.9	245.9	245.9	245.9



TEST NUMBER: P331637-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	271.5	272.5	273.6	274.6	275.7	276.2	276.0	275.8	275.8	275.6	275.2
115°	316.2	317.3	318.3	319.4	320.4	320.8	320.4	320.1	319.7	319.4	319.2
117.5°	360.8	362.2	363.6	365.0	366.5	366.6	365.7	364.6	363.7	362.7	362.3
120°	390.5	392.0	393.3	394.7	396.2	396.2	394.7	393.3	392.0	390.5	390.5
122.5°	417.7	419.4	421.1	422.8	424.5	424.8	423.8	422.9	421.9	420.9	420.5
125°	460.1	461.7	463.3	464.9	466.4	467.0	466.4	465.9	465.4	464.9	464.3
127.5°	501.4	503.4	505.4	507.4	509.4	510.1	509.5	508.8	508.2	507.6	506.9
130°	527.3	529.6	531.9	534.2	536.5	537.4	537.0	536.7	536.4	536.0	535.7
132.5°	556.4	558.3	560.2	562.0	563.9	564.8	564.9	565.0	565.0	565.1	564.4
135°	595.3	597.2	599.1	601.1	603.0	604.2	604.5	604.8	605.2	605.5	605.4
137.5°	636.3	637.8	639.4	641.0	642.5	643.6	644.0	644.5	645.0	645.4	645.3
140°	660.9	662.5	664.1	665.7	667.3	668.4	669.3	670.2	671.1	672.0	672.0
142.5°	686.2	687.8	689.4	690.9	692.5	693.6	694.2	694.8	695.4	696.0	696.2
145°	722.5	723.8	725.0	726.3	727.5	728.6	729.7	730.7	731.8	732.8	733.0
147.5°	754.9	756.5	758.0	759.4	760.9	762.0	762.7	763.3	764.1	764.8	765.2
150°	777.1	778.2	779.2	780.3	781.3	782.2	782.9	783.6	784.3	785.1	785.5
152.5°	796.7	797.8	798.8	799.9	801.0	801.9	802.7	803.6	804.4	805.3	806.0
155°	826.2	826.6	827.2	827.8	828.2	828.8	829.3	829.8	830.4	830.8	831.8
157.5°	851.3	851.6	852.0	852.3	852.7	853.0	853.3	853.7	854.0	854.3	855.5
160°	866.5	866.8	867.1	867.5	867.8	868.2	868.3	868.5	868.6	868.8	869.9
162.5°	880.4	880.4	880.5	880.6	880.7	880.7	881.0	881.1	881.3	881.5	882.6
165°	898.9	898.7	898.5	898.3	898.2	898.1	898.1	898.1	898.1	898.1	899.3
167.5°	914.3	913.9	913.3	912.8	912.3	912.0	912.0	911.9	911.9	911.8	913.1
170°	922.6	922.0	921.5	921.0	920.4	920.1	920.0	919.8	919.6	919.4	920.7
172.5°	928.3	927.7	927.2	926.7	926.1	925.8	925.7	925.4	925.3	925.1	926.4
175°	935.3	934.7	934.1	933.7	933.1	932.7	932.3	932.0	931.6	931.3	932.5
177.5°	938.1	937.6	937.2	936.8	936.4	936.0	935.7	935.5	935.2	934.9	935.7
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331637-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7
2.5°	395.8	396.4	397.0	397.3	397.2	397.0	396.9	396.8
5°	392.6	393.3	394.0	394.3	394.0	393.8	393.6	393.3
7.5°	386.3	386.5	386.7	386.6	386.2	385.7	385.3	384.9
10°	379.9	379.7	379.5	379.1	378.6	378.1	377.6	377.2
12.5°	372.6	372.2	371.8	371.1	370.3	369.6	368.8	368.0
15°	359.0	357.4	355.9	354.8	354.0	353.2	352.4	351.6
17.5°	343.6	341.7	340.0	338.4	337.0	335.6	334.2	332.9
20°	332.9	330.8	328.8	326.9	325.2	323.4	321.7	320.0
22.5°	321.1	318.5	315.9	313.9	312.6	311.3	310.0	308.7
25°	301.5	298.2	294.9	292.7	291.5	290.3	289.1	287.9
27.5°	282.8	279.0	275.2	272.4	270.5	268.5	266.6	264.7
30°	269.7	265.6	261.5	258.4	256.2	254.1	251.9	249.8
32.5°	256.4	251.8	247.1	243.8	241.8	239.7	237.7	235.7
35°	235.8	230.7	225.6	222.2	220.5	218.7	217.0	215.2
37.5°	215.6	210.0	204.5	200.7	198.7	196.6	194.6	192.6
40°	202.1	196.4	190.7	186.8	184.7	182.7	180.5	178.5
42.5°	188.4	182.5	176.7	172.8	170.7	168.7	166.7	164.7
45°	168.6	162.9	157.2	153.4	151.5	149.6	147.7	145.8
47.5°	149.2	143.6	138.0	134.3	132.5	130.8	129.0	127.3
50°	136.9	131.3	125.8	122.2	120.6	118.9	117.2	115.5
52.5°	125.2	119.9	114.5	111.1	109.6	108.0	106.4	104.9
55°	107.3	102.6	97.8	94.6	93.1	91.6	90.1	88.6
57.5°	91.2	86.7	82.4	79.5	78.3	77.0	75.7	74.4
60°	80.0	76.0	71.9	69.2	67.9	66.6	65.4	64.1
62.5°	70.3	66.5	62.6	60.2	59.4	58.7	57.9	57.1
65°	57.2	54.4	51.7	50.2	50.0	49.7	49.5	49.3
67.5°	46.2	44.9	43.6	42.9	42.6	42.4	42.1	41.9
70°	40.2	39.4	38.6	38.0	37.6	37.3	37.0	36.7
72.5°	34.9	34.2	33.6	33.2	33.0	32.8	32.6	32.4
75°	27.6	27.1	26.5	26.2	26.1	26.1	26.0	25.9
77.5°	20.9	20.6	20.3	20.1	20.0	19.8	19.7	19.6
80°	16.6	16.3	16.0	15.8	15.8	15.8	15.8	15.8
82.5°	12.6	12.4	12.2	12.1	12.1	12.1	12.1	12.1
85°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
87.5°	7.6	7.4	7.3	7.3	7.3	7.3	7.4	7.4
90°	26.9	26.6	26.3	26.1	26.4	26.5	26.7	26.9
92.5°	25.3	25.3	25.4	25.5	25.5	25.5	25.6	25.6
95°	50.6	50.6	50.6	50.4	50.1	49.7	49.4	49.0
97.5°	85.1	85.1	85.1	85.1	85.0	85.0	84.9	84.9
100°	109.1	109.1	109.1	109.0	108.8	108.7	108.4	108.3
102.5°	135.3	135.5	135.6	135.5	135.4	135.2	135.1	134.9
105°	174.6	175.0	175.3	175.5	175.5	175.5	175.5	175.5
107.5°	217.1	217.2	217.3	217.0	216.2	215.4	214.6	213.7
110°	245.9	245.9	245.9	245.6	245.1	244.5	244.0	243.5





TEST NUMBER: P331637-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	274.7	274.3	273.9	273.5	273.1	272.7	272.4	272.0
115°	319.0	318.9	318.7	318.3	317.8	317.3	316.7	316.2
117.5°	361.9	361.5	361.0	360.5	360.0	359.5	358.9	358.5
120°	390.5	390.5	390.5	390.3	389.8	389.2	388.7	388.2
122.5°	420.0	419.6	419.2	418.8	418.4	418.0	417.6	417.2
125°	463.8	463.3	462.7	462.4	462.2	462.0	461.8	461.7
127.5°	506.3	505.6	505.0	504.4	503.8	503.3	502.7	502.2
130°	535.3	535.0	534.6	534.1	533.4	532.7	532.0	531.2
132.5°	563.6	562.8	562.0	561.3	560.8	560.2	559.7	559.1
135°	605.2	605.1	604.8	604.5	604.0	603.5	602.9	602.4
137.5°	645.2	645.0	644.8	644.4	643.7	643.0	642.3	641.6
140°	672.0	672.0	672.0	671.6	670.9	670.2	669.6	668.8
142.5°	696.3	696.4	696.6	696.3	695.6	694.9	694.2	693.5
145°	733.2	733.4	733.6	733.3	732.6	731.9	731.2	730.5
147.5°	765.6	766.0	766.4	766.2	765.6	764.9	764.2	763.5
150°	786.1	786.6	787.1	787.1	786.6	786.1	785.5	785.1
152.5°	806.6	807.2	807.9	807.9	807.2	806.6	806.0	805.3
155°	832.7	833.5	834.4	834.6	834.0	833.5	833.0	832.4
157.5°	856.7	857.9	859.0	859.2	858.4	857.5	856.7	855.9
160°	870.9	872.0	873.1	873.2	872.5	871.8	871.1	870.4
162.5°	883.8	885.0	886.2	886.5	885.6	884.7	883.9	883.0
165°	900.6	901.7	903.0	903.2	902.3	901.4	900.6	899.7
167.5°	914.3	915.5	916.7	916.9	916.0	915.0	914.2	913.2
170°	921.9	923.1	924.3	924.4	923.4	922.3	921.2	920.2
172.5°	927.6	928.8	930.0	930.1	929.1	928.0	926.9	925.9
175°	933.7	934.9	936.2	936.3	935.3	934.1	933.1	932.1
177.5°	936.6	937.5	938.3	938.3	937.5	936.6	935.7	934.9
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8

(END OF REPORT)