

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331674-927

Luminaire Tested: **S122RDIP-S485D1080U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331674-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S485D1080U927-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4678.8 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331674-927

CATALOG NUMBER: S122RDIP-S485D1080U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331674-927

CATALOG NUMBER: S122RDIP-S485D1080U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37	29
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	78	72	68	76	70	65	61	55	52	49	42	40	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23	18
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	23	22	20	16
5	65	54	47	41	58	49	43	38	39	34	31	30	27	24	21	19	18	14
6	60	49	41	36	54	44	37	33	35	30	27	27	24	21	19	17	16	12
7	56	44	36	31	50	40	33	29	32	27	24	25	21	19	18	16	14	11
8	52	40	32	27	46	36	30	25	29	24	21	23	19	17	16	14	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	22	40	30	24	20	24	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10555	10555	10555
5°	10595	10423	10481
10°	10516	10252	10165
15°	10394	9949	9663
20°	10227	9514	9036
25°	10055	9021	8432
30°	9818	8516	7655
35°	9585	7965	6974
40°	9352	7396	6184
45°	9079	6754	5471
50°	8796	6106	4770
55°	8510	5413	4096
60°	8176	4682	3400
65°	7798	3931	3095
70°	7345	3238	2851
75°	6787	2951	2658
80°	5997	2641	2427
85°	4705	2075	2075



TEST NUMBER: P331674-927

CATALOG NUMBER: S122RDIP-S485D1080U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.2	1.3
10°-20°	168.0	3.6
20°-30°	235.9	5.0
30°-40°	257.3	5.5
40°-50°	236.6	5.1
50°-60°	185.8	4.0
60°-70°	121.1	2.6
70°-80°	62.5	1.3
80°-90°	20.5	0.4
90°-100°	191.3	4.1
100°-110°	649.3	13.9
110°-120°	689.8	14.7
120°-130°	567.8	12.1
130°-140°	456.0	9.7
140°-150°	344.6	7.4
150°-160°	242.2	5.2
160°-170°	142.6	3.0
170°-180°	46.4	1.0
0°-30°	465.2	9.9
0°-40°	722.4	15.4
0°-60°	1144.8	24.5
0°-90°	1348.9	28.8
90°-120°	1530.4	32.7
90°-150°	2898.8	62.0
90°-180°	3330.0	71.2
0°-180°	4678.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	654	654	654	654	654	
5°	654	650	643	648	647	62
15°	622	615	595	584	578	175
25°	564	544	506	483	473	259
35°	486	455	404	368	354	304
45°	398	357	296	255	240	307
55°	302	255	192	158	146	270
65°	204	156	103	84	81	202
75°	109	69	47	43	43	115
85°	25	14	11	11	11	30
90°	1	12	31	30	30	3
95°	32	79	361	136	105	34
105°	112	169	682	1219	1037	119
115°	198	250	570	1177	1365	196
125°	276	327	548	954	1107	245
135°	324	386	542	802	918	250
145°	370	425	539	670	732	232
155°	421	454	524	592	616	193
165°	458	472	502	532	540	129
175°	478	478	482	488	487	45
180°	479	479	479	479	479	



TEST NUMBER: P331674-927

CATALOG NUMBER: S122RDIP-S485D1080U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	656.1	655.6	655.1	654.5	654.0	653.2	652.0	650.9	649.7	648.6	649.6
5°	653.7	653.1	652.4	651.8	651.1	649.9	648.2	646.5	644.8	643.1	644.3
7.5°	647.0	646.2	645.4	644.5	643.7	642.3	640.3	638.3	636.4	634.4	634.7
10°	641.4	640.4	639.4	638.6	637.6	635.9	633.3	630.6	628.0	625.3	625.0
12.5°	634.2	633.1	631.9	630.8	629.7	627.5	624.1	620.8	617.3	614.0	613.3
15°	621.8	620.4	618.9	617.4	616.0	613.1	608.6	604.1	599.7	595.2	592.7
17.5°	606.6	604.4	602.1	599.9	597.7	593.7	588.0	582.3	576.6	570.8	567.8
20°	595.2	592.6	589.9	587.3	584.6	580.0	573.5	566.9	560.3	553.7	550.5
22.5°	582.9	580.0	576.9	574.0	571.1	565.9	558.5	551.0	543.7	536.2	532.0
25°	564.4	560.2	556.0	551.8	547.6	541.1	532.4	523.8	515.1	506.4	501.1
27.5°	542.2	537.6	533.0	528.5	523.9	516.7	506.9	497.1	487.4	477.5	471.3
30°	526.6	521.6	516.6	511.6	506.6	498.8	488.3	477.8	467.2	456.8	450.0
32.5°	511.4	505.6	499.7	493.9	488.1	479.7	469.1	458.3	447.6	436.9	429.2
35°	486.3	479.6	472.9	466.2	459.5	450.4	438.8	427.2	415.7	404.1	395.8
37.5°	461.2	453.8	446.5	439.1	431.8	421.9	409.6	397.3	384.9	372.6	363.5
40°	443.7	435.9	427.9	420.1	412.2	401.9	389.1	376.4	363.6	350.9	341.5
42.5°	425.7	417.4	409.1	400.8	392.5	381.8	368.6	355.4	342.2	329.1	319.4
45°	397.6	388.8	379.9	371.1	362.3	351.0	337.2	323.4	309.6	295.8	286.5
47.5°	370.1	360.8	351.5	342.1	332.8	321.0	306.7	292.5	278.2	264.0	254.7
50°	350.2	340.9	331.6	322.3	312.9	301.0	286.5	272.1	257.6	243.1	234.1
52.5°	330.8	321.1	311.3	301.6	291.8	279.9	265.7	251.6	237.4	223.3	214.5
55°	302.3	292.1	281.8	271.6	261.3	249.1	234.9	220.7	206.4	192.3	184.4
57.5°	273.1	262.6	252.1	241.5	231.0	219.0	205.3	191.6	178.0	164.4	157.1
60°	253.2	242.7	232.2	221.7	211.1	199.2	185.6	172.1	158.5	145.0	138.2
62.5°	233.8	223.3	212.8	202.2	191.7	180.1	167.2	154.2	141.3	128.4	122.0
65°	204.1	193.5	182.8	172.1	161.5	150.3	138.5	126.6	114.8	102.9	98.5
67.5°	175.5	164.9	154.3	143.8	133.2	122.6	111.9	101.3	90.6	80.0	78.0
70°	155.6	145.4	135.1	124.8	114.5	104.9	95.9	86.7	77.7	68.6	67.3
72.5°	136.7	126.8	117.0	107.2	97.4	88.8	81.5	74.2	66.9	59.7	58.5
75°	108.8	99.7	90.5	81.3	72.0	65.2	60.8	56.2	51.8	47.3	46.4
77.5°	81.5	73.4	65.4	57.3	49.3	44.1	42.0	39.8	37.6	35.5	34.9
80°	64.5	57.8	51.1	44.4	37.6	33.7	32.3	31.1	29.7	28.4	27.9
82.5°	48.9	43.6	38.4	33.2	28.0	24.9	24.0	23.1	22.2	21.3	21.0
85°	25.4	22.7	19.9	17.2	14.4	12.8	12.4	12.0	11.6	11.2	11.2
87.5°	7.8	7.4	7.4	6.9	6.4	6.6	7.4	8.8	9.8	10.1	9.7
90°	1.0	3.6	7.4	9.2	11.0	13.8	18.4	24.9	30.3	31.3	30.3
92.5°	11.2	16.2	22.8	26.9	33.1	41.7	62.6	91.8	118.0	119.6	101.1
95°	32.2	35.9	45.1	53.4	68.1	90.2	132.5	212.5	319.3	360.8	315.7
97.5°	52.4	57.4	67.2	79.7	96.6	121.7	174.8	286.4	463.8	615.8	646.0
100°	70.8	73.6	81.9	96.6	115.0	140.8	189.6	301.8	500.6	727.0	859.5
102.5°	87.8	89.8	98.1	112.8	132.0	157.7	202.8	302.6	486.6	730.7	939.1
105°	112.3	116.0	122.4	136.2	156.5	182.2	225.5	307.4	459.2	681.9	926.7
107.5°	138.8	141.7	148.0	160.7	180.8	206.7	248.7	320.0	445.6	629.6	845.9
110°	156.5	160.1	165.6	177.6	196.9	223.6	264.1	330.3	442.7	604.6	795.1



TEST NUMBER: P331674-927

CATALOG NUMBER: S122RDIP-S485D1080U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.6	176.3	182.6	193.8	212.4	239.8	278.8	341.4	443.4	588.4	759.8
115°	197.9	202.5	207.9	219.0	237.4	262.3	301.8	358.0	447.3	570.5	716.0
117.5°	224.0	227.7	233.2	243.0	260.6	286.4	323.0	375.7	453.8	561.9	688.3
120°	240.2	243.8	249.4	257.7	276.1	301.8	337.7	387.5	458.3	556.7	673.6
122.5°	255.6	258.6	264.1	273.1	291.5	318.1	351.7	397.8	463.4	553.8	661.1
125°	276.1	278.8	284.4	295.4	313.8	339.6	372.7	414.2	471.2	548.5	643.3
127.5°	292.2	296.0	303.7	315.8	333.5	360.0	392.2	429.4	479.1	545.3	626.7
130°	301.8	305.5	314.7	327.6	346.0	371.8	404.0	438.9	485.0	543.8	615.7
132.5°	310.7	315.1	325.0	338.7	357.8	383.6	414.3	448.5	490.8	543.1	606.8
135°	323.9	327.6	338.7	352.4	373.6	399.4	428.8	461.1	497.9	542.0	594.5
137.5°	336.4	340.9	351.9	366.6	387.6	411.5	440.6	470.6	504.1	541.9	585.8
140°	346.0	349.7	360.8	375.5	395.7	419.6	447.3	475.8	507.1	541.1	580.7
142.5°	355.6	358.5	368.8	383.6	403.1	425.6	452.4	480.2	509.3	541.1	575.5
145°	369.9	373.6	382.9	396.6	415.0	435.3	460.1	485.9	511.7	539.2	568.7
147.5°	385.4	388.2	397.0	409.7	425.0	443.0	466.4	489.0	512.4	536.0	561.7
150°	395.7	398.5	405.8	417.8	431.6	448.1	469.4	490.5	511.7	533.8	555.8
152.5°	406.0	407.3	414.6	425.2	438.2	453.3	472.3	491.2	510.2	530.0	550.6
155°	420.6	421.4	427.0	437.1	447.3	461.1	476.7	492.3	507.9	523.6	541.1
157.5°	432.7	433.6	438.1	446.9	455.0	466.6	479.8	492.3	503.7	517.0	532.1
160°	440.8	441.7	445.4	452.7	460.1	470.2	481.3	492.3	501.5	512.6	525.5
162.5°	448.9	448.4	452.0	457.9	464.5	472.5	482.0	491.6	499.3	508.9	519.6
165°	458.3	457.4	459.2	464.7	469.4	474.8	483.2	489.6	495.1	501.5	509.8
167.5°	466.0	464.9	466.6	470.1	473.4	476.9	482.9	488.3	490.8	495.1	500.3
170°	471.2	469.4	470.2	473.0	474.8	477.6	482.2	486.8	488.6	491.4	495.1
172.5°	474.1	473.0	472.5	475.2	476.3	478.3	481.5	484.6	485.7	487.0	490.0
175°	477.6	476.7	475.8	477.6	477.6	478.6	480.4	482.2	481.3	482.2	483.2
177.5°	479.3	477.8	477.1	478.6	478.6	478.6	479.3	480.8	479.3	478.6	479.3
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6



TEST NUMBER: P331674-927

CATALOG NUMBER: S122RDIP-S485D1080U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	650.6	651.7	652.8	653.2	653.0	652.8	652.5	652.4
5°	645.5	646.7	647.8	648.2	647.8	647.5	647.1	646.7
7.5°	635.0	635.3	635.7	635.6	634.9	634.1	633.5	632.8
10°	624.6	624.2	623.8	623.2	622.4	621.6	620.8	620.0
12.5°	612.6	611.9	611.2	610.1	608.8	607.5	606.2	604.9
15°	590.2	587.7	585.2	583.3	581.9	580.7	579.3	578.1
17.5°	564.8	561.9	558.9	556.3	554.1	551.8	549.5	547.2
20°	547.2	543.9	540.6	537.5	534.6	531.7	528.9	525.9
22.5°	527.8	523.6	519.4	516.1	514.0	511.8	509.7	507.5
25°	495.7	490.3	484.9	481.2	479.2	477.2	475.3	473.3
27.5°	465.0	458.7	452.4	447.7	444.6	441.5	438.3	435.2
30°	443.3	436.7	429.9	424.8	421.2	417.7	414.2	410.6
32.5°	421.5	413.9	406.2	400.8	397.4	394.1	390.7	387.4
35°	387.5	379.2	371.0	365.4	362.5	359.6	356.7	353.8
37.5°	354.3	345.2	336.1	329.9	326.6	323.3	320.0	316.6
40°	332.2	322.8	313.5	307.1	303.7	300.3	296.8	293.4
42.5°	309.7	300.1	290.5	284.0	280.7	277.3	274.0	270.7
45°	277.1	267.8	258.5	252.2	249.1	245.9	242.7	239.6
47.5°	245.4	236.1	226.9	220.8	217.9	215.1	212.1	209.3
50°	225.0	215.9	206.8	201.0	198.2	195.4	192.7	189.9
52.5°	205.7	197.0	188.2	182.6	180.1	177.5	174.9	172.4
55°	176.5	168.6	160.7	155.5	153.0	150.5	148.1	145.5
57.5°	149.9	142.7	135.5	130.8	128.7	126.6	124.5	122.3
60°	131.5	124.8	118.1	113.8	111.6	109.5	107.4	105.3
62.5°	115.6	109.2	102.8	99.0	97.8	96.5	95.2	94.0
65°	94.0	89.5	85.1	82.6	82.2	81.8	81.4	81.0
67.5°	75.9	73.8	71.8	70.6	70.1	69.7	69.3	68.8
70°	66.0	64.7	63.4	62.4	61.9	61.4	60.8	60.4
72.5°	57.4	56.3	55.2	54.5	54.2	53.9	53.6	53.2
75°	45.5	44.6	43.6	43.1	43.0	42.9	42.7	42.6
77.5°	34.5	33.9	33.4	33.0	32.8	32.6	32.4	32.2
80°	27.3	26.9	26.3	26.1	26.1	26.1	26.1	26.1
82.5°	20.7	20.4	20.0	19.9	19.9	19.9	19.9	19.9
85°	11.2	11.2	11.2	11.2	11.2	11.2	11.2	11.2
87.5°	9.4	9.0	9.3	9.3	9.3	9.3	9.3	9.3
90°	29.5	27.6	29.5	30.3	30.3	30.3	30.3	30.3
92.5°	80.2	68.8	61.1	55.4	54.7	51.7	52.4	51.0
95°	241.1	185.0	146.3	126.0	114.1	106.8	104.0	104.9
97.5°	562.6	460.3	360.8	294.3	250.3	227.7	214.2	206.5
100°	840.2	726.1	600.0	488.6	412.3	372.7	346.0	329.5
102.5°	1022.1	996.2	904.0	786.1	703.1	635.6	602.2	579.8
105°	1118.1	1222.1	1234.1	1203.7	1146.6	1089.6	1050.0	1037.1
107.5°	1048.9	1205.5	1301.2	1345.8	1353.0	1349.8	1341.9	1324.8
110°	989.3	1154.0	1271.8	1347.3	1386.8	1404.3	1412.6	1411.7



TEST NUMBER: P331674-927

CATALOG NUMBER: S122RDIP-S485D1080U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	934.8	1092.9	1218.8	1305.3	1360.3	1389.6	1405.3	1410.2
115°	867.8	1009.6	1130.0	1224.9	1290.2	1332.5	1356.5	1364.8
117.5°	817.4	941.8	1051.1	1140.0	1206.7	1251.3	1276.6	1283.6
120°	792.3	906.4	1004.0	1087.7	1152.1	1195.4	1222.1	1231.3
122.5°	772.5	877.0	969.4	1045.0	1102.8	1145.3	1169.1	1176.8
125°	743.5	838.4	919.3	988.3	1041.7	1076.7	1099.7	1107.1
127.5°	715.0	800.8	877.2	940.9	987.5	1020.2	1040.1	1046.0
130°	696.6	775.8	848.5	909.2	954.3	985.6	1004.0	1011.4
132.5°	679.0	752.3	819.0	876.1	920.4	951.7	968.7	975.3
135°	654.3	715.0	775.8	827.3	866.9	897.2	913.8	917.5
137.5°	634.6	685.4	733.6	778.6	814.6	840.7	855.3	860.8
140°	622.1	666.3	708.6	749.1	778.6	802.5	816.3	821.8
142.5°	611.8	649.4	685.8	719.6	747.6	769.4	781.6	782.8
145°	597.2	627.6	656.2	682.9	704.9	720.6	729.8	732.5
147.5°	586.1	610.0	632.2	651.7	669.9	682.5	688.7	690.4
150°	577.9	598.2	617.5	634.1	647.8	658.9	664.4	665.4
152.5°	569.8	588.6	605.0	619.3	630.2	639.8	643.8	644.0
155°	558.6	573.3	587.1	597.2	607.4	613.8	617.5	615.7
157.5°	545.5	557.9	569.4	577.3	584.6	589.9	591.5	591.5
160°	537.4	547.6	557.7	564.1	570.5	575.1	576.1	576.1
162.5°	529.3	538.0	546.6	551.6	558.0	561.2	562.1	561.3
165°	517.2	523.6	530.0	533.8	537.4	541.1	541.1	540.2
167.5°	505.6	510.6	515.0	518.3	519.9	522.0	521.8	520.7
170°	499.7	502.5	506.1	507.9	508.9	511.7	510.7	508.9
172.5°	493.1	495.1	498.0	499.2	500.1	501.4	500.4	499.3
175°	485.9	486.8	487.7	488.6	488.6	489.6	488.6	486.8
177.5°	480.8	480.8	481.5	481.5	481.5	481.5	480.8	479.3
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6

(END OF REPORT)