

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331675-927

Luminaire Tested: **S122RDIP-S675D330U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331675-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S675D330U927-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 330 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3049.5 lumens  
Efficiency: N/A  
Efficacy: 87.1 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331675-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331675-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	102	98	95	91	96	93	90	87	82	80	78	73	71	70	64	63	62	58
2	94	87	81	77	88	82	77	73	74	70	66	65	62	60	58	56	54	50
3	87	78	71	65	81	74	67	62	66	61	57	59	55	52	52	49	47	44
4	80	70	62	56	75	66	59	54	59	54	50	53	49	46	48	44	42	39
5	74	63	55	49	70	60	53	47	54	48	44	49	44	40	43	40	37	34
6	69	57	49	44	65	54	47	42	49	43	39	44	40	36	40	36	33	31
7	64	52	44	39	60	50	43	38	45	39	35	41	36	33	37	33	30	28
8	60	48	40	35	56	46	39	34	42	36	32	38	33	30	34	30	28	25
9	56	44	37	32	53	42	35	31	38	33	29	35	30	27	32	28	25	23
10	52	41	34	29	50	39	32	28	36	30	26	33	28	25	30	26	23	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	18791	18791	18791	18791
5°	20985	18908	16765	18908
10°	23282	18775	14532	18775
15°	24428	18501	11450	18501
20°	21179	18093	9907	18093
25°	13890	17533	8845	17533
30°	9350	16858	8006	16858
35°	7571	16005	7222	16005
40°	6734	15076	6681	15076
45°	6094	13988	5966	13988
50°	5546	12911	5526	12911
55°	5213	11713	5146	11713
60°	4363	10618	4308	10618
65°	3679	9639	4172	9639
70°	3399	8611	3932	8611
75°	3175	7492	3631	7492
80°	2929	6165	3236	6165
85°	2705	4872	2853	4872



TEST NUMBER: P331675-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.3	3.6
10°-20°	307.4	10.1
20°-30°	396.1	13.0
30°-40°	376.4	12.3
40°-50°	322.5	10.6
50°-60°	245.6	8.1
60°-70°	155.2	5.1
70°-80°	77.5	2.5
80°-90°	21.1	0.7
90°-100°	11.8	0.4
100°-110°	43.3	1.4
110°-120°	115.7	3.8
120°-130°	191.1	6.3
130°-140°	203.2	6.7
140°-150°	188.9	6.2
150°-160°	151.8	5.0
160°-170°	97.8	3.2
170°-180°	33.7	1.1
0°-30°	813.8	26.7
0°-40°	1190.3	39.0
0°-60°	1758.3	57.7
0°-90°	2012.1	66.0
90°-120°	170.8	5.6
90°-150°	754.0	24.7
90°-180°	1037.0	34.0
0°-180°	3049.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1164	1164	1164	1164	1164	
5°	1295	1167	1034	1167	1295	128
15°	1461	1107	685	1107	1461	394
25°	780	984	496	984	780	370
35°	384	812	366	812	384	246
45°	267	613	261	613	267	207
55°	185	416	183	416	185	163
65°	96	252	109	252	96	98
75°	51	120	58	120	51	54
85°	15	26	15	26	15	16
90°	7	0	7	0	7	4
95°	11	17	11	17	11	10
105°	20	78	20	78	20	20
115°	21	147	21	147	21	53
125°	219	208	219	208	219	190
135°	266	258	266	258	266	205
145°	304	299	304	299	304	190
155°	329	329	329	329	329	152
165°	346	347	346	347	346	98
175°	353	355	353	355	353	34
180°	354	354	354	354	354	



TEST NUMBER: P331675-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1211.0	1212.0	1213.0	1210.7	1210.7	1208.7	1204.5	1201.3	1192.2	1191.0	1191.0
5°	1294.8	1294.0	1295.6	1290.4	1283.1	1281.4	1273.7	1263.7	1253.2	1241.4	1239.0
7.5°	1378.1	1376.9	1373.6	1372.8	1367.1	1354.9	1342.6	1329.4	1311.9	1294.9	1286.3
10°	1420.1	1433.5	1425.4	1411.3	1414.1	1395.1	1385.0	1367.6	1353.0	1327.5	1321.9
12.5°	1461.6	1466.8	1464.3	1456.2	1452.5	1439.4	1425.8	1410.6	1383.8	1360.9	1341.0
15°	1461.4	1469.1	1471.1	1468.7	1470.7	1469.9	1462.6	1450.1	1426.6	1401.5	1379.7
17.5°	1353.5	1358.8	1372.1	1381.1	1392.4	1416.3	1428.1	1432.7	1429.3	1415.0	1399.6
20°	1232.6	1223.6	1260.8	1279.8	1296.0	1336.4	1371.2	1384.6	1406.0	1405.6	1401.5
22.5°	1061.0	1063.2	1098.4	1121.0	1168.2	1208.6	1248.3	1298.5	1340.0	1367.4	1383.5
25°	779.7	795.0	830.2	860.9	913.5	988.7	1057.0	1136.3	1211.1	1270.1	1326.4
27.5°	585.5	586.7	614.6	642.9	674.1	735.8	821.8	916.5	1023.1	1111.1	1212.4
30°	501.5	499.0	510.7	528.1	554.8	602.5	667.2	760.3	866.6	999.2	1117.3
32.5°	441.9	442.0	450.9	463.7	485.9	518.1	562.4	637.9	738.5	868.9	1007.3
35°	384.1	383.7	390.2	399.5	408.8	429.4	459.8	499.4	568.5	690.2	831.8
37.5°	342.8	344.5	347.7	353.5	363.8	375.3	393.5	420.1	469.3	541.3	660.3
40°	319.5	320.3	324.7	329.5	335.6	344.5	359.5	380.9	416.9	474.4	561.3
42.5°	298.1	298.9	302.1	306.6	311.3	320.3	332.6	351.2	380.3	425.2	496.9
45°	266.9	266.9	269.7	271.7	277.0	285.1	295.2	310.5	330.8	363.9	411.6
47.5°	237.6	237.7	239.6	243.0	246.4	252.6	262.6	275.1	289.9	315.5	356.2
50°	220.8	221.2	222.4	225.2	227.3	232.9	240.6	251.5	266.9	286.7	320.7
52.5°	207.2	206.9	208.5	209.7	211.1	215.2	220.9	230.5	244.2	261.5	289.6
55°	185.2	183.5	186.0	188.1	189.3	190.8	194.1	200.2	211.9	226.5	247.5
57.5°	157.7	157.1	158.8	160.7	164.5	168.8	171.5	175.4	181.5	191.9	212.8
60°	135.1	135.1	138.7	139.9	144.3	150.0	155.7	158.9	165.0	171.8	187.2
62.5°	115.0	115.3	117.0	118.3	120.7	127.7	135.6	142.8	148.5	155.0	165.2
65°	96.3	97.0	97.0	97.8	99.5	101.1	104.3	110.0	120.1	129.4	137.0
67.5°	81.7	81.9	82.1	82.9	83.4	85.2	86.4	89.0	91.3	100.1	109.6
70°	72.0	73.2	72.8	73.6	74.0	74.8	76.4	77.6	81.3	83.3	89.0
72.5°	62.9	63.8	63.7	64.2	65.3	65.4	66.7	68.0	70.3	72.0	75.0
75°	50.9	50.5	50.9	51.7	52.1	52.6	52.6	54.2	55.4	57.0	59.0
77.5°	39.3	39.7	39.6	39.7	39.8	40.5	40.4	41.2	42.4	43.2	44.1
80°	31.5	31.9	31.5	31.9	32.3	32.7	32.3	32.7	34.0	34.8	34.8
82.5°	24.4	24.5	24.7	24.8	24.9	25.0	25.6	25.7	26.5	26.4	26.7
85°	14.6	14.2	14.2	14.2	14.6	15.0	14.6	14.6	15.0	15.0	15.0
87.5°	6.6	6.9	6.8	6.8	6.8	6.7	6.7	7.0	6.6	6.8	6.4
90°	6.9	6.8	6.7	6.6	6.5	6.3	5.9	5.7	5.4	5.1	4.7
92.5°	6.9	6.8	6.8	6.7	6.7	6.5	6.4	6.3	6.1	5.9	5.7
95°	11.0	11.1	11.1	11.2	11.2	11.1	10.9	10.5	10.3	10.0	9.6
97.5°	14.7	14.7	14.6	14.5	14.4	14.3	14.0	13.9	13.6	13.4	12.4
100°	17.2	17.0	17.0	16.8	16.7	16.4	16.0	15.5	15.1	14.6	13.6
102.5°	18.4	18.2	18.1	17.9	17.7	17.3	16.8	16.2	15.6	15.0	23.1
105°	19.5	19.3	19.0	18.8	18.5	18.1	17.5	16.9	16.2	15.6	31.1
107.5°	20.0	19.8	19.6	19.3	19.1	19.3	20.0	20.6	21.2	21.9	40.5
110°	20.2	20.0	19.8	19.6	19.3	22.0	27.7	33.4	39.1	44.8	61.2



TEST NUMBER: P331675-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	20.4	20.3	20.0	19.9	19.7	30.0	50.8	71.5	92.3	113.0	117.1
115°	21.0	25.1	29.2	33.3	37.4	52.6	79.0	105.4	131.7	158.0	156.6
117.5°	85.8	99.3	112.7	126.2	139.7	149.6	155.9	162.3	168.7	175.1	174.0
120°	156.2	163.9	171.6	179.3	187.0	190.4	189.8	189.1	188.5	187.7	186.7
122.5°	195.0	196.5	198.0	199.5	200.9	201.5	201.1	200.7	200.3	199.9	198.8
125°	219.0	218.8	218.6	218.5	218.3	218.0	217.6	217.2	216.8	216.4	215.3
127.5°	234.2	234.1	234.1	234.1	234.0	233.7	233.1	232.6	232.0	231.4	230.6
130°	243.6	243.7	243.7	243.8	243.8	243.5	242.9	242.2	241.6	241.1	240.4
132.5°	252.8	252.9	252.9	252.9	253.0	252.8	252.2	251.8	251.2	250.6	250.0
135°	266.1	266.3	266.3	266.5	266.6	266.3	265.8	265.2	264.7	264.1	263.6
137.5°	278.3	278.5	278.7	278.8	279.0	278.8	278.3	277.7	277.2	276.6	276.1
140°	285.8	286.1	286.5	286.7	287.0	286.8	286.4	285.8	285.3	284.8	284.2
142.5°	293.2	293.5	293.8	294.1	294.4	294.3	293.8	293.3	292.9	292.4	291.7
145°	303.5	303.8	304.1	304.4	304.7	304.6	304.2	303.8	303.4	303.0	302.1
147.5°	312.6	312.8	313.1	313.3	313.5	313.5	313.2	312.9	312.6	312.4	311.4
150°	318.1	318.4	318.7	319.0	319.2	319.2	318.9	318.5	318.2	317.9	317.0
152.5°	322.8	323.2	323.6	323.9	324.3	324.3	324.0	323.7	323.3	323.0	322.1
155°	329.4	329.9	330.3	330.7	331.2	331.3	330.9	330.6	330.3	329.9	329.2
157.5°	335.4	335.8	336.3	336.7	337.2	337.2	336.8	336.4	336.0	335.6	335.2
160°	338.9	339.3	339.7	340.1	340.5	340.5	340.2	339.8	339.5	339.1	338.8
162.5°	341.7	342.2	342.7	343.2	343.7	343.7	343.3	342.9	342.6	342.2	341.9
165°	346.0	346.4	346.8	347.2	347.6	347.6	347.2	346.8	346.4	346.0	345.9
167.5°	348.7	349.3	349.7	350.3	350.8	350.9	350.5	350.1	349.7	349.3	349.1
170°	350.4	350.9	351.4	352.0	352.4	352.5	352.1	351.7	351.3	350.9	350.8
172.5°	351.6	352.1	352.7	353.2	353.7	353.7	353.3	352.9	352.5	352.1	352.0
175°	352.7	353.2	353.9	354.4	355.0	355.1	354.7	354.3	353.9	353.5	353.4
177.5°	353.4	353.8	354.2	354.6	355.0	355.1	354.7	354.4	354.1	353.8	353.7
180°	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9



TEST NUMBER: P331675-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1191.6	1189.0	1186.8	1180.9	1178.1	1171.6	1170.6	1170.3	1161.8	1153.7	1151.5
5°	1232.6	1226.1	1216.3	1205.0	1193.3	1181.1	1173.1	1166.6	1150.4	1135.0	1126.2
7.5°	1273.7	1259.9	1243.1	1221.7	1203.8	1183.8	1168.9	1155.6	1132.6	1110.6	1095.7
10°	1304.5	1281.8	1259.6	1230.1	1207.0	1184.4	1163.4	1145.2	1119.3	1090.2	1069.5
12.5°	1323.6	1298.7	1268.0	1239.1	1209.3	1180.5	1152.4	1129.0	1098.6	1068.5	1044.0
15°	1349.4	1322.7	1285.5	1244.3	1205.9	1168.2	1135.9	1106.8	1067.1	1031.2	1001.2
17.5°	1370.5	1333.8	1293.8	1246.1	1201.7	1153.8	1112.1	1075.0	1030.9	987.5	952.2
20°	1377.3	1340.9	1294.8	1247.1	1194.5	1138.3	1093.4	1053.0	1005.7	958.4	917.9
22.5°	1373.1	1344.8	1293.5	1236.4	1182.6	1123.7	1073.0	1026.1	973.7	925.3	878.5
25°	1344.6	1334.8	1286.3	1224.0	1162.6	1094.2	1035.6	984.2	924.4	872.7	821.7
27.5°	1277.9	1298.9	1268.8	1202.5	1134.2	1060.9	995.0	936.5	874.4	816.2	765.4
30°	1213.9	1262.0	1249.1	1187.6	1111.2	1039.3	965.3	904.2	837.9	778.0	727.9
32.5°	1126.2	1205.8	1218.4	1167.0	1087.9	1008.8	931.3	870.5	801.3	738.2	689.4
35°	986.7	1105.6	1160.2	1127.4	1048.1	962.8	882.7	812.0	742.4	680.2	631.6
37.5°	820.1	982.1	1073.0	1075.4	1002.6	913.9	826.7	756.5	685.2	624.1	571.6
40°	712.1	887.6	1006.1	1032.4	970.9	875.0	786.9	715.3	645.8	585.9	525.7
42.5°	615.1	789.9	935.6	981.3	932.4	837.2	748.8	673.9	606.3	549.7	488.1
45°	497.4	650.2	810.8	892.5	865.4	777.2	683.8	612.6	549.1	500.2	441.2
47.5°	419.5	527.3	682.6	793.1	792.7	712.2	620.3	552.2	493.3	447.4	399.6
50°	375.3	469.1	600.5	725.9	736.3	668.8	581.5	514.0	459.0	410.8	372.4
52.5°	335.5	412.8	530.9	651.1	681.0	622.6	537.8	475.5	422.1	377.9	344.9
55°	283.4	343.3	433.1	545.5	590.8	549.5	474.4	416.1	372.8	335.6	307.3
57.5°	239.8	284.7	356.7	447.3	499.9	474.0	411.9	364.6	327.6	294.0	271.6
60°	212.3	249.1	310.1	385.8	444.0	425.8	372.8	328.8	297.2	268.1	247.1
62.5°	186.4	218.0	270.4	331.8	385.2	377.6	334.3	297.4	269.7	243.2	225.4
65°	150.0	173.1	213.9	262.1	304.9	308.6	277.4	252.3	227.7	206.6	190.8
67.5°	119.5	134.5	163.3	203.8	235.9	247.4	228.4	209.2	189.6	173.4	159.7
70°	100.7	112.8	133.9	166.6	196.1	208.3	197.3	182.4	165.4	152.0	140.3
72.5°	81.6	93.4	108.9	132.9	158.3	171.3	167.5	156.9	143.1	132.0	120.9
75°	61.5	65.1	75.7	91.8	111.6	122.9	125.8	120.1	109.2	100.7	94.2
77.5°	45.5	47.6	52.7	61.2	74.1	84.2	88.3	87.7	80.2	75.2	69.2
80°	36.4	37.6	40.0	43.6	53.4	63.5	66.3	66.3	61.1	59.0	53.0
82.5°	27.6	28.5	30.0	32.0	36.5	45.4	48.6	49.2	45.9	43.2	38.4
85°	15.8	15.4	16.2	17.3	18.2	20.6	25.5	26.3	25.5	22.3	21.0
87.5°	6.3	6.6	6.5	6.0	6.3	6.4	7.9	9.4	8.2	7.4	6.9
90°	4.2	3.7	3.3	2.8	2.1	1.5	0.9	0.2	0.9	1.5	2.1
92.5°	5.5	5.2	5.1	4.9	5.0	5.1	5.1	5.1	5.1	5.1	5.0
95°	9.2	8.8	8.4	9.1	11.0	12.9	14.7	16.6	14.7	12.9	11.0
97.5°	11.5	10.6	9.7	11.9	17.2	22.4	27.7	33.0	27.7	22.4	17.2
100°	12.7	11.7	10.7	14.2	21.9	29.7	37.5	45.3	37.5	29.7	21.9
102.5°	31.2	39.3	47.4	52.3	53.9	55.5	57.2	58.9	57.2	55.5	53.9
105°	46.7	62.3	77.8	84.7	83.0	81.3	79.5	77.9	79.5	81.3	83.0
107.5°	59.2	77.8	96.4	105.0	103.7	102.3	100.9	99.5	100.9	102.3	103.7
110°	77.7	94.2	110.6	118.3	117.1	115.9	114.6	113.4	114.6	115.9	117.1





TEST NUMBER: P331675-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	121.2	125.2	129.3	130.8	129.8	128.7	127.6	126.6	127.6	128.7	129.8
115°	155.2	153.8	152.3	151.1	150.2	149.2	148.2	147.3	148.2	149.2	150.2
117.5°	173.1	172.1	171.1	170.1	169.1	167.9	166.8	165.8	166.8	167.9	169.1
120°	185.7	184.7	183.6	182.7	181.9	181.0	180.1	179.3	180.1	181.0	181.9
122.5°	197.6	196.5	195.4	194.4	193.5	192.6	191.7	190.8	191.7	192.6	193.5
125°	214.3	213.2	212.1	211.2	210.5	209.7	209.0	208.3	209.0	209.7	210.5
127.5°	229.8	228.9	228.1	227.4	226.6	225.7	224.9	224.0	224.9	225.7	226.6
130°	239.8	239.2	238.5	237.7	236.9	235.9	235.0	234.1	235.0	235.9	236.9
132.5°	249.4	248.7	248.1	247.5	246.7	245.9	245.1	244.4	245.1	245.9	246.7
135°	263.1	262.5	262.1	261.3	260.4	259.5	258.6	257.7	258.6	259.5	260.4
137.5°	275.4	274.9	274.3	273.7	273.1	272.4	271.8	271.2	271.8	272.4	273.1
140°	283.6	283.0	282.3	281.8	281.3	280.8	280.4	280.0	280.4	280.8	281.3
142.5°	291.0	290.3	289.5	289.0	288.6	288.1	287.7	287.3	287.7	288.1	288.6
145°	301.1	300.1	299.1	298.7	298.7	298.8	298.9	298.9	298.9	298.8	298.7
147.5°	310.5	309.4	308.5	308.2	308.3	308.6	308.8	309.0	308.8	308.6	308.3
150°	316.1	315.1	314.3	313.9	314.3	314.7	315.1	315.5	315.1	314.7	314.3
152.5°	321.2	320.4	319.5	319.3	319.7	320.2	320.7	321.1	320.7	320.2	319.7
155°	328.5	327.9	327.2	327.1	327.6	328.1	328.6	329.2	328.6	328.1	327.6
157.5°	334.7	334.2	333.7	333.7	334.1	334.5	335.0	335.4	335.0	334.5	334.1
160°	338.4	338.1	337.8	337.8	338.1	338.4	338.8	339.1	338.8	338.4	338.1
162.5°	341.6	341.3	341.0	341.0	341.4	341.7	342.1	342.4	342.1	341.7	341.4
165°	345.7	345.5	345.4	345.5	345.8	346.1	346.5	346.8	346.5	346.1	345.8
167.5°	349.0	348.8	348.6	348.7	349.0	349.4	349.7	350.1	349.7	349.4	349.0
170°	350.7	350.5	350.5	350.5	350.9	351.3	351.6	352.0	351.6	351.3	350.9
172.5°	351.9	351.8	351.6	351.8	352.1	352.4	352.8	353.2	352.8	352.4	352.1
175°	353.2	353.2	353.0	353.2	353.6	353.9	354.3	354.7	354.3	353.9	353.6
177.5°	353.7	353.6	353.6	353.7	354.0	354.3	354.7	355.0	354.7	354.3	354.0
180°	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9



TEST NUMBER: P331675-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1147.3	1145.0	1140.8	1134.3	1130.4	1123.6	1119.1	1121.7	1122.4	1121.7	1121.1
5°	1116.5	1107.9	1096.2	1084.9	1074.4	1063.1	1056.6	1053.8	1048.1	1044.9	1043.3
7.5°	1079.2	1064.5	1048.0	1028.3	1011.5	994.0	985.0	980.5	968.9	962.7	957.1
10°	1051.4	1028.3	1011.8	985.9	970.1	947.1	931.3	931.7	915.9	907.0	900.6
12.5°	1020.6	995.3	967.7	944.4	922.5	904.0	885.0	877.3	860.5	852.0	834.6
15°	969.7	940.2	911.1	879.5	857.3	828.5	801.1	767.5	740.4	716.9	710.5
17.5°	914.0	877.5	848.3	811.3	773.2	724.8	693.0	673.5	657.2	644.8	635.6
20°	875.8	838.7	807.6	751.7	700.4	667.7	644.2	629.2	612.2	598.9	591.6
22.5°	835.8	796.9	754.5	692.2	652.2	625.9	605.0	587.8	576.3	565.9	559.3
25°	778.8	736.3	666.4	623.5	591.2	563.7	549.1	538.6	526.5	512.3	505.9
27.5°	718.7	651.1	600.9	569.0	538.1	520.2	507.2	491.5	480.6	474.3	467.5
30°	673.7	606.2	567.0	532.2	510.3	490.5	475.2	466.3	455.7	444.8	440.4
32.5°	623.5	569.6	532.0	503.0	480.9	464.0	451.9	437.4	429.8	423.1	413.8
35°	561.3	520.5	486.1	462.6	441.6	427.9	413.7	405.2	391.4	385.8	382.1
37.5°	508.5	473.1	447.5	422.7	406.1	390.9	382.2	368.7	362.7	354.9	347.2
40°	478.8	444.0	419.3	399.1	380.5	369.2	358.3	347.4	338.4	334.9	325.5
42.5°	448.4	420.1	395.4	373.2	360.8	348.8	335.0	327.0	317.7	311.9	306.1
45°	406.4	381.4	360.3	342.1	328.4	315.8	306.9	293.6	288.4	276.6	271.7
47.5°	369.6	346.2	326.1	308.9	295.4	287.2	274.3	263.8	255.4	248.2	242.0
50°	343.3	323.9	304.5	289.1	277.0	265.3	251.9	246.7	233.7	230.0	226.5
52.5°	319.4	301.0	283.1	268.1	256.0	244.5	232.8	225.9	217.2	213.6	211.0
55°	285.9	268.1	251.1	237.7	225.6	213.9	206.6	198.1	194.1	191.2	188.1
57.5°	252.2	236.2	223.2	209.7	197.5	188.2	179.7	174.7	170.5	166.8	162.9
60°	230.9	215.6	203.8	191.2	178.7	171.0	164.6	158.5	153.7	148.0	146.4
62.5°	208.3	194.8	184.1	171.8	161.0	153.9	147.7	142.0	136.2	127.9	125.6
65°	177.1	166.6	155.3	145.2	135.5	128.6	119.7	113.2	110.8	110.0	109.6
67.5°	149.0	139.0	129.3	119.0	110.1	103.8	99.3	98.2	96.6	96.1	95.0
70°	130.2	120.9	111.2	101.5	93.0	91.8	90.2	88.6	86.5	85.7	84.9
72.5°	113.4	103.8	94.0	86.3	82.6	81.1	79.5	77.9	76.5	75.7	75.2
75°	86.9	78.0	71.6	68.8	66.7	65.5	63.1	61.9	61.1	59.8	59.4
77.5°	62.6	57.6	54.6	52.8	50.7	49.4	48.0	46.8	45.9	45.7	45.1
80°	47.7	45.3	43.3	40.9	40.0	38.4	38.0	36.8	37.2	36.0	36.0
82.5°	37.1	34.0	32.2	31.1	30.3	29.1	28.6	28.0	28.1	27.3	27.3
85°	19.0	18.2	17.3	16.6	16.6	15.4	15.8	15.4	15.4	14.6	14.2
87.5°	6.7	6.5	5.9	6.0	6.1	5.9	5.9	5.7	5.7	5.8	5.5
90°	2.8	3.3	3.7	4.2	4.7	5.1	5.4	5.7	5.9	6.3	6.5
92.5°	4.9	5.1	5.2	5.5	5.7	5.9	6.1	6.3	6.4	6.5	6.7
95°	9.1	8.4	8.8	9.2	9.6	10.0	10.3	10.5	10.9	11.1	11.2
97.5°	11.9	9.7	10.6	11.5	12.4	13.4	13.6	13.9	14.0	14.3	14.4
100°	14.2	10.7	11.7	12.7	13.6	14.6	15.1	15.5	16.0	16.4	16.7
102.5°	52.3	47.4	39.3	31.2	23.1	15.0	15.6	16.2	16.8	17.3	17.7
105°	84.7	77.8	62.3	46.7	31.1	15.6	16.2	16.9	17.5	18.1	18.5
107.5°	105.0	96.4	77.8	59.2	40.5	21.9	21.2	20.6	20.0	19.3	19.1
110°	118.3	110.6	94.2	77.7	61.2	44.8	39.1	33.4	27.7	22.0	19.3



TEST NUMBER: P331675-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	130.8	129.3	125.2	121.2	117.1	113.0	92.3	71.5	50.8	30.0	19.7
115°	151.1	152.3	153.8	155.2	156.6	158.0	131.7	105.4	79.0	52.6	37.4
117.5°	170.1	171.1	172.1	173.1	174.0	175.1	168.7	162.3	155.9	149.6	139.7
120°	182.7	183.6	184.7	185.7	186.7	187.7	188.5	189.1	189.8	190.4	187.0
122.5°	194.4	195.4	196.5	197.6	198.8	199.9	200.3	200.7	201.1	201.5	200.9
125°	211.2	212.1	213.2	214.3	215.3	216.4	216.8	217.2	217.6	218.0	218.3
127.5°	227.4	228.1	228.9	229.8	230.6	231.4	232.0	232.6	233.1	233.7	234.0
130°	237.7	238.5	239.2	239.8	240.4	241.1	241.6	242.2	242.9	243.5	243.8
132.5°	247.5	248.1	248.7	249.4	250.0	250.6	251.2	251.8	252.2	252.8	253.0
135°	261.3	262.1	262.5	263.1	263.6	264.1	264.7	265.2	265.8	266.3	266.6
137.5°	273.7	274.3	274.9	275.4	276.1	276.6	277.2	277.7	278.3	278.8	279.0
140°	281.8	282.3	283.0	283.6	284.2	284.8	285.3	285.8	286.4	286.8	287.0
142.5°	289.0	289.5	290.3	291.0	291.7	292.4	292.9	293.3	293.8	294.3	294.4
145°	298.7	299.1	300.1	301.1	302.1	303.0	303.4	303.8	304.2	304.6	304.7
147.5°	308.2	308.5	309.4	310.5	311.4	312.4	312.6	312.9	313.2	313.5	313.5
150°	313.9	314.3	315.1	316.1	317.0	317.9	318.2	318.5	318.9	319.2	319.2
152.5°	319.3	319.5	320.4	321.2	322.1	323.0	323.3	323.7	324.0	324.3	324.3
155°	327.1	327.2	327.9	328.5	329.2	329.9	330.3	330.6	330.9	331.3	331.2
157.5°	333.7	333.7	334.2	334.7	335.2	335.6	336.0	336.4	336.8	337.2	337.2
160°	337.8	337.8	338.1	338.4	338.8	339.1	339.5	339.8	340.2	340.5	340.5
162.5°	341.0	341.0	341.3	341.6	341.9	342.2	342.6	342.9	343.3	343.7	343.7
165°	345.5	345.4	345.5	345.7	345.9	346.0	346.4	346.8	347.2	347.6	347.6
167.5°	348.7	348.6	348.8	349.0	349.1	349.3	349.7	350.1	350.5	350.9	350.8
170°	350.5	350.5	350.5	350.7	350.8	350.9	351.3	351.7	352.1	352.5	352.4
172.5°	351.8	351.6	351.8	351.9	352.0	352.1	352.5	352.9	353.3	353.7	353.7
175°	353.2	353.0	353.2	353.2	353.4	353.5	353.9	354.3	354.7	355.1	355.0
177.5°	353.7	353.6	353.6	353.7	353.7	353.8	354.1	354.4	354.7	355.1	355.0
180°	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9



TEST NUMBER: P331675-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1117.5	1118.2	1117.2	1117.8	1117.2	1118.2	1117.5	1121.1	1121.7	1122.4	1121.7
5°	1041.2	1036.4	1035.6	1034.4	1035.6	1036.4	1041.2	1043.3	1044.9	1048.1	1053.8
7.5°	950.2	949.4	947.5	944.6	947.5	949.4	950.2	957.1	962.7	968.9	980.5
10°	891.6	889.6	889.2	886.4	889.2	889.6	891.6	900.6	907.0	915.9	931.7
12.5°	823.1	810.0	808.7	801.6	808.7	810.0	823.1	834.6	852.0	860.5	877.3
15°	700.8	698.4	690.2	685.0	690.2	698.4	700.8	710.5	716.9	740.4	767.5
17.5°	630.9	623.0	620.4	619.3	620.4	623.0	630.9	635.6	644.8	657.2	673.5
20°	585.9	578.7	577.4	576.6	577.4	578.7	585.9	591.6	598.9	612.2	629.2
22.5°	554.8	547.2	544.2	541.7	544.2	547.2	554.8	559.3	565.9	576.3	587.8
25°	501.8	499.0	497.4	496.5	497.4	499.0	501.8	505.9	512.3	526.5	538.6
27.5°	460.3	454.1	452.9	450.8	452.9	454.1	460.3	467.5	474.3	480.6	491.5
30°	436.7	434.7	431.9	429.4	431.9	434.7	436.7	440.4	444.8	455.7	466.3
32.5°	408.9	407.2	404.7	403.5	404.7	407.2	408.9	413.8	423.1	429.8	437.4
35°	378.1	372.4	370.0	366.4	370.0	372.4	378.1	382.1	385.8	391.4	405.2
37.5°	345.5	342.5	339.1	340.3	339.1	342.5	345.5	347.2	354.9	362.7	368.7
40°	320.3	318.2	317.4	317.0	317.4	318.2	320.3	325.5	334.9	338.4	347.4
42.5°	300.2	294.6	292.6	292.5	292.6	294.6	300.2	306.1	311.9	317.7	327.0
45°	269.7	264.4	260.8	261.3	260.8	264.4	269.7	271.7	276.6	288.4	293.6
47.5°	238.5	238.4	236.1	236.8	236.1	238.4	238.5	242.0	248.2	255.4	263.8
50°	223.6	221.2	219.6	220.0	219.6	221.2	223.6	226.5	230.0	233.7	246.7
52.5°	209.4	207.3	206.0	207.7	206.0	207.3	209.4	211.0	213.6	217.2	225.9
55°	186.0	183.5	183.2	182.8	183.2	183.5	186.0	188.1	191.2	194.1	198.1
57.5°	159.9	158.3	155.8	154.8	155.8	158.3	159.9	162.9	166.8	170.5	174.7
60°	141.1	137.9	133.9	133.4	133.9	137.9	141.1	146.4	148.0	153.7	158.5
62.5°	124.0	123.3	122.6	122.5	122.6	123.3	124.0	125.6	127.9	136.2	142.0
65°	108.8	108.4	108.8	109.2	108.8	108.4	108.8	109.6	110.0	110.8	113.2
67.5°	94.8	94.0	93.3	93.6	93.3	94.0	94.8	95.0	96.1	96.6	98.2
70°	84.1	83.7	83.3	83.3	83.3	83.7	84.1	84.9	85.7	86.5	88.6
72.5°	73.8	73.7	73.3	73.0	73.3	73.7	73.8	75.2	75.7	76.5	77.9
75°	59.0	58.2	58.2	58.2	58.2	58.2	59.0	59.4	59.8	61.1	61.9
77.5°	45.0	44.6	44.1	43.8	44.1	44.6	45.0	45.1	45.7	45.9	46.8
80°	35.6	35.2	34.8	34.8	34.8	35.2	35.6	36.0	36.0	37.2	36.8
82.5°	27.2	26.8	26.7	26.4	26.7	26.8	27.2	27.3	27.3	28.1	28.0
85°	14.6	15.0	14.6	15.4	14.6	15.0	14.6	14.2	14.6	15.4	15.4
87.5°	5.5	5.2	5.5	5.2	5.5	5.2	5.5	5.5	5.8	5.7	5.7
90°	6.6	6.7	6.8	6.9	6.8	6.7	6.6	6.5	6.3	5.9	5.7
92.5°	6.7	6.8	6.8	6.9	6.8	6.8	6.7	6.7	6.5	6.4	6.3
95°	11.2	11.1	11.1	11.0	11.1	11.1	11.2	11.2	11.1	10.9	10.5
97.5°	14.5	14.6	14.7	14.7	14.7	14.6	14.5	14.4	14.3	14.0	13.9
100°	16.8	17.0	17.0	17.2	17.0	17.0	16.8	16.7	16.4	16.0	15.5
102.5°	17.9	18.1	18.2	18.4	18.2	18.1	17.9	17.7	17.3	16.8	16.2
105°	18.8	19.0	19.3	19.5	19.3	19.0	18.8	18.5	18.1	17.5	16.9
107.5°	19.3	19.6	19.8	20.0	19.8	19.6	19.3	19.1	19.3	20.0	20.6
110°	19.6	19.8	20.0	20.2	20.0	19.8	19.6	19.3	22.0	27.7	33.4



TEST NUMBER: P331675-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	19.9	20.0	20.3	20.4	20.3	20.0	19.9	19.7	30.0	50.8	71.5
115°	33.3	29.2	25.1	21.0	25.1	29.2	33.3	37.4	52.6	79.0	105.4
117.5°	126.2	112.7	99.3	85.8	99.3	112.7	126.2	139.7	149.6	155.9	162.3
120°	179.3	171.6	163.9	156.2	163.9	171.6	179.3	187.0	190.4	189.8	189.1
122.5°	199.5	198.0	196.5	195.0	196.5	198.0	199.5	200.9	201.5	201.1	200.7
125°	218.5	218.6	218.8	219.0	218.8	218.6	218.5	218.3	218.0	217.6	217.2
127.5°	234.1	234.1	234.1	234.2	234.1	234.1	234.1	234.0	233.7	233.1	232.6
130°	243.8	243.7	243.7	243.6	243.7	243.7	243.8	243.8	243.5	242.9	242.2
132.5°	252.9	252.9	252.9	252.8	252.9	252.9	252.9	253.0	252.8	252.2	251.8
135°	266.5	266.3	266.3	266.1	266.3	266.3	266.5	266.6	266.3	265.8	265.2
137.5°	278.8	278.7	278.5	278.3	278.5	278.7	278.8	279.0	278.8	278.3	277.7
140°	286.7	286.5	286.1	285.8	286.1	286.5	286.7	287.0	286.8	286.4	285.8
142.5°	294.1	293.8	293.5	293.2	293.5	293.8	294.1	294.4	294.3	293.8	293.3
145°	304.4	304.1	303.8	303.5	303.8	304.1	304.4	304.7	304.6	304.2	303.8
147.5°	313.3	313.1	312.8	312.6	312.8	313.1	313.3	313.5	313.5	313.2	312.9
150°	319.0	318.7	318.4	318.1	318.4	318.7	319.0	319.2	319.2	318.9	318.5
152.5°	323.9	323.6	323.2	322.8	323.2	323.6	323.9	324.3	324.3	324.0	323.7
155°	330.7	330.3	329.9	329.4	329.9	330.3	330.7	331.2	331.3	330.9	330.6
157.5°	336.7	336.3	335.8	335.4	335.8	336.3	336.7	337.2	337.2	336.8	336.4
160°	340.1	339.7	339.3	338.9	339.3	339.7	340.1	340.5	340.5	340.2	339.8
162.5°	343.2	342.7	342.2	341.7	342.2	342.7	343.2	343.7	343.7	343.3	342.9
165°	347.2	346.8	346.4	346.0	346.4	346.8	347.2	347.6	347.6	347.2	346.8
167.5°	350.3	349.7	349.3	348.7	349.3	349.7	350.3	350.8	350.9	350.5	350.1
170°	352.0	351.4	350.9	350.4	350.9	351.4	352.0	352.4	352.5	352.1	351.7
172.5°	353.2	352.7	352.1	351.6	352.1	352.7	353.2	353.7	353.7	353.3	352.9
175°	354.4	353.9	353.2	352.7	353.2	353.9	354.4	355.0	355.1	354.7	354.3
177.5°	354.6	354.2	353.8	353.4	353.8	354.2	354.6	355.0	355.1	354.7	354.4
180°	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9



TEST NUMBER: P331675-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1119.1	1123.6	1130.4	1134.3	1140.8	1145.0	1147.3	1151.5	1153.7	1161.8	1170.3
5°	1056.6	1063.1	1074.4	1084.9	1096.2	1107.9	1116.5	1126.2	1135.0	1150.4	1166.6
7.5°	985.0	994.0	1011.5	1028.3	1048.0	1064.5	1079.2	1095.7	1110.6	1132.6	1155.6
10°	931.3	947.1	970.1	985.9	1011.8	1028.3	1051.4	1069.5	1090.2	1119.3	1145.2
12.5°	885.0	904.0	922.5	944.4	967.7	995.3	1020.6	1044.0	1068.5	1098.6	1129.0
15°	801.1	828.5	857.3	879.5	911.1	940.2	969.7	1001.2	1031.2	1067.1	1106.8
17.5°	693.0	724.8	773.2	811.3	848.3	877.5	914.0	952.2	987.5	1030.9	1075.0
20°	644.2	667.7	700.4	751.7	807.6	838.7	875.8	917.9	958.4	1005.7	1053.0
22.5°	605.0	625.9	652.2	692.2	754.5	796.9	835.8	878.5	925.3	973.7	1026.1
25°	549.1	563.7	591.2	623.5	666.4	736.3	778.8	821.7	872.7	924.4	984.2
27.5°	507.2	520.2	538.1	569.0	600.9	651.1	718.7	765.4	816.2	874.4	936.5
30°	475.2	490.5	510.3	532.2	567.0	606.2	673.7	727.9	778.0	837.9	904.2
32.5°	451.9	464.0	480.9	503.0	532.0	569.6	623.5	689.4	738.2	801.3	870.5
35°	413.7	427.9	441.6	462.6	486.1	520.5	561.3	631.6	680.2	742.4	812.0
37.5°	382.2	390.9	406.1	422.7	447.5	473.1	508.5	571.6	624.1	685.2	756.5
40°	358.3	369.2	380.5	399.1	419.3	444.0	478.8	525.7	585.9	645.8	715.3
42.5°	335.0	348.8	360.8	373.2	395.4	420.1	448.4	488.1	549.7	606.3	673.9
45°	306.9	315.8	328.4	342.1	360.3	381.4	406.4	441.2	500.2	549.1	612.6
47.5°	274.3	287.2	295.4	308.9	326.1	346.2	369.6	399.6	447.4	493.3	552.2
50°	251.9	265.3	277.0	289.1	304.5	323.9	343.3	372.4	410.8	459.0	514.0
52.5°	232.8	244.5	256.0	268.1	283.1	301.0	319.4	344.9	377.9	422.1	475.5
55°	206.6	213.9	225.6	237.7	251.1	268.1	285.9	307.3	335.6	372.8	416.1
57.5°	179.7	188.2	197.5	209.7	223.2	236.2	252.2	271.6	294.0	327.6	364.6
60°	164.6	171.0	178.7	191.2	203.8	215.6	230.9	247.1	268.1	297.2	328.8
62.5°	147.7	153.9	161.0	171.8	184.1	194.8	208.3	225.4	243.2	269.7	297.4
65°	119.7	128.6	135.5	145.2	155.3	166.6	177.1	190.8	206.6	227.7	252.3
67.5°	99.3	103.8	110.1	119.0	129.3	139.0	149.0	159.7	173.4	189.6	209.2
70°	90.2	91.8	93.0	101.5	111.2	120.9	130.2	140.3	152.0	165.4	182.4
72.5°	79.5	81.1	82.6	86.3	94.0	103.8	113.4	120.9	132.0	143.1	156.9
75°	63.1	65.5	66.7	68.8	71.6	78.0	86.9	94.2	100.7	109.2	120.1
77.5°	48.0	49.4	50.7	52.8	54.6	57.6	62.6	69.2	75.2	80.2	87.7
80°	38.0	38.4	40.0	40.9	43.3	45.3	47.7	53.0	59.0	61.1	66.3
82.5°	28.6	29.1	30.3	31.1	32.2	34.0	37.1	38.4	43.2	45.9	49.2
85°	15.8	15.4	16.6	16.6	17.3	18.2	19.0	21.0	22.3	25.5	26.3
87.5°	5.9	5.9	6.1	6.0	5.9	6.5	6.7	6.9	7.4	8.2	9.4
90°	5.4	5.1	4.7	4.2	3.7	3.3	2.8	2.1	1.5	0.9	0.2
92.5°	6.1	5.9	5.7	5.5	5.2	5.1	4.9	5.0	5.1	5.1	5.1
95°	10.3	10.0	9.6	9.2	8.8	8.4	9.1	11.0	12.9	14.7	16.6
97.5°	13.6	13.4	12.4	11.5	10.6	9.7	11.9	17.2	22.4	27.7	33.0
100°	15.1	14.6	13.6	12.7	11.7	10.7	14.2	21.9	29.7	37.5	45.3
102.5°	15.6	15.0	23.1	31.2	39.3	47.4	52.3	53.9	55.5	57.2	58.9
105°	16.2	15.6	31.1	46.7	62.3	77.8	84.7	83.0	81.3	79.5	77.9
107.5°	21.2	21.9	40.5	59.2	77.8	96.4	105.0	103.7	102.3	100.9	99.5
110°	39.1	44.8	61.2	77.7	94.2	110.6	118.3	117.1	115.9	114.6	113.4



TEST NUMBER: P331675-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	92.3	113.0	117.1	121.2	125.2	129.3	130.8	129.8	128.7	127.6	126.6
115°	131.7	158.0	156.6	155.2	153.8	152.3	151.1	150.2	149.2	148.2	147.3
117.5°	168.7	175.1	174.0	173.1	172.1	171.1	170.1	169.1	167.9	166.8	165.8
120°	188.5	187.7	186.7	185.7	184.7	183.6	182.7	181.9	181.0	180.1	179.3
122.5°	200.3	199.9	198.8	197.6	196.5	195.4	194.4	193.5	192.6	191.7	190.8
125°	216.8	216.4	215.3	214.3	213.2	212.1	211.2	210.5	209.7	209.0	208.3
127.5°	232.0	231.4	230.6	229.8	228.9	228.1	227.4	226.6	225.7	224.9	224.0
130°	241.6	241.1	240.4	239.8	239.2	238.5	237.7	236.9	235.9	235.0	234.1
132.5°	251.2	250.6	250.0	249.4	248.7	248.1	247.5	246.7	245.9	245.1	244.4
135°	264.7	264.1	263.6	263.1	262.5	262.1	261.3	260.4	259.5	258.6	257.7
137.5°	277.2	276.6	276.1	275.4	274.9	274.3	273.7	273.1	272.4	271.8	271.2
140°	285.3	284.8	284.2	283.6	283.0	282.3	281.8	281.3	280.8	280.4	280.0
142.5°	292.9	292.4	291.7	291.0	290.3	289.5	289.0	288.6	288.1	287.7	287.3
145°	303.4	303.0	302.1	301.1	300.1	299.1	298.7	298.7	298.8	298.9	298.9
147.5°	312.6	312.4	311.4	310.5	309.4	308.5	308.2	308.3	308.6	308.8	309.0
150°	318.2	317.9	317.0	316.1	315.1	314.3	313.9	314.3	314.7	315.1	315.5
152.5°	323.3	323.0	322.1	321.2	320.4	319.5	319.3	319.7	320.2	320.7	321.1
155°	330.3	329.9	329.2	328.5	327.9	327.2	327.1	327.6	328.1	328.6	329.2
157.5°	336.0	335.6	335.2	334.7	334.2	333.7	333.7	334.1	334.5	335.0	335.4
160°	339.5	339.1	338.8	338.4	338.1	337.8	337.8	338.1	338.4	338.8	339.1
162.5°	342.6	342.2	341.9	341.6	341.3	341.0	341.0	341.4	341.7	342.1	342.4
165°	346.4	346.0	345.9	345.7	345.5	345.4	345.5	345.8	346.1	346.5	346.8
167.5°	349.7	349.3	349.1	349.0	348.8	348.6	348.7	349.0	349.4	349.7	350.1
170°	351.3	350.9	350.8	350.7	350.5	350.5	350.5	350.9	351.3	351.6	352.0
172.5°	352.5	352.1	352.0	351.9	351.8	351.6	351.8	352.1	352.4	352.8	353.2
175°	353.9	353.5	353.4	353.2	353.2	353.0	353.2	353.6	353.9	354.3	354.7
177.5°	354.1	353.8	353.7	353.7	353.6	353.6	353.7	354.0	354.3	354.7	355.0
180°	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9



TEST NUMBER: P331675-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1170.6	1171.6	1178.1	1180.9	1186.8	1189.0	1191.6	1191.0	1191.0	1192.2	1201.3
5°	1173.1	1181.1	1193.3	1205.0	1216.3	1226.1	1232.6	1239.0	1241.4	1253.2	1263.7
7.5°	1168.9	1183.8	1203.8	1221.7	1243.1	1259.9	1273.7	1286.3	1294.9	1311.9	1329.4
10°	1163.4	1184.4	1207.0	1230.1	1259.6	1281.8	1304.5	1321.9	1327.5	1353.0	1367.6
12.5°	1152.4	1180.5	1209.3	1239.1	1268.0	1298.7	1323.6	1341.0	1360.9	1383.8	1410.6
15°	1135.9	1168.2	1205.9	1244.3	1285.5	1322.7	1349.4	1379.7	1401.5	1426.6	1450.1
17.5°	1112.1	1153.8	1201.7	1246.1	1293.8	1333.8	1370.5	1399.6	1415.0	1429.3	1432.7
20°	1093.4	1138.3	1194.5	1247.1	1294.8	1340.9	1377.3	1401.5	1405.6	1406.0	1384.6
22.5°	1073.0	1123.7	1182.6	1236.4	1293.5	1344.8	1373.1	1383.5	1367.4	1340.0	1298.5
25°	1035.6	1094.2	1162.6	1224.0	1286.3	1334.8	1344.6	1326.4	1270.1	1211.1	1136.3
27.5°	995.0	1060.9	1134.2	1202.5	1268.8	1298.9	1277.9	1212.4	1111.1	1023.1	916.5
30°	965.3	1039.3	1111.2	1187.6	1249.1	1262.0	1213.9	1117.3	999.2	866.6	760.3
32.5°	931.3	1008.8	1087.9	1167.0	1218.4	1205.8	1126.2	1007.3	868.9	738.5	637.9
35°	882.7	962.8	1048.1	1127.4	1160.2	1105.6	986.7	831.8	690.2	568.5	499.4
37.5°	826.7	913.9	1002.6	1075.4	1073.0	982.1	820.1	660.3	541.3	469.3	420.1
40°	786.9	875.0	970.9	1032.4	1006.1	887.6	712.1	561.3	474.4	416.9	380.9
42.5°	748.8	837.2	932.4	981.3	935.6	789.9	615.1	496.9	425.2	380.3	351.2
45°	683.8	777.2	865.4	892.5	810.8	650.2	497.4	411.6	363.9	330.8	310.5
47.5°	620.3	712.2	792.7	793.1	682.6	527.3	419.5	356.2	315.5	289.9	275.1
50°	581.5	668.8	736.3	725.9	600.5	469.1	375.3	320.7	286.7	266.9	251.5
52.5°	537.8	622.6	681.0	651.1	530.9	412.8	335.5	289.6	261.5	244.2	230.5
55°	474.4	549.5	590.8	545.5	433.1	343.3	283.4	247.5	226.5	211.9	200.2
57.5°	411.9	474.0	499.9	447.3	356.7	284.7	239.8	212.8	191.9	181.5	175.4
60°	372.8	425.8	444.0	385.8	310.1	249.1	212.3	187.2	171.8	165.0	158.9
62.5°	334.3	377.6	385.2	331.8	270.4	218.0	186.4	165.2	155.0	148.5	142.8
65°	277.4	308.6	304.9	262.1	213.9	173.1	150.0	137.0	129.4	120.1	110.0
67.5°	228.4	247.4	235.9	203.8	163.3	134.5	119.5	109.6	100.1	91.3	89.0
70°	197.3	208.3	196.1	166.6	133.9	112.8	100.7	89.0	83.3	81.3	77.6
72.5°	167.5	171.3	158.3	132.9	108.9	93.4	81.6	75.0	72.0	70.3	68.0
75°	125.8	122.9	111.6	91.8	75.7	65.1	61.5	59.0	57.0	55.4	54.2
77.5°	88.3	84.2	74.1	61.2	52.7	47.6	45.5	44.1	43.2	42.4	41.2
80°	66.3	63.5	53.4	43.6	40.0	37.6	36.4	34.8	34.8	34.0	32.7
82.5°	48.6	45.4	36.5	32.0	30.0	28.5	27.6	26.7	26.4	26.5	25.7
85°	25.5	20.6	18.2	17.3	16.2	15.4	15.8	15.0	15.0	15.0	14.6
87.5°	7.9	6.4	6.3	6.0	6.5	6.6	6.3	6.4	6.8	6.6	7.0
90°	0.9	1.5	2.1	2.8	3.3	3.7	4.2	4.7	5.1	5.4	5.7
92.5°	5.1	5.1	5.0	4.9	5.1	5.2	5.5	5.7	5.9	6.1	6.3
95°	14.7	12.9	11.0	9.1	8.4	8.8	9.2	9.6	10.0	10.3	10.5
97.5°	27.7	22.4	17.2	11.9	9.7	10.6	11.5	12.4	13.4	13.6	13.9
100°	37.5	29.7	21.9	14.2	10.7	11.7	12.7	13.6	14.6	15.1	15.5
102.5°	57.2	55.5	53.9	52.3	47.4	39.3	31.2	23.1	15.0	15.6	16.2
105°	79.5	81.3	83.0	84.7	77.8	62.3	46.7	31.1	15.6	16.2	16.9
107.5°	100.9	102.3	103.7	105.0	96.4	77.8	59.2	40.5	21.9	21.2	20.6
110°	114.6	115.9	117.1	118.3	110.6	94.2	77.7	61.2	44.8	39.1	33.4





TEST NUMBER: P331675-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	127.6	128.7	129.8	130.8	129.3	125.2	121.2	117.1	113.0	92.3	71.5
115°	148.2	149.2	150.2	151.1	152.3	153.8	155.2	156.6	158.0	131.7	105.4
117.5°	166.8	167.9	169.1	170.1	171.1	172.1	173.1	174.0	175.1	168.7	162.3
120°	180.1	181.0	181.9	182.7	183.6	184.7	185.7	186.7	187.7	188.5	189.1
122.5°	191.7	192.6	193.5	194.4	195.4	196.5	197.6	198.8	199.9	200.3	200.7
125°	209.0	209.7	210.5	211.2	212.1	213.2	214.3	215.3	216.4	216.8	217.2
127.5°	224.9	225.7	226.6	227.4	228.1	228.9	229.8	230.6	231.4	232.0	232.6
130°	235.0	235.9	236.9	237.7	238.5	239.2	239.8	240.4	241.1	241.6	242.2
132.5°	245.1	245.9	246.7	247.5	248.1	248.7	249.4	250.0	250.6	251.2	251.8
135°	258.6	259.5	260.4	261.3	262.1	262.5	263.1	263.6	264.1	264.7	265.2
137.5°	271.8	272.4	273.1	273.7	274.3	274.9	275.4	276.1	276.6	277.2	277.7
140°	280.4	280.8	281.3	281.8	282.3	283.0	283.6	284.2	284.8	285.3	285.8
142.5°	287.7	288.1	288.6	289.0	289.5	290.3	291.0	291.7	292.4	292.9	293.3
145°	298.9	298.8	298.7	298.7	299.1	300.1	301.1	302.1	303.0	303.4	303.8
147.5°	308.8	308.6	308.3	308.2	308.5	309.4	310.5	311.4	312.4	312.6	312.9
150°	315.1	314.7	314.3	313.9	314.3	315.1	316.1	317.0	317.9	318.2	318.5
152.5°	320.7	320.2	319.7	319.3	319.5	320.4	321.2	322.1	323.0	323.3	323.7
155°	328.6	328.1	327.6	327.1	327.2	327.9	328.5	329.2	329.9	330.3	330.6
157.5°	335.0	334.5	334.1	333.7	333.7	334.2	334.7	335.2	335.6	336.0	336.4
160°	338.8	338.4	338.1	337.8	337.8	338.1	338.4	338.8	339.1	339.5	339.8
162.5°	342.1	341.7	341.4	341.0	341.0	341.3	341.6	341.9	342.2	342.6	342.9
165°	346.5	346.1	345.8	345.5	345.4	345.5	345.7	345.9	346.0	346.4	346.8
167.5°	349.7	349.4	349.0	348.7	348.6	348.8	349.0	349.1	349.3	349.7	350.1
170°	351.6	351.3	350.9	350.5	350.5	350.5	350.7	350.8	350.9	351.3	351.7
172.5°	352.8	352.4	352.1	351.8	351.6	351.8	351.9	352.0	352.1	352.5	352.9
175°	354.3	353.9	353.6	353.2	353.0	353.2	353.2	353.4	353.5	353.9	354.3
177.5°	354.7	354.3	354.0	353.7	353.6	353.6	353.7	353.7	353.8	354.1	354.4
180°	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9



TEST NUMBER: P331675-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1204.5	1208.7	1210.7	1210.7	1213.0	1212.0	1211.0
5°	1273.7	1281.4	1283.1	1290.4	1295.6	1294.0	1294.8
7.5°	1342.6	1354.9	1367.1	1372.8	1373.6	1376.9	1378.1
10°	1385.0	1395.1	1414.1	1411.3	1425.4	1433.5	1420.1
12.5°	1425.8	1439.4	1452.5	1456.2	1464.3	1466.8	1461.6
15°	1462.6	1469.9	1470.7	1468.7	1471.1	1469.1	1461.4
17.5°	1428.1	1416.3	1392.4	1381.1	1372.1	1358.8	1353.5
20°	1371.2	1336.4	1296.0	1279.8	1260.8	1223.6	1232.6
22.5°	1248.3	1208.6	1168.2	1121.0	1098.4	1063.2	1061.0
25°	1057.0	988.7	913.5	860.9	830.2	795.0	779.7
27.5°	821.8	735.8	674.1	642.9	614.6	586.7	585.5
30°	667.2	602.5	554.8	528.1	510.7	499.0	501.5
32.5°	562.4	518.1	485.9	463.7	450.9	442.0	441.9
35°	459.8	429.4	408.8	399.5	390.2	383.7	384.1
37.5°	393.5	375.3	363.8	353.5	347.7	344.5	342.8
40°	359.5	344.5	335.6	329.5	324.7	320.3	319.5
42.5°	332.6	320.3	311.3	306.6	302.1	298.9	298.1
45°	295.2	285.1	277.0	271.7	269.7	266.9	266.9
47.5°	262.6	252.6	246.4	243.0	239.6	237.7	237.6
50°	240.6	232.9	227.3	225.2	222.4	221.2	220.8
52.5°	220.9	215.2	211.1	209.7	208.5	206.9	207.2
55°	194.1	190.8	189.3	188.1	186.0	183.5	185.2
57.5°	171.5	168.8	164.5	160.7	158.8	157.1	157.7
60°	155.7	150.0	144.3	139.9	138.7	135.1	135.1
62.5°	135.6	127.7	120.7	118.3	117.0	115.3	115.0
65°	104.3	101.1	99.5	97.8	97.0	97.0	96.3
67.5°	86.4	85.2	83.4	82.9	82.1	81.9	81.7
70°	76.4	74.8	74.0	73.6	72.8	73.2	72.0
72.5°	66.7	65.4	65.3	64.2	63.7	63.8	62.9
75°	52.6	52.6	52.1	51.7	50.9	50.5	50.9
77.5°	40.4	40.5	39.8	39.7	39.6	39.7	39.3
80°	32.3	32.7	32.3	31.9	31.5	31.9	31.5
82.5°	25.6	25.0	24.9	24.8	24.7	24.5	24.4
85°	14.6	15.0	14.6	14.2	14.2	14.2	14.6
87.5°	6.7	6.7	6.8	6.8	6.8	6.9	6.6
90°	5.9	6.3	6.5	6.6	6.7	6.8	6.9
92.5°	6.4	6.5	6.7	6.7	6.8	6.8	6.9
95°	10.9	11.1	11.2	11.2	11.1	11.1	11.0
97.5°	14.0	14.3	14.4	14.5	14.6	14.7	14.7
100°	16.0	16.4	16.7	16.8	17.0	17.0	17.2
102.5°	16.8	17.3	17.7	17.9	18.1	18.2	18.4
105°	17.5	18.1	18.5	18.8	19.0	19.3	19.5
107.5°	20.0	19.3	19.1	19.3	19.6	19.8	20.0
110°	27.7	22.0	19.3	19.6	19.8	20.0	20.2



TEST NUMBER: P331675-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	50.8	30.0	19.7	19.9	20.0	20.3	20.4
115°	79.0	52.6	37.4	33.3	29.2	25.1	21.0
117.5°	155.9	149.6	139.7	126.2	112.7	99.3	85.8
120°	189.8	190.4	187.0	179.3	171.6	163.9	156.2
122.5°	201.1	201.5	200.9	199.5	198.0	196.5	195.0
125°	217.6	218.0	218.3	218.5	218.6	218.8	219.0
127.5°	233.1	233.7	234.0	234.1	234.1	234.1	234.2
130°	242.9	243.5	243.8	243.8	243.7	243.7	243.6
132.5°	252.2	252.8	253.0	252.9	252.9	252.9	252.8
135°	265.8	266.3	266.6	266.5	266.3	266.3	266.1
137.5°	278.3	278.8	279.0	278.8	278.7	278.5	278.3
140°	286.4	286.8	287.0	286.7	286.5	286.1	285.8
142.5°	293.8	294.3	294.4	294.1	293.8	293.5	293.2
145°	304.2	304.6	304.7	304.4	304.1	303.8	303.5
147.5°	313.2	313.5	313.5	313.3	313.1	312.8	312.6
150°	318.9	319.2	319.2	319.0	318.7	318.4	318.1
152.5°	324.0	324.3	324.3	323.9	323.6	323.2	322.8
155°	330.9	331.3	331.2	330.7	330.3	329.9	329.4
157.5°	336.8	337.2	337.2	336.7	336.3	335.8	335.4
160°	340.2	340.5	340.5	340.1	339.7	339.3	338.9
162.5°	343.3	343.7	343.7	343.2	342.7	342.2	341.7
165°	347.2	347.6	347.6	347.2	346.8	346.4	346.0
167.5°	350.5	350.9	350.8	350.3	349.7	349.3	348.7
170°	352.1	352.5	352.4	352.0	351.4	350.9	350.4
172.5°	353.3	353.7	353.7	353.2	352.7	352.1	351.6
175°	354.7	355.1	355.0	354.4	353.9	353.2	352.7
177.5°	354.7	355.1	355.0	354.6	354.2	353.8	353.4
180°	353.9	353.9	353.9	353.9	353.9	353.9	353.9

(END OF REPORT)