

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931178

Luminaire Tested: DFN2DS-SQ4F0-120DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931178
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-120DS840-RLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10210.2 lumens
Efficiency: N/A
Efficacy: 81.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 125.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931178

CATALOG NUMBER: DFN2DS-SQ4F0-120DS840-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931178

CATALOG NUMBER: DFN2DS-SQ4F0-120DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3484	3484	3484
5°	3497	3440	3459
10°	3470	3384	3355
15°	3430	3283	3189
20°	3375	3140	2982
25°	3319	2977	2783
30°	3240	2810	2526
35°	3164	2629	2301
40°	3086	2440	2041
45°	2996	2229	1805
50°	2904	2016	1575
55°	2808	1786	1352
60°	2699	1545	1123
65°	2574	1298	1022
70°	2424	1069	940
75°	2241	975	877
80°	1978	870	799
85°	1555	687	687

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2996 cd/sqm

TEST NUMBER: P931178

CATALOG NUMBER: DFN2DS-SQ4F0-120DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	465.3	4.6
10°-20°	1277.3	12.5
20°-30°	1793.3	17.6
30°-40°	1954.8	19.1
40°-50°	1796.7	17.6
50°-60°	1411.0	13.8
60°-70°	918.4	9.0
70°-80°	472.8	4.6
80°-90°	120.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3535.9	34.6
0°-40°	5490.6	53.8
0°-60°	8698.3	85.2
0°-90°	10210.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10210.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4965	4965	4965	4965	4965	
5°	4965	4942	4884	4924	4911	471
15°	4722	4672	4520	4434	4390	1331
25°	4286	4142	3846	3662	3594	1971
35°	3693	3464	3069	2786	2686	2312
45°	3019	2718	2246	1927	1819	2332
55°	2296	1945	1460	1191	1105	2051
65°	1550	1186	782	629	615	1537
75°	826	512	360	328	324	874
85°	193	99	85	85	85	232
90°	0	0	0	0	0	

TEST NUMBER: P931178

CATALOG NUMBER: DFN2DS-SQ4F0-120DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4964.6	4964.6	4964.6	4964.6	4964.6
2.5°	4987.0	4964.6	4915.0	4960.3	4951.1
5°	4964.6	4942.1	4883.5	4924.0	4910.7
7.5°	4924.0	4897.3	4834.4	4852.0	4829.6
10°	4870.2	4838.7	4749.0	4735.2	4708.6
12.5°	4802.9	4762.5	4640.8	4614.2	4564.7
15°	4721.9	4672.4	4519.8	4434.4	4389.7
17.5°	4627.5	4555.6	4366.8	4268.2	4196.2
20°	4519.8	4429.7	4205.2	4093.2	3994.0
22.5°	4403.0	4299.6	4038.8	3886.3	3819.1
25°	4286.3	4142.2	3845.7	3661.8	3594.1
27.5°	4147.0	3994.0	3666.1	3455.0	3351.4
30°	3998.8	3827.7	3468.3	3239.4	3117.9
32.5°	3854.9	3647.9	3280.0	3010.2	2897.7
35°	3693.3	3464.0	3068.8	2785.7	2686.5
37.5°	3535.9	3288.6	2871.0	2560.7	2448.6
40°	3369.6	3100.3	2664.2	2345.2	2228.4
42.5°	3198.9	2911.5	2457.8	2125.0	2013.0
45°	3019.2	2718.0	2246.5	1927.2	1819.4
47.5°	2848.5	2529.7	2044.4	1725.1	1626.4
50°	2659.9	2340.9	1846.6	1536.3	1442.4
52.5°	2475.4	2138.3	1657.9	1361.4	1276.1
55°	2295.7	1945.3	1460.1	1190.7	1105.4
57.5°	2111.6	1752.3	1285.1	1033.4	961.5
60°	1922.9	1563.5	1100.6	871.9	799.9
62.5°	1738.9	1379.5	943.3	727.9	692.1
65°	1550.1	1186.0	781.8	629.2	615.4
67.5°	1370.5	1006.2	629.2	552.5	539.1
70°	1181.7	831.3	521.0	476.2	458.1
72.5°	1002.0	669.3	435.6	399.9	390.9
75°	826.5	511.9	359.5	327.9	323.6
77.5°	651.7	363.7	283.2	265.1	256.0
80°	489.6	260.8	215.4	197.8	197.8
82.5°	341.3	175.4	148.2	139.1	139.1
85°	193.1	98.7	85.3	85.3	85.3
87.5°	72.0	35.7	35.7	31.4	31.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931178

CATALOG NUMBER: DFN2DS-SQ4F0-120DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.57	17.09	15.94	17.41	17.72	11.53	13.05	11.90	13.37	13.68
	3H	17.34	18.70	17.71	19.03	19.39	12.80	14.16	13.17	14.49	14.85
	4H	18.00	19.28	18.40	19.63	20.01	13.30	14.58	13.70	14.93	15.31
	6H	18.49	19.67	18.90	20.04	20.43	13.68	14.86	14.09	15.23	15.62
	8H	18.66	19.78	19.08	20.17	20.57	13.80	14.93	14.23	15.32	15.72
	12H	18.76	19.84	19.19	20.22	20.65	13.88	14.96	14.32	15.34	15.77
4H	2H	15.67	16.96	16.07	17.30	17.68	12.23	13.51	12.63	13.86	14.23
	3H	17.61	18.67	18.02	19.07	19.47	13.67	14.73	14.08	15.13	15.53
	4H	18.36	19.31	18.79	19.73	20.17	14.27	15.23	14.70	15.64	16.08
	6H	18.95	19.78	19.41	20.22	20.68	14.76	15.59	15.21	16.03	16.49
	8H	19.16	19.94	19.63	20.39	20.85	14.92	15.70	15.38	16.14	16.61
	12H	19.32	20.01	19.80	20.49	20.96	15.04	15.73	15.52	16.21	16.68
8H	4H	18.38	19.16	18.85	19.60	20.07	14.62	15.40	15.09	15.84	16.31
	6H	19.02	19.66	19.52	20.15	20.63	15.21	15.85	15.71	16.34	16.82
	8H	19.27	19.85	19.78	20.36	20.84	15.43	16.01	15.94	16.52	17.01
	12H	19.47	19.98	19.98	20.48	21.04	15.61	16.12	16.12	16.61	17.18
12H	4H	18.37	19.06	18.85	19.54	20.01	14.67	15.36	15.15	15.84	16.31
	6H	19.00	19.58	19.51	20.09	20.58	15.27	15.85	15.79	16.36	16.85
	8H	19.28	19.79	19.79	20.29	20.85	15.55	16.06	16.06	16.55	17.11

END OF REPORT