

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331245-830

Luminaire Tested: **S122DIP-S290D330U830-4F0-1E-UDD-D4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331245-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S290D330U830-4F0-1E-UDD-D4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2333.7 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331245-830

CATALOG NUMBER: S122DIP-S290D330U830-4F0-1E-UDD-D4

Luminous Intensity Polar Plot





TEST NUMBER: P331245-830

CATALOG NUMBER: S122DIP-S290D330U830-4F0-1E-UDD-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43
1	95	90	86	82	86	82	79	75	68	65	62	54	52	51	42	41	39	34
2	86	78	71	66	78	71	65	61	59	54	51	47	44	41	36	34	32	27
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	32	29	27	22
4	71	60	52	45	64	55	48	42	45	40	35	36	32	29	28	25	23	19
5	65	53	45	39	59	49	41	36	40	35	30	32	28	25	25	22	20	16
6	60	47	39	33	54	44	36	31	36	30	26	29	25	22	23	19	17	14
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	21	17	15	12
8	51	39	31	25	47	36	29	24	30	24	20	24	20	17	19	16	13	11
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12	10
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4771	4771	4771
5°	4794	4593	4573
10°	4763	4457	4407
15°	4698	4312	4229
20°	4614	4159	4059
25°	4533	4009	3902
30°	4418	3857	3747
35°	4301	3711	3638
40°	4178	3584	3528
45°	4060	3473	3434
50°	3936	3371	3343
55°	3802	3261	3248
60°	3643	3149	3150
65°	3474	3016	3031
70°	3286	2872	2904
75°	3050	2735	2786
80°	2669	2592	2667
85°	2319	2468	2574



TEST NUMBER: P331245-830

CATALOG NUMBER: S122DIP-S290D330U830-4F0-1E-UDD-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.0	1.2
10°-20°	80.3	3.4
20°-30°	121.6	5.2
30°-40°	148.2	6.3
40°-50°	159.4	6.8
50°-60°	154.8	6.6
60°-70°	135.2	5.8
70°-80°	104.1	4.5
80°-90°	71.4	3.1
90°-100°	117.4	5.0
100°-110°	270.1	11.6
110°-120°	272.8	11.7
120°-130°	218.4	9.4
130°-140°	170.4	7.3
140°-150°	125.6	5.4
150°-160°	87.6	3.8
160°-170°	51.6	2.2
170°-180°	16.8	0.7
0°-30°	229.9	9.9
0°-40°	378.1	16.2
0°-60°	692.3	29.7
0°-90°	1002.9	43.0
90°-120°	660.3	28.3
90°-150°	1174.8	50.3
90°-180°	1331.0	57.0
0°-180°	2333.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	296	296	296	296	296	
5°	296	295	292	295	294	28
15°	283	283	283	287	287	80
25°	257	260	264	269	270	118
35°	221	229	237	246	249	138
45°	182	193	208	221	226	140
55°	139	155	177	192	198	124
65°	95	116	141	158	164	94
75°	53	77	104	122	128	56
85°	16	42	69	87	93	17
90°	5	34	68	84	90	4
95°	15	52	180	114	109	15
105°	43	76	284	492	432	46
115°	73	98	232	464	537	73
125°	101	120	213	371	431	90
135°	118	140	201	303	349	91
145°	134	154	195	245	270	84
155°	152	164	190	214	223	70
165°	166	171	182	192	196	47
175°	173	173	174	177	176	16
180°	173	173	173	173	173	



TEST NUMBER: P331245-830

CATALOG NUMBER: S122DIP-S290D330U830-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5
2.5°	297.2	296.9	296.7	296.4	296.2	295.9	295.3	294.8	294.3	293.7	294.1
5°	296.3	296.1	295.8	295.5	295.1	294.7	294.2	293.6	293.0	292.5	293.0
7.5°	293.6	293.4	293.2	293.0	292.8	292.6	292.1	291.7	291.2	290.8	291.5
10°	291.6	291.4	291.2	291.1	290.9	290.6	290.3	290.0	289.7	289.5	290.2
12.5°	288.1	288.2	288.2	288.3	288.3	288.2	288.0	287.9	287.6	287.4	288.1
15°	282.6	282.8	283.0	283.1	283.3	283.4	283.4	283.4	283.4	283.4	284.3
17.5°	275.4	275.8	276.2	276.6	277.0	277.4	277.7	278.0	278.2	278.6	279.5
20°	270.6	271.1	271.5	272.0	272.5	273.0	273.3	273.7	274.1	274.5	275.5
22.5°	265.5	266.0	266.6	267.1	267.7	268.2	268.7	269.3	269.8	270.3	271.4
25°	256.9	257.6	258.3	258.9	259.6	260.3	261.2	262.0	262.9	263.7	264.9
27.5°	246.7	247.7	248.8	249.9	251.0	252.0	253.0	254.0	255.1	256.1	257.5
30°	239.8	241.0	242.2	243.5	244.7	246.0	247.2	248.5	249.7	250.9	252.4
32.5°	232.2	233.7	235.0	236.4	237.8	239.2	240.7	242.1	243.6	245.1	246.9
35°	221.4	223.0	224.6	226.2	227.8	229.5	231.4	233.2	235.0	236.8	238.8
37.5°	209.5	211.4	213.3	215.2	217.0	219.1	221.5	223.8	226.1	228.5	230.8
40°	201.7	203.8	205.9	207.9	210.0	212.4	214.9	217.5	220.1	222.6	225.1
42.5°	194.2	196.2	198.3	200.4	202.6	205.0	208.0	210.9	213.9	216.8	219.5
45°	181.5	184.1	186.7	189.3	191.8	194.7	198.1	201.4	204.7	208.1	211.0
47.5°	169.1	171.9	174.7	177.5	180.3	183.7	187.6	191.4	195.4	199.3	202.4
50°	160.6	163.5	166.5	169.4	172.4	176.0	180.3	184.5	188.8	193.1	196.3
52.5°	152.3	155.4	158.5	161.6	164.8	168.5	173.1	177.6	182.1	186.6	189.9
55°	139.1	142.6	146.0	149.4	152.9	157.0	162.0	166.9	171.9	176.8	180.3
57.5°	126.1	130.0	133.8	137.7	141.6	146.0	151.1	156.1	161.2	166.3	169.9
60°	116.9	121.0	125.1	129.1	133.3	138.0	143.5	148.8	154.3	159.7	163.3
62.5°	108.7	112.9	117.2	121.4	125.6	130.4	135.9	141.3	146.8	152.2	156.0
65°	95.0	99.7	104.3	109.1	113.7	118.9	124.4	130.1	135.7	141.3	145.2
67.5°	82.6	87.5	92.3	97.2	102.1	107.4	113.1	118.9	124.6	130.4	134.3
70°	73.6	78.6	83.5	88.5	93.4	98.9	104.7	110.7	116.6	122.4	126.6
72.5°	65.4	70.5	75.6	80.7	85.9	91.3	97.4	103.3	109.3	115.3	119.3
75°	52.7	58.0	63.3	68.6	74.0	79.6	85.8	91.9	97.9	104.1	108.1
77.5°	40.3	45.9	51.5	57.0	62.7	68.5	74.7	80.9	87.1	93.2	97.4
80°	32.1	37.9	43.7	49.5	55.3	61.4	67.5	73.7	79.8	86.1	90.0
82.5°	25.3	31.0	36.8	42.4	48.2	54.2	60.4	66.7	73.0	79.2	83.2
85°	15.5	21.3	27.2	33.1	39.0	45.0	51.1	57.2	63.2	69.4	73.3
87.5°	8.5	14.3	20.3	26.1	31.9	38.0	44.4	50.9	57.4	63.6	67.4
90°	4.6	11.1	18.0	24.1	30.3	37.1	44.9	53.3	61.5	67.9	71.4
92.5°	8.0	14.9	22.4	29.1	36.5	45.1	58.5	74.9	90.3	96.7	93.7
95°	15.1	20.9	28.7	36.2	46.0	59.0	80.0	114.7	159.1	179.7	167.1
97.5°	22.0	27.7	35.3	43.7	53.9	67.7	92.4	138.3	207.9	268.4	282.9
100°	28.7	33.2	39.7	48.5	58.7	72.5	95.5	141.4	218.7	305.9	357.4
102.5°	34.4	38.4	44.6	53.2	63.2	76.8	98.3	139.6	211.3	304.8	383.7
105°	42.8	46.8	51.9	59.7	69.7	82.9	103.6	138.2	198.0	283.6	375.5
107.5°	52.3	55.5	60.0	66.8	76.3	89.2	109.1	139.7	189.8	261.2	342.6
110°	58.3	61.5	65.5	71.7	80.6	93.5	112.8	141.5	186.8	250.1	322.1



TEST NUMBER: P331245-830

CATALOG NUMBER: S122DIP-S290D330U830-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	64.2	67.1	71.0	76.6	84.9	97.9	116.5	143.5	184.8	241.8	306.9
115°	73.3	76.1	79.1	84.1	91.8	103.5	122.1	146.7	183.2	232.1	287.7
117.5°	82.4	84.4	87.0	91.2	98.3	110.0	127.2	150.2	182.5	225.6	274.1
120°	88.2	89.9	92.3	95.7	102.7	114.1	130.9	152.7	182.2	221.6	266.6
122.5°	93.8	95.0	97.2	100.6	107.4	118.9	134.6	154.9	182.2	218.5	259.9
125°	100.8	101.8	103.8	107.7	114.4	125.3	140.3	158.3	182.0	213.0	249.9
127.5°	106.6	107.8	110.6	114.9	121.2	132.0	146.0	161.9	182.4	208.9	240.6
130°	110.1	111.3	114.5	119.1	125.7	136.0	149.6	164.3	182.9	206.2	234.5
132.5°	113.3	114.8	118.3	123.1	130.0	140.0	152.7	166.6	183.4	203.9	229.1
135°	117.6	118.9	123.0	128.0	135.6	145.4	157.0	169.7	183.9	200.9	221.9
137.5°	122.2	123.8	127.7	133.1	140.6	149.5	160.4	171.7	184.3	198.3	215.9
140°	125.6	126.9	130.8	136.0	143.3	151.9	162.1	172.7	184.2	196.7	212.5
142.5°	129.1	130.1	133.7	138.9	145.9	154.0	163.8	173.9	184.5	196.0	209.6
145°	133.8	135.3	138.6	143.5	150.2	157.5	166.5	175.9	185.1	195.1	206.4
147.5°	139.5	140.4	143.6	148.3	153.8	160.3	168.8	177.0	185.4	194.0	203.4
150°	143.2	144.2	146.8	151.2	156.2	162.2	169.8	177.5	185.1	193.1	201.1
152.5°	146.9	147.4	150.1	153.8	158.6	164.0	170.9	177.8	184.6	191.8	199.3
155°	152.2	152.5	154.5	158.2	161.8	166.8	172.5	178.1	183.8	189.5	195.9
157.5°	156.6	156.9	158.5	161.7	164.7	168.8	173.6	178.1	182.3	187.1	192.6
160°	159.5	159.9	161.2	163.8	166.5	170.2	174.2	178.1	181.5	185.5	190.1
162.5°	162.5	162.2	163.6	165.7	168.1	171.0	174.5	177.9	180.7	184.2	188.0
165°	165.9	165.5	166.2	168.1	169.8	171.8	174.8	177.2	179.2	181.5	184.5
167.5°	168.6	168.2	168.8	170.1	171.4	172.6	174.7	176.7	177.7	179.2	181.1
170°	170.5	169.8	170.2	171.2	171.8	172.9	174.5	176.2	176.8	177.9	179.2
172.5°	171.5	171.2	171.0	172.0	172.4	173.1	174.3	175.4	175.8	176.3	177.3
175°	172.9	172.5	172.2	172.9	172.9	173.1	173.8	174.5	174.2	174.5	174.8
177.5°	173.4	172.9	172.7	173.1	173.1	173.1	173.4	174.0	173.4	173.1	173.4
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1



TEST NUMBER: P331245-830

CATALOG NUMBER: S122DIP-S290D330U830-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5
2.5°	294.5	294.8	295.2	295.4	295.2	295.0	294.9	294.7
5°	293.6	294.2	294.7	294.9	294.8	294.7	294.6	294.5
7.5°	292.2	292.8	293.6	293.9	293.8	293.7	293.6	293.5
10°	291.0	291.7	292.5	292.8	292.8	292.7	292.6	292.5
12.5°	288.9	289.6	290.4	290.8	290.7	290.6	290.5	290.4
15°	285.1	286.1	286.9	287.3	287.2	287.1	287.0	286.9
17.5°	280.4	281.3	282.1	282.6	282.6	282.6	282.6	282.6
20°	276.5	277.6	278.6	279.2	279.2	279.2	279.2	279.2
22.5°	272.5	273.5	274.6	275.1	275.3	275.4	275.6	275.8
25°	266.1	267.2	268.3	269.0	269.3	269.6	269.8	270.1
27.5°	258.9	260.4	261.8	262.7	262.9	263.1	263.3	263.5
30°	253.9	255.5	257.0	257.9	258.2	258.4	258.7	259.0
32.5°	248.5	250.3	252.1	253.3	253.7	254.3	254.8	255.2
35°	241.0	243.1	245.2	246.6	247.2	247.9	248.5	249.2
37.5°	233.1	235.4	237.8	239.3	240.0	240.7	241.4	242.0
40°	227.6	230.1	232.5	234.2	235.1	235.9	236.8	237.6
42.5°	222.3	224.9	227.6	229.4	230.3	231.1	232.0	232.8
45°	214.0	217.0	219.9	221.9	222.8	223.8	224.7	225.6
47.5°	205.5	208.5	211.6	213.7	214.7	215.7	216.8	217.8
50°	199.5	202.8	206.0	208.2	209.2	210.3	211.3	212.4
52.5°	193.2	196.5	199.8	202.1	203.2	204.3	205.5	206.5
55°	183.7	187.1	190.6	192.8	194.1	195.4	196.6	197.8
57.5°	173.6	177.3	181.0	183.4	184.7	186.0	187.2	188.5
60°	166.9	170.6	174.2	176.6	178.0	179.3	180.7	182.0
62.5°	159.9	163.7	167.6	170.1	171.4	172.6	173.9	175.1
65°	149.1	153.0	156.9	159.5	160.7	161.9	163.2	164.4
67.5°	138.2	142.1	146.1	148.7	150.0	151.3	152.6	153.9
70°	130.6	134.7	138.8	141.5	142.6	143.7	144.9	146.0
72.5°	123.3	127.3	131.3	134.0	135.3	136.8	138.2	139.5
75°	112.3	116.3	120.5	123.1	124.3	125.5	126.8	128.0
77.5°	101.4	105.5	109.5	112.3	113.6	114.9	116.2	117.5
80°	94.1	98.0	102.1	104.7	106.0	107.4	108.7	110.0
82.5°	87.2	91.2	95.2	97.8	99.1	100.4	101.6	102.8
85°	77.4	81.3	85.4	88.0	89.4	90.7	92.0	93.3
87.5°	71.3	74.9	79.0	81.6	82.8	84.0	85.2	86.4
90°	74.7	77.9	82.4	85.2	86.3	87.5	88.6	89.7
92.5°	89.9	89.5	90.5	90.9	91.7	91.8	93.2	93.8
95°	143.7	127.1	116.7	111.7	108.5	107.0	107.2	108.6
97.5°	256.2	222.7	190.2	168.4	153.6	146.6	142.9	141.2
100°	353.9	316.1	274.0	236.0	209.4	196.1	187.6	182.6
102.5°	417.2	411.3	381.4	340.9	311.9	288.5	277.5	270.4
105°	448.1	489.1	496.7	488.0	468.3	448.7	435.5	431.9
107.5°	419.2	479.2	517.0	535.3	538.9	538.8	537.0	531.9
110°	395.4	458.0	503.7	533.0	548.4	555.8	559.8	560.5



TEST NUMBER: P331245-830

CATALOG NUMBER: S122DIP-S290D330U830-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	373.2	433.5	482.1	515.5	536.4	548.1	554.8	557.6
115°	345.4	399.5	446.1	482.3	507.0	523.4	533.1	537.2
117.5°	323.6	371.5	413.9	447.9	473.0	490.1	500.2	503.7
120°	312.2	356.2	394.1	426.3	450.6	467.3	478.1	482.4
122.5°	302.7	343.2	379.2	408.3	430.2	446.5	455.9	459.6
125°	288.8	325.6	357.5	384.2	404.4	417.9	427.1	430.6
127.5°	274.9	308.4	338.4	363.0	380.7	393.4	401.4	404.4
130°	266.1	297.0	325.6	349.1	366.2	378.2	385.7	389.1
132.5°	257.5	286.2	312.5	334.7	351.6	363.6	370.5	373.6
135°	245.5	269.5	293.4	313.5	328.6	340.4	347.0	349.1
137.5°	235.4	255.5	274.8	292.2	305.9	315.9	321.9	324.5
140°	229.0	246.6	263.3	279.1	290.3	299.5	305.1	307.6
142.5°	224.0	238.8	253.2	266.4	276.9	285.3	290.3	291.2
145°	217.3	228.8	239.7	249.9	258.4	264.5	268.3	269.8
147.5°	212.3	220.9	229.1	236.3	243.1	247.9	250.3	251.2
150°	209.2	216.5	223.5	229.4	234.4	238.5	240.4	240.8
152.5°	206.2	213.0	219.0	224.1	228.1	231.5	233.0	233.1
155°	202.2	207.5	212.4	216.1	219.8	222.2	223.5	222.8
157.5°	197.5	201.9	206.0	209.0	211.5	213.5	214.1	214.1
160°	194.4	198.1	201.8	204.2	206.5	208.1	208.5	208.5
162.5°	191.5	194.7	197.8	199.6	202.0	203.1	203.4	203.1
165°	187.2	189.5	191.8	193.1	194.4	195.9	195.9	195.5
167.5°	182.9	184.7	186.3	187.6	188.1	188.9	188.8	188.4
170°	180.9	181.8	183.1	183.8	184.2	185.1	184.8	184.2
172.5°	178.4	179.2	180.2	180.6	181.0	181.4	181.1	180.7
175°	175.9	176.2	176.5	176.8	176.8	177.2	176.8	176.2
177.5°	174.0	174.0	174.3	174.3	174.3	174.3	174.0	173.4
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1

(END OF REPORT)