

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931110

Luminaire Tested: DFN2DS-SQ4F0-080DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931110
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-080DS927-RLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5385.6 lumens
Efficiency: N/A
Efficacy: 67.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 79.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931110

CATALOG NUMBER: DFN2DS-SQ4F0-080DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931110

CATALOG NUMBER: DFN2DS-SQ4F0-080DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1837	1837	1837
5°	1844	1814	1824
10°	1830	1785	1770
15°	1809	1732	1682
20°	1780	1656	1573
25°	1750	1570	1468
30°	1709	1482	1332
35°	1669	1387	1214
40°	1628	1287	1077
45°	1580	1176	952
50°	1531	1063	831
55°	1481	942	713
60°	1423	815	592
65°	1358	685	539
70°	1279	564	496
75°	1182	514	463
80°	1043	459	421
85°	820	362	362

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1580 cd/sqm

TEST NUMBER: P931110

CATALOG NUMBER: DFN2DS-SQ4F0-080DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.4	4.6
10°-20°	673.7	12.5
20°-30°	945.9	17.6
30°-40°	1031.1	19.1
40°-50°	947.7	17.6
50°-60°	744.3	13.8
60°-70°	484.4	9.0
70°-80°	249.4	4.6
80°-90°	63.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1865.1	34.6
0°-40°	2896.2	53.8
0°-60°	4588.1	85.2
0°-90°	5385.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5385.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2619	2619	2619	2619	2619	
5°	2619	2607	2576	2597	2590	248
15°	2491	2464	2384	2339	2315	702
25°	2261	2185	2028	1932	1896	1040
35°	1948	1827	1619	1469	1417	1219
45°	1593	1434	1185	1016	960	1230
55°	1211	1026	770	628	583	1082
65°	818	626	412	332	325	811
75°	436	270	190	173	171	461
85°	102	52	45	45	45	122
90°	0	0	0	0	0	

TEST NUMBER: P931110

CATALOG NUMBER: DFN2DS-SQ4F0-080DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2618.7	2618.7	2618.7	2618.7	2618.7
2.5°	2630.5	2618.7	2592.5	2616.4	2611.6
5°	2618.7	2606.9	2575.9	2597.3	2590.2
7.5°	2597.3	2583.2	2550.0	2559.3	2547.5
10°	2568.9	2552.3	2505.0	2497.7	2483.6
12.5°	2533.4	2512.1	2447.9	2433.8	2407.7
15°	2490.7	2464.5	2384.1	2339.1	2315.4
17.5°	2440.9	2402.9	2303.4	2251.3	2213.3
20°	2384.1	2336.6	2218.2	2159.1	2106.7
22.5°	2322.5	2267.9	2130.4	2049.9	2014.5
25°	2260.8	2185.0	2028.5	1931.5	1895.8
27.5°	2187.4	2106.7	1933.7	1822.4	1767.8
30°	2109.3	2019.0	1829.4	1708.7	1644.6
32.5°	2033.3	1924.2	1730.1	1587.8	1528.5
35°	1948.1	1827.1	1618.7	1469.4	1417.0
37.5°	1865.1	1734.6	1514.4	1350.7	1291.6
40°	1777.4	1635.3	1405.2	1237.0	1175.4
42.5°	1687.4	1535.8	1296.3	1120.9	1061.8
45°	1592.6	1433.7	1185.0	1016.5	959.7
47.5°	1502.6	1334.4	1078.4	909.9	857.9
50°	1402.9	1234.8	974.1	810.4	760.8
52.5°	1305.7	1127.9	874.4	718.1	673.1
55°	1210.9	1026.1	770.1	628.1	583.1
57.5°	1113.9	924.3	677.9	545.1	507.1
60°	1014.2	824.7	580.5	459.8	421.9
62.5°	917.2	727.6	497.6	384.0	365.1
65°	817.7	625.5	412.3	331.9	324.6
67.5°	722.9	530.8	331.9	291.4	284.4
70°	623.3	438.5	274.8	251.1	241.6
72.5°	528.5	353.0	229.8	211.0	206.2
75°	436.0	270.1	189.6	173.0	170.8
77.5°	343.7	191.8	149.4	139.8	135.0
80°	258.2	137.6	113.7	104.3	104.3
82.5°	180.0	92.5	78.2	73.4	73.4
85°	101.9	52.0	45.0	45.0	45.0
87.5°	37.9	18.8	18.8	16.6	16.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931110

CATALOG NUMBER: DFN2DS-SQ4F0-080DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.35	14.87	13.71	15.18	15.50	9.31	10.83	9.67	11.14	11.46
	3H	15.11	16.48	15.49	16.81	17.17	10.57	11.94	10.95	12.27	12.63
	4H	15.78	17.06	16.18	17.41	17.79	11.08	12.36	11.48	12.71	13.08
	6H	16.27	17.45	16.68	17.82	18.21	11.46	12.64	11.87	13.01	13.40
	8H	16.43	17.56	16.86	17.95	18.35	11.58	12.71	12.01	13.10	13.50
	12H	16.54	17.62	16.97	18.00	18.43	11.66	12.74	12.09	13.12	13.55
4H	2H	13.45	14.73	13.85	15.08	15.46	10.00	11.28	10.40	11.63	12.01
	3H	15.39	16.45	15.80	16.85	17.25	11.45	12.51	11.86	12.91	13.31
	4H	16.14	17.09	16.57	17.51	17.95	12.05	13.00	12.48	13.42	13.86
	6H	16.73	17.56	17.18	18.00	18.46	12.54	13.37	12.99	13.81	14.27
	8H	16.94	17.72	17.40	18.16	18.63	12.70	13.47	13.16	13.92	14.39
	12H	17.10	17.79	17.58	18.27	18.74	12.81	13.51	13.30	13.99	14.46
8H	4H	16.16	16.94	16.62	17.38	17.85	12.40	13.18	12.86	13.62	14.09
	6H	16.80	17.44	17.29	17.93	18.41	12.99	13.63	13.48	14.12	14.60
	8H	17.05	17.62	17.56	18.13	18.62	13.21	13.78	13.72	14.29	14.78
	12H	17.25	17.76	17.76	18.25	18.82	13.39	13.90	13.90	14.39	14.95
12H	4H	16.14	16.84	16.63	17.32	17.79	12.44	13.14	12.93	13.62	14.09
	6H	16.78	17.36	17.29	17.87	18.35	13.05	13.63	13.56	14.14	14.63
	8H	17.06	17.57	17.57	18.06	18.63	13.32	13.83	13.83	14.33	14.89

END OF REPORT