

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931097

Luminaire Tested: DFN2DS-SQ4F0-070DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931097
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-070DS940-FLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6181.6 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 69.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931097

CATALOG NUMBER: DFN2DS-SQ4F0-070DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931097

CATALOG NUMBER: DFN2DS-SQ4F0-070DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1705	1705	1705
5°	1711	1687	1697
10°	1701	1670	1678
15°	1680	1648	1646
20°	1650	1615	1614
25°	1621	1576	1576
30°	1583	1539	1526
35°	1547	1495	1473
40°	1502	1451	1423
45°	1458	1407	1372
50°	1410	1362	1313
55°	1360	1309	1260
60°	1305	1246	1200
65°	1245	1183	1129
70°	1170	1107	1055
75°	1064	1019	995
80°	944	916	868
85°	770	735	659

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1458 cd/sqm

TEST NUMBER: P931097

CATALOG NUMBER: DFN2DS-SQ4F0-070DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.7	3.7
10°-20°	643.4	10.4
20°-30°	945.5	15.3
30°-40°	1098.2	17.8
40°-50°	1096.8	17.7
50°-60°	956.4	15.5
60°-70°	707.0	11.4
70°-80°	400.0	6.5
80°-90°	105.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1817.6	29.4
0°-40°	2915.8	47.2
0°-60°	4969.0	80.4
0°-90°	6181.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6181.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2430	2430	2430	2430	2430	
5°	2430	2420	2395	2413	2409	231
15°	2313	2299	2268	2278	2266	651
25°	2093	2075	2035	2040	2035	963
35°	1806	1783	1745	1731	1719	1128
45°	1470	1453	1418	1392	1383	1134
55°	1112	1098	1070	1042	1030	994
65°	750	736	713	692	680	742
75°	392	388	376	362	367	419
85°	96	94	91	84	82	112
90°	0	0	0	0	0	

TEST NUMBER: P931097

CATALOG NUMBER: DFN2DS-SQ4F0-070DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2429.5	2429.5	2429.5	2429.5	2429.5
2.5°	2443.7	2432.0	2406.3	2429.5	2425.1
5°	2429.5	2420.4	2394.7	2413.2	2408.8
7.5°	2413.2	2399.3	2373.5	2392.4	2387.7
10°	2387.7	2371.3	2343.3	2361.9	2355.0
12.5°	2352.5	2338.6	2310.6	2322.2	2317.5
15°	2312.9	2299.0	2268.4	2277.9	2266.2
17.5°	2263.7	2249.9	2219.4	2231.1	2219.4
20°	2209.9	2196.1	2163.4	2170.3	2161.1
22.5°	2156.4	2135.4	2104.9	2104.9	2100.1
25°	2093.3	2074.6	2035.0	2039.5	2035.0
27.5°	2023.1	2006.7	1976.5	1969.5	1957.9
30°	1953.2	1934.3	1899.4	1892.5	1883.0
32.5°	1878.3	1864.5	1827.0	1812.9	1803.4
35°	1805.9	1782.7	1745.2	1731.1	1719.4
37.5°	1724.1	1703.1	1665.6	1649.3	1637.6
40°	1640.1	1621.3	1583.8	1563.1	1553.6
42.5°	1558.3	1539.5	1502.3	1478.8	1464.8
45°	1469.6	1453.2	1418.0	1392.5	1383.0
47.5°	1383.0	1366.7	1329.3	1303.5	1289.7
50°	1291.9	1280.2	1247.5	1214.8	1203.1
52.5°	1203.1	1186.8	1156.6	1130.8	1114.4
55°	1112.1	1098.1	1070.0	1042.0	1030.3
57.5°	1021.0	1009.3	978.8	950.8	941.4
60°	929.7	920.5	887.9	862.1	855.2
62.5°	841.0	824.7	801.4	778.1	768.6
65°	750.1	735.9	712.6	691.6	679.9
67.5°	656.6	644.7	623.9	607.5	598.1
70°	570.1	560.7	539.6	523.2	514.1
72.5°	481.3	472.0	460.3	443.9	437.0
75°	392.4	387.9	376.0	362.2	366.9
77.5°	313.1	303.6	298.9	292.0	285.1
80°	233.7	231.3	226.6	219.6	214.9
82.5°	158.9	158.9	156.6	147.3	147.3
85°	95.7	93.5	91.3	84.0	81.8
87.5°	42.1	37.5	32.7	25.8	23.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931097

CATALOG NUMBER: DFN2DS-SQ4F0-070DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.14	14.75	13.50	15.06	15.37	12.69	14.30	13.06	14.62	14.93
	3H	14.89	16.34	15.26	16.67	17.03	14.39	15.85	14.77	16.18	16.54
	4H	15.53	16.90	15.93	17.25	17.63	15.04	16.41	15.44	16.75	17.13
	6H	16.00	17.27	16.41	17.63	18.03	15.50	16.77	15.91	17.13	17.52
	8H	16.14	17.36	16.57	17.74	18.14	15.64	16.85	16.07	17.24	17.64
	12H	16.23	17.39	16.66	17.78	18.21	15.72	16.88	16.15	17.26	17.69
4H	2H	13.70	15.07	14.09	15.41	15.79	13.34	14.71	13.74	15.06	15.44
	3H	15.67	16.82	16.08	17.22	17.62	15.26	16.41	15.67	16.81	17.21
	4H	16.45	17.48	16.88	17.90	18.33	16.02	17.06	16.46	17.47	17.91
	6H	17.04	17.95	17.50	18.39	18.85	16.61	17.52	17.07	17.96	18.41
	8H	17.23	18.08	17.69	18.52	18.99	16.80	17.64	17.26	18.09	18.55
	12H	17.37	18.13	17.85	18.60	19.07	16.91	17.67	17.39	18.15	18.62
8H	4H	16.72	17.57	17.18	18.01	18.48	16.35	17.19	16.81	17.64	18.10
	6H	17.44	18.14	17.93	18.63	19.10	17.05	17.76	17.55	18.25	18.72
	8H	17.69	18.33	18.20	18.83	19.32	17.30	17.93	17.81	18.44	18.93
	12H	17.89	18.45	18.40	18.94	19.50	17.48	18.04	17.99	18.53	19.09
12H	4H	16.75	17.51	17.23	17.98	18.45	16.38	17.14	16.86	17.62	18.09
	6H	17.48	18.11	17.99	18.62	19.11	17.11	17.74	17.62	18.25	18.74
	8H	17.79	18.35	18.30	18.84	19.40	17.42	17.98	17.92	18.47	19.03