

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931281

Luminaire Tested: DFN2DS-TR2F0-050DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931281
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR2F0-050DS830-FLL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4662.9 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.36' x L: 2.04' x H: 0')
CIE Type: Direct

Input Watts (W): 49.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931281

CATALOG NUMBER: DFN2DS-TR2F0-050DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931281

CATALOG NUMBER: DFN2DS-TR2F0-050DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4088	4088	4088
5°	4103	4044	4068
10°	4079	4004	4023
15°	4028	3951	3947
20°	3957	3873	3869
25°	3886	3778	3778
30°	3794	3690	3658
35°	3709	3584	3532
40°	3602	3479	3412
45°	3497	3374	3291
50°	3381	3266	3149
55°	3262	3139	3022
60°	3128	2988	2878
65°	2986	2837	2706
70°	2804	2654	2529
75°	2551	2444	2385
80°	2264	2195	2082
85°	1848	1761	1579

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3497 cd/sqm

TEST NUMBER: P931281

CATALOG NUMBER: DFN2DS-TR2F0-050DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.5	3.7
10°-20°	485.3	10.4
20°-30°	713.2	15.3
30°-40°	828.4	17.8
40°-50°	827.4	17.7
50°-60°	721.4	15.5
60°-70°	533.3	11.4
70°-80°	301.7	6.5
80°-90°	79.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1371.1	29.4
0°-40°	2199.4	47.2
0°-60°	3748.2	80.4
0°-90°	4662.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4662.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1833	1833	1833	1833	1833	
5°	1833	1826	1806	1820	1817	174
15°	1745	1734	1711	1718	1709	491
25°	1579	1565	1535	1538	1535	727
35°	1362	1345	1316	1306	1297	851
45°	1108	1096	1070	1050	1043	856
55°	839	828	807	786	777	750
65°	566	555	538	522	513	559
75°	296	293	284	273	277	316
85°	72	70	69	63	62	85
90°	0	0	0	0	0	

TEST NUMBER: P931281

CATALOG NUMBER: DFN2DS-TR2F0-050DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1832.7	1832.7	1832.7	1832.7	1832.7
2.5°	1843.3	1834.5	1815.1	1832.7	1829.4
5°	1832.7	1825.8	1806.3	1820.3	1817.0
7.5°	1820.3	1809.9	1790.5	1804.7	1801.1
10°	1801.1	1788.8	1767.7	1781.6	1776.4
12.5°	1774.5	1764.1	1743.0	1751.7	1748.2
15°	1744.6	1734.1	1711.1	1718.3	1709.4
17.5°	1707.6	1697.1	1674.1	1682.9	1674.1
20°	1667.1	1656.6	1631.9	1637.1	1630.2
22.5°	1626.6	1610.7	1587.7	1587.7	1584.2
25°	1579.0	1564.9	1535.0	1538.4	1535.0
27.5°	1526.0	1513.7	1490.9	1485.6	1476.9
30°	1473.3	1459.2	1432.8	1427.5	1420.4
32.5°	1416.9	1406.4	1378.1	1367.5	1360.4
35°	1362.2	1344.7	1316.4	1305.8	1297.0
37.5°	1300.5	1284.7	1256.4	1244.1	1235.3
40°	1237.2	1223.0	1194.7	1179.0	1171.9
42.5°	1175.5	1161.3	1133.2	1115.4	1105.0
45°	1108.5	1096.2	1069.6	1050.4	1043.3
47.5°	1043.3	1030.9	1002.8	983.3	972.8
50°	974.5	965.7	941.1	916.4	907.5
52.5°	907.5	895.2	872.4	853.0	840.6
55°	838.9	828.3	807.1	786.0	777.2
57.5°	770.1	761.3	738.3	717.2	710.1
60°	701.3	694.4	669.8	650.3	645.1
62.5°	634.4	622.1	604.5	586.9	579.8
65°	565.8	555.1	537.5	521.7	512.8
67.5°	495.3	486.4	470.6	458.3	451.1
70°	430.0	423.0	407.0	394.7	387.8
72.5°	363.1	356.0	347.2	334.9	329.6
75°	296.0	292.6	283.6	273.2	276.8
77.5°	236.2	229.0	225.5	220.2	215.1
80°	176.3	174.5	170.9	165.7	162.1
82.5°	119.8	119.8	118.1	111.1	111.1
85°	72.2	70.5	68.8	63.4	61.7
87.5°	31.7	28.3	24.7	19.4	17.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931281

CATALOG NUMBER: DFN2DS-TR2F0-050DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.17	17.78	16.54	18.10	18.41	15.73	17.34	16.09	17.65	17.97
	3H	17.92	19.38	18.30	19.71	20.07	17.43	18.89	17.81	19.21	19.57
	4H	18.57	19.94	18.97	20.29	20.66	18.08	19.45	18.47	19.79	20.17
	6H	19.04	20.31	19.45	20.67	21.06	18.54	19.81	18.95	20.17	20.56
	8H	19.18	20.39	19.61	20.78	21.18	18.68	19.89	19.11	20.28	20.68
	12H	19.27	20.43	19.70	20.81	21.24	18.76	19.92	19.19	20.30	20.73
4H	2H	16.73	18.10	17.13	18.45	18.83	16.38	17.75	16.78	18.10	18.47
	3H	18.71	19.86	19.12	20.25	20.65	18.30	19.45	18.71	19.85	20.25
	4H	19.49	20.52	19.92	20.94	21.37	19.06	20.10	19.49	20.51	20.95
	6H	20.08	20.99	20.54	21.43	21.88	19.65	20.56	20.11	21.00	21.45
	8H	20.27	21.12	20.73	21.56	22.03	19.83	20.68	20.30	21.12	21.59
	12H	20.40	21.16	20.88	21.64	22.11	19.95	20.71	20.43	21.19	21.66
8H	4H	19.76	20.61	20.22	21.05	21.51	19.39	20.23	19.85	20.67	21.14
	6H	20.47	21.18	20.97	21.67	22.14	20.09	20.80	20.59	21.28	21.76
	8H	20.73	21.36	21.24	21.87	22.36	20.34	20.97	20.85	21.48	21.97
	12H	20.93	21.49	21.44	21.98	22.54	20.52	21.08	21.03	21.57	22.13
12H	4H	19.79	20.55	20.27	21.02	21.49	19.42	20.18	19.90	20.66	21.13
	6H	20.52	21.15	21.03	21.66	22.14	20.15	20.78	20.66	21.29	21.78
	8H	20.83	21.39	21.34	21.88	22.44	20.46	21.01	20.96	21.50	22.07