

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931268

Luminaire Tested: DFN2DS-TR2F0-040DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931268
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR2F0-040DS840-RLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3403.4 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.36' x L: 2.04' x H: 0')
CIE Type: Direct

Input Watts (W): 38.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931268

CATALOG NUMBER: DFN2DS-TR2F0-040DS840-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931268

CATALOG NUMBER: DFN2DS-TR2F0-040DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3691	3691	3691
5°	3705	3645	3665
10°	3677	3585	3555
15°	3635	3479	3379
20°	3576	3327	3160
25°	3516	3155	2948
30°	3433	2978	2677
35°	3352	2785	2438
40°	3270	2586	2163
45°	3174	2362	1913
50°	3076	2136	1668
55°	2976	1893	1433
60°	2859	1637	1190
65°	2727	1375	1082
70°	2569	1133	996
75°	2374	1032	930
80°	2096	922	848
85°	1648	727	727

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3174 cd/sqm

TEST NUMBER: P931268

CATALOG NUMBER: DFN2DS-TR2F0-040DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.1	4.6
10°-20°	425.8	12.5
20°-30°	597.8	17.6
30°-40°	651.6	19.1
40°-50°	598.9	17.6
50°-60°	470.3	13.8
60°-70°	306.1	9.0
70°-80°	157.6	4.6
80°-90°	40.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1178.6	34.6
0°-40°	1830.2	53.8
0°-60°	2899.4	85.2
0°-90°	3403.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3403.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1655	1655	1655	1655	1655	
5°	1655	1647	1628	1641	1637	157
15°	1574	1558	1507	1478	1463	444
25°	1429	1381	1282	1221	1198	657
35°	1231	1155	1023	928	896	771
45°	1006	906	749	642	606	777
55°	765	648	487	397	368	684
65°	517	395	261	210	205	512
75°	276	171	120	109	108	291
85°	64	33	28	28	28	77
90°	0	0	0	0	0	

TEST NUMBER: P931268

CATALOG NUMBER: DFN2DS-TR2F0-040DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1654.9	1654.9	1654.9	1654.9	1654.9
2.5°	1662.4	1654.9	1638.3	1653.5	1650.3
5°	1654.9	1647.3	1627.8	1641.3	1636.9
7.5°	1641.3	1632.4	1611.5	1617.3	1609.9
10°	1623.4	1612.9	1583.0	1578.4	1569.6
12.5°	1601.0	1587.5	1546.9	1538.0	1521.5
15°	1574.0	1557.5	1506.6	1478.2	1463.3
17.5°	1542.5	1518.5	1455.6	1422.7	1398.7
20°	1506.6	1476.6	1401.7	1364.4	1331.3
22.5°	1467.7	1433.2	1346.2	1295.4	1273.1
25°	1428.7	1380.8	1281.9	1220.6	1198.0
27.5°	1382.4	1331.3	1222.0	1151.7	1117.1
30°	1332.9	1275.9	1156.1	1079.8	1039.3
32.5°	1285.0	1216.0	1093.3	1003.4	965.9
35°	1231.1	1154.7	1022.9	928.5	895.5
37.5°	1178.7	1096.2	957.0	853.6	816.2
40°	1123.2	1033.4	888.1	781.8	742.8
42.5°	1066.3	970.5	819.2	708.3	671.0
45°	1006.4	906.0	748.8	642.4	606.5
47.5°	949.5	843.2	681.5	575.1	542.1
50°	886.6	780.3	615.5	512.1	480.8
52.5°	825.1	712.8	552.7	453.8	425.3
55°	765.3	648.4	486.7	396.9	368.5
57.5°	703.9	584.1	428.3	344.4	320.5
60°	640.9	521.1	366.9	290.6	266.7
62.5°	579.7	459.9	314.4	242.6	230.7
65°	516.7	395.3	260.6	209.7	205.1
67.5°	456.9	335.4	209.7	184.2	179.7
70°	393.9	277.1	173.7	158.8	152.7
72.5°	334.0	223.1	145.2	133.3	130.3
75°	275.5	170.7	119.8	109.3	107.9
77.5°	217.2	121.2	94.4	88.4	85.3
80°	163.2	86.9	71.8	66.0	66.0
82.5°	113.8	58.5	49.4	46.3	46.3
85°	64.4	32.9	28.4	28.4	28.4
87.5°	24.0	11.9	11.9	10.5	10.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931268

CATALOG NUMBER: DFN2DS-TR2F0-040DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.77	17.29	16.14	17.61	17.92	11.73	13.25	12.10	13.57	13.88
	3H	17.54	18.90	17.92	19.23	19.59	13.00	14.36	13.38	14.69	15.05
	4H	18.20	19.48	18.60	19.83	20.21	13.50	14.78	13.90	15.13	15.51
	6H	18.69	19.88	19.10	20.24	20.63	13.88	15.06	14.29	15.43	15.82
	8H	18.86	19.98	19.28	20.37	20.78	14.00	15.13	14.43	15.52	15.92
	12H	18.96	20.04	19.39	20.42	20.85	14.09	15.16	14.52	15.55	15.97
4H	2H	15.88	17.16	16.28	17.51	17.88	12.43	13.71	12.83	14.06	14.44
	3H	17.81	18.87	18.22	19.27	19.67	13.87	14.93	14.28	15.33	15.73
	4H	18.56	19.52	18.99	19.93	20.37	14.47	15.43	14.90	15.84	16.28
	6H	19.15	19.98	19.61	20.43	20.88	14.96	15.79	15.42	16.23	16.69
	8H	19.37	20.14	19.83	20.59	21.05	15.12	15.90	15.58	16.34	16.81
	12H	19.52	20.21	20.00	20.69	21.16	15.24	15.93	15.72	16.41	16.88
8H	4H	18.58	19.36	19.05	19.80	20.27	14.82	15.60	15.29	16.05	16.51
	6H	19.22	19.86	19.72	20.35	20.83	15.41	16.05	15.91	16.55	17.02
	8H	19.47	20.05	19.98	20.56	21.05	15.63	16.21	16.15	16.72	17.21
	12H	19.68	20.19	20.18	20.68	21.24	15.81	16.32	16.32	16.81	17.38
12H	4H	18.57	19.26	19.05	19.74	20.21	14.87	15.56	15.35	16.04	16.51
	6H	19.20	19.78	19.72	20.29	20.78	15.47	16.05	15.99	16.56	17.05
	8H	19.49	20.00	20.00	20.49	21.05	15.75	16.26	16.26	16.75	17.31