

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931285

Luminaire Tested: DFN2DS-TR2F0-050DS840-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931285
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR2F0-050DS840-FLL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4955.0 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.36' x L: 2.04' x H: 0')
CIE Type: Direct

Input Watts (W): 49.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931285

CATALOG NUMBER: DFN2DS-TR2F0-050DS840-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931285

CATALOG NUMBER: DFN2DS-TR2F0-050DS840-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4344	4344	4344
5°	4360	4297	4323
10°	4335	4254	4275
15°	4281	4199	4195
20°	4205	4116	4112
25°	4129	4014	4014
30°	4032	3921	3887
35°	3941	3809	3753
40°	3828	3697	3626
45°	3716	3585	3497
50°	3593	3470	3346
55°	3467	3335	3212
60°	3324	3175	3058
65°	3173	3015	2876
70°	2980	2820	2687
75°	2710	2597	2534
80°	2407	2333	2213
85°	1963	1871	1679

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3716 cd/sqm

TEST NUMBER: P931285

CATALOG NUMBER: DFN2DS-TR2F0-050DS840-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.3	3.7
10°-20°	515.7	10.4
20°-30°	757.9	15.3
30°-40°	880.3	17.8
40°-50°	879.2	17.7
50°-60°	766.6	15.5
60°-70°	566.7	11.4
70°-80°	320.6	6.5
80°-90°	84.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1456.9	29.4
0°-40°	2337.2	47.2
0°-60°	3983.0	80.4
0°-90°	4955.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4955.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1947	1947	1947	1947	1947	
5°	1947	1940	1919	1934	1931	185
15°	1854	1843	1818	1826	1816	522
25°	1678	1663	1631	1635	1631	772
35°	1448	1429	1399	1388	1378	904
45°	1178	1165	1137	1116	1109	909
55°	892	880	858	835	826	797
65°	601	590	571	554	545	594
75°	314	311	301	290	294	336
85°	77	75	73	67	66	90
90°	0	0	0	0	0	

TEST NUMBER: P931285

CATALOG NUMBER: DFN2DS-TR2F0-050DS840-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1947.4	1947.4	1947.4	1947.4	1947.4
2.5°	1958.8	1949.4	1928.8	1947.4	1943.9
5°	1947.4	1940.1	1919.4	1934.3	1930.8
7.5°	1934.3	1923.2	1902.6	1917.7	1913.9
10°	1913.9	1900.8	1878.4	1893.2	1887.7
12.5°	1885.7	1874.6	1852.2	1861.5	1857.7
15°	1853.9	1842.7	1818.3	1825.9	1816.5
17.5°	1814.5	1803.4	1779.0	1788.3	1779.0
20°	1771.5	1760.4	1734.1	1739.6	1732.3
22.5°	1728.5	1711.6	1687.2	1687.2	1683.4
25°	1677.9	1663.0	1631.1	1634.7	1631.1
27.5°	1621.6	1608.5	1584.3	1578.7	1569.4
30°	1565.6	1550.5	1522.5	1516.9	1509.4
32.5°	1505.6	1494.5	1464.5	1453.2	1445.6
35°	1447.5	1428.9	1398.9	1387.6	1378.3
37.5°	1382.0	1365.2	1335.1	1322.0	1312.7
40°	1314.7	1299.6	1269.6	1252.9	1245.3
42.5°	1249.1	1234.0	1204.2	1185.3	1174.2
45°	1178.0	1164.9	1136.6	1116.2	1108.6
47.5°	1108.6	1095.5	1065.6	1044.8	1033.7
50°	1035.5	1026.2	1000.0	973.8	964.4
52.5°	964.4	951.3	927.0	906.4	893.3
55°	891.5	880.2	857.7	835.2	825.9
57.5°	818.3	809.0	784.6	762.2	754.6
60°	745.2	737.9	711.7	691.0	685.5
62.5°	674.2	661.1	642.3	623.6	616.1
65°	601.2	589.9	571.2	554.4	544.9
67.5°	526.3	516.8	500.1	487.0	479.4
70°	457.0	449.4	432.5	419.4	412.1
72.5°	385.9	378.3	369.0	355.9	350.2
75°	314.5	310.9	301.4	290.3	294.1
77.5°	251.0	243.3	239.6	234.0	228.5
80°	187.4	185.4	181.6	176.1	172.3
82.5°	127.3	127.3	125.5	118.0	118.0
85°	76.7	74.9	73.1	67.4	65.6
87.5°	33.7	30.0	26.2	20.6	18.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931285

CATALOG NUMBER: DFN2DS-TR2F0-050DS840-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.39	18.00	16.75	18.31	18.62	15.94	17.55	16.31	17.87	18.18
	3H	18.14	19.59	18.51	19.92	20.28	17.64	19.10	18.02	19.43	19.79
	4H	18.78	20.15	19.18	20.50	20.87	18.29	19.66	18.69	20.00	20.38
	6H	19.25	20.52	19.66	20.88	21.28	18.75	20.02	19.16	20.38	20.77
	8H	19.39	20.60	19.82	20.99	21.39	18.89	20.10	19.32	20.49	20.89
	12H	19.48	20.64	19.91	21.03	21.45	18.97	20.13	19.40	20.51	20.94
4H	2H	16.95	18.31	17.34	18.66	19.04	16.59	17.96	16.99	18.31	18.69
	3H	18.92	20.07	19.33	20.46	20.86	18.51	19.66	18.92	20.06	20.46
	4H	19.70	20.73	20.13	21.15	21.58	19.27	20.31	19.71	20.72	21.16
	6H	20.29	21.20	20.75	21.64	22.10	19.86	20.77	20.32	21.21	21.66
	8H	20.48	21.33	20.94	21.77	22.24	20.05	20.89	20.51	21.33	21.80
	12H	20.62	21.38	21.10	21.85	22.32	20.16	20.92	20.64	21.40	21.87
8H	4H	19.97	20.82	20.43	21.26	21.73	19.60	20.44	20.06	20.89	21.35
	6H	20.69	21.39	21.18	21.88	22.35	20.30	21.01	20.80	21.50	21.97
	8H	20.94	21.57	21.45	22.08	22.57	20.55	21.18	21.06	21.69	22.18
	12H	21.14	21.70	21.65	22.19	22.75	20.73	21.29	21.24	21.78	22.34
12H	4H	20.00	20.76	20.48	21.23	21.70	19.63	20.39	20.11	20.87	21.34
	6H	20.73	21.36	21.24	21.87	22.36	20.36	20.99	20.87	21.50	21.99
	8H	21.04	21.60	21.55	22.09	22.65	20.67	21.22	21.17	21.72	22.28