

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331386-830

Luminaire Tested: **S122DIP-S865D530U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331386-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S865D530U830-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5537.8 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331386-830
CATALOG NUMBER: S122DIP-S865D530U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331386-830

CATALOG NUMBER: S122DIP-S865D530U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65				
1	102	98	94	90	96	92	89	86	81	79	77	72	70	68	63	61	60	56				
2	93	86	80	75	87	81	76	71	72	68	64	64	61	58	56	54	52	48				
3	85	76	69	63	80	72	66	60	64	59	55	57	53	50	50	47	45	41				
4	79	68	60	54	74	64	57	52	57	52	47	51	47	43	45	42	39	36				
5	72	61	53	47	68	58	51	45	52	46	41	46	42	38	41	37	34	32				
6	67	55	47	41	63	52	45	40	47	41	37	42	37	34	38	34	31	28				
7	62	50	42	36	58	48	40	35	43	37	33	39	34	30	34	31	28	25				
8	58	46	38	33	54	43	36	31	39	33	29	35	31	27	32	28	25	23				
9	54	42	34	29	51	40	33	28	36	30	26	33	28	25	29	26	23	21				
10	51	39	31	27	48	37	30	26	34	28	24	30	26	22	27	24	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	26274	26274	26274	26274
5°	29457	26446	23436	26446
10°	33755	26230	20282	26230
15°	37342	25748	17919	25748
20°	36773	25232	16333	25232
25°	33157	24545	15330	24545
30°	27401	23448	14600	23448
35°	19969	22300	14079	22300
40°	15951	20946	13789	20946
45°	13938	19379	13394	19379
50°	13102	17862	13132	17862
55°	12076	16321	12780	16321
60°	11066	14683	12239	14683
65°	10082	13211	11706	13211
70°	9153	11783	10924	11783
75°	8116	10181	9676	10181
80°	6974	8433	7792	8433
85°	6243	6243	4631	6243



TEST NUMBER: P331386-830

CATALOG NUMBER: S122DIP-S865D530U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.0	2.8
10°-20°	450.6	8.1
20°-30°	653.9	11.8
30°-40°	690.0	12.5
40°-50°	611.0	11.0
50°-60°	487.6	8.8
60°-70°	331.4	6.0
70°-80°	169.9	3.1
80°-90°	43.5	0.8
90°-100°	111.8	2.0
100°-110°	379.3	6.8
110°-120°	402.9	7.3
120°-130°	331.7	6.0
130°-140°	266.3	4.8
140°-150°	201.3	3.6
150°-160°	141.4	2.6
160°-170°	83.3	1.5
170°-180°	27.1	0.5
0°-30°	1259.4	22.7
0°-40°	1949.5	35.2
0°-60°	3048.0	55.0
0°-90°	3592.8	64.9
90°-120°	893.9	16.1
90°-150°	1693.2	30.6
90°-180°	1945.0	35.1
0°-180°	5537.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1627	1627	1627	1627	1627	
5°	1818	1632	1446	1632	1818	181
15°	2234	1540	1072	1540	2234	616
25°	1861	1378	860	1378	1861	841
35°	1013	1131	714	1131	1013	659
45°	610	849	587	849	610	480
55°	429	580	454	580	429	385
65°	264	346	306	346	264	262
75°	130	163	155	163	130	139
85°	34	34	25	34	34	37
90°	18	1	18	1	18	11
95°	61	19	61	19	61	80
105°	606	66	606	66	606	586
115°	797	116	797	116	797	781
125°	647	161	647	161	647	584
135°	536	189	536	189	536	416
145°	428	216	428	216	428	272
155°	360	246	360	246	360	168
165°	316	268	316	268	316	90
175°	284	279	284	279	284	28
180°	280	280	280	280	280	



TEST NUMBER: P331386-830

CATALOG NUMBER: S122DIP-S865D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1702.4	1702.9	1703.9	1695.9	1694.9	1694.9	1687.9	1681.9	1674.9	1665.4	1666.4
5°	1817.5	1824.4	1826.8	1819.4	1808.1	1806.9	1796.2	1778.7	1762.5	1749.3	1739.9
7.5°	1954.8	1957.6	1951.4	1941.5	1933.2	1918.2	1898.4	1879.1	1851.9	1827.0	1808.5
10°	2058.9	2062.7	2052.0	2037.6	2025.7	2008.2	1979.4	1950.0	1914.4	1880.0	1852.5
12.5°	2138.0	2147.2	2133.5	2131.7	2111.3	2087.3	2053.0	2038.2	1988.0	1940.0	1910.5
15°	2234.0	2233.4	2234.7	2222.7	2207.7	2203.9	2167.8	2128.4	2057.7	2029.5	1980.8
17.5°	2206.2	2215.7	2220.2	2220.0	2219.6	2217.2	2205.6	2180.8	2145.3	2099.7	2043.3
20°	2140.2	2152.7	2154.6	2169.0	2177.1	2187.7	2192.1	2185.2	2163.3	2125.2	2076.4
22.5°	2038.2	2041.6	2047.5	2069.9	2087.5	2114.2	2128.1	2151.2	2142.8	2124.2	2083.4
25°	1861.2	1855.0	1876.9	1888.1	1928.8	1971.3	2002.0	2035.7	2065.8	2083.9	2072.0
27.5°	1648.9	1639.5	1672.3	1702.1	1735.1	1781.2	1829.0	1885.4	1932.3	1990.9	2011.1
30°	1469.7	1475.4	1506.7	1538.5	1588.6	1653.6	1707.4	1769.3	1836.3	1901.9	1947.6
32.5°	1276.6	1298.3	1318.1	1366.9	1411.0	1483.5	1562.3	1639.7	1723.2	1797.8	1868.5
35°	1013.1	1038.2	1065.7	1101.4	1163.3	1235.2	1312.1	1416.5	1530.4	1632.4	1716.2
37.5°	852.8	848.9	864.6	890.3	940.5	998.5	1087.1	1190.3	1324.3	1444.1	1562.3
40°	756.8	754.2	765.5	789.3	827.5	870.0	947.5	1038.2	1162.6	1309.0	1449.7
42.5°	690.7	692.2	698.4	715.2	741.4	776.4	834.4	911.6	1025.6	1163.4	1314.7
45°	610.4	614.8	621.7	629.8	644.8	673.5	706.1	761.1	851.2	966.3	1115.1
47.5°	552.6	552.7	559.8	566.8	575.8	592.0	618.5	653.1	716.6	810.3	938.3
50°	521.6	517.3	522.3	527.8	537.2	548.5	566.0	598.5	641.0	716.7	823.7
52.5°	483.6	483.7	488.2	490.3	498.7	510.0	525.9	548.5	587.0	646.2	734.1
55°	429.0	432.2	434.7	438.4	445.9	454.0	466.6	481.5	511.6	556.0	621.0
57.5°	377.8	378.7	381.3	388.4	393.1	400.7	412.6	426.1	445.6	478.5	527.4
60°	342.7	342.7	347.7	350.8	357.1	364.6	374.0	387.1	404.6	431.5	471.0
62.5°	310.8	310.2	312.2	317.4	322.1	329.1	338.5	349.6	366.1	390.0	422.4
65°	263.9	262.7	266.5	267.7	272.7	279.6	287.1	299.0	312.1	329.6	358.4
67.5°	218.9	220.4	222.4	224.8	227.5	234.8	239.8	248.2	259.3	273.8	293.3
70°	193.9	193.9	193.9	195.8	199.5	203.3	208.3	215.2	225.7	238.3	255.8
72.5°	165.9	167.9	169.8	168.7	173.5	175.8	181.7	185.6	195.8	203.8	219.2
75°	130.1	130.1	130.1	133.2	135.1	137.0	140.7	144.5	149.5	159.5	167.6
77.5°	97.1	96.8	97.5	98.2	100.2	102.5	103.6	107.0	111.6	116.2	123.1
80°	75.0	76.3	76.9	78.1	78.1	79.5	80.0	84.5	87.6	90.7	95.1
82.5°	58.1	58.2	58.4	58.6	59.2	59.9	61.5	63.0	64.0	66.6	70.0
85°	33.7	33.2	33.2	34.4	33.7	33.7	35.1	36.3	36.3	36.9	38.7
87.5°	16.6	16.6	17.1	16.6	16.6	17.0	16.8	16.5	17.1	17.6	18.1
90°	17.7	17.7	17.7	17.7	17.7	17.2	16.1	17.2	17.7	18.3	17.7
92.5°	29.8	30.6	30.3	32.0	32.3	35.7	40.2	46.8	59.0	69.8	68.9
95°	61.3	60.7	62.4	66.6	73.6	85.5	108.0	140.8	184.4	210.8	186.5
97.5°	120.6	125.2	133.0	146.2	171.9	210.8	268.9	328.7	377.3	359.7	270.9
100°	192.5	202.1	217.7	240.8	285.4	350.4	424.1	490.8	502.0	424.6	292.4
102.5°	338.7	351.8	371.2	410.7	459.1	528.1	581.9	597.0	548.5	426.8	284.3
105°	605.8	613.3	636.4	669.8	703.0	720.9	713.8	653.1	541.3	398.3	268.2
107.5°	773.8	783.8	788.4	790.2	786.1	760.1	704.2	612.7	494.1	367.8	260.2
110°	824.5	825.1	820.3	810.0	786.9	742.8	674.0	577.9	464.4	353.2	258.5



TEST NUMBER: P331386-830

CATALOG NUMBER: S122DIP-S865D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	823.7	820.8	811.6	794.6	762.4	711.9	638.4	546.0	443.7	343.7	259.0
115°	797.1	792.3	778.4	753.6	715.5	660.1	589.7	506.9	418.2	333.3	261.3
117.5°	749.7	745.6	730.9	704.8	665.9	614.0	550.1	477.4	402.1	328.2	265.1
120°	719.2	713.8	698.2	673.0	635.4	586.4	529.4	462.8	393.5	325.2	267.7
122.5°	687.4	682.9	669.0	644.1	610.4	566.2	512.3	451.2	386.2	323.5	270.7
125°	646.7	642.3	628.9	608.5	577.3	537.0	489.7	434.3	375.7	320.4	275.2
127.5°	611.0	607.5	595.9	576.7	549.6	512.4	467.8	417.6	366.1	318.6	279.8
130°	590.7	586.4	575.7	557.4	531.0	495.6	453.2	406.9	359.6	317.6	283.2
132.5°	569.7	565.8	555.9	537.6	511.7	478.4	439.4	396.6	354.4	317.3	286.7
135°	535.9	533.8	524.1	506.3	483.2	453.2	417.6	382.2	347.2	316.6	290.8
137.5°	502.8	499.5	491.1	475.8	454.8	428.5	400.4	370.7	342.1	316.5	294.5
140°	480.0	476.7	468.7	454.8	437.5	413.9	389.2	363.4	339.2	316.0	296.1
142.5°	457.2	456.6	449.4	436.7	420.4	400.6	379.3	357.3	336.2	316.0	297.5
145°	427.8	426.2	420.8	411.7	398.9	383.2	366.6	348.8	332.2	315.0	298.9
147.5°	403.2	402.3	398.6	391.3	380.7	369.3	356.3	342.3	328.1	313.0	299.3
150°	388.6	388.0	384.8	378.4	370.3	360.7	349.4	337.5	324.7	311.8	298.9
152.5°	376.2	376.1	373.7	368.1	361.7	353.4	343.8	332.8	321.7	309.6	298.0
155°	359.6	360.7	358.5	354.8	348.8	342.9	334.9	326.3	316.0	305.9	296.7
157.5°	345.5	345.5	344.6	341.4	337.2	332.6	325.8	318.7	310.8	302.0	294.3
160°	336.5	336.5	335.9	333.3	329.5	325.7	319.8	313.9	306.9	299.4	292.9
162.5°	327.9	328.3	327.8	325.9	322.2	319.3	314.2	309.2	303.5	297.3	291.6
165°	315.6	316.0	316.0	313.9	311.8	309.6	305.9	302.1	297.7	292.9	289.2
167.5°	304.2	304.8	304.9	303.7	302.7	300.8	298.2	295.3	292.2	289.2	286.7
170°	297.3	298.3	298.9	297.3	296.7	295.7	293.5	291.9	289.2	287.0	285.4
172.5°	291.6	292.3	292.8	292.1	291.5	290.9	289.2	288.0	286.2	284.5	283.7
175°	284.4	285.4	286.0	285.4	285.4	284.9	284.4	283.8	282.2	281.6	281.2
177.5°	279.9	280.8	281.3	281.3	281.3	281.3	280.8	280.8	279.9	279.5	279.9
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5



TEST NUMBER: P331386-830

CATALOG NUMBER: S122DIP-S865D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1669.9	1665.8	1663.4	1654.4	1646.3	1638.3	1635.9	1636.8	1625.9	1615.3	1610.8
5°	1734.9	1722.4	1710.5	1693.7	1673.7	1651.7	1640.5	1631.7	1609.9	1586.1	1572.3
7.5°	1793.2	1775.3	1752.5	1720.7	1691.5	1657.1	1635.2	1615.8	1583.8	1550.3	1529.7
10°	1828.7	1804.3	1774.9	1736.2	1700.5	1658.6	1629.2	1599.9	1562.3	1522.3	1497.2
12.5°	1859.3	1826.4	1797.4	1747.7	1705.5	1653.1	1618.3	1576.8	1537.3	1489.8	1465.3
15°	1931.9	1871.2	1816.2	1759.9	1708.0	1634.8	1596.1	1540.4	1488.5	1429.7	1401.6
17.5°	1988.1	1920.0	1833.2	1761.7	1701.1	1620.1	1563.2	1496.5	1435.1	1367.9	1329.6
20°	2020.2	1941.9	1848.7	1763.7	1691.1	1598.6	1536.6	1468.5	1396.6	1320.9	1279.6
22.5°	2039.1	1956.9	1864.7	1756.1	1671.1	1581.0	1503.2	1428.4	1355.6	1273.8	1230.6
25°	2045.1	1970.1	1872.5	1749.9	1646.2	1544.2	1450.4	1377.8	1289.6	1213.3	1150.2
27.5°	2015.3	1961.5	1867.7	1738.1	1617.2	1498.0	1393.5	1311.3	1218.2	1135.4	1071.9
30°	1978.9	1947.6	1856.2	1726.2	1594.2	1466.0	1350.9	1257.7	1165.2	1081.4	1016.3
32.5°	1922.3	1915.5	1835.2	1709.1	1569.7	1425.5	1306.4	1212.2	1109.7	1027.3	965.3
35°	1811.2	1841.3	1790.5	1671.1	1523.5	1367.8	1239.0	1131.4	1025.1	946.2	888.1
37.5°	1662.4	1736.9	1723.6	1615.4	1461.2	1305.0	1162.8	1050.4	949.0	869.5	812.4
40°	1559.8	1654.8	1668.6	1572.9	1417.2	1256.5	1105.8	993.8	894.9	822.5	764.9
42.5°	1449.7	1560.8	1598.6	1521.9	1369.1	1205.4	1054.7	938.8	840.9	770.4	719.3
45°	1265.3	1412.2	1480.4	1436.6	1289.0	1121.3	966.3	848.7	759.9	693.6	654.2
47.5°	1092.7	1253.3	1345.0	1329.6	1199.8	1033.8	880.4	767.6	681.2	628.3	593.0
50°	970.6	1135.8	1246.4	1251.5	1135.8	971.3	817.5	711.1	631.7	582.3	553.5
52.5°	864.6	1022.2	1142.9	1169.4	1064.2	906.3	760.9	655.1	585.1	539.7	514.0
55°	726.1	859.3	993.2	1042.0	957.5	807.4	673.0	579.8	514.1	482.9	460.3
57.5°	603.7	714.7	838.3	892.2	840.2	711.7	585.6	504.7	451.4	424.0	406.8
60°	539.1	626.7	736.8	801.2	756.1	641.7	531.6	454.7	410.9	386.5	370.2
62.5°	479.1	556.7	649.7	708.6	684.1	576.2	477.6	409.6	371.8	349.0	337.2
65°	395.3	456.6	528.5	582.9	566.7	484.7	404.1	345.8	315.8	297.7	288.3
67.5°	325.5	369.8	419.6	467.3	454.2	396.2	331.3	286.1	263.7	248.1	242.4
70°	281.4	315.2	359.6	397.8	387.1	339.6	288.3	249.6	230.2	217.1	211.4
72.5°	239.4	267.2	301.0	332.2	325.1	285.6	242.8	213.5	198.6	186.5	181.9
75°	180.8	202.0	222.6	243.3	241.4	210.8	185.8	163.2	151.4	141.9	140.1
77.5°	133.5	145.3	159.4	171.6	168.2	150.7	131.1	118.2	109.4	103.2	102.2
80°	102.0	108.9	118.9	127.6	123.2	115.7	100.1	90.7	84.5	78.1	75.7
82.5°	73.9	80.8	86.8	91.5	88.2	81.2	71.5	65.1	61.5	57.1	56.2
85°	38.7	42.5	45.1	46.3	45.1	40.6	36.3	33.7	30.6	28.7	28.2
87.5°	17.9	17.2	16.6	17.3	15.6	15.4	12.9	11.1	10.9	10.8	10.1
90°	14.5	10.7	8.1	6.4	5.4	4.3	2.2	0.6	2.2	4.3	5.4
92.5°	53.6	36.6	24.4	19.3	15.7	13.3	9.4	6.6	9.4	13.3	15.7
95°	124.1	77.4	52.7	39.8	31.2	26.3	20.9	18.9	20.9	26.3	31.2
97.5°	167.3	102.2	71.1	56.5	46.6	39.2	33.6	30.6	33.6	39.2	46.6
100°	176.3	110.7	82.3	67.2	56.5	47.9	43.0	41.4	43.0	47.9	56.5
102.5°	176.7	118.5	92.1	77.1	65.9	57.3	52.5	51.3	52.5	57.3	65.9
105°	179.6	131.7	106.4	91.3	79.6	71.4	67.8	65.6	67.8	71.4	79.6
107.5°	186.9	145.2	120.7	105.6	93.9	86.4	82.8	81.1	82.8	86.4	93.9
110°	192.9	154.3	130.6	115.0	103.8	96.8	93.5	91.3	93.5	96.8	103.8



TEST NUMBER: P331386-830

CATALOG NUMBER: S122DIP-S865D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	199.4	162.9	140.1	124.0	113.2	106.6	103.0	100.9	103.0	106.6	113.2
115°	209.1	176.3	153.2	138.6	127.9	121.5	118.3	115.6	118.3	121.5	127.9
117.5°	219.4	188.7	167.3	152.2	141.9	136.2	133.0	130.8	133.0	136.2	141.9
120°	226.3	197.3	176.3	161.3	150.5	145.6	142.4	140.3	142.4	145.6	150.5
122.5°	232.3	205.5	185.8	170.3	159.6	154.3	151.1	149.3	151.1	154.3	159.6
125°	241.9	217.7	198.3	183.3	172.6	166.1	162.9	161.3	162.9	166.1	172.6
127.5°	250.8	229.1	210.3	194.8	184.5	177.4	172.9	170.7	172.9	177.4	184.5
130°	256.4	236.0	217.2	202.1	191.3	183.8	178.4	176.3	178.4	183.8	191.3
132.5°	262.0	242.0	224.0	209.0	197.8	189.8	184.1	181.4	184.1	189.8	197.8
135°	269.3	250.5	233.3	218.2	205.9	197.8	191.3	189.2	191.3	197.8	205.9
137.5°	274.8	257.4	240.3	226.4	214.1	205.6	199.1	196.5	199.1	205.6	214.1
140°	277.9	261.3	245.2	231.1	219.3	210.8	204.2	202.1	204.2	210.8	219.3
142.5°	280.5	264.3	248.5	235.4	224.0	215.5	209.4	207.7	209.4	215.5	224.0
145°	283.8	268.7	254.2	242.4	231.7	223.6	218.2	216.1	218.2	223.6	231.7
147.5°	285.7	272.4	258.7	248.3	239.3	231.9	226.7	225.1	226.7	231.9	239.3
150°	286.5	274.1	261.7	252.1	244.0	237.0	232.7	231.1	232.7	237.0	244.0
152.5°	286.9	275.9	264.8	256.0	248.4	242.2	237.9	237.1	237.9	242.2	248.4
155°	287.6	278.4	269.3	261.3	255.3	249.4	246.2	245.6	246.2	249.4	255.3
157.5°	287.6	280.2	272.5	265.8	261.0	255.9	253.3	252.7	253.3	255.9	261.0
160°	287.6	281.2	274.7	268.7	264.5	260.1	258.0	257.5	258.0	260.1	264.5
162.5°	287.1	281.5	276.0	271.4	267.5	264.0	261.8	262.2	261.8	264.0	267.5
165°	286.0	282.2	277.4	274.1	271.5	268.2	267.1	267.7	267.1	268.2	271.5
167.5°	285.2	282.1	278.5	276.5	274.6	272.5	271.5	272.2	271.5	272.5	274.6
170°	284.4	281.6	279.0	277.4	276.3	274.7	274.1	275.2	274.1	274.7	276.3
172.5°	283.0	281.3	279.4	278.2	277.6	276.0	276.3	276.9	276.3	276.0	277.6
175°	281.6	280.6	279.5	279.0	279.0	277.9	278.4	279.0	278.4	277.9	279.0
177.5°	280.8	279.9	279.5	279.5	279.5	278.6	279.1	279.9	279.1	278.6	279.5
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5



TEST NUMBER: P331386-830

CATALOG NUMBER: S122DIP-S865D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1605.8	1602.8	1592.3	1586.9	1577.8	1569.3	1563.8	1566.3	1568.3	1567.3	1565.8
5°	1559.8	1547.9	1529.7	1514.1	1502.9	1482.2	1473.5	1469.1	1465.4	1460.9	1456.6
7.5°	1505.1	1486.3	1460.2	1437.9	1416.9	1391.3	1376.7	1367.9	1359.0	1349.1	1340.3
10°	1466.0	1439.7	1412.2	1380.9	1355.9	1332.8	1312.1	1298.4	1285.9	1273.9	1265.3
12.5°	1424.9	1394.7	1360.7	1317.9	1290.3	1257.3	1254.1	1229.8	1210.3	1203.0	1192.7
15°	1359.7	1317.1	1273.9	1223.3	1201.5	1171.4	1152.6	1133.9	1117.0	1105.1	1102.0
17.5°	1285.5	1230.5	1187.5	1151.1	1115.2	1084.5	1067.2	1052.3	1038.3	1022.5	1020.3
20°	1229.0	1181.4	1134.5	1102.6	1065.7	1034.4	1013.1	998.2	986.3	976.9	968.7
22.5°	1175.4	1123.4	1080.4	1045.6	1009.2	983.9	967.1	952.6	942.7	932.4	924.7
25°	1089.5	1048.9	1001.9	962.5	932.5	916.2	902.5	889.9	883.7	876.8	868.1
27.5°	1014.3	969.1	925.3	894.8	868.4	853.9	844.2	835.7	829.8	825.8	820.8
30°	961.3	915.6	881.2	851.2	829.3	814.9	808.7	803.7	796.8	794.3	791.8
32.5°	910.2	869.1	839.7	813.7	792.8	783.4	777.7	773.2	767.8	765.3	760.3
35°	838.1	803.7	774.9	760.5	743.7	735.5	731.1	724.9	719.8	717.4	716.7
37.5°	770.2	740.3	721.3	702.9	695.7	690.7	684.8	680.4	678.9	678.5	678.0
40°	726.1	701.7	684.9	669.9	666.7	659.2	654.2	650.4	650.4	651.1	650.4
42.5°	686.1	664.2	649.3	636.3	632.6	628.2	623.2	622.9	624.0	626.0	624.0
45°	625.4	609.8	599.2	592.9	586.0	581.6	581.0	582.9	583.5	584.2	586.0
47.5°	569.7	559.2	549.6	542.7	539.7	538.9	538.2	541.5	544.5	545.6	548.5
50°	536.6	524.7	516.6	512.2	509.7	508.5	509.7	513.5	515.9	519.1	520.9
52.5°	499.5	491.2	485.6	482.2	481.2	481.9	482.2	486.4	490.5	491.5	492.5
55°	448.5	442.1	440.9	435.3	437.8	437.2	440.3	442.8	446.6	450.3	450.9
57.5°	397.4	392.4	389.0	389.6	390.3	393.0	395.7	400.0	404.1	408.0	408.4
60°	363.4	360.9	359.0	359.0	360.2	364.0	367.1	371.5	374.0	376.5	378.3
62.5°	332.3	329.9	328.0	328.9	332.2	334.5	338.1	340.4	343.0	345.4	346.4
65°	283.3	282.1	284.0	285.2	285.8	289.0	293.3	295.2	297.7	299.0	303.3
67.5°	238.2	238.4	238.2	239.9	243.6	244.3	248.5	252.8	253.3	255.7	258.5
70°	207.6	208.9	210.2	211.4	214.5	215.7	218.9	220.7	223.3	225.2	227.1
72.5°	179.6	179.8	181.2	180.9	183.5	186.2	188.9	190.8	193.2	195.7	197.5
75°	138.2	138.2	139.5	140.1	143.3	146.4	145.7	146.9	149.5	151.9	153.3
77.5°	100.9	99.5	100.9	101.6	102.5	105.2	105.7	107.4	110.3	109.4	110.8
80°	76.9	75.0	76.9	77.6	77.6	80.7	80.7	81.9	83.8	81.9	83.8
82.5°	55.0	54.0	55.4	55.5	56.6	56.6	57.7	57.9	59.8	58.9	59.8
85°	27.5	26.9	27.5	26.9	27.5	28.2	28.2	27.5	27.5	28.7	26.9
87.5°	9.8	9.6	9.6	10.4	10.6	10.2	9.5	9.4	9.2	8.5	8.6
90°	6.4	8.1	10.7	14.5	17.7	18.3	17.7	17.2	16.1	17.2	17.7
92.5°	19.3	24.4	36.6	53.6	68.9	69.8	59.0	46.8	40.2	35.7	32.3
95°	39.8	52.7	77.4	124.1	186.5	210.8	184.4	140.8	108.0	85.5	73.6
97.5°	56.5	71.1	102.2	167.3	270.9	359.7	377.3	328.7	268.9	210.8	171.9
100°	67.2	82.3	110.7	176.3	292.4	424.6	502.0	490.8	424.1	350.4	285.4
102.5°	77.1	92.1	118.5	176.7	284.3	426.8	548.5	597.0	581.9	528.1	459.1
105°	91.3	106.4	131.7	179.6	268.2	398.3	541.3	653.1	713.8	720.9	703.0
107.5°	105.6	120.7	145.2	186.9	260.2	367.8	494.1	612.7	704.2	760.1	786.1
110°	115.0	130.6	154.3	192.9	258.5	353.2	464.4	577.9	674.0	742.8	786.9



TEST NUMBER: P331386-830

CATALOG NUMBER: S122DIP-S865D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	124.0	140.1	162.9	199.4	259.0	343.7	443.7	546.0	638.4	711.9	762.4
115°	138.6	153.2	176.3	209.1	261.3	333.3	418.2	506.9	589.7	660.1	715.5
117.5°	152.2	167.3	188.7	219.4	265.1	328.2	402.1	477.4	550.1	614.0	665.9
120°	161.3	176.3	197.3	226.3	267.7	325.2	393.5	462.8	529.4	586.4	635.4
122.5°	170.3	185.8	205.5	232.3	270.7	323.5	386.2	451.2	512.3	566.2	610.4
125°	183.3	198.3	217.7	241.9	275.2	320.4	375.7	434.3	489.7	537.0	577.3
127.5°	194.8	210.3	229.1	250.8	279.8	318.6	366.1	417.6	467.8	512.4	549.6
130°	202.1	217.2	236.0	256.4	283.2	317.6	359.6	406.9	453.2	495.6	531.0
132.5°	209.0	224.0	242.0	262.0	286.7	317.3	354.4	396.6	439.4	478.4	511.7
135°	218.2	233.3	250.5	269.3	290.8	316.6	347.2	382.2	417.6	453.2	483.2
137.5°	226.4	240.3	257.4	274.8	294.5	316.5	342.1	370.7	400.4	428.5	454.8
140°	231.1	245.2	261.3	277.9	296.1	316.0	339.2	363.4	389.2	413.9	437.5
142.5°	235.4	248.5	264.3	280.5	297.5	316.0	336.2	357.3	379.3	400.6	420.4
145°	242.4	254.2	268.7	283.8	298.9	315.0	332.2	348.8	366.6	383.2	398.9
147.5°	248.3	258.7	272.4	285.7	299.3	313.0	328.1	342.3	356.3	369.3	380.7
150°	252.1	261.7	274.1	286.5	298.9	311.8	324.7	337.5	349.4	360.7	370.3
152.5°	256.0	264.8	275.9	286.9	298.0	309.6	321.7	332.8	343.8	353.4	361.7
155°	261.3	269.3	278.4	287.6	296.7	305.9	316.0	326.3	334.9	342.9	348.8
157.5°	265.8	272.5	280.2	287.6	294.3	302.0	310.8	318.7	325.8	332.6	337.2
160°	268.7	274.7	281.2	287.6	292.9	299.4	306.9	313.9	319.8	325.7	329.5
162.5°	271.4	276.0	281.5	287.1	291.6	297.3	303.5	309.2	314.2	319.3	322.2
165°	274.1	277.4	282.2	286.0	289.2	292.9	297.7	302.1	305.9	309.6	311.8
167.5°	276.5	278.5	282.1	285.2	286.7	289.2	292.2	295.3	298.2	300.8	302.7
170°	277.4	279.0	281.6	284.4	285.4	287.0	289.2	291.9	293.5	295.7	296.7
172.5°	278.2	279.4	281.3	283.0	283.7	284.5	286.2	288.0	289.2	290.9	291.5
175°	279.0	279.5	280.6	281.6	281.2	281.6	282.2	283.8	284.4	284.9	285.4
177.5°	279.5	279.5	279.9	280.8	279.9	279.5	279.9	280.8	280.8	281.3	281.3
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5



TEST NUMBER: P331386-830

CATALOG NUMBER: S122DIP-S865D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1560.8	1559.8	1559.8	1555.3	1559.8	1559.8	1560.8	1565.8	1567.3	1568.3	1566.3
5°	1447.8	1446.0	1442.8	1446.0	1442.8	1446.0	1447.8	1456.6	1460.9	1465.4	1469.1
7.5°	1336.1	1328.6	1327.5	1320.1	1327.5	1328.6	1336.1	1340.3	1349.1	1359.0	1367.9
10°	1254.6	1249.6	1249.0	1237.1	1249.0	1249.6	1254.6	1265.3	1273.9	1285.9	1298.4
12.5°	1192.6	1180.5	1182.9	1176.0	1182.9	1180.5	1192.6	1192.7	1203.0	1210.3	1229.8
15°	1085.1	1085.1	1082.6	1072.0	1082.6	1085.1	1085.1	1102.0	1105.1	1117.0	1133.9
17.5°	1008.0	1006.6	1000.7	1003.7	1000.7	1006.6	1008.0	1020.3	1022.5	1038.3	1052.3
20°	961.9	958.2	950.6	950.6	950.6	958.2	961.9	968.7	976.9	986.3	998.2
22.5°	918.4	918.1	910.1	912.6	910.1	918.1	918.4	924.7	932.4	942.7	952.6
25°	867.4	862.4	858.8	860.5	858.8	862.4	867.4	868.1	876.8	883.7	889.9
27.5°	819.2	816.4	816.1	811.1	816.1	816.4	819.2	820.8	825.8	829.8	835.7
30°	791.2	784.9	786.2	783.1	786.2	784.9	791.2	791.8	794.3	796.8	803.7
32.5°	759.1	756.9	755.6	753.0	755.6	756.9	759.1	760.3	765.3	767.8	773.2
35°	715.5	716.1	712.9	714.3	712.9	716.1	715.5	716.7	717.4	719.8	724.9
37.5°	677.3	679.3	677.9	678.3	677.9	679.3	677.3	678.0	678.5	678.9	680.4
40°	652.3	652.3	652.3	654.2	652.3	652.3	652.3	650.4	651.1	650.4	650.4
42.5°	628.3	627.3	626.3	626.1	626.3	627.3	628.3	624.0	626.0	624.0	622.9
45°	587.3	589.2	589.7	586.6	589.7	589.2	587.3	586.0	584.2	583.5	582.9
47.5°	550.2	550.4	550.2	552.9	550.2	550.4	550.2	548.5	545.6	544.5	541.5
50°	524.1	522.8	524.1	522.8	524.1	522.8	524.1	520.9	519.1	515.9	513.5
52.5°	496.6	496.8	496.1	495.9	496.1	496.8	496.6	492.5	491.5	490.5	486.4
55°	453.5	454.7	454.0	454.0	454.0	454.7	453.5	450.9	450.3	446.6	442.8
57.5°	408.8	409.9	410.8	408.0	410.8	409.9	408.8	408.4	408.0	404.1	400.0
60°	377.8	380.9	380.2	379.0	380.2	380.9	377.8	378.3	376.5	374.0	371.5
62.5°	349.2	350.3	350.2	350.0	350.2	350.3	349.2	346.4	345.4	343.0	340.4
65°	305.2	306.4	304.5	306.4	304.5	306.4	305.2	303.3	299.0	297.7	295.2
67.5°	257.8	258.2	259.6	260.4	259.6	258.2	257.8	258.5	255.7	253.3	252.8
70°	228.3	227.6	229.5	231.4	229.5	227.6	228.3	227.1	225.2	223.3	220.7
72.5°	197.3	198.6	198.0	199.3	198.0	198.6	197.3	197.5	195.7	193.2	190.8
75°	151.9	153.8	153.3	155.1	153.3	153.8	151.9	153.3	151.9	149.5	146.9
77.5°	109.8	110.1	109.8	110.8	109.8	110.1	109.8	110.8	109.4	110.3	107.4
80°	83.8	82.6	81.3	83.8	81.3	82.6	83.8	83.8	81.9	83.8	81.9
82.5°	58.2	59.0	57.8	57.8	57.8	59.0	58.2	59.8	58.9	59.8	57.9
85°	26.9	26.3	25.0	25.0	25.0	26.3	26.9	26.9	28.7	27.5	27.5
87.5°	8.6	8.0	8.0	7.5	8.0	8.0	8.6	8.6	8.5	9.2	9.4
90°	17.7	17.7	17.7	17.7	17.7	17.7	17.7	17.7	17.2	16.1	17.2
92.5°	32.0	30.3	30.6	29.8	30.6	30.3	32.0	32.3	35.7	40.2	46.8
95°	66.6	62.4	60.7	61.3	60.7	62.4	66.6	73.6	85.5	108.0	140.8
97.5°	146.2	133.0	125.2	120.6	125.2	133.0	146.2	171.9	210.8	268.9	328.7
100°	240.8	217.7	202.1	192.5	202.1	217.7	240.8	285.4	350.4	424.1	490.8
102.5°	410.7	371.2	351.8	338.7	351.8	371.2	410.7	459.1	528.1	581.9	597.0
105°	669.8	636.4	613.3	605.8	613.3	636.4	669.8	703.0	720.9	713.8	653.1
107.5°	790.2	788.4	783.8	773.8	783.8	788.4	790.2	786.1	760.1	704.2	612.7
110°	810.0	820.3	825.1	824.5	825.1	820.3	810.0	786.9	742.8	674.0	577.9



TEST NUMBER: P331386-830

CATALOG NUMBER: S122DIP-S865D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	794.6	811.6	820.8	823.7	820.8	811.6	794.6	762.4	711.9	638.4	546.0
115°	753.6	778.4	792.3	797.1	792.3	778.4	753.6	715.5	660.1	589.7	506.9
117.5°	704.8	730.9	745.6	749.7	745.6	730.9	704.8	665.9	614.0	550.1	477.4
120°	673.0	698.2	713.8	719.2	713.8	698.2	673.0	635.4	586.4	529.4	462.8
122.5°	644.1	669.0	682.9	687.4	682.9	669.0	644.1	610.4	566.2	512.3	451.2
125°	608.5	628.9	642.3	646.7	642.3	628.9	608.5	577.3	537.0	489.7	434.3
127.5°	576.7	595.9	607.5	611.0	607.5	595.9	576.7	549.6	512.4	467.8	417.6
130°	557.4	575.7	586.4	590.7	586.4	575.7	557.4	531.0	495.6	453.2	406.9
132.5°	537.6	555.9	565.8	569.7	565.8	555.9	537.6	511.7	478.4	439.4	396.6
135°	506.3	524.1	533.8	535.9	533.8	524.1	506.3	483.2	453.2	417.6	382.2
137.5°	475.8	491.1	499.5	502.8	499.5	491.1	475.8	454.8	428.5	400.4	370.7
140°	454.8	468.7	476.7	480.0	476.7	468.7	454.8	437.5	413.9	389.2	363.4
142.5°	436.7	449.4	456.6	457.2	456.6	449.4	436.7	420.4	400.6	379.3	357.3
145°	411.7	420.8	426.2	427.8	426.2	420.8	411.7	398.9	383.2	366.6	348.8
147.5°	391.3	398.6	402.3	403.2	402.3	398.6	391.3	380.7	369.3	356.3	342.3
150°	378.4	384.8	388.0	388.6	388.0	384.8	378.4	370.3	360.7	349.4	337.5
152.5°	368.1	373.7	376.1	376.2	376.1	373.7	368.1	361.7	353.4	343.8	332.8
155°	354.8	358.5	360.7	359.6	360.7	358.5	354.8	348.8	342.9	334.9	326.3
157.5°	341.4	344.6	345.5	345.5	345.5	344.6	341.4	337.2	332.6	325.8	318.7
160°	333.3	335.9	336.5	336.5	336.5	335.9	333.3	329.5	325.7	319.8	313.9
162.5°	325.9	327.8	328.3	327.9	328.3	327.8	325.9	322.2	319.3	314.2	309.2
165°	313.9	316.0	316.0	315.6	316.0	316.0	313.9	311.8	309.6	305.9	302.1
167.5°	303.7	304.9	304.8	304.2	304.8	304.9	303.7	302.7	300.8	298.2	295.3
170°	297.3	298.9	298.3	297.3	298.3	298.9	297.3	296.7	295.7	293.5	291.9
172.5°	292.1	292.8	292.3	291.6	292.3	292.8	292.1	291.5	290.9	289.2	288.0
175°	285.4	286.0	285.4	284.4	285.4	286.0	285.4	285.4	284.9	284.4	283.8
177.5°	281.3	281.3	280.8	279.9	280.8	281.3	281.3	281.3	281.3	280.8	280.8
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5



TEST NUMBER: P331386-830

CATALOG NUMBER: S122DIP-S865D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1563.8	1569.3	1577.8	1586.9	1592.3	1602.8	1605.8	1610.8	1615.3	1625.9	1636.8
5°	1473.5	1482.2	1502.9	1514.1	1529.7	1547.9	1559.8	1572.3	1586.1	1609.9	1631.7
7.5°	1376.7	1391.3	1416.9	1437.9	1460.2	1486.3	1505.1	1529.7	1550.3	1583.8	1615.8
10°	1312.1	1332.8	1355.9	1380.9	1412.2	1439.7	1466.0	1497.2	1522.3	1562.3	1599.9
12.5°	1254.1	1257.3	1290.3	1317.9	1360.7	1394.7	1424.9	1465.3	1489.8	1537.3	1576.8
15°	1152.6	1171.4	1201.5	1223.3	1273.9	1317.1	1359.7	1401.6	1429.7	1488.5	1540.4
17.5°	1067.2	1084.5	1115.2	1151.1	1187.5	1230.5	1285.5	1329.6	1367.9	1435.1	1496.5
20°	1013.1	1034.4	1065.7	1102.6	1134.5	1181.4	1229.0	1279.6	1320.9	1396.6	1468.5
22.5°	967.1	983.9	1009.2	1045.6	1080.4	1123.4	1175.4	1230.6	1273.8	1355.6	1428.4
25°	902.5	916.2	932.5	962.5	1001.9	1048.9	1089.5	1150.2	1213.3	1289.6	1377.8
27.5°	844.2	853.9	868.4	894.8	925.3	969.1	1014.3	1071.9	1135.4	1218.2	1311.3
30°	808.7	814.9	829.3	851.2	881.2	915.6	961.3	1016.3	1081.4	1165.2	1257.7
32.5°	777.7	783.4	792.8	813.7	839.7	869.1	910.2	965.3	1027.3	1109.7	1212.2
35°	731.1	735.5	743.7	760.5	774.9	803.7	838.1	888.1	946.2	1025.1	1131.4
37.5°	684.8	690.7	695.7	702.9	721.3	740.3	770.2	812.4	869.5	949.0	1050.4
40°	654.2	659.2	666.7	669.9	684.9	701.7	726.1	764.9	822.5	894.9	993.8
42.5°	623.2	628.2	632.6	636.3	649.3	664.2	686.1	719.3	770.4	840.9	938.8
45°	581.0	581.6	586.0	592.9	599.2	609.8	625.4	654.2	693.6	759.9	848.7
47.5°	538.2	538.9	539.7	542.7	549.6	559.2	569.7	593.0	628.3	681.2	767.6
50°	509.7	508.5	509.7	512.2	516.6	524.7	536.6	553.5	582.3	631.7	711.1
52.5°	482.2	481.9	481.2	482.2	485.6	491.2	499.5	514.0	539.7	585.1	655.1
55°	440.3	437.2	437.8	435.3	440.9	442.1	448.5	460.3	482.9	514.1	579.8
57.5°	395.7	393.0	390.3	389.6	389.0	392.4	397.4	406.8	424.0	451.4	504.7
60°	367.1	364.0	360.2	359.0	359.0	360.9	363.4	370.2	386.5	410.9	454.7
62.5°	338.1	334.5	332.2	328.9	328.0	329.9	332.3	337.2	349.0	371.8	409.6
65°	293.3	289.0	285.8	285.2	284.0	282.1	283.3	288.3	297.7	315.8	345.8
67.5°	248.5	244.3	243.6	239.9	238.2	238.4	238.2	242.4	248.1	263.7	286.1
70°	218.9	215.7	214.5	211.4	210.2	208.9	207.6	211.4	217.1	230.2	249.6
72.5°	188.9	186.2	183.5	180.9	181.2	179.8	179.6	181.9	186.5	198.6	213.5
75°	145.7	146.4	143.3	140.1	139.5	138.2	138.2	140.1	141.9	151.4	163.2
77.5°	105.7	105.2	102.5	101.6	100.9	99.5	100.9	102.2	103.2	109.4	118.2
80°	80.7	80.7	77.6	77.6	76.9	75.0	76.9	75.7	78.1	84.5	90.7
82.5°	57.7	56.6	56.6	55.5	55.4	54.0	55.0	56.2	57.1	61.5	65.1
85°	28.2	28.2	27.5	26.9	27.5	26.9	27.5	28.2	28.7	30.6	33.7
87.5°	9.5	10.2	10.6	10.4	9.6	9.6	9.8	10.1	10.8	10.9	11.1
90°	17.7	18.3	17.7	14.5	10.7	8.1	6.4	5.4	4.3	2.2	0.6
92.5°	59.0	69.8	68.9	53.6	36.6	24.4	19.3	15.7	13.3	9.4	6.6
95°	184.4	210.8	186.5	124.1	77.4	52.7	39.8	31.2	26.3	20.9	18.9
97.5°	377.3	359.7	270.9	167.3	102.2	71.1	56.5	46.6	39.2	33.6	30.6
100°	502.0	424.6	292.4	176.3	110.7	82.3	67.2	56.5	47.9	43.0	41.4
102.5°	548.5	426.8	284.3	176.7	118.5	92.1	77.1	65.9	57.3	52.5	51.3
105°	541.3	398.3	268.2	179.6	131.7	106.4	91.3	79.6	71.4	67.8	65.6
107.5°	494.1	367.8	260.2	186.9	145.2	120.7	105.6	93.9	86.4	82.8	81.1
110°	464.4	353.2	258.5	192.9	154.3	130.6	115.0	103.8	96.8	93.5	91.3



TEST NUMBER: P331386-830

CATALOG NUMBER: S122DIP-S865D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	443.7	343.7	259.0	199.4	162.9	140.1	124.0	113.2	106.6	103.0	100.9
115°	418.2	333.3	261.3	209.1	176.3	153.2	138.6	127.9	121.5	118.3	115.6
117.5°	402.1	328.2	265.1	219.4	188.7	167.3	152.2	141.9	136.2	133.0	130.8
120°	393.5	325.2	267.7	226.3	197.3	176.3	161.3	150.5	145.6	142.4	140.3
122.5°	386.2	323.5	270.7	232.3	205.5	185.8	170.3	159.6	154.3	151.1	149.3
125°	375.7	320.4	275.2	241.9	217.7	198.3	183.3	172.6	166.1	162.9	161.3
127.5°	366.1	318.6	279.8	250.8	229.1	210.3	194.8	184.5	177.4	172.9	170.7
130°	359.6	317.6	283.2	256.4	236.0	217.2	202.1	191.3	183.8	178.4	176.3
132.5°	354.4	317.3	286.7	262.0	242.0	224.0	209.0	197.8	189.8	184.1	181.4
135°	347.2	316.6	290.8	269.3	250.5	233.3	218.2	205.9	197.8	191.3	189.2
137.5°	342.1	316.5	294.5	274.8	257.4	240.3	226.4	214.1	205.6	199.1	196.5
140°	339.2	316.0	296.1	277.9	261.3	245.2	231.1	219.3	210.8	204.2	202.1
142.5°	336.2	316.0	297.5	280.5	264.3	248.5	235.4	224.0	215.5	209.4	207.7
145°	332.2	315.0	298.9	283.8	268.7	254.2	242.4	231.7	223.6	218.2	216.1
147.5°	328.1	313.0	299.3	285.7	272.4	258.7	248.3	239.3	231.9	226.7	225.1
150°	324.7	311.8	298.9	286.5	274.1	261.7	252.1	244.0	237.0	232.7	231.1
152.5°	321.7	309.6	298.0	286.9	275.9	264.8	256.0	248.4	242.2	237.9	237.1
155°	316.0	305.9	296.7	287.6	278.4	269.3	261.3	255.3	249.4	246.2	245.6
157.5°	310.8	302.0	294.3	287.6	280.2	272.5	265.8	261.0	255.9	253.3	252.7
160°	306.9	299.4	292.9	287.6	281.2	274.7	268.7	264.5	260.1	258.0	257.5
162.5°	303.5	297.3	291.6	287.1	281.5	276.0	271.4	267.5	264.0	261.8	262.2
165°	297.7	292.9	289.2	286.0	282.2	277.4	274.1	271.5	268.2	267.1	267.7
167.5°	292.2	289.2	286.7	285.2	282.1	278.5	276.5	274.6	272.5	271.5	272.2
170°	289.2	287.0	285.4	284.4	281.6	279.0	277.4	276.3	274.7	274.1	275.2
172.5°	286.2	284.5	283.7	283.0	281.3	279.4	278.2	277.6	276.0	276.3	276.9
175°	282.2	281.6	281.2	281.6	280.6	279.5	279.0	279.0	277.9	278.4	279.0
177.5°	279.9	279.5	279.9	280.8	279.9	279.5	279.5	279.5	278.6	279.1	279.9
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5



TEST NUMBER: P331386-830

CATALOG NUMBER: S122DIP-S865D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1635.9	1638.3	1646.3	1654.4	1663.4	1665.8	1669.9	1666.4	1665.4	1674.9	1681.9
5°	1640.5	1651.7	1673.7	1693.7	1710.5	1722.4	1734.9	1739.9	1749.3	1762.5	1778.7
7.5°	1635.2	1657.1	1691.5	1720.7	1752.5	1775.3	1793.2	1808.5	1827.0	1851.9	1879.1
10°	1629.2	1658.6	1700.5	1736.2	1774.9	1804.3	1828.7	1852.5	1880.0	1914.4	1950.0
12.5°	1618.3	1653.1	1705.5	1747.7	1797.4	1826.4	1859.3	1910.5	1940.0	1988.0	2038.2
15°	1596.1	1634.8	1708.0	1759.9	1816.2	1871.2	1931.9	1980.8	2029.5	2057.7	2128.4
17.5°	1563.2	1620.1	1701.1	1761.7	1833.2	1920.0	1988.1	2043.3	2099.7	2145.3	2180.8
20°	1536.6	1598.6	1691.1	1763.7	1848.7	1941.9	2020.2	2076.4	2125.2	2163.3	2185.2
22.5°	1503.2	1581.0	1671.1	1756.1	1864.7	1956.9	2039.1	2083.4	2124.2	2142.8	2151.2
25°	1450.4	1544.2	1646.2	1749.9	1872.5	1970.1	2045.1	2072.0	2083.9	2065.8	2035.7
27.5°	1393.5	1498.0	1617.2	1738.1	1867.7	1961.5	2015.3	2011.1	1990.9	1932.3	1885.4
30°	1350.9	1466.0	1594.2	1726.2	1856.2	1947.6	1978.9	1947.6	1901.9	1836.3	1769.3
32.5°	1306.4	1425.5	1569.7	1709.1	1835.2	1915.5	1922.3	1868.5	1797.8	1723.2	1639.7
35°	1239.0	1367.8	1523.5	1671.1	1790.5	1841.3	1811.2	1716.2	1632.4	1530.4	1416.5
37.5°	1162.8	1305.0	1461.2	1615.4	1723.6	1736.9	1662.4	1562.3	1444.1	1324.3	1190.3
40°	1105.8	1256.5	1417.2	1572.9	1668.6	1654.8	1559.8	1449.7	1309.0	1162.6	1038.2
42.5°	1054.7	1205.4	1369.1	1521.9	1598.6	1560.8	1449.7	1314.7	1163.4	1025.6	911.6
45°	966.3	1121.3	1289.0	1436.6	1480.4	1412.2	1265.3	1115.1	966.3	851.2	761.1
47.5°	880.4	1033.8	1199.8	1329.6	1345.0	1253.3	1092.7	938.3	810.3	716.6	653.1
50°	817.5	971.3	1135.8	1251.5	1246.4	1135.8	970.6	823.7	716.7	641.0	598.5
52.5°	760.9	906.3	1064.2	1169.4	1142.9	1022.2	864.6	734.1	646.2	587.0	548.5
55°	673.0	807.4	957.5	1042.0	993.2	859.3	726.1	621.0	556.0	511.6	481.5
57.5°	585.6	711.7	840.2	892.2	838.3	714.7	603.7	527.4	478.5	445.6	426.1
60°	531.6	641.7	756.1	801.2	736.8	626.7	539.1	471.0	431.5	404.6	387.1
62.5°	477.6	576.2	684.1	708.6	649.7	556.7	479.1	422.4	390.0	366.1	349.6
65°	404.1	484.7	566.7	582.9	528.5	456.6	395.3	358.4	329.6	312.1	299.0
67.5°	331.3	396.2	454.2	467.3	419.6	369.8	325.5	293.3	273.8	259.3	248.2
70°	288.3	339.6	387.1	397.8	359.6	315.2	281.4	255.8	238.3	225.7	215.2
72.5°	242.8	285.6	325.1	332.2	301.0	267.2	239.4	219.2	203.8	195.8	185.6
75°	185.8	210.8	241.4	243.3	222.6	202.0	180.8	167.6	159.5	149.5	144.5
77.5°	131.1	150.7	168.2	171.6	159.4	145.3	133.5	123.1	116.2	111.6	107.0
80°	100.1	115.7	123.2	127.6	118.9	108.9	102.0	95.1	90.7	87.6	84.5
82.5°	71.5	81.2	88.2	91.5	86.8	80.8	73.9	70.0	66.6	64.0	63.0
85°	36.3	40.6	45.1	46.3	45.1	42.5	38.7	38.7	36.9	36.3	36.3
87.5°	12.9	15.4	15.6	17.3	16.6	17.2	17.9	18.1	17.6	17.1	16.5
90°	2.2	4.3	5.4	6.4	8.1	10.7	14.5	17.7	18.3	17.7	17.2
92.5°	9.4	13.3	15.7	19.3	24.4	36.6	53.6	68.9	69.8	59.0	46.8
95°	20.9	26.3	31.2	39.8	52.7	77.4	124.1	186.5	210.8	184.4	140.8
97.5°	33.6	39.2	46.6	56.5	71.1	102.2	167.3	270.9	359.7	377.3	328.7
100°	43.0	47.9	56.5	67.2	82.3	110.7	176.3	292.4	424.6	502.0	490.8
102.5°	52.5	57.3	65.9	77.1	92.1	118.5	176.7	284.3	426.8	548.5	597.0
105°	67.8	71.4	79.6	91.3	106.4	131.7	179.6	268.2	398.3	541.3	653.1
107.5°	82.8	86.4	93.9	105.6	120.7	145.2	186.9	260.2	367.8	494.1	612.7
110°	93.5	96.8	103.8	115.0	130.6	154.3	192.9	258.5	353.2	464.4	577.9



TEST NUMBER: P331386-830

CATALOG NUMBER: S122DIP-S865D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	103.0	106.6	113.2	124.0	140.1	162.9	199.4	259.0	343.7	443.7	546.0
115°	118.3	121.5	127.9	138.6	153.2	176.3	209.1	261.3	333.3	418.2	506.9
117.5°	133.0	136.2	141.9	152.2	167.3	188.7	219.4	265.1	328.2	402.1	477.4
120°	142.4	145.6	150.5	161.3	176.3	197.3	226.3	267.7	325.2	393.5	462.8
122.5°	151.1	154.3	159.6	170.3	185.8	205.5	232.3	270.7	323.5	386.2	451.2
125°	162.9	166.1	172.6	183.3	198.3	217.7	241.9	275.2	320.4	375.7	434.3
127.5°	172.9	177.4	184.5	194.8	210.3	229.1	250.8	279.8	318.6	366.1	417.6
130°	178.4	183.8	191.3	202.1	217.2	236.0	256.4	283.2	317.6	359.6	406.9
132.5°	184.1	189.8	197.8	209.0	224.0	242.0	262.0	286.7	317.3	354.4	396.6
135°	191.3	197.8	205.9	218.2	233.3	250.5	269.3	290.8	316.6	347.2	382.2
137.5°	199.1	205.6	214.1	226.4	240.3	257.4	274.8	294.5	316.5	342.1	370.7
140°	204.2	210.8	219.3	231.1	245.2	261.3	277.9	296.1	316.0	339.2	363.4
142.5°	209.4	215.5	224.0	235.4	248.5	264.3	280.5	297.5	316.0	336.2	357.3
145°	218.2	223.6	231.7	242.4	254.2	268.7	283.8	298.9	315.0	332.2	348.8
147.5°	226.7	231.9	239.3	248.3	258.7	272.4	285.7	299.3	313.0	328.1	342.3
150°	232.7	237.0	244.0	252.1	261.7	274.1	286.5	298.9	311.8	324.7	337.5
152.5°	237.9	242.2	248.4	256.0	264.8	275.9	286.9	298.0	309.6	321.7	332.8
155°	246.2	249.4	255.3	261.3	269.3	278.4	287.6	296.7	305.9	316.0	326.3
157.5°	253.3	255.9	261.0	265.8	272.5	280.2	287.6	294.3	302.0	310.8	318.7
160°	258.0	260.1	264.5	268.7	274.7	281.2	287.6	292.9	299.4	306.9	313.9
162.5°	261.8	264.0	267.5	271.4	276.0	281.5	287.1	291.6	297.3	303.5	309.2
165°	267.1	268.2	271.5	274.1	277.4	282.2	286.0	289.2	292.9	297.7	302.1
167.5°	271.5	272.5	274.6	276.5	278.5	282.1	285.2	286.7	289.2	292.2	295.3
170°	274.1	274.7	276.3	277.4	279.0	281.6	284.4	285.4	287.0	289.2	291.9
172.5°	276.3	276.0	277.6	278.2	279.4	281.3	283.0	283.7	284.5	286.2	288.0
175°	278.4	277.9	279.0	279.0	279.5	280.6	281.6	281.2	281.6	282.2	283.8
177.5°	279.1	278.6	279.5	279.5	279.5	279.9	280.8	279.9	279.5	279.9	280.8
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5



TEST NUMBER: P331386-830

CATALOG NUMBER: S122DIP-S865D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1687.9	1694.9	1694.9	1695.9	1703.9	1702.9	1702.4
5°	1796.2	1806.9	1808.1	1819.4	1826.8	1824.4	1817.5
7.5°	1898.4	1918.2	1933.2	1941.5	1951.4	1957.6	1954.8
10°	1979.4	2008.2	2025.7	2037.6	2052.0	2062.7	2058.9
12.5°	2053.0	2087.3	2111.3	2131.7	2133.5	2147.2	2138.0
15°	2167.8	2203.9	2207.7	2222.7	2234.7	2233.4	2234.0
17.5°	2205.6	2217.2	2219.6	2220.0	2220.2	2215.7	2206.2
20°	2192.1	2187.7	2177.1	2169.0	2154.6	2152.7	2140.2
22.5°	2128.1	2114.2	2087.5	2069.9	2047.5	2041.6	2038.2
25°	2002.0	1971.3	1928.8	1888.1	1876.9	1855.0	1861.2
27.5°	1829.0	1781.2	1735.1	1702.1	1672.3	1639.5	1648.9
30°	1707.4	1653.6	1588.6	1538.5	1506.7	1475.4	1469.7
32.5°	1562.3	1483.5	1411.0	1366.9	1318.1	1298.3	1276.6
35°	1312.1	1235.2	1163.3	1101.4	1065.7	1038.2	1013.1
37.5°	1087.1	998.5	940.5	890.3	864.6	848.9	852.8
40°	947.5	870.0	827.5	789.3	765.5	754.2	756.8
42.5°	834.4	776.4	741.4	715.2	698.4	692.2	690.7
45°	706.1	673.5	644.8	629.8	621.7	614.8	610.4
47.5°	618.5	592.0	575.8	566.8	559.8	552.7	552.6
50°	566.0	548.5	537.2	527.8	522.3	517.3	521.6
52.5°	525.9	510.0	498.7	490.3	488.2	483.7	483.6
55°	466.6	454.0	445.9	438.4	434.7	432.2	429.0
57.5°	412.6	400.7	393.1	388.4	381.3	378.7	377.8
60°	374.0	364.6	357.1	350.8	347.7	342.7	342.7
62.5°	338.5	329.1	322.1	317.4	312.2	310.2	310.8
65°	287.1	279.6	272.7	267.7	266.5	262.7	263.9
67.5°	239.8	234.8	227.5	224.8	222.4	220.4	218.9
70°	208.3	203.3	199.5	195.8	193.9	193.9	193.9
72.5°	181.7	175.8	173.5	168.7	169.8	167.9	165.9
75°	140.7	137.0	135.1	133.2	130.1	130.1	130.1
77.5°	103.6	102.5	100.2	98.2	97.5	96.8	97.1
80°	80.0	79.5	78.1	78.1	76.9	76.3	75.0
82.5°	61.5	59.9	59.2	58.6	58.4	58.2	58.1
85°	35.1	33.7	33.7	34.4	33.2	33.2	33.7
87.5°	16.8	17.0	16.6	16.6	17.1	16.6	16.6
90°	16.1	17.2	17.7	17.7	17.7	17.7	17.7
92.5°	40.2	35.7	32.3	32.0	30.3	30.6	29.8
95°	108.0	85.5	73.6	66.6	62.4	60.7	61.3
97.5°	268.9	210.8	171.9	146.2	133.0	125.2	120.6
100°	424.1	350.4	285.4	240.8	217.7	202.1	192.5
102.5°	581.9	528.1	459.1	410.7	371.2	351.8	338.7
105°	713.8	720.9	703.0	669.8	636.4	613.3	605.8
107.5°	704.2	760.1	786.1	790.2	788.4	783.8	773.8
110°	674.0	742.8	786.9	810.0	820.3	825.1	824.5



TEST NUMBER: P331386-830

CATALOG NUMBER: S122DIP-S865D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	638.4	711.9	762.4	794.6	811.6	820.8	823.7
115°	589.7	660.1	715.5	753.6	778.4	792.3	797.1
117.5°	550.1	614.0	665.9	704.8	730.9	745.6	749.7
120°	529.4	586.4	635.4	673.0	698.2	713.8	719.2
122.5°	512.3	566.2	610.4	644.1	669.0	682.9	687.4
125°	489.7	537.0	577.3	608.5	628.9	642.3	646.7
127.5°	467.8	512.4	549.6	576.7	595.9	607.5	611.0
130°	453.2	495.6	531.0	557.4	575.7	586.4	590.7
132.5°	439.4	478.4	511.7	537.6	555.9	565.8	569.7
135°	417.6	453.2	483.2	506.3	524.1	533.8	535.9
137.5°	400.4	428.5	454.8	475.8	491.1	499.5	502.8
140°	389.2	413.9	437.5	454.8	468.7	476.7	480.0
142.5°	379.3	400.6	420.4	436.7	449.4	456.6	457.2
145°	366.6	383.2	398.9	411.7	420.8	426.2	427.8
147.5°	356.3	369.3	380.7	391.3	398.6	402.3	403.2
150°	349.4	360.7	370.3	378.4	384.8	388.0	388.6
152.5°	343.8	353.4	361.7	368.1	373.7	376.1	376.2
155°	334.9	342.9	348.8	354.8	358.5	360.7	359.6
157.5°	325.8	332.6	337.2	341.4	344.6	345.5	345.5
160°	319.8	325.7	329.5	333.3	335.9	336.5	336.5
162.5°	314.2	319.3	322.2	325.9	327.8	328.3	327.9
165°	305.9	309.6	311.8	313.9	316.0	316.0	315.6
167.5°	298.2	300.8	302.7	303.7	304.9	304.8	304.2
170°	293.5	295.7	296.7	297.3	298.9	298.3	297.3
172.5°	289.2	290.9	291.5	292.1	292.8	292.3	291.6
175°	284.4	284.9	285.4	285.4	286.0	285.4	284.4
177.5°	280.8	281.3	281.3	281.3	281.3	280.8	279.9
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5

(END OF REPORT)