

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331758-830

Luminaire Tested: **S122RDIP-S1005D925U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331758-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S1005D925U830-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6691.1 lumens  
Efficiency: N/A  
Efficacy: 100.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331758-830

CATALOG NUMBER: S122RDIP-S1005D925U830-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331758-830

CATALOG NUMBER: S122RDIP-S1005D925U830-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35	31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31	27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24
6	64	52	44	39	59	49	42	37	42	36	32	36	31	28	30	27	24	21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	25770	25770	25770
5°	25869	25449	25590
10°	25671	25032	24819
15°	25377	24289	23590
20°	24967	23230	22063
25°	24549	22026	20587
30°	23968	20789	18690
35°	23402	19446	17026
40°	22835	18054	15099
45°	22165	16493	13358
50°	21481	14913	11645
55°	20777	13216	10001
60°	19963	11428	8302
65°	19037	9605	7561
70°	17934	7912	6954
75°	16581	7211	6488
80°	14635	6453	5904
85°	11504	5076	5076



TEST NUMBER: P331758-830

CATALOG NUMBER: S122RDIP-S1005D925U830-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	149.4	2.2
10°-20°	410.2	6.1
20°-30°	576.1	8.6
30°-40°	628.2	9.4
40°-50°	577.6	8.6
50°-60°	453.6	6.8
60°-70°	295.8	4.4
70°-80°	152.5	2.3
80°-90°	43.9	0.7
90°-100°	195.6	2.9
100°-110°	663.7	9.9
110°-120°	705.1	10.5
120°-130°	580.4	8.7
130°-140°	466.1	7.0
140°-150°	352.2	5.3
150°-160°	247.5	3.7
160°-170°	145.7	2.2
170°-180°	47.4	0.7
0°-30°	1135.7	17.0
0°-40°	1763.9	26.4
0°-60°	2795.1	41.8
0°-90°	3287.3	49.1
90°-120°	1564.4	23.4
90°-150°	2963.2	44.3
90°-180°	3404.0	50.9
0°-180°	6691.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1596	1596	1596	1596	1596	
5°	1596	1588	1570	1582	1579	151
15°	1518	1500	1453	1426	1411	427
25°	1378	1329	1236	1179	1156	633
35°	1187	1111	987	899	864	743
45°	971	871	722	623	585	749
55°	738	623	470	386	355	659
65°	498	381	251	205	198	494
75°	266	168	116	106	104	281
85°	62	33	27	27	27	73
90°	1	13	32	31	31	4
95°	33	81	369	139	107	35
105°	115	173	697	1246	1060	122
115°	202	255	583	1204	1395	200
125°	282	334	561	975	1132	251
135°	331	395	554	819	938	256
145°	378	435	551	684	749	237
155°	430	464	535	605	629	198
165°	468	483	513	544	552	132
175°	488	489	493	499	498	46
180°	489	489	489	489	489	



TEST NUMBER: P331758-830

CATALOG NUMBER: S122RDIP-S1005D925U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1
2.5°	1601.9	1600.6	1599.3	1598.1	1596.8	1594.7	1591.9	1589.1	1586.3	1583.5	1586.0
5°	1596.1	1594.5	1592.9	1591.3	1589.7	1586.9	1582.6	1578.5	1574.3	1570.2	1573.0
7.5°	1579.7	1577.7	1575.7	1573.7	1571.7	1568.3	1563.4	1558.5	1553.7	1548.8	1549.6
10°	1565.8	1563.6	1561.3	1559.1	1556.8	1552.5	1546.1	1539.6	1533.2	1526.8	1525.9
12.5°	1548.5	1545.7	1542.9	1540.2	1537.5	1531.9	1523.7	1515.5	1507.3	1499.1	1497.3
15°	1518.2	1514.6	1511.1	1507.5	1504.0	1496.8	1485.9	1475.0	1464.1	1453.1	1447.1
17.5°	1480.8	1475.5	1470.1	1464.7	1459.3	1449.6	1435.6	1421.6	1407.6	1393.6	1386.4
20°	1453.1	1446.7	1440.3	1433.9	1427.5	1416.3	1400.1	1384.1	1368.1	1352.0	1344.0
22.5°	1423.1	1415.9	1408.7	1401.6	1394.3	1381.7	1363.6	1345.5	1327.4	1309.3	1298.9
25°	1378.0	1367.7	1357.4	1347.2	1336.9	1321.3	1300.0	1278.8	1257.6	1236.4	1223.3
27.5°	1323.7	1312.6	1301.4	1290.2	1279.0	1261.5	1237.7	1213.7	1189.9	1166.0	1150.7
30°	1285.6	1273.4	1261.2	1249.0	1236.8	1217.9	1192.1	1166.5	1140.9	1115.1	1098.7
32.5°	1248.6	1234.4	1220.1	1205.9	1191.6	1171.4	1145.2	1119.0	1092.8	1066.6	1047.9
35°	1187.3	1171.0	1154.6	1138.2	1121.9	1099.6	1071.3	1043.1	1014.8	986.6	966.4
37.5°	1126.1	1108.1	1090.1	1072.1	1054.2	1030.2	1000.0	970.0	939.8	909.7	887.5
40°	1083.4	1064.1	1044.8	1025.6	1006.4	981.1	950.0	918.9	887.7	856.6	833.8
42.5°	1039.4	1019.2	998.9	978.5	958.3	932.1	899.9	867.7	835.6	803.4	779.9
45°	970.7	949.1	927.7	906.2	884.7	857.1	823.3	789.7	755.9	722.3	699.5
47.5°	903.6	880.9	858.1	835.3	812.5	783.7	748.9	714.1	679.3	644.5	621.9
50°	855.2	832.4	809.5	786.7	763.9	734.9	699.6	664.3	629.0	593.7	571.6
52.5°	807.8	783.9	760.2	736.3	712.5	683.3	648.8	614.3	579.7	545.2	523.8
55°	738.1	713.1	688.1	663.0	638.0	608.1	573.4	538.8	504.2	469.5	450.2
57.5°	666.8	641.1	615.4	589.7	564.0	534.5	501.2	467.9	434.6	401.2	383.6
60°	618.2	592.6	566.8	541.2	515.5	486.2	453.1	420.0	386.9	353.9	337.5
62.5°	570.9	545.2	519.5	493.8	468.2	439.5	408.0	376.5	345.0	313.5	297.8
65°	498.3	472.3	446.4	420.4	394.4	366.9	338.0	309.2	280.2	251.4	240.4
67.5°	428.4	402.7	376.8	351.0	325.2	299.3	273.3	247.3	221.3	195.3	190.3
70°	379.9	354.9	329.8	304.8	279.7	256.2	234.0	211.9	189.7	167.6	164.4
72.5°	333.7	309.6	285.7	261.6	237.6	216.7	199.0	181.2	163.3	145.6	142.9
75°	265.8	243.3	220.8	198.4	175.9	159.2	148.3	137.4	126.5	115.6	113.3
77.5°	199.1	179.4	159.7	140.0	120.2	107.7	102.5	97.2	91.9	86.7	85.4
80°	157.4	141.1	124.7	108.3	92.0	82.2	79.0	75.8	72.6	69.4	68.1
82.5°	119.3	106.5	93.8	81.0	68.2	60.7	58.5	56.4	54.2	52.0	51.3
85°	62.1	55.3	48.6	41.8	35.2	31.3	30.3	29.4	28.4	27.4	27.4
87.5°	18.7	17.2	15.9	14.2	12.5	12.1	13.0	14.3	15.5	15.6	15.2
90°	0.9	3.8	7.5	9.4	11.3	14.1	18.9	25.4	31.0	32.0	31.0
92.5°	11.5	16.6	23.4	27.4	33.8	42.7	64.0	93.9	120.6	122.2	103.3
95°	32.9	36.7	46.1	54.6	69.7	92.2	135.4	217.3	326.4	368.7	322.6
97.5°	53.6	58.7	68.7	81.4	98.8	124.3	178.7	292.8	474.1	629.5	660.3
100°	72.4	75.2	83.7	98.8	117.6	143.9	193.8	308.6	511.7	743.1	878.6
102.5°	89.7	91.8	100.3	115.4	134.9	161.3	207.4	309.3	497.5	746.9	959.9
105°	114.8	118.6	125.1	139.2	159.9	186.2	230.5	314.1	469.4	697.0	947.3
107.5°	141.9	144.9	151.3	164.3	184.7	211.3	254.2	327.2	455.4	643.7	864.7
110°	159.9	163.7	169.3	181.5	201.3	228.6	269.9	337.7	452.5	618.0	812.8



TEST NUMBER: P331758-830

CATALOG NUMBER: S122RDIP-S1005D925U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	176.4	180.2	186.6	198.1	217.1	245.2	285.0	349.0	453.2	601.4	776.7
115°	202.3	207.0	212.6	223.9	242.7	268.1	308.6	365.9	457.1	583.2	731.9
117.5°	228.9	232.7	238.4	248.4	266.4	292.8	330.2	384.0	463.9	574.4	703.6
120°	245.5	249.3	255.0	263.3	282.2	308.6	345.3	396.1	468.4	569.1	688.6
122.5°	261.4	264.3	269.9	279.2	298.0	325.1	359.5	406.5	473.7	566.1	675.8
125°	282.2	285.0	290.7	302.0	320.7	347.1	381.0	423.3	481.6	560.6	657.5
127.5°	298.8	302.6	310.4	322.8	340.9	368.0	401.0	438.9	489.7	557.4	640.6
130°	308.6	312.3	321.7	334.9	353.7	380.0	412.9	448.7	495.8	555.9	629.3
132.5°	317.5	322.1	332.2	346.2	365.7	392.1	423.5	458.5	501.7	555.2	620.3
135°	331.1	334.9	346.2	360.2	381.9	408.2	438.4	471.3	508.9	554.0	607.7
137.5°	343.9	348.5	359.7	374.8	396.2	420.7	450.4	481.1	515.3	553.8	598.8
140°	353.7	357.5	368.7	383.8	404.5	429.0	457.1	486.4	518.3	553.1	593.6
142.5°	363.4	366.5	377.0	392.1	412.0	435.0	462.4	490.9	520.6	553.1	588.3
145°	378.1	381.9	391.3	405.5	424.2	445.0	470.3	496.7	523.0	551.2	581.4
147.5°	394.0	396.8	405.8	418.8	434.4	452.9	476.7	499.9	523.8	547.9	574.2
150°	404.5	407.3	414.8	427.1	441.2	458.1	479.8	501.3	523.0	545.6	568.2
152.5°	415.0	416.3	423.9	434.6	448.0	463.4	482.8	502.1	521.5	541.9	562.9
155°	429.9	430.8	436.5	446.9	457.1	471.3	487.3	503.2	519.2	535.3	553.1
157.5°	442.3	443.3	447.8	456.8	465.1	476.9	490.5	503.2	514.9	528.5	543.9
160°	450.6	451.6	455.2	462.8	470.3	480.7	492.0	503.2	512.6	524.0	537.2
162.5°	458.8	458.3	462.0	468.1	474.9	483.0	492.8	502.5	510.4	520.2	531.1
165°	468.4	467.5	469.4	475.0	479.8	485.4	493.9	500.5	506.1	512.6	521.1
167.5°	476.4	475.2	476.9	480.5	483.9	487.5	493.7	499.2	501.7	506.1	511.3
170°	481.6	479.8	480.7	483.5	485.4	488.2	492.9	497.7	499.5	502.3	506.1
172.5°	484.7	483.5	483.0	485.8	486.9	489.0	492.2	495.4	496.5	497.9	500.9
175°	488.2	487.3	486.4	488.2	488.2	489.2	491.1	492.9	492.0	492.9	493.9
177.5°	489.9	488.4	487.7	489.2	489.2	489.2	489.9	491.4	489.9	489.2	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331758-830

CATALOG NUMBER: S122RDIP-S1005D925U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1
2.5°	1588.6	1591.1	1593.7	1594.7	1594.2	1593.7	1593.2	1592.7
5°	1575.9	1578.9	1581.7	1582.6	1581.7	1580.7	1579.8	1578.9
7.5°	1550.4	1551.2	1552.1	1551.7	1550.0	1548.3	1546.7	1545.0
10°	1524.8	1523.9	1523.0	1521.5	1519.6	1517.7	1515.7	1513.8
12.5°	1495.6	1493.8	1492.1	1489.7	1486.5	1483.3	1480.1	1476.9
15°	1441.0	1434.8	1428.7	1424.1	1420.9	1417.7	1414.5	1411.3
17.5°	1379.1	1371.9	1364.6	1358.2	1352.7	1347.2	1341.6	1336.1
20°	1336.0	1327.9	1319.9	1312.4	1305.3	1298.3	1291.2	1284.1
22.5°	1288.6	1278.3	1267.9	1260.1	1254.9	1249.6	1244.3	1239.1
25°	1210.1	1197.0	1183.8	1174.9	1170.0	1165.2	1160.4	1155.6
27.5°	1135.3	1119.9	1104.6	1093.1	1085.4	1077.8	1070.2	1062.5
30°	1082.4	1066.0	1049.6	1037.2	1028.5	1019.8	1011.2	1002.5
32.5°	1029.3	1010.6	991.8	978.5	970.3	962.1	953.9	945.8
35°	946.1	926.0	905.7	892.0	885.0	877.9	870.8	863.8
37.5°	865.2	842.9	820.6	805.4	797.4	789.3	781.2	773.1
40°	811.0	788.2	765.4	749.9	741.5	733.1	724.8	716.4
42.5°	756.3	732.7	709.2	693.3	685.2	677.1	669.1	661.0
45°	676.7	653.8	631.0	615.9	608.1	600.4	592.7	585.0
47.5°	599.2	576.6	553.8	539.0	532.1	525.1	518.0	511.0
50°	549.4	527.3	505.1	490.6	483.9	477.1	470.4	463.6
52.5°	502.4	481.0	459.7	445.8	439.6	433.4	427.2	420.9
55°	430.9	411.7	392.4	379.8	373.6	367.5	361.5	355.3
57.5°	366.0	348.3	330.6	319.2	314.1	309.0	303.9	298.7
60°	321.1	304.8	288.4	277.7	272.5	267.4	262.2	257.1
62.5°	282.3	266.6	251.1	241.7	238.7	235.5	232.4	229.4
65°	229.5	218.6	207.6	201.7	200.8	199.8	198.9	197.9
67.5°	185.3	180.3	175.2	172.2	171.3	170.2	169.2	168.1
70°	161.2	158.0	154.8	152.5	151.2	149.9	148.6	147.3
72.5°	140.3	137.5	134.8	133.1	132.3	131.6	130.7	130.0
75°	111.0	108.9	106.6	105.3	105.0	104.6	104.3	104.0
77.5°	84.1	82.8	81.5	80.6	80.1	79.6	79.1	78.6
80°	66.7	65.5	64.2	63.5	63.5	63.5	63.5	63.5
82.5°	50.4	49.7	48.9	48.5	48.5	48.5	48.5	48.5
85°	27.4	27.4	27.4	27.4	27.4	27.4	27.4	27.4
87.5°	14.8	14.1	14.2	14.3	14.3	14.3	14.3	14.3
90°	30.1	28.2	30.1	31.0	31.0	31.0	31.0	31.0
92.5°	82.0	70.4	62.5	56.6	55.9	52.9	53.6	52.1
95°	246.5	189.1	149.6	128.8	116.7	109.1	106.3	107.3
97.5°	575.1	470.5	368.7	300.9	255.9	232.7	219.0	211.1
100°	858.8	742.2	613.3	499.5	421.4	381.0	353.7	336.8
102.5°	1044.7	1018.4	924.2	803.5	718.7	649.6	615.6	592.7
105°	1142.9	1249.2	1261.5	1230.4	1172.1	1113.8	1073.3	1060.2
107.5°	1072.2	1232.3	1330.1	1375.6	1383.0	1379.8	1371.7	1354.2
110°	1011.3	1179.6	1300.0	1377.1	1417.6	1435.5	1444.0	1443.0





TEST NUMBER: P331758-830

CATALOG NUMBER: S122RDIP-S1005D925U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	955.5	1117.2	1245.9	1334.3	1390.5	1420.4	1436.4	1441.5
115°	887.0	1031.9	1155.2	1252.1	1318.8	1362.1	1386.6	1395.1
117.5°	835.5	962.7	1074.4	1165.4	1233.4	1279.1	1305.0	1312.0
120°	809.9	926.6	1026.2	1111.9	1177.7	1221.9	1249.2	1258.7
122.5°	789.6	896.5	990.9	1068.3	1127.3	1170.7	1195.0	1203.0
125°	760.1	857.0	939.7	1010.3	1064.9	1100.6	1124.1	1131.6
127.5°	730.9	818.6	896.6	961.8	1009.4	1042.8	1063.2	1069.2
130°	712.1	793.0	867.3	929.4	975.5	1007.5	1026.2	1033.8
132.5°	694.0	768.9	837.2	895.5	940.8	972.9	990.1	996.9
135°	668.8	730.9	793.0	845.6	886.1	917.2	934.1	937.8
137.5°	648.7	700.6	749.9	795.8	832.7	859.4	874.3	880.0
140°	635.9	681.1	724.3	765.7	795.8	820.3	834.4	840.0
142.5°	625.4	663.7	701.0	735.7	764.2	786.5	799.0	800.1
145°	610.5	641.6	670.7	698.0	720.6	736.6	745.9	748.8
147.5°	599.0	623.5	646.2	666.2	684.9	697.6	704.0	705.7
150°	590.8	611.4	631.2	648.1	662.2	673.5	679.2	680.1
152.5°	582.5	601.6	618.4	633.1	644.1	653.9	658.1	658.3
155°	571.0	586.1	600.1	610.5	620.9	627.5	631.2	629.3
157.5°	557.6	570.2	582.1	590.2	597.5	602.9	604.6	604.6
160°	549.3	559.7	570.0	576.6	583.2	588.0	588.9	588.9
162.5°	541.1	549.9	558.7	563.8	570.4	573.6	574.6	573.8
165°	528.7	535.3	541.9	545.6	549.3	553.1	553.1	552.1
167.5°	516.8	521.9	526.4	529.8	531.5	533.6	533.4	532.3
170°	510.8	513.6	517.4	519.2	520.2	523.0	522.1	520.2
172.5°	504.0	506.1	509.1	510.2	511.1	512.5	511.5	510.4
175°	496.7	497.7	498.6	499.5	499.5	500.5	499.5	497.7
177.5°	491.4	491.4	492.2	492.2	492.2	492.2	491.4	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2

(END OF REPORT)