

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331654-830

Luminaire Tested: **S122RDIP-S485D530U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331654-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S485D530U830-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 530 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3593.6 lumens  
Efficiency: N/A  
Efficacy: 109.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331654-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331654-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	34	33	28
4	74	64	56	51	68	59	52	47	50	45	41	41	37	35	33	30	28	25
5	68	57	49	44	63	53	46	41	45	39	35	37	33	30	30	27	25	22
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	24	22	19
7	58	47	39	33	54	43	36	31	37	31	28	31	27	24	25	22	20	17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16
9	51	39	31	27	46	36	29	25	31	26	22	26	22	19	21	18	16	14
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12558	12558	12558
5°	12606	12402	12470
10°	12511	12198	12095
15°	12366	11836	11497
20°	12167	11320	10753
25°	11965	10735	10033
30°	11680	10133	9107
35°	11404	9477	8296
40°	11126	8800	7358
45°	10803	8035	6510
50°	10467	7267	5674
55°	10125	6441	4873
60°	9726	5570	4046
65°	9280	4676	3683
70°	8738	3852	3389
75°	8079	3512	3163
80°	7132	3133	2882
85°	5613	2482	2482



TEST NUMBER: P331654-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.8	2.0
10°-20°	199.9	5.6
20°-30°	280.7	7.8
30°-40°	306.1	8.5
40°-50°	281.5	7.8
50°-60°	221.1	6.2
60°-70°	144.1	4.0
70°-80°	74.3	2.1
80°-90°	21.0	0.6
90°-100°	22.7	0.6
100°-110°	83.2	2.3
110°-120°	222.3	6.2
120°-130°	366.9	10.2
130°-140°	390.2	10.9
140°-150°	362.7	10.1
150°-160°	291.6	8.1
160°-170°	187.9	5.2
170°-180°	64.7	1.8
0°-30°	553.4	15.4
0°-40°	859.6	23.9
0°-60°	1362.1	37.9
0°-90°	1601.5	44.6
90°-120°	328.1	9.1
90°-150°	1447.9	40.3
90°-180°	1992.0	55.4
0°-180°	3593.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	778	778	778	778	778	
5°	778	774	765	771	769	74
15°	740	731	708	695	688	208
25°	672	648	603	575	563	309
35°	579	541	481	438	421	362
45°	473	424	352	304	285	365
55°	360	304	229	188	173	321
65°	243	186	122	100	96	241
75°	130	82	56	52	51	137
85°	30	16	13	13	13	36
90°	0	6	10	12	13	3
95°	32	17	19	22	21	39
105°	150	156	30	35	37	160
115°	283	291	304	86	40	278
125°	400	406	416	419	421	356
135°	495	502	507	512	511	382
145°	574	574	582	585	583	359
155°	632	628	634	636	632	291
165°	666	663	664	668	664	188
175°	681	678	679	682	677	65
180°	680	680	680	680	680	



TEST NUMBER: P331654-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	780.6	780.0	779.4	778.7	778.2	777.1	775.8	774.4	773.0	771.7	772.9
5°	777.8	777.0	776.3	775.5	774.7	773.3	771.3	769.2	767.2	765.2	766.6
7.5°	769.8	768.8	767.9	766.9	765.9	764.2	761.9	759.5	757.1	754.8	755.2
10°	763.1	762.0	760.8	759.8	758.7	756.6	753.5	750.3	747.2	744.0	743.6
12.5°	754.6	753.3	751.9	750.5	749.2	746.6	742.5	738.6	734.5	730.6	729.7
15°	739.8	738.1	736.4	734.6	732.9	729.4	724.1	718.8	713.5	708.1	705.2
17.5°	721.7	719.1	716.4	713.8	711.1	706.4	699.6	692.8	686.0	679.1	675.6
20°	708.1	705.0	701.9	698.8	695.6	690.1	682.3	674.5	666.7	658.8	655.0
22.5°	693.5	690.0	686.5	683.0	679.5	673.4	664.5	655.6	646.9	638.0	633.0
25°	671.6	666.6	661.6	656.5	651.5	643.9	633.5	623.2	612.8	602.6	596.2
27.5°	645.1	639.6	634.1	628.8	623.3	614.7	603.1	591.4	579.9	568.2	560.7
30°	626.5	620.6	614.6	608.7	602.8	593.5	581.0	568.4	555.9	543.5	535.5
32.5°	608.5	601.5	594.6	587.7	580.7	570.8	558.1	545.3	532.5	519.8	510.7
35°	578.6	570.6	562.7	554.7	546.7	535.8	522.1	508.3	494.6	480.8	470.9
37.5°	548.7	540.0	531.2	522.5	513.8	502.0	487.4	472.7	458.0	443.4	432.4
40°	527.9	518.6	509.2	499.8	490.4	478.2	463.0	447.8	432.6	417.5	406.3
42.5°	506.5	496.6	486.7	476.9	467.0	454.2	438.6	422.8	407.2	391.5	380.0
45°	473.1	462.6	452.0	441.6	431.1	417.6	401.2	384.8	368.3	351.9	340.8
47.5°	440.4	429.2	418.2	407.1	396.0	381.9	365.0	348.0	331.0	314.1	303.0
50°	416.7	405.6	394.5	383.4	372.3	358.2	340.9	323.8	306.5	289.3	278.5
52.5°	393.6	382.0	370.4	358.8	347.2	333.0	316.1	299.4	282.5	265.7	255.2
55°	359.7	347.5	335.3	323.1	310.9	296.3	279.5	262.6	245.6	228.8	219.4
57.5°	324.9	312.5	299.9	287.4	274.8	260.5	244.3	228.0	211.8	195.6	186.9
60°	301.2	288.8	276.3	263.7	251.2	237.0	220.8	204.7	188.6	172.5	164.5
62.5°	278.1	265.7	253.2	240.6	228.1	214.2	198.9	183.5	168.1	152.8	145.2
65°	242.9	230.2	217.5	204.8	192.2	178.8	164.8	150.6	136.6	122.4	117.2
67.5°	208.8	196.2	183.6	171.1	158.4	145.8	133.2	120.6	107.8	95.2	92.7
70°	185.1	173.0	160.7	148.5	136.3	124.8	114.0	103.2	92.5	81.6	80.1
72.5°	162.6	150.9	139.2	127.5	115.8	105.7	97.0	88.3	79.6	71.0	69.7
75°	129.5	118.6	107.6	96.7	85.7	77.6	72.3	66.9	61.6	56.3	55.2
77.5°	97.0	87.4	77.8	68.1	58.6	52.5	50.0	47.4	44.8	42.2	41.6
80°	76.7	68.7	60.8	52.8	44.8	40.1	38.5	36.9	35.3	33.7	33.2
82.5°	58.2	51.9	45.7	39.5	33.3	29.6	28.6	27.4	26.4	25.4	25.0
85°	30.3	27.0	23.7	20.5	17.2	15.3	14.8	14.3	13.9	13.4	13.4
87.5°	9.1	8.4	7.5	6.8	6.0	5.7	5.9	6.1	6.3	6.5	6.5
90°	0.5	1.7	2.9	4.1	5.3	6.3	7.3	8.1	9.0	9.8	10.4
92.5°	9.9	9.8	9.7	9.6	9.5	9.7	10.1	10.6	10.9	11.4	11.7
95°	32.0	28.4	24.8	21.1	17.5	16.1	16.9	17.6	18.4	19.2	19.7
97.5°	63.4	53.3	43.2	33.0	22.8	18.6	20.4	22.1	23.9	25.6	26.1
100°	87.1	72.1	57.1	42.1	27.1	20.6	22.4	24.3	26.2	28.0	28.9
102.5°	113.0	109.9	106.7	103.5	100.4	91.0	75.5	59.9	44.4	28.8	30.0
105°	149.5	152.8	156.1	159.4	162.7	149.4	119.5	89.7	59.9	30.0	31.2
107.5°	191.1	193.8	196.4	199.1	201.7	185.1	149.4	113.6	77.8	42.0	40.8
110°	217.9	220.2	222.5	224.8	227.1	212.4	180.9	149.3	117.6	86.1	75.1



TEST NUMBER: P331654-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	243.1	245.2	247.1	249.2	251.2	248.4	240.5	232.7	224.9	217.2	177.2
115°	282.9	284.6	286.5	288.4	290.3	292.6	295.3	298.0	300.8	303.5	252.9
117.5°	318.4	320.5	322.5	324.6	326.7	328.7	330.5	332.4	334.3	336.1	324.0
120°	344.3	345.9	347.6	349.2	350.9	352.7	354.7	356.7	358.5	360.5	361.8
122.5°	366.4	368.1	369.9	371.6	373.2	375.2	377.3	379.5	381.6	383.8	384.6
125°	399.9	401.3	402.7	404.2	405.6	407.4	409.4	411.5	413.6	415.7	416.4
127.5°	430.3	431.9	433.5	435.0	436.6	438.2	439.7	441.3	442.8	444.4	445.4
130°	449.6	451.3	453.1	454.9	456.6	458.1	459.3	460.4	461.7	462.9	464.1
132.5°	469.3	470.7	472.2	473.7	475.2	476.5	477.8	479.0	480.1	481.4	482.4
135°	494.8	496.6	498.3	500.1	501.8	503.2	504.2	505.2	506.1	507.1	508.2
137.5°	520.8	521.9	523.1	524.3	525.6	526.8	527.9	529.0	530.1	531.2	532.3
140°	537.6	538.5	539.4	540.3	541.1	542.2	543.4	544.6	545.7	547.0	548.0
142.5°	551.8	552.6	553.4	554.1	555.0	556.0	557.4	558.7	560.2	561.6	562.4
145°	574.0	573.9	573.8	573.7	573.6	574.5	576.4	578.2	580.0	581.9	582.7
147.5°	593.4	593.0	592.6	592.2	591.7	592.5	594.3	596.2	597.9	599.8	600.4
150°	606.0	605.2	604.5	603.7	602.9	603.4	605.2	606.9	608.7	610.4	611.1
152.5°	616.6	615.8	614.9	614.1	613.2	613.6	615.3	617.0	618.6	620.3	620.9
155°	632.1	631.1	630.1	629.1	628.1	628.3	629.6	630.9	632.3	633.6	634.2
157.5°	644.1	643.4	642.5	641.7	640.8	640.9	641.8	642.7	643.7	644.6	645.3
160°	651.3	650.6	650.0	649.3	648.7	648.7	649.3	650.0	650.6	651.3	652.0
162.5°	657.5	656.9	656.2	655.5	655.0	654.9	655.4	656.0	656.6	657.1	657.9
165°	666.0	665.3	664.7	664.0	663.4	663.3	663.5	663.8	664.2	664.5	665.3
167.5°	672.3	671.7	671.0	670.3	669.7	669.5	669.8	670.1	670.4	670.7	671.5
170°	675.8	675.2	674.6	673.9	673.3	673.0	673.3	673.4	673.6	673.9	674.7
172.5°	678.3	677.6	676.9	676.3	675.6	675.3	675.6	675.8	676.0	676.3	677.0
175°	681.3	680.5	679.8	679.0	678.2	678.0	678.2	678.3	678.5	678.8	679.6
177.5°	681.7	681.2	680.5	680.0	679.3	679.0	679.1	679.2	679.3	679.4	680.0
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331654-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	774.1	775.4	776.7	777.1	776.9	776.7	776.4	776.2
5°	768.0	769.4	770.8	771.3	770.8	770.3	769.9	769.4
7.5°	755.5	755.9	756.4	756.2	755.4	754.5	753.8	752.9
10°	743.1	742.6	742.2	741.5	740.6	739.6	738.7	737.7
12.5°	728.9	728.0	727.2	725.9	724.3	722.8	721.2	719.7
15°	702.2	699.3	696.3	694.0	692.4	690.9	689.3	687.8
17.5°	672.0	668.5	665.0	661.9	659.2	656.5	653.8	651.1
20°	651.0	647.1	643.2	639.5	636.1	632.6	629.2	625.8
22.5°	627.9	622.9	617.9	614.1	611.5	609.0	606.4	603.8
25°	589.7	583.3	576.9	572.5	570.1	567.8	565.5	563.2
27.5°	553.3	545.7	538.3	532.7	529.0	525.3	521.5	517.8
30°	527.4	519.5	511.5	505.4	501.1	497.0	492.8	488.5
32.5°	501.5	492.5	483.3	476.8	472.9	468.9	464.9	460.9
35°	461.1	451.2	441.4	434.7	431.3	427.8	424.4	420.9
37.5°	421.6	410.8	399.9	392.5	388.6	384.7	380.7	376.7
40°	395.2	384.1	373.0	365.4	361.4	357.3	353.2	349.1
42.5°	368.5	357.0	345.6	337.9	333.9	330.0	326.0	322.1
45°	329.7	318.7	307.6	300.1	296.3	292.6	288.8	285.1
47.5°	292.0	281.0	269.9	262.7	259.3	255.9	252.4	249.0
50°	267.7	256.9	246.1	239.1	235.8	232.5	229.2	225.9
52.5°	244.8	234.4	223.9	217.3	214.2	211.2	208.1	205.1
55°	210.0	200.6	191.2	185.0	182.1	179.1	176.2	173.1
57.5°	178.3	169.8	161.2	155.6	153.1	150.6	148.1	145.5
60°	156.5	148.5	140.5	135.3	132.8	130.3	127.8	125.3
62.5°	137.5	130.0	122.3	117.8	116.3	114.8	113.3	111.8
65°	111.9	106.5	101.2	98.3	97.8	97.4	96.9	96.4
67.5°	90.3	87.8	85.4	84.0	83.4	82.9	82.5	81.9
70°	78.5	77.0	75.4	74.3	73.7	73.0	72.4	71.8
72.5°	68.3	67.0	65.7	64.8	64.5	64.1	63.7	63.3
75°	54.1	53.1	51.9	51.3	51.2	51.0	50.8	50.7
77.5°	41.0	40.3	39.8	39.3	39.0	38.8	38.5	38.3
80°	32.5	32.0	31.3	31.0	31.0	31.0	31.0	31.0
82.5°	24.6	24.2	23.8	23.7	23.7	23.7	23.7	23.7
85°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4
87.5°	6.4	6.4	6.4	6.4	6.5	6.5	6.6	6.6
90°	10.9	11.5	12.1	12.4	12.6	12.8	13.1	13.3
92.5°	12.0	12.3	12.5	12.7	12.9	13.0	13.2	13.3
95°	20.3	20.8	21.4	21.6	21.5	21.4	21.3	21.1
97.5°	26.6	27.0	27.4	27.7	27.8	28.0	28.1	28.3
100°	29.8	30.6	31.6	32.0	32.3	32.5	32.7	33.0
102.5°	31.1	32.2	33.4	34.1	34.4	34.7	35.0	35.3
105°	32.4	33.6	34.8	35.6	36.1	36.5	36.9	37.4
107.5°	39.6	38.4	37.1	36.8	37.1	37.6	38.0	38.5
110°	64.2	53.3	42.3	37.1	37.5	38.0	38.5	38.8





TEST NUMBER: P331654-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	137.3	97.5	57.6	37.9	38.2	38.5	38.9	39.2
115°	202.3	151.7	101.0	71.8	63.9	56.1	48.2	40.3
117.5°	311.7	299.4	287.2	268.2	242.2	216.4	190.6	164.7
120°	363.2	364.5	365.8	359.1	344.3	329.6	314.8	300.0
122.5°	385.3	386.2	386.9	385.9	383.0	380.1	377.3	374.4
125°	417.2	417.9	418.7	419.2	419.6	419.9	420.3	420.6
127.5°	446.6	447.7	448.8	449.4	449.5	449.6	449.6	449.7
130°	465.2	466.5	467.7	468.3	468.1	468.0	467.9	467.8
132.5°	483.4	484.5	485.5	485.9	485.8	485.7	485.6	485.5
135°	509.3	510.4	511.5	512.0	511.7	511.5	511.3	511.0
137.5°	533.4	534.4	535.6	535.8	535.5	535.1	534.8	534.4
140°	548.9	549.9	550.9	551.1	550.5	550.1	549.5	548.9
142.5°	563.4	564.2	565.1	565.3	564.8	564.2	563.6	563.1
145°	583.4	584.2	584.9	585.0	584.6	584.0	583.4	582.9
147.5°	601.0	601.5	602.1	602.1	601.7	601.2	600.8	600.3
150°	611.7	612.4	613.0	613.1	612.6	612.0	611.4	611.0
152.5°	621.6	622.3	622.9	622.8	622.2	621.4	620.7	620.0
155°	634.9	635.6	636.2	636.0	635.2	634.3	633.5	632.5
157.5°	646.0	646.8	647.5	647.5	646.6	645.7	644.9	644.0
160°	652.5	653.2	653.8	653.8	653.1	652.3	651.5	650.7
162.5°	658.6	659.4	660.2	660.1	659.1	658.2	657.2	656.3
165°	666.1	666.8	667.6	667.6	666.8	666.1	665.3	664.5
167.5°	672.2	673.1	673.8	673.7	672.7	671.8	670.7	669.8
170°	675.4	676.2	676.9	676.8	675.8	674.9	673.9	672.9
172.5°	677.8	678.5	679.3	679.2	678.3	677.2	676.3	675.2
175°	680.3	681.1	681.8	681.7	680.6	679.5	678.4	677.3
177.5°	680.6	681.3	681.8	681.7	681.0	680.1	679.4	678.6
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8

(END OF REPORT)