

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331699-830

Luminaire Tested: **S122RDIP-S675D1080U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331699-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S675D1080U830-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1080 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6454.4 lumens  
Efficiency: N/A  
Efficacy: 113.4 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331699-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331699-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37																				
1	95	91	88	85	86	83	80	77	68	65	64	53	52	51	40	39	38	32																				
2	87	81	75	70	79	73	69	64	60	56	54	47	45	43	36	35	33	28																				
3	80	71	64	59	72	65	59	55	53	49	46	42	40	37	32	31	29	25																				
4	74	63	56	50	67	58	52	47	48	43	40	38	35	32	29	27	26	22																				
5	68	57	49	44	61	52	45	41	43	38	34	35	31	29	27	25	23	19																				
6	63	51	44	38	57	47	40	36	39	34	30	32	28	25	25	22	20	17																				
7	58	46	39	34	53	43	36	31	36	31	27	29	25	23	23	20	18	16																				
8	54	42	35	30	49	39	32	28	33	28	24	27	23	20	21	19	17	14																				
9	50	39	32	27	46	36	29	25	30	25	22	25	21	19	20	17	15	13																				
10	47	36	29	24	43	33	27	23	28	23	20	23	19	17	18	16	14	12																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	22357	22357	22357	22357
5°	24969	22498	19947	22498
10°	27702	22338	17290	22338
15°	29065	22011	13623	22011
20°	25197	21526	11789	21526
25°	16527	20861	10525	20861
30°	11123	20057	9527	20057
35°	9008	19042	8592	19042
40°	8011	17939	7950	17939
45°	7250	16643	7099	16643
50°	6599	15360	6574	15360
55°	6204	13937	6120	13937
60°	5189	12633	5125	12633
65°	4374	11469	4963	11469
70°	4046	10244	4683	10244
75°	3780	8914	4323	8914
80°	3487	7336	3849	7336
85°	3205	5798	3390	5798



TEST NUMBER: P331699-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.3	2.0
10°-20°	365.7	5.7
20°-30°	471.3	7.3
30°-40°	447.9	6.9
40°-50°	383.7	5.9
50°-60°	292.2	4.5
60°-70°	184.7	2.9
70°-80°	92.2	1.4
80°-90°	27.4	0.4
90°-100°	46.2	0.7
100°-110°	169.4	2.6
110°-120°	452.8	7.0
120°-130°	747.4	11.6
130°-140°	794.9	12.3
140°-150°	738.8	11.4
150°-160°	594.0	9.2
160°-170°	382.8	5.9
170°-180°	131.8	2.0
0°-30°	968.3	15.0
0°-40°	1416.2	21.9
0°-60°	2092.1	32.4
0°-90°	2396.4	37.1
90°-120°	668.4	10.4
90°-150°	2949.4	45.7
90°-180°	4058.0	62.9
0°-180°	6454.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1385	1385	1385	1385	1385	
5°	1541	1388	1231	1388	1541	152
15°	1739	1317	815	1317	1739	469
25°	928	1171	591	1171	928	440
35°	457	966	436	966	457	292
45°	318	729	311	729	318	246
55°	220	495	217	495	220	193
65°	114	300	130	300	114	117
75°	61	143	69	143	61	64
85°	17	31	18	31	17	19
90°	27	1	27	1	27	13
95°	43	65	43	65	43	40
105°	76	305	76	305	76	79
115°	82	576	82	576	82	206
125°	857	815	857	815	857	741
135°	1041	1008	1041	1008	1041	802
145°	1187	1169	1187	1169	1187	743
155°	1288	1288	1288	1288	1288	595
165°	1354	1357	1354	1357	1354	382
175°	1380	1388	1380	1388	1380	131
180°	1385	1385	1385	1385	1385	



TEST NUMBER: P331699-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1440.9	1442.0	1443.2	1440.5	1440.5	1438.1	1433.1	1429.4	1418.5	1417.0	1417.0
5°	1540.6	1539.5	1541.5	1535.3	1526.6	1524.7	1515.5	1503.5	1491.0	1477.1	1474.1
7.5°	1639.6	1638.2	1634.4	1633.3	1626.6	1612.1	1597.4	1581.8	1560.9	1540.7	1530.5
10°	1689.7	1705.6	1695.9	1679.1	1682.5	1659.9	1647.8	1627.2	1609.9	1579.5	1572.8
12.5°	1739.0	1745.2	1742.2	1732.6	1728.2	1712.6	1696.4	1678.4	1646.4	1619.2	1595.5
15°	1738.8	1747.9	1750.3	1747.5	1749.8	1748.9	1740.2	1725.3	1697.4	1667.5	1641.6
17.5°	1610.4	1616.7	1632.6	1643.2	1656.7	1685.2	1699.2	1704.7	1700.5	1683.6	1665.3
20°	1466.5	1455.9	1500.2	1522.8	1542.0	1590.1	1631.4	1647.4	1672.8	1672.4	1667.5
22.5°	1262.4	1265.0	1306.9	1333.8	1390.0	1438.0	1485.3	1545.0	1594.3	1626.9	1646.1
25°	927.7	945.9	987.8	1024.4	1086.8	1176.4	1257.6	1352.0	1441.0	1511.2	1578.1
27.5°	696.6	698.0	731.2	765.0	802.1	875.4	977.8	1090.4	1217.3	1322.0	1442.5
30°	596.6	593.7	607.7	628.4	660.1	716.9	793.8	904.6	1031.0	1188.8	1329.4
32.5°	525.8	525.9	536.5	551.8	578.2	616.4	669.1	759.0	878.6	1033.8	1198.4
35°	457.0	456.6	464.3	475.3	486.4	511.0	547.1	594.2	676.5	821.2	989.7
37.5°	407.8	409.9	413.7	420.6	432.8	446.5	468.2	499.8	558.4	644.0	785.6
40°	380.1	381.1	386.3	392.1	399.4	409.9	427.7	453.2	496.1	564.4	667.8
42.5°	354.7	355.6	359.4	364.8	370.4	381.1	395.8	417.8	452.5	505.9	591.2
45°	317.5	317.5	320.9	323.3	329.6	339.2	351.2	369.5	393.6	433.0	489.7
47.5°	282.7	282.8	285.0	289.2	293.1	300.6	312.5	327.3	344.9	375.4	423.9
50°	262.7	263.2	264.6	268.0	270.4	277.1	286.3	299.3	317.5	341.1	381.5
52.5°	246.6	246.2	248.1	249.5	251.2	256.0	262.8	274.3	290.6	311.1	344.6
55°	220.4	218.4	221.3	223.8	225.2	227.1	230.9	238.2	252.1	269.5	294.5
57.5°	187.7	186.9	188.9	191.1	195.7	200.9	204.1	208.7	215.9	228.4	253.2
60°	160.7	160.7	165.0	166.5	171.7	178.5	185.2	189.1	196.3	204.4	222.7
62.5°	136.9	137.2	139.2	140.7	143.6	151.9	161.4	169.8	176.6	184.5	196.6
65°	114.5	115.5	115.5	116.4	118.4	120.3	124.1	130.8	142.9	153.9	163.1
67.5°	97.2	97.5	97.7	98.7	99.2	101.3	102.8	105.8	108.7	119.1	130.4
70°	85.7	87.1	86.6	87.6	88.0	89.0	91.0	92.4	96.7	99.2	105.8
72.5°	74.8	75.9	75.8	76.4	77.7	77.9	79.4	80.9	83.6	85.7	89.3
75°	60.6	60.1	60.6	61.5	62.0	62.6	62.6	64.5	65.9	67.9	70.2
77.5°	46.8	47.2	47.1	47.2	47.3	48.2	48.1	49.0	50.4	51.4	52.5
80°	37.5	38.0	37.5	38.0	38.5	38.9	38.5	38.9	40.4	41.4	41.4
82.5°	29.0	29.1	29.4	29.5	29.6	29.7	30.4	30.5	31.6	31.4	31.8
85°	17.3	16.9	16.9	16.9	17.3	17.8	17.3	17.3	17.8	17.8	17.8
87.5°	11.6	11.9	11.8	11.7	11.6	11.4	11.2	11.4	10.7	10.9	10.2
90°	27.1	26.6	26.2	25.7	25.3	24.5	23.4	22.2	21.1	20.1	18.3
92.5°	27.1	26.8	26.5	26.3	26.0	25.5	25.0	24.4	23.8	23.3	22.3
95°	43.1	43.3	43.5	43.7	44.0	43.5	42.4	41.3	40.2	39.1	37.5
97.5°	57.5	57.2	57.0	56.7	56.5	55.9	55.0	54.1	53.2	52.3	48.7
100°	67.1	66.7	66.3	65.8	65.3	64.3	62.5	60.7	58.9	57.1	53.3
102.5°	71.9	71.4	70.7	70.0	69.5	68.0	65.7	63.3	61.1	58.7	90.4
105°	76.2	75.2	74.4	73.5	72.6	70.9	68.4	66.0	63.5	61.1	121.9
107.5°	78.3	77.5	76.5	75.7	74.8	75.6	78.0	80.6	83.0	85.6	158.4
110°	79.2	78.2	77.4	76.4	75.6	86.2	108.6	130.8	153.1	175.3	239.7



TEST NUMBER: P331699-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	79.9	79.3	78.5	77.9	77.1	117.3	198.6	279.8	361.1	442.2	458.2
115°	82.2	98.2	114.2	130.3	146.3	205.9	309.0	412.0	515.1	618.2	612.7
117.5°	335.5	388.1	440.8	493.5	546.2	585.0	609.9	634.9	659.8	684.8	680.9
120°	611.2	641.2	671.3	701.3	731.4	745.2	742.4	739.8	737.1	734.4	730.5
122.5°	762.7	768.5	774.4	780.2	786.0	788.2	786.6	784.9	783.3	781.7	777.4
125°	856.7	856.0	855.4	854.7	854.0	852.9	851.3	849.8	848.2	846.7	842.4
127.5°	916.0	915.9	915.8	915.6	915.5	914.3	912.0	909.7	907.5	905.2	902.0
130°	952.9	953.1	953.3	953.6	953.8	952.6	950.2	947.7	945.3	942.8	940.4
132.5°	988.9	989.2	989.4	989.6	989.9	988.9	986.8	984.7	982.6	980.5	978.1
135°	1041.0	1041.5	1041.9	1042.4	1042.8	1041.9	1039.7	1037.5	1035.3	1033.0	1031.0
137.5°	1088.5	1089.3	1090.1	1090.8	1091.6	1090.8	1088.6	1086.5	1084.3	1082.1	1079.9
140°	1118.2	1119.3	1120.4	1121.5	1122.7	1122.2	1120.2	1118.2	1116.2	1114.2	1111.7
142.5°	1147.1	1148.2	1149.2	1150.4	1151.5	1151.1	1149.3	1147.5	1145.7	1143.9	1141.0
145°	1187.3	1188.5	1189.6	1190.7	1191.8	1191.6	1190.0	1188.5	1186.8	1185.3	1181.6
147.5°	1222.8	1223.7	1224.6	1225.6	1226.5	1226.4	1225.3	1224.1	1222.9	1221.8	1218.0
150°	1244.4	1245.6	1246.7	1247.7	1248.9	1248.8	1247.5	1246.1	1244.8	1243.4	1239.9
152.5°	1262.9	1264.3	1265.8	1267.2	1268.8	1268.9	1267.5	1266.1	1264.8	1263.5	1260.1
155°	1288.5	1290.3	1292.1	1293.8	1295.6	1295.9	1294.6	1293.2	1291.8	1290.5	1287.9
157.5°	1311.9	1313.7	1315.4	1317.2	1318.9	1319.0	1317.5	1316.0	1314.5	1313.0	1311.1
160°	1325.6	1327.2	1328.7	1330.3	1331.8	1331.9	1330.6	1329.3	1327.9	1326.6	1325.3
162.5°	1336.8	1338.7	1340.7	1342.6	1344.4	1344.7	1343.1	1341.6	1340.1	1338.6	1337.5
165°	1353.7	1355.2	1356.8	1358.3	1359.9	1359.9	1358.3	1356.8	1355.2	1353.7	1353.0
167.5°	1364.2	1366.3	1368.3	1370.3	1372.2	1372.5	1370.9	1369.4	1367.8	1366.3	1365.6
170°	1370.6	1372.7	1374.7	1376.7	1378.7	1378.9	1377.3	1375.8	1374.2	1372.7	1372.2
172.5°	1375.5	1377.5	1379.5	1381.5	1383.6	1383.7	1382.1	1380.6	1379.0	1377.5	1377.1
175°	1379.7	1382.0	1384.1	1386.4	1388.6	1388.9	1387.4	1385.8	1384.3	1382.7	1382.2
177.5°	1382.3	1383.9	1385.5	1387.1	1388.7	1388.9	1387.6	1386.4	1385.2	1383.9	1383.7
180°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7



TEST NUMBER: P331699-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1417.8	1414.7	1412.0	1405.0	1401.7	1393.9	1392.8	1392.4	1382.3	1372.7	1370.1
5°	1466.5	1458.8	1447.2	1433.7	1419.8	1405.3	1395.7	1388.1	1368.8	1350.5	1339.9
7.5°	1515.5	1499.0	1479.0	1453.6	1432.3	1408.4	1390.7	1374.9	1347.6	1321.4	1303.7
10°	1552.1	1525.1	1498.7	1463.6	1436.2	1409.2	1384.2	1362.5	1331.7	1297.1	1272.5
12.5°	1574.8	1545.2	1508.7	1474.3	1438.9	1404.6	1371.1	1343.3	1307.1	1271.3	1242.2
15°	1605.5	1573.8	1529.5	1480.5	1434.7	1390.0	1351.5	1316.8	1269.7	1226.9	1191.3
17.5°	1630.6	1587.0	1539.4	1482.6	1429.7	1372.8	1323.2	1279.0	1226.5	1174.9	1132.9
20°	1638.7	1595.4	1540.6	1483.8	1421.3	1354.3	1301.0	1252.8	1196.6	1140.3	1092.1
22.5°	1633.7	1600.1	1539.0	1471.1	1407.0	1337.0	1276.7	1220.9	1158.5	1101.0	1045.2
25°	1599.8	1588.2	1530.5	1456.3	1383.3	1301.9	1232.2	1171.0	1099.9	1038.3	977.6
27.5°	1520.5	1545.5	1509.7	1430.8	1349.4	1262.3	1183.8	1114.3	1040.4	971.1	910.7
30°	1444.4	1501.6	1486.2	1413.1	1322.1	1236.5	1148.5	1075.8	996.9	925.7	866.0
32.5°	1340.0	1434.6	1449.6	1388.5	1294.4	1200.3	1108.1	1035.8	953.4	878.4	820.2
35°	1173.9	1315.4	1380.4	1341.3	1247.1	1145.6	1050.3	966.1	883.4	809.3	751.5
37.5°	975.8	1168.5	1276.7	1279.5	1192.9	1087.3	983.6	900.0	815.3	742.5	680.1
40°	847.3	1056.0	1197.0	1228.3	1155.2	1041.1	936.2	851.1	768.4	697.1	625.5
42.5°	731.8	939.8	1113.1	1167.5	1109.4	996.1	890.9	801.8	721.4	654.0	580.8
45°	591.8	773.6	964.7	1061.9	1029.6	924.7	813.6	728.9	653.4	595.1	524.9
47.5°	499.2	627.4	812.2	943.7	943.1	847.3	738.0	657.0	586.9	532.3	475.4
50°	446.5	558.1	714.4	863.7	876.1	795.8	691.8	611.5	546.1	488.8	443.1
52.5°	399.2	491.2	631.7	774.7	810.3	740.7	639.9	565.7	502.2	449.6	410.4
55°	337.2	408.5	515.3	649.0	702.9	653.8	564.4	495.1	443.6	399.4	365.6
57.5°	285.3	338.7	424.4	532.2	594.8	564.0	490.1	433.9	389.8	349.8	323.2
60°	252.6	296.3	369.0	459.0	528.3	506.6	443.6	391.2	353.6	319.0	294.0
62.5°	221.8	259.4	321.7	394.7	458.3	449.3	397.8	353.8	320.9	289.4	268.2
65°	178.5	205.9	254.5	311.8	362.8	367.1	330.1	300.2	270.9	245.8	227.1
67.5°	142.1	160.0	194.3	242.5	280.7	294.4	271.7	248.9	225.6	206.3	190.0
70°	119.8	134.2	159.3	198.2	233.4	247.8	234.8	217.0	196.8	180.9	166.9
72.5°	97.1	111.1	129.6	158.2	188.3	203.9	199.3	186.6	170.2	157.0	143.8
75°	73.1	77.5	90.0	109.2	132.8	146.3	149.7	142.9	129.9	119.8	112.1
77.5°	54.1	56.6	62.7	72.8	88.1	100.2	105.1	104.3	95.4	89.4	82.3
80°	43.3	44.8	47.6	51.9	63.5	75.5	78.9	78.9	72.7	70.2	63.1
82.5°	32.9	33.9	35.7	38.1	43.5	54.0	57.8	58.5	54.6	51.4	45.7
85°	18.8	18.3	19.2	20.6	21.7	24.5	30.3	31.3	30.3	26.5	25.0
87.5°	9.8	9.9	9.5	8.7	8.6	8.5	9.9	11.4	10.3	9.6	9.3
90°	16.5	14.7	12.9	10.8	8.4	5.9	3.5	1.0	3.5	5.9	8.4
92.5°	21.5	20.5	19.7	19.3	19.6	19.8	20.0	20.3	20.0	19.8	19.6
95°	36.0	34.4	32.8	35.7	43.1	50.4	57.8	65.1	57.8	50.4	43.1
97.5°	45.1	41.5	37.9	46.5	67.1	87.8	108.6	129.2	108.6	87.8	67.1
100°	49.6	45.7	41.9	55.3	85.9	116.3	146.8	177.4	146.8	116.3	85.9
102.5°	122.1	153.7	185.4	204.4	210.8	217.4	223.8	230.3	223.8	217.4	210.8
105°	182.7	243.5	304.3	331.3	324.6	317.9	311.3	304.6	311.3	317.9	324.6
107.5°	231.4	304.3	377.2	410.9	405.5	400.1	394.7	389.4	394.7	400.1	405.5
110°	304.1	368.3	432.7	462.6	457.9	453.3	448.6	443.8	448.6	453.3	457.9





TEST NUMBER: P331699-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	474.1	489.9	505.9	511.7	507.6	503.4	499.4	495.2	499.4	503.4	507.6
115°	607.1	601.5	596.0	591.3	587.5	583.7	579.9	576.2	579.9	583.7	587.5
117.5°	677.1	673.3	669.4	665.4	661.2	657.0	652.7	648.5	652.7	657.0	661.2
120°	726.4	722.5	718.4	714.7	711.4	708.0	704.7	701.3	704.7	708.0	711.4
122.5°	773.0	768.6	764.3	760.3	756.9	753.3	749.8	746.3	749.8	753.3	756.9
125°	838.2	834.0	829.7	826.1	823.3	820.4	817.5	814.6	817.5	820.4	823.3
127.5°	898.8	895.7	892.5	889.4	886.2	883.0	879.8	876.6	879.8	883.0	886.2
130°	937.9	935.5	933.0	930.0	926.5	922.9	919.4	915.8	919.4	922.9	926.5
132.5°	975.6	973.2	970.7	968.0	965.0	962.0	958.9	955.8	958.9	962.0	965.0
135°	1029.0	1027.0	1025.0	1022.2	1018.7	1015.1	1011.5	1008.0	1011.5	1015.1	1018.7
137.5°	1077.6	1075.3	1073.0	1070.6	1068.2	1065.6	1063.2	1060.6	1063.2	1065.6	1068.2
140°	1109.3	1106.8	1104.4	1102.3	1100.5	1098.7	1096.9	1095.1	1096.9	1098.7	1100.5
142.5°	1138.2	1135.4	1132.7	1130.4	1128.8	1127.2	1125.6	1124.0	1125.6	1127.2	1128.8
145°	1177.7	1173.9	1170.2	1168.4	1168.7	1168.8	1169.0	1169.3	1169.0	1168.8	1168.7
147.5°	1214.3	1210.6	1206.8	1205.4	1206.3	1207.1	1208.0	1208.8	1208.0	1207.1	1206.3
150°	1236.3	1232.8	1229.2	1228.2	1229.7	1231.3	1232.8	1234.4	1232.8	1231.3	1229.7
152.5°	1256.7	1253.3	1249.9	1249.2	1250.8	1252.5	1254.3	1256.0	1254.3	1252.5	1250.8
155°	1285.2	1282.5	1279.9	1279.5	1281.5	1283.6	1285.5	1287.5	1285.5	1283.6	1281.5
157.5°	1309.2	1307.4	1305.5	1305.4	1307.1	1308.8	1310.5	1312.2	1310.5	1308.8	1307.1
160°	1323.9	1322.6	1321.3	1321.3	1322.6	1323.9	1325.3	1326.6	1325.3	1323.9	1322.6
162.5°	1336.3	1335.1	1334.0	1334.1	1335.4	1336.7	1338.1	1339.4	1338.1	1336.7	1335.4
165°	1352.4	1351.6	1350.9	1351.3	1352.6	1354.0	1355.3	1356.7	1355.3	1354.0	1352.6
167.5°	1365.0	1364.4	1363.8	1364.1	1365.5	1366.8	1368.2	1369.5	1368.2	1366.8	1365.5
170°	1371.8	1371.4	1370.9	1371.4	1372.7	1374.0	1375.4	1376.7	1375.4	1374.0	1372.7
172.5°	1376.6	1376.2	1375.7	1376.2	1377.5	1378.8	1380.2	1381.5	1380.2	1378.8	1377.5
175°	1381.9	1381.4	1380.9	1381.5	1383.1	1384.6	1386.2	1387.7	1386.2	1384.6	1383.1
177.5°	1383.6	1383.4	1383.2	1383.7	1385.0	1386.2	1387.5	1388.7	1387.5	1386.2	1385.0
180°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7



TEST NUMBER: P331699-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1365.1	1362.4	1357.4	1349.6	1345.0	1336.9	1331.5	1334.6	1335.4	1334.6	1333.9
5°	1328.4	1318.2	1304.3	1290.8	1278.4	1264.9	1257.2	1253.8	1247.1	1243.2	1241.3
7.5°	1284.0	1266.6	1246.9	1223.4	1203.4	1182.6	1172.0	1166.6	1152.8	1145.4	1138.8
10°	1250.9	1223.5	1203.8	1173.0	1154.2	1126.8	1108.1	1108.5	1089.8	1079.1	1071.5
12.5°	1214.4	1184.2	1151.4	1123.7	1097.6	1075.6	1053.0	1043.9	1023.9	1013.7	993.0
15°	1153.8	1118.6	1084.0	1046.4	1020.0	985.8	953.1	913.1	880.9	853.0	845.4
17.5°	1087.5	1044.1	1009.3	965.3	919.9	862.4	824.5	801.3	781.9	767.2	756.2
20°	1042.1	997.9	960.8	894.4	833.3	794.4	766.5	748.7	728.4	712.6	703.9
22.5°	994.4	948.2	897.7	823.6	776.0	744.7	719.8	699.4	685.7	673.3	665.4
25°	926.6	876.1	792.9	741.9	703.4	670.7	653.4	640.8	626.4	609.5	601.9
27.5°	855.1	774.7	714.9	677.0	640.3	619.0	603.4	584.8	571.8	564.3	556.3
30°	801.5	721.2	674.6	633.2	607.2	583.6	565.3	554.8	542.2	529.2	524.0
32.5°	741.9	677.7	633.0	598.5	572.1	552.0	537.6	520.5	511.4	503.4	492.4
35°	667.8	619.3	578.3	550.4	525.4	509.1	492.2	482.1	465.7	459.0	454.7
37.5°	605.0	562.9	532.4	502.9	483.1	465.1	454.8	438.7	431.6	422.3	413.1
40°	569.7	528.3	498.9	474.9	452.7	439.2	426.3	413.3	402.7	398.4	387.3
42.5°	533.5	499.8	470.4	444.0	429.2	415.0	398.6	389.1	378.1	371.1	364.2
45°	483.5	453.7	428.7	407.0	390.7	375.8	365.1	349.3	343.1	329.0	323.3
47.5°	439.7	411.9	388.0	367.5	351.5	341.8	326.3	313.9	303.9	295.3	287.9
50°	408.5	385.4	362.3	344.0	329.6	315.7	299.7	293.5	278.1	273.7	269.5
52.5°	380.0	358.1	336.9	319.0	304.5	291.0	277.0	268.8	258.4	254.1	251.0
55°	340.2	319.0	298.8	282.9	268.4	254.5	245.8	235.7	230.9	227.5	223.8
57.5°	300.1	281.1	265.6	249.5	235.0	223.9	213.9	207.8	202.8	198.4	193.8
60°	274.8	256.5	242.5	227.5	212.6	203.5	195.9	188.6	182.9	176.1	174.2
62.5°	247.8	231.8	219.0	204.4	191.5	183.1	175.8	169.0	162.0	152.2	149.5
65°	210.8	198.2	184.7	172.8	161.2	153.0	142.4	134.7	131.9	130.8	130.4
67.5°	177.3	165.4	153.8	141.6	131.0	123.5	118.1	116.9	114.9	114.3	113.0
70°	155.0	143.8	132.3	120.7	110.7	109.2	107.3	105.4	102.9	102.0	101.0
72.5°	134.9	123.5	111.9	102.6	98.3	96.5	94.6	92.7	91.0	90.1	89.4
75°	103.4	92.8	85.2	81.8	79.4	77.9	75.0	73.6	72.7	71.2	70.7
77.5°	74.5	68.5	64.9	62.9	60.3	58.8	57.1	55.7	54.7	54.4	53.6
80°	56.7	53.9	51.5	48.6	47.6	45.7	45.2	43.8	44.3	42.8	42.8
82.5°	44.1	40.4	38.4	37.0	36.1	34.6	34.0	33.4	33.5	32.4	32.4
85°	22.6	21.7	20.6	19.7	19.7	18.3	18.8	18.3	18.3	17.3	16.9
87.5°	9.5	9.5	9.1	9.4	9.8	9.8	10.0	9.8	10.1	10.3	10.1
90°	10.8	12.9	14.7	16.5	18.3	20.1	21.1	22.2	23.4	24.5	25.3
92.5°	19.3	19.7	20.5	21.5	22.3	23.3	23.8	24.4	25.0	25.5	26.0
95°	35.7	32.8	34.4	36.0	37.5	39.1	40.2	41.3	42.4	43.5	44.0
97.5°	46.5	37.9	41.5	45.1	48.7	52.3	53.2	54.1	55.0	55.9	56.5
100°	55.3	41.9	45.7	49.6	53.3	57.1	58.9	60.7	62.5	64.3	65.3
102.5°	204.4	185.4	153.7	122.1	90.4	58.7	61.1	63.3	65.7	68.0	69.5
105°	331.3	304.3	243.5	182.7	121.9	61.1	63.5	66.0	68.4	70.9	72.6
107.5°	410.9	377.2	304.3	231.4	158.4	85.6	83.0	80.6	78.0	75.6	74.8
110°	462.6	432.7	368.3	304.1	239.7	175.3	153.1	130.8	108.6	86.2	75.6



TEST NUMBER: P331699-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	511.7	505.9	489.9	474.1	458.2	442.2	361.1	279.8	198.6	117.3	77.1
115°	591.3	596.0	601.5	607.1	612.7	618.2	515.1	412.0	309.0	205.9	146.3
117.5°	665.4	669.4	673.3	677.1	680.9	684.8	659.8	634.9	609.9	585.0	546.2
120°	714.7	718.4	722.5	726.4	730.5	734.4	737.1	739.8	742.4	745.2	731.4
122.5°	760.3	764.3	768.6	773.0	777.4	781.7	783.3	784.9	786.6	788.2	786.0
125°	826.1	829.7	834.0	838.2	842.4	846.7	848.2	849.8	851.3	852.9	854.0
127.5°	889.4	892.5	895.7	898.8	902.0	905.2	907.5	909.7	912.0	914.3	915.5
130°	930.0	933.0	935.5	937.9	940.4	942.8	945.3	947.7	950.2	952.6	953.8
132.5°	968.0	970.7	973.2	975.6	978.1	980.5	982.6	984.7	986.8	988.9	989.9
135°	1022.2	1025.0	1027.0	1029.0	1031.0	1033.0	1035.3	1037.5	1039.7	1041.9	1042.8
137.5°	1070.6	1073.0	1075.3	1077.6	1079.9	1082.1	1084.3	1086.5	1088.6	1090.8	1091.6
140°	1102.3	1104.4	1106.8	1109.3	1111.7	1114.2	1116.2	1118.2	1120.2	1122.2	1122.7
142.5°	1130.4	1132.7	1135.4	1138.2	1141.0	1143.9	1145.7	1147.5	1149.3	1151.1	1151.5
145°	1168.4	1170.2	1173.9	1177.7	1181.6	1185.3	1186.8	1188.5	1190.0	1191.6	1191.8
147.5°	1205.4	1206.8	1210.6	1214.3	1218.0	1221.8	1222.9	1224.1	1225.3	1226.4	1226.5
150°	1228.2	1229.2	1232.8	1236.3	1239.9	1243.4	1244.8	1246.1	1247.5	1248.8	1248.9
152.5°	1249.2	1249.9	1253.3	1256.7	1260.1	1263.5	1264.8	1266.1	1267.5	1268.9	1268.8
155°	1279.5	1279.9	1282.5	1285.2	1287.9	1290.5	1291.8	1293.2	1294.6	1295.9	1295.6
157.5°	1305.4	1305.5	1307.4	1309.2	1311.1	1313.0	1314.5	1316.0	1317.5	1319.0	1318.9
160°	1321.3	1321.3	1322.6	1323.9	1325.3	1326.6	1327.9	1329.3	1330.6	1331.9	1331.8
162.5°	1334.1	1334.0	1335.1	1336.3	1337.5	1338.6	1340.1	1341.6	1343.1	1344.7	1344.4
165°	1351.3	1350.9	1351.6	1352.4	1353.0	1353.7	1355.2	1356.8	1358.3	1359.9	1359.9
167.5°	1364.1	1363.8	1364.4	1365.0	1365.6	1366.3	1367.8	1369.4	1370.9	1372.5	1372.2
170°	1371.4	1370.9	1371.4	1371.8	1372.2	1372.7	1374.2	1375.8	1377.3	1378.9	1378.7
172.5°	1376.2	1375.7	1376.2	1376.6	1377.1	1377.5	1379.0	1380.6	1382.1	1383.7	1383.6
175°	1381.5	1380.9	1381.4	1381.9	1382.2	1382.7	1384.3	1385.8	1387.4	1388.9	1388.6
177.5°	1383.7	1383.2	1383.4	1383.6	1383.7	1383.9	1385.2	1386.4	1387.6	1388.9	1388.7
180°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7



TEST NUMBER: P331699-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1329.6	1330.4	1329.3	1330.0	1329.3	1330.4	1329.6	1333.9	1334.6	1335.4	1334.6
5°	1238.9	1233.1	1232.2	1230.7	1232.2	1233.1	1238.9	1241.3	1243.2	1247.1	1253.8
7.5°	1130.6	1129.6	1127.3	1123.9	1127.3	1129.6	1130.6	1138.8	1145.4	1152.8	1166.6
10°	1060.8	1058.5	1058.0	1054.6	1058.0	1058.5	1060.8	1071.5	1079.1	1089.8	1108.5
12.5°	979.3	963.7	962.1	953.8	962.1	963.7	979.3	993.0	1013.7	1023.9	1043.9
15°	833.8	830.9	821.2	815.0	821.2	830.9	833.8	845.4	853.0	880.9	913.1
17.5°	750.6	741.2	738.2	736.9	738.2	741.2	750.6	756.2	767.2	781.9	801.3
20°	697.1	688.5	687.0	686.1	687.0	688.5	697.1	703.9	712.6	728.4	748.7
22.5°	660.2	651.1	647.4	644.5	647.4	651.1	660.2	665.4	673.3	685.7	699.4
25°	597.1	593.7	591.8	590.8	591.8	593.7	597.1	601.9	609.5	626.4	640.8
27.5°	547.7	540.3	538.9	536.4	538.9	540.3	547.7	556.3	564.3	571.8	584.8
30°	519.6	517.2	513.9	511.0	513.9	517.2	519.6	524.0	529.2	542.2	554.8
32.5°	486.5	484.5	481.5	480.1	481.5	484.5	486.5	492.4	503.4	511.4	520.5
35°	449.9	443.1	440.3	435.9	440.3	443.1	449.9	454.7	459.0	465.7	482.1
37.5°	411.0	407.6	403.5	404.9	403.5	407.6	411.0	413.1	422.3	431.6	438.7
40°	381.1	378.6	377.7	377.2	377.7	378.6	381.1	387.3	398.4	402.7	413.3
42.5°	357.2	350.5	348.1	348.0	348.1	350.5	357.2	364.2	371.1	378.1	389.1
45°	320.9	314.6	310.3	310.9	310.3	314.6	320.9	323.3	329.0	343.1	349.3
47.5°	283.8	283.6	280.9	281.7	280.9	283.6	283.8	287.9	295.3	303.9	313.9
50°	266.1	263.2	261.3	261.7	261.3	263.2	266.1	269.5	273.7	278.1	293.5
52.5°	249.1	246.7	245.1	247.1	245.1	246.7	249.1	251.0	254.1	258.4	268.8
55°	221.3	218.4	217.9	217.4	217.9	218.4	221.3	223.8	227.5	230.9	235.7
57.5°	190.2	188.3	185.4	184.2	185.4	188.3	190.2	193.8	198.4	202.8	207.8
60°	167.9	164.1	159.3	158.7	159.3	164.1	167.9	174.2	176.1	182.9	188.6
62.5°	147.5	146.8	145.8	145.7	145.8	146.8	147.5	149.5	152.2	162.0	169.0
65°	129.4	128.9	129.4	129.9	129.4	128.9	129.4	130.4	130.8	131.9	134.7
67.5°	112.8	111.9	111.0	111.4	111.0	111.9	112.8	113.0	114.3	114.9	116.9
70°	100.1	99.6	99.2	99.2	99.2	99.6	100.1	101.0	102.0	102.9	105.4
72.5°	87.8	87.7	87.2	86.8	87.2	87.7	87.8	89.4	90.1	91.0	92.7
75°	70.2	69.3	69.3	69.3	69.3	69.3	70.2	70.7	71.2	72.7	73.6
77.5°	53.5	53.1	52.5	52.1	52.5	53.1	53.5	53.6	54.4	54.7	55.7
80°	42.3	41.8	41.4	41.4	41.4	41.8	42.3	42.8	42.8	44.3	43.8
82.5°	32.3	31.9	31.8	31.4	31.8	31.9	32.3	32.4	32.4	33.5	33.4
85°	17.3	17.8	17.3	18.3	17.3	17.8	17.3	16.9	17.3	18.3	18.3
87.5°	10.2	9.9	10.4	10.0	10.4	9.9	10.2	10.1	10.3	10.1	9.8
90°	25.7	26.2	26.6	27.1	26.6	26.2	25.7	25.3	24.5	23.4	22.2
92.5°	26.3	26.5	26.8	27.1	26.8	26.5	26.3	26.0	25.5	25.0	24.4
95°	43.7	43.5	43.3	43.1	43.3	43.5	43.7	44.0	43.5	42.4	41.3
97.5°	56.7	57.0	57.2	57.5	57.2	57.0	56.7	56.5	55.9	55.0	54.1
100°	65.8	66.3	66.7	67.1	66.7	66.3	65.8	65.3	64.3	62.5	60.7
102.5°	70.0	70.7	71.4	71.9	71.4	70.7	70.0	69.5	68.0	65.7	63.3
105°	73.5	74.4	75.2	76.2	75.2	74.4	73.5	72.6	70.9	68.4	66.0
107.5°	75.7	76.5	77.5	78.3	77.5	76.5	75.7	74.8	75.6	78.0	80.6
110°	76.4	77.4	78.2	79.2	78.2	77.4	76.4	75.6	86.2	108.6	130.8



TEST NUMBER: P331699-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	77.9	78.5	79.3	79.9	79.3	78.5	77.9	77.1	117.3	198.6	279.8
115°	130.3	114.2	98.2	82.2	98.2	114.2	130.3	146.3	205.9	309.0	412.0
117.5°	493.5	440.8	388.1	335.5	388.1	440.8	493.5	546.2	585.0	609.9	634.9
120°	701.3	671.3	641.2	611.2	641.2	671.3	701.3	731.4	745.2	742.4	739.8
122.5°	780.2	774.4	768.5	762.7	768.5	774.4	780.2	786.0	788.2	786.6	784.9
125°	854.7	855.4	856.0	856.7	856.0	855.4	854.7	854.0	852.9	851.3	849.8
127.5°	915.6	915.8	915.9	916.0	915.9	915.8	915.6	915.5	914.3	912.0	909.7
130°	953.6	953.3	953.1	952.9	953.1	953.3	953.6	953.8	952.6	950.2	947.7
132.5°	989.6	989.4	989.2	988.9	989.2	989.4	989.6	989.9	988.9	986.8	984.7
135°	1042.4	1041.9	1041.5	1041.0	1041.5	1041.9	1042.4	1042.8	1041.9	1039.7	1037.5
137.5°	1090.8	1090.1	1089.3	1088.5	1089.3	1090.1	1090.8	1091.6	1090.8	1088.6	1086.5
140°	1121.5	1120.4	1119.3	1118.2	1119.3	1120.4	1121.5	1122.7	1122.2	1120.2	1118.2
142.5°	1150.4	1149.2	1148.2	1147.1	1148.2	1149.2	1150.4	1151.5	1151.1	1149.3	1147.5
145°	1190.7	1189.6	1188.5	1187.3	1188.5	1189.6	1190.7	1191.8	1191.6	1190.0	1188.5
147.5°	1225.6	1224.6	1223.7	1222.8	1223.7	1224.6	1225.6	1226.5	1226.4	1225.3	1224.1
150°	1247.7	1246.7	1245.6	1244.4	1245.6	1246.7	1247.7	1248.9	1248.8	1247.5	1246.1
152.5°	1267.2	1265.8	1264.3	1262.9	1264.3	1265.8	1267.2	1268.8	1268.9	1267.5	1266.1
155°	1293.8	1292.1	1290.3	1288.5	1290.3	1292.1	1293.8	1295.6	1295.9	1294.6	1293.2
157.5°	1317.2	1315.4	1313.7	1311.9	1313.7	1315.4	1317.2	1318.9	1319.0	1317.5	1316.0
160°	1330.3	1328.7	1327.2	1325.6	1327.2	1328.7	1330.3	1331.8	1331.9	1330.6	1329.3
162.5°	1342.6	1340.7	1338.7	1336.8	1338.7	1340.7	1342.6	1344.4	1344.7	1343.1	1341.6
165°	1358.3	1356.8	1355.2	1353.7	1355.2	1356.8	1358.3	1359.9	1359.9	1358.3	1356.8
167.5°	1370.3	1368.3	1366.3	1364.2	1366.3	1368.3	1370.3	1372.2	1372.5	1370.9	1369.4
170°	1376.7	1374.7	1372.7	1370.6	1372.7	1374.7	1376.7	1378.7	1378.9	1377.3	1375.8
172.5°	1381.5	1379.5	1377.5	1375.5	1377.5	1379.5	1381.5	1383.6	1383.7	1382.1	1380.6
175°	1386.4	1384.1	1382.0	1379.7	1382.0	1384.1	1386.4	1388.6	1388.9	1387.4	1385.8
177.5°	1387.1	1385.5	1383.9	1382.3	1383.9	1385.5	1387.1	1388.7	1388.9	1387.6	1386.4
180°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7



TEST NUMBER: P331699-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1331.5	1336.9	1345.0	1349.6	1357.4	1362.4	1365.1	1370.1	1372.7	1382.3	1392.4
5°	1257.2	1264.9	1278.4	1290.8	1304.3	1318.2	1328.4	1339.9	1350.5	1368.8	1388.1
7.5°	1172.0	1182.6	1203.4	1223.4	1246.9	1266.6	1284.0	1303.7	1321.4	1347.6	1374.9
10°	1108.1	1126.8	1154.2	1173.0	1203.8	1223.5	1250.9	1272.5	1297.1	1331.7	1362.5
12.5°	1053.0	1075.6	1097.6	1123.7	1151.4	1184.2	1214.4	1242.2	1271.3	1307.1	1343.3
15°	953.1	985.8	1020.0	1046.4	1084.0	1118.6	1153.8	1191.3	1226.9	1269.7	1316.8
17.5°	824.5	862.4	919.9	965.3	1009.3	1044.1	1087.5	1132.9	1174.9	1226.5	1279.0
20°	766.5	794.4	833.3	894.4	960.8	997.9	1042.1	1092.1	1140.3	1196.6	1252.8
22.5°	719.8	744.7	776.0	823.6	897.7	948.2	994.4	1045.2	1101.0	1158.5	1220.9
25°	653.4	670.7	703.4	741.9	792.9	876.1	926.6	977.6	1038.3	1099.9	1171.0
27.5°	603.4	619.0	640.3	677.0	714.9	774.7	855.1	910.7	971.1	1040.4	1114.3
30°	565.3	583.6	607.2	633.2	674.6	721.2	801.5	866.0	925.7	996.9	1075.8
32.5°	537.6	552.0	572.1	598.5	633.0	677.7	741.9	820.2	878.4	953.4	1035.8
35°	492.2	509.1	525.4	550.4	578.3	619.3	667.8	751.5	809.3	883.4	966.1
37.5°	454.8	465.1	483.1	502.9	532.4	562.9	605.0	680.1	742.5	815.3	900.0
40°	426.3	439.2	452.7	474.9	498.9	528.3	569.7	625.5	697.1	768.4	851.1
42.5°	398.6	415.0	429.2	444.0	470.4	499.8	533.5	580.8	654.0	721.4	801.8
45°	365.1	375.8	390.7	407.0	428.7	453.7	483.5	524.9	595.1	653.4	728.9
47.5°	326.3	341.8	351.5	367.5	388.0	411.9	439.7	475.4	532.3	586.9	657.0
50°	299.7	315.7	329.6	344.0	362.3	385.4	408.5	443.1	488.8	546.1	611.5
52.5°	277.0	291.0	304.5	319.0	336.9	358.1	380.0	410.4	449.6	502.2	565.7
55°	245.8	254.5	268.4	282.9	298.8	319.0	340.2	365.6	399.4	443.6	495.1
57.5°	213.9	223.9	235.0	249.5	265.6	281.1	300.1	323.2	349.8	389.8	433.9
60°	195.9	203.5	212.6	227.5	242.5	256.5	274.8	294.0	319.0	353.6	391.2
62.5°	175.8	183.1	191.5	204.4	219.0	231.8	247.8	268.2	289.4	320.9	353.8
65°	142.4	153.0	161.2	172.8	184.7	198.2	210.8	227.1	245.8	270.9	300.2
67.5°	118.1	123.5	131.0	141.6	153.8	165.4	177.3	190.0	206.3	225.6	248.9
70°	107.3	109.2	110.7	120.7	132.3	143.8	155.0	166.9	180.9	196.8	217.0
72.5°	94.6	96.5	98.3	102.6	111.9	123.5	134.9	143.8	157.0	170.2	186.6
75°	75.0	77.9	79.4	81.8	85.2	92.8	103.4	112.1	119.8	129.9	142.9
77.5°	57.1	58.8	60.3	62.9	64.9	68.5	74.5	82.3	89.4	95.4	104.3
80°	45.2	45.7	47.6	48.6	51.5	53.9	56.7	63.1	70.2	72.7	78.9
82.5°	34.0	34.6	36.1	37.0	38.4	40.4	44.1	45.7	51.4	54.6	58.5
85°	18.8	18.3	19.7	19.7	20.6	21.7	22.6	25.0	26.5	30.3	31.3
87.5°	10.0	9.8	9.8	9.4	9.1	9.5	9.5	9.3	9.6	10.3	11.4
90°	21.1	20.1	18.3	16.5	14.7	12.9	10.8	8.4	5.9	3.5	1.0
92.5°	23.8	23.3	22.3	21.5	20.5	19.7	19.3	19.6	19.8	20.0	20.3
95°	40.2	39.1	37.5	36.0	34.4	32.8	35.7	43.1	50.4	57.8	65.1
97.5°	53.2	52.3	48.7	45.1	41.5	37.9	46.5	67.1	87.8	108.6	129.2
100°	58.9	57.1	53.3	49.6	45.7	41.9	55.3	85.9	116.3	146.8	177.4
102.5°	61.1	58.7	90.4	122.1	153.7	185.4	204.4	210.8	217.4	223.8	230.3
105°	63.5	61.1	121.9	182.7	243.5	304.3	331.3	324.6	317.9	311.3	304.6
107.5°	83.0	85.6	158.4	231.4	304.3	377.2	410.9	405.5	400.1	394.7	389.4
110°	153.1	175.3	239.7	304.1	368.3	432.7	462.6	457.9	453.3	448.6	443.8



TEST NUMBER: P331699-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	361.1	442.2	458.2	474.1	489.9	505.9	511.7	507.6	503.4	499.4	495.2
115°	515.1	618.2	612.7	607.1	601.5	596.0	591.3	587.5	583.7	579.9	576.2
117.5°	659.8	684.8	680.9	677.1	673.3	669.4	665.4	661.2	657.0	652.7	648.5
120°	737.1	734.4	730.5	726.4	722.5	718.4	714.7	711.4	708.0	704.7	701.3
122.5°	783.3	781.7	777.4	773.0	768.6	764.3	760.3	756.9	753.3	749.8	746.3
125°	848.2	846.7	842.4	838.2	834.0	829.7	826.1	823.3	820.4	817.5	814.6
127.5°	907.5	905.2	902.0	898.8	895.7	892.5	889.4	886.2	883.0	879.8	876.6
130°	945.3	942.8	940.4	937.9	935.5	933.0	930.0	926.5	922.9	919.4	915.8
132.5°	982.6	980.5	978.1	975.6	973.2	970.7	968.0	965.0	962.0	958.9	955.8
135°	1035.3	1033.0	1031.0	1029.0	1027.0	1025.0	1022.2	1018.7	1015.1	1011.5	1008.0
137.5°	1084.3	1082.1	1079.9	1077.6	1075.3	1073.0	1070.6	1068.2	1065.6	1063.2	1060.6
140°	1116.2	1114.2	1111.7	1109.3	1106.8	1104.4	1102.3	1100.5	1098.7	1096.9	1095.1
142.5°	1145.7	1143.9	1141.0	1138.2	1135.4	1132.7	1130.4	1128.8	1127.2	1125.6	1124.0
145°	1186.8	1185.3	1181.6	1177.7	1173.9	1170.2	1168.4	1168.7	1168.8	1169.0	1169.3
147.5°	1222.9	1221.8	1218.0	1214.3	1210.6	1206.8	1205.4	1206.3	1207.1	1208.0	1208.8
150°	1244.8	1243.4	1239.9	1236.3	1232.8	1229.2	1228.2	1229.7	1231.3	1232.8	1234.4
152.5°	1264.8	1263.5	1260.1	1256.7	1253.3	1249.9	1249.2	1250.8	1252.5	1254.3	1256.0
155°	1291.8	1290.5	1287.9	1285.2	1282.5	1279.9	1279.5	1281.5	1283.6	1285.5	1287.5
157.5°	1314.5	1313.0	1311.1	1309.2	1307.4	1305.5	1305.4	1307.1	1308.8	1310.5	1312.2
160°	1327.9	1326.6	1325.3	1323.9	1322.6	1321.3	1321.3	1322.6	1323.9	1325.3	1326.6
162.5°	1340.1	1338.6	1337.5	1336.3	1335.1	1334.0	1334.1	1335.4	1336.7	1338.1	1339.4
165°	1355.2	1353.7	1353.0	1352.4	1351.6	1350.9	1351.3	1352.6	1354.0	1355.3	1356.7
167.5°	1367.8	1366.3	1365.6	1365.0	1364.4	1363.8	1364.1	1365.5	1366.8	1368.2	1369.5
170°	1374.2	1372.7	1372.2	1371.8	1371.4	1370.9	1371.4	1372.7	1374.0	1375.4	1376.7
172.5°	1379.0	1377.5	1377.1	1376.6	1376.2	1375.7	1376.2	1377.5	1378.8	1380.2	1381.5
175°	1384.3	1382.7	1382.2	1381.9	1381.4	1380.9	1381.5	1383.1	1384.6	1386.2	1387.7
177.5°	1385.2	1383.9	1383.7	1383.6	1383.4	1383.2	1383.7	1385.0	1386.2	1387.5	1388.7
180°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7



TEST NUMBER: P331699-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1392.8	1393.9	1401.7	1405.0	1412.0	1414.7	1417.8	1417.0	1417.0	1418.5	1429.4
5°	1395.7	1405.3	1419.8	1433.7	1447.2	1458.8	1466.5	1474.1	1477.1	1491.0	1503.5
7.5°	1390.7	1408.4	1432.3	1453.6	1479.0	1499.0	1515.5	1530.5	1540.7	1560.9	1581.8
10°	1384.2	1409.2	1436.2	1463.6	1498.7	1525.1	1552.1	1572.8	1579.5	1609.9	1627.2
12.5°	1371.1	1404.6	1438.9	1474.3	1508.7	1545.2	1574.8	1595.5	1619.2	1646.4	1678.4
15°	1351.5	1390.0	1434.7	1480.5	1529.5	1573.8	1605.5	1641.6	1667.5	1697.4	1725.3
17.5°	1323.2	1372.8	1429.7	1482.6	1539.4	1587.0	1630.6	1665.3	1683.6	1700.5	1704.7
20°	1301.0	1354.3	1421.3	1483.8	1540.6	1595.4	1638.7	1667.5	1672.4	1672.8	1647.4
22.5°	1276.7	1337.0	1407.0	1471.1	1539.0	1600.1	1633.7	1646.1	1626.9	1594.3	1545.0
25°	1232.2	1301.9	1383.3	1456.3	1530.5	1588.2	1599.8	1578.1	1511.2	1441.0	1352.0
27.5°	1183.8	1262.3	1349.4	1430.8	1509.7	1545.5	1520.5	1442.5	1322.0	1217.3	1090.4
30°	1148.5	1236.5	1322.1	1413.1	1486.2	1501.6	1444.4	1329.4	1188.8	1031.0	904.6
32.5°	1108.1	1200.3	1294.4	1388.5	1449.6	1434.6	1340.0	1198.4	1033.8	878.6	759.0
35°	1050.3	1145.6	1247.1	1341.3	1380.4	1315.4	1173.9	989.7	821.2	676.5	594.2
37.5°	983.6	1087.3	1192.9	1279.5	1276.7	1168.5	975.8	785.6	644.0	558.4	499.8
40°	936.2	1041.1	1155.2	1228.3	1197.0	1056.0	847.3	667.8	564.4	496.1	453.2
42.5°	890.9	996.1	1109.4	1167.5	1113.1	939.8	731.8	591.2	505.9	452.5	417.8
45°	813.6	924.7	1029.6	1061.9	964.7	773.6	591.8	489.7	433.0	393.6	369.5
47.5°	738.0	847.3	943.1	943.7	812.2	627.4	499.2	423.9	375.4	344.9	327.3
50°	691.8	795.8	876.1	863.7	714.4	558.1	446.5	381.5	341.1	317.5	299.3
52.5°	639.9	740.7	810.3	774.7	631.7	491.2	399.2	344.6	311.1	290.6	274.3
55°	564.4	653.8	702.9	649.0	515.3	408.5	337.2	294.5	269.5	252.1	238.2
57.5°	490.1	564.0	594.8	532.2	424.4	338.7	285.3	253.2	228.4	215.9	208.7
60°	443.6	506.6	528.3	459.0	369.0	296.3	252.6	222.7	204.4	196.3	189.1
62.5°	397.8	449.3	458.3	394.7	321.7	259.4	221.8	196.6	184.5	176.6	169.8
65°	330.1	367.1	362.8	311.8	254.5	205.9	178.5	163.1	153.9	142.9	130.8
67.5°	271.7	294.4	280.7	242.5	194.3	160.0	142.1	130.4	119.1	108.7	105.8
70°	234.8	247.8	233.4	198.2	159.3	134.2	119.8	105.8	99.2	96.7	92.4
72.5°	199.3	203.9	188.3	158.2	129.6	111.1	97.1	89.3	85.7	83.6	80.9
75°	149.7	146.3	132.8	109.2	90.0	77.5	73.1	70.2	67.9	65.9	64.5
77.5°	105.1	100.2	88.1	72.8	62.7	56.6	54.1	52.5	51.4	50.4	49.0
80°	78.9	75.5	63.5	51.9	47.6	44.8	43.3	41.4	41.4	40.4	38.9
82.5°	57.8	54.0	43.5	38.1	35.7	33.9	32.9	31.8	31.4	31.6	30.5
85°	30.3	24.5	21.7	20.6	19.2	18.3	18.8	17.8	17.8	17.8	17.3
87.5°	9.9	8.5	8.6	8.7	9.5	9.9	9.8	10.2	10.9	10.7	11.4
90°	3.5	5.9	8.4	10.8	12.9	14.7	16.5	18.3	20.1	21.1	22.2
92.5°	20.0	19.8	19.6	19.3	19.7	20.5	21.5	22.3	23.3	23.8	24.4
95°	57.8	50.4	43.1	35.7	32.8	34.4	36.0	37.5	39.1	40.2	41.3
97.5°	108.6	87.8	67.1	46.5	37.9	41.5	45.1	48.7	52.3	53.2	54.1
100°	146.8	116.3	85.9	55.3	41.9	45.7	49.6	53.3	57.1	58.9	60.7
102.5°	223.8	217.4	210.8	204.4	185.4	153.7	122.1	90.4	58.7	61.1	63.3
105°	311.3	317.9	324.6	331.3	304.3	243.5	182.7	121.9	61.1	63.5	66.0
107.5°	394.7	400.1	405.5	410.9	377.2	304.3	231.4	158.4	85.6	83.0	80.6
110°	448.6	453.3	457.9	462.6	432.7	368.3	304.1	239.7	175.3	153.1	130.8





TEST NUMBER: P331699-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	499.4	503.4	507.6	511.7	505.9	489.9	474.1	458.2	442.2	361.1	279.8
115°	579.9	583.7	587.5	591.3	596.0	601.5	607.1	612.7	618.2	515.1	412.0
117.5°	652.7	657.0	661.2	665.4	669.4	673.3	677.1	680.9	684.8	659.8	634.9
120°	704.7	708.0	711.4	714.7	718.4	722.5	726.4	730.5	734.4	737.1	739.8
122.5°	749.8	753.3	756.9	760.3	764.3	768.6	773.0	777.4	781.7	783.3	784.9
125°	817.5	820.4	823.3	826.1	829.7	834.0	838.2	842.4	846.7	848.2	849.8
127.5°	879.8	883.0	886.2	889.4	892.5	895.7	898.8	902.0	905.2	907.5	909.7
130°	919.4	922.9	926.5	930.0	933.0	935.5	937.9	940.4	942.8	945.3	947.7
132.5°	958.9	962.0	965.0	968.0	970.7	973.2	975.6	978.1	980.5	982.6	984.7
135°	1011.5	1015.1	1018.7	1022.2	1025.0	1027.0	1029.0	1031.0	1033.0	1035.3	1037.5
137.5°	1063.2	1065.6	1068.2	1070.6	1073.0	1075.3	1077.6	1079.9	1082.1	1084.3	1086.5
140°	1096.9	1098.7	1100.5	1102.3	1104.4	1106.8	1109.3	1111.7	1114.2	1116.2	1118.2
142.5°	1125.6	1127.2	1128.8	1130.4	1132.7	1135.4	1138.2	1141.0	1143.9	1145.7	1147.5
145°	1169.0	1168.8	1168.7	1168.4	1170.2	1173.9	1177.7	1181.6	1185.3	1186.8	1188.5
147.5°	1208.0	1207.1	1206.3	1205.4	1206.8	1210.6	1214.3	1218.0	1221.8	1222.9	1224.1
150°	1232.8	1231.3	1229.7	1228.2	1229.2	1232.8	1236.3	1239.9	1243.4	1244.8	1246.1
152.5°	1254.3	1252.5	1250.8	1249.2	1249.9	1253.3	1256.7	1260.1	1263.5	1264.8	1266.1
155°	1285.5	1283.6	1281.5	1279.5	1279.9	1282.5	1285.2	1287.9	1290.5	1291.8	1293.2
157.5°	1310.5	1308.8	1307.1	1305.4	1305.5	1307.4	1309.2	1311.1	1313.0	1314.5	1316.0
160°	1325.3	1323.9	1322.6	1321.3	1321.3	1322.6	1323.9	1325.3	1326.6	1327.9	1329.3
162.5°	1338.1	1336.7	1335.4	1334.1	1334.0	1335.1	1336.3	1337.5	1338.6	1340.1	1341.6
165°	1355.3	1354.0	1352.6	1351.3	1350.9	1351.6	1352.4	1353.0	1353.7	1355.2	1356.8
167.5°	1368.2	1366.8	1365.5	1364.1	1363.8	1364.4	1365.0	1365.6	1366.3	1367.8	1369.4
170°	1375.4	1374.0	1372.7	1371.4	1370.9	1371.4	1371.8	1372.2	1372.7	1374.2	1375.8
172.5°	1380.2	1378.8	1377.5	1376.2	1375.7	1376.2	1376.6	1377.1	1377.5	1379.0	1380.6
175°	1386.2	1384.6	1383.1	1381.5	1380.9	1381.4	1381.9	1382.2	1382.7	1384.3	1385.8
177.5°	1387.5	1386.2	1385.0	1383.7	1383.2	1383.4	1383.6	1383.7	1383.9	1385.2	1386.4
180°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7



TEST NUMBER: P331699-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1433.1	1438.1	1440.5	1440.5	1443.2	1442.0	1440.9
5°	1515.5	1524.7	1526.6	1535.3	1541.5	1539.5	1540.6
7.5°	1597.4	1612.1	1626.6	1633.3	1634.4	1638.2	1639.6
10°	1647.8	1659.9	1682.5	1679.1	1695.9	1705.6	1689.7
12.5°	1696.4	1712.6	1728.2	1732.6	1742.2	1745.2	1739.0
15°	1740.2	1748.9	1749.8	1747.5	1750.3	1747.9	1738.8
17.5°	1699.2	1685.2	1656.7	1643.2	1632.6	1616.7	1610.4
20°	1631.4	1590.1	1542.0	1522.8	1500.2	1455.9	1466.5
22.5°	1485.3	1438.0	1390.0	1333.8	1306.9	1265.0	1262.4
25°	1257.6	1176.4	1086.8	1024.4	987.8	945.9	927.7
27.5°	977.8	875.4	802.1	765.0	731.2	698.0	696.6
30°	793.8	716.9	660.1	628.4	607.7	593.7	596.6
32.5°	669.1	616.4	578.2	551.8	536.5	525.9	525.8
35°	547.1	511.0	486.4	475.3	464.3	456.6	457.0
37.5°	468.2	446.5	432.8	420.6	413.7	409.9	407.8
40°	427.7	409.9	399.4	392.1	386.3	381.1	380.1
42.5°	395.8	381.1	370.4	364.8	359.4	355.6	354.7
45°	351.2	339.2	329.6	323.3	320.9	317.5	317.5
47.5°	312.5	300.6	293.1	289.2	285.0	282.8	282.7
50°	286.3	277.1	270.4	268.0	264.6	263.2	262.7
52.5°	262.8	256.0	251.2	249.5	248.1	246.2	246.6
55°	230.9	227.1	225.2	223.8	221.3	218.4	220.4
57.5°	204.1	200.9	195.7	191.1	188.9	186.9	187.7
60°	185.2	178.5	171.7	166.5	165.0	160.7	160.7
62.5°	161.4	151.9	143.6	140.7	139.2	137.2	136.9
65°	124.1	120.3	118.4	116.4	115.5	115.5	114.5
67.5°	102.8	101.3	99.2	98.7	97.7	97.5	97.2
70°	91.0	89.0	88.0	87.6	86.6	87.1	85.7
72.5°	79.4	77.9	77.7	76.4	75.8	75.9	74.8
75°	62.6	62.6	62.0	61.5	60.6	60.1	60.6
77.5°	48.1	48.2	47.3	47.2	47.1	47.2	46.8
80°	38.5	38.9	38.5	38.0	37.5	38.0	37.5
82.5°	30.4	29.7	29.6	29.5	29.4	29.1	29.0
85°	17.3	17.8	17.3	16.9	16.9	16.9	17.3
87.5°	11.2	11.4	11.6	11.7	11.8	11.9	11.6
90°	23.4	24.5	25.3	25.7	26.2	26.6	27.1
92.5°	25.0	25.5	26.0	26.3	26.5	26.8	27.1
95°	42.4	43.5	44.0	43.7	43.5	43.3	43.1
97.5°	55.0	55.9	56.5	56.7	57.0	57.2	57.5
100°	62.5	64.3	65.3	65.8	66.3	66.7	67.1
102.5°	65.7	68.0	69.5	70.0	70.7	71.4	71.9
105°	68.4	70.9	72.6	73.5	74.4	75.2	76.2
107.5°	78.0	75.6	74.8	75.7	76.5	77.5	78.3
110°	108.6	86.2	75.6	76.4	77.4	78.2	79.2



TEST NUMBER: P331699-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	198.6	117.3	77.1	77.9	78.5	79.3	79.9
115°	309.0	205.9	146.3	130.3	114.2	98.2	82.2
117.5°	609.9	585.0	546.2	493.5	440.8	388.1	335.5
120°	742.4	745.2	731.4	701.3	671.3	641.2	611.2
122.5°	786.6	788.2	786.0	780.2	774.4	768.5	762.7
125°	851.3	852.9	854.0	854.7	855.4	856.0	856.7
127.5°	912.0	914.3	915.5	915.6	915.8	915.9	916.0
130°	950.2	952.6	953.8	953.6	953.3	953.1	952.9
132.5°	986.8	988.9	989.9	989.6	989.4	989.2	988.9
135°	1039.7	1041.9	1042.8	1042.4	1041.9	1041.5	1041.0
137.5°	1088.6	1090.8	1091.6	1090.8	1090.1	1089.3	1088.5
140°	1120.2	1122.2	1122.7	1121.5	1120.4	1119.3	1118.2
142.5°	1149.3	1151.1	1151.5	1150.4	1149.2	1148.2	1147.1
145°	1190.0	1191.6	1191.8	1190.7	1189.6	1188.5	1187.3
147.5°	1225.3	1226.4	1226.5	1225.6	1224.6	1223.7	1222.8
150°	1247.5	1248.8	1248.9	1247.7	1246.7	1245.6	1244.4
152.5°	1267.5	1268.9	1268.8	1267.2	1265.8	1264.3	1262.9
155°	1294.6	1295.9	1295.6	1293.8	1292.1	1290.3	1288.5
157.5°	1317.5	1319.0	1318.9	1317.2	1315.4	1313.7	1311.9
160°	1330.6	1331.9	1331.8	1330.3	1328.7	1327.2	1325.6
162.5°	1343.1	1344.7	1344.4	1342.6	1340.7	1338.7	1336.8
165°	1358.3	1359.9	1359.9	1358.3	1356.8	1355.2	1353.7
167.5°	1370.9	1372.5	1372.2	1370.3	1368.3	1366.3	1364.2
170°	1377.3	1378.9	1378.7	1376.7	1374.7	1372.7	1370.6
172.5°	1382.1	1383.7	1383.6	1381.5	1379.5	1377.5	1375.5
175°	1387.4	1388.9	1388.6	1386.4	1384.1	1382.0	1379.7
177.5°	1387.6	1388.9	1388.7	1387.1	1385.5	1383.9	1382.3
180°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7

(END OF REPORT)