

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331428-930

Luminaire Tested: **S122DIP-S1005D330U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331428-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S1005D330U930-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4349.7 lumens
Efficiency: N/A
Efficacy: 87.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331428-930

CATALOG NUMBER: S122DIP-S1005D330U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331428-930

CATALOG NUMBER: S122DIP-S1005D330U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	80	80	80	76
1	104	99	95	91	98	95	91	88	86	83	81	78	76	74	71	69	68	64
2	94	87	80	75	90	83	77	72	75	71	67	69	65	62	62	60	57	54
3	86	76	69	62	82	73	66	60	67	61	56	61	56	52	55	52	49	45
4	79	68	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42	39
5	73	60	52	46	69	58	50	44	53	47	42	49	43	39	45	40	37	34
6	67	54	46	40	64	52	44	39	48	41	36	44	39	34	40	36	32	30
7	62	49	41	35	59	47	40	34	44	37	32	40	35	30	37	32	29	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	24
9	54	41	33	28	51	40	32	27	37	30	26	34	29	25	31	27	23	21
10	50	38	30	25	48	37	29	25	34	28	24	32	26	22	29	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20980	20980	20980
5°	21060	20757	20879
10°	20935	20546	20649
15°	20677	20279	20259
20°	20309	19880	19859
25°	19946	19388	19388
30°	19475	18938	18776
35°	19036	18398	18126
40°	18487	17856	17513
45°	17945	17317	16890
50°	17357	16759	16164
55°	16743	16110	15510
60°	16059	15332	14767
65°	15320	14560	13891
70°	14389	13624	12977
75°	13094	12545	12239
80°	11623	11269	10693
85°	9485	9040	8096



TEST NUMBER: P331428-930

CATALOG NUMBER: S122DIP-S1005D330U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.2	2.8
10°-20°	343.8	7.9
20°-30°	505.4	11.6
30°-40°	587.0	13.5
40°-50°	586.4	13.5
50°-60°	511.4	11.8
60°-70°	378.1	8.7
70°-80°	214.2	4.9
80°-90°	58.9	1.4
90°-100°	59.9	1.4
100°-110°	203.2	4.7
110°-120°	215.9	5.0
120°-130°	177.7	4.1
130°-140°	142.7	3.3
140°-150°	107.9	2.5
150°-160°	75.8	1.7
160°-170°	44.6	1.0
170°-180°	14.5	0.3
0°-30°	971.4	22.3
0°-40°	1558.4	35.8
0°-60°	2656.1	61.1
0°-90°	3307.3	76.0
90°-120°	479.1	11.0
90°-150°	907.4	20.9
90°-180°	1042.0	24.0
0°-180°	4349.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1299	1299	1299	1299	1299	
5°	1299	1294	1281	1290	1288	123
15°	1237	1229	1213	1218	1212	348
25°	1120	1109	1088	1090	1088	515
35°	966	953	933	926	920	603
45°	786	777	758	745	740	606
55°	595	587	572	558	551	532
65°	401	393	381	370	364	397
75°	210	207	201	194	196	224
85°	51	50	49	45	44	59
90°	0	4	10	9	10	3
95°	10	25	113	43	33	11
105°	35	53	213	382	325	37
115°	62	78	179	369	427	61
125°	86	102	172	299	347	77
135°	101	121	170	251	287	78
145°	116	133	169	210	229	73
155°	132	142	164	185	193	61
165°	144	148	157	166	169	40
175°	150	150	151	153	152	14
180°	150	150	150	150	150	



TEST NUMBER: P331428-930

CATALOG NUMBER: S122DIP-S1005D330U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1305.5	1304.3	1303.3	1302.1	1301.0	1299.3	1296.8	1294.4	1291.9	1289.5	1291.7
5°	1299.4	1298.4	1297.2	1296.1	1295.0	1292.9	1289.9	1286.8	1283.8	1280.7	1283.0
7.5°	1287.9	1286.2	1284.5	1282.8	1281.1	1278.6	1275.5	1272.4	1269.3	1266.2	1268.4
10°	1276.9	1275.0	1273.1	1271.1	1269.2	1266.6	1263.2	1259.9	1256.5	1253.2	1255.5
12.5°	1262.0	1260.2	1258.5	1256.8	1255.1	1252.5	1249.2	1245.9	1242.6	1239.3	1240.8
15°	1237.0	1235.3	1233.6	1232.0	1230.3	1227.7	1224.1	1220.4	1216.8	1213.2	1214.4
17.5°	1205.0	1203.3	1201.7	1200.0	1198.3	1195.6	1192.0	1188.3	1184.6	1181.0	1182.3
20°	1182.0	1180.3	1178.7	1177.0	1175.3	1172.6	1168.7	1164.8	1160.9	1157.0	1157.8
22.5°	1159.0	1156.7	1154.4	1152.0	1149.7	1146.7	1143.0	1139.4	1135.7	1132.0	1132.2
25°	1119.6	1117.3	1115.1	1112.9	1110.7	1107.2	1102.4	1097.7	1093.0	1088.3	1088.8
27.5°	1074.6	1072.5	1070.6	1068.5	1066.6	1063.7	1060.0	1056.2	1052.6	1048.8	1048.0
30°	1044.6	1042.4	1040.1	1037.9	1035.7	1032.5	1028.3	1024.2	1020.0	1015.8	1015.0
32.5°	1012.6	1010.8	1009.0	1007.2	1005.4	1002.4	998.0	993.6	989.2	984.8	983.3
35°	965.8	963.0	960.3	957.5	954.7	951.1	946.6	942.2	937.8	933.4	931.7
37.5°	913.1	910.7	908.2	905.8	903.4	899.9	895.4	891.0	886.6	882.2	880.0
40°	877.1	874.9	872.7	870.5	868.2	865.0	860.5	856.1	851.6	847.2	844.7
42.5°	842.1	839.9	837.7	835.5	833.2	829.9	825.5	821.0	816.6	812.1	809.4
45°	785.9	784.0	782.0	780.1	778.1	775.1	770.9	766.8	762.6	758.4	755.4
47.5°	729.9	728.1	726.3	724.5	722.6	719.5	715.2	710.9	706.5	702.2	699.0
50°	691.0	689.6	688.2	686.8	685.4	682.7	678.9	675.0	671.1	667.2	663.3
52.5°	653.0	651.2	649.3	647.5	645.6	642.9	639.2	635.5	631.9	628.3	625.0
55°	594.8	593.0	591.4	589.8	588.1	585.5	582.3	578.9	575.6	572.3	568.9
57.5°	536.3	534.9	533.6	532.3	530.9	528.5	524.8	521.1	517.5	513.8	510.5
60°	497.3	496.2	495.0	494.0	492.8	490.3	486.5	482.6	478.7	474.8	471.7
62.5°	459.3	457.5	455.8	454.0	452.2	449.8	446.8	443.8	440.8	437.8	435.0
65°	401.0	399.4	397.8	396.1	394.4	392.2	389.4	386.6	383.8	381.1	378.6
67.5°	341.9	340.6	339.2	337.9	336.6	334.6	332.1	329.6	327.1	324.7	322.7
70°	304.8	303.8	302.6	301.6	300.4	298.6	296.1	293.6	291.1	288.6	286.7
72.5°	266.8	265.8	264.6	263.6	262.4	261.1	259.5	257.9	256.2	254.6	252.7
75°	209.9	209.4	208.8	208.2	207.7	206.7	205.3	203.9	202.5	201.1	199.5
77.5°	158.9	158.0	157.0	156.1	155.2	154.4	153.8	153.3	152.7	152.2	151.3
80°	125.0	124.7	124.4	124.1	123.8	123.4	122.9	122.3	121.7	121.2	120.3
82.5°	92.9	92.9	92.9	92.8	92.7	92.5	92.2	91.9	91.6	91.2	90.2
85°	51.2	51.0	50.7	50.4	50.1	49.8	49.6	49.2	49.0	48.8	47.9
87.5°	18.0	17.8	17.5	17.2	16.9	16.6	16.5	16.5	16.3	16.0	15.2
90°	0.3	1.1	2.3	2.9	3.4	4.3	5.8	7.7	9.5	9.8	9.5
92.5°	3.5	5.1	7.2	8.4	10.4	13.0	19.6	28.8	36.9	37.4	31.6
95°	10.1	11.3	14.1	16.7	21.3	28.2	41.5	66.5	100.0	112.9	98.8
97.5°	16.4	17.9	21.0	24.9	30.2	38.1	54.7	89.7	145.2	192.7	202.2
100°	22.2	23.1	25.6	30.2	36.0	44.1	59.4	94.5	156.7	227.6	269.0
102.5°	27.5	28.1	30.7	35.3	41.3	49.4	63.5	94.7	152.3	228.7	293.9
105°	35.1	36.3	38.3	42.6	49.0	57.1	70.6	96.2	143.7	213.4	290.1
107.5°	43.5	44.4	46.3	50.3	56.6	64.7	77.9	100.2	139.5	197.1	264.8
110°	49.0	50.1	51.9	55.6	61.6	70.0	82.7	103.4	138.6	189.2	248.9



TEST NUMBER: P331428-930

CATALOG NUMBER: S122DIP-S1005D330U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	54.1	55.2	57.2	60.7	66.4	75.1	87.3	106.9	138.8	184.2	237.8
115°	62.0	63.3	65.1	68.6	74.4	82.1	94.5	112.0	140.0	178.6	224.1
117.5°	70.1	71.3	73.0	76.1	81.6	89.7	101.1	117.6	142.1	175.9	215.5
120°	75.2	76.3	78.1	80.6	86.4	94.5	105.7	121.3	143.5	174.3	210.8
122.5°	80.1	81.0	82.7	85.5	91.2	99.5	110.1	124.5	145.0	173.3	206.9
125°	86.4	87.3	89.0	92.5	98.2	106.3	116.7	129.6	147.5	171.7	201.4
127.5°	91.5	92.6	95.1	98.9	104.4	112.7	122.8	134.4	149.9	170.7	196.2
130°	94.5	95.6	98.5	102.6	108.4	116.3	126.5	137.4	151.8	170.2	192.7
132.5°	97.3	98.7	101.7	106.0	112.0	120.1	129.7	140.4	153.7	170.0	190.0
135°	101.4	102.6	106.0	110.3	117.0	125.0	134.3	144.3	155.9	169.7	186.1
137.5°	105.3	106.7	110.1	114.8	121.3	128.8	137.9	147.3	157.8	169.6	183.4
140°	108.4	109.5	112.9	117.6	123.8	131.3	140.0	149.0	158.7	169.4	181.7
142.5°	111.3	112.3	115.4	120.1	126.2	133.2	141.6	150.3	159.4	169.4	180.2
145°	115.8	117.0	119.8	124.2	130.0	136.2	144.1	152.1	160.1	168.8	178.1
147.5°	120.7	121.5	124.3	128.2	133.1	138.7	146.0	153.1	160.4	167.8	175.9
150°	123.8	124.7	127.0	130.8	135.1	140.3	146.9	153.5	160.1	167.1	174.0
152.5°	127.1	127.5	129.8	133.1	137.2	141.9	147.8	153.8	159.7	165.9	172.4
155°	131.7	131.9	133.6	136.8	140.0	144.3	149.2	154.1	159.0	163.9	169.4
157.5°	135.4	135.7	137.1	139.9	142.4	146.0	150.2	154.1	157.7	161.8	166.6
160°	137.9	138.3	139.4	141.7	144.1	147.2	150.7	154.1	157.0	160.5	164.4
162.5°	140.6	140.3	141.5	143.3	145.4	147.9	150.9	153.8	156.3	159.3	162.7
165°	143.5	143.2	143.7	145.4	146.9	148.6	151.2	153.3	155.0	157.0	159.6
167.5°	145.9	145.5	146.0	147.2	148.2	149.3	151.2	152.9	153.7	155.0	156.6
170°	147.5	146.9	147.2	148.1	148.6	149.5	150.9	152.4	153.0	153.8	155.0
172.5°	148.4	148.1	147.9	148.8	149.1	149.8	150.7	151.7	152.1	152.5	153.4
175°	149.5	149.2	149.0	149.5	149.5	149.8	150.3	150.9	150.7	150.9	151.2
177.5°	150.0	149.5	149.4	149.8	149.8	149.8	150.0	150.5	150.0	149.8	150.0
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8



TEST NUMBER: P331428-930

CATALOG NUMBER: S122DIP-S1005D330U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1293.9	1296.1	1298.4	1299.3	1298.8	1298.4	1297.9	1297.5
5°	1285.2	1287.4	1289.6	1290.5	1289.9	1289.3	1288.7	1288.2
7.5°	1270.6	1272.8	1275.1	1275.9	1275.3	1274.7	1274.1	1273.5
10°	1257.7	1259.9	1262.1	1262.8	1262.0	1261.1	1260.3	1259.5
12.5°	1242.4	1243.9	1245.5	1245.9	1245.3	1244.7	1244.1	1243.5
15°	1215.4	1216.6	1217.6	1217.6	1216.2	1214.8	1213.4	1212.0
17.5°	1183.6	1184.9	1186.1	1186.1	1184.7	1183.4	1182.1	1180.7
20°	1158.7	1159.5	1160.3	1160.2	1159.1	1158.0	1156.9	1155.8
22.5°	1132.4	1132.5	1132.7	1132.5	1131.8	1131.1	1130.4	1129.8
25°	1089.4	1090.0	1090.5	1090.5	1090.0	1089.4	1088.8	1088.3
27.5°	1047.2	1046.3	1045.5	1044.4	1043.1	1041.7	1040.4	1039.1
30°	1014.2	1013.3	1012.5	1011.5	1010.4	1009.3	1008.2	1007.1
32.5°	981.9	980.3	978.8	977.5	976.4	975.3	974.2	973.1
35°	930.0	928.4	926.7	925.2	923.8	922.4	921.0	919.6
37.5°	878.0	876.0	873.9	872.2	870.9	869.5	868.2	866.9
40°	842.1	839.7	837.1	835.4	834.2	833.2	832.0	830.9
42.5°	806.7	804.0	801.3	799.2	797.6	796.1	794.5	792.9
45°	752.4	749.3	746.2	744.1	743.0	741.9	740.8	739.7
47.5°	695.8	692.5	689.3	686.9	685.3	683.7	682.1	680.4
50°	659.4	655.6	651.7	649.1	647.7	646.3	644.9	643.5
52.5°	621.8	618.6	615.4	612.9	611.0	609.2	607.3	605.5
55°	565.6	562.2	559.0	556.6	555.2	553.8	552.4	551.0
57.5°	507.2	503.9	500.7	498.5	497.5	496.4	495.4	494.3
60°	468.7	465.6	462.6	460.6	459.8	459.0	458.1	457.3
62.5°	432.2	429.3	426.5	424.5	423.5	422.4	421.3	420.3
65°	376.1	373.6	371.1	369.2	367.8	366.4	365.0	363.6
67.5°	320.7	318.8	316.8	315.3	314.2	313.1	312.0	310.9
70°	284.7	282.8	280.9	279.3	278.2	277.1	276.0	274.9
72.5°	250.8	248.8	246.9	245.5	244.6	243.7	242.8	241.9
75°	197.9	196.2	194.5	194.0	194.5	195.0	195.6	196.2
77.5°	150.5	149.7	148.9	148.1	147.2	146.5	145.7	145.0
80°	119.5	118.7	117.9	117.2	116.6	116.1	115.5	115.0
82.5°	89.1	88.1	87.0	86.4	86.3	86.2	86.1	85.9
85°	47.0	46.2	45.4	44.8	44.6	44.3	44.0	43.7
87.5°	14.5	13.7	13.2	12.8	12.6	12.3	12.1	11.9
90°	9.2	8.6	9.2	9.5	9.5	9.5	9.5	9.5
92.5°	25.1	21.5	19.2	17.4	17.1	16.2	16.4	16.0
95°	75.5	57.9	45.8	39.5	35.7	33.4	32.5	32.9
97.5°	176.1	144.1	112.9	92.1	78.4	71.3	67.1	64.7
100°	263.0	227.3	187.8	153.0	129.1	116.7	108.4	103.1
102.5°	319.9	311.9	283.0	246.1	220.0	198.9	188.5	181.5
105°	350.0	382.5	386.3	376.8	358.9	341.0	328.6	324.7
107.5°	328.3	377.4	407.3	421.3	423.5	422.6	420.0	414.7
110°	309.7	361.3	398.1	421.8	434.1	439.6	442.2	441.9



TEST NUMBER: P331428-930

CATALOG NUMBER: S122DIP-S1005D330U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	292.6	342.1	381.5	408.6	425.8	435.0	439.9	441.4
115°	271.7	316.0	353.8	383.4	403.9	417.1	424.6	427.2
117.5°	255.8	294.8	329.1	356.9	377.7	391.8	399.6	401.8
120°	248.0	283.7	314.3	340.5	360.7	374.2	382.5	385.5
122.5°	241.8	274.5	303.5	327.1	345.2	358.6	366.0	368.4
125°	232.8	262.4	287.8	309.4	326.1	337.0	344.2	346.6
127.5°	223.8	250.7	274.6	294.5	309.1	319.4	325.5	327.4
130°	218.1	242.9	265.6	284.6	298.7	308.5	314.3	316.6
132.5°	212.5	235.5	256.4	274.3	288.1	297.9	303.2	305.3
135°	204.8	223.8	242.9	258.9	271.3	280.9	286.1	287.2
137.5°	198.7	214.6	229.7	243.7	255.0	263.2	267.7	269.5
140°	194.7	208.6	221.8	234.5	243.7	251.2	255.5	257.2
142.5°	191.5	203.3	214.7	225.3	234.0	240.8	244.7	245.0
145°	186.9	196.5	205.4	213.8	220.6	225.6	228.4	229.3
147.5°	183.4	190.9	197.9	204.0	209.7	213.6	215.6	216.1
150°	180.9	187.3	193.3	198.4	202.8	206.3	208.0	208.3
152.5°	178.4	184.3	189.4	193.9	197.3	200.2	201.5	201.6
155°	174.9	179.4	183.8	186.9	190.1	192.2	193.3	192.7
157.5°	170.8	174.6	178.2	180.8	183.0	184.7	185.2	185.2
160°	168.2	171.4	174.6	176.6	178.6	180.0	180.3	180.3
162.5°	165.7	168.4	171.1	172.7	174.7	175.7	175.9	175.7
165°	161.9	163.9	165.9	167.1	168.2	169.4	169.4	169.1
167.5°	158.2	159.8	161.2	162.2	162.7	163.4	163.3	163.0
170°	156.5	157.3	158.4	159.0	159.3	160.1	159.9	159.3
172.5°	154.3	155.0	155.9	156.2	156.5	156.9	156.6	156.3
175°	152.1	152.4	152.7	153.0	153.0	153.3	153.0	152.4
177.5°	150.5	150.5	150.7	150.7	150.7	150.7	150.5	150.0
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8

(END OF REPORT)