

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331443-930

Luminaire Tested: **S122DIP-S1005D725U930-4F0-1E-UDD-D4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331443-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S1005D725U930-4F0-1E-UDD-D4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5598.2 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: General Diffuse


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331443-930

CATALOG NUMBER: S122DIP-S1005D725U930-4F0-1E-UDD-D4

Luminous Intensity Polar Plot





TEST NUMBER: P331443-930

CATALOG NUMBER: S122DIP-S1005D725U930-4F0-1E-UDD-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	97	92	87	83	89	85	81	77	72	69	66	60	58	56	49	47	46	41
2	87	79	72	67	80	73	67	62	62	57	54	52	48	45	42	40	38	33
3	79	69	61	55	73	64	57	51	54	49	44	45	41	38	37	34	31	27
4	72	61	52	46	66	56	49	43	48	42	37	40	35	32	33	29	27	23
5	66	54	45	39	61	50	42	37	43	37	32	36	31	27	29	26	23	20
6	61	48	40	34	56	45	37	32	38	32	28	32	27	24	26	23	20	17
7	56	43	35	29	52	40	33	28	35	29	24	29	24	21	24	20	18	15
8	52	39	31	26	48	37	29	24	31	26	21	27	22	18	22	18	16	13
9	49	36	28	23	45	33	26	22	29	23	19	24	20	17	20	17	14	12
10	45	33	25	20	42	31	24	19	27	21	17	23	18	15	19	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13919	13919	13919
5°	13988	13400	13350
10°	13899	13004	12858
15°	13709	12584	12339
20°	13467	12136	11842
25°	13227	11701	11390
30°	12890	11257	10936
35°	12550	10828	10617
40°	12191	10461	10297
45°	11850	10133	10022
50°	11485	9837	9754
55°	11101	9519	9479
60°	10631	9187	9189
65°	10145	8801	8846
70°	9596	8384	8474
75°	8897	7976	8132
80°	7792	7559	7784
85°	6733	7197	7515



TEST NUMBER: P331443-930

CATALOG NUMBER: S122DIP-S1005D725U930-4F0-1E-UDD-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.7	1.5
10°-20°	234.3	4.2
20°-30°	355.0	6.3
30°-40°	432.4	7.7
40°-50°	465.2	8.3
50°-60°	451.7	8.1
60°-70°	394.4	7.0
70°-80°	303.7	5.4
80°-90°	206.8	3.7
90°-100°	272.9	4.9
100°-110°	552.2	9.9
110°-120°	545.4	9.7
120°-130°	431.0	7.7
130°-140°	331.6	5.9
140°-150°	241.4	4.3
150°-160°	167.7	3.0
160°-170°	98.7	1.8
170°-180°	32.1	0.6
0°-30°	670.9	12.0
0°-40°	1103.3	19.7
0°-60°	2020.2	36.1
0°-90°	2925.0	52.2
90°-120°	1370.5	24.5
90°-150°	2374.6	42.4
90°-180°	2673.0	47.7
0°-180°	5598.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	862	862	862	862	862	
5°	865	861	853	860	860	82
15°	825	827	827	838	837	232
25°	750	759	770	784	788	345
35°	646	667	691	717	727	404
45°	530	564	607	644	658	409
55°	406	452	516	559	577	363
65°	277	339	412	462	480	275
75°	154	224	304	355	374	163
85°	45	123	202	253	272	48
90°	13	94	187	234	251	10
95°	32	124	394	284	279	32
105°	84	161	580	994	883	90
115°	142	194	470	927	1071	140
125°	194	231	422	736	854	172
135°	226	270	389	594	685	175
145°	256	294	374	471	521	161
155°	291	314	363	410	426	134
165°	317	327	347	368	374	89
175°	331	331	334	338	337	31
180°	331	331	331	331	331	



TEST NUMBER: P331443-930

CATALOG NUMBER: S122DIP-S1005D725U930-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	862.1	862.1	862.1	862.1	862.1	862.1	862.1	862.1	862.1	862.1	862.1
2.5°	867.2	866.5	865.8	865.1	864.5	863.3	861.8	860.2	858.7	857.1	858.3
5°	864.6	863.8	863.0	862.1	861.3	860.1	858.4	856.7	855.1	853.4	855.1
7.5°	856.9	856.3	855.7	855.2	854.7	853.8	852.5	851.2	849.9	848.6	850.6
10°	850.9	850.4	849.8	849.2	848.6	848.0	847.2	846.3	845.5	844.7	846.9
12.5°	840.9	841.0	841.1	841.2	841.3	841.1	840.5	839.8	839.3	838.6	840.9
15°	824.7	825.2	825.7	826.3	826.9	827.1	827.1	827.1	827.1	827.1	829.6
17.5°	803.6	804.9	806.0	807.1	808.3	809.3	810.2	811.1	812.0	812.9	815.5
20°	789.7	791.1	792.5	793.9	795.2	796.5	797.6	798.7	799.8	801.0	804.0
22.5°	774.7	776.2	777.9	779.5	781.1	782.7	784.2	785.8	787.3	788.9	792.0
25°	749.7	751.6	753.6	755.5	757.5	759.7	762.1	764.7	767.2	769.6	773.0
27.5°	719.7	722.8	726.0	729.2	732.4	735.4	738.3	741.3	744.2	747.2	751.4
30°	699.7	703.3	706.9	710.5	714.1	717.8	721.4	725.0	728.6	732.2	736.6
32.5°	677.7	681.8	685.8	689.9	693.9	698.1	702.4	706.6	710.9	715.2	720.3
35°	646.0	650.7	655.4	660.1	664.9	669.8	675.1	680.4	685.7	691.0	697.1
37.5°	611.5	616.9	622.4	627.8	633.2	639.4	646.2	653.1	659.9	666.8	673.5
40°	588.5	594.6	600.7	606.8	612.9	619.7	627.2	634.7	642.2	649.7	657.0
42.5°	566.6	572.6	578.7	584.8	590.9	598.3	606.9	615.6	624.1	632.8	640.6
45°	529.8	537.3	544.8	552.3	559.8	568.3	578.1	587.8	597.5	607.2	615.9
47.5°	493.6	501.7	509.9	518.0	526.2	536.0	547.4	558.7	570.1	581.5	590.5
50°	468.6	477.2	485.8	494.4	503.0	513.6	526.0	538.5	551.0	563.5	573.0
52.5°	444.6	453.6	462.7	471.7	480.8	491.9	505.0	518.2	531.3	544.5	554.2
55°	406.1	416.0	426.1	436.1	446.1	458.3	472.7	487.1	501.6	516.0	526.0
57.5°	368.1	379.4	390.6	401.9	413.2	426.2	440.9	455.6	470.3	485.0	495.8
60°	341.1	353.0	365.0	376.9	388.9	402.8	418.6	434.4	450.2	466.0	476.6
62.5°	317.2	329.5	341.9	354.2	366.6	380.7	396.6	412.4	428.3	444.1	455.3
65°	277.4	291.0	304.6	318.2	331.8	346.8	363.2	379.5	395.9	412.3	423.7
67.5°	240.9	255.1	269.3	283.6	297.7	313.2	330.0	346.8	363.5	380.3	391.8
70°	214.9	229.3	243.8	258.2	272.6	288.5	305.7	322.9	340.1	357.3	369.2
72.5°	190.9	205.8	220.7	235.5	250.5	266.6	284.1	301.5	318.9	336.4	348.1
75°	153.7	169.3	184.7	200.3	215.9	232.5	250.3	268.1	285.8	303.6	315.5
77.5°	117.7	134.0	150.3	166.5	182.8	199.9	218.0	236.0	254.0	272.1	284.1
80°	93.7	110.6	127.6	144.6	161.4	179.0	197.0	215.1	233.1	251.1	262.8
82.5°	73.7	90.4	107.1	123.8	140.6	158.1	176.3	194.6	212.9	231.1	242.8
85°	45.0	62.2	79.4	96.6	113.8	131.3	149.1	166.9	184.7	202.4	214.1
87.5°	24.6	41.6	58.6	75.4	92.2	109.7	128.2	146.8	165.3	183.3	194.4
90°	13.1	31.1	49.8	67.2	84.5	103.4	124.3	146.6	168.2	186.6	197.1
92.5°	19.2	37.7	57.3	75.1	94.4	116.4	148.0	185.3	220.5	238.8	236.8
95°	32.3	47.9	67.3	86.1	109.3	139.5	185.5	257.6	348.2	393.5	372.8
97.5°	45.1	60.1	78.5	98.7	122.1	153.2	206.0	299.3	438.1	559.5	590.6
100°	57.8	70.0	86.0	106.5	129.5	160.3	209.6	302.9	456.1	628.4	730.5
102.5°	68.6	79.3	94.5	114.1	136.6	166.7	213.1	297.3	439.9	623.9	778.3
105°	84.0	94.6	107.1	124.7	146.8	175.9	220.3	291.5	411.1	579.7	759.0
107.5°	102.1	110.6	121.4	136.6	156.9	185.1	228.0	291.2	392.0	533.3	692.4
110°	113.3	121.5	130.9	144.6	163.6	191.7	233.3	292.8	384.2	510.0	650.8



TEST NUMBER: P331443-930

CATALOG NUMBER: S122DIP-S1005D725U930-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	124.6	131.8	140.8	153.2	170.7	198.5	238.5	294.8	378.3	491.7	619.3
115°	142.0	148.3	155.2	165.8	181.6	206.6	246.5	297.9	372.2	470.1	579.1
117.5°	158.9	163.4	169.3	178.0	192.2	216.9	253.8	301.7	367.5	453.9	549.7
120°	170.1	173.7	178.7	185.6	199.4	223.3	259.3	304.8	365.0	444.3	533.0
122.5°	180.8	183.3	187.5	194.2	207.4	231.2	265.0	307.3	363.2	436.3	518.1
125°	193.7	195.6	199.4	207.1	219.8	242.1	273.9	311.5	359.9	422.3	495.5
127.5°	204.9	207.2	212.2	220.4	232.4	254.1	283.6	316.5	358.1	411.2	474.4
130°	211.6	213.8	219.9	228.5	241.0	261.6	289.8	319.8	357.5	404.1	460.5
132.5°	217.7	220.5	227.1	236.2	249.2	269.1	294.9	323.1	356.9	397.6	448.2
135°	225.6	228.1	235.8	245.3	260.0	279.2	302.4	327.5	355.8	389.1	431.3
137.5°	234.2	237.3	244.8	255.0	269.5	286.7	308.0	330.0	354.4	381.7	417.4
140°	240.9	243.1	250.5	260.4	274.2	290.9	310.5	330.8	353.1	377.2	409.1
142.5°	247.5	249.2	256.2	266.0	279.3	294.7	313.5	332.8	353.1	375.3	402.6
145°	256.2	258.8	265.1	274.7	287.4	301.4	318.7	336.5	354.3	373.5	395.5
147.5°	266.9	268.8	274.9	283.7	294.3	306.8	323.0	338.7	354.9	371.2	389.2
150°	274.0	276.0	281.0	289.3	298.9	310.4	325.1	339.7	354.3	369.7	384.9
152.5°	281.2	282.1	287.1	294.4	303.5	314.0	327.1	340.2	353.4	367.1	381.4
155°	291.2	291.9	295.7	302.7	309.7	319.3	330.1	341.0	351.8	362.6	374.7
157.5°	299.7	300.3	303.4	309.5	315.1	323.1	332.3	341.0	348.9	358.1	368.5
160°	305.2	305.9	308.4	313.6	318.7	325.6	333.3	341.0	347.3	355.0	363.9
162.5°	310.9	310.5	313.1	317.2	321.7	327.2	333.9	340.5	345.8	352.5	359.8
165°	317.4	316.7	318.0	321.9	325.1	328.9	334.6	339.1	342.9	347.3	353.1
167.5°	322.8	322.0	323.1	325.5	327.8	330.3	334.4	338.2	340.0	342.9	346.4
170°	326.3	325.1	325.6	327.6	328.9	330.8	333.9	337.1	338.4	340.3	342.9
172.5°	328.3	327.6	327.2	329.1	329.9	331.3	333.5	335.6	336.4	337.3	339.3
175°	330.8	330.1	329.5	330.8	330.8	331.4	332.6	333.9	333.3	333.9	334.6
177.5°	331.9	330.9	330.4	331.4	331.4	331.4	331.9	333.0	331.9	331.4	331.9
180°	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4



TEST NUMBER: P331443-930

CATALOG NUMBER: S122DIP-S1005D725U930-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	862.1	862.1	862.1	862.1	862.1	862.1	862.1	862.1
2.5°	859.3	860.5	861.6	861.9	861.4	861.0	860.5	860.1
5°	856.7	858.4	860.1	860.7	860.5	860.2	859.9	859.7
7.5°	852.6	854.7	856.6	857.5	857.2	857.0	856.6	856.4
10°	849.1	851.3	853.5	854.5	854.2	853.9	853.7	853.4
12.5°	843.1	845.3	847.5	848.5	848.2	847.9	847.7	847.4
15°	832.2	834.6	837.1	838.3	838.0	837.7	837.4	837.1
17.5°	818.2	820.8	823.4	824.7	824.7	824.7	824.7	824.7
20°	807.0	810.1	813.1	814.6	814.6	814.6	814.6	814.6
22.5°	795.0	798.1	801.1	802.9	803.3	803.8	804.2	804.7
25°	776.3	779.7	783.0	785.1	785.9	786.8	787.6	788.4
27.5°	755.6	759.9	764.1	766.5	767.1	767.7	768.3	768.9
30°	741.1	745.5	750.0	752.6	753.4	754.2	755.1	755.9
32.5°	725.5	730.5	735.6	738.9	740.5	741.9	743.5	744.9
35°	703.2	709.3	715.4	719.4	721.4	723.3	725.3	727.2
37.5°	680.3	687.1	693.8	698.2	700.3	702.4	704.4	706.5
40°	664.1	671.4	678.6	683.5	686.0	688.4	691.0	693.5
42.5°	648.5	656.4	664.3	669.4	672.0	674.5	676.9	679.5
45°	624.4	633.1	641.6	647.3	650.1	652.9	655.7	658.4
47.5°	599.5	608.5	617.5	623.5	626.6	629.7	632.7	635.8
50°	582.4	591.8	601.3	607.6	610.6	613.6	616.7	619.7
52.5°	563.9	573.5	583.2	589.6	592.9	596.2	599.5	602.8
55°	536.1	546.0	556.0	562.8	566.4	570.1	573.6	577.2
57.5°	506.6	517.4	528.2	535.3	539.0	542.7	546.3	550.0
60°	487.1	497.7	508.3	515.5	519.3	523.3	527.2	531.0
62.5°	466.5	477.7	488.9	496.4	500.0	503.7	507.4	511.0
65°	435.1	446.5	457.9	465.4	469.0	472.5	476.2	479.8
67.5°	403.3	414.8	426.3	434.0	437.7	441.5	445.3	449.1
70°	381.2	393.1	405.1	412.7	416.0	419.4	422.7	426.1
72.5°	359.8	371.5	383.2	391.1	395.1	399.1	403.1	407.1
75°	327.5	339.4	351.4	359.1	362.7	366.4	370.0	373.6
77.5°	295.9	307.8	319.7	327.6	331.4	335.3	339.2	343.1
80°	274.4	286.2	297.8	305.6	309.5	313.3	317.2	321.1
82.5°	254.5	266.1	277.8	285.4	289.1	292.8	296.4	300.1
85°	225.8	237.4	249.1	256.8	260.7	264.6	268.5	272.4
87.5°	205.7	216.7	228.3	235.9	239.5	243.0	246.5	250.1
90°	207.6	217.4	229.8	237.6	240.9	244.3	247.6	250.9
92.5°	233.3	236.3	241.8	244.9	247.8	249.1	252.9	255.2
95°	331.7	303.5	287.2	280.1	275.2	273.5	274.8	278.8
97.5°	543.2	482.6	423.9	384.7	357.4	345.0	339.0	337.0
100°	727.3	658.6	581.6	511.1	461.3	436.9	421.5	413.1
102.5°	845.9	838.0	784.2	709.1	654.7	611.0	590.9	578.5
105°	901.2	983.0	1000.9	986.3	949.9	913.4	889.1	883.2
107.5°	842.3	960.1	1035.7	1072.8	1080.8	1081.7	1079.2	1070.4
110°	794.1	917.0	1007.5	1065.8	1096.3	1111.4	1120.1	1122.6



TEST NUMBER: P331443-930

CATALOG NUMBER: S122DIP-S1005D725U930-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	749.3	867.7	963.8	1029.7	1070.9	1094.2	1108.1	1114.6
115°	692.6	799.1	890.9	962.2	1010.6	1042.9	1062.6	1071.3
117.5°	647.3	741.6	825.6	892.7	941.6	975.4	995.7	1003.4
120°	623.0	709.8	785.1	848.6	896.2	929.2	950.8	960.2
122.5°	602.8	682.7	754.3	811.8	854.4	886.5	905.5	913.5
125°	572.4	645.6	709.1	762.0	801.4	828.1	846.5	854.2
127.5°	542.4	608.7	668.5	717.3	752.0	777.1	793.3	799.8
130°	523.3	584.7	641.7	688.3	721.7	745.6	760.6	767.8
132.5°	504.6	561.7	614.5	658.4	691.3	715.2	729.1	735.9
135°	478.6	526.4	574.3	614.1	643.7	666.9	680.6	685.4
137.5°	456.2	496.5	535.0	569.6	596.5	616.4	628.4	634.1
140°	442.2	477.3	511.0	542.1	564.2	582.4	593.6	599.1
142.5°	431.3	460.9	489.7	515.6	536.4	552.9	562.9	565.1
145°	416.9	439.7	461.1	481.1	497.7	510.0	517.7	521.1
147.5°	406.3	423.1	438.7	452.7	465.9	475.3	480.3	482.1
150°	400.2	414.3	427.6	439.1	448.7	456.3	460.2	460.8
152.5°	394.6	407.6	419.0	428.9	436.4	443.0	445.9	446.0
155°	386.9	397.1	406.6	413.6	420.6	425.1	427.6	426.4
157.5°	377.8	386.4	394.4	399.8	404.8	408.5	409.7	409.7
160°	372.2	379.2	386.2	390.7	395.2	398.4	398.9	398.9
162.5°	366.6	372.6	378.5	382.0	386.5	388.7	389.3	388.7
165°	358.2	362.6	367.1	369.7	372.2	374.7	374.7	374.1
167.5°	350.2	353.6	356.6	359.0	360.1	361.5	361.3	360.6
170°	346.1	348.0	350.5	351.8	352.5	354.3	353.7	352.5
172.5°	341.4	342.9	345.0	345.7	346.3	347.2	346.6	345.8
175°	336.5	337.1	337.8	338.4	338.4	339.1	338.4	337.1
177.5°	333.0	333.0	333.5	333.5	333.5	333.5	333.0	331.9
180°	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4

(END OF REPORT)