

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931276

Luminaire Tested: DFN2DS-TR2F0-040DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931276
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR2F0-040DS935-RLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2924.0 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.36' x L: 2.04' x H: 0')
CIE Type: Direct

Input Watts (W): 38.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931276

CATALOG NUMBER: DFN2DS-TR2F0-040DS935-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931276

CATALOG NUMBER: DFN2DS-TR2F0-040DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3171	3171	3171
5°	3183	3131	3149
10°	3159	3080	3054
15°	3123	2989	2903
20°	3072	2858	2715
25°	3021	2710	2533
30°	2949	2558	2300
35°	2880	2393	2095
40°	2810	2222	1858
45°	2727	2029	1644
50°	2643	1835	1433
55°	2557	1626	1231
60°	2457	1406	1022
65°	2343	1182	930
70°	2207	973	856
75°	2040	887	799
80°	1801	793	728
85°	1415	624	624

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2727 cd/sqm

TEST NUMBER: P931276

CATALOG NUMBER: DFN2DS-TR2F0-040DS935-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.2	4.6
10°-20°	365.8	12.5
20°-30°	513.6	17.6
30°-40°	559.8	19.1
40°-50°	514.5	17.6
50°-60°	404.1	13.8
60°-70°	263.0	9.0
70°-80°	135.4	4.6
80°-90°	34.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1012.6	34.6
0°-40°	1572.4	53.8
0°-60°	2491.0	85.2
0°-90°	2924.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2924.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1422	1422	1422	1422	1422	
5°	1422	1415	1398	1410	1406	135
15°	1352	1338	1294	1270	1257	381
25°	1228	1186	1101	1049	1029	565
35°	1058	992	879	798	769	662
45°	865	778	643	552	521	668
55°	658	557	418	341	317	588
65°	444	340	224	180	176	440
75°	237	147	103	94	93	250
85°	55	28	24	24	24	66
90°	0	0	0	0	0	

TEST NUMBER: P931276

CATALOG NUMBER: DFN2DS-TR2F0-040DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1421.8	1421.8	1421.8	1421.8	1421.8
2.5°	1428.2	1421.8	1407.6	1420.5	1417.9
5°	1421.8	1415.3	1398.5	1410.1	1406.4
7.5°	1410.1	1402.5	1384.5	1389.5	1383.1
10°	1394.7	1385.7	1360.0	1356.0	1348.5
12.5°	1375.5	1363.9	1329.0	1321.4	1307.2
15°	1352.3	1338.1	1294.4	1270.0	1257.1
17.5°	1325.3	1304.6	1250.5	1222.3	1201.7
20°	1294.4	1268.6	1204.3	1172.2	1143.8
22.5°	1260.9	1231.3	1156.6	1112.9	1093.7
25°	1227.5	1186.3	1101.3	1048.7	1029.2
27.5°	1187.7	1143.8	1049.9	989.4	959.8
30°	1145.2	1096.2	993.2	927.7	892.9
32.5°	1104.0	1044.7	939.3	862.1	829.8
35°	1057.7	992.0	878.8	797.7	769.4
37.5°	1012.6	941.8	822.2	733.3	701.2
40°	965.0	887.9	763.0	671.7	638.2
42.5°	916.1	833.8	703.8	608.5	576.5
45°	864.6	778.4	643.4	551.9	521.1
47.5°	815.8	724.5	585.5	494.1	465.8
50°	761.7	670.4	528.8	440.0	413.1
52.5°	708.9	612.4	474.8	389.8	365.4
55°	657.5	557.1	418.1	341.0	316.6
57.5°	604.8	501.8	368.0	295.9	275.4
60°	550.7	447.7	315.2	249.7	229.1
62.5°	498.0	395.1	270.1	208.5	198.2
65°	443.9	339.6	223.9	180.2	176.2
67.5°	392.5	288.2	180.2	158.2	154.4
70°	338.4	238.0	149.2	136.4	131.2
72.5°	287.0	191.7	124.8	114.6	112.0
75°	236.7	146.6	102.9	93.9	92.7
77.5°	186.6	104.1	81.1	75.9	73.3
80°	140.2	74.6	61.7	56.7	56.7
82.5°	97.8	50.2	42.5	39.8	39.8
85°	55.3	28.3	24.4	24.4	24.4
87.5°	20.6	10.2	10.2	9.0	9.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931276

CATALOG NUMBER: DFN2DS-TR2F0-040DS935-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.24	16.77	15.61	17.08	17.39	11.20	12.73	11.57	13.04	13.35
	3H	17.01	18.37	17.39	18.70	19.06	12.47	13.84	12.85	14.16	14.52
	4H	17.68	18.96	18.08	19.31	19.68	12.97	14.25	13.37	14.60	14.98
	6H	18.16	19.35	18.58	19.71	20.11	13.35	14.54	13.77	14.90	15.29
	8H	18.33	19.46	18.76	19.85	20.25	13.48	14.60	13.90	14.99	15.39
	12H	18.43	19.51	18.86	19.89	20.32	13.56	14.64	13.99	15.02	15.45
4H	2H	15.35	16.63	15.75	16.98	17.36	11.90	13.18	12.30	13.53	13.91
	3H	17.28	18.34	17.69	18.74	19.15	13.34	14.41	13.75	14.81	15.21
	4H	18.03	18.99	18.46	19.40	19.84	13.94	14.90	14.38	15.32	15.75
	6H	18.62	19.45	19.08	19.90	20.36	14.43	15.26	14.89	15.71	16.17
	8H	18.84	19.61	19.30	20.06	20.53	14.59	15.37	15.06	15.81	16.28
	12H	18.99	19.69	19.47	20.16	20.63	14.71	15.40	15.19	15.88	16.35
8H	4H	18.06	18.83	18.52	19.28	19.74	14.30	15.07	14.76	15.52	15.99
	6H	18.69	19.33	19.19	19.83	20.30	14.88	15.53	15.38	16.02	16.49
	8H	18.94	19.52	19.46	20.03	20.52	15.10	15.68	15.62	16.19	16.68
	12H	19.15	19.66	19.66	20.15	20.71	15.28	15.79	15.79	16.28	16.85
12H	4H	18.04	18.73	18.52	19.21	19.68	14.34	15.03	14.82	15.51	15.98
	6H	18.67	19.25	19.19	19.76	20.25	14.95	15.52	15.46	16.03	16.52
	8H	18.96	19.47	19.47	19.96	20.52	15.22	15.73	15.73	16.22	16.79