

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931311

Luminaire Tested: DFN2DS-TR2F0-060DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931311
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR2F0-060DS935-FLL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5108.4 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.36' x L: 2.04' x H: 0')
CIE Type: Direct

Input Watts (W): 61.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931311

CATALOG NUMBER: DFN2DS-TR2F0-060DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931311

CATALOG NUMBER: DFN2DS-TR2F0-060DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4478	4478	4478
5°	4495	4431	4457
10°	4469	4386	4408
15°	4413	4329	4325
20°	4335	4243	4239
25°	4257	4138	4138
30°	4157	4043	4008
35°	4064	3927	3869
40°	3946	3811	3738
45°	3831	3696	3605
50°	3705	3578	3450
55°	3574	3439	3311
60°	3427	3273	3152
65°	3271	3108	2965
70°	3072	2908	2770
75°	2794	2678	2613
80°	2482	2404	2281
85°	2022	1927	1730

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3831 cd/sqm

TEST NUMBER: P931311

CATALOG NUMBER: DFN2DS-TR2F0-060DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	3.7
10°-20°	531.7	10.4
20°-30°	781.4	15.3
30°-40°	907.5	17.8
40°-50°	906.4	17.7
50°-60°	790.4	15.5
60°-70°	584.3	11.4
70°-80°	330.6	6.5
80°-90°	87.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1502.1	29.4
0°-40°	2409.6	47.2
0°-60°	4106.3	80.4
0°-90°	5108.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5108.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2008	2008	2008	2008	2008	
5°	2008	2000	1979	1994	1991	191
15°	1911	1900	1875	1882	1873	538
25°	1730	1714	1682	1685	1682	796
35°	1492	1473	1442	1430	1421	932
45°	1214	1201	1172	1151	1143	937
55°	919	907	884	861	852	822
65°	620	608	589	572	562	613
75°	324	321	311	299	303	346
85°	79	77	75	69	68	93
90°	0	0	0	0	0	

TEST NUMBER: P931311

CATALOG NUMBER: DFN2DS-TR2F0-060DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2007.8	2007.8	2007.8	2007.8	2007.8
2.5°	2019.5	2009.8	1988.5	2007.8	2004.1
5°	2007.8	2000.2	1978.9	1994.3	1990.6
7.5°	1994.3	1982.8	1961.5	1977.1	1973.2
10°	1973.2	1959.7	1936.5	1951.9	1946.1
12.5°	1944.1	1932.6	1909.5	1919.1	1915.2
15°	1911.3	1899.8	1874.6	1882.5	1872.8
17.5°	1870.8	1859.3	1834.1	1843.7	1834.1
20°	1826.3	1814.9	1787.8	1793.5	1786.0
22.5°	1782.1	1764.6	1739.4	1739.4	1735.6
25°	1729.8	1714.5	1681.6	1685.3	1681.6
27.5°	1671.8	1658.3	1633.3	1627.6	1618.0
30°	1614.1	1598.5	1569.7	1563.9	1556.1
32.5°	1552.2	1540.8	1509.8	1498.1	1490.4
35°	1492.4	1473.2	1442.2	1430.5	1420.9
37.5°	1424.8	1407.4	1376.5	1362.9	1353.3
40°	1355.4	1339.8	1308.9	1291.7	1283.9
42.5°	1287.8	1272.2	1241.5	1222.1	1210.5
45°	1214.5	1200.9	1171.8	1150.8	1142.9
47.5°	1142.9	1129.4	1098.6	1077.2	1065.7
50°	1067.6	1058.0	1031.0	1003.9	994.2
52.5°	994.2	980.7	955.7	934.5	921.0
55°	919.1	907.4	884.3	861.1	851.5
57.5°	843.7	834.1	808.9	785.8	778.0
60°	768.3	760.8	733.8	712.4	706.7
62.5°	695.0	681.5	662.2	642.9	635.2
65°	619.8	608.2	588.9	571.5	561.8
67.5°	542.6	532.8	515.6	502.1	494.2
70°	471.1	463.4	445.9	432.4	424.8
72.5°	397.8	390.0	380.4	366.9	361.1
75°	324.2	320.6	310.7	299.3	303.2
77.5°	258.7	250.9	247.0	241.3	235.6
80°	193.2	191.1	187.2	181.5	177.6
82.5°	131.3	131.3	129.4	121.7	121.7
85°	79.0	77.2	75.3	69.4	67.6
87.5°	34.8	31.0	27.0	21.3	19.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931311

CATALOG NUMBER: DFN2DS-TR2F0-060DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.49	18.10	16.86	18.42	18.73	16.05	17.66	16.41	17.97	18.29
	3H	18.24	19.70	18.62	20.02	20.38	17.75	19.21	18.13	19.53	19.89
	4H	18.89	20.26	19.29	20.60	20.98	18.39	19.76	18.79	20.11	20.49
	6H	19.36	20.63	19.77	20.99	21.38	18.86	20.12	19.27	20.49	20.88
	8H	19.50	20.71	19.92	21.10	21.50	19.00	20.21	19.42	20.60	21.00
	12H	19.59	20.75	20.02	21.13	21.56	19.08	20.24	19.51	20.62	21.05
4H	2H	17.05	18.42	17.45	18.77	19.14	16.70	18.07	17.10	18.42	18.79
	3H	19.03	20.17	19.44	20.57	20.97	18.62	19.77	19.03	20.16	20.56
	4H	19.80	20.84	20.23	21.25	21.69	19.38	20.42	19.81	20.83	21.27
	6H	20.40	21.30	20.85	21.75	22.20	19.97	20.87	20.42	21.31	21.77
	8H	20.59	21.44	21.05	21.88	22.34	20.15	21.00	20.61	21.44	21.91
	12H	20.72	21.48	21.20	21.96	22.43	20.27	21.03	20.75	21.51	21.97
8H	4H	20.08	20.92	20.54	21.37	21.83	19.70	20.55	20.16	20.99	21.46
	6H	20.79	21.49	21.28	21.98	22.46	20.41	21.11	20.90	21.60	22.08
	8H	21.05	21.68	21.56	22.19	22.67	20.66	21.29	21.17	21.80	22.28
	12H	21.25	21.81	21.76	22.30	22.86	20.84	21.40	21.34	21.89	22.45
12H	4H	20.10	20.86	20.58	21.34	21.81	19.74	20.50	20.22	20.97	21.44
	6H	20.84	21.47	21.35	21.98	22.46	20.47	21.10	20.98	21.61	22.09
	8H	21.15	21.71	21.66	22.20	22.76	20.77	21.33	21.28	21.82	22.38

END OF REPORT