

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931312

Luminaire Tested: DFN2DS-TR2F0-060DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931312
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR2F0-060DS935-RLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4386.0 lumens
Efficiency: N/A
Efficacy: 71.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.36' x L: 2.04' x H: 0')
CIE Type: Direct

Input Watts (W): 61.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931312

CATALOG NUMBER: DFN2DS-TR2F0-060DS935-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931312

CATALOG NUMBER: DFN2DS-TR2F0-060DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4757	4757	4757
5°	4775	4697	4723
10°	4738	4620	4581
15°	4684	4483	4354
20°	4608	4288	4072
25°	4531	4066	3800
30°	4424	3837	3450
35°	4320	3590	3142
40°	4215	3332	2787
45°	4091	3044	2465
50°	3965	2753	2150
55°	3835	2439	1846
60°	3685	2109	1533
65°	3514	1772	1395
70°	3310	1459	1283
75°	3060	1331	1199
80°	2701	1188	1092
85°	2122	937	937

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4091 cd/sqm

TEST NUMBER: P931312

CATALOG NUMBER: DFN2DS-TR2F0-060DS935-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.9	4.6
10°-20°	548.7	12.5
20°-30°	770.3	17.6
30°-40°	839.7	19.1
40°-50°	771.8	17.6
50°-60°	606.1	13.8
60°-70°	394.5	9.0
70°-80°	203.1	4.6
80°-90°	51.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1518.9	34.6
0°-40°	2358.6	53.8
0°-60°	3736.5	85.2
0°-90°	4386.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4386.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2133	2133	2133	2133	2133	
5°	2133	2123	2098	2115	2110	202
15°	2028	2007	1942	1905	1886	572
25°	1841	1779	1652	1573	1544	847
35°	1586	1488	1318	1197	1154	993
45°	1297	1168	965	828	782	1002
55°	986	836	627	512	475	881
65°	666	510	336	270	264	660
75°	355	220	154	141	139	376
85°	83	42	37	37	37	99
90°	0	0	0	0	0	

TEST NUMBER: P931312

CATALOG NUMBER: DFN2DS-TR2F0-060DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2132.6	2132.6	2132.6	2132.6	2132.6
2.5°	2142.3	2132.6	2111.3	2130.7	2126.9
5°	2132.6	2123.0	2097.8	2115.3	2109.5
7.5°	2115.3	2103.7	2076.7	2084.3	2074.7
10°	2092.0	2078.5	2040.1	2034.2	2022.6
12.5°	2063.2	2045.8	1993.6	1982.1	1960.8
15°	2028.4	2007.1	1941.5	1904.9	1885.6
17.5°	1987.9	1956.9	1875.8	1833.4	1802.6
20°	1941.5	1902.8	1806.4	1758.3	1715.7
22.5°	1891.4	1846.9	1735.0	1669.4	1640.5
25°	1841.3	1779.4	1652.1	1573.0	1544.0
27.5°	1781.5	1715.7	1574.8	1484.1	1439.7
30°	1717.8	1644.2	1489.9	1391.6	1339.4
32.5°	1655.9	1567.1	1409.0	1293.1	1244.8
35°	1586.5	1488.1	1318.3	1196.6	1154.0
37.5°	1518.9	1412.6	1233.3	1100.0	1051.9
40°	1447.5	1331.8	1144.4	1007.4	957.3
42.5°	1374.2	1250.7	1055.7	912.8	864.7
45°	1297.0	1167.5	965.1	827.8	781.6
47.5°	1223.7	1086.7	878.2	741.1	698.7
50°	1142.6	1005.6	793.3	660.0	619.6
52.5°	1063.3	918.6	712.2	584.8	548.2
55°	986.2	835.7	627.2	511.5	474.8
57.5°	907.1	752.7	552.0	443.9	413.0
60°	826.0	671.7	472.8	374.5	343.6
62.5°	747.0	592.6	405.2	312.7	297.3
65°	665.9	509.5	335.8	270.3	264.4
67.5°	588.7	432.2	270.3	237.4	231.6
70°	507.6	357.1	223.8	204.6	196.8
72.5°	430.4	287.5	187.1	171.8	167.9
75°	355.1	219.9	154.4	140.9	139.1
77.5°	279.9	156.3	121.6	113.9	110.0
80°	210.3	112.0	92.5	85.0	85.0
82.5°	146.6	75.3	63.6	59.8	59.8
85°	82.9	42.4	36.6	36.6	36.6
87.5°	31.0	15.4	15.4	13.5	13.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931312

CATALOG NUMBER: DFN2DS-TR2F0-060DS935-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.65	18.17	17.02	18.49	18.80	12.61	14.14	12.98	14.45	14.76
	3H	18.42	19.78	18.80	20.11	20.47	13.88	15.24	14.26	15.57	15.93
	4H	19.08	20.37	19.48	20.71	21.09	14.38	15.66	14.78	16.01	16.39
	6H	19.57	20.76	19.99	21.12	21.52	14.76	15.95	15.17	16.31	16.70
	8H	19.74	20.87	20.17	21.26	21.66	14.89	16.01	15.31	16.40	16.80
	12H	19.84	20.92	20.27	21.30	21.73	14.97	16.05	15.40	16.43	16.86
4H	2H	16.76	18.04	17.16	18.39	18.76	13.31	14.59	13.71	14.94	15.32
	3H	18.69	19.75	19.10	20.15	20.55	14.75	15.82	15.16	16.21	16.62
	4H	19.44	20.40	19.87	20.81	21.25	15.35	16.31	15.78	16.72	17.16
	6H	20.03	20.86	20.49	21.31	21.77	15.84	16.67	16.30	17.12	17.57
	8H	20.25	21.02	20.71	21.47	21.93	16.00	16.78	16.47	17.22	17.69
	12H	20.40	21.09	20.88	21.57	22.04	16.12	16.81	16.60	17.29	17.76
8H	4H	19.46	20.24	19.93	20.69	21.15	15.71	16.48	16.17	16.93	17.39
	6H	20.10	20.74	20.60	21.24	21.71	16.29	16.94	16.79	17.43	17.90
	8H	20.35	20.93	20.87	21.44	21.93	16.51	17.09	17.03	17.60	18.09
	12H	20.56	21.07	21.07	21.56	22.12	16.69	17.20	17.20	17.69	18.26
12H	4H	19.45	20.14	19.93	20.62	21.09	15.75	16.44	16.23	16.92	17.39
	6H	20.08	20.66	20.60	21.17	21.66	16.36	16.93	16.87	17.44	17.93
	8H	20.37	20.88	20.88	21.37	21.93	16.63	17.14	17.14	17.63	18.20