

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331367-930

Luminaire Tested: **S122DIP-S675D1080U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331367-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S675D1080U930-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5531.6 lumens  
Efficiency: N/A  
Efficacy: 97.2 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331367-930

CATALOG NUMBER: S122DIP-S675D1080U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331367-930

CATALOG NUMBER: S122DIP-S675D1080U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43																												
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43	37																												
2	88	81	75	70	81	75	70	65	62	58	55	51	48	46	40	38	37	32																												
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	27																												
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24																												
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	27	24	21																												
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19																												
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17																												
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	23	20	18	15																												
9	50	39	31	26	46	36	29	25	30	25	22	26	22	19	21	18	16	14																												
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	17486	17486	17486	17486
5°	19603	17598	15595	17598
10°	22463	17454	13496	17454
15°	24849	17135	11925	17135
20°	24471	16790	10869	16790
25°	22066	16335	10203	16335
30°	18233	15605	9715	15605
35°	13291	14840	9368	14840
40°	10614	13940	9177	13940
45°	9275	12896	8914	12896
50°	8719	11886	8741	11886
55°	8037	10860	8504	10860
60°	7363	9771	8147	9771
65°	6709	8795	7790	8795
70°	6090	7841	7270	7841
75°	5402	6775	6438	6775
80°	4649	5607	5188	5607
85°	4168	4168	3075	4168



TEST NUMBER: P331367-930

CATALOG NUMBER: S122DIP-S675D1080U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.1	1.9
10°-20°	299.8	5.4
20°-30°	435.1	7.9
30°-40°	459.2	8.3
40°-50°	406.6	7.3
50°-60°	324.5	5.9
60°-70°	220.5	4.0
70°-80°	113.1	2.0
80°-90°	31.7	0.6
90°-100°	71.1	1.3
100°-110°	220.9	4.0
110°-120°	377.5	6.8
120°-130°	496.5	9.0
130°-140°	557.2	10.1
140°-150°	546.4	9.9
150°-160°	458.3	8.3
160°-170°	304.0	5.5
170°-180°	106.2	1.9
0°-30°	838.1	15.2
0°-40°	1297.3	23.5
0°-60°	2028.3	36.7
0°-90°	2393.7	43.3
90°-120°	669.5	12.1
90°-150°	2269.5	41.0
90°-180°	3138.0	56.7
0°-180°	5531.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1083	1083	1083	1083	1083	
5°	1210	1086	962	1086	1210	121
15°	1487	1025	713	1025	1487	410
25°	1239	917	573	917	1239	560
35°	674	753	475	753	674	439
45°	406	565	390	565	406	319
55°	286	386	302	386	286	256
65°	176	230	204	230	176	175
75°	87	109	103	109	87	93
85°	22	22	17	22	22	25
90°	32	1	32	1	32	15
95°	59	49	59	49	59	65
105°	210	204	210	204	210	221
115°	379	379	379	379	379	374
125°	553	551	553	551	553	493
135°	722	713	722	713	722	555
145°	875	866	875	866	875	546
155°	997	990	997	990	997	459
165°	1078	1077	1078	1077	1078	304
175°	1117	1120	1117	1120	1117	106
180°	1122	1122	1122	1122	1122	



TEST NUMBER: P331367-930

CATALOG NUMBER: S122DIP-S675D1080U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1132.9	1133.2	1133.9	1128.5	1127.9	1127.9	1123.2	1119.2	1114.6	1108.2	1108.9
5°	1209.5	1214.1	1215.7	1210.7	1203.2	1202.4	1195.3	1183.7	1172.8	1164.1	1157.9
7.5°	1300.9	1302.7	1298.6	1292.0	1286.5	1276.5	1263.3	1250.4	1232.3	1215.8	1203.5
10°	1370.1	1372.6	1365.5	1356.0	1348.1	1336.4	1317.3	1297.7	1274.0	1251.1	1232.7
12.5°	1422.7	1428.9	1419.8	1418.5	1405.0	1389.0	1366.2	1356.3	1322.9	1291.0	1271.4
15°	1486.6	1486.2	1487.1	1479.2	1469.2	1466.6	1442.5	1416.3	1369.3	1350.5	1318.1
17.5°	1468.2	1474.5	1477.4	1477.3	1477.1	1475.5	1467.8	1451.2	1427.7	1397.3	1359.8
20°	1424.2	1432.6	1433.8	1443.4	1448.8	1455.9	1458.7	1454.2	1439.7	1414.2	1381.8
22.5°	1356.3	1358.6	1362.5	1377.4	1389.2	1406.9	1416.2	1431.6	1426.0	1413.6	1386.4
25°	1238.6	1234.4	1249.0	1256.5	1283.5	1311.8	1332.3	1354.7	1374.7	1386.7	1378.8
27.5°	1097.2	1091.0	1112.8	1132.7	1154.7	1185.4	1217.2	1254.7	1285.9	1324.9	1338.3
30°	978.0	981.8	1002.7	1023.9	1057.1	1100.4	1136.2	1177.5	1222.0	1265.7	1296.0
32.5°	849.5	864.0	877.1	909.6	938.9	987.2	1039.7	1091.2	1146.7	1196.4	1243.4
35°	674.3	690.9	709.2	733.0	774.1	822.0	873.2	942.6	1018.5	1086.3	1142.1
37.5°	567.5	564.8	575.4	592.5	625.9	664.5	723.4	792.1	881.3	961.0	1039.7
40°	503.6	501.9	509.4	525.2	550.7	578.9	630.6	690.9	773.7	871.1	964.7
42.5°	459.7	460.6	464.8	476.0	493.3	516.7	555.3	606.7	682.5	774.2	874.8
45°	406.2	409.1	413.7	419.1	429.1	448.3	469.9	506.5	566.5	643.0	742.1
47.5°	367.8	367.9	372.5	377.2	383.2	394.0	411.6	434.6	476.9	539.2	624.4
50°	347.1	344.2	347.6	351.2	357.5	365.0	376.7	398.3	426.6	477.0	548.1
52.5°	321.8	321.9	324.9	326.3	331.9	339.3	350.0	365.0	390.6	430.0	488.5
55°	285.5	287.6	289.3	291.7	296.8	302.1	310.5	320.5	340.5	370.0	413.3
57.5°	251.4	252.0	253.7	258.4	261.6	266.6	274.5	283.6	296.6	318.5	351.0
60°	228.0	228.0	231.4	233.5	237.7	242.6	248.9	257.6	269.3	287.1	313.4
62.5°	206.8	206.4	207.7	211.2	214.3	219.0	225.3	232.7	243.6	259.5	281.1
65°	175.6	174.8	177.3	178.1	181.5	186.1	191.0	198.9	207.7	219.3	238.5
67.5°	145.7	146.7	148.0	149.6	151.4	156.2	159.6	165.2	172.5	182.2	195.2
70°	129.0	129.0	129.0	130.3	132.7	135.3	138.6	143.2	150.3	158.6	170.2
72.5°	110.4	111.7	113.0	112.3	115.4	116.9	120.9	123.5	130.3	135.6	145.9
75°	86.6	86.6	86.6	88.6	89.9	91.2	93.7	96.1	99.5	106.2	111.5
77.5°	64.6	64.4	64.8	65.3	66.7	68.2	68.9	71.2	74.3	77.3	81.9
80°	50.0	50.8	51.2	52.0	52.0	52.8	53.2	56.2	58.3	60.3	63.3
82.5°	38.6	38.8	38.9	39.1	39.4	39.9	40.9	41.9	42.6	44.4	46.6
85°	22.5	22.1	22.1	22.9	22.5	22.5	23.3	24.1	24.1	24.5	25.8
87.5°	15.1	15.1	15.3	15.0	14.9	15.2	15.3	15.1	15.6	16.0	15.3
90°	32.2	32.0	31.8	31.6	31.4	31.5	31.9	32.3	32.7	33.2	28.5
92.5°	30.7	30.7	30.6	30.6	30.5	30.5	30.3	30.2	30.2	30.1	29.0
95°	58.7	59.1	59.6	60.0	60.4	60.6	60.6	60.6	60.6	60.6	60.2
97.5°	101.7	101.7	101.8	101.8	101.9	101.9	101.9	101.9	101.9	101.9	101.1
100°	129.7	130.0	130.2	130.4	130.6	130.7	130.7	130.7	130.7	130.7	130.0
102.5°	161.6	161.8	162.0	162.2	162.4	162.4	162.2	162.1	161.9	161.8	160.9
105°	210.3	210.3	210.3	210.3	210.3	210.0	209.6	209.2	208.8	208.3	207.9
107.5°	256.1	257.1	258.0	259.0	259.9	260.3	260.2	260.0	259.8	259.7	259.7
110°	291.7	292.3	292.9	293.6	294.2	294.6	294.6	294.6	294.6	294.6	294.6



TEST NUMBER: P331367-930

CATALOG NUMBER: S122DIP-S675D1080U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	325.8	326.3	326.7	327.2	327.7	328.2	328.6	329.1	329.6	330.1	330.3
115°	378.8	379.4	380.1	380.7	381.3	381.7	382.0	382.2	382.4	382.6	383.0
117.5°	429.4	430.0	430.6	431.3	431.9	432.5	433.0	433.5	434.0	434.5	435.7
120°	465.0	465.6	466.3	466.9	467.5	467.8	467.8	467.8	467.8	467.8	469.5
122.5°	499.9	500.3	500.8	501.2	501.7	502.1	502.7	503.2	503.7	504.2	505.4
125°	553.1	553.3	553.5	553.7	553.9	554.3	555.0	555.6	556.2	556.8	557.5
127.5°	601.5	602.3	602.9	603.6	604.2	605.0	605.7	606.5	607.2	608.0	608.8
130°	636.4	637.2	638.1	639.0	639.8	640.4	640.8	641.2	641.6	642.1	642.5
132.5°	669.8	670.4	671.1	671.8	672.5	673.3	674.2	675.1	676.0	676.9	676.9
135°	721.6	722.3	722.9	723.5	724.1	724.6	724.8	725.0	725.2	725.5	725.0
137.5°	768.6	769.5	770.3	771.1	772.0	772.5	772.7	772.8	773.0	773.1	772.6
140°	801.2	802.0	802.9	803.7	804.5	804.9	804.9	804.9	804.9	804.9	804.0
142.5°	830.7	831.6	832.4	833.2	834.1	834.5	834.3	834.1	834.0	833.8	833.1
145°	875.1	875.9	876.8	877.6	878.4	878.7	878.6	878.3	878.1	877.9	876.6
147.5°	914.7	915.4	916.2	917.0	917.9	918.0	917.5	917.1	916.6	916.2	915.3
150°	940.4	941.0	941.7	942.3	943.0	943.0	942.3	941.7	941.0	940.4	939.6
152.5°	964.7	965.5	966.3	967.0	967.8	967.8	967.0	966.3	965.5	964.7	963.7
155°	997.2	997.8	998.5	999.1	999.7	999.6	998.5	997.4	996.4	995.3	994.7
157.5°	1025.2	1026.3	1027.3	1028.3	1029.3	1029.1	1027.7	1026.2	1024.8	1023.4	1023.0
160°	1042.7	1043.5	1044.4	1045.2	1046.0	1045.9	1044.6	1043.3	1042.0	1040.8	1040.6
162.5°	1057.9	1058.8	1059.9	1060.9	1061.8	1061.7	1060.2	1058.8	1057.4	1056.0	1055.7
165°	1077.7	1078.8	1079.9	1080.9	1081.9	1081.7	1080.3	1078.8	1077.3	1075.9	1075.9
167.5°	1094.1	1095.1	1096.2	1097.3	1098.4	1098.2	1096.7	1095.3	1093.8	1092.3	1092.3
170°	1102.4	1103.6	1104.9	1106.1	1107.4	1107.3	1105.8	1104.3	1102.9	1101.4	1101.6
172.5°	1109.1	1110.4	1111.7	1113.0	1114.2	1114.1	1112.6	1111.2	1109.7	1108.2	1108.4
175°	1116.6	1117.9	1119.1	1120.4	1121.6	1121.5	1120.1	1118.6	1117.1	1115.6	1116.1
177.5°	1120.0	1121.0	1122.0	1123.0	1124.0	1124.0	1123.0	1122.0	1121.0	1120.0	1120.3
180°	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3



TEST NUMBER: P331367-930

CATALOG NUMBER: S122DIP-S675D1080U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1111.3	1108.6	1106.9	1100.9	1095.6	1090.3	1088.6	1089.2	1082.0	1075.0	1072.0
5°	1154.5	1146.2	1138.3	1127.1	1113.8	1099.2	1091.7	1085.8	1071.3	1055.5	1046.4
7.5°	1193.4	1181.5	1166.2	1145.0	1125.7	1102.8	1088.2	1075.3	1053.9	1031.7	1018.0
10°	1217.0	1200.7	1181.1	1155.4	1131.6	1103.8	1084.2	1064.6	1039.7	1013.0	996.4
12.5°	1237.3	1215.4	1196.1	1163.0	1135.0	1100.1	1076.8	1049.3	1023.0	991.4	975.1
15°	1285.6	1245.3	1208.6	1171.2	1136.6	1087.9	1062.2	1025.1	990.5	951.5	932.7
17.5°	1323.0	1277.7	1219.9	1172.3	1132.0	1078.2	1040.2	995.9	955.0	910.3	884.8
20°	1344.3	1292.2	1230.3	1173.7	1125.4	1063.8	1022.6	977.2	929.4	879.0	851.5
22.5°	1357.0	1302.3	1241.0	1168.7	1112.1	1052.1	1000.3	950.6	902.0	847.7	818.9
25°	1361.0	1311.0	1246.1	1164.5	1095.4	1027.6	965.2	916.9	858.2	807.4	765.4
27.5°	1341.2	1305.4	1242.9	1156.7	1076.2	996.9	927.3	872.6	810.7	755.5	713.3
30°	1316.9	1296.0	1235.3	1148.7	1060.9	975.6	898.9	837.0	775.3	719.6	676.3
32.5°	1279.2	1274.7	1221.3	1137.3	1044.6	948.6	869.4	806.7	738.4	683.6	642.4
35°	1205.3	1225.3	1191.6	1112.1	1013.8	910.2	824.5	752.9	682.2	629.7	591.0
37.5°	1106.3	1155.8	1147.0	1075.1	972.4	868.5	773.8	699.0	631.5	578.6	540.6
40°	1038.0	1101.2	1110.4	1046.8	943.1	836.2	735.8	661.4	595.6	547.3	509.0
42.5°	964.7	1038.7	1063.8	1012.8	911.1	802.2	701.9	624.7	559.6	512.7	478.7
45°	842.0	939.8	985.1	956.0	857.8	746.2	643.0	564.8	505.6	461.5	435.4
47.5°	727.2	834.1	895.0	884.8	798.4	687.9	586.0	510.9	453.3	418.1	394.6
50°	646.0	755.8	829.5	832.8	755.8	646.4	544.0	473.2	420.4	387.5	368.4
52.5°	575.4	680.2	760.6	778.2	708.2	603.1	506.4	435.9	389.4	359.1	342.0
55°	483.2	571.9	660.9	693.4	637.2	537.3	447.8	385.8	342.1	321.3	306.3
57.5°	401.7	475.6	557.9	593.8	559.1	473.6	389.7	335.9	300.4	282.2	270.7
60°	358.7	417.0	490.2	533.1	503.2	427.1	353.8	302.6	273.5	257.2	246.4
62.5°	318.8	370.4	432.4	471.6	455.3	383.4	317.8	272.6	247.4	232.2	224.5
65°	263.0	303.9	351.7	387.9	377.1	322.5	268.9	230.2	210.2	198.1	191.8
67.5°	216.6	246.1	279.2	311.0	302.2	263.6	220.5	190.4	175.5	165.1	161.3
70°	187.3	209.8	239.3	264.7	257.6	226.0	191.8	166.1	153.2	144.4	140.6
72.5°	159.3	177.8	200.3	221.1	216.3	190.0	161.6	142.1	132.2	124.1	121.0
75°	120.3	134.4	148.1	161.9	160.6	140.2	123.6	108.6	100.7	94.5	93.2
77.5°	88.8	96.7	106.1	114.2	111.9	100.3	87.2	78.7	72.8	68.6	68.0
80°	67.8	72.4	79.1	84.9	82.0	77.0	66.6	60.3	56.2	52.0	50.4
82.5°	49.2	53.8	57.8	60.9	58.7	54.1	47.6	43.4	40.8	38.1	37.3
85°	25.8	28.3	30.0	30.8	30.0	27.1	24.1	22.5	20.4	19.2	18.8
87.5°	14.8	13.9	12.9	12.9	11.3	10.8	9.0	7.5	7.7	7.8	7.7
90°	23.9	19.2	14.6	11.1	8.6	6.0	3.5	1.0	3.5	6.0	8.6
92.5°	28.0	26.8	25.8	24.3	22.4	20.5	18.7	16.9	18.7	20.5	22.4
95°	59.8	59.4	58.9	57.6	55.5	53.5	51.4	49.2	51.4	53.5	55.5
97.5°	100.3	99.5	98.7	97.3	95.6	93.7	91.8	90.0	91.8	93.7	95.6
100°	129.4	128.8	128.2	127.0	125.3	123.7	122.0	120.3	122.0	123.7	125.3
102.5°	160.1	159.4	158.6	157.5	156.1	154.8	153.4	152.1	153.4	154.8	156.1
105°	207.5	207.1	206.7	206.1	205.5	204.9	204.2	203.6	204.2	204.9	205.5
107.5°	259.7	259.7	259.7	259.2	258.3	257.4	256.4	255.5	256.4	257.4	258.3
110°	294.6	294.6	294.6	293.9	292.6	291.4	290.1	288.9	290.1	291.4	292.6





TEST NUMBER: P331367-930

CATALOG NUMBER: S122DIP-S675D1080U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	330.4	330.6	330.8	330.3	329.0	327.8	326.4	325.2	326.4	327.8	329.0
115°	383.4	383.8	384.3	383.8	382.6	381.3	380.1	378.8	380.1	381.3	382.6
117.5°	436.8	438.1	439.2	439.0	437.2	435.6	433.9	432.2	433.9	435.6	437.2
120°	471.2	472.9	474.6	474.6	472.9	471.2	469.5	467.8	469.5	471.2	472.9
122.5°	506.5	507.8	508.9	508.5	506.5	504.4	502.5	500.4	502.5	504.4	506.5
125°	558.2	558.7	559.4	558.7	556.8	555.0	553.1	551.1	553.1	555.0	556.8
127.5°	609.5	610.3	611.1	610.2	607.8	605.4	603.0	600.6	603.0	605.4	607.8
130°	642.9	643.4	643.8	642.6	639.8	637.2	634.4	631.7	634.4	637.2	639.8
132.5°	676.8	676.7	676.6	675.5	673.2	671.0	668.8	666.5	668.8	671.0	673.2
135°	724.6	724.1	723.7	722.4	720.1	717.8	715.4	713.1	715.4	717.8	720.1
137.5°	772.1	771.5	770.9	769.7	767.8	766.0	764.1	762.1	764.1	766.0	767.8
140°	802.9	801.8	800.8	799.3	797.4	795.5	793.6	791.7	793.6	795.5	797.4
142.5°	832.3	831.6	830.9	829.6	827.7	825.8	823.9	822.1	823.9	825.8	827.7
145°	875.4	874.1	872.9	871.5	870.0	868.5	867.1	865.6	867.1	868.5	870.0
147.5°	914.5	913.6	912.8	911.5	909.7	907.9	906.2	904.4	906.2	907.9	909.7
150°	938.7	937.9	937.0	936.0	934.7	933.4	932.2	930.9	932.2	933.4	934.7
152.5°	962.6	961.6	960.6	959.4	958.2	956.9	955.7	954.4	955.7	956.9	958.2
155°	994.1	993.4	992.8	992.2	991.6	990.9	990.3	989.7	990.3	990.9	991.6
157.5°	1022.6	1022.2	1021.8	1021.5	1021.0	1020.6	1020.2	1019.8	1020.2	1020.6	1021.0
160°	1040.4	1040.2	1039.9	1039.7	1039.2	1038.8	1038.4	1038.0	1038.4	1038.8	1039.2
162.5°	1055.5	1055.3	1055.1	1055.0	1054.8	1054.8	1054.7	1054.6	1054.7	1054.8	1054.8
165°	1075.9	1075.9	1075.9	1076.0	1076.1	1076.4	1076.6	1076.8	1076.6	1076.4	1076.1
167.5°	1092.4	1092.4	1092.5	1092.8	1093.5	1094.1	1094.7	1095.4	1094.7	1094.1	1093.5
170°	1101.8	1102.0	1102.3	1102.7	1103.3	1103.9	1104.6	1105.2	1104.6	1103.9	1103.3
172.5°	1108.6	1108.9	1109.1	1109.5	1110.1	1110.8	1111.4	1112.0	1111.4	1110.8	1110.1
175°	1116.5	1116.9	1117.3	1117.9	1118.4	1119.1	1119.7	1120.4	1119.7	1119.1	1118.4
177.5°	1120.6	1121.0	1121.3	1121.8	1122.3	1122.7	1123.2	1123.7	1123.2	1122.7	1122.3
180°	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3



TEST NUMBER: P331367-930

CATALOG NUMBER: S122DIP-S675D1080U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1068.6	1066.7	1059.6	1056.0	1049.9	1044.3	1040.6	1042.4	1043.7	1043.0	1042.0
5°	1038.0	1030.0	1018.0	1007.6	1000.1	986.3	980.6	977.6	975.2	972.2	969.3
7.5°	1001.5	989.0	971.8	956.9	942.9	925.9	916.2	910.3	904.3	897.7	891.9
10°	975.6	958.1	939.8	918.9	902.3	886.9	873.2	864.1	855.7	847.8	842.0
12.5°	948.3	928.1	905.5	877.0	858.7	836.7	834.5	818.4	805.4	800.5	793.7
15°	904.8	876.5	847.8	814.1	799.5	779.5	767.0	754.6	743.3	735.4	733.4
17.5°	855.4	818.8	790.3	766.1	742.2	721.7	710.2	700.2	691.0	680.4	679.0
20°	817.8	786.2	755.0	733.8	709.2	688.4	674.3	664.2	656.3	650.1	644.7
22.5°	782.2	747.5	719.0	695.8	671.6	654.8	643.6	634.0	627.4	620.4	615.4
25°	725.0	698.0	666.8	640.5	620.5	609.8	600.5	592.2	588.1	583.5	577.7
27.5°	675.0	644.9	615.7	595.4	577.9	568.3	561.7	556.1	552.2	549.5	546.3
30°	639.7	609.3	586.4	566.5	551.9	542.3	538.2	534.8	530.3	528.6	526.9
32.5°	605.8	578.4	558.8	541.4	527.6	521.3	517.5	514.5	510.9	509.2	505.9
35°	557.7	534.8	515.7	506.1	494.9	489.4	486.6	482.3	479.1	477.4	477.0
37.5°	512.5	492.6	480.0	467.7	463.0	459.7	455.7	452.8	451.8	451.6	451.2
40°	483.2	467.0	455.8	445.7	443.7	438.6	435.4	432.8	432.8	433.3	432.8
42.5°	456.6	442.0	432.1	423.5	421.0	418.0	414.7	414.5	415.2	416.6	415.2
45°	416.2	405.8	398.7	394.5	390.0	387.0	386.6	387.9	388.3	388.7	390.0
47.5°	379.0	372.2	365.7	361.2	359.1	358.7	358.2	360.4	362.3	363.1	365.0
50°	357.1	349.2	343.8	340.9	339.2	338.3	339.2	341.7	343.3	345.4	346.7
52.5°	332.5	326.9	323.1	320.9	320.2	320.7	320.9	323.8	326.4	327.1	327.8
55°	298.4	294.2	293.4	289.7	291.3	290.9	293.0	294.6	297.2	299.6	300.1
57.5°	264.5	261.1	258.9	259.2	259.7	261.5	263.3	266.2	268.9	271.5	271.7
60°	241.8	240.1	238.9	238.9	239.7	242.2	244.3	247.2	248.9	250.5	251.8
62.5°	221.2	219.5	218.3	218.9	221.1	222.6	225.0	226.6	228.2	229.9	230.5
65°	188.5	187.7	189.0	189.8	190.2	192.2	195.2	196.4	198.1	198.9	201.9
67.5°	158.5	158.7	158.5	159.6	162.1	162.6	165.3	168.2	168.5	170.2	172.0
70°	138.2	139.0	139.8	140.6	142.8	143.6	145.7	146.9	148.5	149.9	151.1
72.5°	119.5	119.7	120.5	120.3	122.1	123.9	125.7	126.9	128.6	130.2	131.4
75°	92.0	92.0	92.8	93.2	95.3	97.4	96.9	97.8	99.5	101.1	102.0
77.5°	67.2	66.3	67.2	67.6	68.2	70.0	70.4	71.5	73.4	72.8	73.8
80°	51.2	50.0	51.2	51.6	51.6	53.7	53.7	54.5	55.8	54.5	55.8
82.5°	36.5	36.0	36.9	36.9	37.6	37.7	38.4	38.6	39.8	39.2	39.8
85°	18.3	17.9	18.3	17.9	18.3	18.8	18.8	18.3	18.3	19.2	17.9
87.5°	7.9	8.2	8.8	9.8	10.4	10.9	10.5	10.4	10.4	9.6	9.6
90°	11.1	14.6	19.2	23.9	28.5	33.2	32.7	32.3	31.9	31.5	31.4
92.5°	24.3	25.8	26.8	28.0	29.0	30.1	30.2	30.2	30.3	30.5	30.5
95°	57.6	58.9	59.4	59.8	60.2	60.6	60.6	60.6	60.6	60.6	60.4
97.5°	97.3	98.7	99.5	100.3	101.1	101.9	101.9	101.9	101.9	101.9	101.9
100°	127.0	128.2	128.8	129.4	130.0	130.7	130.7	130.7	130.7	130.7	130.6
102.5°	157.5	158.6	159.4	160.1	160.9	161.8	161.9	162.1	162.2	162.4	162.4
105°	206.1	206.7	207.1	207.5	207.9	208.3	208.8	209.2	209.6	210.0	210.3
107.5°	259.2	259.7	259.7	259.7	259.7	259.7	259.8	260.0	260.2	260.3	259.9
110°	293.9	294.6	294.6	294.6	294.6	294.6	294.6	294.6	294.6	294.6	294.2



TEST NUMBER: P331367-930

CATALOG NUMBER: S122DIP-S675D1080U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	330.3	330.8	330.6	330.4	330.3	330.1	329.6	329.1	328.6	328.2	327.7
115°	383.8	384.3	383.8	383.4	383.0	382.6	382.4	382.2	382.0	381.7	381.3
117.5°	439.0	439.2	438.1	436.8	435.7	434.5	434.0	433.5	433.0	432.5	431.9
120°	474.6	474.6	472.9	471.2	469.5	467.8	467.8	467.8	467.8	467.8	467.5
122.5°	508.5	508.9	507.8	506.5	505.4	504.2	503.7	503.2	502.7	502.1	501.7
125°	558.7	559.4	558.7	558.2	557.5	556.8	556.2	555.6	555.0	554.3	553.9
127.5°	610.2	611.1	610.3	609.5	608.8	608.0	607.2	606.5	605.7	605.0	604.2
130°	642.6	643.8	643.4	642.9	642.5	642.1	641.6	641.2	640.8	640.4	639.8
132.5°	675.5	676.6	676.7	676.8	676.9	676.9	676.0	675.1	674.2	673.3	672.5
135°	722.4	723.7	724.1	724.6	725.0	725.5	725.2	725.0	724.8	724.6	724.1
137.5°	769.7	770.9	771.5	772.1	772.6	773.1	773.0	772.8	772.7	772.5	772.0
140°	799.3	800.8	801.8	802.9	804.0	804.9	804.9	804.9	804.9	804.9	804.5
142.5°	829.6	830.9	831.6	832.3	833.1	833.8	834.0	834.1	834.3	834.5	834.1
145°	871.5	872.9	874.1	875.4	876.6	877.9	878.1	878.3	878.6	878.7	878.4
147.5°	911.5	912.8	913.6	914.5	915.3	916.2	916.6	917.1	917.5	918.0	917.9
150°	936.0	937.0	937.9	938.7	939.6	940.4	941.0	941.7	942.3	943.0	943.0
152.5°	959.4	960.6	961.6	962.6	963.7	964.7	965.5	966.3	967.0	967.8	967.8
155°	992.2	992.8	993.4	994.1	994.7	995.3	996.4	997.4	998.5	999.6	999.7
157.5°	1021.5	1021.8	1022.2	1022.6	1023.0	1023.4	1024.8	1026.2	1027.7	1029.1	1029.3
160°	1039.7	1039.9	1040.2	1040.4	1040.6	1040.8	1042.0	1043.3	1044.6	1045.9	1046.0
162.5°	1055.0	1055.1	1055.3	1055.5	1055.7	1056.0	1057.4	1058.8	1060.2	1061.7	1061.8
165°	1076.0	1075.9	1075.9	1075.9	1075.9	1075.9	1077.3	1078.8	1080.3	1081.7	1081.9
167.5°	1092.8	1092.5	1092.4	1092.4	1092.3	1092.3	1093.8	1095.3	1096.7	1098.2	1098.4
170°	1102.7	1102.3	1102.0	1101.8	1101.6	1101.4	1102.9	1104.3	1105.8	1107.3	1107.4
172.5°	1109.5	1109.1	1108.9	1108.6	1108.4	1108.2	1109.7	1111.2	1112.6	1114.1	1114.2
175°	1117.9	1117.3	1116.9	1116.5	1116.1	1115.6	1117.1	1118.6	1120.1	1121.5	1121.6
177.5°	1121.8	1121.3	1121.0	1120.6	1120.3	1120.0	1121.0	1122.0	1123.0	1124.0	1124.0
180°	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3



TEST NUMBER: P331367-930

CATALOG NUMBER: S122DIP-S675D1080U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1038.7	1038.0	1038.0	1035.0	1038.0	1038.0	1038.7	1042.0	1043.0	1043.7	1042.4
5°	963.5	962.2	960.2	962.2	960.2	962.2	963.5	969.3	972.2	975.2	977.6
7.5°	889.2	884.2	883.5	878.5	883.5	884.2	889.2	891.9	897.7	904.3	910.3
10°	834.9	831.5	831.1	823.2	831.1	831.5	834.9	842.0	847.8	855.7	864.1
12.5°	793.6	785.6	787.2	782.6	787.2	785.6	793.6	793.7	800.5	805.4	818.4
15°	722.1	722.1	720.4	713.4	720.4	722.1	722.1	733.4	735.4	743.3	754.6
17.5°	670.7	669.9	665.9	667.9	665.9	669.9	670.7	679.0	680.4	691.0	700.2
20°	640.1	637.6	632.6	632.6	632.6	637.6	640.1	644.7	650.1	656.3	664.2
22.5°	611.1	611.0	605.7	607.3	605.7	611.0	611.1	615.4	620.4	627.4	634.0
25°	577.2	574.0	571.4	572.7	571.4	574.0	577.2	577.7	583.5	588.1	592.2
27.5°	545.1	543.3	543.2	539.7	543.2	543.3	545.1	546.3	549.5	552.2	556.1
30°	526.5	522.4	523.2	521.1	523.2	522.4	526.5	526.9	528.6	530.3	534.8
32.5°	505.2	503.7	502.9	501.1	502.9	503.7	505.2	505.9	509.2	510.9	514.5
35°	476.1	476.5	474.5	475.3	474.5	476.5	476.1	477.0	477.4	479.1	482.3
37.5°	450.8	452.1	451.1	451.3	451.1	452.1	450.8	451.2	451.6	451.8	452.8
40°	434.1	434.1	434.1	435.4	434.1	434.1	434.1	432.8	433.3	432.8	432.8
42.5°	418.1	417.4	416.8	416.7	416.8	417.4	418.1	415.2	416.6	415.2	414.5
45°	390.8	392.1	392.5	390.4	392.5	392.1	390.8	390.0	388.7	388.3	387.9
47.5°	366.1	366.2	366.1	367.9	366.1	366.2	366.1	365.0	363.1	362.3	360.4
50°	348.8	348.0	348.8	348.0	348.8	348.0	348.8	346.7	345.4	343.3	341.7
52.5°	330.4	330.6	330.1	330.0	330.1	330.6	330.4	327.8	327.1	326.4	323.8
55°	301.7	302.6	302.1	302.1	302.1	302.6	301.7	300.1	299.6	297.2	294.6
57.5°	272.1	272.8	273.4	271.5	273.4	272.8	272.1	271.7	271.5	268.9	266.2
60°	251.4	253.5	253.1	252.3	253.1	253.5	251.4	251.8	250.5	248.9	247.2
62.5°	232.4	233.2	233.1	232.9	233.1	233.2	232.4	230.5	229.9	228.2	226.6
65°	203.1	203.9	202.7	203.9	202.7	203.9	203.1	201.9	198.9	198.1	196.4
67.5°	171.5	171.8	172.8	173.3	172.8	171.8	171.5	172.0	170.2	168.5	168.2
70°	151.9	151.5	152.7	154.0	152.7	151.5	151.9	151.1	149.9	148.5	146.9
72.5°	131.3	132.2	131.8	132.6	131.8	132.2	131.3	131.4	130.2	128.6	126.9
75°	101.1	102.4	102.0	103.2	102.0	102.4	101.1	102.0	101.1	99.5	97.8
77.5°	73.1	73.2	73.1	73.8	73.1	73.2	73.1	73.8	72.8	73.4	71.5
80°	55.8	55.0	54.1	55.8	54.1	55.0	55.8	55.8	54.5	55.8	54.5
82.5°	38.8	39.3	38.5	38.5	38.5	39.3	38.8	39.8	39.2	39.8	38.6
85°	17.9	17.4	16.6	16.6	16.6	17.4	17.9	17.9	19.2	18.3	18.3
87.5°	9.6	9.4	9.4	9.1	9.4	9.4	9.6	9.6	9.6	10.4	10.4
90°	31.6	31.8	32.0	32.2	32.0	31.8	31.6	31.4	31.5	31.9	32.3
92.5°	30.6	30.6	30.7	30.7	30.7	30.6	30.6	30.5	30.5	30.3	30.2
95°	60.0	59.6	59.1	58.7	59.1	59.6	60.0	60.4	60.6	60.6	60.6
97.5°	101.8	101.8	101.7	101.7	101.7	101.8	101.8	101.9	101.9	101.9	101.9
100°	130.4	130.2	130.0	129.7	130.0	130.2	130.4	130.6	130.7	130.7	130.7
102.5°	162.2	162.0	161.8	161.6	161.8	162.0	162.2	162.4	162.4	162.2	162.1
105°	210.3	210.3	210.3	210.3	210.3	210.3	210.3	210.3	210.0	209.6	209.2
107.5°	259.0	258.0	257.1	256.1	257.1	258.0	259.0	259.9	260.3	260.2	260.0
110°	293.6	292.9	292.3	291.7	292.3	292.9	293.6	294.2	294.6	294.6	294.6



TEST NUMBER: P331367-930

CATALOG NUMBER: S122DIP-S675D1080U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	327.2	326.7	326.3	325.8	326.3	326.7	327.2	327.7	328.2	328.6	329.1
115°	380.7	380.1	379.4	378.8	379.4	380.1	380.7	381.3	381.7	382.0	382.2
117.5°	431.3	430.6	430.0	429.4	430.0	430.6	431.3	431.9	432.5	433.0	433.5
120°	466.9	466.3	465.6	465.0	465.6	466.3	466.9	467.5	467.8	467.8	467.8
122.5°	501.2	500.8	500.3	499.9	500.3	500.8	501.2	501.7	502.1	502.7	503.2
125°	553.7	553.5	553.3	553.1	553.3	553.5	553.7	553.9	554.3	555.0	555.6
127.5°	603.6	602.9	602.3	601.5	602.3	602.9	603.6	604.2	605.0	605.7	606.5
130°	639.0	638.1	637.2	636.4	637.2	638.1	639.0	639.8	640.4	640.8	641.2
132.5°	671.8	671.1	670.4	669.8	670.4	671.1	671.8	672.5	673.3	674.2	675.1
135°	723.5	722.9	722.3	721.6	722.3	722.9	723.5	724.1	724.6	724.8	725.0
137.5°	771.1	770.3	769.5	768.6	769.5	770.3	771.1	772.0	772.5	772.7	772.8
140°	803.7	802.9	802.0	801.2	802.0	802.9	803.7	804.5	804.9	804.9	804.9
142.5°	833.2	832.4	831.6	830.7	831.6	832.4	833.2	834.1	834.5	834.3	834.1
145°	877.6	876.8	875.9	875.1	875.9	876.8	877.6	878.4	878.7	878.6	878.3
147.5°	917.0	916.2	915.4	914.7	915.4	916.2	917.0	917.9	918.0	917.5	917.1
150°	942.3	941.7	941.0	940.4	941.0	941.7	942.3	943.0	943.0	942.3	941.7
152.5°	967.0	966.3	965.5	964.7	965.5	966.3	967.0	967.8	967.8	967.0	966.3
155°	999.1	998.5	997.8	997.2	997.8	998.5	999.1	999.7	999.6	998.5	997.4
157.5°	1028.3	1027.3	1026.3	1025.2	1026.3	1027.3	1028.3	1029.3	1029.1	1027.7	1026.2
160°	1045.2	1044.4	1043.5	1042.7	1043.5	1044.4	1045.2	1046.0	1045.9	1044.6	1043.3
162.5°	1060.9	1059.9	1058.8	1057.9	1058.8	1059.9	1060.9	1061.8	1061.7	1060.2	1058.8
165°	1080.9	1079.9	1078.8	1077.7	1078.8	1079.9	1080.9	1081.9	1081.7	1080.3	1078.8
167.5°	1097.3	1096.2	1095.1	1094.1	1095.1	1096.2	1097.3	1098.4	1098.2	1096.7	1095.3
170°	1106.1	1104.9	1103.6	1102.4	1103.6	1104.9	1106.1	1107.4	1107.3	1105.8	1104.3
172.5°	1113.0	1111.7	1110.4	1109.1	1110.4	1111.7	1113.0	1114.2	1114.1	1112.6	1111.2
175°	1120.4	1119.1	1117.9	1116.6	1117.9	1119.1	1120.4	1121.6	1121.5	1120.1	1118.6
177.5°	1123.0	1122.0	1121.0	1120.0	1121.0	1122.0	1123.0	1124.0	1124.0	1123.0	1122.0
180°	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3



TEST NUMBER: P331367-930

CATALOG NUMBER: S122DIP-S675D1080U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1040.6	1044.3	1049.9	1056.0	1059.6	1066.7	1068.6	1072.0	1075.0	1082.0	1089.2
5°	980.6	986.3	1000.1	1007.6	1018.0	1030.0	1038.0	1046.4	1055.5	1071.3	1085.8
7.5°	916.2	925.9	942.9	956.9	971.8	989.0	1001.5	1018.0	1031.7	1053.9	1075.3
10°	873.2	886.9	902.3	918.9	939.8	958.1	975.6	996.4	1013.0	1039.7	1064.6
12.5°	834.5	836.7	858.7	877.0	905.5	928.1	948.3	975.1	991.4	1023.0	1049.3
15°	767.0	779.5	799.5	814.1	847.8	876.5	904.8	932.7	951.5	990.5	1025.1
17.5°	710.2	721.7	742.2	766.1	790.3	818.8	855.4	884.8	910.3	955.0	995.9
20°	674.3	688.4	709.2	733.8	755.0	786.2	817.8	851.5	879.0	929.4	977.2
22.5°	643.6	654.8	671.6	695.8	719.0	747.5	782.2	818.9	847.7	902.0	950.6
25°	600.5	609.8	620.5	640.5	666.8	698.0	725.0	765.4	807.4	858.2	916.9
27.5°	561.7	568.3	577.9	595.4	615.7	644.9	675.0	713.3	755.5	810.7	872.6
30°	538.2	542.3	551.9	566.5	586.4	609.3	639.7	676.3	719.6	775.3	837.0
32.5°	517.5	521.3	527.6	541.4	558.8	578.4	605.8	642.4	683.6	738.4	806.7
35°	486.6	489.4	494.9	506.1	515.7	534.8	557.7	591.0	629.7	682.2	752.9
37.5°	455.7	459.7	463.0	467.7	480.0	492.6	512.5	540.6	578.6	631.5	699.0
40°	435.4	438.6	443.7	445.7	455.8	467.0	483.2	509.0	547.3	595.6	661.4
42.5°	414.7	418.0	421.0	423.5	432.1	442.0	456.6	478.7	512.7	559.6	624.7
45°	386.6	387.0	390.0	394.5	398.7	405.8	416.2	435.4	461.5	505.6	564.8
47.5°	358.2	358.7	359.1	361.2	365.7	372.2	379.0	394.6	418.1	453.3	510.9
50°	339.2	338.3	339.2	340.9	343.8	349.2	357.1	368.4	387.5	420.4	473.2
52.5°	320.9	320.7	320.2	320.9	323.1	326.9	332.5	342.0	359.1	389.4	435.9
55°	293.0	290.9	291.3	289.7	293.4	294.2	298.4	306.3	321.3	342.1	385.8
57.5°	263.3	261.5	259.7	259.2	258.9	261.1	264.5	270.7	282.2	300.4	335.9
60°	244.3	242.2	239.7	238.9	238.9	240.1	241.8	246.4	257.2	273.5	302.6
62.5°	225.0	222.6	221.1	218.9	218.3	219.5	221.2	224.5	232.2	247.4	272.6
65°	195.2	192.2	190.2	189.8	189.0	187.7	188.5	191.8	198.1	210.2	230.2
67.5°	165.3	162.6	162.1	159.6	158.5	158.7	158.5	161.3	165.1	175.5	190.4
70°	145.7	143.6	142.8	140.6	139.8	139.0	138.2	140.6	144.4	153.2	166.1
72.5°	125.7	123.9	122.1	120.3	120.5	119.7	119.5	121.0	124.1	132.2	142.1
75°	96.9	97.4	95.3	93.2	92.8	92.0	92.0	93.2	94.5	100.7	108.6
77.5°	70.4	70.0	68.2	67.6	67.2	66.3	67.2	68.0	68.6	72.8	78.7
80°	53.7	53.7	51.6	51.6	51.2	50.0	51.2	50.4	52.0	56.2	60.3
82.5°	38.4	37.7	37.6	36.9	36.9	36.0	36.5	37.3	38.1	40.8	43.4
85°	18.8	18.8	18.3	17.9	18.3	17.9	18.3	18.8	19.2	20.4	22.5
87.5°	10.5	10.9	10.4	9.8	8.8	8.2	7.9	7.7	7.8	7.7	7.5
90°	32.7	33.2	28.5	23.9	19.2	14.6	11.1	8.6	6.0	3.5	1.0
92.5°	30.2	30.1	29.0	28.0	26.8	25.8	24.3	22.4	20.5	18.7	16.9
95°	60.6	60.6	60.2	59.8	59.4	58.9	57.6	55.5	53.5	51.4	49.2
97.5°	101.9	101.9	101.1	100.3	99.5	98.7	97.3	95.6	93.7	91.8	90.0
100°	130.7	130.7	130.0	129.4	128.8	128.2	127.0	125.3	123.7	122.0	120.3
102.5°	161.9	161.8	160.9	160.1	159.4	158.6	157.5	156.1	154.8	153.4	152.1
105°	208.8	208.3	207.9	207.5	207.1	206.7	206.1	205.5	204.9	204.2	203.6
107.5°	259.8	259.7	259.7	259.7	259.7	259.7	259.2	258.3	257.4	256.4	255.5
110°	294.6	294.6	294.6	294.6	294.6	294.6	293.9	292.6	291.4	290.1	288.9



TEST NUMBER: P331367-930

CATALOG NUMBER: S122DIP-S675D1080U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	329.6	330.1	330.3	330.4	330.6	330.8	330.3	329.0	327.8	326.4	325.2
115°	382.4	382.6	383.0	383.4	383.8	384.3	383.8	382.6	381.3	380.1	378.8
117.5°	434.0	434.5	435.7	436.8	438.1	439.2	439.0	437.2	435.6	433.9	432.2
120°	467.8	467.8	469.5	471.2	472.9	474.6	474.6	472.9	471.2	469.5	467.8
122.5°	503.7	504.2	505.4	506.5	507.8	508.9	508.5	506.5	504.4	502.5	500.4
125°	556.2	556.8	557.5	558.2	558.7	559.4	558.7	556.8	555.0	553.1	551.1
127.5°	607.2	608.0	608.8	609.5	610.3	611.1	610.2	607.8	605.4	603.0	600.6
130°	641.6	642.1	642.5	642.9	643.4	643.8	642.6	639.8	637.2	634.4	631.7
132.5°	676.0	676.9	676.9	676.8	676.7	676.6	675.5	673.2	671.0	668.8	666.5
135°	725.2	725.5	725.0	724.6	724.1	723.7	722.4	720.1	717.8	715.4	713.1
137.5°	773.0	773.1	772.6	772.1	771.5	770.9	769.7	767.8	766.0	764.1	762.1
140°	804.9	804.9	804.0	802.9	801.8	800.8	799.3	797.4	795.5	793.6	791.7
142.5°	834.0	833.8	833.1	832.3	831.6	830.9	829.6	827.7	825.8	823.9	822.1
145°	878.1	877.9	876.6	875.4	874.1	872.9	871.5	870.0	868.5	867.1	865.6
147.5°	916.6	916.2	915.3	914.5	913.6	912.8	911.5	909.7	907.9	906.2	904.4
150°	941.0	940.4	939.6	938.7	937.9	937.0	936.0	934.7	933.4	932.2	930.9
152.5°	965.5	964.7	963.7	962.6	961.6	960.6	959.4	958.2	956.9	955.7	954.4
155°	996.4	995.3	994.7	994.1	993.4	992.8	992.2	991.6	990.9	990.3	989.7
157.5°	1024.8	1023.4	1023.0	1022.6	1022.2	1021.8	1021.5	1021.0	1020.6	1020.2	1019.8
160°	1042.0	1040.8	1040.6	1040.4	1040.2	1039.9	1039.7	1039.2	1038.8	1038.4	1038.0
162.5°	1057.4	1056.0	1055.7	1055.5	1055.3	1055.1	1055.0	1054.8	1054.8	1054.7	1054.6
165°	1077.3	1075.9	1075.9	1075.9	1075.9	1075.9	1076.0	1076.1	1076.4	1076.6	1076.8
167.5°	1093.8	1092.3	1092.3	1092.4	1092.4	1092.5	1092.8	1093.5	1094.1	1094.7	1095.4
170°	1102.9	1101.4	1101.6	1101.8	1102.0	1102.3	1102.7	1103.3	1103.9	1104.6	1105.2
172.5°	1109.7	1108.2	1108.4	1108.6	1108.9	1109.1	1109.5	1110.1	1110.8	1111.4	1112.0
175°	1117.1	1115.6	1116.1	1116.5	1116.9	1117.3	1117.9	1118.4	1119.1	1119.7	1120.4
177.5°	1121.0	1120.0	1120.3	1120.6	1121.0	1121.3	1121.8	1122.3	1122.7	1123.2	1123.7
180°	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3



TEST NUMBER: P331367-930

CATALOG NUMBER: S122DIP-S675D1080U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1088.6	1090.3	1095.6	1100.9	1106.9	1108.6	1111.3	1108.9	1108.2	1114.6	1119.2
5°	1091.7	1099.2	1113.8	1127.1	1138.3	1146.2	1154.5	1157.9	1164.1	1172.8	1183.7
7.5°	1088.2	1102.8	1125.7	1145.0	1166.2	1181.5	1193.4	1203.5	1215.8	1232.3	1250.4
10°	1084.2	1103.8	1131.6	1155.4	1181.1	1200.7	1217.0	1232.7	1251.1	1274.0	1297.7
12.5°	1076.8	1100.1	1135.0	1163.0	1196.1	1215.4	1237.3	1271.4	1291.0	1322.9	1356.3
15°	1062.2	1087.9	1136.6	1171.2	1208.6	1245.3	1285.6	1318.1	1350.5	1369.3	1416.3
17.5°	1040.2	1078.2	1132.0	1172.3	1219.9	1277.7	1323.0	1359.8	1397.3	1427.7	1451.2
20°	1022.6	1063.8	1125.4	1173.7	1230.3	1292.2	1344.3	1381.8	1414.2	1439.7	1454.2
22.5°	1000.3	1052.1	1112.1	1168.7	1241.0	1302.3	1357.0	1386.4	1413.6	1426.0	1431.6
25°	965.2	1027.6	1095.4	1164.5	1246.1	1311.0	1361.0	1378.8	1386.7	1374.7	1354.7
27.5°	927.3	996.9	1076.2	1156.7	1242.9	1305.4	1341.2	1338.3	1324.9	1285.9	1254.7
30°	898.9	975.6	1060.9	1148.7	1235.3	1296.0	1316.9	1296.0	1265.7	1222.0	1177.5
32.5°	869.4	948.6	1044.6	1137.3	1221.3	1274.7	1279.2	1243.4	1196.4	1146.7	1091.2
35°	824.5	910.2	1013.8	1112.1	1191.6	1225.3	1205.3	1142.1	1086.3	1018.5	942.6
37.5°	773.8	868.5	972.4	1075.1	1147.0	1155.8	1106.3	1039.7	961.0	881.3	792.1
40°	735.8	836.2	943.1	1046.8	1110.4	1101.2	1038.0	964.7	871.1	773.7	690.9
42.5°	701.9	802.2	911.1	1012.8	1063.8	1038.7	964.7	874.8	774.2	682.5	606.7
45°	643.0	746.2	857.8	956.0	985.1	939.8	842.0	742.1	643.0	566.5	506.5
47.5°	586.0	687.9	798.4	884.8	895.0	834.1	727.2	624.4	539.2	476.9	434.6
50°	544.0	646.4	755.8	832.8	829.5	755.8	646.0	548.1	477.0	426.6	398.3
52.5°	506.4	603.1	708.2	778.2	760.6	680.2	575.4	488.5	430.0	390.6	365.0
55°	447.8	537.3	637.2	693.4	660.9	571.9	483.2	413.3	370.0	340.5	320.5
57.5°	389.7	473.6	559.1	593.8	557.9	475.6	401.7	351.0	318.5	296.6	283.6
60°	353.8	427.1	503.2	533.1	490.2	417.0	358.7	313.4	287.1	269.3	257.6
62.5°	317.8	383.4	455.3	471.6	432.4	370.4	318.8	281.1	259.5	243.6	232.7
65°	268.9	322.5	377.1	387.9	351.7	303.9	263.0	238.5	219.3	207.7	198.9
67.5°	220.5	263.6	302.2	311.0	279.2	246.1	216.6	195.2	182.2	172.5	165.2
70°	191.8	226.0	257.6	264.7	239.3	209.8	187.3	170.2	158.6	150.3	143.2
72.5°	161.6	190.0	216.3	221.1	200.3	177.8	159.3	145.9	135.6	130.3	123.5
75°	123.6	140.2	160.6	161.9	148.1	134.4	120.3	111.5	106.2	99.5	96.1
77.5°	87.2	100.3	111.9	114.2	106.1	96.7	88.8	81.9	77.3	74.3	71.2
80°	66.6	77.0	82.0	84.9	79.1	72.4	67.8	63.3	60.3	58.3	56.2
82.5°	47.6	54.1	58.7	60.9	57.8	53.8	49.2	46.6	44.4	42.6	41.9
85°	24.1	27.1	30.0	30.8	30.0	28.3	25.8	25.8	24.5	24.1	24.1
87.5°	9.0	10.8	11.3	12.9	12.9	13.9	14.8	15.3	16.0	15.6	15.1
90°	3.5	6.0	8.6	11.1	14.6	19.2	23.9	28.5	33.2	32.7	32.3
92.5°	18.7	20.5	22.4	24.3	25.8	26.8	28.0	29.0	30.1	30.2	30.2
95°	51.4	53.5	55.5	57.6	58.9	59.4	59.8	60.2	60.6	60.6	60.6
97.5°	91.8	93.7	95.6	97.3	98.7	99.5	100.3	101.1	101.9	101.9	101.9
100°	122.0	123.7	125.3	127.0	128.2	128.8	129.4	130.0	130.7	130.7	130.7
102.5°	153.4	154.8	156.1	157.5	158.6	159.4	160.1	160.9	161.8	161.9	162.1
105°	204.2	204.9	205.5	206.1	206.7	207.1	207.5	207.9	208.3	208.8	209.2
107.5°	256.4	257.4	258.3	259.2	259.7	259.7	259.7	259.7	259.7	259.8	260.0
110°	290.1	291.4	292.6	293.9	294.6	294.6	294.6	294.6	294.6	294.6	294.6





TEST NUMBER: P331367-930

CATALOG NUMBER: S122DIP-S675D1080U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	326.4	327.8	329.0	330.3	330.8	330.6	330.4	330.3	330.1	329.6	329.1
115°	380.1	381.3	382.6	383.8	384.3	383.8	383.4	383.0	382.6	382.4	382.2
117.5°	433.9	435.6	437.2	439.0	439.2	438.1	436.8	435.7	434.5	434.0	433.5
120°	469.5	471.2	472.9	474.6	474.6	472.9	471.2	469.5	467.8	467.8	467.8
122.5°	502.5	504.4	506.5	508.5	508.9	507.8	506.5	505.4	504.2	503.7	503.2
125°	553.1	555.0	556.8	558.7	559.4	558.7	558.2	557.5	556.8	556.2	555.6
127.5°	603.0	605.4	607.8	610.2	611.1	610.3	609.5	608.8	608.0	607.2	606.5
130°	634.4	637.2	639.8	642.6	643.8	643.4	642.9	642.5	642.1	641.6	641.2
132.5°	668.8	671.0	673.2	675.5	676.6	676.7	676.8	676.9	676.9	676.0	675.1
135°	715.4	717.8	720.1	722.4	723.7	724.1	724.6	725.0	725.5	725.2	725.0
137.5°	764.1	766.0	767.8	769.7	770.9	771.5	772.1	772.6	773.1	773.0	772.8
140°	793.6	795.5	797.4	799.3	800.8	801.8	802.9	804.0	804.9	804.9	804.9
142.5°	823.9	825.8	827.7	829.6	830.9	831.6	832.3	833.1	833.8	834.0	834.1
145°	867.1	868.5	870.0	871.5	872.9	874.1	875.4	876.6	877.9	878.1	878.3
147.5°	906.2	907.9	909.7	911.5	912.8	913.6	914.5	915.3	916.2	916.6	917.1
150°	932.2	933.4	934.7	936.0	937.0	937.9	938.7	939.6	940.4	941.0	941.7
152.5°	955.7	956.9	958.2	959.4	960.6	961.6	962.6	963.7	964.7	965.5	966.3
155°	990.3	990.9	991.6	992.2	992.8	993.4	994.1	994.7	995.3	996.4	997.4
157.5°	1020.2	1020.6	1021.0	1021.5	1021.8	1022.2	1022.6	1023.0	1023.4	1024.8	1026.2
160°	1038.4	1038.8	1039.2	1039.7	1039.9	1040.2	1040.4	1040.6	1040.8	1042.0	1043.3
162.5°	1054.7	1054.8	1054.8	1055.0	1055.1	1055.3	1055.5	1055.7	1056.0	1057.4	1058.8
165°	1076.6	1076.4	1076.1	1076.0	1075.9	1075.9	1075.9	1075.9	1075.9	1077.3	1078.8
167.5°	1094.7	1094.1	1093.5	1092.8	1092.5	1092.4	1092.4	1092.3	1092.3	1093.8	1095.3
170°	1104.6	1103.9	1103.3	1102.7	1102.3	1102.0	1101.8	1101.6	1101.4	1102.9	1104.3
172.5°	1111.4	1110.8	1110.1	1109.5	1109.1	1108.9	1108.6	1108.4	1108.2	1109.7	1111.2
175°	1119.7	1119.1	1118.4	1117.9	1117.3	1116.9	1116.5	1116.1	1115.6	1117.1	1118.6
177.5°	1123.2	1122.7	1122.3	1121.8	1121.3	1121.0	1120.6	1120.3	1120.0	1121.0	1122.0
180°	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3



TEST NUMBER: P331367-930

CATALOG NUMBER: S122DIP-S675D1080U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1123.2	1127.9	1127.9	1128.5	1133.9	1133.2	1132.9
5°	1195.3	1202.4	1203.2	1210.7	1215.7	1214.1	1209.5
7.5°	1263.3	1276.5	1286.5	1292.0	1298.6	1302.7	1300.9
10°	1317.3	1336.4	1348.1	1356.0	1365.5	1372.6	1370.1
12.5°	1366.2	1389.0	1405.0	1418.5	1419.8	1428.9	1422.7
15°	1442.5	1466.6	1469.2	1479.2	1487.1	1486.2	1486.6
17.5°	1467.8	1475.5	1477.1	1477.3	1477.4	1474.5	1468.2
20°	1458.7	1455.9	1448.8	1443.4	1433.8	1432.6	1424.2
22.5°	1416.2	1406.9	1389.2	1377.4	1362.5	1358.6	1356.3
25°	1332.3	1311.8	1283.5	1256.5	1249.0	1234.4	1238.6
27.5°	1217.2	1185.4	1154.7	1132.7	1112.8	1091.0	1097.2
30°	1136.2	1100.4	1057.1	1023.9	1002.7	981.8	978.0
32.5°	1039.7	987.2	938.9	909.6	877.1	864.0	849.5
35°	873.2	822.0	774.1	733.0	709.2	690.9	674.3
37.5°	723.4	664.5	625.9	592.5	575.4	564.8	567.5
40°	630.6	578.9	550.7	525.2	509.4	501.9	503.6
42.5°	555.3	516.7	493.3	476.0	464.8	460.6	459.7
45°	469.9	448.3	429.1	419.1	413.7	409.1	406.2
47.5°	411.6	394.0	383.2	377.2	372.5	367.9	367.8
50°	376.7	365.0	357.5	351.2	347.6	344.2	347.1
52.5°	350.0	339.3	331.9	326.3	324.9	321.9	321.8
55°	310.5	302.1	296.8	291.7	289.3	287.6	285.5
57.5°	274.5	266.6	261.6	258.4	253.7	252.0	251.4
60°	248.9	242.6	237.7	233.5	231.4	228.0	228.0
62.5°	225.3	219.0	214.3	211.2	207.7	206.4	206.8
65°	191.0	186.1	181.5	178.1	177.3	174.8	175.6
67.5°	159.6	156.2	151.4	149.6	148.0	146.7	145.7
70°	138.6	135.3	132.7	130.3	129.0	129.0	129.0
72.5°	120.9	116.9	115.4	112.3	113.0	111.7	110.4
75°	93.7	91.2	89.9	88.6	86.6	86.6	86.6
77.5°	68.9	68.2	66.7	65.3	64.8	64.4	64.6
80°	53.2	52.8	52.0	52.0	51.2	50.8	50.0
82.5°	40.9	39.9	39.4	39.1	38.9	38.8	38.6
85°	23.3	22.5	22.5	22.9	22.1	22.1	22.5
87.5°	15.3	15.2	14.9	15.0	15.3	15.1	15.1
90°	31.9	31.5	31.4	31.6	31.8	32.0	32.2
92.5°	30.3	30.5	30.5	30.6	30.6	30.7	30.7
95°	60.6	60.6	60.4	60.0	59.6	59.1	58.7
97.5°	101.9	101.9	101.9	101.8	101.8	101.7	101.7
100°	130.7	130.7	130.6	130.4	130.2	130.0	129.7
102.5°	162.2	162.4	162.4	162.2	162.0	161.8	161.6
105°	209.6	210.0	210.3	210.3	210.3	210.3	210.3
107.5°	260.2	260.3	259.9	259.0	258.0	257.1	256.1
110°	294.6	294.6	294.2	293.6	292.9	292.3	291.7



TEST NUMBER: P331367-930

CATALOG NUMBER: S122DIP-S675D1080U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	328.6	328.2	327.7	327.2	326.7	326.3	325.8
115°	382.0	381.7	381.3	380.7	380.1	379.4	378.8
117.5°	433.0	432.5	431.9	431.3	430.6	430.0	429.4
120°	467.8	467.8	467.5	466.9	466.3	465.6	465.0
122.5°	502.7	502.1	501.7	501.2	500.8	500.3	499.9
125°	555.0	554.3	553.9	553.7	553.5	553.3	553.1
127.5°	605.7	605.0	604.2	603.6	602.9	602.3	601.5
130°	640.8	640.4	639.8	639.0	638.1	637.2	636.4
132.5°	674.2	673.3	672.5	671.8	671.1	670.4	669.8
135°	724.8	724.6	724.1	723.5	722.9	722.3	721.6
137.5°	772.7	772.5	772.0	771.1	770.3	769.5	768.6
140°	804.9	804.9	804.5	803.7	802.9	802.0	801.2
142.5°	834.3	834.5	834.1	833.2	832.4	831.6	830.7
145°	878.6	878.7	878.4	877.6	876.8	875.9	875.1
147.5°	917.5	918.0	917.9	917.0	916.2	915.4	914.7
150°	942.3	943.0	943.0	942.3	941.7	941.0	940.4
152.5°	967.0	967.8	967.8	967.0	966.3	965.5	964.7
155°	998.5	999.6	999.7	999.1	998.5	997.8	997.2
157.5°	1027.7	1029.1	1029.3	1028.3	1027.3	1026.3	1025.2
160°	1044.6	1045.9	1046.0	1045.2	1044.4	1043.5	1042.7
162.5°	1060.2	1061.7	1061.8	1060.9	1059.9	1058.8	1057.9
165°	1080.3	1081.7	1081.9	1080.9	1079.9	1078.8	1077.7
167.5°	1096.7	1098.2	1098.4	1097.3	1096.2	1095.1	1094.1
170°	1105.8	1107.3	1107.4	1106.1	1104.9	1103.6	1102.4
172.5°	1112.6	1114.1	1114.2	1113.0	1111.7	1110.4	1109.1
175°	1120.1	1121.5	1121.6	1120.4	1119.1	1117.9	1116.6
177.5°	1123.0	1124.0	1124.0	1123.0	1122.0	1121.0	1120.0
180°	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3

(END OF REPORT)