

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931277

Luminaire Tested: DFN2DS-TR2F0-040DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931277
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR2F0-040DS940-FLL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3532.3 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.36' x L: 2.04' x H: 0')
CIE Type: Direct

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931277

CATALOG NUMBER: DFN2DS-TR2F0-040DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931277

CATALOG NUMBER: DFN2DS-TR2F0-040DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3097	3097	3097
5°	3108	3064	3082
10°	3090	3033	3048
15°	3052	2993	2990
20°	2997	2934	2931
25°	2944	2862	2862
30°	2874	2795	2771
35°	2810	2716	2675
40°	2729	2635	2585
45°	2649	2556	2493
50°	2562	2474	2386
55°	2472	2378	2290
60°	2370	2263	2180
65°	2262	2149	2051
70°	2125	2011	1915
75°	1932	1852	1806
80°	1715	1662	1577
85°	1400	1333	1195

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2649 cd/sqm

TEST NUMBER: P931277

CATALOG NUMBER: DFN2DS-TR2F0-040DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.7	3.7
10°-20°	367.6	10.4
20°-30°	540.3	15.3
30°-40°	627.5	17.8
40°-50°	626.8	17.7
50°-60°	546.5	15.5
60°-70°	404.0	11.4
70°-80°	228.6	6.5
80°-90°	60.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1038.6	29.4
0°-40°	1666.2	47.2
0°-60°	2839.4	80.4
0°-90°	3532.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3532.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1388	1388	1388	1388	1388	
5°	1388	1383	1368	1379	1376	132
15°	1322	1314	1296	1302	1295	372
25°	1196	1186	1163	1165	1163	550
35°	1032	1019	997	989	982	644
45°	840	830	810	796	790	648
55°	636	627	612	595	589	568
65°	429	420	407	395	389	424
75°	224	222	215	207	210	239
85°	55	53	52	48	47	64
90°	0	0	0	0	0	

TEST NUMBER: P931277

CATALOG NUMBER: DFN2DS-TR2F0-040DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1396.4	1389.7	1375.0	1388.3	1385.8
5°	1388.3	1383.0	1368.3	1378.9	1376.4
7.5°	1378.9	1371.0	1356.3	1367.1	1364.4
10°	1364.4	1355.0	1339.1	1349.7	1345.7
12.5°	1344.2	1336.3	1320.3	1327.0	1324.3
15°	1321.6	1313.6	1296.3	1301.6	1295.0
17.5°	1293.6	1285.6	1268.2	1274.8	1268.2
20°	1262.8	1254.9	1236.2	1240.1	1235.0
22.5°	1232.2	1220.2	1202.8	1202.8	1200.1
25°	1196.1	1185.5	1162.8	1165.4	1162.8
27.5°	1156.0	1146.7	1129.5	1125.4	1118.8
30°	1116.1	1105.4	1085.4	1081.4	1076.0
32.5°	1073.3	1065.4	1044.0	1036.0	1030.5
35°	1032.0	1018.7	997.3	989.2	982.5
37.5°	985.2	973.2	951.8	942.5	935.8
40°	937.2	926.4	905.0	893.2	887.8
42.5°	890.5	879.7	858.5	845.0	837.1
45°	839.7	830.5	810.3	795.8	790.3
47.5°	790.3	780.9	759.6	744.9	737.0
50°	738.2	731.5	712.9	694.2	687.5
52.5°	687.5	678.2	660.9	646.2	636.8
55°	635.6	627.4	611.5	595.4	588.8
57.5°	583.4	576.8	559.3	543.3	538.0
60°	531.3	526.0	507.4	492.7	488.6
62.5°	480.6	471.2	458.0	444.6	439.2
65°	428.6	420.5	407.2	395.2	388.6
67.5°	375.2	368.4	356.5	347.2	341.8
70°	325.8	320.4	308.4	299.0	293.7
72.5°	275.1	269.7	263.1	253.7	249.7
75°	224.2	221.7	214.9	206.9	209.6
77.5°	178.8	173.5	170.8	166.8	162.9
80°	133.5	132.1	129.4	125.5	122.8
82.5°	90.8	90.8	89.6	84.1	84.1
85°	54.7	53.4	52.1	48.0	46.7
87.5°	24.1	21.4	18.7	14.7	13.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931277

CATALOG NUMBER: DFN2DS-TR2F0-040DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.21	16.82	15.57	17.13	17.45	14.77	16.38	15.13	16.69	17.00
	3H	16.96	18.41	17.34	18.74	19.10	16.47	17.92	16.85	18.25	18.61
	4H	17.61	18.98	18.00	19.32	19.70	17.11	18.48	17.51	18.83	19.20
	6H	18.08	19.34	18.49	19.71	20.10	17.57	18.84	17.98	19.21	19.60
	8H	18.22	19.43	18.64	19.82	20.22	17.72	18.93	18.14	19.31	19.71
	12H	18.31	19.47	18.74	19.85	20.28	17.80	18.96	18.23	19.34	19.77
4H	2H	15.77	17.14	16.17	17.49	17.86	15.42	16.79	15.82	17.13	17.51
	3H	17.75	18.89	18.16	19.29	19.69	17.34	18.48	17.75	18.88	19.28
	4H	18.52	19.56	18.95	19.97	20.41	18.10	19.13	18.53	19.55	19.98
	6H	19.12	20.02	19.57	20.46	20.92	18.69	19.59	19.14	20.03	20.49
	8H	19.31	20.15	19.77	20.60	21.06	18.87	19.72	19.33	20.16	20.62
	12H	19.44	20.20	19.92	20.68	21.14	18.99	19.75	19.47	20.22	20.69
8H	4H	18.80	19.64	19.26	20.08	20.55	18.42	19.27	18.88	19.71	20.18
	6H	19.51	20.21	20.00	20.70	21.18	19.13	19.83	19.62	20.32	20.79
	8H	19.77	20.40	20.28	20.91	21.39	19.38	20.01	19.89	20.51	21.00
	12H	19.97	20.53	20.48	21.02	21.58	19.55	20.11	20.06	20.60	21.16
12H	4H	18.82	19.58	19.30	20.06	20.53	18.46	19.22	18.94	19.69	20.16
	6H	19.55	20.19	20.06	20.69	21.18	19.19	19.82	19.70	20.32	20.81
	8H	19.87	20.43	20.38	20.92	21.48	19.49	20.05	20.00	20.54	21.10