

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931279

Luminaire Tested: DFN2DS-TR2F0-040DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931279
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR2F0-040DS950-FLL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3742.2 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.36' x L: 2.04' x H: 0')
CIE Type: Direct

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931279

CATALOG NUMBER: DFN2DS-TR2F0-040DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931279

CATALOG NUMBER: DFN2DS-TR2F0-040DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3281	3281	3281
5°	3293	3246	3265
10°	3274	3213	3229
15°	3233	3171	3168
20°	3175	3109	3106
25°	3119	3032	3032
30°	3045	2962	2936
35°	2977	2877	2834
40°	2891	2792	2739
45°	2806	2708	2641
50°	2714	2620	2527
55°	2618	2519	2426
60°	2511	2398	2309
65°	2397	2277	2172
70°	2251	2131	2029
75°	2048	1962	1914
80°	1818	1761	1671
85°	1482	1413	1267

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2806 cd/sqm

TEST NUMBER: P931279

CATALOG NUMBER: DFN2DS-TR2F0-040DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.4	3.7
10°-20°	389.5	10.4
20°-30°	572.4	15.3
30°-40°	664.8	17.8
40°-50°	664.0	17.7
50°-60°	579.0	15.5
60°-70°	428.0	11.4
70°-80°	242.2	6.5
80°-90°	63.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1100.3	29.4
0°-40°	1765.2	47.2
0°-60°	3008.1	80.4
0°-90°	3742.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3742.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1471	1471	1471	1471	1471	
5°	1471	1465	1450	1461	1458	140
15°	1400	1392	1373	1379	1372	394
25°	1267	1256	1232	1235	1232	583
35°	1093	1079	1056	1048	1041	683
45°	890	880	858	843	837	687
55°	673	665	648	631	624	602
65°	454	446	431	419	412	449
75°	238	235	228	219	222	254
85°	58	57	55	51	50	68
90°	0	0	0	0	0	

TEST NUMBER: P931279

CATALOG NUMBER: DFN2DS-TR2F0-040DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1470.8	1470.8	1470.8	1470.8	1470.8
2.5°	1479.4	1472.3	1456.7	1470.8	1468.2
5°	1470.8	1465.2	1449.6	1460.9	1458.2
7.5°	1460.9	1452.5	1436.9	1448.3	1445.5
10°	1445.5	1435.5	1418.6	1429.9	1425.6
12.5°	1424.1	1415.7	1398.8	1405.9	1402.9
15°	1400.1	1391.7	1373.3	1378.9	1372.0
17.5°	1370.4	1362.0	1343.6	1350.6	1343.6
20°	1337.8	1329.4	1309.7	1313.8	1308.4
22.5°	1305.4	1292.7	1274.2	1274.2	1271.4
25°	1267.2	1255.9	1231.9	1234.6	1231.9
27.5°	1224.7	1214.8	1196.6	1192.3	1185.3
30°	1182.4	1171.0	1149.9	1145.6	1140.0
32.5°	1137.1	1128.7	1106.0	1097.5	1091.8
35°	1093.3	1079.2	1056.5	1048.0	1040.9
37.5°	1043.8	1031.0	1008.3	998.5	991.4
40°	992.9	981.5	958.8	946.2	940.6
42.5°	943.4	932.0	909.5	895.2	886.8
45°	889.6	879.8	858.4	843.0	837.3
47.5°	837.3	827.3	804.8	789.2	780.8
50°	782.1	775.0	755.2	735.4	728.3
52.5°	728.3	718.5	700.2	684.6	674.6
55°	673.3	664.7	647.8	630.8	623.8
57.5°	618.0	611.0	592.5	575.6	569.9
60°	562.8	557.3	537.5	521.9	517.7
62.5°	509.2	499.2	485.2	471.0	465.3
65°	454.1	445.5	431.4	418.6	411.6
67.5°	397.5	390.3	377.7	367.8	362.1
70°	345.1	339.4	326.7	316.8	311.2
72.5°	291.4	285.7	278.7	268.8	264.5
75°	237.6	234.8	227.7	219.2	222.1
77.5°	189.5	183.8	181.0	176.7	172.6
80°	141.5	140.0	137.1	133.0	130.1
82.5°	96.2	96.2	94.9	89.1	89.1
85°	57.9	56.6	55.2	50.8	49.5
87.5°	25.5	22.7	19.8	15.6	14.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931279

CATALOG NUMBER: DFN2DS-TR2F0-040DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.41	17.02	15.77	17.33	17.65	14.97	16.58	15.33	16.89	17.20
	3H	17.16	18.61	17.54	18.94	19.30	16.67	18.12	17.05	18.45	18.81
	4H	17.81	19.18	18.20	19.52	19.90	17.31	18.68	17.71	19.03	19.40
	6H	18.28	19.54	18.69	19.91	20.30	17.77	19.04	18.19	19.41	19.80
	8H	18.42	19.63	18.84	20.02	20.42	17.92	19.13	18.34	19.52	19.91
	12H	18.51	19.67	18.94	20.05	20.48	18.00	19.16	18.43	19.54	19.97
4H	2H	15.97	17.34	16.37	17.69	18.06	15.62	16.99	16.02	17.33	17.71
	3H	17.95	19.09	18.36	19.49	19.89	17.54	18.69	17.95	19.08	19.48
	4H	18.72	19.76	19.15	20.17	20.61	18.30	19.33	18.73	19.75	20.18
	6H	19.32	20.22	19.77	20.66	21.12	18.89	19.79	19.34	20.23	20.69
	8H	19.51	20.35	19.97	20.80	21.26	19.07	19.92	19.53	20.36	20.82
	12H	19.64	20.40	20.12	20.88	21.35	19.19	19.95	19.67	20.42	20.89
8H	4H	19.00	19.84	19.46	20.28	20.75	18.62	19.47	19.08	19.91	20.38
	6H	19.71	20.41	20.20	20.90	21.38	19.33	20.03	19.82	20.52	21.00
	8H	19.97	20.60	20.48	21.11	21.59	19.58	20.21	20.09	20.71	21.20
	12H	20.17	20.73	20.68	21.22	21.78	19.76	20.31	20.26	20.80	21.37
12H	4H	19.02	19.78	19.50	20.26	20.73	18.66	19.42	19.14	19.89	20.36
	6H	19.75	20.39	20.26	20.89	21.38	19.39	20.02	19.90	20.53	21.01
	8H	20.07	20.63	20.58	21.12	21.68	19.69	20.25	20.20	20.74	21.30