

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331356-930

Luminaire Tested: **S122DIP-S675D725U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331356-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S675D725U930-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4511.3 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331356-930

CATALOG NUMBER: S122DIP-S675D725U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331356-930

CATALOG NUMBER: S122DIP-S675D725U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	93	89	86	90	86	83	80	72	70	68	60	58	57	49	48	46	41
2	89	81	75	70	82	75	70	65	64	60	56	53	50	47	43	41	39	34
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33	29
4	74	63	55	49	68	59	52	46	50	44	40	42	38	34	34	31	29	25
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25	22
6	63	51	42	37	58	47	40	35	40	34	30	34	29	26	28	25	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13976	13976	13976
5°	14029	13827	13908
10°	13946	13686	13754
15°	13772	13508	13494
20°	13527	13242	13228
25°	13286	12916	12916
30°	12972	12616	12506
35°	12682	12254	12073
40°	12313	11894	11666
45°	11953	11536	11250
50°	11560	11163	10766
55°	11153	10731	10331
60°	10698	10214	9836
65°	10208	9700	9253
70°	9588	9073	8644
75°	8721	8359	8153
80°	7736	7504	7122
85°	6336	6002	5391



TEST NUMBER: P331356-930

CATALOG NUMBER: S122DIP-S675D725U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.4	1.8
10°-20°	229.0	5.1
20°-30°	336.6	7.5
30°-40°	391.0	8.7
40°-50°	390.6	8.7
50°-60°	340.6	7.6
60°-70°	251.9	5.6
70°-80°	142.7	3.2
80°-90°	41.3	0.9
90°-100°	132.5	2.9
100°-110°	449.7	10.0
110°-120°	477.7	10.6
120°-130°	393.2	8.7
130°-140°	315.8	7.0
140°-150°	238.6	5.3
150°-160°	167.7	3.7
160°-170°	98.7	2.2
170°-180°	32.1	0.7
0°-30°	647.0	14.3
0°-40°	1038.1	23.0
0°-60°	1769.3	39.2
0°-90°	2205.2	48.9
90°-120°	1059.9	23.5
90°-150°	2007.6	44.5
90°-180°	2306.0	51.1
0°-180°	4511.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	866	862	853	859	858	82
15°	824	819	808	811	807	232
25°	746	739	725	726	725	343
35°	643	635	622	617	612	402
45°	524	517	505	496	493	404
55°	396	391	381	372	367	354
65°	267	262	254	247	242	264
75°	140	138	134	129	131	149
85°	34	33	32	30	29	39
90°	1	9	22	21	21	3
95°	22	55	250	94	73	24
105°	78	117	472	844	718	83
115°	137	173	395	815	945	136
125°	191	226	380	661	767	170
135°	224	268	375	555	635	173
145°	256	294	374	464	507	161
155°	291	314	363	410	426	134
165°	317	327	347	368	374	89
175°	331	331	334	338	337	31
180°	331	331	331	331	331	



TEST NUMBER: P331356-930

CATALOG NUMBER: S122DIP-S675D725U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6
2.5°	869.6	868.9	868.1	867.4	866.7	865.4	863.8	862.2	860.5	858.9	860.4
5°	865.6	864.9	864.1	863.4	862.7	861.3	859.2	857.2	855.2	853.1	854.6
7.5°	857.9	856.8	855.7	854.5	853.4	851.7	849.7	847.6	845.5	843.4	844.9
10°	850.6	849.3	848.0	846.7	845.5	843.7	841.5	839.3	837.0	834.8	836.3
12.5°	840.7	839.5	838.3	837.1	836.0	834.4	832.1	829.9	827.7	825.5	826.6
15°	823.9	822.9	821.7	820.7	819.5	817.7	815.4	812.9	810.6	808.1	808.9
17.5°	802.7	801.5	800.5	799.3	798.3	796.5	794.0	791.6	789.1	786.7	787.6
20°	787.3	786.3	785.1	784.0	782.9	781.1	778.4	775.9	773.3	770.7	771.3
22.5°	772.0	770.5	768.9	767.4	765.8	763.9	761.4	759.0	756.5	754.1	754.2
25°	745.8	744.3	742.8	741.3	739.8	737.5	734.3	731.2	728.1	725.0	725.3
27.5°	715.8	714.4	713.1	711.8	710.5	708.6	706.0	703.6	701.1	698.6	698.1
30°	695.8	694.3	692.8	691.4	689.9	687.8	685.0	682.2	679.5	676.7	676.1
32.5°	674.5	673.3	672.1	670.9	669.8	667.7	664.8	661.9	658.9	656.0	655.0
35°	643.4	641.6	639.7	637.8	635.9	633.6	630.6	627.6	624.7	621.7	620.6
37.5°	608.2	606.6	605.0	603.3	601.8	599.4	596.5	593.5	590.6	587.6	586.2
40°	584.2	582.8	581.3	579.8	578.4	576.2	573.2	570.2	567.3	564.3	562.6
42.5°	561.0	559.5	558.0	556.5	555.1	552.9	549.8	546.9	544.0	541.0	539.2
45°	523.5	522.2	520.9	519.7	518.4	516.3	513.6	510.8	508.0	505.2	503.2
47.5°	486.2	485.0	483.8	482.6	481.4	479.3	476.4	473.5	470.7	467.7	465.6
50°	460.2	459.3	458.4	457.5	456.6	454.8	452.2	449.6	447.0	444.4	441.9
52.5°	435.0	433.7	432.5	431.3	430.1	428.3	425.8	423.4	420.9	418.5	416.4
55°	396.2	395.1	394.0	392.8	391.8	390.0	387.8	385.6	383.4	381.2	379.0
57.5°	357.2	356.4	355.5	354.6	353.7	352.0	349.6	347.2	344.7	342.3	340.1
60°	331.3	330.5	329.8	329.1	328.3	326.6	324.1	321.5	318.9	316.3	314.2
62.5°	306.0	304.8	303.6	302.4	301.3	299.6	297.7	295.6	293.7	291.6	289.8
65°	267.2	266.0	265.0	263.8	262.7	261.2	259.4	257.6	255.7	253.9	252.2
67.5°	227.7	226.8	225.9	225.0	224.1	222.9	221.2	219.6	217.9	216.2	214.9
70°	203.1	202.4	201.6	200.9	200.2	198.9	197.2	195.6	194.0	192.2	190.9
72.5°	177.8	177.0	176.3	175.5	174.8	173.9	172.8	171.8	170.7	169.6	168.4
75°	139.8	139.4	139.1	138.7	138.4	137.7	136.8	135.8	134.9	134.0	132.9
77.5°	105.9	105.3	104.6	104.0	103.4	102.9	102.5	102.1	101.7	101.3	100.9
80°	83.2	83.1	82.8	82.7	82.5	82.2	81.9	81.4	81.1	80.7	80.1
82.5°	62.0	61.9	61.9	61.8	61.8	61.6	61.4	61.2	61.0	60.7	60.1
85°	34.2	33.9	33.8	33.6	33.3	33.2	33.0	32.9	32.6	32.4	31.9
87.5°	12.1	12.2	12.4	12.4	12.3	12.4	12.7	13.4	13.9	13.6	13.0
90°	0.7	2.5	5.1	6.4	7.7	9.5	12.7	17.2	21.0	21.7	21.0
92.5°	7.7	11.3	15.8	18.6	22.9	28.9	43.4	63.6	81.7	82.8	70.0
95°	22.3	24.9	31.2	36.9	47.1	62.5	91.8	147.2	221.2	249.8	218.6
97.5°	36.4	39.8	46.6	55.2	66.9	84.2	121.1	198.4	321.2	426.5	447.4
100°	49.1	51.0	56.7	66.9	79.7	97.5	131.3	209.0	346.7	503.4	595.3
102.5°	60.8	62.2	67.9	78.1	91.4	109.3	140.5	209.5	337.0	506.1	650.3
105°	77.8	80.3	84.8	94.3	108.4	126.2	156.1	212.9	318.0	472.2	641.8
107.5°	96.1	98.2	102.5	111.3	125.1	143.2	172.2	221.7	308.6	436.0	585.8
110°	108.4	110.9	114.7	123.0	136.4	154.9	182.9	228.8	306.6	418.7	550.7



TEST NUMBER: P331356-930

CATALOG NUMBER: S122DIP-S675D725U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	119.5	122.1	126.5	134.2	147.1	166.1	193.1	236.4	307.0	407.5	526.2
115°	137.1	140.2	144.1	151.6	164.4	181.6	209.0	247.9	309.7	395.2	495.9
117.5°	155.2	157.7	161.5	168.3	180.5	198.4	223.7	260.2	314.3	389.1	476.7
120°	166.3	168.9	172.7	178.5	191.2	209.0	233.9	268.3	317.4	385.6	466.5
122.5°	177.1	179.1	182.9	189.1	201.9	220.3	243.6	275.5	321.0	383.5	457.9
125°	191.2	193.1	196.9	204.6	217.4	235.1	258.1	286.8	326.3	379.8	445.5
127.5°	202.4	205.0	210.3	218.7	231.0	249.3	271.7	297.3	331.8	377.6	434.0
130°	209.0	211.6	217.9	226.9	239.6	257.5	279.8	304.0	335.9	376.7	426.4
132.5°	215.2	218.3	225.1	234.6	247.8	265.6	286.9	310.6	340.0	376.2	420.3
135°	224.4	226.9	234.6	244.1	258.8	276.6	297.0	319.3	344.8	375.4	411.7
137.5°	233.0	236.0	243.7	253.9	268.5	285.0	305.2	326.0	349.1	375.3	405.7
140°	239.6	242.1	249.8	260.0	274.0	290.7	309.7	329.5	351.1	374.7	402.2
142.5°	246.2	248.3	255.4	265.6	279.2	294.7	313.3	332.6	352.7	374.7	398.6
145°	256.2	258.8	265.1	274.7	287.4	301.4	318.7	336.5	354.3	373.5	393.9
147.5°	266.9	268.8	274.9	283.7	294.3	306.8	323.0	338.7	354.9	371.2	389.1
150°	274.0	276.0	281.0	289.3	298.9	310.4	325.1	339.7	354.3	369.7	384.9
152.5°	281.2	282.1	287.1	294.4	303.5	314.0	327.1	340.2	353.4	367.1	381.4
155°	291.2	291.9	295.7	302.7	309.7	319.3	330.1	341.0	351.8	362.6	374.7
157.5°	299.7	300.3	303.4	309.5	315.1	323.1	332.3	341.0	348.9	358.1	368.5
160°	305.2	305.9	308.4	313.6	318.7	325.6	333.3	341.0	347.3	355.0	363.9
162.5°	310.9	310.5	313.1	317.2	321.7	327.2	333.9	340.5	345.8	352.5	359.8
165°	317.4	316.7	318.0	321.9	325.1	328.9	334.6	339.1	342.9	347.3	353.1
167.5°	322.8	322.0	323.1	325.5	327.8	330.3	334.4	338.2	340.0	342.9	346.4
170°	326.3	325.1	325.6	327.6	328.9	330.8	333.9	337.1	338.4	340.3	342.9
172.5°	328.3	327.6	327.2	329.1	329.9	331.3	333.5	335.6	336.4	337.3	339.3
175°	330.8	330.1	329.5	330.8	330.8	331.4	332.6	333.9	333.3	333.9	334.6
177.5°	331.9	330.9	330.4	331.4	331.4	331.4	331.9	333.0	331.9	331.4	331.9
180°	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4



TEST NUMBER: P331356-930

CATALOG NUMBER: S122DIP-S675D725U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6
2.5°	861.9	863.4	864.9	865.4	865.1	864.9	864.5	864.3
5°	856.1	857.5	859.0	859.6	859.2	858.8	858.5	858.1
7.5°	846.4	847.9	849.4	849.9	849.5	849.1	848.7	848.3
10°	837.7	839.3	840.7	841.1	840.7	840.1	839.5	838.9
12.5°	827.5	828.6	829.6	829.9	829.5	829.2	828.8	828.3
15°	809.7	810.4	811.1	811.1	810.1	809.2	808.3	807.3
17.5°	788.4	789.2	790.1	790.1	789.2	788.3	787.4	786.5
20°	771.8	772.4	772.9	772.8	772.1	771.4	770.6	769.9
22.5°	754.3	754.4	754.5	754.3	753.9	753.4	753.0	752.6
25°	725.7	726.0	726.4	726.4	726.0	725.7	725.3	725.0
27.5°	697.5	697.0	696.4	695.7	694.8	693.9	693.0	692.1
30°	675.6	675.0	674.4	673.8	673.0	672.3	671.6	670.8
32.5°	654.0	653.1	652.0	651.2	650.4	649.7	648.9	648.2
35°	619.5	618.4	617.3	616.3	615.4	614.4	613.5	612.5
37.5°	584.9	583.5	582.1	581.0	580.1	579.2	578.4	577.5
40°	561.0	559.3	557.7	556.4	555.7	555.0	554.2	553.5
42.5°	537.4	535.6	533.8	532.3	531.2	530.3	529.2	528.2
45°	501.2	499.1	497.1	495.7	495.0	494.2	493.5	492.7
47.5°	463.5	461.3	459.2	457.5	456.5	455.4	454.4	453.3
50°	439.3	436.7	434.1	432.4	431.4	430.5	429.6	428.6
52.5°	414.2	412.1	409.9	408.2	407.0	405.8	404.6	403.3
55°	376.7	374.5	372.3	370.7	369.8	368.9	367.9	367.0
57.5°	337.9	335.7	333.5	332.1	331.3	330.7	330.0	329.2
60°	312.2	310.1	308.1	306.9	306.3	305.7	305.2	304.6
62.5°	287.9	286.0	284.1	282.8	282.1	281.4	280.7	280.0
65°	250.5	248.8	247.2	245.9	245.0	244.0	243.1	242.2
67.5°	213.6	212.4	211.1	210.0	209.3	208.6	207.8	207.1
70°	189.6	188.4	187.1	186.1	185.3	184.6	183.8	183.1
72.5°	167.1	165.8	164.4	163.5	162.9	162.3	161.8	161.1
75°	131.8	130.7	129.6	129.2	129.6	130.0	130.3	130.7
77.5°	100.3	99.7	99.1	98.7	98.1	97.6	97.1	96.5
80°	79.7	79.1	78.5	78.0	77.7	77.3	77.0	76.6
82.5°	59.4	58.6	58.0	57.6	57.5	57.4	57.3	57.2
85°	31.4	30.8	30.2	29.8	29.7	29.5	29.4	29.1
87.5°	12.5	11.8	11.7	11.5	11.3	11.2	11.0	10.8
90°	20.4	19.2	20.4	21.0	21.0	21.0	21.0	21.0
92.5°	55.6	47.7	42.3	38.4	37.8	35.8	36.4	35.3
95°	167.0	128.1	101.3	87.3	79.0	73.9	72.0	72.6
97.5°	389.6	318.8	249.8	203.8	173.3	157.7	148.4	143.0
100°	581.9	502.9	415.6	338.4	285.5	258.1	239.6	228.1
102.5°	707.8	690.0	626.1	544.4	486.9	440.1	417.0	401.5
105°	774.4	846.4	854.7	833.6	794.1	754.6	727.2	718.3
107.5°	726.4	834.9	901.2	932.1	937.0	934.8	929.4	917.5
110°	685.1	799.2	880.8	933.0	960.4	972.6	978.3	977.6



TEST NUMBER: P331356-930

CATALOG NUMBER: S122DIP-S675D725U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	647.4	756.8	844.1	904.0	942.1	962.4	973.2	976.6
115°	601.0	699.1	782.6	848.2	893.5	922.8	939.4	945.2
117.5°	566.1	652.2	728.0	789.5	835.7	866.7	884.1	888.9
120°	548.7	627.8	695.3	753.3	797.9	827.9	846.4	852.7
122.5°	535.0	607.4	671.3	723.7	763.8	793.2	809.7	815.0
125°	514.9	580.6	636.7	684.4	721.5	745.7	761.6	766.7
127.5°	495.2	554.6	607.5	651.6	683.9	706.5	720.3	724.4
130°	482.4	537.3	587.6	629.7	660.9	682.6	695.3	700.4
132.5°	470.2	521.0	567.2	606.7	637.5	659.1	670.8	675.4
135°	453.1	495.2	537.3	572.9	600.4	621.4	632.8	635.4
137.5°	439.5	474.7	508.1	539.2	564.2	582.3	592.3	596.1
140°	430.8	461.5	490.7	518.8	539.2	555.7	565.3	569.2
142.5°	423.7	449.7	474.9	498.4	517.8	532.8	541.4	542.1
145°	413.6	434.6	454.4	472.9	488.2	499.0	505.4	507.3
147.5°	405.9	422.4	437.8	451.3	464.0	472.6	477.0	478.1
150°	400.2	414.3	427.6	439.1	448.7	456.3	460.2	460.8
152.5°	394.6	407.6	419.0	428.9	436.4	443.0	445.9	446.0
155°	386.9	397.1	406.6	413.6	420.6	425.1	427.6	426.4
157.5°	377.8	386.4	394.4	399.8	404.8	408.5	409.7	409.7
160°	372.2	379.2	386.2	390.7	395.2	398.4	398.9	398.9
162.5°	366.6	372.6	378.5	382.0	386.5	388.7	389.3	388.7
165°	358.2	362.6	367.1	369.7	372.2	374.7	374.7	374.1
167.5°	350.2	353.6	356.6	359.0	360.1	361.5	361.3	360.6
170°	346.1	348.0	350.5	351.8	352.5	354.3	353.7	352.5
172.5°	341.4	342.9	345.0	345.7	346.3	347.2	346.6	345.8
175°	336.5	337.1	337.8	338.4	338.4	339.1	338.4	337.1
177.5°	333.0	333.0	333.5	333.5	333.5	333.5	333.0	331.9
180°	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4

(END OF REPORT)