

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331363-930

Luminaire Tested: **S122DIP-S675D925U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331363-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S675D925U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5220.4 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331363-930

CATALOG NUMBER: S122DIP-S675D925U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331363-930

CATALOG NUMBER: S122DIP-S675D925U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42																												
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	41	36																												
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	30																												
3	80	70	63	57	73	65	58	53	53	49	45	43	40	37	34	32	30	25																												
4	73	62	54	48	66	57	50	45	47	42	38	39	35	32	30	28	26	22																												
5	67	55	47	41	61	51	44	39	42	37	33	35	31	28	27	24	22	19																												
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17																												
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	22	20	17	15																												
8	53	41	33	28	48	37	31	26	32	26	22	26	22	19	21	18	16	13																												
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12																												
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13976	13976	13976
5°	14029	13827	13908
10°	13946	13686	13754
15°	13772	13508	13494
20°	13527	13242	13228
25°	13286	12916	12916
30°	12972	12616	12506
35°	12682	12254	12073
40°	12313	11894	11666
45°	11953	11536	11250
50°	11560	11163	10766
55°	11153	10731	10331
60°	10698	10214	9836
65°	10208	9700	9253
70°	9588	9073	8644
75°	8721	8359	8153
80°	7736	7504	7122
85°	6336	6002	5391



TEST NUMBER: P331363-930

CATALOG NUMBER: S122DIP-S675D925U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.4	1.6
10°-20°	229.0	4.4
20°-30°	336.6	6.4
30°-40°	391.0	7.5
40°-50°	390.6	7.5
50°-60°	340.6	6.5
60°-70°	251.9	4.8
70°-80°	142.7	2.7
80°-90°	40.9	0.8
90°-100°	34.3	0.7
100°-110°	125.9	2.4
110°-120°	336.5	6.4
120°-130°	555.4	10.6
130°-140°	590.7	11.3
140°-150°	549.0	10.5
150°-160°	441.4	8.5
160°-170°	284.5	5.4
170°-180°	97.9	1.9
0°-30°	647.0	12.4
0°-40°	1038.1	19.9
0°-60°	1769.3	33.9
0°-90°	2204.7	42.2
90°-120°	496.7	9.5
90°-150°	2191.9	42.0
90°-180°	3016.0	57.8
0°-180°	5220.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	866	862	853	859	858	82
15°	824	819	808	811	807	232
25°	746	739	725	726	725	343
35°	643	635	622	617	612	402
45°	524	517	505	496	493	404
55°	396	391	381	372	367	354
65°	267	262	254	247	242	264
75°	140	138	134	129	131	149
85°	34	33	32	30	29	39
90°	1	9	15	18	20	4
95°	48	26	29	33	32	59
105°	226	236	45	53	57	242
115°	428	441	459	131	61	421
125°	605	615	629	634	637	540
135°	749	761	768	775	774	578
145°	869	869	881	886	882	543
155°	957	951	959	963	958	441
165°	1008	1004	1006	1011	1006	285
175°	1031	1026	1028	1032	1025	98
180°	1029	1029	1029	1029	1029	



TEST NUMBER: P331363-930

CATALOG NUMBER: S122DIP-S675D925U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6
2.5°	869.6	868.9	868.1	867.4	866.7	865.4	863.8	862.2	860.5	858.9	860.4
5°	865.6	864.9	864.1	863.4	862.7	861.3	859.2	857.2	855.2	853.1	854.6
7.5°	857.9	856.8	855.7	854.5	853.4	851.7	849.7	847.6	845.5	843.4	844.9
10°	850.6	849.3	848.0	846.7	845.5	843.7	841.5	839.3	837.0	834.8	836.3
12.5°	840.7	839.5	838.3	837.1	836.0	834.4	832.1	829.9	827.7	825.5	826.6
15°	823.9	822.9	821.7	820.7	819.5	817.7	815.4	812.9	810.6	808.1	808.9
17.5°	802.7	801.5	800.5	799.3	798.3	796.5	794.0	791.6	789.1	786.7	787.6
20°	787.3	786.3	785.1	784.0	782.9	781.1	778.4	775.9	773.3	770.7	771.3
22.5°	772.0	770.5	768.9	767.4	765.8	763.9	761.4	759.0	756.5	754.1	754.2
25°	745.8	744.3	742.8	741.3	739.8	737.5	734.3	731.2	728.1	725.0	725.3
27.5°	715.8	714.4	713.1	711.8	710.5	708.6	706.0	703.6	701.1	698.6	698.1
30°	695.8	694.3	692.8	691.4	689.9	687.8	685.0	682.2	679.5	676.7	676.1
32.5°	674.5	673.3	672.1	670.9	669.8	667.7	664.8	661.9	658.9	656.0	655.0
35°	643.4	641.6	639.7	637.8	635.9	633.6	630.6	627.6	624.7	621.7	620.6
37.5°	608.2	606.6	605.0	603.3	601.8	599.4	596.5	593.5	590.6	587.6	586.2
40°	584.2	582.8	581.3	579.8	578.4	576.2	573.2	570.2	567.3	564.3	562.6
42.5°	561.0	559.5	558.0	556.5	555.1	552.9	549.8	546.9	544.0	541.0	539.2
45°	523.5	522.2	520.9	519.7	518.4	516.3	513.6	510.8	508.0	505.2	503.2
47.5°	486.2	485.0	483.8	482.6	481.4	479.3	476.4	473.5	470.7	467.7	465.6
50°	460.2	459.3	458.4	457.5	456.6	454.8	452.2	449.6	447.0	444.4	441.9
52.5°	435.0	433.7	432.5	431.3	430.1	428.3	425.8	423.4	420.9	418.5	416.4
55°	396.2	395.1	394.0	392.8	391.8	390.0	387.8	385.6	383.4	381.2	379.0
57.5°	357.2	356.4	355.5	354.6	353.7	352.0	349.6	347.2	344.7	342.3	340.1
60°	331.3	330.5	329.8	329.1	328.3	326.6	324.1	321.5	318.9	316.3	314.2
62.5°	306.0	304.8	303.6	302.4	301.3	299.6	297.7	295.6	293.7	291.6	289.8
65°	267.2	266.0	265.0	263.8	262.7	261.2	259.4	257.6	255.7	253.9	252.2
67.5°	227.7	226.8	225.9	225.0	224.1	222.9	221.2	219.6	217.9	216.2	214.9
70°	203.1	202.4	201.6	200.9	200.2	198.9	197.2	195.6	194.0	192.2	190.9
72.5°	177.8	177.0	176.3	175.5	174.8	173.9	172.8	171.8	170.7	169.6	168.4
75°	139.8	139.4	139.1	138.7	138.4	137.7	136.8	135.8	134.9	134.0	132.9
77.5°	105.9	105.3	104.6	104.0	103.4	102.9	102.5	102.1	101.7	101.3	100.9
80°	83.2	83.1	82.8	82.7	82.5	82.2	81.9	81.4	81.1	80.7	80.1
82.5°	62.0	61.9	61.9	61.8	61.8	61.6	61.4	61.2	61.0	60.7	60.1
85°	34.2	33.9	33.8	33.6	33.3	33.2	33.0	32.9	32.6	32.4	31.9
87.5°	12.1	12.2	12.2	12.3	12.4	12.4	12.4	12.4	12.3	12.3	12.0
90°	0.7	2.5	4.4	6.2	8.0	9.6	10.9	12.2	13.5	14.9	15.7
92.5°	15.0	14.8	14.7	14.5	14.3	14.6	15.3	16.0	16.6	17.3	17.7
95°	48.4	43.0	37.5	32.0	26.6	24.4	25.6	26.7	27.9	29.0	29.8
97.5°	96.0	80.6	65.3	49.9	34.5	28.1	30.8	33.5	36.2	38.9	39.5
100°	131.8	109.1	86.4	63.8	41.1	31.2	34.0	36.9	39.6	42.5	43.8
102.5°	171.1	166.3	161.5	156.7	151.9	137.8	114.2	90.7	67.2	43.6	45.3
105°	226.3	231.3	236.3	241.2	246.2	226.1	180.9	135.7	90.6	45.4	47.2
107.5°	289.3	293.3	297.3	301.3	305.4	280.3	226.1	171.9	117.7	63.6	61.7
110°	329.9	333.4	336.8	340.3	343.7	321.6	273.8	225.9	178.1	130.3	113.7



TEST NUMBER: P331363-930

CATALOG NUMBER: S122DIP-S675D925U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	367.9	371.0	374.1	377.2	380.3	375.9	364.1	352.3	340.5	328.6	268.3
115°	428.1	431.0	433.7	436.6	439.4	442.9	447.0	451.2	455.3	459.4	382.8
117.5°	481.9	485.0	488.2	491.4	494.5	497.5	500.3	503.2	506.1	508.8	490.3
120°	521.2	523.7	526.2	528.6	531.2	533.9	536.9	539.8	542.8	545.8	547.8
122.5°	554.6	557.2	559.8	562.4	565.0	567.9	571.2	574.5	577.7	581.0	582.1
125°	605.4	607.5	609.7	611.8	614.0	616.6	619.8	622.9	626.1	629.2	630.4
127.5°	651.3	653.8	656.2	658.5	660.9	663.2	665.6	668.0	670.3	672.7	674.3
130°	680.6	683.2	685.8	688.5	691.1	693.4	695.2	697.0	698.9	700.7	702.5
132.5°	710.4	712.6	714.9	717.1	719.3	721.4	723.3	725.0	726.8	728.6	730.3
135°	749.1	751.7	754.4	757.0	759.7	761.7	763.2	764.8	766.2	767.7	769.3
137.5°	788.2	790.1	792.0	793.8	795.7	797.4	799.1	800.8	802.5	804.2	805.8
140°	813.8	815.2	816.5	817.8	819.1	820.8	822.6	824.3	826.2	828.0	829.5
142.5°	835.3	836.5	837.7	838.9	840.1	841.7	843.8	845.9	848.0	850.0	851.4
145°	868.9	868.8	868.6	868.5	868.3	869.6	872.5	875.2	878.1	880.8	882.0
147.5°	898.3	897.6	897.1	896.4	895.8	896.8	899.6	902.5	905.2	908.0	908.8
150°	917.4	916.2	915.0	913.9	912.7	913.5	916.2	918.8	921.5	924.1	925.0
152.5°	933.4	932.1	930.8	929.6	928.3	928.9	931.4	933.9	936.5	939.0	940.0
155°	956.8	955.4	953.8	952.4	950.9	951.1	953.1	955.1	957.1	959.0	960.0
157.5°	975.1	973.9	972.7	971.3	970.1	970.2	971.6	973.0	974.4	975.8	976.9
160°	985.9	984.9	983.9	982.8	981.9	981.9	982.8	983.9	984.9	985.9	986.8
162.5°	995.4	994.4	993.4	992.4	991.4	991.3	992.2	993.0	993.9	994.8	995.9
165°	1008.2	1007.2	1006.2	1005.2	1004.2	1004.0	1004.4	1004.9	1005.5	1006.0	1007.1
167.5°	1017.7	1016.8	1015.8	1014.7	1013.7	1013.5	1014.0	1014.4	1014.9	1015.4	1016.5
170°	1023.1	1022.1	1021.1	1020.1	1019.1	1018.8	1019.1	1019.5	1019.8	1020.1	1021.2
172.5°	1026.6	1025.6	1024.7	1023.7	1022.7	1022.4	1022.7	1023.0	1023.4	1023.7	1024.8
175°	1031.3	1030.1	1029.0	1027.8	1026.6	1026.2	1026.5	1026.9	1027.2	1027.5	1028.7
177.5°	1032.0	1031.1	1030.2	1029.2	1028.3	1027.9	1028.1	1028.2	1028.3	1028.4	1029.4
180°	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1



TEST NUMBER: P331363-930

CATALOG NUMBER: S122DIP-S675D925U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6
2.5°	861.9	863.4	864.9	865.4	865.1	864.9	864.5	864.3
5°	856.1	857.5	859.0	859.6	859.2	858.8	858.5	858.1
7.5°	846.4	847.9	849.4	849.9	849.5	849.1	848.7	848.3
10°	837.7	839.3	840.7	841.1	840.7	840.1	839.5	838.9
12.5°	827.5	828.6	829.6	829.9	829.5	829.2	828.8	828.3
15°	809.7	810.4	811.1	811.1	810.1	809.2	808.3	807.3
17.5°	788.4	789.2	790.1	790.1	789.2	788.3	787.4	786.5
20°	771.8	772.4	772.9	772.8	772.1	771.4	770.6	769.9
22.5°	754.3	754.4	754.5	754.3	753.9	753.4	753.0	752.6
25°	725.7	726.0	726.4	726.4	726.0	725.7	725.3	725.0
27.5°	697.5	697.0	696.4	695.7	694.8	693.9	693.0	692.1
30°	675.6	675.0	674.4	673.8	673.0	672.3	671.6	670.8
32.5°	654.0	653.1	652.0	651.2	650.4	649.7	648.9	648.2
35°	619.5	618.4	617.3	616.3	615.4	614.4	613.5	612.5
37.5°	584.9	583.5	582.1	581.0	580.1	579.2	578.4	577.5
40°	561.0	559.3	557.7	556.4	555.7	555.0	554.2	553.5
42.5°	537.4	535.6	533.8	532.3	531.2	530.3	529.2	528.2
45°	501.2	499.1	497.1	495.7	495.0	494.2	493.5	492.7
47.5°	463.5	461.3	459.2	457.5	456.5	455.4	454.4	453.3
50°	439.3	436.7	434.1	432.4	431.4	430.5	429.6	428.6
52.5°	414.2	412.1	409.9	408.2	407.0	405.8	404.6	403.3
55°	376.7	374.5	372.3	370.7	369.8	368.9	367.9	367.0
57.5°	337.9	335.7	333.5	332.1	331.3	330.7	330.0	329.2
60°	312.2	310.1	308.1	306.9	306.3	305.7	305.2	304.6
62.5°	287.9	286.0	284.1	282.8	282.1	281.4	280.7	280.0
65°	250.5	248.8	247.2	245.9	245.0	244.0	243.1	242.2
67.5°	213.6	212.4	211.1	210.0	209.3	208.6	207.8	207.1
70°	189.6	188.4	187.1	186.1	185.3	184.6	183.8	183.1
72.5°	167.1	165.8	164.4	163.5	162.9	162.3	161.8	161.1
75°	131.8	130.7	129.6	129.2	129.6	130.0	130.3	130.7
77.5°	100.3	99.7	99.1	98.7	98.1	97.6	97.1	96.5
80°	79.7	79.1	78.5	78.0	77.7	77.3	77.0	76.6
82.5°	59.4	58.6	58.0	57.6	57.5	57.4	57.3	57.2
85°	31.4	30.8	30.2	29.8	29.7	29.5	29.4	29.1
87.5°	11.7	11.5	11.2	11.0	10.9	10.8	10.8	10.7
90°	16.6	17.4	18.2	18.8	19.1	19.4	19.8	20.1
92.5°	18.1	18.6	19.0	19.3	19.5	19.7	19.9	20.1
95°	30.7	31.6	32.4	32.7	32.5	32.4	32.2	32.0
97.5°	40.2	40.8	41.5	41.9	42.2	42.3	42.6	42.7
100°	45.1	46.4	47.8	48.6	48.9	49.2	49.6	49.9
102.5°	47.0	48.8	50.5	51.6	52.1	52.5	53.0	53.5
105°	49.1	50.9	52.7	54.0	54.6	55.3	55.9	56.6
107.5°	59.8	58.0	56.2	55.6	56.3	56.9	57.6	58.2
110°	97.2	80.6	64.1	56.2	56.8	57.5	58.1	58.9



TEST NUMBER: P331363-930

CATALOG NUMBER: S122DIP-S675D925U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	208.0	147.6	87.2	57.3	57.8	58.4	58.9	59.4
115°	306.2	229.6	153.0	108.7	96.8	84.9	73.0	61.1
117.5°	471.8	453.3	434.7	405.9	366.7	327.6	288.5	249.3
120°	549.8	551.8	553.8	543.6	521.2	498.9	476.5	454.2
122.5°	583.3	584.5	585.7	584.2	579.8	575.4	571.1	566.8
125°	631.5	632.7	633.8	634.6	635.1	635.6	636.2	636.7
127.5°	676.0	677.8	679.5	680.3	680.4	680.5	680.6	680.7
130°	704.3	706.1	707.9	708.8	708.7	708.4	708.3	708.1
132.5°	731.8	733.4	734.9	735.6	735.4	735.2	735.1	734.9
135°	771.0	772.7	774.3	774.9	774.6	774.3	774.0	773.6
137.5°	807.4	809.0	810.7	811.2	810.7	810.1	809.5	808.9
140°	831.0	832.5	834.0	834.3	833.5	832.7	831.8	831.0
142.5°	852.7	854.1	855.5	855.7	854.9	854.1	853.3	852.4
145°	883.2	884.4	885.5	885.7	884.8	884.0	883.2	882.4
147.5°	909.7	910.5	911.4	911.5	910.8	910.1	909.4	908.7
150°	926.0	927.1	928.1	928.1	927.3	926.4	925.6	924.8
152.5°	940.9	941.9	942.9	942.9	941.8	940.7	939.6	938.5
155°	961.1	962.1	963.0	962.9	961.6	960.2	958.9	957.6
157.5°	978.0	979.1	980.2	980.2	978.8	977.5	976.2	975.0
160°	987.8	988.9	989.9	989.8	988.6	987.4	986.3	985.1
162.5°	997.0	998.2	999.3	999.1	997.8	996.3	994.9	993.4
165°	1008.3	1009.4	1010.6	1010.6	1009.4	1008.3	1007.1	1006.0
167.5°	1017.7	1018.8	1020.0	1019.8	1018.3	1016.8	1015.4	1013.8
170°	1022.5	1023.6	1024.7	1024.6	1023.1	1021.6	1020.1	1018.6
172.5°	1026.0	1027.2	1028.3	1028.2	1026.6	1025.2	1023.7	1022.2
175°	1029.9	1031.0	1032.2	1031.9	1030.3	1028.7	1027.0	1025.3
177.5°	1030.3	1031.3	1032.2	1032.0	1030.9	1029.6	1028.4	1027.3
180°	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1

(END OF REPORT)