

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331417-930

Luminaire Tested: **S122DIP-S865D1080U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331417-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S865D1080U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6375.6 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331417-930

CATALOG NUMBER: S122DIP-S865D1080U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331417-930

CATALOG NUMBER: S122DIP-S865D1080U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	51	51	51	45					45			
1	97	92	88	85	88	85	81	78	71	68	66	57	56	54	45	44	43	38					38			
2	88	81	75	69	80	74	69	64	62	58	55	50	48	45	40	38	37	32					32			
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	35	33	31	27					27			
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23					23			
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20					20			
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18					18			
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16					16			
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14					14			
9	49	37	30	25	45	35	28	23	29	24	21	25	21	18	20	17	15	13					13			
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11					11			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18166	18166	18166
5°	18235	17973	18078
10°	18126	17790	17879
15°	17904	17560	17541
20°	17584	17213	17194
25°	17268	16787	16787
30°	16861	16397	16257
35°	16484	15928	15693
40°	16008	15460	15163
45°	15536	14995	14625
50°	15028	14511	13996
55°	14494	13948	13430
60°	13905	13275	12788
65°	13268	12607	12027
70°	12463	11797	11235
75°	11335	10861	10593
80°	10060	9754	9252
85°	8225	7818	7003



TEST NUMBER: P331417-930

CATALOG NUMBER: S122DIP-S865D1080U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.8	1.7
10°-20°	297.7	4.7
20°-30°	437.6	6.9
30°-40°	508.3	8.0
40°-50°	507.7	8.0
50°-60°	442.8	6.9
60°-70°	327.4	5.1
70°-80°	185.4	2.9
80°-90°	52.8	0.8
90°-100°	40.0	0.6
100°-110°	146.5	2.3
110°-120°	391.7	6.1
120°-130°	646.5	10.1
130°-140°	687.6	10.8
140°-150°	639.1	10.0
150°-160°	513.8	8.1
160°-170°	331.1	5.2
170°-180°	114.0	1.8
0°-30°	841.1	13.2
0°-40°	1349.3	21.2
0°-60°	2299.8	36.1
0°-90°	2865.4	44.9
90°-120°	578.1	9.1
90°-150°	2551.3	40.0
90°-180°	3510.0	55.1
0°-180°	6375.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1125	1125	1125	1125	1125	
5°	1125	1120	1109	1117	1115	107
15°	1071	1064	1050	1054	1049	301
25°	969	960	942	944	942	446
35°	836	825	808	802	796	522
45°	680	672	657	645	640	525
55°	515	508	496	483	477	460
65°	347	341	330	320	315	343
75°	182	179	174	168	170	194
85°	44	43	42	39	38	51
90°	1	10	17	22	23	5
95°	56	30	34	38	37	69
105°	264	275	53	62	66	282
115°	498	513	535	152	71	491
125°	705	716	732	738	741	628
135°	872	885	894	902	900	673
145°	1012	1011	1025	1031	1027	632
155°	1114	1107	1116	1121	1115	513
165°	1174	1169	1171	1176	1171	331
175°	1200	1195	1196	1201	1193	114
180°	1198	1198	1198	1198	1198	



TEST NUMBER: P331417-930

CATALOG NUMBER: S122DIP-S865D1080U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1130.3	1129.4	1128.4	1127.5	1126.5	1124.9	1122.8	1120.7	1118.6	1116.5	1118.4
5°	1125.1	1124.1	1123.2	1122.3	1121.3	1119.5	1116.9	1114.2	1111.6	1108.9	1110.8
7.5°	1115.2	1113.7	1112.2	1110.7	1109.2	1107.1	1104.4	1101.7	1099.0	1096.3	1098.3
10°	1105.6	1104.0	1102.3	1100.6	1098.9	1096.7	1093.7	1090.9	1088.0	1085.1	1087.0
12.5°	1092.7	1091.2	1089.7	1088.2	1086.7	1084.5	1081.7	1078.7	1075.9	1073.0	1074.3
15°	1071.1	1069.6	1068.1	1066.7	1065.3	1063.0	1059.9	1056.7	1053.6	1050.5	1051.4
17.5°	1043.3	1041.9	1040.5	1039.0	1037.5	1035.3	1032.1	1028.9	1025.7	1022.5	1023.7
20°	1023.4	1022.0	1020.6	1019.1	1017.7	1015.3	1011.9	1008.5	1005.2	1001.8	1002.5
22.5°	1003.6	1001.5	999.5	997.4	995.5	992.9	989.7	986.5	983.3	980.2	980.3
25°	969.3	967.4	965.5	963.6	961.6	958.6	954.6	950.5	946.4	942.3	942.8
27.5°	930.4	928.7	926.9	925.2	923.5	921.0	917.8	914.5	911.3	908.1	907.4
30°	904.4	902.5	900.6	898.7	896.7	894.0	890.4	886.8	883.1	879.5	878.8
32.5°	876.8	875.2	873.7	872.1	870.6	867.9	864.1	860.3	856.6	852.7	851.4
35°	836.3	833.9	831.4	829.1	826.6	823.5	819.7	815.9	812.0	808.1	806.7
37.5°	790.6	788.5	786.4	784.2	782.2	779.2	775.3	771.5	767.6	763.8	762.0
40°	759.5	757.6	755.6	753.7	751.8	748.9	745.0	741.2	737.4	733.5	731.3
42.5°	729.2	727.2	725.3	723.4	721.5	718.6	714.8	710.9	707.0	703.2	700.8
45°	680.4	678.8	677.1	675.5	673.8	671.1	667.5	663.9	660.3	656.7	654.0
47.5°	632.0	630.5	628.8	627.3	625.7	623.0	619.2	615.5	611.7	608.0	605.2
50°	598.3	597.0	595.9	594.7	593.5	591.2	587.8	584.4	581.1	577.7	574.4
52.5°	565.4	563.8	562.2	560.6	559.1	556.7	553.5	550.3	547.1	544.0	541.2
55°	514.9	513.6	512.1	510.6	509.2	507.0	504.2	501.2	498.4	495.5	492.6
57.5°	464.3	463.2	462.0	460.9	459.7	457.5	454.4	451.2	448.0	444.8	442.1
60°	430.6	429.6	428.7	427.7	426.7	424.6	421.2	417.8	414.5	411.1	408.5
62.5°	397.7	396.2	394.6	393.1	391.5	389.5	386.9	384.3	381.6	379.1	376.7
65°	347.3	345.8	344.4	342.9	341.5	339.6	337.2	334.8	332.4	330.0	327.8
67.5°	296.0	294.8	293.7	292.5	291.4	289.8	287.6	285.4	283.2	281.0	279.4
70°	264.0	263.0	262.0	261.1	260.2	258.5	256.4	254.2	252.1	249.9	248.3
72.5°	231.1	230.2	229.2	228.2	227.2	226.1	224.7	223.3	221.8	220.5	218.8
75°	181.7	181.2	180.8	180.3	179.9	179.0	177.8	176.6	175.4	174.1	172.8
77.5°	137.6	136.8	136.0	135.2	134.4	133.7	133.2	132.7	132.2	131.8	131.0
80°	108.2	107.9	107.7	107.5	107.2	106.9	106.4	105.9	105.4	104.9	104.2
82.5°	80.5	80.5	80.4	80.3	80.3	80.1	79.8	79.6	79.2	79.0	78.0
85°	44.4	44.1	43.9	43.6	43.4	43.1	42.9	42.6	42.4	42.2	41.5
87.5°	15.7	15.8	15.8	15.9	15.9	15.9	15.8	15.7	15.7	15.6	15.2
90°	0.9	3.0	5.1	7.3	9.4	11.2	12.7	14.3	15.8	17.4	18.3
92.5°	17.5	17.3	17.1	17.0	16.7	17.0	17.8	18.6	19.3	20.1	20.6
95°	56.3	50.0	43.6	37.3	30.9	28.4	29.8	31.1	32.4	33.8	34.7
97.5°	111.8	93.9	76.0	58.0	40.2	32.8	35.9	39.0	42.2	45.2	46.0
100°	153.4	127.0	100.6	74.3	47.9	36.3	39.5	42.9	46.1	49.4	51.0
102.5°	199.2	193.6	188.0	182.4	176.8	160.4	133.0	105.6	78.2	50.8	52.8
105°	263.5	269.3	275.0	280.8	286.6	263.2	210.6	158.0	105.4	52.8	55.0
107.5°	336.8	341.4	346.1	350.7	355.5	326.3	263.2	200.2	137.1	74.0	71.8
110°	383.9	388.0	392.1	396.1	400.1	374.3	318.6	263.0	207.3	151.6	132.4



TEST NUMBER: P331417-930

CATALOG NUMBER: S122DIP-S865D1080U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	428.4	431.9	435.5	439.0	442.6	437.6	423.8	410.1	396.3	382.5	312.3
115°	498.4	501.7	504.9	508.2	511.4	515.5	520.3	525.1	529.9	534.8	445.6
117.5°	560.9	564.6	568.3	571.9	575.6	579.0	582.4	585.7	589.0	592.3	570.7
120°	606.7	609.6	612.5	615.4	618.2	621.4	624.9	628.4	631.9	635.3	637.6
122.5°	645.6	648.6	651.6	654.7	657.7	661.1	664.9	668.6	672.5	676.2	677.6
125°	704.7	707.1	709.6	712.2	714.6	717.7	721.4	725.0	728.7	732.4	733.7
127.5°	758.2	761.0	763.8	766.5	769.3	772.0	774.8	777.5	780.2	783.0	785.0
130°	792.1	795.2	798.3	801.4	804.5	807.1	809.2	811.3	813.4	815.5	817.7
132.5°	826.8	829.5	832.1	834.7	837.3	839.7	841.8	843.9	846.0	848.2	849.9
135°	871.9	875.0	878.1	881.2	884.2	886.6	888.4	890.1	891.9	893.6	895.5
137.5°	917.5	919.7	921.8	924.0	926.1	928.1	930.2	932.1	934.1	936.0	937.9
140°	947.3	948.8	950.4	951.9	953.5	955.3	957.4	959.5	961.6	963.8	965.5
142.5°	972.2	973.6	975.0	976.4	977.8	979.7	982.1	984.6	987.0	989.4	991.0
145°	1011.5	1011.2	1011.1	1010.9	1010.6	1012.2	1015.5	1018.7	1022.1	1025.3	1026.6
147.5°	1045.6	1044.9	1044.2	1043.4	1042.7	1043.9	1047.2	1050.4	1053.6	1056.9	1057.9
150°	1067.8	1066.4	1065.1	1063.7	1062.4	1063.2	1066.3	1069.4	1072.5	1075.5	1076.8
152.5°	1086.5	1085.0	1083.5	1082.0	1080.5	1081.2	1084.1	1087.0	1090.0	1092.9	1094.1
155°	1113.7	1112.0	1110.3	1108.5	1106.8	1107.1	1109.4	1111.7	1114.0	1116.3	1117.4
157.5°	1135.1	1133.6	1132.1	1130.7	1129.2	1129.3	1130.9	1132.5	1134.1	1135.7	1137.0
160°	1147.5	1146.4	1145.2	1144.0	1142.9	1142.9	1144.0	1145.2	1146.4	1147.5	1148.7
162.5°	1158.6	1157.5	1156.3	1155.1	1154.0	1153.9	1154.9	1155.9	1156.9	1157.9	1159.2
165°	1173.5	1172.3	1171.2	1170.0	1168.9	1168.6	1169.1	1169.8	1170.4	1170.9	1172.2
167.5°	1184.6	1183.5	1182.3	1181.1	1180.0	1179.7	1180.2	1180.7	1181.3	1181.9	1183.2
170°	1190.8	1189.7	1188.5	1187.4	1186.3	1185.9	1186.3	1186.6	1187.0	1187.4	1188.7
172.5°	1195.0	1193.8	1192.7	1191.6	1190.4	1190.0	1190.4	1190.7	1191.2	1191.6	1192.9
175°	1200.4	1199.1	1197.7	1196.4	1195.0	1194.5	1194.9	1195.3	1195.6	1196.0	1197.4
177.5°	1201.3	1200.2	1199.1	1198.0	1196.9	1196.5	1196.6	1196.8	1196.9	1197.1	1198.2
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331417-930

CATALOG NUMBER: S122DIP-S865D1080U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1120.3	1122.3	1124.1	1124.9	1124.5	1124.1	1123.8	1123.4
5°	1112.7	1114.7	1116.6	1117.3	1116.9	1116.4	1115.9	1115.4
7.5°	1100.2	1102.1	1104.1	1104.7	1104.2	1103.7	1103.2	1102.6
10°	1088.9	1090.9	1092.8	1093.4	1092.7	1091.9	1091.2	1090.5
12.5°	1075.7	1077.0	1078.4	1078.8	1078.2	1077.7	1077.2	1076.7
15°	1052.4	1053.4	1054.3	1054.2	1053.0	1051.8	1050.6	1049.4
17.5°	1024.7	1025.9	1027.0	1027.0	1025.8	1024.7	1023.5	1022.4
20°	1003.2	1004.0	1004.7	1004.5	1003.6	1002.7	1001.7	1000.7
22.5°	980.5	980.6	980.7	980.6	979.9	979.3	978.8	978.2
25°	943.3	943.7	944.2	944.2	943.7	943.3	942.8	942.3
27.5°	906.7	906.0	905.2	904.3	903.1	902.0	900.8	899.7
30°	878.1	877.4	876.7	875.8	874.9	873.9	872.9	872.0
32.5°	850.1	848.8	847.5	846.4	845.5	844.5	843.5	842.5
35°	805.3	803.8	802.4	801.0	799.9	798.7	797.4	796.2
37.5°	760.3	758.5	756.7	755.2	754.1	752.9	751.8	750.6
40°	729.2	727.0	724.9	723.3	722.4	721.4	720.4	719.4
42.5°	698.5	696.1	693.8	691.9	690.6	689.3	687.9	686.6
45°	651.4	648.7	646.1	644.3	643.4	642.4	641.4	640.5
47.5°	602.4	599.7	596.9	594.8	593.4	592.0	590.6	589.2
50°	571.0	567.6	564.3	562.0	560.8	559.5	558.4	557.2
52.5°	538.3	535.6	532.8	530.6	529.0	527.4	525.9	524.2
55°	489.8	486.8	484.0	481.9	480.7	479.5	478.3	477.1
57.5°	439.2	436.3	433.5	431.6	430.7	429.8	428.9	428.0
60°	405.9	403.2	400.6	398.8	398.1	397.4	396.6	396.0
62.5°	374.1	371.7	369.2	367.6	366.6	365.7	364.8	363.9
65°	325.6	323.5	321.3	319.6	318.5	317.2	316.0	314.8
67.5°	277.7	276.0	274.3	273.0	272.1	271.1	270.1	269.1
70°	246.5	244.8	243.2	241.8	240.9	239.9	239.0	238.0
72.5°	217.1	215.4	213.8	212.5	211.7	211.0	210.2	209.5
75°	171.3	169.8	168.4	168.0	168.4	168.9	169.3	169.8
77.5°	130.4	129.6	128.9	128.2	127.5	126.9	126.2	125.5
80°	103.5	102.8	102.1	101.4	100.9	100.5	100.0	99.5
82.5°	77.1	76.2	75.3	74.8	74.7	74.6	74.5	74.4
85°	40.8	40.0	39.3	38.8	38.6	38.3	38.1	37.8
87.5°	14.8	14.4	14.0	13.8	13.7	13.5	13.5	13.4
90°	19.2	20.2	21.2	21.9	22.3	22.7	23.0	23.4
92.5°	21.1	21.6	22.1	22.5	22.7	22.9	23.2	23.4
95°	35.7	36.7	37.7	38.1	37.8	37.7	37.4	37.3
97.5°	46.8	47.5	48.3	48.8	49.1	49.3	49.5	49.7
100°	52.5	54.1	55.6	56.5	56.9	57.3	57.7	58.0
102.5°	54.8	56.8	58.8	60.1	60.6	61.1	61.7	62.2
105°	57.1	59.2	61.3	62.8	63.6	64.3	65.1	65.9
107.5°	69.7	67.5	65.4	64.7	65.5	66.2	67.0	67.8
110°	113.2	93.9	74.6	65.4	66.1	66.9	67.7	68.5



TEST NUMBER: P331417-930

CATALOG NUMBER: S122DIP-S865D1080U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	242.1	171.8	101.5	66.7	67.3	67.9	68.6	69.1
115°	356.4	267.3	178.1	126.5	112.7	98.8	85.0	71.1
117.5°	549.2	527.6	506.1	472.5	426.9	381.3	335.7	290.2
120°	639.9	642.2	644.6	632.7	606.7	580.7	554.6	528.7
122.5°	679.0	680.4	681.8	679.9	674.9	669.8	664.8	659.7
125°	735.1	736.4	737.8	738.7	739.3	739.9	740.5	741.0
127.5°	786.9	788.9	790.8	791.9	792.0	792.1	792.2	792.3
130°	819.8	821.9	824.0	825.0	824.8	824.6	824.4	824.3
132.5°	851.7	853.6	855.4	856.2	856.0	855.8	855.7	855.4
135°	897.4	899.4	901.2	902.0	901.6	901.2	900.9	900.5
137.5°	939.8	941.7	943.5	944.2	943.5	942.9	942.2	941.6
140°	967.3	969.0	970.7	971.1	970.1	969.1	968.2	967.3
142.5°	992.5	994.2	995.7	996.1	995.1	994.1	993.2	992.2
145°	1028.0	1029.3	1030.7	1030.9	1030.0	1029.0	1028.0	1027.0
147.5°	1058.8	1059.9	1060.9	1060.9	1060.1	1059.3	1058.5	1057.7
150°	1077.9	1079.0	1080.2	1080.3	1079.3	1078.4	1077.4	1076.4
152.5°	1095.2	1096.4	1097.6	1097.5	1096.2	1094.9	1093.6	1092.4
155°	1118.6	1119.8	1121.0	1120.7	1119.2	1117.7	1116.1	1114.6
157.5°	1138.3	1139.6	1140.9	1140.8	1139.4	1137.8	1136.4	1134.8
160°	1149.8	1151.0	1152.1	1152.0	1150.7	1149.3	1148.0	1146.6
162.5°	1160.5	1161.8	1163.2	1162.9	1161.3	1159.7	1158.0	1156.3
165°	1173.6	1174.9	1176.3	1176.3	1174.9	1173.6	1172.2	1170.9
167.5°	1184.5	1185.9	1187.2	1187.0	1185.3	1183.6	1181.9	1180.1
170°	1190.1	1191.4	1192.8	1192.5	1190.8	1189.1	1187.4	1185.6
172.5°	1194.3	1195.6	1196.9	1196.8	1195.0	1193.3	1191.6	1189.8
175°	1198.7	1200.1	1201.4	1201.2	1199.2	1197.3	1195.4	1193.4
177.5°	1199.2	1200.3	1201.4	1201.3	1199.9	1198.5	1197.1	1195.7
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8

(END OF REPORT)