

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331418-930

Luminaire Tested: **S122DIP-S865D1080U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331418-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S865D1080U930-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6004.9 lumens  
Efficiency: N/A  
Efficacy: 91.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331418-930

CATALOG NUMBER: S122DIP-S865D1080U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331418-930

CATALOG NUMBER: S122DIP-S865D1080U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48					48			
1	97	93	89	86	89	86	82	79	72	70	67	59	58	56	48	47	46					40				
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38					34				
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33					29				
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28					24				
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25					21				
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22					19				
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19					17				
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17					15				
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	16					13				
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14					12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18166	18166	18166
5°	18235	17973	18078
10°	18126	17790	17879
15°	17904	17560	17541
20°	17584	17213	17194
25°	17268	16787	16787
30°	16861	16397	16257
35°	16484	15928	15693
40°	16008	15460	15163
45°	15536	14995	14625
50°	15028	14511	13996
55°	14494	13948	13430
60°	13905	13275	12788
65°	13268	12607	12027
70°	12463	11797	11235
75°	11335	10861	10593
80°	10060	9754	9252
85°	8225	7818	7003



TEST NUMBER: P331418-930

CATALOG NUMBER: S122DIP-S865D1080U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.8	1.8
10°-20°	297.7	5.0
20°-30°	437.6	7.3
30°-40°	508.3	8.5
40°-50°	507.7	8.5
50°-60°	442.8	7.4
60°-70°	327.4	5.5
70°-80°	185.4	3.1
80°-90°	54.3	0.9
90°-100°	71.1	1.2
100°-110°	220.9	3.7
110°-120°	377.5	6.3
120°-130°	496.5	8.3
130°-140°	557.2	9.3
140°-150°	546.4	9.1
150°-160°	458.3	7.6
160°-170°	304.0	5.1
170°-180°	106.2	1.8
0°-30°	841.1	14.0
0°-40°	1349.3	22.5
0°-60°	2299.8	38.3
0°-90°	2867.0	47.7
90°-120°	669.5	11.1
90°-150°	2269.5	37.8
90°-180°	3138.0	52.3
0°-180°	6004.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1125	1125	1125	1125	1125	
5°	1125	1120	1109	1117	1115	107
15°	1071	1064	1050	1054	1049	301
25°	969	960	942	944	942	446
35°	836	825	808	802	796	522
45°	680	672	657	645	640	525
55°	515	508	496	483	477	460
65°	347	341	330	320	315	343
75°	182	179	174	168	170	194
85°	44	43	42	39	38	51
90°	1	13	33	31	32	5
95°	49	58	61	60	59	56
105°	204	206	208	210	210	215
115°	379	384	383	382	379	375
125°	551	559	557	554	553	492
135°	713	723	726	724	722	551
145°	866	872	878	879	875	541
155°	990	992	995	1000	997	455
165°	1077	1076	1076	1082	1078	304
175°	1120	1118	1116	1122	1117	106
180°	1122	1122	1122	1122	1122	



TEST NUMBER: P331418-930

CATALOG NUMBER: S122DIP-S865D1080U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1130.3	1129.4	1128.4	1127.5	1126.5	1124.9	1122.8	1120.7	1118.6	1116.5	1118.4
5°	1125.1	1124.1	1123.2	1122.3	1121.3	1119.5	1116.9	1114.2	1111.6	1108.9	1110.8
7.5°	1115.2	1113.7	1112.2	1110.7	1109.2	1107.1	1104.4	1101.7	1099.0	1096.3	1098.3
10°	1105.6	1104.0	1102.3	1100.6	1098.9	1096.7	1093.7	1090.9	1088.0	1085.1	1087.0
12.5°	1092.7	1091.2	1089.7	1088.2	1086.7	1084.5	1081.7	1078.7	1075.9	1073.0	1074.3
15°	1071.1	1069.6	1068.1	1066.7	1065.3	1063.0	1059.9	1056.7	1053.6	1050.5	1051.4
17.5°	1043.3	1041.9	1040.5	1039.0	1037.5	1035.3	1032.1	1028.9	1025.7	1022.5	1023.7
20°	1023.4	1022.0	1020.6	1019.1	1017.7	1015.3	1011.9	1008.5	1005.2	1001.8	1002.5
22.5°	1003.6	1001.5	999.5	997.4	995.5	992.9	989.7	986.5	983.3	980.2	980.3
25°	969.3	967.4	965.5	963.6	961.6	958.6	954.6	950.5	946.4	942.3	942.8
27.5°	930.4	928.7	926.9	925.2	923.5	921.0	917.8	914.5	911.3	908.1	907.4
30°	904.4	902.5	900.6	898.7	896.7	894.0	890.4	886.8	883.1	879.5	878.8
32.5°	876.8	875.2	873.7	872.1	870.6	867.9	864.1	860.3	856.6	852.7	851.4
35°	836.3	833.9	831.4	829.1	826.6	823.5	819.7	815.9	812.0	808.1	806.7
37.5°	790.6	788.5	786.4	784.2	782.2	779.2	775.3	771.5	767.6	763.8	762.0
40°	759.5	757.6	755.6	753.7	751.8	748.9	745.0	741.2	737.4	733.5	731.3
42.5°	729.2	727.2	725.3	723.4	721.5	718.6	714.8	710.9	707.0	703.2	700.8
45°	680.4	678.8	677.1	675.5	673.8	671.1	667.5	663.9	660.3	656.7	654.0
47.5°	632.0	630.5	628.8	627.3	625.7	623.0	619.2	615.5	611.7	608.0	605.2
50°	598.3	597.0	595.9	594.7	593.5	591.2	587.8	584.4	581.1	577.7	574.4
52.5°	565.4	563.8	562.2	560.6	559.1	556.7	553.5	550.3	547.1	544.0	541.2
55°	514.9	513.6	512.1	510.6	509.2	507.0	504.2	501.2	498.4	495.5	492.6
57.5°	464.3	463.2	462.0	460.9	459.7	457.5	454.4	451.2	448.0	444.8	442.1
60°	430.6	429.6	428.7	427.7	426.7	424.6	421.2	417.8	414.5	411.1	408.5
62.5°	397.7	396.2	394.6	393.1	391.5	389.5	386.9	384.3	381.6	379.1	376.7
65°	347.3	345.8	344.4	342.9	341.5	339.6	337.2	334.8	332.4	330.0	327.8
67.5°	296.0	294.8	293.7	292.5	291.4	289.8	287.6	285.4	283.2	281.0	279.4
70°	264.0	263.0	262.0	261.1	260.2	258.5	256.4	254.2	252.1	249.9	248.3
72.5°	231.1	230.2	229.2	228.2	227.2	226.1	224.7	223.3	221.8	220.5	218.8
75°	181.7	181.2	180.8	180.3	179.9	179.0	177.8	176.6	175.4	174.1	172.8
77.5°	137.6	136.8	136.0	135.2	134.4	133.7	133.2	132.7	132.2	131.8	131.0
80°	108.2	107.9	107.7	107.5	107.2	106.9	106.4	105.9	105.4	104.9	104.2
82.5°	80.5	80.5	80.4	80.3	80.3	80.1	79.8	79.6	79.2	79.0	78.0
85°	44.4	44.1	43.9	43.6	43.4	43.1	42.9	42.6	42.4	42.2	41.5
87.5°	15.7	15.9	16.0	16.1	16.2	16.6	17.1	17.7	18.2	18.8	18.1
90°	1.0	3.5	6.0	8.6	11.1	14.6	19.2	23.9	28.5	33.2	32.7
92.5°	16.9	18.7	20.5	22.4	24.3	25.8	26.8	28.0	29.0	30.1	30.2
95°	49.2	51.4	53.5	55.5	57.6	58.9	59.4	59.8	60.2	60.6	60.6
97.5°	90.0	91.8	93.7	95.6	97.3	98.7	99.5	100.3	101.1	101.9	101.9
100°	120.3	122.0	123.7	125.3	127.0	128.2	128.8	129.4	130.0	130.7	130.7
102.5°	152.1	153.4	154.8	156.1	157.5	158.6	159.4	160.1	160.9	161.8	161.9
105°	203.6	204.2	204.9	205.5	206.1	206.7	207.1	207.5	207.9	208.3	208.8
107.5°	255.5	256.4	257.4	258.3	259.2	259.7	259.7	259.7	259.7	259.7	259.8
110°	288.9	290.1	291.4	292.6	293.9	294.6	294.6	294.6	294.6	294.6	294.6



TEST NUMBER: P331418-930

CATALOG NUMBER: S122DIP-S865D1080U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	325.2	326.4	327.8	329.0	330.3	330.8	330.6	330.4	330.3	330.1	329.6
115°	378.8	380.1	381.3	382.6	383.8	384.3	383.8	383.4	383.0	382.6	382.4
117.5°	432.2	433.9	435.6	437.2	439.0	439.2	438.1	436.8	435.7	434.5	434.0
120°	467.8	469.5	471.2	472.9	474.6	474.6	472.9	471.2	469.5	467.8	467.8
122.5°	500.4	502.5	504.4	506.5	508.5	508.9	507.8	506.5	505.4	504.2	503.7
125°	551.1	553.1	555.0	556.8	558.7	559.4	558.7	558.2	557.5	556.8	556.2
127.5°	600.6	603.0	605.4	607.8	610.2	611.1	610.3	609.5	608.8	608.0	607.2
130°	631.7	634.4	637.2	639.8	642.6	643.8	643.4	642.9	642.5	642.1	641.6
132.5°	666.5	668.8	671.0	673.2	675.5	676.6	676.7	676.8	676.9	676.9	676.0
135°	713.1	715.4	717.8	720.1	722.4	723.7	724.1	724.6	725.0	725.5	725.2
137.5°	762.1	764.1	766.0	767.8	769.7	770.9	771.5	772.1	772.6	773.1	773.0
140°	791.7	793.6	795.5	797.4	799.3	800.8	801.8	802.9	804.0	804.9	804.9
142.5°	822.1	823.9	825.8	827.7	829.6	830.9	831.6	832.3	833.1	833.8	834.0
145°	865.6	867.1	868.5	870.0	871.5	872.9	874.1	875.4	876.6	877.9	878.1
147.5°	904.4	906.2	907.9	909.7	911.5	912.8	913.6	914.5	915.3	916.2	916.6
150°	930.9	932.2	933.4	934.7	936.0	937.0	937.9	938.7	939.6	940.4	941.0
152.5°	954.4	955.7	956.9	958.2	959.4	960.6	961.6	962.6	963.7	964.7	965.5
155°	989.7	990.3	990.9	991.6	992.2	992.8	993.4	994.1	994.7	995.3	996.4
157.5°	1019.8	1020.2	1020.6	1021.0	1021.5	1021.8	1022.2	1022.6	1023.0	1023.4	1024.8
160°	1038.0	1038.4	1038.8	1039.2	1039.7	1039.9	1040.2	1040.4	1040.6	1040.8	1042.0
162.5°	1054.6	1054.7	1054.8	1054.8	1055.0	1055.1	1055.3	1055.5	1055.7	1056.0	1057.4
165°	1076.8	1076.6	1076.4	1076.1	1076.0	1075.9	1075.9	1075.9	1075.9	1075.9	1077.3
167.5°	1095.4	1094.7	1094.1	1093.5	1092.8	1092.5	1092.4	1092.4	1092.3	1092.3	1093.8
170°	1105.2	1104.6	1103.9	1103.3	1102.7	1102.3	1102.0	1101.8	1101.6	1101.4	1102.9
172.5°	1112.0	1111.4	1110.8	1110.1	1109.5	1109.1	1108.9	1108.6	1108.4	1108.2	1109.7
175°	1120.4	1119.7	1119.1	1118.4	1117.9	1117.3	1116.9	1116.5	1116.1	1115.6	1117.1
177.5°	1123.7	1123.2	1122.7	1122.3	1121.8	1121.3	1121.0	1120.6	1120.3	1120.0	1121.0
180°	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3



TEST NUMBER: P331418-930

CATALOG NUMBER: S122DIP-S865D1080U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1120.3	1122.3	1124.1	1124.9	1124.5	1124.1	1123.8	1123.4
5°	1112.7	1114.7	1116.6	1117.3	1116.9	1116.4	1115.9	1115.4
7.5°	1100.2	1102.1	1104.1	1104.7	1104.2	1103.7	1103.2	1102.6
10°	1088.9	1090.9	1092.8	1093.4	1092.7	1091.9	1091.2	1090.5
12.5°	1075.7	1077.0	1078.4	1078.8	1078.2	1077.7	1077.2	1076.7
15°	1052.4	1053.4	1054.3	1054.2	1053.0	1051.8	1050.6	1049.4
17.5°	1024.7	1025.9	1027.0	1027.0	1025.8	1024.7	1023.5	1022.4
20°	1003.2	1004.0	1004.7	1004.5	1003.6	1002.7	1001.7	1000.7
22.5°	980.5	980.6	980.7	980.6	979.9	979.3	978.8	978.2
25°	943.3	943.7	944.2	944.2	943.7	943.3	942.8	942.3
27.5°	906.7	906.0	905.2	904.3	903.1	902.0	900.8	899.7
30°	878.1	877.4	876.7	875.8	874.9	873.9	872.9	872.0
32.5°	850.1	848.8	847.5	846.4	845.5	844.5	843.5	842.5
35°	805.3	803.8	802.4	801.0	799.9	798.7	797.4	796.2
37.5°	760.3	758.5	756.7	755.2	754.1	752.9	751.8	750.6
40°	729.2	727.0	724.9	723.3	722.4	721.4	720.4	719.4
42.5°	698.5	696.1	693.8	691.9	690.6	689.3	687.9	686.6
45°	651.4	648.7	646.1	644.3	643.4	642.4	641.4	640.5
47.5°	602.4	599.7	596.9	594.8	593.4	592.0	590.6	589.2
50°	571.0	567.6	564.3	562.0	560.8	559.5	558.4	557.2
52.5°	538.3	535.6	532.8	530.6	529.0	527.4	525.9	524.2
55°	489.8	486.8	484.0	481.9	480.7	479.5	478.3	477.1
57.5°	439.2	436.3	433.5	431.6	430.7	429.8	428.9	428.0
60°	405.9	403.2	400.6	398.8	398.1	397.4	396.6	396.0
62.5°	374.1	371.7	369.2	367.6	366.6	365.7	364.8	363.9
65°	325.6	323.5	321.3	319.6	318.5	317.2	316.0	314.8
67.5°	277.7	276.0	274.3	273.0	272.1	271.1	270.1	269.1
70°	246.5	244.8	243.2	241.8	240.9	239.9	239.0	238.0
72.5°	217.1	215.4	213.8	212.5	211.7	211.0	210.2	209.5
75°	171.3	169.8	168.4	168.0	168.4	168.9	169.3	169.8
77.5°	130.4	129.6	128.9	128.2	127.5	126.9	126.2	125.5
80°	103.5	102.8	102.1	101.4	100.9	100.5	100.0	99.5
82.5°	77.1	76.2	75.3	74.8	74.7	74.6	74.5	74.4
85°	40.8	40.0	39.3	38.8	38.6	38.3	38.1	37.8
87.5°	17.4	16.8	16.1	15.7	15.6	15.4	15.2	15.1
90°	32.3	31.9	31.5	31.4	31.6	31.8	32.0	32.2
92.5°	30.2	30.3	30.5	30.5	30.6	30.6	30.7	30.7
95°	60.6	60.6	60.6	60.4	60.0	59.6	59.1	58.7
97.5°	101.9	101.9	101.9	101.9	101.8	101.8	101.7	101.7
100°	130.7	130.7	130.7	130.6	130.4	130.2	130.0	129.7
102.5°	162.1	162.2	162.4	162.4	162.2	162.0	161.8	161.6
105°	209.2	209.6	210.0	210.3	210.3	210.3	210.3	210.3
107.5°	260.0	260.2	260.3	259.9	259.0	258.0	257.1	256.1
110°	294.6	294.6	294.6	294.2	293.6	292.9	292.3	291.7





TEST NUMBER: P331418-930

CATALOG NUMBER: S122DIP-S865D1080U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	329.1	328.6	328.2	327.7	327.2	326.7	326.3	325.8
115°	382.2	382.0	381.7	381.3	380.7	380.1	379.4	378.8
117.5°	433.5	433.0	432.5	431.9	431.3	430.6	430.0	429.4
120°	467.8	467.8	467.8	467.5	466.9	466.3	465.6	465.0
122.5°	503.2	502.7	502.1	501.7	501.2	500.8	500.3	499.9
125°	555.6	555.0	554.3	553.9	553.7	553.5	553.3	553.1
127.5°	606.5	605.7	605.0	604.2	603.6	602.9	602.3	601.5
130°	641.2	640.8	640.4	639.8	639.0	638.1	637.2	636.4
132.5°	675.1	674.2	673.3	672.5	671.8	671.1	670.4	669.8
135°	725.0	724.8	724.6	724.1	723.5	722.9	722.3	721.6
137.5°	772.8	772.7	772.5	772.0	771.1	770.3	769.5	768.6
140°	804.9	804.9	804.9	804.5	803.7	802.9	802.0	801.2
142.5°	834.1	834.3	834.5	834.1	833.2	832.4	831.6	830.7
145°	878.3	878.6	878.7	878.4	877.6	876.8	875.9	875.1
147.5°	917.1	917.5	918.0	917.9	917.0	916.2	915.4	914.7
150°	941.7	942.3	943.0	943.0	942.3	941.7	941.0	940.4
152.5°	966.3	967.0	967.8	967.8	967.0	966.3	965.5	964.7
155°	997.4	998.5	999.6	999.7	999.1	998.5	997.8	997.2
157.5°	1026.2	1027.7	1029.1	1029.3	1028.3	1027.3	1026.3	1025.2
160°	1043.3	1044.6	1045.9	1046.0	1045.2	1044.4	1043.5	1042.7
162.5°	1058.8	1060.2	1061.7	1061.8	1060.9	1059.9	1058.8	1057.9
165°	1078.8	1080.3	1081.7	1081.9	1080.9	1079.9	1078.8	1077.7
167.5°	1095.3	1096.7	1098.2	1098.4	1097.3	1096.2	1095.1	1094.1
170°	1104.3	1105.8	1107.3	1107.4	1106.1	1104.9	1103.6	1102.4
172.5°	1111.2	1112.6	1114.1	1114.2	1113.0	1111.7	1110.4	1109.1
175°	1118.6	1120.1	1121.5	1121.6	1120.4	1119.1	1117.9	1116.6
177.5°	1122.0	1123.0	1124.0	1124.0	1123.0	1122.0	1121.0	1120.0
180°	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3

(END OF REPORT)