

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331410-930

Luminaire Tested: **S122DIP-S865D925U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331410-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S865D925U930-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5810.6 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331410-930

CATALOG NUMBER: S122DIP-S865D925U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331410-930

CATALOG NUMBER: S122DIP-S865D925U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49
1	98	93	89	86	90	86	83	80	73	70	68	60	59	57	49	48	47	42
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	39	35
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	34	29
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	31	29	25
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19
7	58	46	38	32	53	43	35	30	36	31	27	31	26	23	26	22	20	17
8	54	42	34	28	50	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16	14
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18166	18166	18166
5°	18235	17973	18078
10°	18126	17790	17879
15°	17904	17560	17541
20°	17584	17213	17194
25°	17268	16787	16787
30°	16861	16397	16257
35°	16484	15928	15693
40°	16008	15460	15163
45°	15536	14995	14625
50°	15028	14511	13996
55°	14494	13948	13430
60°	13905	13275	12788
65°	13268	12607	12027
70°	12463	11797	11235
75°	11335	10861	10593
80°	10060	9754	9252
85°	8225	7818	7003



TEST NUMBER: P331410-930

CATALOG NUMBER: S122DIP-S865D925U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.8	1.8
10°-20°	297.7	5.1
20°-30°	437.6	7.5
30°-40°	508.3	8.7
40°-50°	507.7	8.7
50°-60°	442.8	7.6
60°-70°	327.4	5.6
70°-80°	185.4	3.2
80°-90°	53.7	0.9
90°-100°	169.2	2.9
100°-110°	574.1	9.9
110°-120°	609.9	10.5
120°-130°	502.1	8.6
130°-140°	403.2	6.9
140°-150°	304.7	5.2
150°-160°	214.1	3.7
160°-170°	126.0	2.2
170°-180°	41.0	0.7
0°-30°	841.1	14.5
0°-40°	1349.3	23.2
0°-60°	2299.8	39.6
0°-90°	2866.3	49.3
90°-120°	1353.2	23.3
90°-150°	2563.1	44.1
90°-180°	2944.0	50.7
0°-180°	5810.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1125	1125	1125	1125	1125	
5°	1125	1120	1109	1117	1115	107
15°	1071	1064	1050	1054	1049	301
25°	969	960	942	944	942	446
35°	836	825	808	802	796	522
45°	680	672	657	645	640	525
55°	515	508	496	483	477	460
65°	347	341	330	320	315	343
75°	182	179	174	168	170	194
85°	44	43	42	39	38	51
90°	1	11	28	26	27	4
95°	28	70	319	120	93	30
105°	99	150	603	1078	917	106
115°	175	221	504	1041	1207	173
125°	244	289	485	843	979	217
135°	286	342	479	709	811	221
145°	327	376	477	592	648	205
155°	372	402	463	524	544	171
165°	405	417	443	470	478	114
175°	422	423	426	432	430	40
180°	423	423	423	423	423	



TEST NUMBER: P331410-930

CATALOG NUMBER: S122DIP-S865D925U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1130.3	1129.4	1128.4	1127.5	1126.5	1124.9	1122.8	1120.7	1118.6	1116.5	1118.4
5°	1125.1	1124.1	1123.2	1122.3	1121.3	1119.5	1116.9	1114.2	1111.6	1108.9	1110.8
7.5°	1115.2	1113.7	1112.2	1110.7	1109.2	1107.1	1104.4	1101.7	1099.0	1096.3	1098.3
10°	1105.6	1104.0	1102.3	1100.6	1098.9	1096.7	1093.7	1090.9	1088.0	1085.1	1087.0
12.5°	1092.7	1091.2	1089.7	1088.2	1086.7	1084.5	1081.7	1078.7	1075.9	1073.0	1074.3
15°	1071.1	1069.6	1068.1	1066.7	1065.3	1063.0	1059.9	1056.7	1053.6	1050.5	1051.4
17.5°	1043.3	1041.9	1040.5	1039.0	1037.5	1035.3	1032.1	1028.9	1025.7	1022.5	1023.7
20°	1023.4	1022.0	1020.6	1019.1	1017.7	1015.3	1011.9	1008.5	1005.2	1001.8	1002.5
22.5°	1003.6	1001.5	999.5	997.4	995.5	992.9	989.7	986.5	983.3	980.2	980.3
25°	969.3	967.4	965.5	963.6	961.6	958.6	954.6	950.5	946.4	942.3	942.8
27.5°	930.4	928.7	926.9	925.2	923.5	921.0	917.8	914.5	911.3	908.1	907.4
30°	904.4	902.5	900.6	898.7	896.7	894.0	890.4	886.8	883.1	879.5	878.8
32.5°	876.8	875.2	873.7	872.1	870.6	867.9	864.1	860.3	856.6	852.7	851.4
35°	836.3	833.9	831.4	829.1	826.6	823.5	819.7	815.9	812.0	808.1	806.7
37.5°	790.6	788.5	786.4	784.2	782.2	779.2	775.3	771.5	767.6	763.8	762.0
40°	759.5	757.6	755.6	753.7	751.8	748.9	745.0	741.2	737.4	733.5	731.3
42.5°	729.2	727.2	725.3	723.4	721.5	718.6	714.8	710.9	707.0	703.2	700.8
45°	680.4	678.8	677.1	675.5	673.8	671.1	667.5	663.9	660.3	656.7	654.0
47.5°	632.0	630.5	628.8	627.3	625.7	623.0	619.2	615.5	611.7	608.0	605.2
50°	598.3	597.0	595.9	594.7	593.5	591.2	587.8	584.4	581.1	577.7	574.4
52.5°	565.4	563.8	562.2	560.6	559.1	556.7	553.5	550.3	547.1	544.0	541.2
55°	514.9	513.6	512.1	510.6	509.2	507.0	504.2	501.2	498.4	495.5	492.6
57.5°	464.3	463.2	462.0	460.9	459.7	457.5	454.4	451.2	448.0	444.8	442.1
60°	430.6	429.6	428.7	427.7	426.7	424.6	421.2	417.8	414.5	411.1	408.5
62.5°	397.7	396.2	394.6	393.1	391.5	389.5	386.9	384.3	381.6	379.1	376.7
65°	347.3	345.8	344.4	342.9	341.5	339.6	337.2	334.8	332.4	330.0	327.8
67.5°	296.0	294.8	293.7	292.5	291.4	289.8	287.6	285.4	283.2	281.0	279.4
70°	264.0	263.0	262.0	261.1	260.2	258.5	256.4	254.2	252.1	249.9	248.3
72.5°	231.1	230.2	229.2	228.2	227.2	226.1	224.7	223.3	221.8	220.5	218.8
75°	181.7	181.2	180.8	180.3	179.9	179.0	177.8	176.6	175.4	174.1	172.8
77.5°	137.6	136.8	136.0	135.2	134.4	133.7	133.2	132.7	132.2	131.8	131.0
80°	108.2	107.9	107.7	107.5	107.2	106.9	106.4	105.9	105.4	104.9	104.2
82.5°	80.5	80.5	80.4	80.3	80.3	80.1	79.8	79.6	79.2	79.0	78.0
85°	44.4	44.1	43.9	43.6	43.4	43.1	42.9	42.6	42.4	42.2	41.5
87.5°	15.7	15.8	16.1	16.1	16.0	16.1	16.6	17.3	17.9	17.6	16.9
90°	0.8	3.3	6.5	8.2	9.8	12.2	16.3	21.9	26.8	27.6	26.8
92.5°	9.9	14.3	20.2	23.7	29.3	36.9	55.4	81.2	104.3	105.7	89.4
95°	28.5	31.7	39.9	47.2	60.3	79.7	117.2	187.9	282.3	318.9	279.1
97.5°	46.4	50.8	59.4	70.4	85.4	107.5	154.6	253.2	410.1	544.5	571.2
100°	62.6	65.1	72.4	85.4	101.7	124.5	167.6	266.9	442.6	642.8	760.0
102.5°	77.6	79.4	86.7	99.8	116.7	139.5	179.4	267.6	430.3	646.0	830.3
105°	99.3	102.6	108.2	120.4	138.4	161.1	199.3	271.7	406.0	602.9	819.4
107.5°	122.7	125.3	130.9	142.1	159.8	182.8	219.9	283.0	394.0	556.8	748.0
110°	138.4	141.6	146.4	157.0	174.1	197.7	233.5	292.1	391.4	534.6	703.0



TEST NUMBER: P331410-930

CATALOG NUMBER: S122DIP-S865D925U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	152.6	155.9	161.4	171.4	187.8	212.1	246.5	301.9	392.0	520.2	671.8
115°	175.0	179.0	183.9	193.6	209.9	231.9	266.9	316.5	395.4	504.5	633.1
117.5°	198.0	201.3	206.2	214.8	230.4	253.2	285.6	332.2	401.3	496.8	608.6
120°	212.4	215.6	220.5	227.8	244.1	266.9	298.6	342.6	405.2	492.3	595.7
122.5°	226.1	228.6	233.5	241.5	257.8	281.2	311.0	351.6	409.8	489.7	584.6
125°	244.1	246.5	251.4	261.2	277.4	300.3	329.5	366.2	416.6	484.9	568.8
127.5°	258.4	261.7	268.5	279.2	294.9	318.3	346.8	379.7	423.6	482.2	554.2
130°	266.9	270.1	278.3	289.7	306.0	328.7	357.2	388.2	428.8	480.9	544.4
132.5°	274.7	278.6	287.4	299.5	316.3	339.2	366.3	396.6	434.0	480.2	536.5
135°	286.4	289.7	299.5	311.6	330.4	353.1	379.2	407.6	440.2	479.2	525.6
137.5°	297.5	301.4	311.1	324.2	342.8	363.9	389.6	416.1	445.7	479.1	518.0
140°	306.0	309.2	318.9	332.0	349.9	371.0	395.4	420.7	448.3	478.4	513.5
142.5°	314.4	317.0	326.1	339.2	356.4	376.3	400.0	424.6	450.3	478.4	508.9
145°	327.1	330.4	338.5	350.7	367.0	384.9	406.8	429.7	452.4	476.8	502.9
147.5°	340.8	343.2	351.0	362.2	375.8	391.8	412.4	432.4	453.1	473.9	496.7
150°	349.9	352.3	358.8	369.4	381.6	396.2	415.0	433.7	452.4	472.0	491.5
152.5°	359.0	360.1	366.6	375.9	387.5	400.8	417.6	434.3	451.1	468.7	486.9
155°	371.9	372.7	377.6	386.5	395.4	407.6	421.5	435.3	449.1	463.0	478.4
157.5°	382.6	383.4	387.3	395.1	402.3	412.5	424.3	435.3	445.4	457.1	470.5
160°	389.8	390.6	393.8	400.3	406.8	415.8	425.6	435.3	443.4	453.2	464.6
162.5°	396.9	396.4	399.7	404.9	410.7	417.8	426.2	434.6	441.5	450.0	459.4
165°	405.2	404.4	406.0	410.9	415.0	419.9	427.2	432.9	437.7	443.4	450.8
167.5°	412.1	411.1	412.5	415.6	418.6	421.7	427.1	431.8	434.0	437.7	442.3
170°	416.6	415.0	415.8	418.2	419.9	422.3	426.4	430.5	432.1	434.5	437.7
172.5°	419.2	418.2	417.8	420.2	421.2	423.0	425.7	428.5	429.5	430.6	433.3
175°	422.3	421.5	420.7	422.3	422.3	423.1	424.8	426.4	425.6	426.4	427.2
177.5°	423.8	422.5	421.8	423.1	423.1	423.1	423.8	425.1	423.8	423.1	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331410-930

CATALOG NUMBER: S122DIP-S865D925U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1120.3	1122.3	1124.1	1124.9	1124.5	1124.1	1123.8	1123.4
5°	1112.7	1114.7	1116.6	1117.3	1116.9	1116.4	1115.9	1115.4
7.5°	1100.2	1102.1	1104.1	1104.7	1104.2	1103.7	1103.2	1102.6
10°	1088.9	1090.9	1092.8	1093.4	1092.7	1091.9	1091.2	1090.5
12.5°	1075.7	1077.0	1078.4	1078.8	1078.2	1077.7	1077.2	1076.7
15°	1052.4	1053.4	1054.3	1054.2	1053.0	1051.8	1050.6	1049.4
17.5°	1024.7	1025.9	1027.0	1027.0	1025.8	1024.7	1023.5	1022.4
20°	1003.2	1004.0	1004.7	1004.5	1003.6	1002.7	1001.7	1000.7
22.5°	980.5	980.6	980.7	980.6	979.9	979.3	978.8	978.2
25°	943.3	943.7	944.2	944.2	943.7	943.3	942.8	942.3
27.5°	906.7	906.0	905.2	904.3	903.1	902.0	900.8	899.7
30°	878.1	877.4	876.7	875.8	874.9	873.9	872.9	872.0
32.5°	850.1	848.8	847.5	846.4	845.5	844.5	843.5	842.5
35°	805.3	803.8	802.4	801.0	799.9	798.7	797.4	796.2
37.5°	760.3	758.5	756.7	755.2	754.1	752.9	751.8	750.6
40°	729.2	727.0	724.9	723.3	722.4	721.4	720.4	719.4
42.5°	698.5	696.1	693.8	691.9	690.6	689.3	687.9	686.6
45°	651.4	648.7	646.1	644.3	643.4	642.4	641.4	640.5
47.5°	602.4	599.7	596.9	594.8	593.4	592.0	590.6	589.2
50°	571.0	567.6	564.3	562.0	560.8	559.5	558.4	557.2
52.5°	538.3	535.6	532.8	530.6	529.0	527.4	525.9	524.2
55°	489.8	486.8	484.0	481.9	480.7	479.5	478.3	477.1
57.5°	439.2	436.3	433.5	431.6	430.7	429.8	428.9	428.0
60°	405.9	403.2	400.6	398.8	398.1	397.4	396.6	396.0
62.5°	374.1	371.7	369.2	367.6	366.6	365.7	364.8	363.9
65°	325.6	323.5	321.3	319.6	318.5	317.2	316.0	314.8
67.5°	277.7	276.0	274.3	273.0	272.1	271.1	270.1	269.1
70°	246.5	244.8	243.2	241.8	240.9	239.9	239.0	238.0
72.5°	217.1	215.4	213.8	212.5	211.7	211.0	210.2	209.5
75°	171.3	169.8	168.4	168.0	168.4	168.9	169.3	169.8
77.5°	130.4	129.6	128.9	128.2	127.5	126.9	126.2	125.5
80°	103.5	102.8	102.1	101.4	100.9	100.5	100.0	99.5
82.5°	77.1	76.2	75.3	74.8	74.7	74.6	74.5	74.4
85°	40.8	40.0	39.3	38.8	38.6	38.3	38.1	37.8
87.5°	16.1	15.2	15.0	14.8	14.6	14.4	14.2	14.0
90°	26.0	24.4	26.0	26.8	26.8	26.8	26.8	26.8
92.5°	70.9	60.9	54.1	49.0	48.3	45.7	46.4	45.1
95°	213.2	163.5	129.4	111.5	100.9	94.4	92.0	92.8
97.5°	497.5	407.0	318.9	260.2	221.4	201.3	189.4	182.6
100°	742.9	642.0	530.5	432.1	364.5	329.5	306.0	291.3
102.5°	903.7	880.9	799.4	695.0	621.7	561.9	532.5	512.7
105°	988.6	1080.6	1091.2	1064.3	1013.8	963.4	928.4	917.0
107.5°	927.5	1065.9	1150.6	1189.9	1196.3	1193.5	1186.5	1171.4
110°	874.7	1020.3	1124.5	1191.2	1226.2	1241.7	1249.0	1248.2



TEST NUMBER: P331410-930

CATALOG NUMBER: S122DIP-S865D925U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	826.6	966.4	1077.7	1154.1	1202.8	1228.7	1242.5	1246.9
115°	767.3	892.6	999.2	1083.0	1140.8	1178.2	1199.4	1206.7
117.5°	722.7	832.7	929.4	1008.0	1066.9	1106.4	1128.8	1134.9
120°	700.6	801.5	887.7	961.8	1018.7	1057.0	1080.6	1088.8
122.5°	683.0	775.4	857.1	924.1	975.1	1012.7	1033.7	1040.6
125°	657.5	741.3	812.9	873.9	921.1	952.0	972.3	978.8
127.5°	632.3	708.1	775.6	831.9	873.1	902.0	919.7	924.9
130°	616.0	685.9	750.2	804.0	843.8	871.5	887.7	894.2
132.5°	600.3	665.1	724.1	774.6	813.8	841.6	856.5	862.3
135°	578.5	632.3	685.9	731.5	766.5	793.4	808.0	811.2
137.5°	561.1	606.0	648.7	688.4	720.3	743.4	756.3	761.2
140°	550.1	589.1	626.6	662.3	688.4	709.6	721.8	726.6
142.5°	541.0	574.1	606.3	636.3	661.0	680.3	691.1	692.1
145°	528.1	555.0	580.2	603.7	623.3	637.2	645.2	647.7
147.5°	518.1	539.3	559.0	576.3	592.4	603.4	608.9	610.4
150°	511.0	528.9	546.0	560.6	572.8	582.6	587.5	588.3
152.5°	503.9	520.4	534.9	547.6	557.2	565.7	569.2	569.4
155°	493.9	507.0	519.1	528.1	537.0	542.7	546.0	544.4
157.5°	482.3	493.3	503.5	510.5	516.8	521.5	523.0	523.0
160°	475.2	484.1	493.1	498.8	504.5	508.6	509.4	509.4
162.5°	468.1	475.6	483.3	487.7	493.4	496.2	497.0	496.4
165°	457.3	463.0	468.7	472.0	475.2	478.4	478.4	477.6
167.5°	447.0	451.4	455.3	458.3	459.7	461.5	461.4	460.4
170°	441.8	444.3	447.5	449.1	450.0	452.4	451.6	450.0
172.5°	435.9	437.7	440.3	441.3	442.1	443.3	442.5	441.5
175°	429.7	430.5	431.3	432.1	432.1	432.9	432.1	430.5
177.5°	425.1	425.1	425.7	425.7	425.7	425.7	425.1	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1

(END OF REPORT)