

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331758-930

Luminaire Tested: **S122RDIP-S1005D925U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331758-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S1005D925U930-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5787.8 lumens  
Efficiency: N/A  
Efficacy: 86.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331758-930

CATALOG NUMBER: S122RDIP-S1005D925U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331758-930

CATALOG NUMBER: S122RDIP-S1005D925U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35	31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31	27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24
6	64	52	44	39	59	49	42	37	42	36	32	36	31	28	30	27	24	21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	22291	22291	22291
5°	22376	22013	22135
10°	22207	21653	21469
15°	21951	21010	20404
20°	21596	20094	19086
25°	21235	19053	17808
30°	20734	17984	16168
35°	20243	16821	14728
40°	19751	15616	13061
45°	19173	14266	11556
50°	18580	12901	10073
55°	17973	11431	8653
60°	17270	9884	7182
65°	16466	8306	6541
70°	15512	6845	6014
75°	14342	6238	5608
80°	12664	5579	5114
85°	9948	4390	4390



TEST NUMBER: P331758-930

CATALOG NUMBER: S122RDIP-S1005D925U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	129.2	2.2
10°-20°	354.8	6.1
20°-30°	498.3	8.6
30°-40°	543.4	9.4
40°-50°	499.6	8.6
50°-60°	392.4	6.8
60°-70°	255.8	4.4
70°-80°	131.9	2.3
80°-90°	38.0	0.7
90°-100°	169.2	2.9
100°-110°	574.1	9.9
110°-120°	609.9	10.5
120°-130°	502.1	8.7
130°-140°	403.2	7.0
140°-150°	304.7	5.3
150°-160°	214.1	3.7
160°-170°	126.0	2.2
170°-180°	41.0	0.7
0°-30°	982.4	17.0
0°-40°	1525.7	26.4
0°-60°	2417.7	41.8
0°-90°	2843.5	49.1
90°-120°	1353.2	23.4
90°-150°	2563.1	44.3
90°-180°	2944.0	50.9
0°-180°	5787.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1381	1381	1381	1381	1381	
5°	1381	1374	1358	1369	1366	131
15°	1313	1298	1257	1234	1221	370
25°	1192	1150	1070	1020	1000	548
35°	1027	961	853	778	747	642
45°	840	753	625	539	506	648
55°	638	539	406	334	307	570
65°	431	329	217	177	171	427
75°	230	145	100	92	90	243
85°	54	29	24	24	24	63
90°	1	11	28	26	27	4
95°	28	70	319	120	93	30
105°	99	150	603	1078	917	106
115°	175	221	504	1041	1207	173
125°	244	289	485	843	979	217
135°	286	342	479	709	811	221
145°	327	376	477	592	648	205
155°	372	402	463	524	544	171
165°	405	417	443	470	478	114
175°	422	423	426	432	430	40
180°	423	423	423	423	423	



TEST NUMBER: P331758-930

CATALOG NUMBER: S122RDIP-S1005D925U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6
2.5°	1385.7	1384.5	1383.4	1382.3	1381.2	1379.4	1377.0	1374.6	1372.1	1369.7	1371.9
5°	1380.6	1379.2	1377.9	1376.5	1375.1	1372.6	1369.0	1365.4	1361.8	1358.2	1360.7
7.5°	1366.4	1364.7	1363.0	1361.2	1359.5	1356.6	1352.3	1348.1	1343.9	1339.7	1340.4
10°	1354.5	1352.5	1350.5	1348.6	1346.6	1342.9	1337.3	1331.8	1326.2	1320.7	1319.9
12.5°	1339.5	1337.0	1334.6	1332.3	1329.9	1325.1	1318.0	1310.9	1303.8	1296.7	1295.2
15°	1313.2	1310.1	1307.1	1304.0	1301.0	1294.7	1285.3	1275.9	1266.4	1256.9	1251.7
17.5°	1280.9	1276.3	1271.6	1267.0	1262.3	1253.9	1241.8	1229.7	1217.6	1205.5	1199.2
20°	1256.9	1251.4	1245.9	1240.3	1234.8	1225.1	1211.1	1197.3	1183.4	1169.5	1162.5
22.5°	1230.9	1224.7	1218.5	1212.4	1206.1	1195.1	1179.5	1163.8	1148.2	1132.5	1123.6
25°	1192.0	1183.1	1174.2	1165.3	1156.4	1142.9	1124.5	1106.2	1087.9	1069.5	1058.2
27.5°	1145.0	1135.4	1125.7	1116.1	1106.4	1091.2	1070.6	1049.9	1029.2	1008.6	995.3
30°	1112.1	1101.5	1091.0	1080.4	1069.8	1053.4	1031.2	1009.0	986.8	964.6	950.4
32.5°	1080.0	1067.7	1055.4	1043.1	1030.7	1013.3	990.6	967.9	945.3	922.6	906.4
35°	1027.0	1012.9	998.7	984.6	970.5	951.1	926.7	902.3	877.8	853.4	835.9
37.5°	974.1	958.5	943.0	927.4	911.9	891.1	865.0	839.0	812.9	786.9	767.7
40°	937.1	920.5	903.8	887.1	870.5	848.6	821.7	794.8	767.8	740.9	721.2
42.5°	899.1	881.6	864.1	846.4	828.9	806.2	778.4	750.6	722.8	695.0	674.6
45°	839.7	821.0	802.4	783.8	765.2	741.4	712.2	683.1	653.9	624.8	605.0
47.5°	781.6	762.0	742.2	722.5	702.8	677.9	647.8	617.7	587.6	557.5	537.9
50°	739.7	720.0	700.3	680.5	660.8	635.7	605.2	574.6	544.0	513.6	494.4
52.5°	698.7	678.1	657.5	636.9	616.3	591.1	561.2	531.3	501.4	471.6	453.1
55°	638.5	616.9	595.2	573.5	551.9	526.0	496.0	466.0	436.1	406.1	389.4
57.5°	576.7	554.6	532.3	510.1	487.9	462.4	433.6	404.7	375.9	347.1	331.8
60°	534.8	512.6	490.3	468.1	445.9	420.5	391.9	363.3	334.7	306.1	292.0
62.5°	493.8	471.6	449.4	427.1	405.0	380.2	352.9	325.6	298.4	271.2	257.6
65°	431.0	408.5	386.1	363.6	341.1	317.4	292.4	267.4	242.4	217.4	208.0
67.5°	370.6	348.3	326.0	303.6	281.3	258.9	236.4	213.9	191.4	168.9	164.6
70°	328.6	307.0	285.3	263.7	242.0	221.6	202.4	183.3	164.1	145.0	142.2
72.5°	288.6	267.8	247.1	226.3	205.5	187.4	172.1	156.7	141.3	126.0	123.6
75°	229.9	210.4	191.0	171.6	152.1	137.7	128.2	118.9	109.4	100.0	98.0
77.5°	172.2	155.2	138.1	121.1	104.0	93.2	88.6	84.1	79.5	75.0	73.9
80°	136.2	122.1	107.9	93.7	79.6	71.1	68.3	65.6	62.8	60.0	58.9
82.5°	103.2	92.1	81.1	70.0	59.0	52.5	50.6	48.8	46.9	45.0	44.4
85°	53.7	47.9	42.1	36.2	30.4	27.1	26.3	25.4	24.5	23.7	23.7
87.5°	16.1	14.8	13.8	12.3	10.8	10.4	11.3	12.4	13.4	13.5	13.1
90°	0.8	3.3	6.5	8.2	9.8	12.2	16.3	21.9	26.8	27.6	26.8
92.5°	9.9	14.3	20.2	23.7	29.3	36.9	55.4	81.2	104.3	105.7	89.4
95°	28.5	31.7	39.9	47.2	60.3	79.7	117.2	187.9	282.3	318.9	279.1
97.5°	46.4	50.8	59.4	70.4	85.4	107.5	154.6	253.2	410.1	544.5	571.2
100°	62.6	65.1	72.4	85.4	101.7	124.5	167.6	266.9	442.6	642.8	760.0
102.5°	77.6	79.4	86.7	99.8	116.7	139.5	179.4	267.6	430.3	646.0	830.3
105°	99.3	102.6	108.2	120.4	138.4	161.1	199.3	271.7	406.0	602.9	819.4
107.5°	122.7	125.3	130.9	142.1	159.8	182.8	219.9	283.0	394.0	556.8	748.0
110°	138.4	141.6	146.4	157.0	174.1	197.7	233.5	292.1	391.4	534.6	703.0



TEST NUMBER: P331758-930

CATALOG NUMBER: S122RDIP-S1005D925U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	152.6	155.9	161.4	171.4	187.8	212.1	246.5	301.9	392.0	520.2	671.8
115°	175.0	179.0	183.9	193.6	209.9	231.9	266.9	316.5	395.4	504.5	633.1
117.5°	198.0	201.3	206.2	214.8	230.4	253.2	285.6	332.2	401.3	496.8	608.6
120°	212.4	215.6	220.5	227.8	244.1	266.9	298.6	342.6	405.2	492.3	595.7
122.5°	226.1	228.6	233.5	241.5	257.8	281.2	311.0	351.6	409.8	489.7	584.6
125°	244.1	246.5	251.4	261.2	277.4	300.3	329.5	366.2	416.6	484.9	568.8
127.5°	258.4	261.7	268.5	279.2	294.9	318.3	346.8	379.7	423.6	482.2	554.2
130°	266.9	270.1	278.3	289.7	306.0	328.7	357.2	388.2	428.8	480.9	544.4
132.5°	274.7	278.6	287.4	299.5	316.3	339.2	366.3	396.6	434.0	480.2	536.5
135°	286.4	289.7	299.5	311.6	330.4	353.1	379.2	407.6	440.2	479.2	525.6
137.5°	297.5	301.4	311.1	324.2	342.8	363.9	389.6	416.1	445.7	479.1	518.0
140°	306.0	309.2	318.9	332.0	349.9	371.0	395.4	420.7	448.3	478.4	513.5
142.5°	314.4	317.0	326.1	339.2	356.4	376.3	400.0	424.6	450.3	478.4	508.9
145°	327.1	330.4	338.5	350.7	367.0	384.9	406.8	429.7	452.4	476.8	502.9
147.5°	340.8	343.2	351.0	362.2	375.8	391.8	412.4	432.4	453.1	473.9	496.7
150°	349.9	352.3	358.8	369.4	381.6	396.2	415.0	433.7	452.4	472.0	491.5
152.5°	359.0	360.1	366.6	375.9	387.5	400.8	417.6	434.3	451.1	468.7	486.9
155°	371.9	372.7	377.6	386.5	395.4	407.6	421.5	435.3	449.1	463.0	478.4
157.5°	382.6	383.4	387.3	395.1	402.3	412.5	424.3	435.3	445.4	457.1	470.5
160°	389.8	390.6	393.8	400.3	406.8	415.8	425.6	435.3	443.4	453.2	464.6
162.5°	396.9	396.4	399.7	404.9	410.7	417.8	426.2	434.6	441.5	450.0	459.4
165°	405.2	404.4	406.0	410.9	415.0	419.9	427.2	432.9	437.7	443.4	450.8
167.5°	412.1	411.1	412.5	415.6	418.6	421.7	427.1	431.8	434.0	437.7	442.3
170°	416.6	415.0	415.8	418.2	419.9	422.3	426.4	430.5	432.1	434.5	437.7
172.5°	419.2	418.2	417.8	420.2	421.2	423.0	425.7	428.5	429.5	430.6	433.3
175°	422.3	421.5	420.7	422.3	422.3	423.1	424.8	426.4	425.6	426.4	427.2
177.5°	423.8	422.5	421.8	423.1	423.1	423.1	423.8	425.1	423.8	423.1	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331758-930

CATALOG NUMBER: S122RDIP-S1005D925U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6
2.5°	1374.1	1376.3	1378.6	1379.4	1379.0	1378.6	1378.1	1377.7
5°	1363.2	1365.7	1368.2	1369.0	1368.2	1367.3	1366.5	1365.7
7.5°	1341.1	1341.8	1342.6	1342.2	1340.8	1339.3	1337.9	1336.4
10°	1319.0	1318.2	1317.4	1316.1	1314.4	1312.8	1311.1	1309.5
12.5°	1293.7	1292.2	1290.7	1288.6	1285.8	1283.0	1280.3	1277.5
15°	1246.4	1241.1	1235.8	1231.8	1229.1	1226.3	1223.5	1220.7
17.5°	1192.9	1186.7	1180.4	1174.8	1170.1	1165.3	1160.5	1155.8
20°	1155.6	1148.7	1141.7	1135.2	1129.1	1123.0	1116.9	1110.8
22.5°	1114.7	1105.7	1096.7	1090.0	1085.5	1080.9	1076.4	1071.8
25°	1046.8	1035.4	1024.0	1016.3	1012.0	1007.9	1003.7	999.6
27.5°	982.0	968.7	955.4	945.5	938.9	932.3	925.7	919.1
30°	936.3	922.1	907.9	897.2	889.7	882.2	874.7	867.2
32.5°	890.3	874.2	857.9	846.4	839.4	832.3	825.2	818.2
35°	818.4	801.0	783.4	771.6	765.5	759.4	753.3	747.2
37.5°	748.4	729.1	709.8	696.7	689.7	682.7	675.7	668.7
40°	701.5	681.8	662.1	648.7	641.4	634.1	627.0	619.7
42.5°	654.2	633.8	613.4	599.7	592.7	585.7	578.8	571.8
45°	585.3	565.6	545.8	532.7	526.0	519.3	512.7	506.1
47.5°	518.3	498.7	479.1	466.3	460.2	454.2	448.1	442.1
50°	475.2	456.1	436.9	424.4	418.6	412.7	406.9	401.0
52.5°	434.6	416.0	397.6	385.6	380.3	374.9	369.5	364.1
55°	372.8	356.1	339.4	328.5	323.2	317.9	312.7	307.4
57.5°	316.6	301.3	286.0	276.1	271.7	267.3	262.9	258.4
60°	277.8	263.7	249.5	240.2	235.7	231.3	226.8	222.4
62.5°	244.2	230.6	217.2	209.0	206.4	203.7	201.1	198.4
65°	198.5	189.1	179.6	174.5	173.7	172.8	172.0	171.2
67.5°	160.3	156.0	151.6	149.0	148.1	147.2	146.3	145.4
70°	139.4	136.6	133.9	131.9	130.8	129.6	128.6	127.4
72.5°	121.3	119.0	116.6	115.1	114.5	113.8	113.1	112.4
75°	96.0	94.2	92.2	91.1	90.8	90.5	90.3	89.9
77.5°	72.7	71.7	70.5	69.7	69.3	68.9	68.4	68.0
80°	57.7	56.7	55.5	55.0	55.0	55.0	55.0	55.0
82.5°	43.6	43.0	42.3	42.0	42.0	42.0	42.0	42.0
85°	23.7	23.7	23.7	23.7	23.7	23.7	23.7	23.7
87.5°	12.8	12.2	12.3	12.4	12.4	12.4	12.4	12.4
90°	26.0	24.4	26.0	26.8	26.8	26.8	26.8	26.8
92.5°	70.9	60.9	54.1	49.0	48.3	45.7	46.4	45.1
95°	213.2	163.5	129.4	111.5	100.9	94.4	92.0	92.8
97.5°	497.5	407.0	318.9	260.2	221.4	201.3	189.4	182.6
100°	742.9	642.0	530.5	432.1	364.5	329.5	306.0	291.3
102.5°	903.7	880.9	799.4	695.0	621.7	561.9	532.5	512.7
105°	988.6	1080.6	1091.2	1064.3	1013.8	963.4	928.4	917.0
107.5°	927.5	1065.9	1150.6	1189.9	1196.3	1193.5	1186.5	1171.4
110°	874.7	1020.3	1124.5	1191.2	1226.2	1241.7	1249.0	1248.2





TEST NUMBER: P331758-930

CATALOG NUMBER: S122RDIP-S1005D925U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	826.6	966.4	1077.7	1154.1	1202.8	1228.7	1242.5	1246.9
115°	767.3	892.6	999.2	1083.0	1140.8	1178.2	1199.4	1206.7
117.5°	722.7	832.7	929.4	1008.0	1066.9	1106.4	1128.8	1134.9
120°	700.6	801.5	887.7	961.8	1018.7	1057.0	1080.6	1088.8
122.5°	683.0	775.4	857.1	924.1	975.1	1012.7	1033.7	1040.6
125°	657.5	741.3	812.9	873.9	921.1	952.0	972.3	978.8
127.5°	632.3	708.1	775.6	831.9	873.1	902.0	919.7	924.9
130°	616.0	685.9	750.2	804.0	843.8	871.5	887.7	894.2
132.5°	600.3	665.1	724.1	774.6	813.8	841.6	856.5	862.3
135°	578.5	632.3	685.9	731.5	766.5	793.4	808.0	811.2
137.5°	561.1	606.0	648.7	688.4	720.3	743.4	756.3	761.2
140°	550.1	589.1	626.6	662.3	688.4	709.6	721.8	726.6
142.5°	541.0	574.1	606.3	636.3	661.0	680.3	691.1	692.1
145°	528.1	555.0	580.2	603.7	623.3	637.2	645.2	647.7
147.5°	518.1	539.3	559.0	576.3	592.4	603.4	608.9	610.4
150°	511.0	528.9	546.0	560.6	572.8	582.6	587.5	588.3
152.5°	503.9	520.4	534.9	547.6	557.2	565.7	569.2	569.4
155°	493.9	507.0	519.1	528.1	537.0	542.7	546.0	544.4
157.5°	482.3	493.3	503.5	510.5	516.8	521.5	523.0	523.0
160°	475.2	484.1	493.1	498.8	504.5	508.6	509.4	509.4
162.5°	468.1	475.6	483.3	487.7	493.4	496.2	497.0	496.4
165°	457.3	463.0	468.7	472.0	475.2	478.4	478.4	477.6
167.5°	447.0	451.4	455.3	458.3	459.7	461.5	461.4	460.4
170°	441.8	444.3	447.5	449.1	450.0	452.4	451.6	450.0
172.5°	435.9	437.7	440.3	441.3	442.1	443.3	442.5	441.5
175°	429.7	430.5	431.3	432.1	432.1	432.9	432.1	430.5
177.5°	425.1	425.1	425.7	425.7	425.7	425.7	425.1	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1

(END OF REPORT)