

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931499

Luminaire Tested: DFN2DS-TR4F0-070DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931499
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-070DS835-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6930.0 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931499

CATALOG NUMBER: DFN2DS-TR4F0-070DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931499

CATALOG NUMBER: DFN2DS-TR4F0-070DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2164	2164	2164
5°	2172	2141	2153
10°	2159	2119	2130
15°	2133	2092	2090
20°	2095	2050	2048
25°	2057	2000	2000
30°	2009	1953	1936
35°	1964	1897	1869
40°	1907	1841	1806
45°	1851	1786	1742
50°	1790	1728	1667
55°	1727	1662	1600
60°	1656	1582	1523
65°	1581	1502	1433
70°	1484	1405	1339
75°	1350	1294	1262
80°	1199	1162	1102
85°	978	932	836

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1851 cd/sqm

TEST NUMBER: P931499

CATALOG NUMBER: DFN2DS-TR4F0-070DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.4	3.7
10°-20°	721.3	10.4
20°-30°	1060.0	15.3
30°-40°	1231.1	17.8
40°-50°	1229.6	17.7
50°-60°	1072.2	15.5
60°-70°	792.6	11.4
70°-80°	448.4	6.5
80°-90°	118.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2037.7	29.4
0°-40°	3268.8	47.2
0°-60°	5570.6	80.4
0°-90°	6930.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6930.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2724	2724	2724	2724	2724	
5°	2724	2714	2685	2705	2700	259
15°	2593	2577	2543	2554	2541	730
25°	2347	2326	2281	2286	2281	1080
35°	2025	1998	1956	1941	1928	1264
45°	1648	1629	1590	1561	1550	1271
55°	1247	1231	1200	1168	1155	1115
65°	841	825	799	775	762	831
75°	440	435	422	406	411	470
85°	107	105	102	94	92	126
90°	0	0	0	0	0	

TEST NUMBER: P931499

CATALOG NUMBER: DFN2DS-TR4F0-070DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2723.7	2723.7	2723.7	2723.7	2723.7
2.5°	2739.6	2726.5	2697.6	2723.7	2718.7
5°	2723.7	2713.5	2684.6	2705.4	2700.4
7.5°	2705.4	2689.8	2660.9	2682.1	2676.8
10°	2676.8	2658.4	2627.0	2647.9	2640.1
12.5°	2637.3	2621.8	2590.4	2603.4	2598.1
15°	2592.9	2577.3	2543.1	2553.7	2540.6
17.5°	2537.8	2522.3	2488.1	2501.2	2488.1
20°	2477.5	2462.0	2425.3	2433.1	2422.8
22.5°	2417.5	2393.9	2359.7	2359.7	2354.4
25°	2346.7	2325.8	2281.4	2286.4	2281.4
27.5°	2268.0	2249.7	2215.8	2208.0	2194.9
30°	2189.7	2168.5	2129.4	2121.6	2111.0
32.5°	2105.7	2090.2	2048.2	2032.4	2021.8
35°	2024.6	1998.5	1956.5	1940.7	1927.6
37.5°	1932.9	1909.3	1867.3	1849.0	1835.9
40°	1838.7	1817.6	1775.6	1752.3	1741.7
42.5°	1747.0	1725.9	1684.2	1657.8	1642.2
45°	1647.5	1629.2	1589.7	1561.1	1550.5
47.5°	1550.5	1532.2	1490.2	1461.3	1445.8
50°	1448.3	1435.2	1398.5	1361.9	1348.8
52.5°	1348.8	1330.5	1296.6	1267.7	1249.3
55°	1246.8	1231.0	1199.6	1168.2	1155.1
57.5°	1144.6	1131.5	1097.3	1065.9	1055.4
60°	1042.3	1032.0	995.4	966.5	958.7
62.5°	942.8	924.5	898.4	872.3	861.7
65°	840.9	825.0	798.9	775.3	762.2
67.5°	736.1	722.8	699.4	681.1	670.5
70°	639.1	628.6	604.9	586.6	576.3
72.5°	539.6	529.1	516.0	497.7	489.9
75°	439.9	434.9	421.5	406.0	411.3
77.5°	351.0	340.4	335.1	327.3	319.6
80°	262.0	259.3	254.0	246.2	240.9
82.5°	178.1	178.1	175.6	165.1	165.1
85°	107.3	104.8	102.3	94.2	91.7
87.5°	47.2	42.0	36.7	28.9	26.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931499

CATALOG NUMBER: DFN2DS-TR4F0-070DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.96	15.58	14.33	15.89	16.20	13.52	15.13	13.88	15.44	15.76
	3H	15.71	17.17	16.09	17.50	17.86	15.22	16.68	15.60	17.00	17.36
	4H	16.36	17.73	16.76	18.08	18.45	15.87	17.23	16.26	17.58	17.96
	6H	16.83	18.10	17.24	18.46	18.85	16.33	17.60	16.74	17.96	18.35
	8H	16.97	18.18	17.40	18.57	18.97	16.47	17.68	16.89	18.07	18.47
	12H	17.06	18.22	17.49	18.60	19.03	16.55	17.71	16.98	18.09	18.52
4H	2H	14.52	15.89	14.92	16.24	16.62	14.17	15.54	14.57	15.89	16.26
	3H	16.50	17.65	16.91	18.04	18.44	16.09	17.24	16.50	17.64	18.04
	4H	17.28	18.31	17.71	18.73	19.16	16.85	17.89	17.28	18.30	18.74
	6H	17.87	18.78	18.33	19.22	19.67	17.44	18.35	17.89	18.79	19.24
	8H	18.06	18.91	18.52	19.35	19.82	17.62	18.47	18.09	18.91	19.38
	12H	18.19	18.95	18.67	19.43	19.90	17.74	18.50	18.22	18.98	19.45
8H	4H	17.55	18.40	18.01	18.84	19.30	17.18	18.02	17.64	18.46	18.93
	6H	18.26	18.97	18.76	19.46	19.93	17.88	18.59	18.38	19.07	19.55
	8H	18.52	19.15	19.03	19.66	20.15	18.13	18.76	18.64	19.27	19.76
	12H	18.72	19.28	19.23	19.77	20.33	18.31	18.87	18.82	19.36	19.92
12H	4H	17.58	18.34	18.06	18.81	19.28	17.21	17.97	17.69	18.45	18.92
	6H	18.31	18.94	18.82	19.45	19.93	17.94	18.57	18.45	19.08	19.57
	8H	18.62	19.18	19.13	19.67	20.23	18.25	18.80	18.75	19.29	19.86