

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931517

Luminaire Tested: DFN2DS-TR4F0-080DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931517
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-080DS835-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7920.0 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 81.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931517

CATALOG NUMBER: DFN2DS-TR4F0-080DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931517

CATALOG NUMBER: DFN2DS-TR4F0-080DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2473	2473	2473
5°	2482	2447	2461
10°	2468	2422	2434
15°	2437	2390	2388
20°	2394	2343	2341
25°	2351	2285	2285
30°	2296	2232	2213
35°	2244	2169	2137
40°	2179	2105	2064
45°	2115	2041	1991
50°	2046	1975	1905
55°	1974	1899	1828
60°	1893	1807	1741
65°	1806	1716	1637
70°	1697	1606	1530
75°	1543	1479	1443
80°	1370	1328	1259
85°	1118	1066	955

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2115 cd/sqm

TEST NUMBER: P931517

CATALOG NUMBER: DFN2DS-TR4F0-080DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.0	3.7
10°-20°	824.3	10.4
20°-30°	1211.5	15.3
30°-40°	1407.0	17.8
40°-50°	1405.3	17.7
50°-60°	1225.4	15.5
60°-70°	905.8	11.4
70°-80°	512.5	6.5
80°-90°	135.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2328.8	29.4
0°-40°	3735.8	47.2
0°-60°	6366.4	80.4
0°-90°	7920.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7920.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3113	3113	3113	3113	3113	
5°	3113	3101	3068	3092	3086	295
15°	2963	2946	2906	2918	2904	835
25°	2682	2658	2607	2613	2607	1234
35°	2314	2284	2236	2218	2203	1445
45°	1883	1862	1817	1784	1772	1453
55°	1425	1407	1371	1335	1320	1274
65°	961	943	913	886	871	950
75°	503	497	482	464	470	537
85°	123	120	117	108	105	144
90°	0	0	0	0	0	

TEST NUMBER: P931517

CATALOG NUMBER: DFN2DS-TR4F0-080DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3112.8	3112.8	3112.8	3112.8	3112.8
2.5°	3130.9	3116.0	3083.0	3112.8	3107.1
5°	3112.8	3101.1	3068.1	3091.9	3086.2
7.5°	3091.9	3074.1	3041.1	3065.2	3059.2
10°	3059.2	3038.2	3002.3	3026.1	3017.3
12.5°	3014.1	2996.3	2960.4	2975.3	2969.3
15°	2963.3	2945.5	2906.4	2918.5	2903.6
17.5°	2900.4	2882.6	2843.5	2858.5	2843.5
20°	2831.5	2813.7	2771.8	2780.7	2768.9
22.5°	2762.9	2735.9	2696.8	2696.8	2690.8
25°	2681.9	2658.1	2607.3	2613.0	2607.3
27.5°	2592.0	2571.1	2532.3	2523.4	2508.5
30°	2502.5	2478.3	2433.6	2424.7	2412.6
32.5°	2406.6	2388.8	2340.8	2322.7	2310.7
35°	2313.8	2284.0	2236.0	2217.9	2203.0
37.5°	2209.0	2182.0	2134.1	2113.1	2098.2
40°	2101.4	2077.2	2029.3	2002.6	1990.5
42.5°	1996.6	1972.4	1924.8	1894.6	1876.9
45°	1882.9	1861.9	1816.8	1784.1	1772.1
47.5°	1772.1	1751.1	1703.1	1670.1	1652.3
50°	1655.2	1640.3	1598.3	1556.4	1541.5
52.5°	1541.5	1520.5	1481.8	1448.8	1427.8
55°	1424.9	1406.8	1371.0	1335.1	1320.1
57.5°	1308.1	1293.2	1254.1	1218.2	1206.1
60°	1191.2	1179.5	1137.5	1104.5	1095.6
62.5°	1077.5	1056.6	1026.7	996.9	984.8
65°	961.0	942.9	913.0	886.0	871.1
67.5°	841.2	826.0	799.3	778.4	766.3
70°	730.4	718.3	691.4	670.4	658.6
72.5°	616.7	604.7	589.7	568.8	559.9
75°	502.7	497.0	481.8	464.0	470.0
77.5°	401.1	389.0	383.0	374.1	365.2
80°	299.5	296.3	290.3	281.4	275.3
82.5°	203.6	203.6	200.7	188.6	188.6
85°	122.6	119.7	116.9	107.7	104.8
87.5°	54.0	48.0	41.9	33.0	29.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931517

CATALOG NUMBER: DFN2DS-TR4F0-080DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.43	16.04	14.79	16.35	16.67	13.98	15.59	14.35	15.91	16.22
	3H	16.18	17.63	16.56	17.96	18.32	15.69	17.14	16.06	17.47	17.83
	4H	16.82	18.19	17.22	18.54	18.92	16.33	17.70	16.73	18.05	18.42
	6H	17.29	18.56	17.70	18.93	19.32	16.79	18.06	17.20	18.43	18.82
	8H	17.44	18.65	17.86	19.04	19.44	16.93	18.14	17.36	18.53	18.93
	12H	17.53	18.69	17.96	19.07	19.50	17.01	18.17	17.44	18.56	18.99
4H	2H	14.99	16.36	15.39	16.71	17.08	14.64	16.00	15.03	16.35	16.73
	3H	16.96	18.11	17.37	18.51	18.91	16.56	17.70	16.97	18.10	18.50
	4H	17.74	18.78	18.17	19.19	19.63	17.32	18.35	17.75	18.77	19.20
	6H	18.34	19.24	18.79	19.68	20.14	17.90	18.81	18.36	19.25	19.71
	8H	18.53	19.37	18.99	19.82	20.28	18.09	18.93	18.55	19.38	19.84
	12H	18.66	19.42	19.14	19.89	20.36	18.21	18.97	18.69	19.44	19.91
8H	4H	18.01	18.86	18.47	19.30	19.77	17.64	18.49	18.10	18.93	19.39
	6H	18.73	19.43	19.22	19.92	20.39	18.35	19.05	18.84	19.54	20.01
	8H	18.99	19.62	19.50	20.12	20.61	18.60	19.23	19.11	19.73	20.22
	12H	19.19	19.74	19.69	20.24	20.80	18.77	19.33	19.28	19.82	20.38
12H	4H	18.04	18.80	18.52	19.28	19.74	17.68	18.43	18.16	18.91	19.38
	6H	18.77	19.41	19.28	19.91	20.40	18.40	19.04	18.91	19.54	20.03
	8H	19.09	19.65	19.59	20.14	20.70	18.71	19.27	19.22	19.76	20.32