

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331649-930

Luminaire Tested: **S122RDIP-S485D330U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331649-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S485D330U930-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2339.6 lumens  
Efficiency: N/A  
Efficacy: 85.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331649-930

CATALOG NUMBER: S122RDIP-S485D330U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331649-930

CATALOG NUMBER: S122RDIP-S485D330U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48	44
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41	38
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36	33
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	35	32	29
6	66	54	46	40	61	51	44	39	45	39	35	40	35	32	35	31	28	26
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21	19
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10863	10863	10863
5°	10904	10728	10786
10°	10822	10552	10462
15°	10696	10238	9944
20°	10524	9792	9301
25°	10349	9285	8678
30°	10103	8764	7879
35°	9865	8198	7177
40°	9624	7611	6365
45°	9344	6951	5631
50°	9053	6285	4908
55°	8757	5571	4217
60°	8415	4818	3500
65°	8027	4046	3186
70°	7558	3333	2932
75°	6987	3038	2739
80°	6174	2715	2492
85°	4854	2149	2149



TEST NUMBER: P331649-930

CATALOG NUMBER: S122RDIP-S485D330U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.0	2.7
10°-20°	172.9	7.4
20°-30°	242.8	10.4
30°-40°	264.8	11.3
40°-50°	243.5	10.4
50°-60°	191.2	8.2
60°-70°	124.7	5.3
70°-80°	64.3	2.7
80°-90°	18.1	0.8
90°-100°	21.6	0.9
100°-110°	67.2	2.9
110°-120°	114.8	4.9
120°-130°	151.0	6.5
130°-140°	169.5	7.2
140°-150°	166.2	7.1
150°-160°	139.4	6.0
160°-170°	92.4	4.0
170°-180°	32.3	1.4
0°-30°	478.7	20.5
0°-40°	743.5	31.8
0°-60°	1178.2	50.4
0°-90°	1385.2	59.2
90°-120°	203.6	8.7
90°-150°	690.3	29.5
90°-180°	954.0	40.8
0°-180°	2339.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	673	673	673	673	673	
5°	673	670	662	667	666	64
15°	640	632	612	601	595	180
25°	581	560	521	497	487	267
35°	500	468	416	379	364	313
45°	409	367	304	263	247	316
55°	311	263	198	163	150	278
65°	210	160	106	86	83	208
75°	112	71	49	45	44	119
85°	26	14	12	12	12	31
90°	0	4	10	10	10	2
95°	15	18	18	18	18	17
105°	62	63	63	64	64	65
115°	115	117	116	116	115	114
125°	168	170	169	168	168	150
135°	217	220	221	220	220	168
145°	263	265	267	267	266	164
155°	301	302	303	304	303	138
165°	328	327	327	329	328	92
175°	341	340	339	341	340	32
180°	341	341	341	341	341	



TEST NUMBER: P331649-930

CATALOG NUMBER: S122RDIP-S485D330U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	675.2	674.7	674.2	673.6	673.1	672.2	671.1	669.8	668.6	667.5	668.5
5°	672.8	672.1	671.5	670.8	670.1	668.9	667.2	665.4	663.7	661.9	663.1
7.5°	665.9	665.0	664.2	663.3	662.5	661.0	659.0	657.0	654.9	652.9	653.2
10°	660.1	659.1	658.1	657.2	656.2	654.4	651.8	649.0	646.3	643.6	643.2
12.5°	652.7	651.6	650.4	649.2	648.1	645.8	642.3	638.9	635.4	631.9	631.2
15°	639.9	638.5	637.0	635.4	634.0	631.0	626.3	621.7	617.2	612.5	610.0
17.5°	624.3	622.0	619.7	617.4	615.1	611.1	605.2	599.2	593.4	587.4	584.4
20°	612.5	609.8	607.2	604.5	601.7	597.0	590.2	583.4	576.7	569.9	566.6
22.5°	599.9	596.9	593.8	590.8	587.7	582.4	574.8	567.1	559.5	551.9	547.6
25°	580.9	576.6	572.3	567.9	563.5	556.9	548.0	539.1	530.1	521.2	515.7
27.5°	558.0	553.3	548.5	543.9	539.2	531.7	521.7	511.6	501.6	491.5	485.0
30°	541.9	536.8	531.7	526.5	521.4	513.4	502.6	491.7	480.9	470.1	463.2
32.5°	526.4	520.3	514.3	508.3	502.3	493.7	482.7	471.7	460.6	449.6	441.7
35°	500.5	493.6	486.7	479.8	472.9	463.5	451.6	439.7	427.8	415.9	407.3
37.5°	474.7	467.1	459.5	451.9	444.4	434.2	421.6	408.9	396.2	383.5	374.1
40°	456.6	448.6	440.4	432.4	424.2	413.6	400.5	387.3	374.2	361.1	351.5
42.5°	438.1	429.6	421.0	412.5	404.0	392.9	379.4	365.7	352.2	338.7	328.7
45°	409.2	400.1	391.0	382.0	372.9	361.3	347.1	332.9	318.6	304.4	294.8
47.5°	380.9	371.3	361.7	352.1	342.5	330.4	315.7	301.0	286.3	271.7	262.1
50°	360.4	350.8	341.3	331.7	322.0	309.8	294.9	280.1	265.1	250.2	240.9
52.5°	340.5	330.4	320.4	310.4	300.4	288.0	273.5	258.9	244.3	229.8	220.8
55°	311.1	300.6	290.0	279.5	269.0	256.3	241.7	227.1	212.5	197.9	189.8
57.5°	281.0	270.3	259.4	248.6	237.7	225.3	211.3	197.2	183.2	169.2	161.7
60°	260.6	249.8	239.0	228.1	217.3	205.0	191.0	177.1	163.1	149.2	142.3
62.5°	240.6	229.8	219.0	208.1	197.3	185.3	172.0	158.7	145.4	132.2	125.6
65°	210.1	199.1	188.2	177.2	166.2	154.7	142.5	130.3	118.1	105.9	101.3
67.5°	180.6	169.7	158.8	148.0	137.1	126.1	115.2	104.3	93.3	82.3	80.2
70°	160.1	149.6	139.0	128.5	117.9	107.9	98.7	89.3	80.0	70.6	69.3
72.5°	140.6	130.5	120.4	110.3	100.2	91.4	83.9	76.4	68.9	61.4	60.3
75°	112.0	102.6	93.1	83.6	74.1	67.1	62.5	57.9	53.3	48.7	47.8
77.5°	83.9	75.6	67.3	58.9	50.7	45.4	43.2	41.0	38.7	36.5	36.0
80°	66.4	59.4	52.6	45.7	38.7	34.7	33.3	32.0	30.6	29.2	28.7
82.5°	50.3	44.9	39.5	34.2	28.8	25.6	24.7	23.7	22.8	21.9	21.6
85°	26.2	23.3	20.5	17.7	14.8	13.2	12.8	12.4	12.0	11.6	11.6
87.5°	7.8	7.2	6.4	5.7	5.0	4.8	5.1	5.4	5.6	6.0	5.8
90°	0.3	1.1	1.8	2.6	3.3	4.5	5.9	7.3	8.6	10.1	9.9
92.5°	5.1	5.7	6.3	6.8	7.4	7.8	8.2	8.5	8.8	9.1	9.2
95°	15.0	15.7	16.2	16.9	17.5	17.9	18.0	18.2	18.3	18.4	18.4
97.5°	27.4	28.0	28.5	29.0	29.6	30.0	30.2	30.5	30.7	31.0	31.0
100°	36.6	37.1	37.6	38.2	38.6	39.0	39.1	39.4	39.5	39.8	39.8
102.5°	46.2	46.6	47.0	47.5	47.9	48.3	48.4	48.7	48.9	49.2	49.2
105°	62.0	62.1	62.3	62.5	62.7	62.9	63.0	63.1	63.3	63.3	63.5
107.5°	77.7	78.0	78.3	78.6	78.8	79.0	79.0	79.0	79.0	79.0	79.0
110°	87.9	88.2	88.6	89.0	89.4	89.6	89.6	89.6	89.6	89.6	89.6



TEST NUMBER: P331649-930

CATALOG NUMBER: S122RDIP-S485D330U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	98.9	99.3	99.7	100.0	100.4	100.6	100.5	100.5	100.4	100.4	100.3
115°	115.2	115.6	116.0	116.3	116.8	116.9	116.8	116.6	116.5	116.3	116.3
117.5°	131.4	132.0	132.5	133.0	133.5	133.6	133.2	132.9	132.5	132.2	132.0
120°	142.3	142.8	143.3	143.8	144.3	144.3	143.8	143.3	142.8	142.3	142.3
122.5°	152.2	152.8	153.4	154.0	154.7	154.8	154.4	154.1	153.7	153.4	153.2
125°	167.6	168.2	168.8	169.3	169.9	170.2	169.9	169.7	169.6	169.3	169.2
127.5°	182.7	183.4	184.2	184.8	185.6	185.8	185.6	185.4	185.2	184.9	184.7
130°	192.2	193.0	193.8	194.6	195.4	195.8	195.7	195.6	195.4	195.3	195.2
132.5°	202.8	203.4	204.1	204.7	205.5	205.8	205.8	205.9	205.9	205.9	205.6
135°	216.9	217.6	218.3	219.0	219.7	220.1	220.3	220.4	220.5	220.6	220.5
137.5°	231.8	232.4	232.9	233.6	234.2	234.5	234.6	234.8	235.0	235.1	235.1
140°	240.8	241.4	242.0	242.6	243.1	243.5	243.9	244.2	244.5	244.8	244.8
142.5°	250.1	250.6	251.2	251.8	252.3	252.7	252.9	253.2	253.4	253.6	253.6
145°	263.3	263.7	264.2	264.6	265.1	265.5	265.9	266.3	266.6	267.0	267.1
147.5°	275.1	275.7	276.1	276.7	277.2	277.6	277.9	278.2	278.4	278.7	278.8
150°	283.2	283.6	283.9	284.3	284.7	285.0	285.3	285.5	285.8	286.0	286.3
152.5°	290.3	290.7	291.1	291.5	291.8	292.2	292.4	292.8	293.1	293.4	293.7
155°	301.0	301.2	301.4	301.6	301.7	302.0	302.1	302.3	302.6	302.7	303.0
157.5°	310.1	310.3	310.4	310.5	310.7	310.8	311.0	311.0	311.1	311.3	311.7
160°	315.7	315.8	315.9	316.1	316.2	316.3	316.3	316.4	316.5	316.6	316.9
162.5°	320.7	320.8	320.8	320.8	320.9	320.9	321.0	321.1	321.1	321.1	321.6
165°	327.5	327.4	327.3	327.3	327.3	327.2	327.2	327.2	327.2	327.2	327.7
167.5°	333.1	333.0	332.8	332.6	332.4	332.3	332.2	332.2	332.2	332.2	332.6
170°	336.1	336.0	335.7	335.6	335.4	335.3	335.2	335.1	335.1	335.0	335.4
172.5°	338.2	338.0	337.9	337.6	337.5	337.3	337.3	337.2	337.1	337.0	337.5
175°	340.8	340.6	340.4	340.1	340.0	339.8	339.7	339.6	339.4	339.3	339.7
177.5°	341.8	341.6	341.4	341.4	341.2	341.0	341.0	340.9	340.7	340.6	341.0
180°	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4



TEST NUMBER: P331649-930

CATALOG NUMBER: S122RDIP-S485D330U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	669.6	670.7	671.8	672.2	672.1	671.8	671.6	671.4
5°	664.3	665.5	666.8	667.2	666.8	666.3	665.9	665.5
7.5°	653.5	653.9	654.3	654.1	653.4	652.6	652.0	651.3
10°	642.8	642.4	642.0	641.4	640.6	639.8	639.0	638.1
12.5°	630.5	629.7	629.0	627.9	626.6	625.3	623.9	622.6
15°	607.4	604.9	602.3	600.3	598.9	597.6	596.2	594.9
17.5°	581.3	578.3	575.2	572.5	570.2	567.9	565.6	563.2
20°	563.1	559.8	556.4	553.2	550.2	547.2	544.3	541.3
22.5°	543.2	538.8	534.5	531.2	529.0	526.8	524.6	522.3
25°	510.1	504.6	499.0	495.2	493.2	491.1	489.2	487.1
27.5°	478.6	472.1	465.6	460.8	457.5	454.4	451.1	447.9
30°	456.2	449.4	442.5	437.2	433.5	429.9	426.2	422.6
32.5°	433.8	426.0	418.1	412.5	409.0	405.6	402.1	398.7
35°	398.8	390.3	381.8	376.0	373.1	370.1	367.1	364.1
37.5°	364.7	355.3	345.9	339.5	336.1	332.7	329.3	325.9
40°	341.9	332.2	322.6	316.1	312.6	309.1	305.5	302.0
42.5°	318.8	308.8	299.0	292.3	288.9	285.4	282.0	278.6
45°	285.2	275.7	266.0	259.6	256.3	253.1	249.8	246.6
47.5°	252.6	243.0	233.5	227.2	224.3	221.4	218.3	215.4
50°	231.5	222.3	212.9	206.8	204.0	201.1	198.3	195.4
52.5°	211.7	202.8	193.7	187.9	185.3	182.7	180.0	177.4
55°	181.6	173.5	165.4	160.0	157.5	154.9	152.4	149.8
57.5°	154.3	146.8	139.4	134.6	132.4	130.3	128.1	125.9
60°	135.3	128.5	121.6	117.1	114.9	112.7	110.6	108.4
62.5°	119.0	112.4	105.8	101.9	100.6	99.3	98.0	96.7
65°	96.8	92.1	87.6	85.0	84.6	84.2	83.8	83.4
67.5°	78.1	76.0	73.9	72.6	72.2	71.7	71.3	70.8
70°	67.9	66.6	65.2	64.2	63.8	63.2	62.6	62.1
72.5°	59.1	58.0	56.8	56.1	55.8	55.4	55.1	54.8
75°	46.8	45.9	44.9	44.4	44.3	44.1	43.9	43.9
77.5°	35.5	34.9	34.4	34.0	33.8	33.6	33.3	33.1
80°	28.1	27.6	27.1	26.8	26.8	26.8	26.8	26.8
82.5°	21.3	21.0	20.6	20.5	20.5	20.5	20.5	20.5
85°	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.6
87.5°	5.6	5.5	5.4	5.3	5.3	5.4	5.4	5.4
90°	9.9	9.7	9.5	9.5	9.6	9.7	9.7	9.8
92.5°	9.2	9.2	9.3	9.3	9.3	9.3	9.3	9.3
95°	18.4	18.4	18.4	18.3	18.3	18.1	18.0	17.9
97.5°	31.0	31.0	31.0	31.0	31.0	31.0	31.0	30.9
100°	39.8	39.8	39.8	39.7	39.6	39.6	39.5	39.5
102.5°	49.3	49.3	49.4	49.4	49.3	49.2	49.2	49.2
105°	63.6	63.8	63.9	63.9	63.9	63.9	63.9	63.9
107.5°	79.1	79.2	79.2	79.1	78.8	78.5	78.2	77.9
110°	89.6	89.6	89.6	89.5	89.3	89.1	88.9	88.7





TEST NUMBER: P331649-930

CATALOG NUMBER: S122RDIP-S485D330U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	100.1	100.0	99.8	99.6	99.5	99.4	99.2	99.1
115°	116.3	116.2	116.1	116.0	115.8	115.6	115.4	115.2
117.5°	131.8	131.7	131.5	131.3	131.2	131.0	130.8	130.6
120°	142.3	142.3	142.3	142.2	142.0	141.8	141.6	141.5
122.5°	153.0	152.9	152.7	152.6	152.5	152.3	152.1	152.1
125°	169.0	168.8	168.6	168.4	168.4	168.4	168.3	168.2
127.5°	184.5	184.3	184.0	183.8	183.6	183.4	183.2	183.0
130°	195.0	194.9	194.8	194.6	194.4	194.0	193.8	193.6
132.5°	205.3	205.0	204.8	204.6	204.3	204.2	203.9	203.7
135°	220.5	220.5	220.4	220.3	220.0	219.9	219.7	219.5
137.5°	235.1	235.0	235.0	234.8	234.6	234.3	234.1	233.7
140°	244.8	244.8	244.8	244.7	244.4	244.2	243.9	243.7
142.5°	253.7	253.7	253.8	253.7	253.5	253.2	252.9	252.7
145°	267.2	267.2	267.3	267.2	266.9	266.7	266.4	266.1
147.5°	278.9	279.1	279.2	279.2	278.9	278.7	278.4	278.2
150°	286.4	286.6	286.8	286.8	286.6	286.4	286.3	286.0
152.5°	293.9	294.2	294.4	294.4	294.2	293.9	293.7	293.4
155°	303.4	303.7	304.0	304.1	303.9	303.7	303.5	303.3
157.5°	312.1	312.6	313.0	313.1	312.7	312.4	312.2	311.9
160°	317.3	317.7	318.1	318.1	317.9	317.6	317.4	317.2
162.5°	322.0	322.5	322.9	322.9	322.7	322.4	322.0	321.7
165°	328.1	328.6	329.0	329.1	328.7	328.4	328.1	327.8
167.5°	333.1	333.5	334.0	334.1	333.8	333.4	333.0	332.7
170°	335.9	336.3	336.8	336.8	336.5	336.1	335.7	335.3
172.5°	337.9	338.4	338.8	338.9	338.5	338.1	337.8	337.4
175°	340.2	340.6	341.1	341.1	340.8	340.4	340.0	339.6
177.5°	341.3	341.5	341.9	341.9	341.5	341.3	341.0	340.6
180°	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4

(END OF REPORT)