

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331650-930

Luminaire Tested: **S122RDIP-S485D330U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331650-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S485D330U930-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2427.6 lumens  
Efficiency: N/A  
Efficacy: 88.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331650-930

CATALOG NUMBER: S122RDIP-S485D330U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331650-930

CATALOG NUMBER: S122RDIP-S485D330U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	91	84	78	73	85	79	74	69	68	65	61	59	56	54	50	48	46	42
3	84	75	67	62	78	70	64	58	61	56	52	53	49	46	45	42	40	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	32
5	71	59	52	46	66	56	49	43	49	43	39	43	38	35	37	33	31	28
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	34	30	27	25
7	61	49	41	35	57	46	39	34	40	35	31	35	31	28	31	27	25	22
8	56	44	37	31	53	42	35	30	37	31	27	33	28	25	28	25	22	20
9	53	41	33	28	49	38	32	27	34	29	25	30	26	22	26	23	20	18
10	49	37	30	26	46	35	29	24	32	26	22	28	24	20	25	21	18	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10863	10863	10863
5°	10904	10728	10786
10°	10822	10552	10462
15°	10696	10238	9944
20°	10524	9792	9301
25°	10349	9285	8678
30°	10103	8764	7879
35°	9865	8198	7177
40°	9624	7611	6365
45°	9344	6951	5631
50°	9053	6285	4908
55°	8757	5571	4217
60°	8415	4818	3500
65°	8027	4046	3186
70°	7558	3333	2932
75°	6987	3038	2739
80°	6174	2715	2492
85°	4854	2149	2149



TEST NUMBER: P331650-930

CATALOG NUMBER: S122RDIP-S485D330U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.0	2.6
10°-20°	172.9	7.1
20°-30°	242.8	10.0
30°-40°	264.8	10.9
40°-50°	243.5	10.0
50°-60°	191.2	7.9
60°-70°	124.7	5.1
70°-80°	64.3	2.6
80°-90°	18.0	0.7
90°-100°	59.9	2.5
100°-110°	203.2	8.4
110°-120°	215.9	8.9
120°-130°	177.7	7.3
130°-140°	142.7	5.9
140°-150°	107.9	4.4
150°-160°	75.8	3.1
160°-170°	44.6	1.8
170°-180°	14.5	0.6
0°-30°	478.7	19.7
0°-40°	743.5	30.6
0°-60°	1178.2	48.5
0°-90°	1385.2	57.1
90°-120°	479.1	19.7
90°-150°	907.4	37.4
90°-180°	1042.0	42.9
0°-180°	2427.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	673	673	673	673	673	
5°	673	670	662	667	666	64
15°	640	632	612	601	595	180
25°	581	560	521	497	487	267
35°	500	468	416	379	364	313
45°	409	367	304	263	247	316
55°	311	263	198	163	150	278
65°	210	160	106	86	83	208
75°	112	71	49	45	44	119
85°	26	14	12	12	12	31
90°	0	4	10	9	10	2
95°	10	25	113	43	33	11
105°	35	53	213	382	325	37
115°	62	78	179	369	427	61
125°	86	102	172	299	347	77
135°	101	121	170	251	287	78
145°	116	133	169	210	229	73
155°	132	142	164	185	193	61
165°	144	148	157	166	169	40
175°	150	150	151	153	152	14
180°	150	150	150	150	150	



TEST NUMBER: P331650-930

CATALOG NUMBER: S122RDIP-S485D330U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	675.2	674.7	674.2	673.6	673.1	672.2	671.1	669.8	668.6	667.5	668.5
5°	672.8	672.1	671.5	670.8	670.1	668.9	667.2	665.4	663.7	661.9	663.1
7.5°	665.9	665.0	664.2	663.3	662.5	661.0	659.0	657.0	654.9	652.9	653.2
10°	660.1	659.1	658.1	657.2	656.2	654.4	651.8	649.0	646.3	643.6	643.2
12.5°	652.7	651.6	650.4	649.2	648.1	645.8	642.3	638.9	635.4	631.9	631.2
15°	639.9	638.5	637.0	635.4	634.0	631.0	626.3	621.7	617.2	612.5	610.0
17.5°	624.3	622.0	619.7	617.4	615.1	611.1	605.2	599.2	593.4	587.4	584.4
20°	612.5	609.8	607.2	604.5	601.7	597.0	590.2	583.4	576.7	569.9	566.6
22.5°	599.9	596.9	593.8	590.8	587.7	582.4	574.8	567.1	559.5	551.9	547.6
25°	580.9	576.6	572.3	567.9	563.5	556.9	548.0	539.1	530.1	521.2	515.7
27.5°	558.0	553.3	548.5	543.9	539.2	531.7	521.7	511.6	501.6	491.5	485.0
30°	541.9	536.8	531.7	526.5	521.4	513.4	502.6	491.7	480.9	470.1	463.2
32.5°	526.4	520.3	514.3	508.3	502.3	493.7	482.7	471.7	460.6	449.6	441.7
35°	500.5	493.6	486.7	479.8	472.9	463.5	451.6	439.7	427.8	415.9	407.3
37.5°	474.7	467.1	459.5	451.9	444.4	434.2	421.6	408.9	396.2	383.5	374.1
40°	456.6	448.6	440.4	432.4	424.2	413.6	400.5	387.3	374.2	361.1	351.5
42.5°	438.1	429.6	421.0	412.5	404.0	392.9	379.4	365.7	352.2	338.7	328.7
45°	409.2	400.1	391.0	382.0	372.9	361.3	347.1	332.9	318.6	304.4	294.8
47.5°	380.9	371.3	361.7	352.1	342.5	330.4	315.7	301.0	286.3	271.7	262.1
50°	360.4	350.8	341.3	331.7	322.0	309.8	294.9	280.1	265.1	250.2	240.9
52.5°	340.5	330.4	320.4	310.4	300.4	288.0	273.5	258.9	244.3	229.8	220.8
55°	311.1	300.6	290.0	279.5	269.0	256.3	241.7	227.1	212.5	197.9	189.8
57.5°	281.0	270.3	259.4	248.6	237.7	225.3	211.3	197.2	183.2	169.2	161.7
60°	260.6	249.8	239.0	228.1	217.3	205.0	191.0	177.1	163.1	149.2	142.3
62.5°	240.6	229.8	219.0	208.1	197.3	185.3	172.0	158.7	145.4	132.2	125.6
65°	210.1	199.1	188.2	177.2	166.2	154.7	142.5	130.3	118.1	105.9	101.3
67.5°	180.6	169.7	158.8	148.0	137.1	126.1	115.2	104.3	93.3	82.3	80.2
70°	160.1	149.6	139.0	128.5	117.9	107.9	98.7	89.3	80.0	70.6	69.3
72.5°	140.6	130.5	120.4	110.3	100.2	91.4	83.9	76.4	68.9	61.4	60.3
75°	112.0	102.6	93.1	83.6	74.1	67.1	62.5	57.9	53.3	48.7	47.8
77.5°	83.9	75.6	67.3	58.9	50.7	45.4	43.2	41.0	38.7	36.5	36.0
80°	66.4	59.4	52.6	45.7	38.7	34.7	33.3	32.0	30.6	29.2	28.7
82.5°	50.3	44.9	39.5	34.2	28.8	25.6	24.7	23.7	22.8	21.9	21.6
85°	26.2	23.3	20.5	17.7	14.8	13.2	12.8	12.4	12.0	11.6	11.6
87.5°	7.8	7.2	6.5	5.8	5.1	4.7	5.1	5.5	5.8	5.9	5.7
90°	0.3	1.1	2.3	2.9	3.4	4.3	5.8	7.7	9.5	9.8	9.5
92.5°	3.5	5.1	7.2	8.4	10.4	13.0	19.6	28.8	36.9	37.4	31.6
95°	10.1	11.3	14.1	16.7	21.3	28.2	41.5	66.5	100.0	112.9	98.8
97.5°	16.4	17.9	21.0	24.9	30.2	38.1	54.7	89.7	145.2	192.7	202.2
100°	22.2	23.1	25.6	30.2	36.0	44.1	59.4	94.5	156.7	227.6	269.0
102.5°	27.5	28.1	30.7	35.3	41.3	49.4	63.5	94.7	152.3	228.7	293.9
105°	35.1	36.3	38.3	42.6	49.0	57.1	70.6	96.2	143.7	213.4	290.1
107.5°	43.5	44.4	46.3	50.3	56.6	64.7	77.9	100.2	139.5	197.1	264.8
110°	49.0	50.1	51.9	55.6	61.6	70.0	82.7	103.4	138.6	189.2	248.9



TEST NUMBER: P331650-930

CATALOG NUMBER: S122RDIP-S485D330U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	54.1	55.2	57.2	60.7	66.4	75.1	87.3	106.9	138.8	184.2	237.8
115°	62.0	63.3	65.1	68.6	74.4	82.1	94.5	112.0	140.0	178.6	224.1
117.5°	70.1	71.3	73.0	76.1	81.6	89.7	101.1	117.6	142.1	175.9	215.5
120°	75.2	76.3	78.1	80.6	86.4	94.5	105.7	121.3	143.5	174.3	210.8
122.5°	80.1	81.0	82.7	85.5	91.2	99.5	110.1	124.5	145.0	173.3	206.9
125°	86.4	87.3	89.0	92.5	98.2	106.3	116.7	129.6	147.5	171.7	201.4
127.5°	91.5	92.6	95.1	98.9	104.4	112.7	122.8	134.4	149.9	170.7	196.2
130°	94.5	95.6	98.5	102.6	108.4	116.3	126.5	137.4	151.8	170.2	192.7
132.5°	97.3	98.7	101.7	106.0	112.0	120.1	129.7	140.4	153.7	170.0	190.0
135°	101.4	102.6	106.0	110.3	117.0	125.0	134.3	144.3	155.9	169.7	186.1
137.5°	105.3	106.7	110.1	114.8	121.3	128.8	137.9	147.3	157.8	169.6	183.4
140°	108.4	109.5	112.9	117.6	123.8	131.3	140.0	149.0	158.7	169.4	181.7
142.5°	111.3	112.3	115.4	120.1	126.2	133.2	141.6	150.3	159.4	169.4	180.2
145°	115.8	117.0	119.8	124.2	130.0	136.2	144.1	152.1	160.1	168.8	178.1
147.5°	120.7	121.5	124.3	128.2	133.1	138.7	146.0	153.1	160.4	167.8	175.9
150°	123.8	124.7	127.0	130.8	135.1	140.3	146.9	153.5	160.1	167.1	174.0
152.5°	127.1	127.5	129.8	133.1	137.2	141.9	147.8	153.8	159.7	165.9	172.4
155°	131.7	131.9	133.6	136.8	140.0	144.3	149.2	154.1	159.0	163.9	169.4
157.5°	135.4	135.7	137.1	139.9	142.4	146.0	150.2	154.1	157.7	161.8	166.6
160°	137.9	138.3	139.4	141.7	144.1	147.2	150.7	154.1	157.0	160.5	164.4
162.5°	140.6	140.3	141.5	143.3	145.4	147.9	150.9	153.8	156.3	159.3	162.7
165°	143.5	143.2	143.7	145.4	146.9	148.6	151.2	153.3	155.0	157.0	159.6
167.5°	145.9	145.5	146.0	147.2	148.2	149.3	151.2	152.9	153.7	155.0	156.6
170°	147.5	146.9	147.2	148.1	148.6	149.5	150.9	152.4	153.0	153.8	155.0
172.5°	148.4	148.1	147.9	148.8	149.1	149.8	150.7	151.7	152.1	152.5	153.4
175°	149.5	149.2	149.0	149.5	149.5	149.8	150.3	150.9	150.7	150.9	151.2
177.5°	150.0	149.5	149.4	149.8	149.8	149.8	150.0	150.5	150.0	149.8	150.0
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8



TEST NUMBER: P331650-930

CATALOG NUMBER: S122RDIP-S485D330U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	669.6	670.7	671.8	672.2	672.1	671.8	671.6	671.4
5°	664.3	665.5	666.8	667.2	666.8	666.3	665.9	665.5
7.5°	653.5	653.9	654.3	654.1	653.4	652.6	652.0	651.3
10°	642.8	642.4	642.0	641.4	640.6	639.8	639.0	638.1
12.5°	630.5	629.7	629.0	627.9	626.6	625.3	623.9	622.6
15°	607.4	604.9	602.3	600.3	598.9	597.6	596.2	594.9
17.5°	581.3	578.3	575.2	572.5	570.2	567.9	565.6	563.2
20°	563.1	559.8	556.4	553.2	550.2	547.2	544.3	541.3
22.5°	543.2	538.8	534.5	531.2	529.0	526.8	524.6	522.3
25°	510.1	504.6	499.0	495.2	493.2	491.1	489.2	487.1
27.5°	478.6	472.1	465.6	460.8	457.5	454.4	451.1	447.9
30°	456.2	449.4	442.5	437.2	433.5	429.9	426.2	422.6
32.5°	433.8	426.0	418.1	412.5	409.0	405.6	402.1	398.7
35°	398.8	390.3	381.8	376.0	373.1	370.1	367.1	364.1
37.5°	364.7	355.3	345.9	339.5	336.1	332.7	329.3	325.9
40°	341.9	332.2	322.6	316.1	312.6	309.1	305.5	302.0
42.5°	318.8	308.8	299.0	292.3	288.9	285.4	282.0	278.6
45°	285.2	275.7	266.0	259.6	256.3	253.1	249.8	246.6
47.5°	252.6	243.0	233.5	227.2	224.3	221.4	218.3	215.4
50°	231.5	222.3	212.9	206.8	204.0	201.1	198.3	195.4
52.5°	211.7	202.8	193.7	187.9	185.3	182.7	180.0	177.4
55°	181.6	173.5	165.4	160.0	157.5	154.9	152.4	149.8
57.5°	154.3	146.8	139.4	134.6	132.4	130.3	128.1	125.9
60°	135.3	128.5	121.6	117.1	114.9	112.7	110.6	108.4
62.5°	119.0	112.4	105.8	101.9	100.6	99.3	98.0	96.7
65°	96.8	92.1	87.6	85.0	84.6	84.2	83.8	83.4
67.5°	78.1	76.0	73.9	72.6	72.2	71.7	71.3	70.8
70°	67.9	66.6	65.2	64.2	63.8	63.2	62.6	62.1
72.5°	59.1	58.0	56.8	56.1	55.8	55.4	55.1	54.8
75°	46.8	45.9	44.9	44.4	44.3	44.1	43.9	43.9
77.5°	35.5	34.9	34.4	34.0	33.8	33.6	33.3	33.1
80°	28.1	27.6	27.1	26.8	26.8	26.8	26.8	26.8
82.5°	21.3	21.0	20.6	20.5	20.5	20.5	20.5	20.5
85°	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.6
87.5°	5.5	5.3	5.3	5.3	5.3	5.3	5.3	5.3
90°	9.2	8.6	9.2	9.5	9.5	9.5	9.5	9.5
92.5°	25.1	21.5	19.2	17.4	17.1	16.2	16.4	16.0
95°	75.5	57.9	45.8	39.5	35.7	33.4	32.5	32.9
97.5°	176.1	144.1	112.9	92.1	78.4	71.3	67.1	64.7
100°	263.0	227.3	187.8	153.0	129.1	116.7	108.4	103.1
102.5°	319.9	311.9	283.0	246.1	220.0	198.9	188.5	181.5
105°	350.0	382.5	386.3	376.8	358.9	341.0	328.6	324.7
107.5°	328.3	377.4	407.3	421.3	423.5	422.6	420.0	414.7
110°	309.7	361.3	398.1	421.8	434.1	439.6	442.2	441.9





TEST NUMBER: P331650-930

CATALOG NUMBER: S122RDIP-S485D330U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	292.6	342.1	381.5	408.6	425.8	435.0	439.9	441.4
115°	271.7	316.0	353.8	383.4	403.9	417.1	424.6	427.2
117.5°	255.8	294.8	329.1	356.9	377.7	391.8	399.6	401.8
120°	248.0	283.7	314.3	340.5	360.7	374.2	382.5	385.5
122.5°	241.8	274.5	303.5	327.1	345.2	358.6	366.0	368.4
125°	232.8	262.4	287.8	309.4	326.1	337.0	344.2	346.6
127.5°	223.8	250.7	274.6	294.5	309.1	319.4	325.5	327.4
130°	218.1	242.9	265.6	284.6	298.7	308.5	314.3	316.6
132.5°	212.5	235.5	256.4	274.3	288.1	297.9	303.2	305.3
135°	204.8	223.8	242.9	258.9	271.3	280.9	286.1	287.2
137.5°	198.7	214.6	229.7	243.7	255.0	263.2	267.7	269.5
140°	194.7	208.6	221.8	234.5	243.7	251.2	255.5	257.2
142.5°	191.5	203.3	214.7	225.3	234.0	240.8	244.7	245.0
145°	186.9	196.5	205.4	213.8	220.6	225.6	228.4	229.3
147.5°	183.4	190.9	197.9	204.0	209.7	213.6	215.6	216.1
150°	180.9	187.3	193.3	198.4	202.8	206.3	208.0	208.3
152.5°	178.4	184.3	189.4	193.9	197.3	200.2	201.5	201.6
155°	174.9	179.4	183.8	186.9	190.1	192.2	193.3	192.7
157.5°	170.8	174.6	178.2	180.8	183.0	184.7	185.2	185.2
160°	168.2	171.4	174.6	176.6	178.6	180.0	180.3	180.3
162.5°	165.7	168.4	171.1	172.7	174.7	175.7	175.9	175.7
165°	161.9	163.9	165.9	167.1	168.2	169.4	169.4	169.1
167.5°	158.2	159.8	161.2	162.2	162.7	163.4	163.3	163.0
170°	156.5	157.3	158.4	159.0	159.3	160.1	159.9	159.3
172.5°	154.3	155.0	155.9	156.2	156.5	156.9	156.6	156.3
175°	152.1	152.4	152.7	153.0	153.0	153.3	153.0	152.4
177.5°	150.5	150.5	150.7	150.7	150.7	150.7	150.5	150.0
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8

(END OF REPORT)