

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931536

Luminaire Tested: DFN2DS-TR4F0-090DS835-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931536
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-090DS835-RLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7650.0 lumens
Efficiency: N/A
Efficacy: 81.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 93.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931536

CATALOG NUMBER: DFN2DS-TR4F0-090DS835-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931536

CATALOG NUMBER: DFN2DS-TR4F0-090DS835-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2955	2955	2955
5°	2966	2918	2934
10°	2944	2870	2846
15°	2910	2785	2705
20°	2863	2664	2530
25°	2815	2526	2360
30°	2748	2384	2143
35°	2684	2230	1952
40°	2618	2070	1732
45°	2542	1891	1532
50°	2463	1710	1336
55°	2382	1515	1147
60°	2289	1310	952
65°	2183	1101	867
70°	2057	907	797
75°	1901	827	744
80°	1678	738	678
85°	1318	582	582

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2542 cd/sqm

TEST NUMBER: P931536

CATALOG NUMBER: DFN2DS-TR4F0-090DS835-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	348.6	4.6
10°-20°	957.0	12.5
20°-30°	1343.6	17.6
30°-40°	1464.6	19.1
40°-50°	1346.2	17.6
50°-60°	1057.2	13.8
60°-70°	688.1	9.0
70°-80°	354.2	4.6
80°-90°	90.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2649.2	34.6
0°-40°	4113.9	53.8
0°-60°	6517.2	85.2
0°-90°	7650.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7650.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3720	3720	3720	3720	3720	
5°	3720	3703	3659	3689	3679	353
15°	3538	3501	3386	3322	3289	997
25°	3212	3104	2882	2744	2693	1477
35°	2767	2595	2299	2087	2013	1732
45°	2262	2036	1683	1444	1363	1747
55°	1720	1458	1094	892	828	1537
65°	1161	889	586	471	461	1151
75°	619	384	269	246	242	655
85°	145	74	64	64	64	173
90°	0	0	0	0	0	

TEST NUMBER: P931536

CATALOG NUMBER: DFN2DS-TR4F0-090DS835-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3719.7	3719.7	3719.7	3719.7	3719.7
2.5°	3736.5	3719.7	3682.5	3716.5	3709.7
5°	3719.7	3702.9	3659.0	3689.3	3679.3
7.5°	3689.3	3669.3	3622.2	3635.4	3618.6
10°	3649.0	3625.4	3558.3	3547.9	3527.9
12.5°	3598.6	3568.3	3477.2	3457.2	3420.0
15°	3537.9	3500.8	3386.5	3322.5	3289.0
17.5°	3467.2	3413.3	3271.8	3197.9	3144.0
20°	3386.5	3319.0	3150.7	3066.8	2992.5
22.5°	3299.0	3221.5	3026.1	2911.8	2861.5
25°	3211.5	3103.6	2881.5	2743.6	2692.9
27.5°	3107.2	2992.5	2746.8	2588.6	2511.1
30°	2996.1	2867.9	2598.6	2427.2	2336.1
32.5°	2888.2	2733.2	2457.5	2255.4	2171.1
35°	2767.2	2595.4	2299.3	2087.2	2012.9
37.5°	2649.3	2464.0	2151.1	1918.6	1834.7
40°	2524.7	2322.9	1996.1	1757.2	1669.7
42.5°	2396.8	2181.5	1841.4	1592.2	1508.2
45°	2262.2	2036.5	1683.2	1443.9	1363.2
47.5°	2134.3	1895.4	1531.8	1292.5	1218.6
50°	1992.9	1753.9	1383.6	1151.1	1080.7
52.5°	1854.7	1602.2	1242.2	1020.0	956.1
55°	1720.0	1457.5	1093.9	892.2	828.2
57.5°	1582.2	1312.9	962.9	774.3	720.4
60°	1440.7	1171.4	824.7	653.2	599.3
62.5°	1302.9	1033.6	706.8	545.4	518.6
65°	1161.4	888.6	585.7	471.4	461.1
67.5°	1026.8	753.9	471.4	413.9	403.9
70°	885.4	622.9	390.4	356.8	343.2
72.5°	750.7	501.4	326.4	299.6	292.9
75°	619.3	383.6	269.3	245.7	242.5
77.5°	488.2	272.5	212.1	198.6	191.8
80°	366.8	195.4	161.4	148.2	148.2
82.5°	255.7	131.4	111.1	104.3	104.3
85°	144.6	73.9	63.9	63.9	63.9
87.5°	53.9	26.8	26.8	23.6	23.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931536

CATALOG NUMBER: DFN2DS-TR4F0-090DS835-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.00	16.52	15.36	16.83	17.15	10.96	12.48	11.32	12.80	13.11
	3H	16.76	18.13	17.14	18.46	18.82	12.22	13.59	12.60	13.92	14.28
	4H	17.43	18.71	17.83	19.06	19.44	12.73	14.01	13.13	14.36	14.73
	6H	17.92	19.10	18.33	19.47	19.86	13.11	14.29	13.52	14.66	15.05
	8H	18.09	19.21	18.51	19.60	20.00	13.23	14.36	13.66	14.75	15.15
	12H	18.19	19.27	18.62	19.65	20.08	13.31	14.39	13.74	14.77	15.20
4H	2H	15.10	16.38	15.50	16.73	17.11	11.66	12.94	12.06	13.28	13.66
	3H	17.04	18.10	17.45	18.50	18.90	13.10	14.16	13.51	14.56	14.96
	4H	17.79	18.74	18.22	19.16	19.60	13.70	14.65	14.13	15.07	15.51
	6H	18.38	19.21	18.84	19.65	20.11	14.19	15.02	14.64	15.46	15.92
	8H	18.59	19.37	19.06	19.81	20.28	14.35	15.13	14.81	15.57	16.04
	12H	18.75	19.44	19.23	19.92	20.39	14.47	15.16	14.95	15.64	16.11
8H	4H	17.81	18.59	18.27	19.03	19.50	14.05	14.83	14.51	15.27	15.74
	6H	18.45	19.09	18.94	19.58	20.06	14.64	15.28	15.13	15.77	16.25
	8H	18.70	19.27	19.21	19.78	20.27	14.86	15.44	15.37	15.95	16.43
	12H	18.90	19.41	19.41	19.90	20.47	15.04	15.55	15.55	16.04	16.60
12H	4H	17.79	18.49	18.28	18.97	19.44	14.09	14.79	14.58	15.27	15.74
	6H	18.43	19.01	18.94	19.52	20.00	14.70	15.28	15.22	15.79	16.28
	8H	18.71	19.22	19.22	19.71	20.28	14.97	15.48	15.48	15.98	16.54