

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331420

Luminaire Tested: **S122DIP-S1005D330U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331420
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S1005D330U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5709.9 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331420

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331420

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	105	100	97	93	100	96	93	90	88	85	83	80	78	76	73	71	70	66
2	96	89	83	77	91	85	79	75	78	73	70	71	68	65	65	62	60	57
3	88	79	71	65	84	75	69	63	69	64	59	64	59	56	58	55	52	49
4	81	70	62	56	77	67	60	55	62	56	51	57	52	48	53	49	45	43
5	75	63	55	49	71	61	53	48	56	50	45	52	47	43	48	44	40	38
6	69	57	49	43	66	55	47	42	51	45	40	47	42	38	44	39	36	33
7	64	52	44	38	61	50	43	37	47	40	36	43	38	34	40	36	32	30
8	60	48	40	34	57	46	39	34	43	37	32	40	34	31	37	32	29	27
9	56	44	36	31	54	42	35	30	39	33	29	37	32	28	34	30	26	25
10	53	40	33	28	50	39	32	28	37	31	26	34	29	25	32	27	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	32195	32195	32195	32195
5°	36094	32405	28716	32405
10°	41361	32139	24851	32139
15°	45757	31550	21956	31550
20°	45060	30917	20015	30917
25°	40631	30077	18786	30077
30°	33575	28732	17889	28732
35°	24471	27325	17251	27325
40°	19545	25665	16895	25665
45°	17080	23745	16413	23745
50°	16053	21886	16093	21886
55°	14798	19997	15662	19997
60°	13563	17990	14996	17990
65°	12355	16191	14346	16191
70°	11216	14436	13388	14436
75°	9944	12477	11859	12477
80°	8554	10330	9549	10330
85°	7669	7669	5687	7669



TEST NUMBER: P331420

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.9	3.3
10°-20°	552.1	9.7
20°-30°	801.2	14.0
30°-40°	845.5	14.8
40°-50°	748.6	13.1
50°-60°	597.4	10.5
60°-70°	406.1	7.1
70°-80°	208.2	3.6
80°-90°	51.3	0.9
90°-100°	14.9	0.3
100°-110°	54.7	1.0
110°-120°	146.1	2.6
120°-130°	241.2	4.2
130°-140°	256.5	4.5
140°-150°	238.4	4.2
150°-160°	191.7	3.4
160°-170°	123.5	2.2
170°-180°	42.5	0.7
0°-30°	1543.2	27.0
0°-40°	2388.7	41.8
0°-60°	3734.8	65.4
0°-90°	4400.4	77.1
90°-120°	215.7	3.8
90°-150°	951.8	16.7
90°-180°	1309.0	22.9
0°-180°	5709.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1994	1994	1994	1994	1994	
5°	2227	1999	1772	1999	2227	222
15°	2737	1888	1314	1888	2737	755
25°	2281	1688	1054	1688	2281	1031
35°	1242	1386	875	1386	1242	807
45°	748	1040	719	1040	748	588
55°	526	710	556	710	526	471
65°	323	424	376	424	323	322
75°	159	200	190	200	159	170
85°	41	41	31	41	41	46
90°	9	0	9	0	9	6
95°	14	21	14	21	14	13
105°	25	98	25	98	25	26
115°	26	186	26	186	26	66
125°	276	263	276	263	276	239
135°	336	325	336	325	336	259
145°	383	377	383	377	383	240
155°	416	416	416	416	416	192
165°	437	438	437	438	437	123
175°	445	448	445	448	445	42
180°	447	447	447	447	447	



TEST NUMBER: P331420

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2086.0	2086.6	2087.8	2078.0	2076.8	2076.8	2068.2	2060.9	2052.3	2040.6	2041.9
5°	2227.0	2235.4	2238.5	2229.3	2215.5	2214.0	2201.0	2179.5	2159.6	2143.5	2132.0
7.5°	2395.3	2398.7	2391.2	2379.1	2368.8	2350.4	2326.2	2302.4	2269.2	2238.7	2216.0
10°	2522.8	2527.4	2514.4	2496.8	2482.2	2460.8	2425.5	2389.5	2345.8	2303.7	2269.9
12.5°	2619.7	2631.0	2614.3	2612.0	2587.1	2557.6	2515.6	2497.4	2435.9	2377.2	2341.1
15°	2737.4	2736.6	2738.2	2723.6	2705.2	2700.6	2656.2	2607.9	2521.3	2486.8	2427.0
17.5°	2703.4	2715.0	2720.4	2720.2	2719.8	2716.9	2702.6	2672.1	2628.7	2572.8	2503.8
20°	2622.5	2637.8	2640.1	2657.7	2667.7	2680.7	2686.1	2677.6	2650.8	2604.1	2544.3
22.5°	2497.4	2501.7	2508.9	2536.3	2557.9	2590.6	2607.6	2635.9	2625.7	2602.8	2552.9
25°	2280.7	2273.0	2299.8	2313.6	2363.4	2415.5	2453.1	2494.5	2531.3	2553.5	2538.9
27.5°	2020.4	2008.9	2049.1	2085.7	2126.2	2182.6	2241.1	2310.2	2367.7	2439.6	2464.3
30°	1800.9	1807.8	1846.1	1885.2	1946.5	2026.2	2092.1	2168.0	2250.0	2330.5	2386.4
32.5°	1564.3	1590.8	1615.0	1674.9	1728.9	1817.8	1914.3	2009.2	2111.5	2203.0	2289.6
35°	1241.5	1272.1	1305.9	1349.5	1425.4	1513.5	1607.8	1735.8	1875.3	2000.2	2102.9
37.5°	1045.0	1040.1	1059.4	1091.0	1152.4	1223.6	1332.1	1458.5	1622.7	1769.5	1914.3
40°	927.3	924.2	938.0	967.1	1013.9	1066.0	1161.0	1272.1	1424.6	1604.0	1776.4
42.5°	846.4	848.2	855.9	876.4	908.4	951.3	1022.5	1117.0	1256.7	1425.6	1610.9
45°	748.0	753.3	761.8	771.7	790.1	825.4	865.2	932.7	1043.0	1184.0	1366.4
47.5°	677.1	677.3	685.9	694.6	705.5	725.4	757.9	800.2	878.1	992.9	1149.7
50°	639.1	633.8	639.9	646.8	658.3	672.1	693.5	733.4	785.5	878.2	1009.3
52.5°	592.5	592.7	598.2	600.8	611.1	624.9	644.5	672.1	719.3	791.8	899.5
55°	525.7	529.5	532.6	537.2	546.4	556.4	571.7	590.1	626.9	681.3	761.0
57.5°	462.9	464.1	467.2	475.9	481.7	490.9	505.5	522.2	546.1	586.4	646.3
60°	420.0	420.0	426.1	429.9	437.6	446.8	458.3	474.4	495.8	528.8	577.1
62.5°	380.7	380.1	382.6	388.8	394.7	403.3	414.7	428.4	448.6	477.9	517.6
65°	323.4	321.9	326.5	328.0	334.1	342.6	351.8	366.3	382.4	403.9	439.1
67.5°	268.2	270.1	272.5	275.4	278.8	287.7	293.8	304.1	317.7	335.5	359.4
70°	237.6	237.6	237.6	239.9	244.5	249.1	255.2	263.6	276.7	292.0	313.4
72.5°	203.2	205.7	208.1	206.8	212.6	215.3	222.7	227.5	239.9	249.7	268.7
75°	159.4	159.4	159.4	163.2	165.5	167.8	172.4	177.0	183.2	195.4	205.4
77.5°	118.9	118.6	119.4	120.3	122.8	125.5	126.9	131.0	136.7	142.4	150.8
80°	92.0	93.5	94.3	95.8	95.8	97.3	98.1	103.5	107.3	111.1	116.5
82.5°	71.1	71.4	71.6	71.9	72.5	73.4	75.4	77.1	78.5	81.7	85.8
85°	41.4	40.6	40.6	42.1	41.4	41.4	42.9	44.4	44.4	45.2	47.5
87.5°	17.7	17.7	18.2	17.6	17.6	18.1	18.1	17.4	17.9	18.5	19.0
90°	8.7	8.6	8.4	8.3	8.2	7.9	7.5	7.2	6.8	6.5	5.9
92.5°	8.7	8.6	8.6	8.5	8.4	8.2	8.1	7.9	7.7	7.5	7.2
95°	13.9	14.0	14.0	14.1	14.2	14.0	13.7	13.3	13.0	12.6	12.1
97.5°	18.6	18.5	18.4	18.3	18.2	18.0	17.7	17.5	17.2	16.9	15.7
100°	21.7	21.5	21.4	21.2	21.1	20.7	20.2	19.6	19.0	18.4	17.2
102.5°	23.2	23.0	22.8	22.6	22.4	21.9	21.2	20.4	19.7	18.9	29.2
105°	24.6	24.3	24.0	23.7	23.4	22.9	22.1	21.3	20.5	19.7	39.3
107.5°	25.3	25.0	24.7	24.4	24.1	24.4	25.2	26.0	26.8	27.6	51.1
110°	25.5	25.3	25.0	24.7	24.4	27.8	35.0	42.2	49.4	56.6	77.3



TEST NUMBER: P331420

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	25.8	25.6	25.3	25.1	24.9	37.9	64.1	90.3	116.5	142.7	147.8
115°	26.5	31.7	36.9	42.0	47.2	66.4	99.7	133.0	166.2	199.5	197.7
117.5°	108.3	125.3	142.3	159.3	176.3	188.8	196.8	204.9	212.9	221.0	219.7
120°	197.2	206.9	216.6	226.3	236.0	240.4	239.6	238.7	237.9	237.0	235.7
122.5°	246.1	248.0	249.9	251.8	253.6	254.3	253.8	253.3	252.8	252.3	250.9
125°	276.4	276.2	276.0	275.8	275.6	275.2	274.7	274.2	273.7	273.2	271.8
127.5°	295.6	295.5	295.5	295.5	295.4	295.0	294.3	293.6	292.8	292.1	291.1
130°	307.5	307.6	307.6	307.7	307.8	307.4	306.6	305.8	305.0	304.3	303.5
132.5°	319.1	319.2	319.3	319.3	319.4	319.1	318.4	317.8	317.1	316.4	315.6
135°	335.9	336.1	336.2	336.4	336.5	336.2	335.5	334.8	334.1	333.4	332.7
137.5°	351.3	351.5	351.8	352.0	352.2	352.0	351.3	350.6	349.9	349.2	348.5
140°	360.8	361.2	361.6	361.9	362.3	362.1	361.5	360.8	360.2	359.5	358.8
142.5°	370.1	370.5	370.9	371.2	371.6	371.5	370.9	370.3	369.7	369.1	368.2
145°	383.1	383.5	383.9	384.2	384.6	384.5	384.0	383.5	383.0	382.5	381.3
147.5°	394.6	394.9	395.2	395.5	395.8	395.8	395.4	395.0	394.6	394.3	393.1
150°	401.6	401.9	402.3	402.7	403.0	403.0	402.5	402.1	401.7	401.3	400.1
152.5°	407.5	408.0	408.5	408.9	409.4	409.4	409.0	408.6	408.1	407.7	406.6
155°	415.8	416.4	417.0	417.5	418.1	418.2	417.7	417.3	416.9	416.4	415.6
157.5°	423.4	423.9	424.5	425.0	425.6	425.6	425.2	424.7	424.2	423.7	423.1
160°	427.8	428.3	428.8	429.3	429.8	429.8	429.4	429.0	428.5	428.1	427.7
162.5°	431.4	432.0	432.6	433.2	433.9	433.9	433.4	432.9	432.5	432.0	431.6
165°	436.8	437.3	437.8	438.3	438.8	438.8	438.3	437.8	437.3	436.8	436.6
167.5°	440.2	440.9	441.5	442.2	442.8	442.9	442.4	441.9	441.4	440.9	440.7
170°	442.3	443.0	443.6	444.3	444.9	445.0	444.5	444.0	443.5	443.0	442.8
172.5°	443.9	444.5	445.2	445.8	446.5	446.5	446.0	445.5	445.0	444.5	444.4
175°	445.2	445.9	446.7	447.4	448.1	448.2	447.7	447.2	446.7	446.2	446.1
177.5°	446.1	446.6	447.1	447.6	448.1	448.2	447.8	447.4	447.0	446.6	446.5
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331420

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2046.2	2041.3	2038.2	2027.2	2017.3	2007.5	2004.5	2005.7	1992.2	1979.3	1973.8
5°	2125.9	2110.5	2096.0	2075.3	2050.8	2023.9	2010.1	1999.4	1972.6	1943.5	1926.6
7.5°	2197.3	2175.4	2147.3	2108.4	2072.7	2030.5	2003.7	1979.9	1940.7	1899.6	1874.5
10°	2240.8	2210.9	2174.9	2127.4	2083.7	2032.4	1996.3	1960.3	1914.3	1865.3	1834.6
12.5°	2278.2	2237.9	2202.5	2141.5	2089.8	2025.6	1982.9	1932.1	1883.7	1825.4	1795.4
15°	2367.3	2292.9	2225.5	2156.5	2092.9	2003.2	1955.7	1887.5	1823.9	1751.9	1717.4
17.5°	2436.1	2352.5	2246.3	2158.7	2084.5	1985.2	1915.4	1833.7	1758.5	1676.2	1629.3
20°	2475.3	2379.5	2265.3	2161.1	2072.2	1958.8	1882.9	1799.4	1711.3	1618.5	1568.0
22.5°	2498.6	2397.9	2285.0	2151.9	2047.7	1937.3	1841.8	1750.3	1661.0	1560.9	1507.9
25°	2506.0	2414.0	2294.5	2144.3	2017.0	1892.1	1777.2	1688.3	1580.2	1486.7	1409.3
27.5°	2469.5	2403.6	2288.6	2129.8	1981.6	1835.6	1707.4	1606.7	1492.7	1391.2	1313.4
30°	2424.7	2386.4	2274.5	2115.1	1953.4	1796.3	1655.3	1541.1	1427.7	1325.0	1245.3
32.5°	2355.5	2347.2	2248.8	2094.3	1923.4	1746.7	1600.8	1485.3	1359.7	1258.8	1182.8
35°	2219.4	2256.1	2194.1	2047.7	1866.8	1676.0	1518.1	1386.3	1256.1	1159.5	1088.2
37.5°	2037.0	2128.3	2112.1	1979.5	1790.5	1599.1	1424.8	1287.0	1162.9	1065.4	995.5
40°	1911.3	2027.8	2044.6	1927.4	1736.6	1539.6	1354.9	1217.7	1096.6	1007.8	937.2
42.5°	1776.4	1912.5	1958.8	1864.8	1677.7	1477.1	1292.4	1150.3	1030.4	944.0	881.5
45°	1550.3	1730.4	1814.0	1760.3	1579.5	1374.1	1184.0	1039.9	931.1	849.9	801.6
47.5°	1339.0	1535.8	1648.1	1629.1	1470.2	1266.8	1078.9	940.6	834.7	769.9	726.7
50°	1189.4	1391.7	1527.3	1533.5	1391.7	1190.1	1001.6	871.3	774.0	713.5	678.2
52.5°	1059.4	1252.5	1400.4	1432.9	1304.0	1110.4	932.3	802.7	717.0	661.4	629.8
55°	889.7	1053.0	1217.0	1276.7	1173.3	989.4	824.6	710.4	629.9	591.6	564.0
57.5°	739.7	875.8	1027.2	1093.3	1029.5	872.1	717.6	618.4	553.2	519.6	498.4
60°	660.6	767.9	902.8	981.7	926.5	786.3	651.4	557.1	503.5	473.6	453.7
62.5°	587.0	682.1	796.1	868.3	838.2	706.0	585.2	502.0	455.7	427.6	413.2
65°	484.3	559.4	647.6	714.2	694.3	593.9	495.1	423.8	387.0	364.8	353.3
67.5°	398.8	453.1	514.2	572.6	556.5	485.4	406.0	350.5	323.1	303.9	297.0
70°	344.9	386.2	440.7	487.4	474.4	416.1	353.3	305.8	282.0	265.9	259.0
72.5°	293.4	327.4	368.9	407.1	398.3	349.9	297.5	261.6	243.4	228.5	222.9
75°	221.5	247.5	272.8	298.1	295.8	258.3	227.6	200.0	185.5	174.0	171.7
77.5°	163.5	178.1	195.3	210.3	206.1	184.7	160.6	144.8	134.1	126.4	125.2
80°	124.9	133.3	145.6	156.3	151.0	141.8	122.6	111.1	103.5	95.8	92.7
82.5°	90.6	99.0	106.4	112.2	108.1	99.5	87.7	79.9	75.3	70.0	68.8
85°	47.5	52.1	55.2	56.7	55.2	49.8	44.4	41.4	37.6	35.3	34.5
87.5°	19.5	19.3	19.2	20.3	18.3	18.2	15.5	13.6	13.1	12.6	11.6
90°	5.3	4.7	4.2	3.5	2.7	1.9	1.1	0.3	1.1	1.9	2.7
92.5°	6.9	6.6	6.4	6.2	6.3	6.4	6.5	6.5	6.5	6.4	6.3
95°	11.6	11.1	10.6	11.5	13.9	16.3	18.6	21.0	18.6	16.3	13.9
97.5°	14.5	13.4	12.2	15.0	21.7	28.3	35.0	41.7	35.0	28.3	21.7
100°	16.0	14.8	13.5	17.9	27.7	37.5	47.4	57.2	47.4	37.5	27.7
102.5°	39.4	49.6	59.8	66.0	68.1	70.1	72.2	74.3	72.2	70.1	68.1
105°	59.0	78.6	98.2	106.9	104.8	102.6	100.4	98.3	100.4	102.6	104.8
107.5°	74.7	98.2	121.7	132.6	130.9	129.1	127.4	125.6	127.4	129.1	130.9
110°	98.1	118.9	139.6	149.3	147.8	146.3	144.7	143.2	144.7	146.3	147.8



TEST NUMBER: P331420

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	153.0	158.1	163.2	165.1	163.8	162.5	161.1	159.8	161.1	162.5	163.8
115°	195.9	194.1	192.3	190.8	189.6	188.4	187.1	185.9	187.1	188.4	189.6
117.5°	218.5	217.3	216.0	214.7	213.4	212.0	210.6	209.3	210.6	212.0	213.4
120°	234.4	233.1	231.8	230.6	229.6	228.5	227.4	226.3	227.4	228.5	229.6
122.5°	249.4	248.0	246.6	245.4	244.2	243.1	242.0	240.8	242.0	243.1	244.2
125°	270.5	269.1	267.8	266.6	265.7	264.7	263.8	262.9	263.8	264.7	265.7
127.5°	290.1	289.0	288.0	287.0	286.0	284.9	283.9	282.8	283.9	284.9	286.0
130°	302.7	301.9	301.1	300.1	299.0	297.8	296.7	295.5	296.7	297.8	299.0
132.5°	314.8	314.0	313.2	312.4	311.4	310.4	309.4	308.5	309.4	310.4	311.4
135°	332.1	331.4	330.8	329.9	328.7	327.6	326.4	325.3	326.4	327.6	328.7
137.5°	347.7	347.0	346.3	345.5	344.7	343.9	343.1	342.3	343.1	343.9	344.7
140°	358.0	357.2	356.4	355.7	355.1	354.5	354.0	353.4	354.0	354.5	355.1
142.5°	367.3	366.4	365.5	364.8	364.3	363.7	363.2	362.7	363.2	363.7	364.3
145°	380.1	378.8	377.6	377.0	377.1	377.2	377.3	377.3	377.3	377.2	377.1
147.5°	391.9	390.6	389.4	389.0	389.2	389.5	389.8	390.1	389.8	389.5	389.2
150°	399.0	397.8	396.7	396.3	396.8	397.3	397.8	398.3	397.8	397.3	396.8
152.5°	405.5	404.4	403.3	403.1	403.6	404.2	404.8	405.3	404.8	404.2	403.6
155°	414.7	413.9	413.0	412.9	413.5	414.2	414.8	415.5	414.8	414.2	413.5
157.5°	422.5	421.9	421.3	421.2	421.8	422.3	422.9	423.4	422.9	422.3	421.8
160°	427.2	426.8	426.4	426.4	426.8	427.2	427.7	428.1	427.7	427.2	426.8
162.5°	431.2	430.8	430.5	430.5	430.9	431.4	431.8	432.2	431.8	431.4	430.9
165°	436.4	436.2	436.0	436.1	436.5	436.9	437.4	437.8	437.4	436.9	436.5
167.5°	440.5	440.3	440.1	440.2	440.6	441.1	441.5	441.9	441.5	441.1	440.6
170°	442.7	442.5	442.4	442.5	443.0	443.4	443.8	444.3	443.8	443.4	443.0
172.5°	444.2	444.1	443.9	444.1	444.5	444.9	445.4	445.8	445.4	444.9	444.5
175°	445.9	445.8	445.6	445.8	446.3	446.8	447.3	447.8	447.3	446.8	446.3
177.5°	446.5	446.4	446.4	446.5	446.9	447.3	447.7	448.1	447.7	447.3	446.9
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331420

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	1967.7	1964.0	1951.1	1944.4	1933.4	1922.9	1916.2	1919.3	1921.7	1920.5	1918.6
5°	1911.3	1896.7	1874.5	1855.3	1841.5	1816.3	1805.5	1800.2	1795.6	1790.2	1784.8
7.5°	1844.1	1821.2	1789.3	1762.0	1736.2	1704.8	1686.9	1676.2	1665.1	1653.0	1642.3
10°	1796.3	1764.1	1730.4	1692.1	1661.5	1633.1	1607.8	1590.9	1575.6	1561.1	1550.3
12.5°	1746.1	1709.0	1667.3	1614.9	1581.1	1540.5	1536.7	1507.0	1483.0	1474.0	1461.4
15°	1666.0	1613.9	1561.1	1499.0	1472.2	1435.4	1412.4	1389.4	1368.7	1354.1	1350.3
17.5°	1575.2	1507.7	1455.1	1410.5	1366.6	1328.9	1307.7	1289.3	1272.3	1252.8	1250.2
20°	1505.9	1447.6	1390.2	1351.1	1305.9	1267.5	1241.5	1223.1	1208.5	1197.0	1187.1
22.5°	1440.3	1376.5	1323.9	1281.2	1236.6	1205.6	1185.1	1167.3	1155.2	1142.5	1133.1
25°	1335.0	1285.2	1227.7	1179.4	1142.6	1122.7	1105.8	1090.5	1082.9	1074.4	1063.7
27.5°	1242.9	1187.5	1133.7	1096.3	1064.0	1046.4	1034.4	1024.0	1016.8	1011.9	1005.8
30°	1177.9	1121.9	1079.8	1043.0	1016.2	998.6	990.9	984.8	976.3	973.3	970.2
32.5°	1115.3	1064.9	1028.9	997.0	971.4	959.9	952.9	947.4	940.8	937.7	931.6
35°	1026.9	984.8	949.5	931.9	911.2	901.2	895.9	888.2	882.1	879.0	878.2
37.5°	943.7	907.1	883.9	861.2	852.5	846.4	839.0	833.8	832.0	831.5	830.7
40°	889.7	859.8	839.2	820.8	816.9	807.7	801.6	797.0	797.0	797.8	797.0
42.5°	840.7	813.9	795.6	779.7	775.2	769.7	763.6	763.3	764.5	767.1	764.5
45°	766.4	747.2	734.2	726.5	718.1	712.7	711.9	714.2	715.0	715.8	718.1
47.5°	698.0	685.3	673.5	665.0	661.4	660.4	659.5	663.5	667.2	668.6	672.1
50°	657.5	643.0	633.0	627.6	624.6	623.0	624.6	629.2	632.2	636.1	638.4
52.5°	612.2	601.9	595.0	590.9	589.6	590.6	590.9	596.1	601.0	602.4	603.4
55°	549.5	541.8	540.3	533.4	536.4	535.7	539.5	542.6	547.2	551.8	552.5
57.5°	486.9	480.8	476.7	477.3	478.2	481.6	484.8	490.2	495.1	500.0	500.4
60°	445.3	442.2	439.9	439.9	441.4	446.0	449.8	455.2	458.3	461.3	463.6
62.5°	407.2	404.2	401.9	403.1	407.1	409.8	414.3	417.2	420.3	423.3	424.4
65°	347.2	345.6	347.9	349.5	350.2	354.1	359.4	361.7	364.8	366.3	371.7
67.5°	291.8	292.1	291.8	294.0	298.4	299.3	304.4	309.8	310.4	313.3	316.8
70°	254.4	256.0	257.5	259.0	262.9	264.4	268.2	270.5	273.6	275.9	278.2
72.5°	220.1	220.4	221.9	221.6	224.8	228.2	231.4	233.7	236.8	239.7	242.0
75°	169.4	169.4	170.9	171.7	175.5	179.3	178.6	180.1	183.2	186.2	187.8
77.5°	123.7	122.0	123.7	124.5	125.7	128.9	129.5	131.7	135.2	134.1	135.8
80°	94.3	92.0	94.3	95.0	95.0	98.9	98.9	100.4	102.7	100.4	102.7
82.5°	67.3	66.2	67.9	68.1	69.3	69.4	70.7	71.0	73.3	72.2	73.3
85°	33.7	33.0	33.7	33.0	33.7	34.5	34.5	33.7	33.7	35.3	33.0
87.5°	11.1	10.6	10.1	10.3	9.8	9.3	8.7	8.8	8.9	7.7	7.8
90°	3.5	4.2	4.7	5.3	5.9	6.5	6.8	7.2	7.5	7.9	8.2
92.5°	6.2	6.4	6.6	6.9	7.2	7.5	7.7	7.9	8.1	8.2	8.4
95°	11.5	10.6	11.1	11.6	12.1	12.6	13.0	13.3	13.7	14.0	14.2
97.5°	15.0	12.2	13.4	14.5	15.7	16.9	17.2	17.5	17.7	18.0	18.2
100°	17.9	13.5	14.8	16.0	17.2	18.4	19.0	19.6	20.2	20.7	21.1
102.5°	66.0	59.8	49.6	39.4	29.2	18.9	19.7	20.4	21.2	21.9	22.4
105°	106.9	98.2	78.6	59.0	39.3	19.7	20.5	21.3	22.1	22.9	23.4
107.5°	132.6	121.7	98.2	74.7	51.1	27.6	26.8	26.0	25.2	24.4	24.1
110°	149.3	139.6	118.9	98.1	77.3	56.6	49.4	42.2	35.0	27.8	24.4



TEST NUMBER: P331420

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	165.1	163.2	158.1	153.0	147.8	142.7	116.5	90.3	64.1	37.9	24.9
115°	190.8	192.3	194.1	195.9	197.7	199.5	166.2	133.0	99.7	66.4	47.2
117.5°	214.7	216.0	217.3	218.5	219.7	221.0	212.9	204.9	196.8	188.8	176.3
120°	230.6	231.8	233.1	234.4	235.7	237.0	237.9	238.7	239.6	240.4	236.0
122.5°	245.4	246.6	248.0	249.4	250.9	252.3	252.8	253.3	253.8	254.3	253.6
125°	266.6	267.8	269.1	270.5	271.8	273.2	273.7	274.2	274.7	275.2	275.6
127.5°	287.0	288.0	289.0	290.1	291.1	292.1	292.8	293.6	294.3	295.0	295.4
130°	300.1	301.1	301.9	302.7	303.5	304.3	305.0	305.8	306.6	307.4	307.8
132.5°	312.4	313.2	314.0	314.8	315.6	316.4	317.1	317.8	318.4	319.1	319.4
135°	329.9	330.8	331.4	332.1	332.7	333.4	334.1	334.8	335.5	336.2	336.5
137.5°	345.5	346.3	347.0	347.7	348.5	349.2	349.9	350.6	351.3	352.0	352.2
140°	355.7	356.4	357.2	358.0	358.8	359.5	360.2	360.8	361.5	362.1	362.3
142.5°	364.8	365.5	366.4	367.3	368.2	369.1	369.7	370.3	370.9	371.5	371.6
145°	377.0	377.6	378.8	380.1	381.3	382.5	383.0	383.5	384.0	384.5	384.6
147.5°	389.0	389.4	390.6	391.9	393.1	394.3	394.6	395.0	395.4	395.8	395.8
150°	396.3	396.7	397.8	399.0	400.1	401.3	401.7	402.1	402.5	403.0	403.0
152.5°	403.1	403.3	404.4	405.5	406.6	407.7	408.1	408.6	409.0	409.4	409.4
155°	412.9	413.0	413.9	414.7	415.6	416.4	416.9	417.3	417.7	418.2	418.1
157.5°	421.2	421.3	421.9	422.5	423.1	423.7	424.2	424.7	425.2	425.6	425.6
160°	426.4	426.4	426.8	427.2	427.7	428.1	428.5	429.0	429.4	429.8	429.8
162.5°	430.5	430.5	430.8	431.2	431.6	432.0	432.5	432.9	433.4	433.9	433.9
165°	436.1	436.0	436.2	436.4	436.6	436.8	437.3	437.8	438.3	438.8	438.8
167.5°	440.2	440.1	440.3	440.5	440.7	440.9	441.4	441.9	442.4	442.9	442.8
170°	442.5	442.4	442.5	442.7	442.8	443.0	443.5	444.0	444.5	445.0	444.9
172.5°	444.1	443.9	444.1	444.2	444.4	444.5	445.0	445.5	446.0	446.5	446.5
175°	445.8	445.6	445.8	445.9	446.1	446.2	446.7	447.2	447.7	448.2	448.1
177.5°	446.5	446.4	446.4	446.5	446.5	446.6	447.0	447.4	447.8	448.2	448.1
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331420

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	1912.5	1911.3	1911.3	1905.8	1911.3	1911.3	1912.5	1918.6	1920.5	1921.7	1919.3
5°	1774.1	1771.8	1768.0	1771.8	1768.0	1771.8	1774.1	1784.8	1790.2	1795.6	1800.2
7.5°	1637.2	1628.0	1626.7	1617.6	1626.7	1628.0	1637.2	1642.3	1653.0	1665.1	1676.2
10°	1537.3	1531.2	1530.4	1515.8	1530.4	1531.2	1537.3	1550.3	1561.1	1575.6	1590.9
12.5°	1461.3	1446.6	1449.5	1441.0	1449.5	1446.6	1461.3	1461.4	1474.0	1483.0	1507.0
15°	1329.6	1329.6	1326.6	1313.5	1326.6	1329.6	1329.6	1350.3	1354.1	1368.7	1389.4
17.5°	1235.1	1233.5	1226.2	1229.8	1226.2	1233.5	1235.1	1250.2	1252.8	1272.3	1289.3
20°	1178.6	1174.1	1164.9	1164.9	1164.9	1174.1	1178.6	1187.1	1197.0	1208.5	1223.1
22.5°	1125.3	1125.0	1115.2	1118.3	1115.2	1125.0	1125.3	1133.1	1142.5	1155.2	1167.3
25°	1062.9	1056.8	1052.2	1054.5	1052.2	1056.8	1062.9	1063.7	1074.4	1082.9	1090.5
27.5°	1003.8	1000.4	1000.1	993.8	1000.1	1000.4	1003.8	1005.8	1011.9	1016.8	1024.0
30°	969.4	961.8	963.3	959.5	963.3	961.8	969.4	970.2	973.3	976.3	984.8
32.5°	930.2	927.4	925.9	922.7	925.9	927.4	930.2	931.6	937.7	940.8	947.4
35°	876.7	877.5	873.6	875.2	873.6	877.5	876.7	878.2	879.0	882.1	888.2
37.5°	830.0	832.4	830.6	831.0	830.6	832.4	830.0	830.7	831.5	832.0	833.8
40°	799.3	799.3	799.3	801.6	799.3	799.3	799.3	797.0	797.8	797.0	797.0
42.5°	769.9	768.7	767.4	767.3	767.4	768.7	769.9	764.5	767.1	764.5	763.3
45°	719.6	721.9	722.7	718.8	722.7	721.9	719.6	718.1	715.8	715.0	714.2
47.5°	674.1	674.4	674.1	677.5	674.1	674.4	674.1	672.1	668.6	667.2	663.5
50°	642.2	640.7	642.2	640.7	642.2	640.7	642.2	638.4	636.1	632.2	629.2
52.5°	608.5	608.8	607.9	607.6	607.9	608.8	608.5	603.4	602.4	601.0	596.1
55°	555.6	557.1	556.4	556.4	556.4	557.1	555.6	552.5	551.8	547.2	542.6
57.5°	500.9	502.3	503.3	500.0	503.3	502.3	500.9	500.4	500.0	495.1	490.2
60°	462.9	466.7	465.9	464.4	465.9	466.7	462.9	463.6	461.3	458.3	455.2
62.5°	427.9	429.3	429.2	428.9	429.2	429.3	427.9	424.4	423.3	420.3	417.2
65°	374.0	375.5	373.2	375.5	373.2	375.5	374.0	371.7	366.3	364.8	361.7
67.5°	315.9	316.4	318.0	319.1	318.0	316.4	315.9	316.8	313.3	310.4	309.8
70°	279.7	279.0	281.3	283.6	281.3	279.0	279.7	278.2	275.9	273.6	270.5
72.5°	241.7	243.4	242.6	244.3	242.6	243.4	241.7	242.0	239.7	236.8	233.7
75°	186.2	188.5	187.8	190.1	187.8	188.5	186.2	187.8	186.2	183.2	180.1
77.5°	134.6	134.9	134.6	135.8	134.6	134.9	134.6	135.8	134.1	135.2	131.7
80°	102.7	101.2	99.6	102.7	99.6	101.2	102.7	102.7	100.4	102.7	100.4
82.5°	71.4	72.3	70.8	70.8	70.8	72.3	71.4	73.3	72.2	73.3	71.0
85°	33.0	32.2	30.7	30.7	30.7	32.2	33.0	33.0	35.3	33.7	33.7
87.5°	7.8	7.2	7.2	6.7	7.2	7.2	7.8	7.8	7.7	8.9	8.8
90°	8.3	8.4	8.6	8.7	8.6	8.4	8.3	8.2	7.9	7.5	7.2
92.5°	8.5	8.6	8.6	8.7	8.6	8.6	8.5	8.4	8.2	8.1	7.9
95°	14.1	14.0	14.0	13.9	14.0	14.0	14.1	14.2	14.0	13.7	13.3
97.5°	18.3	18.4	18.5	18.6	18.5	18.4	18.3	18.2	18.0	17.7	17.5
100°	21.2	21.4	21.5	21.7	21.5	21.4	21.2	21.1	20.7	20.2	19.6
102.5°	22.6	22.8	23.0	23.2	23.0	22.8	22.6	22.4	21.9	21.2	20.4
105°	23.7	24.0	24.3	24.6	24.3	24.0	23.7	23.4	22.9	22.1	21.3
107.5°	24.4	24.7	25.0	25.3	25.0	24.7	24.4	24.1	24.4	25.2	26.0
110°	24.7	25.0	25.3	25.5	25.3	25.0	24.7	24.4	27.8	35.0	42.2



TEST NUMBER: P331420

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	25.1	25.3	25.6	25.8	25.6	25.3	25.1	24.9	37.9	64.1	90.3
115°	42.0	36.9	31.7	26.5	31.7	36.9	42.0	47.2	66.4	99.7	133.0
117.5°	159.3	142.3	125.3	108.3	125.3	142.3	159.3	176.3	188.8	196.8	204.9
120°	226.3	216.6	206.9	197.2	206.9	216.6	226.3	236.0	240.4	239.6	238.7
122.5°	251.8	249.9	248.0	246.1	248.0	249.9	251.8	253.6	254.3	253.8	253.3
125°	275.8	276.0	276.2	276.4	276.2	276.0	275.8	275.6	275.2	274.7	274.2
127.5°	295.5	295.5	295.5	295.6	295.5	295.5	295.5	295.4	295.0	294.3	293.6
130°	307.7	307.6	307.6	307.5	307.6	307.6	307.7	307.8	307.4	306.6	305.8
132.5°	319.3	319.3	319.2	319.1	319.2	319.3	319.3	319.4	319.1	318.4	317.8
135°	336.4	336.2	336.1	335.9	336.1	336.2	336.4	336.5	336.2	335.5	334.8
137.5°	352.0	351.8	351.5	351.3	351.5	351.8	352.0	352.2	352.0	351.3	350.6
140°	361.9	361.6	361.2	360.8	361.2	361.6	361.9	362.3	362.1	361.5	360.8
142.5°	371.2	370.9	370.5	370.1	370.5	370.9	371.2	371.6	371.5	370.9	370.3
145°	384.2	383.9	383.5	383.1	383.5	383.9	384.2	384.6	384.5	384.0	383.5
147.5°	395.5	395.2	394.9	394.6	394.9	395.2	395.5	395.8	395.8	395.4	395.0
150°	402.7	402.3	401.9	401.6	401.9	402.3	402.7	403.0	403.0	402.5	402.1
152.5°	408.9	408.5	408.0	407.5	408.0	408.5	408.9	409.4	409.4	409.0	408.6
155°	417.5	417.0	416.4	415.8	416.4	417.0	417.5	418.1	418.2	417.7	417.3
157.5°	425.0	424.5	423.9	423.4	423.9	424.5	425.0	425.6	425.6	425.2	424.7
160°	429.3	428.8	428.3	427.8	428.3	428.8	429.3	429.8	429.8	429.4	429.0
162.5°	433.2	432.6	432.0	431.4	432.0	432.6	433.2	433.9	433.9	433.4	432.9
165°	438.3	437.8	437.3	436.8	437.3	437.8	438.3	438.8	438.8	438.3	437.8
167.5°	442.2	441.5	440.9	440.2	440.9	441.5	442.2	442.8	442.9	442.4	441.9
170°	444.3	443.6	443.0	442.3	443.0	443.6	444.3	444.9	445.0	444.5	444.0
172.5°	445.8	445.2	444.5	443.9	444.5	445.2	445.8	446.5	446.5	446.0	445.5
175°	447.4	446.7	445.9	445.2	445.9	446.7	447.4	448.1	448.2	447.7	447.2
177.5°	447.6	447.1	446.6	446.1	446.6	447.1	447.6	448.1	448.2	447.8	447.4
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331420

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	1916.2	1922.9	1933.4	1944.4	1951.1	1964.0	1967.7	1973.8	1979.3	1992.2	2005.7
5°	1805.5	1816.3	1841.5	1855.3	1874.5	1896.7	1911.3	1926.6	1943.5	1972.6	1999.4
7.5°	1686.9	1704.8	1736.2	1762.0	1789.3	1821.2	1844.1	1874.5	1899.6	1940.7	1979.9
10°	1607.8	1633.1	1661.5	1692.1	1730.4	1764.1	1796.3	1834.6	1865.3	1914.3	1960.3
12.5°	1536.7	1540.5	1581.1	1614.9	1667.3	1709.0	1746.1	1795.4	1825.4	1883.7	1932.1
15°	1412.4	1435.4	1472.2	1499.0	1561.1	1613.9	1666.0	1717.4	1751.9	1823.9	1887.5
17.5°	1307.7	1328.9	1366.6	1410.5	1455.1	1507.7	1575.2	1629.3	1676.2	1758.5	1833.7
20°	1241.5	1267.5	1305.9	1351.1	1390.2	1447.6	1505.9	1568.0	1618.5	1711.3	1799.4
22.5°	1185.1	1205.6	1236.6	1281.2	1323.9	1376.5	1440.3	1507.9	1560.9	1661.0	1750.3
25°	1105.8	1122.7	1142.6	1179.4	1227.7	1285.2	1335.0	1409.3	1486.7	1580.2	1688.3
27.5°	1034.4	1046.4	1064.0	1096.3	1133.7	1187.5	1242.9	1313.4	1391.2	1492.7	1606.7
30°	990.9	998.6	1016.2	1043.0	1079.8	1121.9	1177.9	1245.3	1325.0	1427.7	1541.1
32.5°	952.9	959.9	971.4	997.0	1028.9	1064.9	1115.3	1182.8	1258.8	1359.7	1485.3
35°	895.9	901.2	911.2	931.9	949.5	984.8	1026.9	1088.2	1159.5	1256.1	1386.3
37.5°	839.0	846.4	852.5	861.2	883.9	907.1	943.7	995.5	1065.4	1162.9	1287.0
40°	801.6	807.7	816.9	820.8	839.2	859.8	889.7	937.2	1007.8	1096.6	1217.7
42.5°	763.6	769.7	775.2	779.7	795.6	813.9	840.7	881.5	944.0	1030.4	1150.3
45°	711.9	712.7	718.1	726.5	734.2	747.2	766.4	801.6	849.9	931.1	1039.9
47.5°	659.5	660.4	661.4	665.0	673.5	685.3	698.0	726.7	769.9	834.7	940.6
50°	624.6	623.0	624.6	627.6	633.0	643.0	657.5	678.2	713.5	774.0	871.3
52.5°	590.9	590.6	589.6	590.9	595.0	601.9	612.2	629.8	661.4	717.0	802.7
55°	539.5	535.7	536.4	533.4	540.3	541.8	549.5	564.0	591.6	629.9	710.4
57.5°	484.8	481.6	478.2	477.3	476.7	480.8	486.9	498.4	519.6	553.2	618.4
60°	449.8	446.0	441.4	439.9	439.9	442.2	445.3	453.7	473.6	503.5	557.1
62.5°	414.3	409.8	407.1	403.1	401.9	404.2	407.2	413.2	427.6	455.7	502.0
65°	359.4	354.1	350.2	349.5	347.9	345.6	347.2	353.3	364.8	387.0	423.8
67.5°	304.4	299.3	298.4	294.0	291.8	292.1	291.8	297.0	303.9	323.1	350.5
70°	268.2	264.4	262.9	259.0	257.5	256.0	254.4	259.0	265.9	282.0	305.8
72.5°	231.4	228.2	224.8	221.6	221.9	220.4	220.1	222.9	228.5	243.4	261.6
75°	178.6	179.3	175.5	171.7	170.9	169.4	169.4	171.7	174.0	185.5	200.0
77.5°	129.5	128.9	125.7	124.5	123.7	122.0	123.7	125.2	126.4	134.1	144.8
80°	98.9	98.9	95.0	95.0	94.3	92.0	94.3	92.7	95.8	103.5	111.1
82.5°	70.7	69.4	69.3	68.1	67.9	66.2	67.3	68.8	70.0	75.3	79.9
85°	34.5	34.5	33.7	33.0	33.7	33.0	33.7	34.5	35.3	37.6	41.4
87.5°	8.7	9.3	9.8	10.3	10.1	10.6	11.1	11.6	12.6	13.1	13.6
90°	6.8	6.5	5.9	5.3	4.7	4.2	3.5	2.7	1.9	1.1	0.3
92.5°	7.7	7.5	7.2	6.9	6.6	6.4	6.2	6.3	6.4	6.5	6.5
95°	13.0	12.6	12.1	11.6	11.1	10.6	11.5	13.9	16.3	18.6	21.0
97.5°	17.2	16.9	15.7	14.5	13.4	12.2	15.0	21.7	28.3	35.0	41.7
100°	19.0	18.4	17.2	16.0	14.8	13.5	17.9	27.7	37.5	47.4	57.2
102.5°	19.7	18.9	29.2	39.4	49.6	59.8	66.0	68.1	70.1	72.2	74.3
105°	20.5	19.7	39.3	59.0	78.6	98.2	106.9	104.8	102.6	100.4	98.3
107.5°	26.8	27.6	51.1	74.7	98.2	121.7	132.6	130.9	129.1	127.4	125.6
110°	49.4	56.6	77.3	98.1	118.9	139.6	149.3	147.8	146.3	144.7	143.2



TEST NUMBER: P331420

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	116.5	142.7	147.8	153.0	158.1	163.2	165.1	163.8	162.5	161.1	159.8
115°	166.2	199.5	197.7	195.9	194.1	192.3	190.8	189.6	188.4	187.1	185.9
117.5°	212.9	221.0	219.7	218.5	217.3	216.0	214.7	213.4	212.0	210.6	209.3
120°	237.9	237.0	235.7	234.4	233.1	231.8	230.6	229.6	228.5	227.4	226.3
122.5°	252.8	252.3	250.9	249.4	248.0	246.6	245.4	244.2	243.1	242.0	240.8
125°	273.7	273.2	271.8	270.5	269.1	267.8	266.6	265.7	264.7	263.8	262.9
127.5°	292.8	292.1	291.1	290.1	289.0	288.0	287.0	286.0	284.9	283.9	282.8
130°	305.0	304.3	303.5	302.7	301.9	301.1	300.1	299.0	297.8	296.7	295.5
132.5°	317.1	316.4	315.6	314.8	314.0	313.2	312.4	311.4	310.4	309.4	308.5
135°	334.1	333.4	332.7	332.1	331.4	330.8	329.9	328.7	327.6	326.4	325.3
137.5°	349.9	349.2	348.5	347.7	347.0	346.3	345.5	344.7	343.9	343.1	342.3
140°	360.2	359.5	358.8	358.0	357.2	356.4	355.7	355.1	354.5	354.0	353.4
142.5°	369.7	369.1	368.2	367.3	366.4	365.5	364.8	364.3	363.7	363.2	362.7
145°	383.0	382.5	381.3	380.1	378.8	377.6	377.0	377.1	377.2	377.3	377.3
147.5°	394.6	394.3	393.1	391.9	390.6	389.4	389.0	389.2	389.5	389.8	390.1
150°	401.7	401.3	400.1	399.0	397.8	396.7	396.3	396.8	397.3	397.8	398.3
152.5°	408.1	407.7	406.6	405.5	404.4	403.3	403.1	403.6	404.2	404.8	405.3
155°	416.9	416.4	415.6	414.7	413.9	413.0	412.9	413.5	414.2	414.8	415.5
157.5°	424.2	423.7	423.1	422.5	421.9	421.3	421.2	421.8	422.3	422.9	423.4
160°	428.5	428.1	427.7	427.2	426.8	426.4	426.4	426.8	427.2	427.7	428.1
162.5°	432.5	432.0	431.6	431.2	430.8	430.5	430.5	430.9	431.4	431.8	432.2
165°	437.3	436.8	436.6	436.4	436.2	436.0	436.1	436.5	436.9	437.4	437.8
167.5°	441.4	440.9	440.7	440.5	440.3	440.1	440.2	440.6	441.1	441.5	441.9
170°	443.5	443.0	442.8	442.7	442.5	442.4	442.5	443.0	443.4	443.8	444.3
172.5°	445.0	444.5	444.4	444.2	444.1	443.9	444.1	444.5	444.9	445.4	445.8
175°	446.7	446.2	446.1	445.9	445.8	445.6	445.8	446.3	446.8	447.3	447.8
177.5°	447.0	446.6	446.5	446.5	446.4	446.4	446.5	446.9	447.3	447.7	448.1
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331420

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2004.5	2007.5	2017.3	2027.2	2038.2	2041.3	2046.2	2041.9	2040.6	2052.3	2060.9
5°	2010.1	2023.9	2050.8	2075.3	2096.0	2110.5	2125.9	2132.0	2143.5	2159.6	2179.5
7.5°	2003.7	2030.5	2072.7	2108.4	2147.3	2175.4	2197.3	2216.0	2238.7	2269.2	2302.4
10°	1996.3	2032.4	2083.7	2127.4	2174.9	2210.9	2240.8	2269.9	2303.7	2345.8	2389.5
12.5°	1982.9	2025.6	2089.8	2141.5	2202.5	2237.9	2278.2	2341.1	2377.2	2435.9	2497.4
15°	1955.7	2003.2	2092.9	2156.5	2225.5	2292.9	2367.3	2427.0	2486.8	2521.3	2607.9
17.5°	1915.4	1985.2	2084.5	2158.7	2246.3	2352.5	2436.1	2503.8	2572.8	2628.7	2672.1
20°	1882.9	1958.8	2072.2	2161.1	2265.3	2379.5	2475.3	2544.3	2604.1	2650.8	2677.6
22.5°	1841.8	1937.3	2047.7	2151.9	2285.0	2397.9	2498.6	2552.9	2602.8	2625.7	2635.9
25°	1777.2	1892.1	2017.0	2144.3	2294.5	2414.0	2506.0	2538.9	2553.5	2531.3	2494.5
27.5°	1707.4	1835.6	1981.6	2129.8	2288.6	2403.6	2469.5	2464.3	2439.6	2367.7	2310.2
30°	1655.3	1796.3	1953.4	2115.1	2274.5	2386.4	2424.7	2386.4	2330.5	2250.0	2168.0
32.5°	1600.8	1746.7	1923.4	2094.3	2248.8	2347.2	2355.5	2289.6	2203.0	2111.5	2009.2
35°	1518.1	1676.0	1866.8	2047.7	2194.1	2256.1	2219.4	2102.9	2000.2	1875.3	1735.8
37.5°	1424.8	1599.1	1790.5	1979.5	2112.1	2128.3	2037.0	1914.3	1769.5	1622.7	1458.5
40°	1354.9	1539.6	1736.6	1927.4	2044.6	2027.8	1911.3	1776.4	1604.0	1424.6	1272.1
42.5°	1292.4	1477.1	1677.7	1864.8	1958.8	1912.5	1776.4	1610.9	1425.6	1256.7	1117.0
45°	1184.0	1374.1	1579.5	1760.3	1814.0	1730.4	1550.3	1366.4	1184.0	1043.0	932.7
47.5°	1078.9	1266.8	1470.2	1629.1	1648.1	1535.8	1339.0	1149.7	992.9	878.1	800.2
50°	1001.6	1190.1	1391.7	1533.5	1527.3	1391.7	1189.4	1009.3	878.2	785.5	733.4
52.5°	932.3	1110.4	1304.0	1432.9	1400.4	1252.5	1059.4	899.5	791.8	719.3	672.1
55°	824.6	989.4	1173.3	1276.7	1217.0	1053.0	889.7	761.0	681.3	626.9	590.1
57.5°	717.6	872.1	1029.5	1093.3	1027.2	875.8	739.7	646.3	586.4	546.1	522.2
60°	651.4	786.3	926.5	981.7	902.8	767.9	660.6	577.1	528.8	495.8	474.4
62.5°	585.2	706.0	838.2	868.3	796.1	682.1	587.0	517.6	477.9	448.6	428.4
65°	495.1	593.9	694.3	714.2	647.6	559.4	484.3	439.1	403.9	382.4	366.3
67.5°	406.0	485.4	556.5	572.6	514.2	453.1	398.8	359.4	335.5	317.7	304.1
70°	353.3	416.1	474.4	487.4	440.7	386.2	344.9	313.4	292.0	276.7	263.6
72.5°	297.5	349.9	398.3	407.1	368.9	327.4	293.4	268.7	249.7	239.9	227.5
75°	227.6	258.3	295.8	298.1	272.8	247.5	221.5	205.4	195.4	183.2	177.0
77.5°	160.6	184.7	206.1	210.3	195.3	178.1	163.5	150.8	142.4	136.7	131.0
80°	122.6	141.8	151.0	156.3	145.6	133.3	124.9	116.5	111.1	107.3	103.5
82.5°	87.7	99.5	108.1	112.2	106.4	99.0	90.6	85.8	81.7	78.5	77.1
85°	44.4	49.8	55.2	56.7	55.2	52.1	47.5	47.5	45.2	44.4	44.4
87.5°	15.5	18.2	18.3	20.3	19.2	19.3	19.5	19.0	18.5	17.9	17.4
90°	1.1	1.9	2.7	3.5	4.2	4.7	5.3	5.9	6.5	6.8	7.2
92.5°	6.5	6.4	6.3	6.2	6.4	6.6	6.9	7.2	7.5	7.7	7.9
95°	18.6	16.3	13.9	11.5	10.6	11.1	11.6	12.1	12.6	13.0	13.3
97.5°	35.0	28.3	21.7	15.0	12.2	13.4	14.5	15.7	16.9	17.2	17.5
100°	47.4	37.5	27.7	17.9	13.5	14.8	16.0	17.2	18.4	19.0	19.6
102.5°	72.2	70.1	68.1	66.0	59.8	49.6	39.4	29.2	18.9	19.7	20.4
105°	100.4	102.6	104.8	106.9	98.2	78.6	59.0	39.3	19.7	20.5	21.3
107.5°	127.4	129.1	130.9	132.6	121.7	98.2	74.7	51.1	27.6	26.8	26.0
110°	144.7	146.3	147.8	149.3	139.6	118.9	98.1	77.3	56.6	49.4	42.2



TEST NUMBER: P331420

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	161.1	162.5	163.8	165.1	163.2	158.1	153.0	147.8	142.7	116.5	90.3
115°	187.1	188.4	189.6	190.8	192.3	194.1	195.9	197.7	199.5	166.2	133.0
117.5°	210.6	212.0	213.4	214.7	216.0	217.3	218.5	219.7	221.0	212.9	204.9
120°	227.4	228.5	229.6	230.6	231.8	233.1	234.4	235.7	237.0	237.9	238.7
122.5°	242.0	243.1	244.2	245.4	246.6	248.0	249.4	250.9	252.3	252.8	253.3
125°	263.8	264.7	265.7	266.6	267.8	269.1	270.5	271.8	273.2	273.7	274.2
127.5°	283.9	284.9	286.0	287.0	288.0	289.0	290.1	291.1	292.1	292.8	293.6
130°	296.7	297.8	299.0	300.1	301.1	301.9	302.7	303.5	304.3	305.0	305.8
132.5°	309.4	310.4	311.4	312.4	313.2	314.0	314.8	315.6	316.4	317.1	317.8
135°	326.4	327.6	328.7	329.9	330.8	331.4	332.1	332.7	333.4	334.1	334.8
137.5°	343.1	343.9	344.7	345.5	346.3	347.0	347.7	348.5	349.2	349.9	350.6
140°	354.0	354.5	355.1	355.7	356.4	357.2	358.0	358.8	359.5	360.2	360.8
142.5°	363.2	363.7	364.3	364.8	365.5	366.4	367.3	368.2	369.1	369.7	370.3
145°	377.3	377.2	377.1	377.0	377.6	378.8	380.1	381.3	382.5	383.0	383.5
147.5°	389.8	389.5	389.2	389.0	389.4	390.6	391.9	393.1	394.3	394.6	395.0
150°	397.8	397.3	396.8	396.3	396.7	397.8	399.0	400.1	401.3	401.7	402.1
152.5°	404.8	404.2	403.6	403.1	403.3	404.4	405.5	406.6	407.7	408.1	408.6
155°	414.8	414.2	413.5	412.9	413.0	413.9	414.7	415.6	416.4	416.9	417.3
157.5°	422.9	422.3	421.8	421.2	421.3	421.9	422.5	423.1	423.7	424.2	424.7
160°	427.7	427.2	426.8	426.4	426.4	426.8	427.2	427.7	428.1	428.5	429.0
162.5°	431.8	431.4	430.9	430.5	430.5	430.8	431.2	431.6	432.0	432.5	432.9
165°	437.4	436.9	436.5	436.1	436.0	436.2	436.4	436.6	436.8	437.3	437.8
167.5°	441.5	441.1	440.6	440.2	440.1	440.3	440.5	440.7	440.9	441.4	441.9
170°	443.8	443.4	443.0	442.5	442.4	442.5	442.7	442.8	443.0	443.5	444.0
172.5°	445.4	444.9	444.5	444.1	443.9	444.1	444.2	444.4	444.5	445.0	445.5
175°	447.3	446.8	446.3	445.8	445.6	445.8	445.9	446.1	446.2	446.7	447.2
177.5°	447.7	447.3	446.9	446.5	446.4	446.4	446.5	446.5	446.6	447.0	447.4
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331420

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2068.2	2076.8	2076.8	2078.0	2087.8	2086.6	2086.0
5°	2201.0	2214.0	2215.5	2229.3	2238.5	2235.4	2227.0
7.5°	2326.2	2350.4	2368.8	2379.1	2391.2	2398.7	2395.3
10°	2425.5	2460.8	2482.2	2496.8	2514.4	2527.4	2522.8
12.5°	2515.6	2557.6	2587.1	2612.0	2614.3	2631.0	2619.7
15°	2656.2	2700.6	2705.2	2723.6	2738.2	2736.6	2737.4
17.5°	2702.6	2716.9	2719.8	2720.2	2720.4	2715.0	2703.4
20°	2686.1	2680.7	2667.7	2657.7	2640.1	2637.8	2622.5
22.5°	2607.6	2590.6	2557.9	2536.3	2508.9	2501.7	2497.4
25°	2453.1	2415.5	2363.4	2313.6	2299.8	2273.0	2280.7
27.5°	2241.1	2182.6	2126.2	2085.7	2049.1	2008.9	2020.4
30°	2092.1	2026.2	1946.5	1885.2	1846.1	1807.8	1800.9
32.5°	1914.3	1817.8	1728.9	1674.9	1615.0	1590.8	1564.3
35°	1607.8	1513.5	1425.4	1349.5	1305.9	1272.1	1241.5
37.5°	1332.1	1223.6	1152.4	1091.0	1059.4	1040.1	1045.0
40°	1161.0	1066.0	1013.9	967.1	938.0	924.2	927.3
42.5°	1022.5	951.3	908.4	876.4	855.9	848.2	846.4
45°	865.2	825.4	790.1	771.7	761.8	753.3	748.0
47.5°	757.9	725.4	705.5	694.6	685.9	677.3	677.1
50°	693.5	672.1	658.3	646.8	639.9	633.8	639.1
52.5°	644.5	624.9	611.1	600.8	598.2	592.7	592.5
55°	571.7	556.4	546.4	537.2	532.6	529.5	525.7
57.5°	505.5	490.9	481.7	475.9	467.2	464.1	462.9
60°	458.3	446.8	437.6	429.9	426.1	420.0	420.0
62.5°	414.7	403.3	394.7	388.8	382.6	380.1	380.7
65°	351.8	342.6	334.1	328.0	326.5	321.9	323.4
67.5°	293.8	287.7	278.8	275.4	272.5	270.1	268.2
70°	255.2	249.1	244.5	239.9	237.6	237.6	237.6
72.5°	222.7	215.3	212.6	206.8	208.1	205.7	203.2
75°	172.4	167.8	165.5	163.2	159.4	159.4	159.4
77.5°	126.9	125.5	122.8	120.3	119.4	118.6	118.9
80°	98.1	97.3	95.8	95.8	94.3	93.5	92.0
82.5°	75.4	73.4	72.5	71.9	71.6	71.4	71.1
85°	42.9	41.4	41.4	42.1	40.6	40.6	41.4
87.5°	18.1	18.1	17.6	17.6	18.2	17.7	17.7
90°	7.5	7.9	8.2	8.3	8.4	8.6	8.7
92.5°	8.1	8.2	8.4	8.5	8.6	8.6	8.7
95°	13.7	14.0	14.2	14.1	14.0	14.0	13.9
97.5°	17.7	18.0	18.2	18.3	18.4	18.5	18.6
100°	20.2	20.7	21.1	21.2	21.4	21.5	21.7
102.5°	21.2	21.9	22.4	22.6	22.8	23.0	23.2
105°	22.1	22.9	23.4	23.7	24.0	24.3	24.6
107.5°	25.2	24.4	24.1	24.4	24.7	25.0	25.3
110°	35.0	27.8	24.4	24.7	25.0	25.3	25.5



TEST NUMBER: P331420

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	64.1	37.9	24.9	25.1	25.3	25.6	25.8
115°	99.7	66.4	47.2	42.0	36.9	31.7	26.5
117.5°	196.8	188.8	176.3	159.3	142.3	125.3	108.3
120°	239.6	240.4	236.0	226.3	216.6	206.9	197.2
122.5°	253.8	254.3	253.6	251.8	249.9	248.0	246.1
125°	274.7	275.2	275.6	275.8	276.0	276.2	276.4
127.5°	294.3	295.0	295.4	295.5	295.5	295.5	295.6
130°	306.6	307.4	307.8	307.7	307.6	307.6	307.5
132.5°	318.4	319.1	319.4	319.3	319.3	319.2	319.1
135°	335.5	336.2	336.5	336.4	336.2	336.1	335.9
137.5°	351.3	352.0	352.2	352.0	351.8	351.5	351.3
140°	361.5	362.1	362.3	361.9	361.6	361.2	360.8
142.5°	370.9	371.5	371.6	371.2	370.9	370.5	370.1
145°	384.0	384.5	384.6	384.2	383.9	383.5	383.1
147.5°	395.4	395.8	395.8	395.5	395.2	394.9	394.6
150°	402.5	403.0	403.0	402.7	402.3	401.9	401.6
152.5°	409.0	409.4	409.4	408.9	408.5	408.0	407.5
155°	417.7	418.2	418.1	417.5	417.0	416.4	415.8
157.5°	425.2	425.6	425.6	425.0	424.5	423.9	423.4
160°	429.4	429.8	429.8	429.3	428.8	428.3	427.8
162.5°	433.4	433.9	433.9	433.2	432.6	432.0	431.4
165°	438.3	438.8	438.8	438.3	437.8	437.3	436.8
167.5°	442.4	442.9	442.8	442.2	441.5	440.9	440.2
170°	444.5	445.0	444.9	444.3	443.6	443.0	442.3
172.5°	446.0	446.5	446.5	445.8	445.2	444.5	443.9
175°	447.7	448.2	448.1	447.4	446.7	445.9	445.2
177.5°	447.8	448.2	448.1	447.6	447.1	446.6	446.1
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8

(END OF REPORT)