

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331432

Luminaire Tested: **S122DIP-S1005D530U835-4F0-1E-UDD-D**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331432  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S1005D530U835-4F0-1E-UDD-D  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6149.6 lumens  
Efficiency: N/A  
Efficacy: 111.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42  
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')  
CIE Type: General Diffuse

Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331432  
CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-D

### Luminous Intensity Polar Plot





TEST NUMBER: P331432

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-D

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58
1	98	93	88	84	91	86	82	79	75	71	69	64	61	59	54	52	50	46
2	88	80	73	67	82	75	68	63	64	60	55	55	51	48	46	43	41	37
3	80	70	62	55	74	65	58	52	56	51	46	48	44	40	40	37	34	30
4	73	61	53	46	68	57	50	44	50	43	39	42	38	34	36	32	29	26
5	67	55	46	39	62	51	43	37	44	38	33	38	33	29	32	28	25	22
6	62	49	40	34	57	46	38	32	40	33	29	34	29	25	29	25	22	19
7	57	44	36	30	53	41	34	28	36	30	25	31	26	22	26	22	19	17
8	53	40	32	26	49	37	30	25	33	27	22	28	23	20	24	20	17	15
9	49	36	28	23	46	34	27	22	30	24	20	26	21	18	22	18	15	13
10	46	33	26	21	43	31	24	20	28	22	18	24	19	16	21	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17073	17073	17073
5°	17157	16435	16373
10°	17049	15949	15770
15°	16814	15435	15136
20°	16517	14884	14525
25°	16223	14353	13970
30°	15810	13808	13414
35°	15392	13280	13021
40°	14952	12831	12629
45°	14535	12429	12294
50°	14086	12066	11964
55°	13616	11675	11627
60°	13040	11269	11271
65°	12441	10795	10850
70°	11770	10285	10393
75°	10911	9784	9973
80°	9555	9272	9549
85°	8259	8830	9217



TEST NUMBER: P331432

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-D

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	100.2	1.6
10°-20°	287.3	4.7
20°-30°	435.4	7.1
30°-40°	530.3	8.6
40°-50°	570.5	9.3
50°-60°	554.1	9.0
60°-70°	483.8	7.9
70°-80°	372.4	6.1
80°-90°	251.7	4.1
90°-100°	196.3	3.2
100°-110°	214.0	3.5
110°-120°	318.9	5.2
120°-130°	435.6	7.1
130°-140°	433.4	7.0
140°-150°	388.2	6.3
150°-160°	309.4	5.0
160°-170°	199.4	3.2
170°-180°	68.6	1.1
0°-30°	822.9	13.4
0°-40°	1353.3	22.0
0°-60°	2477.9	40.3
0°-90°	3585.8	58.3
90°-120°	729.1	11.9
90°-150°	1986.4	32.3
90°-180°	2564.0	41.7
0°-180°	6149.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1057	1057	1057	1057	1057	
5°	1060	1056	1047	1055	1054	101
15°	1012	1014	1014	1028	1027	285
25°	920	930	944	962	967	423
35°	792	819	848	880	892	495
45°	650	692	745	790	808	501
55°	498	555	633	686	708	445
65°	340	416	506	566	588	338
75°	188	275	372	436	458	199
85°	55	150	248	310	334	59
90°	16	111	213	274	296	12
95°	46	103	197	255	275	51
105°	166	220	164	221	242	178
115°	306	335	414	228	198	301
125°	427	437	493	536	554	381
135°	526	536	555	591	604	407
145°	609	609	617	630	635	381
155°	671	666	672	675	671	309
165°	707	704	705	708	705	200
175°	723	719	720	723	719	69
180°	721	721	721	721	721	



TEST NUMBER: P331432

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-D

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1057.4	1057.4	1057.4	1057.4	1057.4	1057.4	1057.4	1057.4	1057.4	1057.4	1057.4
2.5°	1063.6	1062.8	1061.9	1061.1	1060.3	1058.9	1057.0	1055.1	1053.2	1051.3	1052.7
5°	1060.5	1059.5	1058.5	1057.4	1056.4	1054.9	1052.9	1050.8	1048.8	1046.7	1048.8
7.5°	1051.0	1050.3	1049.6	1049.0	1048.3	1047.2	1045.6	1044.0	1042.5	1040.9	1043.3
10°	1043.7	1043.0	1042.3	1041.6	1040.9	1040.1	1039.1	1038.0	1037.0	1036.0	1038.7
12.5°	1031.4	1031.5	1031.7	1031.8	1031.9	1031.6	1030.9	1030.1	1029.4	1028.6	1031.4
15°	1011.5	1012.2	1012.8	1013.5	1014.2	1014.5	1014.5	1014.5	1014.5	1014.5	1017.6
17.5°	985.7	987.2	988.6	990.0	991.4	992.7	993.8	994.9	996.0	997.1	1000.3
20°	968.6	970.3	972.0	973.7	975.4	976.9	978.3	979.6	981.0	982.4	986.1
22.5°	950.2	952.1	954.1	956.1	958.1	960.0	961.9	963.8	965.7	967.6	971.4
25°	919.5	921.9	924.3	926.7	929.1	931.8	934.8	937.9	941.0	944.0	948.1
27.5°	882.7	886.6	890.5	894.4	898.3	902.0	905.6	909.2	912.8	916.5	921.6
30°	858.2	862.6	867.1	871.5	875.9	880.4	884.8	889.2	893.6	898.1	903.5
32.5°	831.2	836.2	841.2	846.2	851.1	856.2	861.5	866.7	872.0	877.2	883.5
35°	792.3	798.1	803.9	809.7	815.5	821.6	828.1	834.5	841.0	847.5	855.0
37.5°	750.0	756.7	763.4	770.0	776.7	784.2	792.6	801.0	809.4	817.8	826.1
40°	721.8	729.3	736.8	744.3	751.8	760.1	769.3	778.5	787.7	796.9	805.8
42.5°	694.9	702.3	709.8	717.3	724.8	733.8	744.4	755.0	765.5	776.1	785.7
45°	649.8	659.0	668.2	677.4	686.6	697.1	709.1	721.0	732.9	744.8	755.4
47.5°	605.4	615.4	625.4	635.4	645.4	657.4	671.4	685.3	699.3	713.2	724.3
50°	574.7	585.3	595.8	606.4	616.9	629.9	645.2	660.5	675.8	691.2	702.8
52.5°	545.3	556.4	567.5	578.6	589.7	603.3	619.4	635.6	651.7	667.9	679.7
55°	498.1	510.3	522.6	534.9	547.1	562.1	579.8	597.5	615.2	632.9	645.2
57.5°	451.5	465.3	479.1	493.0	506.8	522.7	540.8	558.8	576.9	594.9	608.1
60°	418.4	433.0	447.7	462.3	477.0	494.0	513.4	532.8	552.2	571.6	584.6
62.5°	389.0	404.1	419.3	434.5	449.7	467.0	486.4	505.8	525.3	544.7	558.4
65°	340.2	356.9	373.6	390.3	407.0	425.4	445.5	465.5	485.6	505.7	519.7
67.5°	295.5	312.9	330.3	347.8	365.2	384.2	404.8	425.4	445.9	466.5	480.6
70°	263.6	281.3	299.0	316.7	334.4	353.8	375.0	396.1	417.2	438.3	452.9
72.5°	234.2	252.4	270.7	288.9	307.2	327.0	348.4	369.8	391.2	412.6	426.9
75°	188.5	207.6	226.6	245.7	264.8	285.2	307.0	328.8	350.6	372.4	387.0
77.5°	144.4	164.3	184.3	204.2	224.2	245.2	267.4	289.5	311.6	333.8	348.4
80°	114.9	135.7	156.5	177.3	198.0	219.5	241.6	263.8	285.9	308.0	322.3
82.5°	90.4	110.9	131.4	151.9	172.4	193.9	216.3	238.7	261.1	283.5	297.8
85°	55.2	76.3	97.4	118.5	139.6	161.1	182.9	204.7	226.5	248.3	262.6
87.5°	30.1	50.7	71.2	91.8	112.4	133.6	155.6	177.6	199.6	221.5	235.6
90°	15.8	36.9	57.9	78.9	100.0	121.8	144.6	167.3	190.0	212.7	226.9
92.5°	24.6	42.9	61.2	79.5	97.7	117.6	139.0	160.5	181.9	203.4	217.0
95°	46.2	58.4	70.5	82.7	94.9	111.6	132.9	154.1	175.3	196.6	210.1
97.5°	78.0	81.5	84.9	88.4	91.8	104.3	125.8	147.3	168.8	190.3	203.4
100°	103.1	99.8	96.5	93.2	89.9	98.8	119.9	140.9	162.0	183.0	196.5
102.5°	129.4	137.6	145.7	153.9	162.0	167.1	169.1	171.2	173.2	175.3	188.8
105°	166.3	179.7	193.0	206.4	219.7	219.4	205.5	191.5	177.6	163.6	176.8
107.5°	210.2	220.9	231.6	242.3	253.0	247.8	226.8	205.8	184.8	163.8	173.9
110°	237.3	246.6	255.8	265.1	274.3	270.5	253.7	236.9	220.0	203.2	202.5



TEST NUMBER: P331432

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-D

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	264.0	271.9	279.8	287.7	295.6	303.3	310.9	318.5	326.1	333.6	302.2
115°	306.2	311.9	317.6	323.4	329.1	341.0	359.3	377.5	395.7	413.9	370.5
117.5°	342.4	347.0	351.7	356.3	361.0	371.4	387.5	403.7	419.9	436.0	433.1
120°	369.9	373.0	376.1	379.2	382.3	391.7	407.4	423.1	438.8	454.6	465.5
122.5°	393.3	395.7	398.0	400.4	402.8	411.5	426.6	441.7	456.8	471.8	481.9
125°	427.3	428.9	430.4	431.9	433.4	440.7	453.8	466.9	480.0	493.1	503.1
127.5°	459.6	460.9	462.3	463.6	464.9	470.8	481.2	491.7	502.1	512.5	522.2
130°	480.1	481.6	483.1	484.6	486.1	491.1	499.5	507.9	516.4	524.8	534.2
132.5°	500.9	502.2	503.4	504.6	505.9	509.9	516.7	523.5	530.3	537.1	546.1
135°	526.5	528.4	530.2	532.1	534.0	537.1	541.6	546.0	550.5	554.9	563.2
137.5°	554.0	555.2	556.4	557.7	558.9	560.9	563.5	566.2	568.9	571.6	579.0
140°	571.9	572.5	573.1	573.7	574.3	575.6	577.5	579.5	581.4	583.4	589.9
142.5°	587.0	587.5	588.0	588.4	588.9	590.0	591.6	593.2	594.8	596.4	601.7
145°	609.0	608.9	608.8	608.7	608.6	609.5	611.5	613.4	615.4	617.4	620.2
147.5°	629.6	629.1	628.7	628.3	627.8	628.6	630.5	632.5	634.4	636.4	637.2
150°	642.9	642.1	641.3	640.5	639.7	640.2	642.1	643.9	645.8	647.6	648.3
152.5°	654.2	653.3	652.4	651.5	650.6	651.0	652.8	654.6	656.3	658.1	658.8
155°	670.6	669.6	668.5	667.5	666.4	666.6	668.0	669.4	670.8	672.2	672.9
157.5°	683.4	682.6	681.7	680.8	679.9	680.0	680.9	681.9	682.9	683.9	684.6
160°	691.0	690.3	689.6	688.9	688.2	688.2	688.9	689.6	690.3	691.0	691.7
162.5°	697.6	696.9	696.2	695.5	694.9	694.8	695.4	696.0	696.6	697.2	698.0
165°	706.6	705.9	705.2	704.5	703.8	703.7	704.0	704.3	704.7	705.0	705.9
167.5°	713.3	712.6	711.9	711.2	710.5	710.3	710.6	711.0	711.3	711.6	712.4
170°	717.0	716.4	715.7	715.0	714.3	714.0	714.3	714.5	714.7	715.0	715.8
172.5°	719.6	718.9	718.2	717.5	716.8	716.5	716.8	717.0	717.2	717.5	718.3
175°	722.8	722.0	721.2	720.4	719.5	719.3	719.5	719.7	719.9	720.2	721.0
177.5°	723.3	722.7	722.0	721.4	720.7	720.4	720.5	720.6	720.7	720.8	721.5
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331432

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-D

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1057.4	1057.4	1057.4	1057.4	1057.4	1057.4	1057.4	1057.4
2.5°	1054.0	1055.4	1056.8	1057.2	1056.6	1056.1	1055.5	1055.0
5°	1050.8	1052.9	1054.9	1055.7	1055.4	1055.1	1054.7	1054.4
7.5°	1045.8	1048.3	1050.7	1051.8	1051.4	1051.1	1050.7	1050.4
10°	1041.4	1044.2	1046.9	1048.1	1047.7	1047.4	1047.1	1046.7
12.5°	1034.1	1036.8	1039.5	1040.7	1040.4	1040.0	1039.7	1039.4
15°	1020.7	1023.7	1026.8	1028.2	1027.8	1027.5	1027.1	1026.8
17.5°	1003.5	1006.7	1009.9	1011.5	1011.5	1011.5	1011.5	1011.5
20°	989.8	993.6	997.3	999.2	999.2	999.2	999.2	999.2
22.5°	975.1	978.9	982.6	984.8	985.3	985.9	986.4	987.0
25°	952.2	956.3	960.4	962.9	964.0	965.0	966.0	967.0
27.5°	926.8	932.0	937.2	940.1	940.9	941.6	942.4	943.1
30°	909.0	914.4	919.9	923.1	924.1	925.1	926.2	927.2
32.5°	889.8	896.0	902.3	906.3	908.2	910.0	911.9	913.7
35°	862.5	870.0	877.5	882.4	884.8	887.2	889.6	891.9
37.5°	834.4	842.7	851.0	856.4	858.9	861.5	864.0	866.5
40°	814.6	823.5	832.3	838.3	841.4	844.4	847.5	850.6
42.5°	795.4	805.1	814.8	821.1	824.2	827.3	830.3	833.4
45°	765.9	776.5	787.0	794.0	797.4	800.8	804.2	807.6
47.5°	735.3	746.3	757.4	764.8	768.5	772.3	776.0	779.8
50°	714.3	725.9	737.5	745.2	748.9	752.6	756.4	760.1
52.5°	691.6	703.4	715.3	723.2	727.2	731.3	735.3	739.3
55°	657.5	669.7	682.0	690.3	694.7	699.2	703.6	708.0
57.5°	621.4	634.6	647.8	656.6	661.1	665.6	670.1	674.6
60°	597.5	610.5	623.4	632.3	637.0	641.8	646.6	651.3
62.5°	572.2	585.9	599.7	608.8	613.3	617.8	622.3	626.8
65°	533.7	547.6	561.6	570.8	575.2	579.6	584.1	588.5
67.5°	494.7	508.8	522.9	532.3	536.9	541.5	546.2	550.8
70°	467.6	482.2	496.9	506.2	510.3	514.4	518.5	522.6
72.5°	441.3	455.7	470.0	479.7	484.6	489.5	494.4	499.3
75°	401.7	416.3	431.0	440.5	444.9	449.4	453.8	458.2
77.5°	362.9	377.5	392.1	401.8	406.5	411.3	416.1	420.8
80°	336.6	351.0	365.3	374.8	379.6	384.3	389.1	393.9
82.5°	312.1	326.4	340.7	350.1	354.6	359.1	363.6	368.1
85°	276.9	291.2	305.5	315.0	319.8	324.6	329.3	334.1
87.5°	249.6	263.6	277.6	286.8	291.2	295.6	300.0	304.4
90°	241.1	255.3	269.5	278.8	283.1	287.4	291.8	296.1
92.5°	230.7	244.3	258.0	266.9	271.1	275.4	279.6	283.8
95°	223.6	237.2	250.7	259.4	263.4	267.4	271.3	275.3
97.5°	216.4	229.5	242.6	251.2	255.3	259.5	263.6	267.8
100°	210.1	223.6	237.1	245.9	249.8	253.8	257.8	261.8
102.5°	202.3	215.9	229.4	238.2	242.3	246.3	250.4	254.5
105°	190.0	203.2	216.4	225.1	229.3	233.5	237.7	242.0
107.5°	184.1	194.2	204.4	211.6	215.8	220.0	224.2	228.4
110°	201.8	201.1	200.4	202.2	206.4	210.6	214.8	219.0





TEST NUMBER: P331432

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-D

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	270.8	239.4	208.0	194.4	198.5	202.6	206.7	210.8
115°	327.0	283.5	240.0	216.0	211.4	206.8	202.2	197.6
117.5°	430.2	427.3	424.4	411.0	387.0	363.0	339.1	315.1
120°	476.4	487.3	498.3	497.8	485.9	474.0	462.0	450.1
122.5°	492.0	502.1	512.2	517.4	517.5	517.7	517.8	518.0
125°	513.1	523.1	533.1	539.8	543.2	546.6	550.1	553.5
127.5°	531.8	541.4	551.0	557.4	560.5	563.5	566.6	569.7
130°	543.7	553.1	562.6	568.6	571.2	573.8	576.4	579.1
132.5°	555.0	564.0	573.0	578.8	581.4	584.0	586.7	589.3
135°	571.5	579.8	588.2	593.6	596.0	598.5	601.0	603.5
137.5°	586.4	593.8	601.2	605.9	607.8	609.7	611.6	613.5
140°	596.4	602.9	609.4	613.3	614.8	616.3	617.7	619.2
142.5°	607.0	612.3	617.6	620.9	622.1	623.3	624.4	625.6
145°	623.1	625.9	628.8	630.8	631.9	633.0	634.2	635.3
147.5°	638.1	639.0	639.9	640.5	640.8	641.1	641.5	641.8
150°	649.0	649.7	650.4	650.5	649.9	649.3	648.7	648.2
152.5°	659.5	660.2	660.9	660.8	660.1	659.3	658.5	657.8
155°	673.6	674.3	675.0	674.8	673.9	673.0	672.1	671.1
157.5°	685.4	686.2	687.0	687.0	686.0	685.1	684.2	683.3
160°	692.3	693.0	693.7	693.7	692.9	692.1	691.2	690.4
162.5°	698.8	699.6	700.4	700.3	699.3	698.3	697.3	696.3
165°	706.7	707.5	708.3	708.3	707.5	706.7	705.9	705.0
167.5°	713.2	714.1	714.9	714.8	713.7	712.7	711.6	710.6
170°	716.6	717.4	718.2	718.1	717.0	716.0	715.0	713.9
172.5°	719.1	719.9	720.7	720.6	719.6	718.5	717.5	716.4
175°	721.8	722.6	723.4	723.3	722.1	720.9	719.8	718.6
177.5°	722.1	722.8	723.4	723.3	722.5	721.6	720.8	720.0
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2

(END OF REPORT)