

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931502

Luminaire Tested: DFN2DS-TR4F0-070DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931502
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-070DS840-RLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5955.9 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931502

CATALOG NUMBER: DFN2DS-TR4F0-070DS840-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931502

CATALOG NUMBER: DFN2DS-TR4F0-070DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2301	2301	2301
5°	2309	2272	2284
10°	2292	2235	2216
15°	2265	2168	2106
20°	2229	2074	1970
25°	2192	1966	1838
30°	2140	1856	1668
35°	2089	1736	1520
40°	2038	1612	1348
45°	1979	1472	1192
50°	1918	1331	1040
55°	1855	1180	893
60°	1782	1020	741
65°	1700	857	675
70°	1601	706	621
75°	1480	643	580
80°	1307	575	528
85°	1026	453	453

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1979 cd/sqm

TEST NUMBER: P931502

CATALOG NUMBER: DFN2DS-TR4F0-070DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.4	4.6
10°-20°	745.1	12.5
20°-30°	1046.1	17.6
30°-40°	1140.3	19.1
40°-50°	1048.1	17.6
50°-60°	823.1	13.8
60°-70°	535.7	9.0
70°-80°	275.8	4.6
80°-90°	70.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2062.6	34.6
0°-40°	3202.9	53.8
0°-60°	5074.0	85.2
0°-90°	5955.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5955.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2896	2896	2896	2896	2896	
5°	2896	2883	2849	2872	2865	275
15°	2754	2726	2636	2587	2561	776
25°	2500	2416	2243	2136	2097	1150
35°	2154	2021	1790	1625	1567	1348
45°	1761	1586	1310	1124	1061	1360
55°	1339	1135	852	695	645	1197
65°	904	692	456	367	359	896
75°	482	299	210	191	189	510
85°	113	58	50	50	50	135
90°	0	0	0	0	0	

TEST NUMBER: P931502

CATALOG NUMBER: DFN2DS-TR4F0-070DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2896.0	2896.0	2896.0	2896.0	2896.0
2.5°	2909.0	2896.0	2867.1	2893.5	2888.2
5°	2896.0	2882.9	2848.7	2872.4	2864.6
7.5°	2872.4	2856.8	2820.1	2830.3	2817.3
10°	2840.9	2822.6	2770.3	2762.3	2746.6
12.5°	2801.7	2778.1	2707.2	2691.6	2662.7
15°	2754.5	2725.5	2636.5	2586.8	2560.7
17.5°	2699.4	2657.5	2547.3	2489.7	2447.7
20°	2636.5	2584.0	2453.1	2387.7	2329.8
22.5°	2568.5	2508.1	2356.0	2267.0	2227.8
25°	2500.3	2416.3	2243.3	2136.0	2096.6
27.5°	2419.1	2329.8	2138.5	2015.4	1955.1
30°	2332.6	2232.8	2023.1	1889.7	1818.8
32.5°	2248.6	2128.0	1913.3	1756.0	1690.3
35°	2154.4	2020.6	1790.2	1625.0	1567.2
37.5°	2062.7	1918.3	1674.8	1493.7	1428.4
40°	1965.6	1808.5	1554.1	1368.1	1299.9
42.5°	1866.1	1698.4	1433.6	1239.5	1174.3
45°	1761.3	1585.5	1310.5	1124.2	1061.4
47.5°	1661.7	1475.7	1192.6	1006.3	948.7
50°	1551.5	1365.6	1077.2	896.2	841.4
52.5°	1443.9	1247.3	967.1	794.1	744.3
55°	1339.1	1134.7	851.7	694.6	644.8
57.5°	1231.8	1022.1	749.6	602.8	560.9
60°	1121.7	912.0	642.0	508.6	466.6
62.5°	1014.3	804.7	550.2	424.6	403.7
65°	904.2	691.8	456.1	367.1	359.0
67.5°	799.4	587.0	367.1	322.2	314.5
70°	689.3	484.9	303.9	277.8	267.2
72.5°	584.5	390.4	254.2	233.3	228.0
75°	482.2	298.6	209.6	191.3	188.8
77.5°	380.1	212.1	165.2	154.6	149.3
80°	285.6	152.1	125.7	115.4	115.4
82.5°	199.1	102.3	86.5	81.2	81.2
85°	112.6	57.6	49.7	49.7	49.7
87.5°	41.9	20.8	20.8	18.3	18.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931502

CATALOG NUMBER: DFN2DS-TR4F0-070DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.13	15.65	14.49	15.96	16.28	10.09	11.61	10.45	11.93	12.24
	3H	15.89	17.26	16.27	17.59	17.95	11.36	12.72	11.73	13.05	13.41
	4H	16.56	17.84	16.96	18.19	18.57	11.86	13.14	12.26	13.49	13.86
	6H	17.05	18.23	17.46	18.60	18.99	12.24	13.42	12.65	13.79	14.18
	8H	17.22	18.34	17.64	18.73	19.13	12.36	13.49	12.79	13.88	14.28
	12H	17.32	18.40	17.75	18.78	19.21	12.44	13.52	12.87	13.90	14.33
4H	2H	14.23	15.51	14.63	15.86	16.24	10.79	12.07	11.19	12.42	12.79
	3H	16.17	17.23	16.58	17.63	18.03	12.23	13.29	12.64	13.69	14.09
	4H	16.92	17.87	17.35	18.29	18.73	12.83	13.78	13.26	14.20	14.64
	6H	17.51	18.34	17.97	18.78	19.24	13.32	14.15	13.77	14.59	15.05
	8H	17.72	18.50	18.19	18.94	19.41	13.48	14.26	13.94	14.70	15.17
	12H	17.88	18.57	18.36	19.05	19.52	13.60	14.29	14.08	14.77	15.24
8H	4H	16.94	17.72	17.40	18.16	18.63	13.18	13.96	13.65	14.40	14.87
	6H	17.58	18.22	18.07	18.71	19.19	13.77	14.41	14.27	14.90	15.38
	8H	17.83	18.40	18.34	18.91	19.40	13.99	14.57	14.50	15.08	15.56
	12H	18.03	18.54	18.54	19.03	19.60	14.17	14.68	14.68	15.17	15.74
12H	4H	16.92	17.62	17.41	18.10	18.57	13.23	13.92	13.71	14.40	14.87
	6H	17.56	18.14	18.07	18.65	19.13	13.83	14.41	14.35	14.92	15.41
	8H	17.84	18.35	18.35	18.85	19.41	14.11	14.62	14.61	15.11	15.67

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

7 of 7