

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331453

Luminaire Tested: **S122DIP-S1005D925U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331453  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S1005D925U835-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7756.9 lumens  
Efficiency: N/A  
Efficacy: 116.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331453  
CATALOG NUMBER: S122DIP-S1005D925U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331453

CATALOG NUMBER: S122DIP-S1005D925U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52				
1	98	94	90	87	91	87	84	81	74	72	69	62	61	59	51	50	49	44				
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	41	37				
3	82	72	65	59	75	67	61	55	57	52	48	48	45	42	40	38	35	31				
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30	27				
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	27	23				
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23	20				
7	58	46	38	33	54	43	36	31	37	32	27	32	27	24	27	23	21	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16				
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15				
10	47	35	28	23	44	33	26	22	29	23	20	25	21	17	21	18	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	25733	25733	25733
5°	25832	25459	25608
10°	25678	25201	25327
15°	25361	24874	24849
20°	24911	24383	24357
25°	24464	23779	23779
30°	23886	23228	23029
35°	23349	22565	22231
40°	22675	21901	21479
45°	22012	21240	20717
50°	21288	20557	19826
55°	20535	19758	19023
60°	19695	18807	18112
65°	18793	17857	17039
70°	17651	16711	15918
75°	16064	15390	15009
80°	14254	13826	13110
85°	11634	11078	9930



TEST NUMBER: P331453

CATALOG NUMBER: S122DIP-S1005D925U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	149.9	1.9
10°-20°	421.7	5.4
20°-30°	619.8	8.0
30°-40°	720.0	9.3
40°-50°	719.2	9.3
50°-60°	627.2	8.1
60°-70°	463.8	6.0
70°-80°	262.7	3.4
80°-90°	73.8	1.0
90°-100°	42.1	0.5
100°-110°	154.4	2.0
110°-120°	412.7	5.3
120°-130°	681.3	8.8
130°-140°	724.5	9.3
140°-150°	673.4	8.7
150°-160°	541.4	7.0
160°-170°	348.9	4.5
170°-180°	120.1	1.5
0°-30°	1191.4	15.4
0°-40°	1911.4	24.6
0°-60°	3257.9	42.0
0°-90°	4058.1	52.3
90°-120°	609.2	7.9
90°-150°	2688.4	34.7
90°-180°	3699.0	47.7
0°-180°	7756.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1594	1587	1571	1582	1580	151
15°	1517	1507	1488	1493	1487	427
25°	1373	1360	1335	1338	1335	631
35°	1185	1169	1145	1136	1128	739
45°	964	953	930	914	907	744
55°	730	720	702	684	676	652
65°	492	482	467	454	446	486
75°	258	254	247	238	241	275
85°	63	61	60	55	54	72
90°	1	11	18	23	25	6
95°	59	31	36	40	39	73
105°	278	290	56	65	69	297
115°	525	541	564	160	75	517
125°	742	755	772	778	781	662
135°	919	933	942	950	949	709
145°	1066	1066	1080	1086	1082	666
155°	1174	1166	1176	1181	1174	541
165°	1237	1232	1234	1240	1234	349
175°	1265	1259	1260	1266	1258	120
180°	1262	1262	1262	1262	1262	



TEST NUMBER: P331453

CATALOG NUMBER: S122DIP-S1005D925U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1601.2	1599.8	1598.5	1597.1	1595.7	1593.6	1590.6	1587.6	1584.6	1581.6	1584.3
5°	1593.8	1592.5	1591.1	1589.7	1588.4	1585.8	1582.1	1578.3	1574.6	1570.8	1573.6
7.5°	1579.7	1577.6	1575.5	1573.4	1571.3	1568.3	1564.5	1560.7	1556.9	1553.1	1555.8
10°	1566.2	1563.9	1561.5	1559.1	1556.7	1553.5	1549.4	1545.3	1541.2	1537.1	1539.9
12.5°	1547.9	1545.7	1543.6	1541.5	1539.4	1536.3	1532.2	1528.1	1524.1	1520.0	1521.9
15°	1517.2	1515.2	1513.1	1511.1	1509.0	1505.8	1501.4	1496.9	1492.5	1488.1	1489.5
17.5°	1478.0	1475.9	1473.9	1471.8	1469.8	1466.5	1462.0	1457.5	1453.0	1448.6	1450.1
20°	1449.8	1447.7	1445.7	1443.6	1441.6	1438.2	1433.4	1428.7	1423.9	1419.1	1420.1
22.5°	1421.6	1418.7	1415.9	1413.0	1410.1	1406.5	1402.0	1397.5	1393.0	1388.5	1388.7
25°	1373.2	1370.4	1367.7	1365.0	1362.3	1358.0	1352.2	1346.4	1340.6	1334.8	1335.5
27.5°	1318.0	1315.5	1313.1	1310.6	1308.2	1304.7	1300.1	1295.5	1291.0	1286.4	1285.4
30°	1281.2	1278.5	1275.7	1273.0	1270.3	1266.4	1261.3	1256.2	1251.1	1245.9	1244.9
32.5°	1242.0	1239.8	1237.6	1235.4	1233.2	1229.5	1224.1	1218.7	1213.3	1207.9	1206.1
35°	1184.6	1181.2	1177.8	1174.4	1171.0	1166.6	1161.1	1155.7	1150.3	1144.8	1142.8
37.5°	1120.0	1117.0	1114.0	1111.0	1108.0	1103.8	1098.3	1092.9	1087.4	1082.0	1079.4
40°	1075.8	1073.1	1070.4	1067.7	1064.9	1060.9	1055.4	1050.0	1044.5	1039.1	1036.0
42.5°	1032.9	1030.2	1027.5	1024.8	1022.0	1017.9	1012.5	1007.0	1001.6	996.1	992.8
45°	964.0	961.6	959.2	956.8	954.4	950.7	945.6	940.5	935.4	930.2	926.5
47.5°	895.3	893.1	890.8	888.6	886.3	882.5	877.2	871.9	866.6	861.3	857.3
50°	847.5	845.8	844.1	842.4	840.7	837.4	832.7	827.9	823.1	818.4	813.6
52.5°	800.9	798.7	796.4	794.2	791.9	788.5	784.0	779.5	775.1	770.6	766.6
55°	729.5	727.4	725.4	723.4	721.3	718.2	714.2	710.1	706.0	701.9	697.8
57.5°	657.8	656.1	654.5	652.9	651.2	648.2	643.7	639.2	634.7	630.2	626.2
60°	609.9	608.6	607.2	605.9	604.5	601.4	596.7	591.9	587.1	582.4	578.6
62.5°	563.4	561.2	559.0	556.8	554.6	551.7	548.0	544.4	540.7	537.0	533.5
65°	491.9	489.9	487.9	485.8	483.8	481.0	477.6	474.2	470.8	467.4	464.4
67.5°	419.3	417.7	416.0	414.4	412.8	410.4	407.3	404.3	401.2	398.2	395.8
70°	373.9	372.6	371.2	369.9	368.5	366.3	363.2	360.1	357.1	354.0	351.6
72.5°	327.3	326.0	324.6	323.3	321.9	320.2	318.3	316.3	314.3	312.3	309.9
75°	257.5	256.8	256.1	255.4	254.7	253.5	251.8	250.1	248.4	246.7	244.7
77.5°	194.9	193.8	192.6	191.5	190.3	189.4	188.7	188.0	187.3	186.7	185.6
80°	153.3	152.9	152.6	152.2	151.9	151.4	150.7	150.0	149.3	148.7	147.6
82.5°	114.0	114.0	113.9	113.8	113.7	113.5	113.1	112.7	112.3	111.9	110.6
85°	62.8	62.5	62.2	61.8	61.5	61.1	60.8	60.4	60.1	59.8	58.7
87.5°	22.3	22.2	22.1	22.0	21.9	21.7	21.5	21.3	21.0	20.8	20.2
90°	0.9	3.1	5.4	7.6	9.8	11.8	13.4	15.0	16.6	18.3	19.3
92.5°	18.4	18.2	18.0	17.8	17.6	17.9	18.8	19.6	20.4	21.2	21.7
95°	59.4	52.7	46.0	39.3	32.6	29.9	31.4	32.8	34.2	35.6	36.6
97.5°	117.8	98.9	80.1	61.2	42.3	34.5	37.8	41.1	44.4	47.7	48.5
100°	161.7	133.8	106.0	78.2	50.4	38.3	41.7	45.2	48.6	52.1	53.7
102.5°	209.9	204.0	198.1	192.2	186.3	169.0	140.1	111.2	82.4	53.5	55.6
105°	277.6	283.7	289.8	295.9	302.0	277.3	221.9	166.5	111.1	55.7	57.9
107.5°	354.9	359.8	364.7	369.6	374.6	343.8	277.3	210.9	144.4	78.0	75.7
110°	404.6	408.9	413.1	417.4	421.6	394.4	335.8	277.1	218.5	159.8	139.5



TEST NUMBER: P331453

CATALOG NUMBER: S122DIP-S1005D925U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	451.3	455.1	458.9	462.7	466.4	461.1	446.6	432.1	417.6	403.1	329.1
115°	525.1	528.6	532.0	535.5	538.9	543.2	548.3	553.4	558.4	563.5	469.5
117.5°	591.1	594.9	598.8	602.7	606.5	610.2	613.7	617.2	620.7	624.1	601.4
120°	639.3	642.3	645.4	648.4	651.5	654.8	658.5	662.1	665.8	669.4	671.9
122.5°	680.2	683.4	686.6	689.8	693.0	696.6	700.6	704.6	708.6	712.6	714.0
125°	742.5	745.1	747.8	750.4	753.1	756.3	760.2	764.0	767.9	771.7	773.2
127.5°	798.9	801.9	804.8	807.7	810.6	813.5	816.4	819.3	822.2	825.1	827.1
130°	834.8	838.0	841.2	844.5	847.7	850.5	852.7	854.9	857.2	859.4	861.6
132.5°	871.3	874.0	876.8	879.6	882.3	884.8	887.1	889.3	891.5	893.7	895.7
135°	918.8	922.0	925.3	928.5	931.8	934.3	936.1	938.0	939.8	941.6	943.6
137.5°	966.8	969.1	971.4	973.6	975.9	978.1	980.1	982.2	984.3	986.4	988.3
140°	998.2	999.9	1001.5	1003.1	1004.7	1006.7	1008.9	1011.1	1013.4	1015.6	1017.4
142.5°	1024.5	1026.0	1027.5	1028.9	1030.4	1032.4	1034.9	1037.5	1040.1	1042.6	1044.3
145°	1065.8	1065.6	1065.4	1065.2	1065.0	1066.6	1070.1	1073.5	1077.0	1080.4	1081.8
147.5°	1101.8	1101.0	1100.3	1099.5	1098.7	1100.0	1103.4	1106.9	1110.3	1113.7	1114.7
150°	1125.2	1123.8	1122.3	1120.9	1119.5	1120.4	1123.7	1126.9	1130.2	1133.4	1134.6
152.5°	1144.9	1143.3	1141.7	1140.2	1138.6	1139.3	1142.4	1145.5	1148.6	1151.7	1152.9
155°	1173.6	1171.8	1169.9	1168.1	1166.3	1166.6	1169.0	1171.5	1173.9	1176.3	1177.5
157.5°	1196.0	1194.5	1193.0	1191.4	1189.9	1190.0	1191.7	1193.4	1195.1	1196.8	1198.2
160°	1209.2	1208.0	1206.8	1205.5	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2	1210.4
162.5°	1220.9	1219.7	1218.5	1217.2	1216.0	1215.9	1217.0	1218.0	1219.1	1220.2	1221.5
165°	1236.6	1235.4	1234.2	1232.9	1231.7	1231.4	1232.0	1232.6	1233.3	1233.9	1235.3
167.5°	1248.3	1247.1	1245.9	1244.6	1243.4	1243.1	1243.7	1244.2	1244.8	1245.4	1246.8
170°	1254.9	1253.6	1252.4	1251.2	1250.0	1249.6	1250.0	1250.4	1250.8	1251.2	1252.6
172.5°	1259.2	1258.0	1256.8	1255.6	1254.4	1254.0	1254.4	1254.8	1255.2	1255.6	1257.0
175°	1264.9	1263.5	1262.1	1260.6	1259.2	1258.7	1259.1	1259.5	1259.9	1260.3	1261.8
177.5°	1265.8	1264.7	1263.6	1262.4	1261.3	1260.8	1261.0	1261.1	1261.3	1261.4	1262.6
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331453

CATALOG NUMBER: S122DIP-S1005D925U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1587.0	1589.7	1592.5	1593.6	1593.0	1592.5	1591.9	1591.4
5°	1576.3	1579.0	1581.7	1582.8	1582.1	1581.4	1580.7	1580.0
7.5°	1558.5	1561.2	1564.0	1565.0	1564.2	1563.5	1562.7	1562.0
10°	1542.6	1545.3	1548.0	1548.9	1547.9	1546.8	1545.8	1544.8
12.5°	1523.8	1525.7	1527.6	1528.2	1527.4	1526.7	1525.9	1525.2
15°	1490.8	1492.2	1493.5	1493.4	1491.7	1490.0	1488.3	1486.6
17.5°	1451.7	1453.3	1454.8	1454.8	1453.1	1451.5	1449.9	1448.2
20°	1421.2	1422.2	1423.2	1423.0	1421.7	1420.3	1419.0	1417.6
22.5°	1388.9	1389.1	1389.3	1389.0	1388.2	1387.4	1386.5	1385.7
25°	1336.2	1336.9	1337.6	1337.6	1336.9	1336.2	1335.5	1334.8
27.5°	1284.4	1283.3	1282.3	1281.0	1279.4	1277.7	1276.1	1274.5
30°	1243.9	1242.9	1241.9	1240.7	1239.3	1237.9	1236.6	1235.2
32.5°	1204.3	1202.4	1200.6	1199.0	1197.6	1196.3	1194.9	1193.5
35°	1140.7	1138.7	1136.6	1134.8	1133.1	1131.4	1129.6	1127.9
37.5°	1076.9	1074.4	1071.9	1069.8	1068.2	1066.5	1064.9	1063.3
40°	1032.9	1029.9	1026.8	1024.6	1023.2	1021.9	1020.5	1019.1
42.5°	989.5	986.1	982.8	980.2	978.3	976.4	974.5	972.5
45°	922.8	919.0	915.3	912.7	911.3	910.0	908.6	907.3
47.5°	853.4	849.4	845.5	842.5	840.5	838.6	836.6	834.6
50°	808.8	804.1	799.3	796.1	794.4	792.7	791.0	789.3
52.5°	762.7	758.7	754.8	751.7	749.4	747.2	744.9	742.7
55°	693.7	689.6	685.6	682.7	681.0	679.3	677.6	675.8
57.5°	622.1	618.1	614.1	611.4	610.2	608.9	607.6	606.3
60°	574.9	571.1	567.4	565.0	564.0	563.0	561.9	560.9
62.5°	530.1	526.6	523.1	520.7	519.4	518.1	516.8	515.5
65°	461.3	458.2	455.2	452.8	451.1	449.4	447.7	446.0
67.5°	393.4	391.0	388.6	386.7	385.4	384.0	382.7	381.3
70°	349.2	346.9	344.5	342.6	341.2	339.9	338.5	337.2
72.5°	307.6	305.2	302.8	301.1	300.0	298.9	297.8	296.7
75°	242.7	240.6	238.6	237.9	238.6	239.2	239.9	240.6
77.5°	184.6	183.6	182.6	181.6	180.6	179.7	178.7	177.8
80°	146.6	145.6	144.6	143.7	143.0	142.4	141.7	141.0
82.5°	109.3	108.0	106.7	106.0	105.8	105.7	105.6	105.4
85°	57.7	56.7	55.7	55.0	54.7	54.3	54.0	53.6
87.5°	19.6	19.0	18.4	18.0	17.8	17.6	17.4	17.2
90°	20.3	21.3	22.3	23.0	23.4	23.8	24.3	24.7
92.5°	22.2	22.8	23.3	23.7	23.9	24.2	24.4	24.7
95°	37.6	38.7	39.7	40.1	39.9	39.7	39.5	39.3
97.5°	49.3	50.1	50.9	51.4	51.7	51.9	52.2	52.4
100°	55.3	56.9	58.6	59.6	60.0	60.4	60.8	61.2
102.5°	57.7	59.9	62.0	63.3	63.9	64.4	65.0	65.6
105°	60.2	62.4	64.6	66.2	67.0	67.8	68.6	69.4
107.5°	73.4	71.2	68.9	68.2	69.0	69.8	70.6	71.4
110°	119.2	98.9	78.6	68.9	69.7	70.5	71.3	72.2





TEST NUMBER: P331453

CATALOG NUMBER: S122DIP-S1005D925U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	255.1	181.0	107.0	70.3	70.9	71.6	72.2	72.9
115°	375.6	281.6	187.6	133.3	118.7	104.1	89.5	74.9
117.5°	578.7	556.0	533.2	497.8	449.8	401.8	353.8	305.8
120°	674.3	676.8	679.2	666.7	639.3	611.9	584.5	557.1
122.5°	715.5	716.9	718.4	716.5	711.2	705.8	700.5	695.2
125°	774.6	776.0	777.4	778.4	779.0	779.6	780.3	780.9
127.5°	829.2	831.3	833.4	834.4	834.6	834.7	834.8	834.9
130°	863.9	866.1	868.3	869.4	869.2	868.9	868.7	868.5
132.5°	897.6	899.5	901.4	902.2	902.0	901.8	901.6	901.4
135°	945.7	947.7	949.7	950.5	950.1	949.7	949.3	948.9
137.5°	990.3	992.3	994.3	995.0	994.3	993.6	992.9	992.2
140°	1019.2	1021.1	1022.9	1023.3	1022.3	1021.3	1020.3	1019.2
142.5°	1045.9	1047.6	1049.3	1049.6	1048.6	1047.6	1046.6	1045.5
145°	1083.3	1084.7	1086.1	1086.3	1085.3	1084.3	1083.3	1082.3
147.5°	1115.8	1116.8	1117.9	1118.0	1117.1	1116.3	1115.4	1114.6
150°	1135.8	1137.1	1138.3	1138.4	1137.4	1136.3	1135.3	1134.3
152.5°	1154.1	1155.3	1156.5	1156.5	1155.1	1153.8	1152.5	1151.1
155°	1178.8	1180.0	1181.2	1181.0	1179.4	1177.7	1176.1	1174.5
157.5°	1199.5	1200.9	1202.3	1202.2	1200.6	1199.0	1197.4	1195.9
160°	1211.6	1212.9	1214.1	1214.0	1212.5	1211.1	1209.7	1208.3
162.5°	1222.9	1224.3	1225.7	1225.5	1223.8	1222.0	1220.3	1218.5
165°	1236.7	1238.1	1239.5	1239.5	1238.1	1236.7	1235.3	1233.9
167.5°	1248.2	1249.6	1251.1	1250.8	1249.0	1247.2	1245.4	1243.5
170°	1254.1	1255.5	1256.9	1256.7	1254.9	1253.0	1251.2	1249.4
172.5°	1258.4	1259.9	1261.3	1261.1	1259.2	1257.4	1255.6	1253.8
175°	1263.2	1264.6	1266.0	1265.7	1263.7	1261.7	1259.6	1257.6
177.5°	1263.7	1264.9	1266.0	1265.8	1264.4	1262.9	1261.4	1260.0
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2

(END OF REPORT)