

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331258

Luminaire Tested: **S122DIP-S290D725U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331258
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S290D725U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4203.6 lumens
Efficiency: N/A
Efficacy: 134.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331258

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331258

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	35	34	33	27
2	86	79	73	68	77	71	66	62	56	53	50	43	41	39	31	30	28	23
3	78	69	62	57	70	63	57	52	50	46	43	38	36	33	28	26	25	20
4	72	61	54	48	64	56	49	44	45	40	36	34	31	29	25	23	21	17
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	22	20	19	15
6	61	49	41	36	54	45	38	33	36	31	28	28	25	22	20	18	17	13
7	56	44	37	31	50	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	28	47	37	30	26	30	25	22	23	20	17	17	15	13	11
9	48	37	30	25	43	33	27	23	27	23	19	21	18	16	16	14	12	10
10	45	34	27	22	41	31	25	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9544	9544	9544	9544
5°	10699	9606	8512	9606
10°	12260	9527	7366	9527
15°	13563	9352	6509	9352
20°	13357	9165	5933	9165
25°	12043	8915	5569	8915
30°	9952	8516	5302	8516
35°	7253	8099	5113	8099
40°	5794	7609	5008	7609
45°	5062	7040	4866	7040
50°	4760	6488	4770	6488
55°	4386	5928	4642	5928
60°	4020	5331	4447	5331
65°	3664	4798	4252	4798
70°	3323	4277	3970	4277
75°	2951	3699	3512	3699
80°	2538	3059	2827	3059
85°	2279	2279	1686	2279



TEST NUMBER: P331258

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	1.3
10°-20°	163.7	3.9
20°-30°	237.5	5.7
30°-40°	250.6	6.0
40°-50°	221.9	5.3
50°-60°	177.1	4.2
60°-70°	120.4	2.9
70°-80°	61.7	1.5
80°-90°	17.3	0.4
90°-100°	33.0	0.8
100°-110°	120.9	2.9
110°-120°	323.3	7.7
120°-130°	533.6	12.7
130°-140°	567.5	13.5
140°-150°	527.5	12.5
150°-160°	424.1	10.1
160°-170°	273.3	6.5
170°-180°	94.1	2.2
0°-30°	457.5	10.9
0°-40°	708.1	16.8
0°-60°	1107.1	26.3
0°-90°	1306.5	31.1
90°-120°	477.2	11.4
90°-150°	2105.7	50.1
90°-180°	2897.0	68.9
0°-180°	4203.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	591	591	591	591	591	
5°	660	593	525	593	660	66
15°	811	560	389	560	811	224
25°	676	500	313	500	676	306
35°	368	411	259	411	368	239
45°	222	308	213	308	222	174
55°	156	211	165	211	156	140
65°	96	126	111	126	96	95
75°	47	59	56	59	47	51
85°	12	12	9	12	12	14
90°	19	1	19	1	19	9
95°	31	46	31	46	31	29
105°	54	218	54	218	54	57
115°	59	411	59	411	59	147
125°	612	582	612	582	612	529
135°	743	720	743	720	743	573
145°	848	835	848	835	848	530
155°	920	919	920	919	920	424
165°	966	969	966	969	966	273
175°	985	991	985	991	985	94
180°	989	989	989	989	989	



TEST NUMBER: P331258

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	618.3	618.5	618.9	616.0	615.6	615.6	613.1	610.9	608.3	604.9	605.3
5°	660.1	662.6	663.5	660.8	656.7	656.3	652.4	646.1	640.1	635.4	632.0
7.5°	710.0	711.0	708.8	705.2	702.2	696.7	689.5	682.5	672.6	663.6	656.9
10°	747.8	749.2	745.3	740.1	735.8	729.4	719.0	708.3	695.4	682.9	672.9
12.5°	776.5	779.9	774.9	774.3	766.9	758.1	745.7	740.3	722.1	704.7	693.9
15°	811.4	811.2	811.7	807.3	801.9	800.5	787.4	773.0	747.4	737.1	719.4
17.5°	801.3	804.8	806.4	806.3	806.2	805.3	801.1	792.1	779.2	762.6	742.2
20°	777.4	781.9	782.6	787.8	790.8	794.6	796.2	793.7	785.8	771.9	754.2
22.5°	740.3	741.6	743.7	751.8	758.2	767.9	772.9	781.4	778.3	771.5	756.7
25°	676.0	673.8	681.7	685.8	700.6	716.0	727.2	739.4	750.3	756.9	752.6
27.5°	598.9	595.5	607.4	618.3	630.2	647.0	664.3	684.8	701.8	723.2	730.5
30°	533.8	535.9	547.2	558.8	577.0	600.6	620.2	642.6	667.0	690.8	707.4
32.5°	463.7	471.5	478.7	496.5	512.5	538.8	567.5	595.6	625.9	653.0	678.7
35°	368.0	377.1	387.1	400.0	422.5	448.6	476.6	514.5	555.9	592.9	623.3
37.5°	309.8	308.3	314.0	323.4	341.6	362.7	394.9	432.3	481.0	524.5	567.5
40°	274.9	274.0	278.0	286.7	300.5	316.0	344.2	377.1	422.3	475.5	526.6
42.5°	250.9	251.4	253.7	259.8	269.3	282.0	303.1	331.1	372.5	422.6	477.5
45°	221.7	223.3	225.8	228.8	234.2	244.7	256.5	276.5	309.2	351.0	405.0
47.5°	200.7	200.8	203.3	205.9	209.1	215.0	224.7	237.2	260.3	294.3	340.8
50°	189.5	187.9	189.7	191.7	195.1	199.2	205.6	217.4	232.8	260.3	299.2
52.5°	175.6	175.7	177.3	178.1	181.1	185.2	191.0	199.2	213.2	234.7	266.6
55°	155.8	157.0	157.9	159.2	162.0	164.9	169.5	174.9	185.8	201.9	225.6
57.5°	137.2	137.6	138.5	141.1	142.8	145.5	149.8	154.8	161.9	173.8	191.6
60°	124.5	124.5	126.3	127.4	129.7	132.4	135.8	140.6	147.0	156.7	171.1
62.5°	112.9	112.7	113.4	115.3	117.0	119.5	122.9	127.0	133.0	141.7	153.4
65°	95.9	95.4	96.8	97.2	99.0	101.5	104.3	108.6	113.4	119.7	130.2
67.5°	79.5	80.1	80.8	81.6	82.6	85.3	87.1	90.1	94.2	99.5	106.5
70°	70.4	70.4	70.4	71.1	72.5	73.8	75.6	78.1	82.0	86.5	92.9
72.5°	60.2	61.0	61.7	61.3	63.0	63.8	66.0	67.4	71.1	74.0	79.6
75°	47.3	47.3	47.3	48.4	49.1	49.7	51.1	52.5	54.3	57.9	60.9
77.5°	35.3	35.2	35.4	35.7	36.4	37.2	37.6	38.8	40.5	42.2	44.7
80°	27.3	27.7	27.9	28.4	28.4	28.8	29.1	30.7	31.8	32.9	34.5
82.5°	21.1	21.2	21.2	21.3	21.5	21.8	22.4	22.9	23.3	24.2	25.4
85°	12.3	12.0	12.0	12.5	12.3	12.3	12.7	13.2	13.2	13.4	14.1
87.5°	8.6	8.5	8.6	8.4	8.3	8.4	8.2	7.9	7.9	7.9	7.9
90°	19.3	19.0	18.7	18.4	18.0	17.5	16.7	15.9	15.1	14.3	13.0
92.5°	19.3	19.1	18.9	18.7	18.6	18.2	17.8	17.4	17.0	16.6	16.0
95°	30.8	30.9	31.1	31.2	31.4	31.1	30.3	29.5	28.7	27.9	26.8
97.5°	41.1	40.9	40.7	40.5	40.3	39.9	39.2	38.6	38.0	37.3	34.8
100°	47.9	47.6	47.3	47.0	46.7	45.9	44.6	43.3	42.0	40.8	38.1
102.5°	51.4	50.9	50.5	50.0	49.6	48.5	46.9	45.2	43.6	41.9	64.5
105°	54.4	53.7	53.1	52.5	51.8	50.6	48.9	47.1	45.4	43.6	87.0
107.5°	55.9	55.3	54.7	54.0	53.4	54.0	55.7	57.5	59.3	61.1	113.1
110°	56.5	55.9	55.2	54.6	54.0	61.6	77.5	93.4	109.3	125.2	171.1



TEST NUMBER: P331258

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	57.1	56.6	56.1	55.6	55.0	83.8	141.8	199.8	257.8	315.7	327.1
115°	58.7	70.1	81.5	93.0	104.4	147.0	220.6	294.2	367.8	441.4	437.4
117.5°	239.5	277.1	314.7	352.3	389.9	417.6	435.4	453.3	471.1	488.9	486.1
120°	436.4	457.8	479.3	500.7	522.2	532.0	530.1	528.2	526.2	524.3	521.5
122.5°	544.5	548.7	552.8	557.0	561.2	562.7	561.5	560.4	559.2	558.1	555.0
125°	611.6	611.1	610.7	610.2	609.7	608.9	607.8	606.7	605.6	604.5	601.4
127.5°	654.0	653.9	653.8	653.7	653.6	652.7	651.1	649.5	647.9	646.2	644.0
130°	680.3	680.4	680.6	680.8	680.9	680.1	678.4	676.6	674.9	673.1	671.4
132.5°	706.0	706.2	706.4	706.5	706.7	706.0	704.5	703.0	701.5	700.0	698.3
135°	743.2	743.5	743.9	744.2	744.5	743.9	742.3	740.7	739.1	737.5	736.1
137.5°	777.1	777.7	778.2	778.8	779.3	778.8	777.2	775.7	774.1	772.6	770.9
140°	798.3	799.1	799.9	800.7	801.5	801.2	799.7	798.3	796.9	795.5	793.7
142.5°	818.9	819.7	820.5	821.3	822.1	821.8	820.5	819.2	817.9	816.6	814.6
145°	847.7	848.5	849.3	850.1	850.8	850.7	849.6	848.5	847.4	846.2	843.5
147.5°	873.0	873.7	874.3	875.0	875.7	875.6	874.8	873.9	873.1	872.3	869.6
150°	888.4	889.2	890.0	890.8	891.6	891.5	890.6	889.6	888.7	887.7	885.2
152.5°	901.6	902.7	903.7	904.8	905.8	905.9	904.9	903.9	903.0	902.0	899.6
155°	919.9	921.2	922.5	923.7	925.0	925.2	924.2	923.3	922.3	921.3	919.4
157.5°	936.7	937.9	939.1	940.4	941.6	941.7	940.6	939.5	938.5	937.4	936.0
160°	946.4	947.5	948.6	949.7	950.8	950.9	950.0	949.0	948.1	947.1	946.1
162.5°	954.4	955.8	957.1	958.5	959.9	960.0	958.9	957.8	956.8	955.7	954.9
165°	966.4	967.5	968.6	969.8	970.9	970.9	969.8	968.6	967.5	966.4	965.9
167.5°	974.0	975.4	976.9	978.3	979.7	979.9	978.8	977.7	976.5	975.4	975.0
170°	978.6	980.0	981.4	982.9	984.3	984.5	983.3	982.2	981.1	980.0	979.7
172.5°	982.0	983.4	984.9	986.3	987.7	987.9	986.8	985.7	984.6	983.4	983.1
175°	985.0	986.6	988.2	989.8	991.4	991.6	990.5	989.4	988.3	987.2	986.8
177.5°	986.9	988.0	989.2	990.3	991.5	991.6	990.7	989.8	988.9	988.0	987.9
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331258

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	606.5	605.1	604.2	600.9	598.0	595.1	594.2	594.5	590.5	586.7	585.1
5°	630.2	625.6	621.3	615.2	607.9	599.9	595.9	592.7	584.7	576.1	571.1
7.5°	651.3	644.8	636.5	625.0	614.4	601.9	593.9	586.9	575.3	563.1	555.6
10°	664.2	655.4	644.7	630.6	617.7	602.4	591.8	581.1	567.5	552.9	543.8
12.5°	675.3	663.4	652.9	634.8	619.5	600.4	587.8	572.7	558.4	541.1	532.2
15°	701.7	679.7	659.7	639.2	620.4	593.8	579.7	559.5	540.7	519.3	509.1
17.5°	722.1	697.3	665.9	639.9	617.9	588.4	567.8	543.6	521.3	496.9	483.0
20°	733.7	705.3	671.5	640.6	614.3	580.6	558.1	533.4	507.3	479.8	464.8
22.5°	740.6	710.8	677.3	637.9	607.0	574.3	546.0	518.8	492.4	462.7	447.0
25°	742.8	715.6	680.1	635.6	597.9	560.9	526.8	500.4	468.4	440.7	417.8
27.5°	732.0	712.5	678.4	631.3	587.4	544.1	506.1	476.3	442.5	412.4	389.3
30°	718.7	707.4	674.2	627.0	579.0	532.5	490.7	456.8	423.2	392.8	369.1
32.5°	698.2	695.8	666.6	620.8	570.1	517.8	474.5	440.3	403.0	373.1	350.6
35°	657.9	668.8	650.4	607.0	553.4	496.8	450.0	410.9	372.3	343.7	322.6
37.5°	603.8	630.9	626.1	586.8	530.7	474.0	422.3	381.5	344.7	315.8	295.1
40°	566.5	601.1	606.1	571.3	514.8	456.4	401.6	361.0	325.1	298.7	277.8
42.5°	526.6	566.9	580.6	552.8	497.3	437.8	383.1	341.0	305.4	279.8	261.3
45°	459.6	512.9	537.7	521.8	468.2	407.3	351.0	308.3	276.0	251.9	237.6
47.5°	396.9	455.2	488.5	482.9	435.8	375.5	319.8	278.8	247.4	228.2	215.4
50°	352.6	412.5	452.7	454.6	412.5	352.8	296.9	258.3	229.4	211.5	201.0
52.5°	314.0	371.3	415.1	424.8	386.5	329.2	276.4	237.9	212.5	196.0	186.7
55°	263.7	312.1	360.7	378.5	347.8	293.3	244.4	210.6	186.7	175.4	167.2
57.5°	219.3	259.6	304.5	324.1	305.2	258.5	212.7	183.3	164.0	154.0	147.7
60°	195.8	227.6	267.6	291.0	274.6	233.1	193.1	165.1	149.2	140.4	134.5
62.5°	174.0	202.2	236.0	257.4	248.5	209.3	173.5	148.8	135.1	126.8	122.5
65°	143.6	165.8	192.0	211.7	205.8	176.1	146.7	125.6	114.7	108.1	104.7
67.5°	118.2	134.3	152.4	169.7	165.0	143.9	120.4	103.9	95.8	90.1	88.0
70°	102.2	114.5	130.6	144.5	140.6	123.4	104.7	90.6	83.6	78.8	76.8
72.5°	87.0	97.0	109.4	120.7	118.1	103.7	88.2	77.6	72.1	67.7	66.1
75°	65.7	73.4	80.9	88.4	87.7	76.6	67.5	59.3	55.0	51.6	50.9
77.5°	48.5	52.8	57.9	62.3	61.1	54.7	47.6	42.9	39.8	37.5	37.1
80°	37.0	39.5	43.2	46.3	44.8	42.0	36.3	32.9	30.7	28.4	27.5
82.5°	26.9	29.3	31.5	33.3	32.0	29.5	26.0	23.7	22.3	20.8	20.4
85°	14.1	15.4	16.4	16.8	16.4	14.8	13.2	12.3	11.1	10.4	10.2
87.5°	7.8	7.6	7.3	7.4	6.5	6.1	5.0	4.1	4.3	4.5	4.5
90°	11.8	10.5	9.2	7.7	6.0	4.2	2.5	0.7	2.5	4.2	6.0
92.5°	15.3	14.7	14.1	13.8	14.0	14.1	14.3	14.4	14.3	14.1	14.0
95°	25.7	24.6	23.4	25.5	30.8	36.0	41.3	46.5	41.3	36.0	30.8
97.5°	32.2	29.6	27.0	33.1	47.9	62.7	77.5	92.3	77.5	62.7	47.9
100°	35.4	32.7	30.0	39.5	61.3	83.1	104.8	126.6	104.8	83.1	61.3
102.5°	87.1	109.7	132.3	145.9	150.6	155.2	159.8	164.4	159.8	155.2	150.6
105°	130.4	173.8	217.2	236.5	231.8	227.0	222.2	217.5	222.2	227.0	231.8
107.5°	165.2	217.2	269.3	293.4	289.5	285.7	281.8	278.0	281.8	285.7	289.5
110°	217.1	263.0	308.9	330.2	326.9	323.6	320.2	316.9	320.2	323.6	326.9



TEST NUMBER: P331258

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	338.4	349.8	361.1	365.3	362.4	359.4	356.5	353.5	356.5	359.4	362.4
115°	433.4	429.4	425.5	422.1	419.4	416.7	414.0	411.3	414.0	416.7	419.4
117.5°	483.4	480.7	477.9	475.0	472.0	469.0	466.0	463.0	466.0	469.0	472.0
120°	518.6	515.8	512.9	510.3	507.9	505.5	503.1	500.7	503.1	505.5	507.9
122.5°	551.9	548.8	545.6	542.8	540.3	537.8	535.3	532.8	535.3	537.8	540.3
125°	598.4	595.4	592.4	589.8	587.8	585.7	583.6	581.6	583.6	585.7	587.8
127.5°	641.7	639.5	637.2	634.9	632.6	630.4	628.1	625.8	628.1	630.4	632.6
130°	669.6	667.9	666.1	664.0	661.4	658.9	656.4	653.8	656.4	658.9	661.4
132.5°	696.5	694.8	693.0	691.1	688.9	686.8	684.6	682.4	684.6	686.8	688.9
135°	734.6	733.2	731.8	729.8	727.3	724.7	722.2	719.6	722.2	724.7	727.3
137.5°	769.3	767.7	766.1	764.4	762.6	760.8	759.0	757.3	759.0	760.8	762.6
140°	792.0	790.2	788.5	786.9	785.7	784.4	783.1	781.9	783.1	784.4	785.7
142.5°	812.6	810.6	808.6	807.0	805.9	804.8	803.6	802.5	803.6	804.8	805.9
145°	840.8	838.1	835.4	834.2	834.3	834.5	834.6	834.8	834.6	834.5	834.3
147.5°	866.9	864.3	861.6	860.6	861.2	861.8	862.4	863.0	862.4	861.8	861.2
150°	882.6	880.1	877.6	876.8	878.0	879.1	880.2	881.3	880.2	879.1	878.0
152.5°	897.2	894.8	892.4	891.8	893.0	894.3	895.5	896.7	895.5	894.3	893.0
155°	917.5	915.6	913.7	913.5	914.9	916.3	917.8	919.2	917.8	916.3	914.9
157.5°	934.7	933.4	932.0	932.0	933.2	934.4	935.6	936.8	935.6	934.4	933.2
160°	945.2	944.2	943.3	943.3	944.2	945.2	946.1	947.1	946.1	945.2	944.2
162.5°	954.0	953.2	952.4	952.4	953.4	954.4	955.3	956.3	955.3	954.4	953.4
165°	965.5	965.0	964.5	964.7	965.7	966.7	967.6	968.6	967.6	966.7	965.7
167.5°	974.5	974.1	973.6	973.9	974.9	975.8	976.8	977.7	976.8	975.8	974.9
170°	979.4	979.1	978.7	979.1	980.0	981.0	981.9	982.9	981.9	981.0	980.0
172.5°	982.8	982.5	982.2	982.5	983.4	984.4	985.3	986.3	985.3	984.4	983.4
175°	986.5	986.2	985.9	986.3	987.4	988.5	989.6	990.7	989.6	988.5	987.4
177.5°	987.8	987.6	987.5	987.9	988.8	989.7	990.6	991.5	990.6	989.7	988.8
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331258

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	583.3	582.2	578.4	576.4	573.1	570.0	568.0	568.9	569.6	569.3	568.7
5°	566.5	562.2	555.6	550.0	545.9	538.4	535.2	533.6	532.2	530.7	529.1
7.5°	546.6	539.8	530.4	522.3	514.7	505.3	500.0	496.9	493.6	490.0	486.8
10°	532.5	522.9	512.9	501.6	492.5	484.1	476.6	471.6	467.0	462.7	459.6
12.5°	517.6	506.6	494.2	478.7	468.7	456.6	455.5	446.7	439.6	436.9	433.2
15°	493.9	478.4	462.7	444.3	436.4	425.5	418.7	411.8	405.7	401.4	400.3
17.5°	466.9	446.9	431.3	418.1	405.1	393.9	387.6	382.2	377.1	371.4	370.6
20°	446.4	429.1	412.1	400.5	387.1	375.7	368.0	362.6	358.2	354.8	351.9
22.5°	426.9	408.0	392.4	379.8	366.6	357.4	351.3	346.0	342.4	338.7	335.9
25°	395.7	381.0	363.9	349.6	338.7	332.8	327.8	323.3	321.0	318.5	315.3
27.5°	368.4	352.0	336.1	325.0	315.4	310.2	306.6	303.5	301.4	299.9	298.1
30°	349.2	332.6	320.1	309.2	301.2	296.0	293.7	291.9	289.4	288.5	287.6
32.5°	330.6	315.7	305.0	295.5	288.0	284.5	282.5	280.8	278.9	278.0	276.1
35°	304.4	291.9	281.5	276.2	270.1	267.1	265.6	263.3	261.5	260.6	260.3
37.5°	279.7	268.9	262.0	255.3	252.7	250.9	248.7	247.2	246.6	246.5	246.2
40°	263.7	254.9	248.7	243.3	242.2	239.4	237.6	236.3	236.3	236.5	236.3
42.5°	249.2	241.2	235.8	231.1	229.8	228.2	226.3	226.3	226.6	227.4	226.6
45°	227.2	221.5	217.6	215.4	212.9	211.3	211.0	211.7	211.9	212.2	212.9
47.5°	206.9	203.1	199.6	197.1	196.0	195.8	195.5	196.7	197.8	198.2	199.2
50°	194.9	190.6	187.6	186.0	185.1	184.7	185.1	186.5	187.4	188.5	189.2
52.5°	181.5	178.4	176.4	175.1	174.8	175.1	175.1	176.7	178.1	178.6	178.9
55°	162.9	160.6	160.2	158.1	159.0	158.8	159.9	160.8	162.2	163.6	163.8
57.5°	144.3	142.5	141.3	141.5	141.8	142.8	143.7	145.3	146.7	148.2	148.3
60°	132.0	131.1	130.4	130.4	130.8	132.2	133.3	134.9	135.8	136.8	137.4
62.5°	120.7	119.8	119.1	119.5	120.7	121.5	122.8	123.7	124.6	125.5	125.8
65°	102.9	102.5	103.1	103.6	103.8	104.9	106.5	107.2	108.1	108.6	110.2
67.5°	86.5	86.6	86.5	87.1	88.5	88.7	90.2	91.8	92.0	92.9	93.9
70°	75.4	75.9	76.3	76.8	77.9	78.4	79.5	80.2	81.1	81.8	82.5
72.5°	65.2	65.3	65.8	65.7	66.7	67.6	68.6	69.3	70.2	71.1	71.7
75°	50.2	50.2	50.7	50.9	52.0	53.2	52.9	53.4	54.3	55.2	55.7
77.5°	36.7	36.2	36.7	36.9	37.3	38.2	38.4	39.0	40.1	39.8	40.3
80°	27.9	27.3	27.9	28.2	28.2	29.3	29.3	29.8	30.4	29.8	30.4
82.5°	19.9	19.6	20.1	20.2	20.5	20.6	20.9	21.0	21.7	21.4	21.7
85°	10.0	9.8	10.0	9.8	10.0	10.2	10.2	10.0	10.0	10.4	9.8
87.5°	4.6	4.8	4.8	5.1	5.2	5.2	5.2	5.4	5.5	5.3	5.4
90°	7.7	9.2	10.5	11.8	13.0	14.3	15.1	15.9	16.7	17.5	18.0
92.5°	13.8	14.1	14.7	15.3	16.0	16.6	17.0	17.4	17.8	18.2	18.6
95°	25.5	23.4	24.6	25.7	26.8	27.9	28.7	29.5	30.3	31.1	31.4
97.5°	33.1	27.0	29.6	32.2	34.8	37.3	38.0	38.6	39.2	39.9	40.3
100°	39.5	30.0	32.7	35.4	38.1	40.8	42.0	43.3	44.6	45.9	46.7
102.5°	145.9	132.3	109.7	87.1	64.5	41.9	43.6	45.2	46.9	48.5	49.6
105°	236.5	217.2	173.8	130.4	87.0	43.6	45.4	47.1	48.9	50.6	51.8
107.5°	293.4	269.3	217.2	165.2	113.1	61.1	59.3	57.5	55.7	54.0	53.4
110°	330.2	308.9	263.0	217.1	171.1	125.2	109.3	93.4	77.5	61.6	54.0



TEST NUMBER: P331258

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	365.3	361.1	349.8	338.4	327.1	315.7	257.8	199.8	141.8	83.8	55.0
115°	422.1	425.5	429.4	433.4	437.4	441.4	367.8	294.2	220.6	147.0	104.4
117.5°	475.0	477.9	480.7	483.4	486.1	488.9	471.1	453.3	435.4	417.6	389.9
120°	510.3	512.9	515.8	518.6	521.5	524.3	526.2	528.2	530.1	532.0	522.2
122.5°	542.8	545.6	548.8	551.9	555.0	558.1	559.2	560.4	561.5	562.7	561.2
125°	589.8	592.4	595.4	598.4	601.4	604.5	605.6	606.7	607.8	608.9	609.7
127.5°	634.9	637.2	639.5	641.7	644.0	646.2	647.9	649.5	651.1	652.7	653.6
130°	664.0	666.1	667.9	669.6	671.4	673.1	674.9	676.6	678.4	680.1	680.9
132.5°	691.1	693.0	694.8	696.5	698.3	700.0	701.5	703.0	704.5	706.0	706.7
135°	729.8	731.8	733.2	734.6	736.1	737.5	739.1	740.7	742.3	743.9	744.5
137.5°	764.4	766.1	767.7	769.3	770.9	772.6	774.1	775.7	777.2	778.8	779.3
140°	786.9	788.5	790.2	792.0	793.7	795.5	796.9	798.3	799.7	801.2	801.5
142.5°	807.0	808.6	810.6	812.6	814.6	816.6	817.9	819.2	820.5	821.8	822.1
145°	834.2	835.4	838.1	840.8	843.5	846.2	847.4	848.5	849.6	850.7	850.8
147.5°	860.6	861.6	864.3	866.9	869.6	872.3	873.1	873.9	874.8	875.6	875.7
150°	876.8	877.6	880.1	882.6	885.2	887.7	888.7	889.6	890.6	891.5	891.6
152.5°	891.8	892.4	894.8	897.2	899.6	902.0	903.0	903.9	904.9	905.9	905.8
155°	913.5	913.7	915.6	917.5	919.4	921.3	922.3	923.3	924.2	925.2	925.0
157.5°	932.0	932.0	933.4	934.7	936.0	937.4	938.5	939.5	940.6	941.7	941.6
160°	943.3	943.3	944.2	945.2	946.1	947.1	948.1	949.0	950.0	950.9	950.8
162.5°	952.4	952.4	953.2	954.0	954.9	955.7	956.8	957.8	958.9	960.0	959.9
165°	964.7	964.5	965.0	965.5	965.9	966.4	967.5	968.6	969.8	970.9	970.9
167.5°	973.9	973.6	974.1	974.5	975.0	975.4	976.5	977.7	978.8	979.9	979.7
170°	979.1	978.7	979.1	979.4	979.7	980.0	981.1	982.2	983.3	984.5	984.3
172.5°	982.5	982.2	982.5	982.8	983.1	983.4	984.6	985.7	986.8	987.9	987.7
175°	986.3	985.9	986.2	986.5	986.8	987.2	988.3	989.4	990.5	991.6	991.4
177.5°	987.9	987.5	987.6	987.8	987.9	988.0	988.9	989.8	990.7	991.6	991.5
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331258

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	566.9	566.5	566.5	564.9	566.5	566.5	566.9	568.7	569.3	569.6	568.9
5°	525.9	525.2	524.1	525.2	524.1	525.2	525.9	529.1	530.7	532.2	533.6
7.5°	485.3	482.6	482.2	479.5	482.2	482.6	485.3	486.8	490.0	493.6	496.9
10°	455.7	453.9	453.6	449.3	453.6	453.9	455.7	459.6	462.7	467.0	471.6
12.5°	433.2	428.8	429.7	427.2	429.7	428.8	433.2	433.2	436.9	439.6	446.7
15°	394.1	394.1	393.2	389.4	393.2	394.1	394.1	400.3	401.4	405.7	411.8
17.5°	366.1	365.6	363.5	364.6	363.5	365.6	366.1	370.6	371.4	377.1	382.2
20°	349.4	348.0	345.3	345.3	345.3	348.0	349.4	351.9	354.8	358.2	362.6
22.5°	333.6	333.5	330.6	331.5	330.6	333.5	333.6	335.9	338.7	342.4	346.0
25°	315.1	313.3	311.9	312.6	311.9	313.3	315.1	315.3	318.5	321.0	323.3
27.5°	297.5	296.5	296.4	294.6	296.4	296.5	297.5	298.1	299.9	301.4	303.5
30°	287.4	285.1	285.5	284.4	285.5	285.1	287.4	287.6	288.5	289.4	291.9
32.5°	275.7	274.9	274.5	273.5	274.5	274.9	275.7	276.1	278.0	278.9	280.8
35°	259.9	260.1	259.0	259.4	259.0	260.1	259.9	260.3	260.6	261.5	263.3
37.5°	246.0	246.7	246.2	246.3	246.2	246.7	246.0	246.2	246.5	246.6	247.2
40°	236.9	236.9	236.9	237.6	236.9	236.9	236.9	236.3	236.5	236.3	236.3
42.5°	228.2	227.8	227.5	227.4	227.5	227.8	228.2	226.6	227.4	226.6	226.3
45°	213.3	214.0	214.2	213.1	214.2	214.0	213.3	212.9	212.2	211.9	211.7
47.5°	199.8	199.9	199.8	200.8	199.8	199.9	199.8	199.2	198.2	197.8	196.7
50°	190.4	189.9	190.4	189.9	190.4	189.9	190.4	189.2	188.5	187.4	186.5
52.5°	180.4	180.5	180.2	180.1	180.2	180.5	180.4	178.9	178.6	178.1	176.7
55°	164.7	165.1	164.9	164.9	164.9	165.1	164.7	163.8	163.6	162.2	160.8
57.5°	148.5	148.9	149.2	148.2	149.2	148.9	148.5	148.3	148.2	146.7	145.3
60°	137.2	138.3	138.1	137.7	138.1	138.3	137.2	137.4	136.8	135.8	134.9
62.5°	126.8	127.3	127.2	127.1	127.2	127.3	126.8	125.8	125.5	124.6	123.7
65°	110.9	111.3	110.6	111.3	110.6	111.3	110.9	110.2	108.6	108.1	107.2
67.5°	93.6	93.8	94.3	94.6	94.3	93.8	93.6	93.9	92.9	92.0	91.8
70°	82.9	82.7	83.4	84.1	83.4	82.7	82.9	82.5	81.8	81.1	80.2
72.5°	71.6	72.1	71.9	72.4	71.9	72.1	71.6	71.7	71.1	70.2	69.3
75°	55.2	55.9	55.7	56.3	55.7	55.9	55.2	55.7	55.2	54.3	53.4
77.5°	39.9	40.0	39.9	40.3	39.9	40.0	39.9	40.3	39.8	40.1	39.0
80°	30.4	30.0	29.5	30.4	29.5	30.0	30.4	30.4	29.8	30.4	29.8
82.5°	21.2	21.4	21.0	21.0	21.0	21.4	21.2	21.7	21.4	21.7	21.0
85°	9.8	9.5	9.1	9.1	9.1	9.5	9.8	9.8	10.4	10.0	10.0
87.5°	5.5	5.4	5.4	5.3	5.4	5.4	5.5	5.4	5.3	5.5	5.4
90°	18.4	18.7	19.0	19.3	19.0	18.7	18.4	18.0	17.5	16.7	15.9
92.5°	18.7	18.9	19.1	19.3	19.1	18.9	18.7	18.6	18.2	17.8	17.4
95°	31.2	31.1	30.9	30.8	30.9	31.1	31.2	31.4	31.1	30.3	29.5
97.5°	40.5	40.7	40.9	41.1	40.9	40.7	40.5	40.3	39.9	39.2	38.6
100°	47.0	47.3	47.6	47.9	47.6	47.3	47.0	46.7	45.9	44.6	43.3
102.5°	50.0	50.5	50.9	51.4	50.9	50.5	50.0	49.6	48.5	46.9	45.2
105°	52.5	53.1	53.7	54.4	53.7	53.1	52.5	51.8	50.6	48.9	47.1
107.5°	54.0	54.7	55.3	55.9	55.3	54.7	54.0	53.4	54.0	55.7	57.5
110°	54.6	55.2	55.9	56.5	55.9	55.2	54.6	54.0	61.6	77.5	93.4



TEST NUMBER: P331258

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	55.6	56.1	56.6	57.1	56.6	56.1	55.6	55.0	83.8	141.8	199.8
115°	93.0	81.5	70.1	58.7	70.1	81.5	93.0	104.4	147.0	220.6	294.2
117.5°	352.3	314.7	277.1	239.5	277.1	314.7	352.3	389.9	417.6	435.4	453.3
120°	500.7	479.3	457.8	436.4	457.8	479.3	500.7	522.2	532.0	530.1	528.2
122.5°	557.0	552.8	548.7	544.5	548.7	552.8	557.0	561.2	562.7	561.5	560.4
125°	610.2	610.7	611.1	611.6	611.1	610.7	610.2	609.7	608.9	607.8	606.7
127.5°	653.7	653.8	653.9	654.0	653.9	653.8	653.7	653.6	652.7	651.1	649.5
130°	680.8	680.6	680.4	680.3	680.4	680.6	680.8	680.9	680.1	678.4	676.6
132.5°	706.5	706.4	706.2	706.0	706.2	706.4	706.5	706.7	706.0	704.5	703.0
135°	744.2	743.9	743.5	743.2	743.5	743.9	744.2	744.5	743.9	742.3	740.7
137.5°	778.8	778.2	777.7	777.1	777.7	778.2	778.8	779.3	778.8	777.2	775.7
140°	800.7	799.9	799.1	798.3	799.1	799.9	800.7	801.5	801.2	799.7	798.3
142.5°	821.3	820.5	819.7	818.9	819.7	820.5	821.3	822.1	821.8	820.5	819.2
145°	850.1	849.3	848.5	847.7	848.5	849.3	850.1	850.8	850.7	849.6	848.5
147.5°	875.0	874.3	873.7	873.0	873.7	874.3	875.0	875.7	875.6	874.8	873.9
150°	890.8	890.0	889.2	888.4	889.2	890.0	890.8	891.6	891.5	890.6	889.6
152.5°	904.8	903.7	902.7	901.6	902.7	903.7	904.8	905.8	905.9	904.9	903.9
155°	923.7	922.5	921.2	919.9	921.2	922.5	923.7	925.0	925.2	924.2	923.3
157.5°	940.4	939.1	937.9	936.7	937.9	939.1	940.4	941.6	941.7	940.6	939.5
160°	949.7	948.6	947.5	946.4	947.5	948.6	949.7	950.8	950.9	950.0	949.0
162.5°	958.5	957.1	955.8	954.4	955.8	957.1	958.5	959.9	960.0	958.9	957.8
165°	969.8	968.6	967.5	966.4	967.5	968.6	969.8	970.9	970.9	969.8	968.6
167.5°	978.3	976.9	975.4	974.0	975.4	976.9	978.3	979.7	979.9	978.8	977.7
170°	982.9	981.4	980.0	978.6	980.0	981.4	982.9	984.3	984.5	983.3	982.2
172.5°	986.3	984.9	983.4	982.0	983.4	984.9	986.3	987.7	987.9	986.8	985.7
175°	989.8	988.2	986.6	985.0	986.6	988.2	989.8	991.4	991.6	990.5	989.4
177.5°	990.3	989.2	988.0	986.9	988.0	989.2	990.3	991.5	991.6	990.7	989.8
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331258

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	568.0	570.0	573.1	576.4	578.4	582.2	583.3	585.1	586.7	590.5	594.5
5°	535.2	538.4	545.9	550.0	555.6	562.2	566.5	571.1	576.1	584.7	592.7
7.5°	500.0	505.3	514.7	522.3	530.4	539.8	546.6	555.6	563.1	575.3	586.9
10°	476.6	484.1	492.5	501.6	512.9	522.9	532.5	543.8	552.9	567.5	581.1
12.5°	455.5	456.6	468.7	478.7	494.2	506.6	517.6	532.2	541.1	558.4	572.7
15°	418.7	425.5	436.4	444.3	462.7	478.4	493.9	509.1	519.3	540.7	559.5
17.5°	387.6	393.9	405.1	418.1	431.3	446.9	466.9	483.0	496.9	521.3	543.6
20°	368.0	375.7	387.1	400.5	412.1	429.1	446.4	464.8	479.8	507.3	533.4
22.5°	351.3	357.4	366.6	379.8	392.4	408.0	426.9	447.0	462.7	492.4	518.8
25°	327.8	332.8	338.7	349.6	363.9	381.0	395.7	417.8	440.7	468.4	500.4
27.5°	306.6	310.2	315.4	325.0	336.1	352.0	368.4	389.3	412.4	442.5	476.3
30°	293.7	296.0	301.2	309.2	320.1	332.6	349.2	369.1	392.8	423.2	456.8
32.5°	282.5	284.5	288.0	295.5	305.0	315.7	330.6	350.6	373.1	403.0	440.3
35°	265.6	267.1	270.1	276.2	281.5	291.9	304.4	322.6	343.7	372.3	410.9
37.5°	248.7	250.9	252.7	255.3	262.0	268.9	279.7	295.1	315.8	344.7	381.5
40°	237.6	239.4	242.2	243.3	248.7	254.9	263.7	277.8	298.7	325.1	361.0
42.5°	226.3	228.2	229.8	231.1	235.8	241.2	249.2	261.3	279.8	305.4	341.0
45°	211.0	211.3	212.9	215.4	217.6	221.5	227.2	237.6	251.9	276.0	308.3
47.5°	195.5	195.8	196.0	197.1	199.6	203.1	206.9	215.4	228.2	247.4	278.8
50°	185.1	184.7	185.1	186.0	187.6	190.6	194.9	201.0	211.5	229.4	258.3
52.5°	175.1	175.1	174.8	175.1	176.4	178.4	181.5	186.7	196.0	212.5	237.9
55°	159.9	158.8	159.0	158.1	160.2	160.6	162.9	167.2	175.4	186.7	210.6
57.5°	143.7	142.8	141.8	141.5	141.3	142.5	144.3	147.7	154.0	164.0	183.3
60°	133.3	132.2	130.8	130.4	130.4	131.1	132.0	134.5	140.4	149.2	165.1
62.5°	122.8	121.5	120.7	119.5	119.1	119.8	120.7	122.5	126.8	135.1	148.8
65°	106.5	104.9	103.8	103.6	103.1	102.5	102.9	104.7	108.1	114.7	125.6
67.5°	90.2	88.7	88.5	87.1	86.5	86.6	86.5	88.0	90.1	95.8	103.9
70°	79.5	78.4	77.9	76.8	76.3	75.9	75.4	76.8	78.8	83.6	90.6
72.5°	68.6	67.6	66.7	65.7	65.8	65.3	65.2	66.1	67.7	72.1	77.6
75°	52.9	53.2	52.0	50.9	50.7	50.2	50.2	50.9	51.6	55.0	59.3
77.5°	38.4	38.2	37.3	36.9	36.7	36.2	36.7	37.1	37.5	39.8	42.9
80°	29.3	29.3	28.2	28.2	27.9	27.3	27.9	27.5	28.4	30.7	32.9
82.5°	20.9	20.6	20.5	20.2	20.1	19.6	19.9	20.4	20.8	22.3	23.7
85°	10.2	10.2	10.0	9.8	10.0	9.8	10.0	10.2	10.4	11.1	12.3
87.5°	5.2	5.2	5.2	5.1	4.8	4.8	4.6	4.5	4.5	4.3	4.1
90°	15.1	14.3	13.0	11.8	10.5	9.2	7.7	6.0	4.2	2.5	0.7
92.5°	17.0	16.6	16.0	15.3	14.7	14.1	13.8	14.0	14.1	14.3	14.4
95°	28.7	27.9	26.8	25.7	24.6	23.4	25.5	30.8	36.0	41.3	46.5
97.5°	38.0	37.3	34.8	32.2	29.6	27.0	33.1	47.9	62.7	77.5	92.3
100°	42.0	40.8	38.1	35.4	32.7	30.0	39.5	61.3	83.1	104.8	126.6
102.5°	43.6	41.9	64.5	87.1	109.7	132.3	145.9	150.6	155.2	159.8	164.4
105°	45.4	43.6	87.0	130.4	173.8	217.2	236.5	231.8	227.0	222.2	217.5
107.5°	59.3	61.1	113.1	165.2	217.2	269.3	293.4	289.5	285.7	281.8	278.0
110°	109.3	125.2	171.1	217.1	263.0	308.9	330.2	326.9	323.6	320.2	316.9



TEST NUMBER: P331258

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	257.8	315.7	327.1	338.4	349.8	361.1	365.3	362.4	359.4	356.5	353.5
115°	367.8	441.4	437.4	433.4	429.4	425.5	422.1	419.4	416.7	414.0	411.3
117.5°	471.1	488.9	486.1	483.4	480.7	477.9	475.0	472.0	469.0	466.0	463.0
120°	526.2	524.3	521.5	518.6	515.8	512.9	510.3	507.9	505.5	503.1	500.7
122.5°	559.2	558.1	555.0	551.9	548.8	545.6	542.8	540.3	537.8	535.3	532.8
125°	605.6	604.5	601.4	598.4	595.4	592.4	589.8	587.8	585.7	583.6	581.6
127.5°	647.9	646.2	644.0	641.7	639.5	637.2	634.9	632.6	630.4	628.1	625.8
130°	674.9	673.1	671.4	669.6	667.9	666.1	664.0	661.4	658.9	656.4	653.8
132.5°	701.5	700.0	698.3	696.5	694.8	693.0	691.1	688.9	686.8	684.6	682.4
135°	739.1	737.5	736.1	734.6	733.2	731.8	729.8	727.3	724.7	722.2	719.6
137.5°	774.1	772.6	770.9	769.3	767.7	766.1	764.4	762.6	760.8	759.0	757.3
140°	796.9	795.5	793.7	792.0	790.2	788.5	786.9	785.7	784.4	783.1	781.9
142.5°	817.9	816.6	814.6	812.6	810.6	808.6	807.0	805.9	804.8	803.6	802.5
145°	847.4	846.2	843.5	840.8	838.1	835.4	834.2	834.3	834.5	834.6	834.8
147.5°	873.1	872.3	869.6	866.9	864.3	861.6	860.6	861.2	861.8	862.4	863.0
150°	888.7	887.7	885.2	882.6	880.1	877.6	876.8	878.0	879.1	880.2	881.3
152.5°	903.0	902.0	899.6	897.2	894.8	892.4	891.8	893.0	894.3	895.5	896.7
155°	922.3	921.3	919.4	917.5	915.6	913.7	913.5	914.9	916.3	917.8	919.2
157.5°	938.5	937.4	936.0	934.7	933.4	932.0	932.0	933.2	934.4	935.6	936.8
160°	948.1	947.1	946.1	945.2	944.2	943.3	943.3	944.2	945.2	946.1	947.1
162.5°	956.8	955.7	954.9	954.0	953.2	952.4	952.4	953.4	954.4	955.3	956.3
165°	967.5	966.4	965.9	965.5	965.0	964.5	964.7	965.7	966.7	967.6	968.6
167.5°	976.5	975.4	975.0	974.5	974.1	973.6	973.9	974.9	975.8	976.8	977.7
170°	981.1	980.0	979.7	979.4	979.1	978.7	979.1	980.0	981.0	981.9	982.9
172.5°	984.6	983.4	983.1	982.8	982.5	982.2	982.5	983.4	984.4	985.3	986.3
175°	988.3	987.2	986.8	986.5	986.2	985.9	986.3	987.4	988.5	989.6	990.7
177.5°	988.9	988.0	987.9	987.8	987.6	987.5	987.9	988.8	989.7	990.6	991.5
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331258

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	594.2	595.1	598.0	600.9	604.2	605.1	606.5	605.3	604.9	608.3	610.9
5°	595.9	599.9	607.9	615.2	621.3	625.6	630.2	632.0	635.4	640.1	646.1
7.5°	593.9	601.9	614.4	625.0	636.5	644.8	651.3	656.9	663.6	672.6	682.5
10°	591.8	602.4	617.7	630.6	644.7	655.4	664.2	672.9	682.9	695.4	708.3
12.5°	587.8	600.4	619.5	634.8	652.9	663.4	675.3	693.9	704.7	722.1	740.3
15°	579.7	593.8	620.4	639.2	659.7	679.7	701.7	719.4	737.1	747.4	773.0
17.5°	567.8	588.4	617.9	639.9	665.9	697.3	722.1	742.2	762.6	779.2	792.1
20°	558.1	580.6	614.3	640.6	671.5	705.3	733.7	754.2	771.9	785.8	793.7
22.5°	546.0	574.3	607.0	637.9	677.3	710.8	740.6	756.7	771.5	778.3	781.4
25°	526.8	560.9	597.9	635.6	680.1	715.6	742.8	752.6	756.9	750.3	739.4
27.5°	506.1	544.1	587.4	631.3	678.4	712.5	732.0	730.5	723.2	701.8	684.8
30°	490.7	532.5	579.0	627.0	674.2	707.4	718.7	707.4	690.8	667.0	642.6
32.5°	474.5	517.8	570.1	620.8	666.6	695.8	698.2	678.7	653.0	625.9	595.6
35°	450.0	496.8	553.4	607.0	650.4	668.8	657.9	623.3	592.9	555.9	514.5
37.5°	422.3	474.0	530.7	586.8	626.1	630.9	603.8	567.5	524.5	481.0	432.3
40°	401.6	456.4	514.8	571.3	606.1	601.1	566.5	526.6	475.5	422.3	377.1
42.5°	383.1	437.8	497.3	552.8	580.6	566.9	526.6	477.5	422.6	372.5	331.1
45°	351.0	407.3	468.2	521.8	537.7	512.9	459.6	405.0	351.0	309.2	276.5
47.5°	319.8	375.5	435.8	482.9	488.5	455.2	396.9	340.8	294.3	260.3	237.2
50°	296.9	352.8	412.5	454.6	452.7	412.5	352.6	299.2	260.3	232.8	217.4
52.5°	276.4	329.2	386.5	424.8	415.1	371.3	314.0	266.6	234.7	213.2	199.2
55°	244.4	293.3	347.8	378.5	360.7	312.1	263.7	225.6	201.9	185.8	174.9
57.5°	212.7	258.5	305.2	324.1	304.5	259.6	219.3	191.6	173.8	161.9	154.8
60°	193.1	233.1	274.6	291.0	267.6	227.6	195.8	171.1	156.7	147.0	140.6
62.5°	173.5	209.3	248.5	257.4	236.0	202.2	174.0	153.4	141.7	133.0	127.0
65°	146.7	176.1	205.8	211.7	192.0	165.8	143.6	130.2	119.7	113.4	108.6
67.5°	120.4	143.9	165.0	169.7	152.4	134.3	118.2	106.5	99.5	94.2	90.1
70°	104.7	123.4	140.6	144.5	130.6	114.5	102.2	92.9	86.5	82.0	78.1
72.5°	88.2	103.7	118.1	120.7	109.4	97.0	87.0	79.6	74.0	71.1	67.4
75°	67.5	76.6	87.7	88.4	80.9	73.4	65.7	60.9	57.9	54.3	52.5
77.5°	47.6	54.7	61.1	62.3	57.9	52.8	48.5	44.7	42.2	40.5	38.8
80°	36.3	42.0	44.8	46.3	43.2	39.5	37.0	34.5	32.9	31.8	30.7
82.5°	26.0	29.5	32.0	33.3	31.5	29.3	26.9	25.4	24.2	23.3	22.9
85°	13.2	14.8	16.4	16.8	16.4	15.4	14.1	14.1	13.4	13.2	13.2
87.5°	5.0	6.1	6.5	7.4	7.3	7.6	7.8	7.9	7.9	7.9	7.9
90°	2.5	4.2	6.0	7.7	9.2	10.5	11.8	13.0	14.3	15.1	15.9
92.5°	14.3	14.1	14.0	13.8	14.1	14.7	15.3	16.0	16.6	17.0	17.4
95°	41.3	36.0	30.8	25.5	23.4	24.6	25.7	26.8	27.9	28.7	29.5
97.5°	77.5	62.7	47.9	33.1	27.0	29.6	32.2	34.8	37.3	38.0	38.6
100°	104.8	83.1	61.3	39.5	30.0	32.7	35.4	38.1	40.8	42.0	43.3
102.5°	159.8	155.2	150.6	145.9	132.3	109.7	87.1	64.5	41.9	43.6	45.2
105°	222.2	227.0	231.8	236.5	217.2	173.8	130.4	87.0	43.6	45.4	47.1
107.5°	281.8	285.7	289.5	293.4	269.3	217.2	165.2	113.1	61.1	59.3	57.5
110°	320.2	323.6	326.9	330.2	308.9	263.0	217.1	171.1	125.2	109.3	93.4



TEST NUMBER: P331258

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	356.5	359.4	362.4	365.3	361.1	349.8	338.4	327.1	315.7	257.8	199.8
115°	414.0	416.7	419.4	422.1	425.5	429.4	433.4	437.4	441.4	367.8	294.2
117.5°	466.0	469.0	472.0	475.0	477.9	480.7	483.4	486.1	488.9	471.1	453.3
120°	503.1	505.5	507.9	510.3	512.9	515.8	518.6	521.5	524.3	526.2	528.2
122.5°	535.3	537.8	540.3	542.8	545.6	548.8	551.9	555.0	558.1	559.2	560.4
125°	583.6	585.7	587.8	589.8	592.4	595.4	598.4	601.4	604.5	605.6	606.7
127.5°	628.1	630.4	632.6	634.9	637.2	639.5	641.7	644.0	646.2	647.9	649.5
130°	656.4	658.9	661.4	664.0	666.1	667.9	669.6	671.4	673.1	674.9	676.6
132.5°	684.6	686.8	688.9	691.1	693.0	694.8	696.5	698.3	700.0	701.5	703.0
135°	722.2	724.7	727.3	729.8	731.8	733.2	734.6	736.1	737.5	739.1	740.7
137.5°	759.0	760.8	762.6	764.4	766.1	767.7	769.3	770.9	772.6	774.1	775.7
140°	783.1	784.4	785.7	786.9	788.5	790.2	792.0	793.7	795.5	796.9	798.3
142.5°	803.6	804.8	805.9	807.0	808.6	810.6	812.6	814.6	816.6	817.9	819.2
145°	834.6	834.5	834.3	834.2	835.4	838.1	840.8	843.5	846.2	847.4	848.5
147.5°	862.4	861.8	861.2	860.6	861.6	864.3	866.9	869.6	872.3	873.1	873.9
150°	880.2	879.1	878.0	876.8	877.6	880.1	882.6	885.2	887.7	888.7	889.6
152.5°	895.5	894.3	893.0	891.8	892.4	894.8	897.2	899.6	902.0	903.0	903.9
155°	917.8	916.3	914.9	913.5	913.7	915.6	917.5	919.4	921.3	922.3	923.3
157.5°	935.6	934.4	933.2	932.0	932.0	933.4	934.7	936.0	937.4	938.5	939.5
160°	946.1	945.2	944.2	943.3	943.3	944.2	945.2	946.1	947.1	948.1	949.0
162.5°	955.3	954.4	953.4	952.4	952.4	953.2	954.0	954.9	955.7	956.8	957.8
165°	967.6	966.7	965.7	964.7	964.5	965.0	965.5	965.9	966.4	967.5	968.6
167.5°	976.8	975.8	974.9	973.9	973.6	974.1	974.5	975.0	975.4	976.5	977.7
170°	981.9	981.0	980.0	979.1	978.7	979.1	979.4	979.7	980.0	981.1	982.2
172.5°	985.3	984.4	983.4	982.5	982.2	982.5	982.8	983.1	983.4	984.6	985.7
175°	989.6	988.5	987.4	986.3	985.9	986.2	986.5	986.8	987.2	988.3	989.4
177.5°	990.6	989.7	988.8	987.9	987.5	987.6	987.8	987.9	988.0	988.9	989.8
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331258

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	613.1	615.6	615.6	616.0	618.9	618.5	618.3
5°	652.4	656.3	656.7	660.8	663.5	662.6	660.1
7.5°	689.5	696.7	702.2	705.2	708.8	711.0	710.0
10°	719.0	729.4	735.8	740.1	745.3	749.2	747.8
12.5°	745.7	758.1	766.9	774.3	774.9	779.9	776.5
15°	787.4	800.5	801.9	807.3	811.7	811.2	811.4
17.5°	801.1	805.3	806.2	806.3	806.4	804.8	801.3
20°	796.2	794.6	790.8	787.8	782.6	781.9	777.4
22.5°	772.9	767.9	758.2	751.8	743.7	741.6	740.3
25°	727.2	716.0	700.6	685.8	681.7	673.8	676.0
27.5°	664.3	647.0	630.2	618.3	607.4	595.5	598.9
30°	620.2	600.6	577.0	558.8	547.2	535.9	533.8
32.5°	567.5	538.8	512.5	496.5	478.7	471.5	463.7
35°	476.6	448.6	422.5	400.0	387.1	377.1	368.0
37.5°	394.9	362.7	341.6	323.4	314.0	308.3	309.8
40°	344.2	316.0	300.5	286.7	278.0	274.0	274.9
42.5°	303.1	282.0	269.3	259.8	253.7	251.4	250.9
45°	256.5	244.7	234.2	228.8	225.8	223.3	221.7
47.5°	224.7	215.0	209.1	205.9	203.3	200.8	200.7
50°	205.6	199.2	195.1	191.7	189.7	187.9	189.5
52.5°	191.0	185.2	181.1	178.1	177.3	175.7	175.6
55°	169.5	164.9	162.0	159.2	157.9	157.0	155.8
57.5°	149.8	145.5	142.8	141.1	138.5	137.6	137.2
60°	135.8	132.4	129.7	127.4	126.3	124.5	124.5
62.5°	122.9	119.5	117.0	115.3	113.4	112.7	112.9
65°	104.3	101.5	99.0	97.2	96.8	95.4	95.9
67.5°	87.1	85.3	82.6	81.6	80.8	80.1	79.5
70°	75.6	73.8	72.5	71.1	70.4	70.4	70.4
72.5°	66.0	63.8	63.0	61.3	61.7	61.0	60.2
75°	51.1	49.7	49.1	48.4	47.3	47.3	47.3
77.5°	37.6	37.2	36.4	35.7	35.4	35.2	35.3
80°	29.1	28.8	28.4	28.4	27.9	27.7	27.3
82.5°	22.4	21.8	21.5	21.3	21.2	21.2	21.1
85°	12.7	12.3	12.3	12.5	12.0	12.0	12.3
87.5°	8.2	8.4	8.3	8.4	8.6	8.5	8.6
90°	16.7	17.5	18.0	18.4	18.7	19.0	19.3
92.5°	17.8	18.2	18.6	18.7	18.9	19.1	19.3
95°	30.3	31.1	31.4	31.2	31.1	30.9	30.8
97.5°	39.2	39.9	40.3	40.5	40.7	40.9	41.1
100°	44.6	45.9	46.7	47.0	47.3	47.6	47.9
102.5°	46.9	48.5	49.6	50.0	50.5	50.9	51.4
105°	48.9	50.6	51.8	52.5	53.1	53.7	54.4
107.5°	55.7	54.0	53.4	54.0	54.7	55.3	55.9
110°	77.5	61.6	54.0	54.6	55.2	55.9	56.5



TEST NUMBER: P331258

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	141.8	83.8	55.0	55.6	56.1	56.6	57.1
115°	220.6	147.0	104.4	93.0	81.5	70.1	58.7
117.5°	435.4	417.6	389.9	352.3	314.7	277.1	239.5
120°	530.1	532.0	522.2	500.7	479.3	457.8	436.4
122.5°	561.5	562.7	561.2	557.0	552.8	548.7	544.5
125°	607.8	608.9	609.7	610.2	610.7	611.1	611.6
127.5°	651.1	652.7	653.6	653.7	653.8	653.9	654.0
130°	678.4	680.1	680.9	680.8	680.6	680.4	680.3
132.5°	704.5	706.0	706.7	706.5	706.4	706.2	706.0
135°	742.3	743.9	744.5	744.2	743.9	743.5	743.2
137.5°	777.2	778.8	779.3	778.8	778.2	777.7	777.1
140°	799.7	801.2	801.5	800.7	799.9	799.1	798.3
142.5°	820.5	821.8	822.1	821.3	820.5	819.7	818.9
145°	849.6	850.7	850.8	850.1	849.3	848.5	847.7
147.5°	874.8	875.6	875.7	875.0	874.3	873.7	873.0
150°	890.6	891.5	891.6	890.8	890.0	889.2	888.4
152.5°	904.9	905.9	905.8	904.8	903.7	902.7	901.6
155°	924.2	925.2	925.0	923.7	922.5	921.2	919.9
157.5°	940.6	941.7	941.6	940.4	939.1	937.9	936.7
160°	950.0	950.9	950.8	949.7	948.6	947.5	946.4
162.5°	958.9	960.0	959.9	958.5	957.1	955.8	954.4
165°	969.8	970.9	970.9	969.8	968.6	967.5	966.4
167.5°	978.8	979.9	979.7	978.3	976.9	975.4	974.0
170°	983.3	984.5	984.3	982.9	981.4	980.0	978.6
172.5°	986.8	987.9	987.7	986.3	984.9	983.4	982.0
175°	990.5	991.6	991.4	989.8	988.2	986.6	985.0
177.5°	990.7	991.6	991.5	990.3	989.2	988.0	986.9
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6

(END OF REPORT)