

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931485

Luminaire Tested: DFN2DS-TR4F0-060DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931485
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-060DS850-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6587.4 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 59.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931485

CATALOG NUMBER: DFN2DS-TR4F0-060DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931485

CATALOG NUMBER: DFN2DS-TR4F0-060DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2057	2057	2057
5°	2065	2035	2047
10°	2053	2014	2024
15°	2027	1988	1986
20°	1991	1949	1947
25°	1955	1901	1901
30°	1909	1857	1841
35°	1867	1804	1777
40°	1813	1750	1717
45°	1760	1698	1656
50°	1701	1643	1585
55°	1642	1579	1521
60°	1574	1503	1448
65°	1503	1428	1362
70°	1411	1336	1272
75°	1283	1230	1200
80°	1140	1104	1048
85°	929	885	795

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1760 cd/sqm

TEST NUMBER: P931485

CATALOG NUMBER: DFN2DS-TR4F0-060DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.7	3.7
10°-20°	685.6	10.4
20°-30°	1007.6	15.3
30°-40°	1170.3	17.8
40°-50°	1168.8	17.7
50°-60°	1019.2	15.5
60°-70°	753.4	11.4
70°-80°	426.3	6.5
80°-90°	112.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1937.0	29.4
0°-40°	3107.2	47.2
0°-60°	5295.3	80.4
0°-90°	6587.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6587.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2589	2589	2589	2589	2589	
5°	2589	2579	2552	2572	2567	246
15°	2465	2450	2417	2428	2415	694
25°	2231	2211	2168	2173	2168	1026
35°	1925	1900	1860	1845	1832	1202
45°	1566	1549	1511	1484	1474	1209
55°	1185	1170	1140	1110	1098	1060
65°	799	784	759	737	724	790
75°	418	413	401	386	391	446
85°	102	100	97	90	87	120
90°	0	0	0	0	0	

TEST NUMBER: P931485

CATALOG NUMBER: DFN2DS-TR4F0-060DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2589.1	2589.1	2589.1	2589.1	2589.1
2.5°	2604.2	2591.7	2564.2	2589.1	2584.3
5°	2589.1	2579.3	2551.8	2571.7	2566.9
7.5°	2571.7	2556.9	2529.4	2549.5	2544.5
10°	2544.5	2527.1	2497.1	2517.0	2509.6
12.5°	2507.0	2492.1	2462.3	2474.7	2469.7
15°	2464.6	2449.9	2417.4	2427.5	2415.1
17.5°	2412.4	2397.7	2365.2	2377.5	2365.2
20°	2355.1	2340.3	2305.4	2312.8	2303.1
22.5°	2298.1	2275.6	2243.1	2243.1	2238.1
25°	2230.6	2210.9	2168.5	2173.3	2168.5
27.5°	2155.9	2138.5	2106.2	2098.9	2086.5
30°	2081.5	2061.3	2024.1	2016.7	2006.6
32.5°	2001.6	1986.9	1947.0	1931.9	1921.9
35°	1924.6	1899.7	1859.8	1844.7	1832.3
37.5°	1837.4	1814.9	1775.1	1757.5	1745.1
40°	1747.8	1727.7	1687.9	1665.7	1655.6
42.5°	1660.6	1640.5	1601.0	1575.9	1561.0
45°	1566.1	1548.6	1511.1	1484.0	1473.9
47.5°	1473.9	1456.4	1416.6	1389.1	1374.3
50°	1376.7	1364.3	1329.5	1294.5	1282.1
52.5°	1282.1	1264.7	1232.4	1205.0	1187.6
55°	1185.2	1170.1	1140.3	1110.4	1098.0
57.5°	1088.0	1075.6	1043.1	1013.3	1003.2
60°	990.8	981.0	946.2	918.7	911.3
62.5°	896.2	878.8	853.9	829.1	819.1
65°	799.3	784.3	759.4	736.9	724.5
67.5°	699.7	687.0	664.8	647.4	637.3
70°	607.5	597.5	575.0	557.6	547.8
72.5°	512.9	502.9	490.5	473.1	465.7
75°	418.1	413.4	400.7	385.9	390.9
77.5°	333.6	323.6	318.5	311.2	303.8
80°	249.1	246.4	241.4	234.0	229.0
82.5°	169.3	169.3	166.9	156.9	156.9
85°	101.9	99.6	97.1	89.5	87.2
87.5°	44.9	39.9	34.8	27.5	24.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931485

CATALOG NUMBER: DFN2DS-TR4F0-060DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.79	15.40	14.15	15.71	16.03	13.34	14.95	13.71	15.27	15.58
	3H	15.54	16.99	15.92	17.32	17.68	15.05	16.50	15.42	16.83	17.19
	4H	16.18	17.55	16.58	17.90	18.28	15.69	17.06	16.09	17.41	17.78
	6H	16.65	17.92	17.06	18.29	18.68	16.15	17.42	16.56	17.79	18.18
	8H	16.80	18.01	17.22	18.40	18.80	16.29	17.50	16.72	17.89	18.29
	12H	16.89	18.05	17.32	18.43	18.86	16.38	17.54	16.80	17.92	18.35
4H	2H	14.35	15.72	14.75	16.07	16.44	14.00	15.37	14.39	15.71	16.09
	3H	16.32	17.47	16.73	17.87	18.27	15.92	17.06	16.33	17.46	17.86
	4H	17.10	18.14	17.53	18.55	18.99	16.68	17.71	17.11	18.13	18.56
	6H	17.70	18.60	18.15	19.04	19.50	17.26	18.17	17.72	18.61	19.07
	8H	17.89	18.73	18.35	19.18	19.64	17.45	18.29	17.91	18.74	19.20
	12H	18.02	18.78	18.50	19.25	19.72	17.57	18.33	18.05	18.80	19.27
8H	4H	17.37	18.22	17.83	18.66	19.13	17.00	17.85	17.46	18.29	18.75
	6H	18.09	18.79	18.58	19.28	19.75	17.71	18.41	18.20	18.90	19.37
	8H	18.35	18.98	18.86	19.48	19.97	17.96	18.59	18.47	19.09	19.58
	12H	18.55	19.10	19.05	19.60	20.16	18.13	18.69	18.64	19.18	19.74
12H	4H	17.40	18.16	17.88	18.64	19.10	17.03	17.79	17.52	18.27	18.74
	6H	18.13	18.77	18.64	19.27	19.76	17.76	18.40	18.27	18.90	19.39
	8H	18.45	19.00	18.95	19.50	20.06	18.07	18.63	18.58	19.12	19.68