

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331261

Luminaire Tested: **S122DIP-S290D725U835-4F0-1E-UDD-D**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331261
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S290D725U835-4F0-1E-UDD-D
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4095.4 lumens
Efficiency: N/A
Efficacy: 131.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331261

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-D

Luminous Intensity Polar Plot





TEST NUMBER: P331261

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	92	87	83	79	81	78	74	71	60	58	56	44	42	41	29	28	27	20
2	83	76	69	64	74	67	62	58	52	48	45	38	36	34	25	23	22	16
3	76	66	59	53	67	59	53	48	46	41	38	33	30	28	22	20	19	13
4	69	58	50	44	61	52	45	40	40	36	32	29	26	24	19	17	16	11
5	63	52	44	38	56	46	39	34	36	31	27	26	23	20	17	15	14	10
6	58	46	38	32	51	41	34	29	32	27	23	24	20	18	16	13	12	8
7	53	41	34	28	47	37	30	25	29	24	20	21	18	15	14	12	10	7
8	49	37	30	25	44	33	27	22	26	21	18	19	16	14	13	11	9	7
9	46	34	27	22	41	30	24	20	24	19	16	18	14	12	12	10	8	6
10	43	31	24	19	38	28	22	17	22	17	14	16	13	11	11	9	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5062	5062	5062
5°	5086	4872	4853
10°	5054	4728	4675
15°	4983	4575	4487
20°	4896	4412	4306
25°	4810	4254	4140
30°	4687	4093	3976
35°	4563	3936	3860
40°	4433	3803	3743
45°	4308	3685	3644
50°	4176	3577	3546
55°	4035	3461	3447
60°	3865	3340	3342
65°	3686	3200	3215
70°	3487	3048	3081
75°	3236	2900	2956
80°	2836	2748	2829
85°	2454	2617	2731



TEST NUMBER: P331261

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.7	0.7
10°-20°	85.2	2.1
20°-30°	129.1	3.2
30°-40°	157.2	3.8
40°-50°	169.1	4.1
50°-60°	164.2	4.0
60°-70°	143.4	3.5
70°-80°	110.4	2.7
80°-90°	76.5	1.9
90°-100°	84.0	2.1
100°-110°	158.2	3.9
110°-120°	347.9	8.5
120°-130°	547.3	13.4
130°-140°	573.2	14.0
140°-150°	528.5	12.9
150°-160°	424.1	10.4
160°-170°	273.3	6.7
170°-180°	94.1	2.3
0°-30°	243.9	6.0
0°-40°	401.1	9.8
0°-60°	734.5	17.9
0°-90°	1064.8	26.0
90°-120°	590.1	14.4
90°-150°	2239.1	54.7
90°-180°	3031.0	74.0
0°-180°	4095.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	314	314	314	314	314	
5°	314	313	310	313	312	30
15°	300	301	301	305	304	84
25°	273	276	280	285	287	125
35°	235	243	251	261	264	147
45°	193	205	221	234	239	149
55°	148	164	188	203	210	132
65°	101	123	150	168	174	100
75°	56	82	110	129	136	59
85°	16	45	74	92	99	18
90°	5	40	74	95	103	5
95°	50	50	80	100	106	60
105°	220	243	83	106	114	235
115°	413	432	469	166	104	406
125°	582	593	620	637	643	519
135°	720	732	742	758	761	556
145°	835	835	846	853	853	522
155°	919	914	921	925	920	423
165°	969	965	966	971	966	274
175°	991	986	987	992	985	94
180°	989	989	989	989	989	



TEST NUMBER: P331261

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-D

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	313.5	313.5	313.5	313.5	313.5	313.5	313.5	313.5	313.5	313.5	313.5
2.5°	315.3	315.0	314.8	314.5	314.3	313.9	313.3	312.8	312.2	311.6	312.0
5°	314.4	314.1	313.8	313.5	313.1	312.7	312.1	311.5	310.9	310.3	310.9
7.5°	311.5	311.3	311.1	310.9	310.7	310.4	309.9	309.5	309.0	308.5	309.3
10°	309.4	309.2	309.0	308.8	308.6	308.3	308.0	307.7	307.4	307.1	307.9
12.5°	305.7	305.8	305.8	305.9	305.9	305.8	305.6	305.4	305.1	304.9	305.7
15°	299.8	300.0	300.2	300.4	300.6	300.7	300.7	300.7	300.7	300.7	301.6
17.5°	292.2	292.6	293.0	293.5	293.9	294.3	294.6	294.9	295.2	295.6	296.5
20°	287.1	287.6	288.1	288.6	289.1	289.6	290.0	290.4	290.8	291.2	292.3
22.5°	281.7	282.2	282.8	283.4	284.0	284.6	285.1	285.7	286.3	286.8	287.9
25°	272.6	273.3	274.0	274.7	275.4	276.2	277.1	278.0	278.9	279.8	281.0
27.5°	261.7	262.8	264.0	265.1	266.3	267.4	268.4	269.5	270.6	271.7	273.2
30°	254.4	255.7	257.0	258.3	259.6	261.0	262.3	263.6	264.9	266.2	267.8
32.5°	246.4	247.9	249.3	250.8	252.3	253.8	255.4	256.9	258.5	260.0	261.9
35°	234.9	236.6	238.3	240.0	241.7	243.5	245.5	247.4	249.3	251.2	253.4
37.5°	222.3	224.3	226.3	228.3	230.2	232.5	235.0	237.4	239.9	242.4	244.9
40°	214.0	216.2	218.4	220.6	222.8	225.3	228.0	230.8	233.5	236.2	238.8
42.5°	206.0	208.2	210.4	212.6	214.9	217.5	220.7	223.8	226.9	230.0	232.9
45°	192.6	195.3	198.1	200.8	203.5	206.6	210.2	213.7	217.2	220.8	223.9
47.5°	179.4	182.4	185.4	188.3	191.3	194.9	199.0	203.1	207.3	211.4	214.7
50°	170.4	173.5	176.6	179.7	182.9	186.7	191.3	195.8	200.3	204.9	208.3
52.5°	161.6	164.9	168.2	171.5	174.8	178.8	183.6	188.4	193.2	198.0	201.5
55°	147.6	151.3	154.9	158.5	162.2	166.6	171.9	177.1	182.4	187.6	191.3
57.5°	133.8	137.9	142.0	146.1	150.2	154.9	160.3	165.6	171.0	176.4	180.3
60°	124.0	128.4	132.7	137.0	141.4	146.4	152.2	157.9	163.7	169.4	173.3
62.5°	115.3	119.8	124.3	128.8	133.3	138.4	144.2	149.9	155.7	161.5	165.5
65°	100.8	105.8	110.7	115.7	120.6	126.1	132.0	138.0	144.0	149.9	154.1
67.5°	87.6	92.8	97.9	103.1	108.3	113.9	120.0	126.1	132.2	138.3	142.5
70°	78.1	83.4	88.6	93.9	99.1	104.9	111.1	117.4	123.7	129.9	134.3
72.5°	69.4	74.8	80.2	85.6	91.1	96.9	103.3	109.6	116.0	122.3	126.6
75°	55.9	61.5	67.2	72.8	78.5	84.5	91.0	97.5	103.9	110.4	114.7
77.5°	42.8	48.7	54.6	60.5	66.5	72.7	79.3	85.8	92.4	98.9	103.3
80°	34.1	40.2	46.4	52.5	58.7	65.1	71.6	78.2	84.7	91.3	95.5
82.5°	26.8	32.9	39.0	45.0	51.1	57.5	64.1	70.8	77.4	84.0	88.3
85°	16.4	22.6	28.9	35.1	41.4	47.7	54.2	60.7	67.1	73.6	77.8
87.5°	9.0	15.4	21.8	28.1	34.5	41.1	47.8	54.5	61.2	67.9	72.2
90°	5.3	12.9	20.5	28.1	35.7	43.3	51.1	58.8	66.5	74.3	79.1
92.5°	18.6	23.9	29.2	34.5	39.8	45.9	52.7	59.6	66.4	73.3	77.7
95°	50.1	49.6	49.1	48.6	48.1	51.5	58.6	65.8	73.0	80.1	84.8
97.5°	95.5	84.9	74.3	63.8	53.2	52.1	60.5	68.9	77.3	85.7	90.0
100°	129.8	111.8	93.7	75.7	57.6	52.8	61.1	69.5	77.8	86.2	91.2
102.5°	167.2	166.0	164.8	163.6	162.4	153.3	136.1	119.0	101.9	84.8	90.1
105°	219.7	227.4	235.1	242.8	250.5	235.3	197.1	159.0	120.9	82.7	88.0
107.5°	280.2	286.3	292.5	298.7	304.9	284.5	237.5	190.5	143.4	96.4	98.0
110°	318.7	324.1	329.4	334.8	340.1	322.3	281.3	240.3	199.3	158.3	145.7



TEST NUMBER: P331261

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	355.3	360.0	364.6	369.3	373.9	372.9	366.3	359.7	353.0	346.4	291.6
115°	413.1	416.9	420.8	424.6	428.4	434.6	443.1	451.6	460.1	468.6	398.0
117.5°	464.3	468.1	471.8	475.6	479.3	484.7	491.6	498.5	505.5	512.4	497.6
120°	502.1	504.9	507.7	510.5	513.2	518.1	525.0	531.9	538.8	545.7	550.4
122.5°	534.1	536.8	539.5	542.2	544.8	549.6	556.5	563.5	570.4	577.3	581.2
125°	582.5	584.5	586.6	588.7	590.7	594.9	601.2	607.4	613.7	619.9	623.7
127.5°	626.7	628.9	631.1	633.2	635.4	639.0	643.8	648.7	653.5	658.4	662.5
130°	654.7	657.2	659.6	662.1	664.5	667.6	671.5	675.4	679.3	683.1	687.3
132.5°	683.3	685.4	687.5	689.5	691.6	694.3	697.7	701.1	704.5	707.8	711.7
135°	720.1	722.6	725.2	727.7	730.3	732.7	735.2	737.6	740.1	742.5	746.2
137.5°	757.7	759.5	761.2	763.0	764.7	766.7	768.7	770.8	772.9	774.9	778.3
140°	782.3	783.5	784.7	785.8	787.0	788.6	790.5	792.5	794.4	796.4	799.4
142.5°	802.9	804.0	805.0	806.0	807.1	808.6	810.7	812.7	814.8	816.8	819.4
145°	834.8	834.6	834.5	834.3	834.2	835.4	838.1	840.8	843.5	846.2	848.0
147.5°	863.0	862.4	861.8	861.2	860.6	861.6	864.3	866.9	869.6	872.3	873.2
150°	881.3	880.2	879.1	878.0	876.8	877.6	880.1	882.6	885.2	887.7	888.7
152.5°	896.7	895.5	894.3	893.0	891.8	892.4	894.8	897.2	899.6	902.0	903.0
155°	919.2	917.8	916.3	914.9	913.5	913.7	915.6	917.5	919.4	921.3	922.3
157.5°	936.8	935.6	934.4	933.2	932.0	932.0	933.4	934.7	936.0	937.4	938.5
160°	947.1	946.1	945.2	944.2	943.3	943.3	944.2	945.2	946.1	947.1	948.1
162.5°	956.3	955.3	954.4	953.4	952.4	952.4	953.2	954.0	954.9	955.7	956.8
165°	968.6	967.6	966.7	965.7	964.7	964.5	965.0	965.5	965.9	966.4	967.5
167.5°	977.7	976.8	975.8	974.9	973.9	973.6	974.1	974.5	975.0	975.4	976.5
170°	982.9	981.9	981.0	980.0	979.1	978.7	979.1	979.4	979.7	980.0	981.1
172.5°	986.3	985.3	984.4	983.4	982.5	982.2	982.5	982.8	983.1	983.4	984.6
175°	990.7	989.6	988.5	987.4	986.3	985.9	986.2	986.5	986.8	987.2	988.3
177.5°	991.5	990.6	989.7	988.8	987.9	987.5	987.6	987.8	987.9	988.0	988.9
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331261

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	313.5	313.5	313.5	313.5	313.5	313.5	313.5	313.5
2.5°	312.4	312.8	313.2	313.4	313.2	313.0	312.9	312.7
5°	311.5	312.1	312.7	312.9	312.8	312.7	312.6	312.5
7.5°	310.0	310.7	311.5	311.8	311.7	311.6	311.5	311.4
10°	308.7	309.5	310.3	310.7	310.6	310.5	310.4	310.3
12.5°	306.5	307.3	308.1	308.5	308.4	308.3	308.2	308.1
15°	302.5	303.5	304.4	304.8	304.7	304.6	304.5	304.4
17.5°	297.5	298.4	299.3	299.8	299.8	299.8	299.8	299.8
20°	293.4	294.5	295.6	296.2	296.2	296.2	296.2	296.2
22.5°	289.1	290.2	291.3	291.9	292.1	292.2	292.4	292.6
25°	282.3	283.5	284.7	285.4	285.7	286.0	286.3	286.6
27.5°	274.7	276.3	277.8	278.7	278.9	279.1	279.3	279.6
30°	269.4	271.1	272.7	273.6	273.9	274.2	274.5	274.8
32.5°	263.7	265.6	267.5	268.7	269.2	269.8	270.3	270.8
35°	255.7	257.9	260.1	261.6	262.3	263.0	263.7	264.4
37.5°	247.3	249.8	252.3	253.9	254.6	255.4	256.1	256.8
40°	241.5	244.1	246.7	248.5	249.4	250.3	251.2	252.1
42.5°	235.8	238.6	241.5	243.4	244.3	245.2	246.1	247.0
45°	227.0	230.2	233.3	235.4	236.4	237.4	238.4	239.4
47.5°	218.0	221.2	224.5	226.7	227.8	228.9	230.0	231.1
50°	211.7	215.2	218.6	220.9	222.0	223.1	224.2	225.3
52.5°	205.0	208.5	212.0	214.4	215.6	216.8	218.0	219.1
55°	194.9	198.5	202.2	204.6	205.9	207.3	208.6	209.9
57.5°	184.2	188.1	192.0	194.6	196.0	197.3	198.6	200.0
60°	177.1	181.0	184.8	187.4	188.8	190.2	191.7	193.1
62.5°	169.6	173.7	177.8	180.5	181.8	183.1	184.5	185.8
65°	158.2	162.3	166.5	169.2	170.5	171.8	173.1	174.4
67.5°	146.6	150.8	155.0	157.8	159.1	160.5	161.9	163.3
70°	138.6	142.9	147.3	150.1	151.3	152.5	153.7	154.9
72.5°	130.8	135.1	139.3	142.2	143.6	145.1	146.6	148.0
75°	119.1	123.4	127.8	130.6	131.9	133.2	134.5	135.8
77.5°	107.6	111.9	116.2	119.1	120.5	121.9	123.3	124.7
80°	99.8	104.0	108.3	111.1	112.5	113.9	115.3	116.7
82.5°	92.5	96.8	101.0	103.8	105.1	106.5	107.8	109.1
85°	82.1	86.3	90.6	93.4	94.8	96.2	97.6	99.0
87.5°	76.5	80.7	85.0	87.8	89.2	90.6	91.9	93.3
90°	83.9	88.8	93.6	96.8	98.3	99.8	101.4	102.9
92.5°	82.0	86.4	90.8	93.7	95.1	96.5	97.9	99.3
95°	89.4	94.0	98.7	101.5	102.6	103.6	104.7	105.7
97.5°	94.4	98.8	103.2	106.0	107.4	108.8	110.2	111.6
100°	96.2	101.2	106.2	109.4	110.9	112.3	113.7	115.2
102.5°	95.4	100.7	106.0	109.5	111.0	112.6	114.1	115.7
105°	93.3	98.5	103.8	107.3	109.1	110.8	112.6	114.3
107.5°	99.7	101.3	102.9	104.6	106.3	108.1	109.8	111.5
110°	133.0	120.3	107.7	102.2	104.0	105.7	107.5	109.2



TEST NUMBER: P331261

CATALOG NUMBER: S122DIP-S290D725U835-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	236.8	182.1	127.3	100.8	102.4	104.0	105.6	107.2
115°	327.5	256.9	186.3	145.9	135.5	125.2	114.9	104.5
117.5°	482.8	467.9	453.1	427.4	390.8	354.3	317.7	281.1
120°	555.2	559.9	564.6	556.8	536.5	516.1	495.8	475.4
122.5°	585.1	588.9	592.8	593.2	590.0	586.7	583.5	580.3
125°	627.6	631.4	635.3	637.9	639.3	640.6	642.0	643.4
127.5°	666.7	670.8	674.9	677.5	678.4	679.4	680.4	681.4
130°	691.5	695.6	699.8	702.2	702.9	703.5	704.2	704.8
132.5°	715.5	719.3	723.2	725.4	726.1	726.7	727.4	728.0
135°	749.9	753.6	757.3	759.4	759.9	760.4	760.9	761.4
137.5°	781.8	785.2	788.6	790.4	790.5	790.7	790.8	790.9
140°	802.5	805.5	808.5	810.0	809.8	809.6	809.4	809.2
142.5°	822.0	824.6	827.2	828.4	828.1	827.8	827.5	827.3
145°	849.7	851.4	853.1	853.8	853.5	853.2	853.0	852.7
147.5°	874.1	875.0	875.9	876.1	875.7	875.3	874.9	874.4
150°	889.6	890.6	891.5	891.6	890.8	890.0	889.2	888.4
152.5°	903.9	904.9	905.9	905.8	904.8	903.7	902.7	901.6
155°	923.3	924.2	925.2	925.0	923.7	922.5	921.2	919.9
157.5°	939.5	940.6	941.7	941.6	940.4	939.1	937.9	936.7
160°	949.0	950.0	950.9	950.8	949.7	948.6	947.5	946.4
162.5°	957.8	958.9	960.0	959.9	958.5	957.1	955.8	954.4
165°	968.6	969.8	970.9	970.9	969.8	968.6	967.5	966.4
167.5°	977.7	978.8	979.9	979.7	978.3	976.9	975.4	974.0
170°	982.2	983.3	984.5	984.3	982.9	981.4	980.0	978.6
172.5°	985.7	986.8	987.9	987.7	986.3	984.9	983.4	982.0
175°	989.4	990.5	991.6	991.4	989.8	988.2	986.6	985.0
177.5°	989.8	990.7	991.6	991.5	990.3	989.2	988.0	986.9
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6

(END OF REPORT)