

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331327

Luminaire Tested: **S122DIP-S485D1080U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331327
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S485D1080U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6285.0 lumens
Efficiency: N/A
Efficacy: 127.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331327

CATALOG NUMBER: S122DIP-S485D1080U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331327

CATALOG NUMBER: S122DIP-S485D1080U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	35	34	33	26
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28	22
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10
9	48	36	28	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12540	12540	12540
5°	12588	12407	12480
10°	12514	12281	12342
15°	12359	12122	12109
20°	12139	11883	11869
25°	11922	11589	11589
30°	11641	11320	11222
35°	11379	10996	10835
40°	11051	10673	10467
45°	10727	10351	10095
50°	10374	10017	9661
55°	10007	9627	9272
60°	9597	9164	8825
65°	9158	8703	8302
70°	8601	8143	7756
75°	7829	7498	7317
80°	6946	6732	6388
85°	5669	5391	4835



TEST NUMBER: P331327

CATALOG NUMBER: S122DIP-S485D1080U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	1.2
10°-20°	205.5	3.3
20°-30°	302.1	4.8
30°-40°	350.9	5.6
40°-50°	350.5	5.6
50°-60°	305.6	4.9
60°-70°	226.0	3.6
70°-80°	128.0	2.0
80°-90°	38.0	0.6
90°-100°	49.0	0.8
100°-110°	179.7	2.9
110°-120°	480.4	7.6
120°-130°	793.0	12.6
130°-140°	843.3	13.4
140°-150°	783.8	12.5
150°-160°	630.2	10.0
160°-170°	406.1	6.5
170°-180°	139.8	2.2
0°-30°	580.6	9.2
0°-40°	931.5	14.8
0°-60°	1587.6	25.3
0°-90°	1979.7	31.5
90°-120°	709.1	11.3
90°-150°	3129.2	49.8
90°-180°	4305.0	68.5
0°-180°	6285.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	777	777	777	777	777	
5°	777	773	766	771	770	74
15°	739	735	725	728	724	208
25°	669	663	650	652	650	308
35°	577	570	558	553	550	360
45°	470	464	453	445	442	362
55°	356	351	342	333	329	318
65°	240	235	228	221	217	237
75°	126	124	120	116	117	134
85°	31	30	29	27	26	35
90°	1	13	21	26	29	5
95°	69	36	42	46	46	85
105°	323	337	65	76	81	345
115°	611	630	656	187	87	602
125°	864	878	898	906	909	770
135°	1069	1086	1096	1106	1104	826
145°	1241	1241	1258	1264	1260	776
155°	1366	1358	1369	1375	1367	629
165°	1439	1434	1436	1443	1436	406
175°	1472	1465	1467	1473	1464	140
180°	1469	1469	1469	1469	1469	



TEST NUMBER: P331327

CATALOG NUMBER: S122DIP-S485D1080U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	780.3	779.6	779.0	778.3	777.6	776.6	775.1	773.7	772.2	770.7	772.1
5°	776.7	776.0	775.4	774.7	774.1	772.8	771.0	769.2	767.3	765.5	766.8
7.5°	769.8	768.8	767.8	766.7	765.7	764.3	762.4	760.6	758.7	756.8	758.2
10°	763.3	762.1	760.9	759.8	758.6	757.0	755.0	753.1	751.1	749.1	750.4
12.5°	754.3	753.3	752.2	751.2	750.2	748.7	746.7	744.7	742.7	740.7	741.6
15°	739.4	738.4	737.4	736.4	735.4	733.8	731.6	729.5	727.3	725.2	725.8
17.5°	720.2	719.3	718.3	717.3	716.3	714.7	712.5	710.3	708.1	705.9	706.7
20°	706.5	705.5	704.5	703.5	702.5	700.9	698.5	696.2	693.9	691.6	692.1
22.5°	692.8	691.4	690.0	688.6	687.2	685.4	683.2	681.0	678.8	676.6	676.7
25°	669.2	667.8	666.5	665.2	663.9	661.8	659.0	656.1	653.3	650.5	650.8
27.5°	642.3	641.1	639.9	638.7	637.5	635.8	633.6	631.3	629.1	626.9	626.4
30°	624.4	623.0	621.7	620.4	619.0	617.1	614.6	612.2	609.7	607.2	606.7
32.5°	605.2	604.2	603.1	602.0	601.0	599.1	596.5	593.9	591.3	588.7	587.8
35°	577.3	575.6	574.0	572.3	570.7	568.5	565.9	563.2	560.5	557.9	556.9
37.5°	545.8	544.3	542.9	541.4	539.9	537.9	535.2	532.6	529.9	527.3	526.0
40°	524.3	522.9	521.6	520.3	519.0	517.0	514.3	511.7	509.0	506.4	504.9
42.5°	503.4	502.0	500.7	499.4	498.1	496.1	493.4	490.8	488.1	485.4	483.8
45°	469.8	468.6	467.4	466.3	465.1	463.3	460.8	458.3	455.8	453.3	451.5
47.5°	436.3	435.2	434.1	433.0	431.9	430.1	427.5	424.9	422.3	419.7	417.8
50°	413.0	412.2	411.3	410.5	409.7	408.1	405.8	403.5	401.1	398.8	396.5
52.5°	390.3	389.2	388.1	387.0	385.9	384.3	382.1	379.9	377.7	375.5	373.6
55°	355.5	354.5	353.5	352.5	351.5	350.0	348.0	346.0	344.0	342.0	340.1
57.5°	320.5	319.7	318.9	318.2	317.4	315.9	313.7	311.5	309.3	307.1	305.1
60°	297.2	296.6	295.9	295.2	294.6	293.1	290.8	288.4	286.1	283.8	282.0
62.5°	274.5	273.5	272.4	271.3	270.3	268.9	267.1	265.3	263.5	261.7	260.0
65°	239.7	238.7	237.7	236.7	235.8	234.4	232.8	231.1	229.4	227.8	226.3
67.5°	204.3	203.5	202.7	201.9	201.1	200.0	198.5	197.0	195.5	194.0	192.9
70°	182.2	181.6	180.9	180.2	179.6	178.5	177.0	175.5	174.0	172.5	171.4
72.5°	159.5	158.9	158.2	157.5	156.9	156.1	155.1	154.1	153.2	152.2	151.0
75°	125.5	125.1	124.8	124.5	124.1	123.6	122.7	121.9	121.1	120.2	119.2
77.5°	95.0	94.4	93.9	93.3	92.7	92.3	92.0	91.6	91.3	91.0	90.5
80°	74.7	74.5	74.4	74.2	74.0	73.8	73.4	73.1	72.8	72.4	71.9
82.5°	55.6	55.5	55.5	55.5	55.4	55.3	55.1	54.9	54.7	54.5	53.9
85°	30.6	30.5	30.3	30.1	30.0	29.8	29.6	29.5	29.3	29.1	28.6
87.5°	11.0	11.2	11.5	11.7	12.0	12.2	12.3	12.4	12.5	12.6	12.5
90°	1.1	3.7	6.3	8.9	11.5	13.7	15.6	17.5	19.4	21.3	22.4
92.5°	21.5	21.2	21.0	20.8	20.5	20.9	21.8	22.8	23.7	24.7	25.3
95°	69.1	61.3	53.5	45.7	37.9	34.8	36.5	38.2	39.8	41.5	42.6
97.5°	137.1	115.2	93.2	71.2	49.3	40.2	44.0	47.8	51.7	55.5	56.4
100°	188.2	155.8	123.4	91.1	58.7	44.5	48.5	52.6	56.6	60.6	62.5
102.5°	244.3	237.4	230.6	223.7	216.9	196.7	163.1	129.5	95.9	62.3	64.8
105°	323.2	330.3	337.3	344.4	351.5	322.8	258.3	193.8	129.3	64.8	67.4
107.5°	413.1	418.8	424.5	430.2	436.0	400.2	322.8	245.5	168.1	90.8	88.1
110°	470.9	475.9	480.9	485.8	490.8	459.1	390.8	322.6	254.3	186.0	162.4



TEST NUMBER: P331327

CATALOG NUMBER: S122DIP-S485D1080U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	525.4	529.8	534.1	538.5	542.9	536.7	519.8	503.0	486.1	469.2	383.1
115°	611.3	615.3	619.3	623.3	627.3	632.3	638.2	644.1	650.0	655.9	546.5
117.5°	688.0	692.5	697.0	701.5	706.0	710.2	714.3	718.4	722.4	726.5	700.0
120°	744.1	747.7	751.2	754.8	758.3	762.2	766.5	770.7	775.0	779.2	782.0
122.5°	791.8	795.5	799.2	803.0	806.7	810.9	815.5	820.1	824.8	829.4	831.1
125°	864.3	867.3	870.4	873.5	876.5	880.3	884.8	889.3	893.8	898.3	899.9
127.5°	930.0	933.4	936.8	940.2	943.6	946.9	950.3	953.6	957.0	960.4	962.8
130°	971.6	975.4	979.2	983.0	986.7	989.9	992.5	995.1	997.7	1000.3	1002.9
132.5°	1014.1	1017.4	1020.6	1023.8	1027.0	1029.9	1032.5	1035.1	1037.7	1040.3	1042.5
135°	1069.4	1073.2	1077.0	1080.8	1084.5	1087.5	1089.6	1091.7	1093.9	1096.0	1098.4
137.5°	1125.3	1128.0	1130.6	1133.3	1135.9	1138.4	1140.9	1143.3	1145.7	1148.1	1150.4
140°	1161.9	1163.8	1165.7	1167.6	1169.5	1171.7	1174.3	1176.9	1179.5	1182.1	1184.2
142.5°	1192.5	1194.2	1195.9	1197.6	1199.3	1201.7	1204.6	1207.6	1210.6	1213.6	1215.5
145°	1240.6	1240.3	1240.1	1239.9	1239.6	1241.5	1245.5	1249.5	1253.6	1257.6	1259.2
147.5°	1282.5	1281.6	1280.7	1279.8	1278.9	1280.4	1284.4	1288.3	1292.3	1296.3	1297.5
150°	1309.7	1308.0	1306.4	1304.7	1303.1	1304.1	1307.9	1311.7	1315.5	1319.2	1320.7
152.5°	1332.6	1330.8	1328.9	1327.1	1325.3	1326.1	1329.7	1333.3	1336.9	1340.5	1341.9
155°	1366.0	1363.9	1361.8	1359.6	1357.5	1357.9	1360.7	1363.5	1366.4	1369.2	1370.6
157.5°	1392.2	1390.4	1388.6	1386.8	1385.0	1385.1	1387.1	1389.0	1391.0	1393.0	1394.6
160°	1407.5	1406.1	1404.6	1403.2	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5	1408.9
162.5°	1421.1	1419.7	1418.2	1416.8	1415.4	1415.3	1416.5	1417.8	1419.0	1420.2	1421.8
165°	1439.4	1437.9	1436.5	1435.1	1433.7	1433.3	1434.0	1434.8	1435.5	1436.2	1437.8
167.5°	1453.0	1451.6	1450.1	1448.7	1447.3	1446.9	1447.6	1448.2	1448.9	1449.6	1451.2
170°	1460.6	1459.2	1457.8	1456.4	1455.0	1454.5	1455.0	1455.4	1455.9	1456.4	1458.0
172.5°	1465.7	1464.3	1462.9	1461.5	1460.1	1459.6	1460.1	1460.5	1461.0	1461.5	1463.1
175°	1472.3	1470.7	1469.0	1467.4	1465.7	1465.1	1465.6	1466.1	1466.5	1467.0	1468.7
177.5°	1473.4	1472.1	1470.7	1469.4	1468.1	1467.5	1467.7	1467.9	1468.1	1468.3	1469.6
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331327

CATALOG NUMBER: S122DIP-S485D1080U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	773.4	774.7	776.0	776.6	776.3	776.0	775.8	775.5
5°	768.2	769.5	770.8	771.3	771.0	770.6	770.3	770.0
7.5°	759.5	760.8	762.2	762.6	762.3	761.9	761.5	761.2
10°	751.7	753.1	754.4	754.8	754.3	753.8	753.3	752.8
12.5°	742.6	743.5	744.4	744.7	744.3	744.0	743.6	743.2
15°	726.5	727.2	727.8	727.7	726.9	726.1	725.3	724.4
17.5°	707.4	708.2	709.0	708.9	708.1	707.4	706.6	705.8
20°	692.6	693.1	693.6	693.5	692.8	692.1	691.5	690.8
22.5°	676.8	676.9	677.0	676.9	676.5	676.1	675.7	675.3
25°	651.2	651.5	651.8	651.8	651.5	651.2	650.8	650.5
27.5°	625.9	625.4	624.9	624.3	623.5	622.7	621.9	621.1
30°	606.2	605.7	605.2	604.6	603.9	603.3	602.6	601.9
32.5°	586.9	586.0	585.1	584.3	583.6	583.0	582.3	581.6
35°	555.9	554.9	553.9	553.0	552.2	551.3	550.5	549.7
37.5°	524.8	523.6	522.4	521.3	520.5	519.7	518.9	518.2
40°	503.4	501.9	500.4	499.3	498.6	498.0	497.3	496.6
42.5°	482.2	480.6	478.9	477.7	476.7	475.8	474.9	473.9
45°	449.7	447.9	446.0	444.8	444.1	443.5	442.8	442.1
47.5°	415.9	413.9	412.0	410.6	409.6	408.7	407.7	406.7
50°	394.2	391.8	389.5	387.9	387.1	386.3	385.4	384.6
52.5°	371.7	369.7	367.8	366.3	365.2	364.1	363.0	361.9
55°	338.1	336.1	334.1	332.7	331.8	331.0	330.2	329.4
57.5°	303.2	301.2	299.3	298.0	297.3	296.7	296.1	295.4
60°	280.1	278.3	276.5	275.3	274.8	274.3	273.8	273.3
62.5°	258.3	256.6	254.9	253.8	253.1	252.5	251.9	251.2
65°	224.8	223.3	221.8	220.6	219.8	219.0	218.2	217.3
67.5°	191.7	190.5	189.4	188.5	187.8	187.1	186.5	185.8
70°	170.2	169.0	167.9	167.0	166.3	165.6	165.0	164.3
72.5°	149.9	148.7	147.6	146.7	146.2	145.6	145.1	144.6
75°	118.2	117.3	116.3	115.9	116.3	116.6	116.9	117.3
77.5°	90.0	89.5	89.0	88.5	88.0	87.6	87.1	86.6
80°	71.4	70.9	70.5	70.0	69.7	69.4	69.0	68.7
82.5°	53.3	52.6	52.0	51.6	51.6	51.5	51.4	51.4
85°	28.1	27.6	27.1	26.8	26.6	26.5	26.3	26.1
87.5°	12.3	12.1	12.0	11.9	11.8	11.8	11.8	11.7
90°	23.6	24.8	26.0	26.8	27.3	27.8	28.2	28.7
92.5°	25.9	26.5	27.1	27.6	27.9	28.1	28.4	28.7
95°	43.8	45.0	46.2	46.7	46.4	46.2	45.9	45.7
97.5°	57.4	58.3	59.3	59.9	60.2	60.5	60.7	61.0
100°	64.4	66.3	68.2	69.3	69.8	70.3	70.8	71.2
102.5°	67.2	69.7	72.1	73.7	74.3	75.0	75.7	76.3
105°	70.0	72.6	75.2	77.0	78.0	78.9	79.8	80.8
107.5°	85.5	82.8	80.2	79.4	80.3	81.2	82.2	83.1
110°	138.8	115.2	91.5	80.2	81.1	82.1	83.0	84.0



TEST NUMBER: P331327

CATALOG NUMBER: S122DIP-S485D1080U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	296.9	210.7	124.5	81.8	82.6	83.3	84.1	84.8
115°	437.1	327.8	218.4	155.2	138.2	121.2	104.2	87.2
117.5°	673.6	647.1	620.7	579.5	523.6	467.7	411.8	355.9
120°	784.9	787.7	790.6	776.0	744.1	712.2	680.3	648.5
122.5°	832.8	834.5	836.2	833.9	827.8	821.6	815.4	809.2
125°	901.6	903.2	904.9	906.1	906.8	907.5	908.2	908.9
127.5°	965.2	967.6	970.0	971.3	971.4	971.6	971.7	971.8
130°	1005.5	1008.1	1010.7	1011.9	1011.7	1011.4	1011.2	1011.0
132.5°	1044.7	1047.0	1049.2	1050.2	1049.9	1049.7	1049.5	1049.2
135°	1100.7	1103.1	1105.4	1106.4	1105.9	1105.4	1105.0	1104.5
137.5°	1152.7	1155.0	1157.3	1158.1	1157.3	1156.5	1155.7	1154.9
140°	1186.4	1188.5	1190.6	1191.1	1189.9	1188.7	1187.5	1186.4
142.5°	1217.4	1219.4	1221.3	1221.7	1220.5	1219.3	1218.2	1217.0
145°	1260.9	1262.5	1264.2	1264.4	1263.3	1262.1	1260.9	1259.7
147.5°	1298.7	1300.0	1301.2	1301.3	1300.3	1299.3	1298.3	1297.3
150°	1322.1	1323.5	1324.9	1325.0	1323.8	1322.7	1321.5	1320.3
152.5°	1343.3	1344.8	1346.2	1346.1	1344.5	1343.0	1341.4	1339.9
155°	1372.0	1373.5	1374.9	1374.6	1372.7	1370.9	1369.0	1367.1
157.5°	1396.2	1397.8	1399.4	1399.3	1397.5	1395.6	1393.8	1391.9
160°	1410.3	1411.7	1413.1	1413.0	1411.4	1409.7	1408.1	1406.4
162.5°	1423.4	1425.0	1426.7	1426.4	1424.4	1422.4	1420.3	1418.3
165°	1439.5	1441.1	1442.8	1442.8	1441.1	1439.5	1437.8	1436.2
167.5°	1452.9	1454.5	1456.2	1455.9	1453.8	1451.7	1449.6	1447.4
170°	1459.7	1461.3	1463.0	1462.7	1460.6	1458.5	1456.4	1454.2
172.5°	1464.8	1466.4	1468.1	1467.9	1465.7	1463.6	1461.5	1459.3
175°	1470.3	1472.0	1473.6	1473.3	1470.9	1468.5	1466.2	1463.8
177.5°	1470.9	1472.2	1473.6	1473.4	1471.7	1470.0	1468.3	1466.6
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1

(END OF REPORT)