

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331303

Luminaire Tested: **S122DIP-S485D725U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331303
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S485D725U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5043.4 lumens
Efficiency: N/A
Efficacy: 131.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331303

CATALOG NUMBER: S122DIP-S485D725U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331303

CATALOG NUMBER: S122DIP-S485D725U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	44	43	42	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	31
3	81	72	65	59	74	66	60	55	55	50	47	45	42	39	35	33	31	27
4	74	64	56	50	67	59	52	47	49	44	40	40	37	34	32	29	27	24
5	68	57	49	43	62	52	46	40	44	39	35	36	32	29	29	26	24	21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	26	24	21	18
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19	17
8	54	42	35	29	49	39	32	28	33	28	24	27	24	21	22	19	17	15
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	21	18	16	14
10	47	35	28	24	43	33	26	22	28	23	20	23	20	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15689	15689	15689	15689
5°	17590	15793	13994	15793
10°	20156	15662	12111	15662
15°	22298	15375	10700	15375
20°	21959	15067	9754	15067
25°	19800	14656	9155	14656
30°	16362	14001	8718	14001
35°	11925	13316	8406	13316
40°	9525	12507	8233	12507
45°	8323	11572	7999	11572
50°	7824	10665	7842	10665
55°	7212	9745	7631	9745
60°	6610	8767	7308	8767
65°	6021	7889	6991	7889
70°	5467	7034	6524	7034
75°	4847	6082	5777	6082
80°	4166	5040	4649	5040
85°	3742	3742	2760	3742



TEST NUMBER: P331303

CATALOG NUMBER: S122DIP-S485D725U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.5	1.8
10°-20°	269.0	5.3
20°-30°	390.5	7.7
30°-40°	412.0	8.2
40°-50°	364.8	7.2
50°-60°	291.1	5.8
60°-70°	197.9	3.9
70°-80°	101.5	2.0
80°-90°	26.9	0.5
90°-100°	33.0	0.7
100°-110°	120.9	2.4
110°-120°	323.3	6.4
120°-130°	533.6	10.6
130°-140°	567.5	11.3
140°-150°	527.5	10.5
150°-160°	424.1	8.4
160°-170°	273.3	5.4
170°-180°	94.1	1.9
0°-30°	752.0	14.9
0°-40°	1164.1	23.1
0°-60°	1820.1	36.1
0°-90°	2146.3	42.6
90°-120°	477.2	9.5
90°-150°	2105.7	41.8
90°-180°	2897.0	57.4
0°-180°	5043.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	972	972	972	972	972	
5°	1085	974	863	974	1085	108
15°	1334	920	640	920	1334	368
25°	1111	823	514	823	1111	502
35°	605	676	426	676	605	393
45°	364	507	350	507	364	287
55°	256	346	271	346	256	230
65°	158	206	183	206	158	157
75°	78	98	93	98	78	83
85°	20	20	15	20	20	23
90°	19	1	19	1	19	10
95°	31	46	31	46	31	29
105°	54	218	54	218	54	57
115°	59	411	59	411	59	147
125°	612	582	612	582	612	529
135°	743	720	743	720	743	573
145°	848	835	848	835	848	530
155°	920	919	920	919	920	424
165°	966	969	966	969	966	273
175°	985	991	985	991	985	94
180°	989	989	989	989	989	



TEST NUMBER: P331303

CATALOG NUMBER: S122DIP-S485D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1016.6	1016.9	1017.4	1012.7	1012.1	1012.1	1007.9	1004.3	1000.1	994.4	995.0
5°	1085.3	1089.4	1090.9	1086.4	1079.7	1078.9	1072.6	1062.1	1052.4	1044.6	1039.0
7.5°	1167.3	1168.9	1165.3	1159.4	1154.4	1145.4	1133.6	1122.0	1105.8	1090.9	1079.9
10°	1229.4	1231.7	1225.3	1216.7	1209.6	1199.2	1182.0	1164.4	1143.2	1122.6	1106.2
12.5°	1276.6	1282.2	1274.0	1272.9	1260.7	1246.4	1225.9	1217.0	1187.1	1158.5	1140.8
15°	1334.0	1333.6	1334.4	1327.3	1318.3	1316.1	1294.4	1270.9	1228.7	1211.9	1182.7
17.5°	1317.4	1323.1	1325.7	1325.6	1325.4	1324.0	1317.0	1302.2	1281.0	1253.8	1220.2
20°	1278.0	1285.4	1286.6	1295.2	1300.0	1306.4	1309.0	1304.9	1291.8	1269.0	1239.9
22.5°	1217.0	1219.1	1222.6	1236.0	1246.5	1262.4	1270.7	1284.5	1279.5	1268.4	1244.1
25°	1111.4	1107.7	1120.7	1127.5	1151.7	1177.1	1195.4	1215.6	1233.5	1244.4	1237.3
27.5°	984.6	979.0	998.6	1016.4	1036.1	1063.6	1092.1	1125.8	1153.8	1188.9	1200.9
30°	877.6	881.0	899.7	918.7	948.6	987.4	1019.5	1056.5	1096.5	1135.7	1162.9
32.5°	762.3	775.2	787.0	816.2	842.5	885.8	932.9	979.1	1029.0	1073.5	1115.7
35°	605.0	619.9	636.4	657.7	694.6	737.6	783.5	845.9	913.9	974.7	1024.8
37.5°	509.2	506.9	516.3	531.7	561.6	596.3	649.1	710.8	790.8	862.3	932.9
40°	451.9	450.4	457.1	471.3	494.1	519.5	565.8	619.9	694.3	781.6	865.7
42.5°	412.4	413.3	417.1	427.1	442.7	463.6	498.3	544.4	612.4	694.7	785.0
45°	364.5	367.1	371.2	376.1	385.0	402.2	421.6	454.5	508.3	577.0	665.9
47.5°	330.0	330.1	334.2	338.5	343.8	353.5	369.4	390.0	427.9	483.9	560.3
50°	311.5	308.8	311.8	315.2	320.8	327.5	338.0	357.4	382.8	428.0	491.8
52.5°	288.8	288.8	291.5	292.8	297.8	304.5	314.1	327.5	350.5	385.9	438.4
55°	256.2	258.1	259.6	261.8	266.3	271.1	278.6	287.6	305.5	332.0	370.8
57.5°	225.6	226.2	227.7	231.9	234.8	239.2	246.3	254.5	266.1	285.8	315.0
60°	204.7	204.7	207.6	209.5	213.2	217.7	223.3	231.2	241.6	257.7	281.2
62.5°	185.5	185.2	186.4	189.5	192.3	196.5	202.1	208.8	218.6	232.9	252.2
65°	157.6	156.9	159.1	159.8	162.8	166.9	171.4	178.5	186.4	196.8	214.0
67.5°	130.7	131.6	132.8	134.2	135.9	140.2	143.2	148.2	154.8	163.5	175.2
70°	115.8	115.8	115.8	116.9	119.1	121.4	124.4	128.5	134.8	142.3	152.7
72.5°	99.0	100.2	101.4	100.8	103.6	104.9	108.5	110.8	116.9	121.7	130.9
75°	77.7	77.7	77.7	79.5	80.7	81.8	84.0	86.3	89.3	95.2	100.1
77.5°	58.0	57.8	58.2	58.6	59.8	61.2	61.8	63.9	66.6	69.4	73.5
80°	44.8	45.6	45.9	46.7	46.7	47.4	47.8	50.4	52.3	54.2	56.8
82.5°	34.7	34.8	34.9	35.0	35.3	35.8	36.7	37.6	38.2	39.8	41.8
85°	20.2	19.8	19.8	20.5	20.2	20.2	20.9	21.7	21.7	22.0	23.2
87.5°	11.6	11.6	11.8	11.4	11.4	11.6	11.4	10.9	11.1	11.2	11.3
90°	19.3	19.0	18.7	18.4	18.0	17.5	16.7	15.9	15.1	14.3	13.0
92.5°	19.3	19.1	18.9	18.7	18.6	18.2	17.8	17.4	17.0	16.6	16.0
95°	30.8	30.9	31.1	31.2	31.4	31.1	30.3	29.5	28.7	27.9	26.8
97.5°	41.1	40.9	40.7	40.5	40.3	39.9	39.2	38.6	38.0	37.3	34.8
100°	47.9	47.6	47.3	47.0	46.7	45.9	44.6	43.3	42.0	40.8	38.1
102.5°	51.4	50.9	50.5	50.0	49.6	48.5	46.9	45.2	43.6	41.9	64.5
105°	54.4	53.7	53.1	52.5	51.8	50.6	48.9	47.1	45.4	43.6	87.0
107.5°	55.9	55.3	54.7	54.0	53.4	54.0	55.7	57.5	59.3	61.1	113.1
110°	56.5	55.9	55.2	54.6	54.0	61.6	77.5	93.4	109.3	125.2	171.1



TEST NUMBER: P331303

CATALOG NUMBER: S122DIP-S485D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	57.1	56.6	56.1	55.6	55.0	83.8	141.8	199.8	257.8	315.7	327.1
115°	58.7	70.1	81.5	93.0	104.4	147.0	220.6	294.2	367.8	441.4	437.4
117.5°	239.5	277.1	314.7	352.3	389.9	417.6	435.4	453.3	471.1	488.9	486.1
120°	436.4	457.8	479.3	500.7	522.2	532.0	530.1	528.2	526.2	524.3	521.5
122.5°	544.5	548.7	552.8	557.0	561.2	562.7	561.5	560.4	559.2	558.1	555.0
125°	611.6	611.1	610.7	610.2	609.7	608.9	607.8	606.7	605.6	604.5	601.4
127.5°	654.0	653.9	653.8	653.7	653.6	652.7	651.1	649.5	647.9	646.2	644.0
130°	680.3	680.4	680.6	680.8	680.9	680.1	678.4	676.6	674.9	673.1	671.4
132.5°	706.0	706.2	706.4	706.5	706.7	706.0	704.5	703.0	701.5	700.0	698.3
135°	743.2	743.5	743.9	744.2	744.5	743.9	742.3	740.7	739.1	737.5	736.1
137.5°	777.1	777.7	778.2	778.8	779.3	778.8	777.2	775.7	774.1	772.6	770.9
140°	798.3	799.1	799.9	800.7	801.5	801.2	799.7	798.3	796.9	795.5	793.7
142.5°	818.9	819.7	820.5	821.3	822.1	821.8	820.5	819.2	817.9	816.6	814.6
145°	847.7	848.5	849.3	850.1	850.8	850.7	849.6	848.5	847.4	846.2	843.5
147.5°	873.0	873.7	874.3	875.0	875.7	875.6	874.8	873.9	873.1	872.3	869.6
150°	888.4	889.2	890.0	890.8	891.6	891.5	890.6	889.6	888.7	887.7	885.2
152.5°	901.6	902.7	903.7	904.8	905.8	905.9	904.9	903.9	903.0	902.0	899.6
155°	919.9	921.2	922.5	923.7	925.0	925.2	924.2	923.3	922.3	921.3	919.4
157.5°	936.7	937.9	939.1	940.4	941.6	941.7	940.6	939.5	938.5	937.4	936.0
160°	946.4	947.5	948.6	949.7	950.8	950.9	950.0	949.0	948.1	947.1	946.1
162.5°	954.4	955.8	957.1	958.5	959.9	960.0	958.9	957.8	956.8	955.7	954.9
165°	966.4	967.5	968.6	969.8	970.9	970.9	969.8	968.6	967.5	966.4	965.9
167.5°	974.0	975.4	976.9	978.3	979.7	979.9	978.8	977.7	976.5	975.4	975.0
170°	978.6	980.0	981.4	982.9	984.3	984.5	983.3	982.2	981.1	980.0	979.7
172.5°	982.0	983.4	984.9	986.3	987.7	987.9	986.8	985.7	984.6	983.4	983.1
175°	985.0	986.6	988.2	989.8	991.4	991.6	990.5	989.4	988.3	987.2	986.8
177.5°	986.9	988.0	989.2	990.3	991.5	991.6	990.7	989.8	988.9	988.0	987.9
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331303

CATALOG NUMBER: S122DIP-S485D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	997.1	994.7	993.2	987.9	983.1	978.3	976.8	977.4	970.8	964.6	961.9
5°	1036.0	1028.5	1021.4	1011.3	999.4	986.3	979.6	974.4	961.3	947.1	938.9
7.5°	1070.8	1060.1	1046.4	1027.5	1010.1	989.5	976.4	964.9	945.7	925.7	913.5
10°	1092.0	1077.4	1059.9	1036.7	1015.4	990.4	972.9	955.3	932.9	909.0	894.1
12.5°	1110.2	1090.6	1073.3	1043.6	1018.4	987.1	966.3	941.6	918.0	889.6	874.9
15°	1153.6	1117.4	1084.5	1050.9	1019.9	976.2	953.1	919.8	888.8	853.7	836.9
17.5°	1187.1	1146.4	1094.7	1052.0	1015.8	967.4	933.4	893.6	856.9	816.8	794.0
20°	1206.3	1159.6	1103.9	1053.2	1009.8	954.6	917.6	876.9	833.9	788.7	764.1
22.5°	1217.6	1168.6	1113.5	1048.7	997.9	944.1	897.6	853.0	809.4	760.7	734.8
25°	1221.2	1176.4	1118.1	1044.9	982.9	922.1	866.0	822.7	770.1	724.5	686.8
27.5°	1203.4	1171.3	1115.3	1037.9	965.7	894.5	832.1	783.0	727.4	678.0	640.0
30°	1181.6	1162.9	1108.4	1030.7	951.9	875.4	806.7	751.0	695.8	645.7	606.9
32.5°	1147.9	1143.8	1095.9	1020.6	937.3	851.2	780.1	723.8	662.6	613.4	576.4
35°	1081.5	1099.5	1069.2	997.9	909.7	816.8	739.8	675.6	612.1	565.0	530.3
37.5°	992.7	1037.2	1029.3	964.6	872.5	779.3	694.3	627.2	566.7	519.2	485.1
40°	931.4	988.2	996.4	939.2	846.3	750.3	660.3	593.4	534.4	491.1	456.7
42.5°	865.7	932.0	954.6	908.8	817.6	719.8	629.8	560.6	502.2	460.0	429.6
45°	755.5	843.3	884.0	857.8	769.7	669.6	577.0	506.8	453.8	414.2	390.6
47.5°	652.5	748.4	803.2	793.9	716.4	617.3	525.8	458.4	406.8	375.2	354.1
50°	579.6	678.2	744.3	747.3	678.2	580.0	488.1	424.6	377.2	347.7	330.5
52.5°	516.3	610.4	682.5	698.3	635.5	541.1	454.3	391.2	349.4	322.3	306.9
55°	433.6	513.1	593.1	622.2	571.8	482.1	401.8	346.2	307.0	288.3	274.9
57.5°	360.5	426.8	500.6	532.8	501.7	425.0	349.7	301.4	269.6	253.2	242.9
60°	321.9	374.2	439.9	478.4	451.5	383.2	317.4	271.5	245.4	230.8	221.1
62.5°	286.1	332.4	387.9	423.1	408.5	344.0	285.2	244.6	222.1	208.4	201.4
65°	236.0	272.6	315.6	348.1	338.4	289.4	241.3	206.5	188.6	177.8	172.2
67.5°	194.3	220.8	250.6	279.0	271.2	236.5	197.9	170.8	157.4	148.1	144.8
70°	168.1	188.2	214.7	237.5	231.2	202.8	172.2	149.0	137.4	129.6	126.2
72.5°	143.0	159.5	179.8	198.4	194.1	170.5	145.0	127.5	118.6	111.4	108.6
75°	107.9	120.6	133.0	145.3	144.2	125.9	110.9	97.5	90.4	84.8	83.7
77.5°	79.7	86.8	95.2	102.5	100.5	90.0	78.3	70.6	65.4	61.6	61.0
80°	60.9	65.0	71.0	76.2	73.6	69.1	59.8	54.2	50.4	46.7	45.2
82.5°	44.1	48.3	51.8	54.7	52.7	48.5	42.7	38.9	36.7	34.1	33.5
85°	23.2	25.4	26.9	27.6	26.9	24.3	21.7	20.2	18.3	17.2	16.8
87.5°	11.3	11.1	10.8	11.1	9.9	9.5	8.0	6.7	6.8	6.8	6.6
90°	11.8	10.5	9.2	7.7	6.0	4.2	2.5	0.7	2.5	4.2	6.0
92.5°	15.3	14.7	14.1	13.8	14.0	14.1	14.3	14.4	14.3	14.1	14.0
95°	25.7	24.6	23.4	25.5	30.8	36.0	41.3	46.5	41.3	36.0	30.8
97.5°	32.2	29.6	27.0	33.1	47.9	62.7	77.5	92.3	77.5	62.7	47.9
100°	35.4	32.7	30.0	39.5	61.3	83.1	104.8	126.6	104.8	83.1	61.3
102.5°	87.1	109.7	132.3	145.9	150.6	155.2	159.8	164.4	159.8	155.2	150.6
105°	130.4	173.8	217.2	236.5	231.8	227.0	222.2	217.5	222.2	227.0	231.8
107.5°	165.2	217.2	269.3	293.4	289.5	285.7	281.8	278.0	281.8	285.7	289.5
110°	217.1	263.0	308.9	330.2	326.9	323.6	320.2	316.9	320.2	323.6	326.9



TEST NUMBER: P331303

CATALOG NUMBER: S122DIP-S485D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	338.4	349.8	361.1	365.3	362.4	359.4	356.5	353.5	356.5	359.4	362.4
115°	433.4	429.4	425.5	422.1	419.4	416.7	414.0	411.3	414.0	416.7	419.4
117.5°	483.4	480.7	477.9	475.0	472.0	469.0	466.0	463.0	466.0	469.0	472.0
120°	518.6	515.8	512.9	510.3	507.9	505.5	503.1	500.7	503.1	505.5	507.9
122.5°	551.9	548.8	545.6	542.8	540.3	537.8	535.3	532.8	535.3	537.8	540.3
125°	598.4	595.4	592.4	589.8	587.8	585.7	583.6	581.6	583.6	585.7	587.8
127.5°	641.7	639.5	637.2	634.9	632.6	630.4	628.1	625.8	628.1	630.4	632.6
130°	669.6	667.9	666.1	664.0	661.4	658.9	656.4	653.8	656.4	658.9	661.4
132.5°	696.5	694.8	693.0	691.1	688.9	686.8	684.6	682.4	684.6	686.8	688.9
135°	734.6	733.2	731.8	729.8	727.3	724.7	722.2	719.6	722.2	724.7	727.3
137.5°	769.3	767.7	766.1	764.4	762.6	760.8	759.0	757.3	759.0	760.8	762.6
140°	792.0	790.2	788.5	786.9	785.7	784.4	783.1	781.9	783.1	784.4	785.7
142.5°	812.6	810.6	808.6	807.0	805.9	804.8	803.6	802.5	803.6	804.8	805.9
145°	840.8	838.1	835.4	834.2	834.3	834.5	834.6	834.8	834.6	834.5	834.3
147.5°	866.9	864.3	861.6	860.6	861.2	861.8	862.4	863.0	862.4	861.8	861.2
150°	882.6	880.1	877.6	876.8	878.0	879.1	880.2	881.3	880.2	879.1	878.0
152.5°	897.2	894.8	892.4	891.8	893.0	894.3	895.5	896.7	895.5	894.3	893.0
155°	917.5	915.6	913.7	913.5	914.9	916.3	917.8	919.2	917.8	916.3	914.9
157.5°	934.7	933.4	932.0	932.0	933.2	934.4	935.6	936.8	935.6	934.4	933.2
160°	945.2	944.2	943.3	943.3	944.2	945.2	946.1	947.1	946.1	945.2	944.2
162.5°	954.0	953.2	952.4	952.4	953.4	954.4	955.3	956.3	955.3	954.4	953.4
165°	965.5	965.0	964.5	964.7	965.7	966.7	967.6	968.6	967.6	966.7	965.7
167.5°	974.5	974.1	973.6	973.9	974.9	975.8	976.8	977.7	976.8	975.8	974.9
170°	979.4	979.1	978.7	979.1	980.0	981.0	981.9	982.9	981.9	981.0	980.0
172.5°	982.8	982.5	982.2	982.5	983.4	984.4	985.3	986.3	985.3	984.4	983.4
175°	986.5	986.2	985.9	986.3	987.4	988.5	989.6	990.7	989.6	988.5	987.4
177.5°	987.8	987.6	987.5	987.9	988.8	989.7	990.6	991.5	990.6	989.7	988.8
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331303

CATALOG NUMBER: S122DIP-S485D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	958.9	957.1	950.8	947.5	942.2	937.1	933.8	935.3	936.5	935.9	935.0
5°	931.4	924.3	913.5	904.1	897.4	885.1	879.9	877.3	875.0	872.4	869.8
7.5°	898.7	887.5	872.0	858.7	846.1	830.8	822.1	816.8	811.4	805.5	800.3
10°	875.4	859.7	843.3	824.6	809.7	795.8	783.5	775.3	767.8	760.7	755.5
12.5°	850.9	832.8	812.5	787.0	770.5	750.7	748.9	734.4	722.7	718.3	712.2
15°	811.9	786.5	760.7	730.5	717.4	699.5	688.3	677.1	667.0	659.9	658.0
17.5°	767.6	734.7	709.1	687.4	666.0	647.6	637.3	628.3	620.0	610.5	609.3
20°	733.8	705.5	677.5	658.4	636.4	617.7	605.0	596.0	588.9	583.3	578.5
22.5°	701.9	670.8	645.2	624.3	602.6	587.5	577.5	568.9	563.0	556.8	552.2
25°	650.6	626.3	598.3	574.8	556.8	547.1	538.9	531.4	527.7	523.6	518.4
27.5°	605.7	578.7	552.5	534.3	518.5	509.9	504.1	499.0	495.5	493.1	490.1
30°	574.0	546.7	526.2	508.3	495.2	486.6	482.9	479.9	475.8	474.3	472.8
32.5°	543.5	519.0	501.4	485.9	473.4	467.8	464.4	461.7	458.5	457.0	454.0
35°	500.4	479.9	462.7	454.1	444.0	439.2	436.6	432.8	429.9	428.4	428.0
37.5°	459.9	442.0	430.7	419.7	415.4	412.4	408.9	406.3	405.4	405.2	404.8
40°	433.6	419.0	408.9	400.0	398.1	393.6	390.6	388.4	388.4	388.8	388.4
42.5°	409.7	396.6	387.7	380.0	377.8	375.1	372.1	372.0	372.6	373.8	372.6
45°	373.5	364.1	357.8	354.0	349.9	347.3	346.9	348.1	348.4	348.8	349.9
47.5°	340.1	333.9	328.2	324.1	322.3	321.8	321.4	323.3	325.1	325.8	327.5
50°	320.4	313.3	308.5	305.9	304.4	303.6	304.4	306.6	308.1	310.0	311.1
52.5°	298.3	293.3	290.0	287.9	287.3	287.8	287.9	290.5	292.9	293.5	294.1
55°	267.8	264.0	263.3	259.9	261.4	261.0	262.9	264.4	266.6	268.9	269.3
57.5°	237.3	234.3	232.3	232.6	233.0	234.7	236.2	238.9	241.3	243.6	243.9
60°	217.0	215.5	214.4	214.4	215.1	217.4	219.2	221.8	223.3	224.8	225.9
62.5°	198.5	197.0	195.8	196.4	198.4	199.7	201.9	203.3	204.8	206.3	206.8
65°	169.2	168.4	169.6	170.3	170.7	172.5	175.2	176.3	177.8	178.5	181.1
67.5°	142.2	142.4	142.2	143.3	145.4	145.9	148.3	151.0	151.3	152.7	154.4
70°	124.0	124.7	125.5	126.2	128.1	128.8	130.7	131.8	133.3	134.4	135.6
72.5°	107.3	107.4	108.2	108.0	109.6	111.2	112.8	113.9	115.4	116.8	117.9
75°	82.5	82.5	83.3	83.7	85.5	87.4	87.0	87.8	89.3	90.8	91.5
77.5°	60.3	59.5	60.3	60.6	61.2	62.8	63.1	64.2	65.9	65.4	66.2
80°	45.9	44.8	45.9	46.3	46.3	48.2	48.2	48.9	50.0	48.9	50.0
82.5°	32.8	32.3	33.1	33.2	33.8	33.8	34.4	34.6	35.7	35.2	35.7
85°	16.4	16.1	16.4	16.1	16.4	16.8	16.8	16.4	16.4	17.2	16.1
87.5°	6.6	6.6	6.6	6.8	6.8	6.7	6.6	6.8	6.9	6.5	6.6
90°	7.7	9.2	10.5	11.8	13.0	14.3	15.1	15.9	16.7	17.5	18.0
92.5°	13.8	14.1	14.7	15.3	16.0	16.6	17.0	17.4	17.8	18.2	18.6
95°	25.5	23.4	24.6	25.7	26.8	27.9	28.7	29.5	30.3	31.1	31.4
97.5°	33.1	27.0	29.6	32.2	34.8	37.3	38.0	38.6	39.2	39.9	40.3
100°	39.5	30.0	32.7	35.4	38.1	40.8	42.0	43.3	44.6	45.9	46.7
102.5°	145.9	132.3	109.7	87.1	64.5	41.9	43.6	45.2	46.9	48.5	49.6
105°	236.5	217.2	173.8	130.4	87.0	43.6	45.4	47.1	48.9	50.6	51.8
107.5°	293.4	269.3	217.2	165.2	113.1	61.1	59.3	57.5	55.7	54.0	53.4
110°	330.2	308.9	263.0	217.1	171.1	125.2	109.3	93.4	77.5	61.6	54.0



TEST NUMBER: P331303

CATALOG NUMBER: S122DIP-S485D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	365.3	361.1	349.8	338.4	327.1	315.7	257.8	199.8	141.8	83.8	55.0
115°	422.1	425.5	429.4	433.4	437.4	441.4	367.8	294.2	220.6	147.0	104.4
117.5°	475.0	477.9	480.7	483.4	486.1	488.9	471.1	453.3	435.4	417.6	389.9
120°	510.3	512.9	515.8	518.6	521.5	524.3	526.2	528.2	530.1	532.0	522.2
122.5°	542.8	545.6	548.8	551.9	555.0	558.1	559.2	560.4	561.5	562.7	561.2
125°	589.8	592.4	595.4	598.4	601.4	604.5	605.6	606.7	607.8	608.9	609.7
127.5°	634.9	637.2	639.5	641.7	644.0	646.2	647.9	649.5	651.1	652.7	653.6
130°	664.0	666.1	667.9	669.6	671.4	673.1	674.9	676.6	678.4	680.1	680.9
132.5°	691.1	693.0	694.8	696.5	698.3	700.0	701.5	703.0	704.5	706.0	706.7
135°	729.8	731.8	733.2	734.6	736.1	737.5	739.1	740.7	742.3	743.9	744.5
137.5°	764.4	766.1	767.7	769.3	770.9	772.6	774.1	775.7	777.2	778.8	779.3
140°	786.9	788.5	790.2	792.0	793.7	795.5	796.9	798.3	799.7	801.2	801.5
142.5°	807.0	808.6	810.6	812.6	814.6	816.6	817.9	819.2	820.5	821.8	822.1
145°	834.2	835.4	838.1	840.8	843.5	846.2	847.4	848.5	849.6	850.7	850.8
147.5°	860.6	861.6	864.3	866.9	869.6	872.3	873.1	873.9	874.8	875.6	875.7
150°	876.8	877.6	880.1	882.6	885.2	887.7	888.7	889.6	890.6	891.5	891.6
152.5°	891.8	892.4	894.8	897.2	899.6	902.0	903.0	903.9	904.9	905.9	905.8
155°	913.5	913.7	915.6	917.5	919.4	921.3	922.3	923.3	924.2	925.2	925.0
157.5°	932.0	932.0	933.4	934.7	936.0	937.4	938.5	939.5	940.6	941.7	941.6
160°	943.3	943.3	944.2	945.2	946.1	947.1	948.1	949.0	950.0	950.9	950.8
162.5°	952.4	952.4	953.2	954.0	954.9	955.7	956.8	957.8	958.9	960.0	959.9
165°	964.7	964.5	965.0	965.5	965.9	966.4	967.5	968.6	969.8	970.9	970.9
167.5°	973.9	973.6	974.1	974.5	975.0	975.4	976.5	977.7	978.8	979.9	979.7
170°	979.1	978.7	979.1	979.4	979.7	980.0	981.1	982.2	983.3	984.5	984.3
172.5°	982.5	982.2	982.5	982.8	983.1	983.4	984.6	985.7	986.8	987.9	987.7
175°	986.3	985.9	986.2	986.5	986.8	987.2	988.3	989.4	990.5	991.6	991.4
177.5°	987.9	987.5	987.6	987.8	987.9	988.0	988.9	989.8	990.7	991.6	991.5
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331303

CATALOG NUMBER: S122DIP-S485D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	932.0	931.4	931.4	928.7	931.4	931.4	932.0	935.0	935.9	936.5	935.3
5°	864.6	863.4	861.6	863.4	861.6	863.4	864.6	869.8	872.4	875.0	877.3
7.5°	797.9	793.4	792.7	788.3	792.7	793.4	797.9	800.3	805.5	811.4	816.8
10°	749.2	746.2	745.8	738.7	745.8	746.2	749.2	755.5	760.7	767.8	775.3
12.5°	712.1	704.9	706.4	702.3	706.4	704.9	712.1	712.2	718.3	722.7	734.4
15°	647.9	647.9	646.5	640.1	646.5	647.9	647.9	658.0	659.9	667.0	677.1
17.5°	601.9	601.1	597.5	599.3	597.5	601.1	601.9	609.3	610.5	620.0	628.3
20°	574.4	572.1	567.7	567.7	567.7	572.1	574.4	578.5	583.3	588.9	596.0
22.5°	548.4	548.2	543.5	545.0	543.5	548.2	548.4	552.2	556.8	563.0	568.9
25°	518.0	515.0	512.8	513.9	512.8	515.0	518.0	518.4	523.6	527.7	531.4
27.5°	489.2	487.5	487.4	484.3	487.4	487.5	489.2	490.1	493.1	495.5	499.0
30°	472.4	468.7	469.4	467.6	469.4	468.7	472.4	472.8	474.3	475.8	479.9
32.5°	453.3	452.0	451.2	449.6	451.2	452.0	453.3	454.0	457.0	458.5	461.7
35°	427.2	427.6	425.7	426.5	425.7	427.6	427.2	428.0	428.4	429.9	432.8
37.5°	404.5	405.7	404.8	405.0	404.8	405.7	404.5	404.8	405.2	405.4	406.3
40°	389.5	389.5	389.5	390.6	389.5	389.5	389.5	388.4	388.8	388.4	388.4
42.5°	375.2	374.6	374.0	373.9	374.0	374.6	375.2	372.6	373.8	372.6	372.0
45°	350.7	351.8	352.2	350.3	352.2	351.8	350.7	349.9	348.8	348.4	348.1
47.5°	328.5	328.6	328.5	330.1	328.5	328.6	328.5	327.5	325.8	325.1	323.3
50°	313.0	312.2	313.0	312.2	313.0	312.2	313.0	311.1	310.0	308.1	306.6
52.5°	296.5	296.7	296.2	296.1	296.2	296.7	296.5	294.1	293.5	292.9	290.5
55°	270.8	271.5	271.1	271.1	271.1	271.5	270.8	269.3	268.9	266.6	264.4
57.5°	244.1	244.8	245.3	243.6	245.3	244.8	244.1	243.9	243.6	241.3	238.9
60°	225.6	227.4	227.1	226.3	227.1	227.4	225.6	225.9	224.8	223.3	221.8
62.5°	208.5	209.2	209.1	209.0	209.1	209.2	208.5	206.8	206.3	204.8	203.3
65°	182.2	183.0	181.9	183.0	181.9	183.0	182.2	181.1	178.5	177.8	176.3
67.5°	153.9	154.2	155.0	155.5	155.0	154.2	153.9	154.4	152.7	151.3	151.0
70°	136.3	135.9	137.1	138.2	137.1	135.9	136.3	135.6	134.4	133.3	131.8
72.5°	117.8	118.6	118.2	119.1	118.2	118.6	117.8	117.9	116.8	115.4	113.9
75°	90.8	91.9	91.5	92.6	91.5	91.9	90.8	91.5	90.8	89.3	87.8
77.5°	65.6	65.7	65.6	66.2	65.6	65.7	65.6	66.2	65.4	65.9	64.2
80°	50.0	49.3	48.5	50.0	48.5	49.3	50.0	50.0	48.9	50.0	48.9
82.5°	34.8	35.3	34.5	34.5	34.5	35.3	34.8	35.7	35.2	35.7	34.6
85°	16.1	15.7	14.9	14.9	14.9	15.7	16.1	16.1	17.2	16.4	16.4
87.5°	6.7	6.4	6.5	6.3	6.5	6.4	6.7	6.6	6.5	6.9	6.8
90°	18.4	18.7	19.0	19.3	19.0	18.7	18.4	18.0	17.5	16.7	15.9
92.5°	18.7	18.9	19.1	19.3	19.1	18.9	18.7	18.6	18.2	17.8	17.4
95°	31.2	31.1	30.9	30.8	30.9	31.1	31.2	31.4	31.1	30.3	29.5
97.5°	40.5	40.7	40.9	41.1	40.9	40.7	40.5	40.3	39.9	39.2	38.6
100°	47.0	47.3	47.6	47.9	47.6	47.3	47.0	46.7	45.9	44.6	43.3
102.5°	50.0	50.5	50.9	51.4	50.9	50.5	50.0	49.6	48.5	46.9	45.2
105°	52.5	53.1	53.7	54.4	53.7	53.1	52.5	51.8	50.6	48.9	47.1
107.5°	54.0	54.7	55.3	55.9	55.3	54.7	54.0	53.4	54.0	55.7	57.5
110°	54.6	55.2	55.9	56.5	55.9	55.2	54.6	54.0	61.6	77.5	93.4



TEST NUMBER: P331303

CATALOG NUMBER: S122DIP-S485D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	55.6	56.1	56.6	57.1	56.6	56.1	55.6	55.0	83.8	141.8	199.8
115°	93.0	81.5	70.1	58.7	70.1	81.5	93.0	104.4	147.0	220.6	294.2
117.5°	352.3	314.7	277.1	239.5	277.1	314.7	352.3	389.9	417.6	435.4	453.3
120°	500.7	479.3	457.8	436.4	457.8	479.3	500.7	522.2	532.0	530.1	528.2
122.5°	557.0	552.8	548.7	544.5	548.7	552.8	557.0	561.2	562.7	561.5	560.4
125°	610.2	610.7	611.1	611.6	611.1	610.7	610.2	609.7	608.9	607.8	606.7
127.5°	653.7	653.8	653.9	654.0	653.9	653.8	653.7	653.6	652.7	651.1	649.5
130°	680.8	680.6	680.4	680.3	680.4	680.6	680.8	680.9	680.1	678.4	676.6
132.5°	706.5	706.4	706.2	706.0	706.2	706.4	706.5	706.7	706.0	704.5	703.0
135°	744.2	743.9	743.5	743.2	743.5	743.9	744.2	744.5	743.9	742.3	740.7
137.5°	778.8	778.2	777.7	777.1	777.7	778.2	778.8	779.3	778.8	777.2	775.7
140°	800.7	799.9	799.1	798.3	799.1	799.9	800.7	801.5	801.2	799.7	798.3
142.5°	821.3	820.5	819.7	818.9	819.7	820.5	821.3	822.1	821.8	820.5	819.2
145°	850.1	849.3	848.5	847.7	848.5	849.3	850.1	850.8	850.7	849.6	848.5
147.5°	875.0	874.3	873.7	873.0	873.7	874.3	875.0	875.7	875.6	874.8	873.9
150°	890.8	890.0	889.2	888.4	889.2	890.0	890.8	891.6	891.5	890.6	889.6
152.5°	904.8	903.7	902.7	901.6	902.7	903.7	904.8	905.8	905.9	904.9	903.9
155°	923.7	922.5	921.2	919.9	921.2	922.5	923.7	925.0	925.2	924.2	923.3
157.5°	940.4	939.1	937.9	936.7	937.9	939.1	940.4	941.6	941.7	940.6	939.5
160°	949.7	948.6	947.5	946.4	947.5	948.6	949.7	950.8	950.9	950.0	949.0
162.5°	958.5	957.1	955.8	954.4	955.8	957.1	958.5	959.9	960.0	958.9	957.8
165°	969.8	968.6	967.5	966.4	967.5	968.6	969.8	970.9	970.9	969.8	968.6
167.5°	978.3	976.9	975.4	974.0	975.4	976.9	978.3	979.7	979.9	978.8	977.7
170°	982.9	981.4	980.0	978.6	980.0	981.4	982.9	984.3	984.5	983.3	982.2
172.5°	986.3	984.9	983.4	982.0	983.4	984.9	986.3	987.7	987.9	986.8	985.7
175°	989.8	988.2	986.6	985.0	986.6	988.2	989.8	991.4	991.6	990.5	989.4
177.5°	990.3	989.2	988.0	986.9	988.0	989.2	990.3	991.5	991.6	990.7	989.8
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331303

CATALOG NUMBER: S122DIP-S485D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	933.8	937.1	942.2	947.5	950.8	957.1	958.9	961.9	964.6	970.8	977.4
5°	879.9	885.1	897.4	904.1	913.5	924.3	931.4	938.9	947.1	961.3	974.4
7.5°	822.1	830.8	846.1	858.7	872.0	887.5	898.7	913.5	925.7	945.7	964.9
10°	783.5	795.8	809.7	824.6	843.3	859.7	875.4	894.1	909.0	932.9	955.3
12.5°	748.9	750.7	770.5	787.0	812.5	832.8	850.9	874.9	889.6	918.0	941.6
15°	688.3	699.5	717.4	730.5	760.7	786.5	811.9	836.9	853.7	888.8	919.8
17.5°	637.3	647.6	666.0	687.4	709.1	734.7	767.6	794.0	816.8	856.9	893.6
20°	605.0	617.7	636.4	658.4	677.5	705.5	733.8	764.1	788.7	833.9	876.9
22.5°	577.5	587.5	602.6	624.3	645.2	670.8	701.9	734.8	760.7	809.4	853.0
25°	538.9	547.1	556.8	574.8	598.3	626.3	650.6	686.8	724.5	770.1	822.7
27.5°	504.1	509.9	518.5	534.3	552.5	578.7	605.7	640.0	678.0	727.4	783.0
30°	482.9	486.6	495.2	508.3	526.2	546.7	574.0	606.9	645.7	695.8	751.0
32.5°	464.4	467.8	473.4	485.9	501.4	519.0	543.5	576.4	613.4	662.6	723.8
35°	436.6	439.2	444.0	454.1	462.7	479.9	500.4	530.3	565.0	612.1	675.6
37.5°	408.9	412.4	415.4	419.7	430.7	442.0	459.9	485.1	519.2	566.7	627.2
40°	390.6	393.6	398.1	400.0	408.9	419.0	433.6	456.7	491.1	534.4	593.4
42.5°	372.1	375.1	377.8	380.0	387.7	396.6	409.7	429.6	460.0	502.2	560.6
45°	346.9	347.3	349.9	354.0	357.8	364.1	373.5	390.6	414.2	453.8	506.8
47.5°	321.4	321.8	322.3	324.1	328.2	333.9	340.1	354.1	375.2	406.8	458.4
50°	304.4	303.6	304.4	305.9	308.5	313.3	320.4	330.5	347.7	377.2	424.6
52.5°	287.9	287.8	287.3	287.9	290.0	293.3	298.3	306.9	322.3	349.4	391.2
55°	262.9	261.0	261.4	259.9	263.3	264.0	267.8	274.9	288.3	307.0	346.2
57.5°	236.2	234.7	233.0	232.6	232.3	234.3	237.3	242.9	253.2	269.6	301.4
60°	219.2	217.4	215.1	214.4	214.4	215.5	217.0	221.1	230.8	245.4	271.5
62.5°	201.9	199.7	198.4	196.4	195.8	197.0	198.5	201.4	208.4	222.1	244.6
65°	175.2	172.5	170.7	170.3	169.6	168.4	169.2	172.2	177.8	188.6	206.5
67.5°	148.3	145.9	145.4	143.3	142.2	142.4	142.2	144.8	148.1	157.4	170.8
70°	130.7	128.8	128.1	126.2	125.5	124.7	124.0	126.2	129.6	137.4	149.0
72.5°	112.8	111.2	109.6	108.0	108.2	107.4	107.3	108.6	111.4	118.6	127.5
75°	87.0	87.4	85.5	83.7	83.3	82.5	82.5	83.7	84.8	90.4	97.5
77.5°	63.1	62.8	61.2	60.6	60.3	59.5	60.3	61.0	61.6	65.4	70.6
80°	48.2	48.2	46.3	46.3	45.9	44.8	45.9	45.2	46.7	50.4	54.2
82.5°	34.4	33.8	33.8	33.2	33.1	32.3	32.8	33.5	34.1	36.7	38.9
85°	16.8	16.8	16.4	16.1	16.4	16.1	16.4	16.8	17.2	18.3	20.2
87.5°	6.6	6.7	6.8	6.8	6.6	6.6	6.6	6.6	6.8	6.8	6.7
90°	15.1	14.3	13.0	11.8	10.5	9.2	7.7	6.0	4.2	2.5	0.7
92.5°	17.0	16.6	16.0	15.3	14.7	14.1	13.8	14.0	14.1	14.3	14.4
95°	28.7	27.9	26.8	25.7	24.6	23.4	25.5	30.8	36.0	41.3	46.5
97.5°	38.0	37.3	34.8	32.2	29.6	27.0	33.1	47.9	62.7	77.5	92.3
100°	42.0	40.8	38.1	35.4	32.7	30.0	39.5	61.3	83.1	104.8	126.6
102.5°	43.6	41.9	64.5	87.1	109.7	132.3	145.9	150.6	155.2	159.8	164.4
105°	45.4	43.6	87.0	130.4	173.8	217.2	236.5	231.8	227.0	222.2	217.5
107.5°	59.3	61.1	113.1	165.2	217.2	269.3	293.4	289.5	285.7	281.8	278.0
110°	109.3	125.2	171.1	217.1	263.0	308.9	330.2	326.9	323.6	320.2	316.9



TEST NUMBER: P331303

CATALOG NUMBER: S122DIP-S485D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	257.8	315.7	327.1	338.4	349.8	361.1	365.3	362.4	359.4	356.5	353.5
115°	367.8	441.4	437.4	433.4	429.4	425.5	422.1	419.4	416.7	414.0	411.3
117.5°	471.1	488.9	486.1	483.4	480.7	477.9	475.0	472.0	469.0	466.0	463.0
120°	526.2	524.3	521.5	518.6	515.8	512.9	510.3	507.9	505.5	503.1	500.7
122.5°	559.2	558.1	555.0	551.9	548.8	545.6	542.8	540.3	537.8	535.3	532.8
125°	605.6	604.5	601.4	598.4	595.4	592.4	589.8	587.8	585.7	583.6	581.6
127.5°	647.9	646.2	644.0	641.7	639.5	637.2	634.9	632.6	630.4	628.1	625.8
130°	674.9	673.1	671.4	669.6	667.9	666.1	664.0	661.4	658.9	656.4	653.8
132.5°	701.5	700.0	698.3	696.5	694.8	693.0	691.1	688.9	686.8	684.6	682.4
135°	739.1	737.5	736.1	734.6	733.2	731.8	729.8	727.3	724.7	722.2	719.6
137.5°	774.1	772.6	770.9	769.3	767.7	766.1	764.4	762.6	760.8	759.0	757.3
140°	796.9	795.5	793.7	792.0	790.2	788.5	786.9	785.7	784.4	783.1	781.9
142.5°	817.9	816.6	814.6	812.6	810.6	808.6	807.0	805.9	804.8	803.6	802.5
145°	847.4	846.2	843.5	840.8	838.1	835.4	834.2	834.3	834.5	834.6	834.8
147.5°	873.1	872.3	869.6	866.9	864.3	861.6	860.6	861.2	861.8	862.4	863.0
150°	888.7	887.7	885.2	882.6	880.1	877.6	876.8	878.0	879.1	880.2	881.3
152.5°	903.0	902.0	899.6	897.2	894.8	892.4	891.8	893.0	894.3	895.5	896.7
155°	922.3	921.3	919.4	917.5	915.6	913.7	913.5	914.9	916.3	917.8	919.2
157.5°	938.5	937.4	936.0	934.7	933.4	932.0	932.0	933.2	934.4	935.6	936.8
160°	948.1	947.1	946.1	945.2	944.2	943.3	943.3	944.2	945.2	946.1	947.1
162.5°	956.8	955.7	954.9	954.0	953.2	952.4	952.4	953.4	954.4	955.3	956.3
165°	967.5	966.4	965.9	965.5	965.0	964.5	964.7	965.7	966.7	967.6	968.6
167.5°	976.5	975.4	975.0	974.5	974.1	973.6	973.9	974.9	975.8	976.8	977.7
170°	981.1	980.0	979.7	979.4	979.1	978.7	979.1	980.0	981.0	981.9	982.9
172.5°	984.6	983.4	983.1	982.8	982.5	982.2	982.5	983.4	984.4	985.3	986.3
175°	988.3	987.2	986.8	986.5	986.2	985.9	986.3	987.4	988.5	989.6	990.7
177.5°	988.9	988.0	987.9	987.8	987.6	987.5	987.9	988.8	989.7	990.6	991.5
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331303

CATALOG NUMBER: S122DIP-S485D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	976.8	978.3	983.1	987.9	993.2	994.7	997.1	995.0	994.4	1000.1	1004.3
5°	979.6	986.3	999.4	1011.3	1021.4	1028.5	1036.0	1039.0	1044.6	1052.4	1062.1
7.5°	976.4	989.5	1010.1	1027.5	1046.4	1060.1	1070.8	1079.9	1090.9	1105.8	1122.0
10°	972.9	990.4	1015.4	1036.7	1059.9	1077.4	1092.0	1106.2	1122.6	1143.2	1164.4
12.5°	966.3	987.1	1018.4	1043.6	1073.3	1090.6	1110.2	1140.8	1158.5	1187.1	1217.0
15°	953.1	976.2	1019.9	1050.9	1084.5	1117.4	1153.6	1182.7	1211.9	1228.7	1270.9
17.5°	933.4	967.4	1015.8	1052.0	1094.7	1146.4	1187.1	1220.2	1253.8	1281.0	1302.2
20°	917.6	954.6	1009.8	1053.2	1103.9	1159.6	1206.3	1239.9	1269.0	1291.8	1304.9
22.5°	897.6	944.1	997.9	1048.7	1113.5	1168.6	1217.6	1244.1	1268.4	1279.5	1284.5
25°	866.0	922.1	982.9	1044.9	1118.1	1176.4	1221.2	1237.3	1244.4	1233.5	1215.6
27.5°	832.1	894.5	965.7	1037.9	1115.3	1171.3	1203.4	1200.9	1188.9	1153.8	1125.8
30°	806.7	875.4	951.9	1030.7	1108.4	1162.9	1181.6	1162.9	1135.7	1096.5	1056.5
32.5°	780.1	851.2	937.3	1020.6	1095.9	1143.8	1147.9	1115.7	1073.5	1029.0	979.1
35°	739.8	816.8	909.7	997.9	1069.2	1099.5	1081.5	1024.8	974.7	913.9	845.9
37.5°	694.3	779.3	872.5	964.6	1029.3	1037.2	992.7	932.9	862.3	790.8	710.8
40°	660.3	750.3	846.3	939.2	996.4	988.2	931.4	865.7	781.6	694.3	619.9
42.5°	629.8	719.8	817.6	908.8	954.6	932.0	865.7	785.0	694.7	612.4	544.4
45°	577.0	669.6	769.7	857.8	884.0	843.3	755.5	665.9	577.0	508.3	454.5
47.5°	525.8	617.3	716.4	793.9	803.2	748.4	652.5	560.3	483.9	427.9	390.0
50°	488.1	580.0	678.2	747.3	744.3	678.2	579.6	491.8	428.0	382.8	357.4
52.5°	454.3	541.1	635.5	698.3	682.5	610.4	516.3	438.4	385.9	350.5	327.5
55°	401.8	482.1	571.8	622.2	593.1	513.1	433.6	370.8	332.0	305.5	287.6
57.5°	349.7	425.0	501.7	532.8	500.6	426.8	360.5	315.0	285.8	266.1	254.5
60°	317.4	383.2	451.5	478.4	439.9	374.2	321.9	281.2	257.7	241.6	231.2
62.5°	285.2	344.0	408.5	423.1	387.9	332.4	286.1	252.2	232.9	218.6	208.8
65°	241.3	289.4	338.4	348.1	315.6	272.6	236.0	214.0	196.8	186.4	178.5
67.5°	197.9	236.5	271.2	279.0	250.6	220.8	194.3	175.2	163.5	154.8	148.2
70°	172.2	202.8	231.2	237.5	214.7	188.2	168.1	152.7	142.3	134.8	128.5
72.5°	145.0	170.5	194.1	198.4	179.8	159.5	143.0	130.9	121.7	116.9	110.8
75°	110.9	125.9	144.2	145.3	133.0	120.6	107.9	100.1	95.2	89.3	86.3
77.5°	78.3	90.0	100.5	102.5	95.2	86.8	79.7	73.5	69.4	66.6	63.9
80°	59.8	69.1	73.6	76.2	71.0	65.0	60.9	56.8	54.2	52.3	50.4
82.5°	42.7	48.5	52.7	54.7	51.8	48.3	44.1	41.8	39.8	38.2	37.6
85°	21.7	24.3	26.9	27.6	26.9	25.4	23.2	23.2	22.0	21.7	21.7
87.5°	8.0	9.5	9.9	11.1	10.8	11.1	11.3	11.3	11.2	11.1	10.9
90°	2.5	4.2	6.0	7.7	9.2	10.5	11.8	13.0	14.3	15.1	15.9
92.5°	14.3	14.1	14.0	13.8	14.1	14.7	15.3	16.0	16.6	17.0	17.4
95°	41.3	36.0	30.8	25.5	23.4	24.6	25.7	26.8	27.9	28.7	29.5
97.5°	77.5	62.7	47.9	33.1	27.0	29.6	32.2	34.8	37.3	38.0	38.6
100°	104.8	83.1	61.3	39.5	30.0	32.7	35.4	38.1	40.8	42.0	43.3
102.5°	159.8	155.2	150.6	145.9	132.3	109.7	87.1	64.5	41.9	43.6	45.2
105°	222.2	227.0	231.8	236.5	217.2	173.8	130.4	87.0	43.6	45.4	47.1
107.5°	281.8	285.7	289.5	293.4	269.3	217.2	165.2	113.1	61.1	59.3	57.5
110°	320.2	323.6	326.9	330.2	308.9	263.0	217.1	171.1	125.2	109.3	93.4



TEST NUMBER: P331303

CATALOG NUMBER: S122DIP-S485D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	356.5	359.4	362.4	365.3	361.1	349.8	338.4	327.1	315.7	257.8	199.8
115°	414.0	416.7	419.4	422.1	425.5	429.4	433.4	437.4	441.4	367.8	294.2
117.5°	466.0	469.0	472.0	475.0	477.9	480.7	483.4	486.1	488.9	471.1	453.3
120°	503.1	505.5	507.9	510.3	512.9	515.8	518.6	521.5	524.3	526.2	528.2
122.5°	535.3	537.8	540.3	542.8	545.6	548.8	551.9	555.0	558.1	559.2	560.4
125°	583.6	585.7	587.8	589.8	592.4	595.4	598.4	601.4	604.5	605.6	606.7
127.5°	628.1	630.4	632.6	634.9	637.2	639.5	641.7	644.0	646.2	647.9	649.5
130°	656.4	658.9	661.4	664.0	666.1	667.9	669.6	671.4	673.1	674.9	676.6
132.5°	684.6	686.8	688.9	691.1	693.0	694.8	696.5	698.3	700.0	701.5	703.0
135°	722.2	724.7	727.3	729.8	731.8	733.2	734.6	736.1	737.5	739.1	740.7
137.5°	759.0	760.8	762.6	764.4	766.1	767.7	769.3	770.9	772.6	774.1	775.7
140°	783.1	784.4	785.7	786.9	788.5	790.2	792.0	793.7	795.5	796.9	798.3
142.5°	803.6	804.8	805.9	807.0	808.6	810.6	812.6	814.6	816.6	817.9	819.2
145°	834.6	834.5	834.3	834.2	835.4	838.1	840.8	843.5	846.2	847.4	848.5
147.5°	862.4	861.8	861.2	860.6	861.6	864.3	866.9	869.6	872.3	873.1	873.9
150°	880.2	879.1	878.0	876.8	877.6	880.1	882.6	885.2	887.7	888.7	889.6
152.5°	895.5	894.3	893.0	891.8	892.4	894.8	897.2	899.6	902.0	903.0	903.9
155°	917.8	916.3	914.9	913.5	913.7	915.6	917.5	919.4	921.3	922.3	923.3
157.5°	935.6	934.4	933.2	932.0	932.0	933.4	934.7	936.0	937.4	938.5	939.5
160°	946.1	945.2	944.2	943.3	943.3	944.2	945.2	946.1	947.1	948.1	949.0
162.5°	955.3	954.4	953.4	952.4	952.4	953.2	954.0	954.9	955.7	956.8	957.8
165°	967.6	966.7	965.7	964.7	964.5	965.0	965.5	965.9	966.4	967.5	968.6
167.5°	976.8	975.8	974.9	973.9	973.6	974.1	974.5	975.0	975.4	976.5	977.7
170°	981.9	981.0	980.0	979.1	978.7	979.1	979.4	979.7	980.0	981.1	982.2
172.5°	985.3	984.4	983.4	982.5	982.2	982.5	982.8	983.1	983.4	984.6	985.7
175°	989.6	988.5	987.4	986.3	985.9	986.2	986.5	986.8	987.2	988.3	989.4
177.5°	990.6	989.7	988.8	987.9	987.5	987.6	987.8	987.9	988.0	988.9	989.8
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331303

CATALOG NUMBER: S122DIP-S485D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1007.9	1012.1	1012.1	1012.7	1017.4	1016.9	1016.6
5°	1072.6	1078.9	1079.7	1086.4	1090.9	1089.4	1085.3
7.5°	1133.6	1145.4	1154.4	1159.4	1165.3	1168.9	1167.3
10°	1182.0	1199.2	1209.6	1216.7	1225.3	1231.7	1229.4
12.5°	1225.9	1246.4	1260.7	1272.9	1274.0	1282.2	1276.6
15°	1294.4	1316.1	1318.3	1327.3	1334.4	1333.6	1334.0
17.5°	1317.0	1324.0	1325.4	1325.6	1325.7	1323.1	1317.4
20°	1309.0	1306.4	1300.0	1295.2	1286.6	1285.4	1278.0
22.5°	1270.7	1262.4	1246.5	1236.0	1222.6	1219.1	1217.0
25°	1195.4	1177.1	1151.7	1127.5	1120.7	1107.7	1111.4
27.5°	1092.1	1063.6	1036.1	1016.4	998.6	979.0	984.6
30°	1019.5	987.4	948.6	918.7	899.7	881.0	877.6
32.5°	932.9	885.8	842.5	816.2	787.0	775.2	762.3
35°	783.5	737.6	694.6	657.7	636.4	619.9	605.0
37.5°	649.1	596.3	561.6	531.7	516.3	506.9	509.2
40°	565.8	519.5	494.1	471.3	457.1	450.4	451.9
42.5°	498.3	463.6	442.7	427.1	417.1	413.3	412.4
45°	421.6	402.2	385.0	376.1	371.2	367.1	364.5
47.5°	369.4	353.5	343.8	338.5	334.2	330.1	330.0
50°	338.0	327.5	320.8	315.2	311.8	308.8	311.5
52.5°	314.1	304.5	297.8	292.8	291.5	288.8	288.8
55°	278.6	271.1	266.3	261.8	259.6	258.1	256.2
57.5°	246.3	239.2	234.8	231.9	227.7	226.2	225.6
60°	223.3	217.7	213.2	209.5	207.6	204.7	204.7
62.5°	202.1	196.5	192.3	189.5	186.4	185.2	185.5
65°	171.4	166.9	162.8	159.8	159.1	156.9	157.6
67.5°	143.2	140.2	135.9	134.2	132.8	131.6	130.7
70°	124.4	121.4	119.1	116.9	115.8	115.8	115.8
72.5°	108.5	104.9	103.6	100.8	101.4	100.2	99.0
75°	84.0	81.8	80.7	79.5	77.7	77.7	77.7
77.5°	61.8	61.2	59.8	58.6	58.2	57.8	58.0
80°	47.8	47.4	46.7	46.7	45.9	45.6	44.8
82.5°	36.7	35.8	35.3	35.0	34.9	34.8	34.7
85°	20.9	20.2	20.2	20.5	19.8	19.8	20.2
87.5°	11.4	11.6	11.4	11.4	11.8	11.6	11.6
90°	16.7	17.5	18.0	18.4	18.7	19.0	19.3
92.5°	17.8	18.2	18.6	18.7	18.9	19.1	19.3
95°	30.3	31.1	31.4	31.2	31.1	30.9	30.8
97.5°	39.2	39.9	40.3	40.5	40.7	40.9	41.1
100°	44.6	45.9	46.7	47.0	47.3	47.6	47.9
102.5°	46.9	48.5	49.6	50.0	50.5	50.9	51.4
105°	48.9	50.6	51.8	52.5	53.1	53.7	54.4
107.5°	55.7	54.0	53.4	54.0	54.7	55.3	55.9
110°	77.5	61.6	54.0	54.6	55.2	55.9	56.5



TEST NUMBER: P331303

CATALOG NUMBER: S122DIP-S485D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	141.8	83.8	55.0	55.6	56.1	56.6	57.1
115°	220.6	147.0	104.4	93.0	81.5	70.1	58.7
117.5°	435.4	417.6	389.9	352.3	314.7	277.1	239.5
120°	530.1	532.0	522.2	500.7	479.3	457.8	436.4
122.5°	561.5	562.7	561.2	557.0	552.8	548.7	544.5
125°	607.8	608.9	609.7	610.2	610.7	611.1	611.6
127.5°	651.1	652.7	653.6	653.7	653.8	653.9	654.0
130°	678.4	680.1	680.9	680.8	680.6	680.4	680.3
132.5°	704.5	706.0	706.7	706.5	706.4	706.2	706.0
135°	742.3	743.9	744.5	744.2	743.9	743.5	743.2
137.5°	777.2	778.8	779.3	778.8	778.2	777.7	777.1
140°	799.7	801.2	801.5	800.7	799.9	799.1	798.3
142.5°	820.5	821.8	822.1	821.3	820.5	819.7	818.9
145°	849.6	850.7	850.8	850.1	849.3	848.5	847.7
147.5°	874.8	875.6	875.7	875.0	874.3	873.7	873.0
150°	890.6	891.5	891.6	890.8	890.0	889.2	888.4
152.5°	904.9	905.9	905.8	904.8	903.7	902.7	901.6
155°	924.2	925.2	925.0	923.7	922.5	921.2	919.9
157.5°	940.6	941.7	941.6	940.4	939.1	937.9	936.7
160°	950.0	950.9	950.8	949.7	948.6	947.5	946.4
162.5°	958.9	960.0	959.9	958.5	957.1	955.8	954.4
165°	969.8	970.9	970.9	969.8	968.6	967.5	966.4
167.5°	978.8	979.9	979.7	978.3	976.9	975.4	974.0
170°	983.3	984.5	984.3	982.9	981.4	980.0	978.6
172.5°	986.8	987.9	987.7	986.3	984.9	983.4	982.0
175°	990.5	991.6	991.4	989.8	988.2	986.6	985.0
177.5°	990.7	991.6	991.5	990.3	989.2	988.0	986.9
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6

(END OF REPORT)