

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931451

Luminaire Tested: DFN2DS-TR4F0-040DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931451
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-040DS927-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3136.3 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 38.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931451

CATALOG NUMBER: DFN2DS-TR4F0-040DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931451

CATALOG NUMBER: DFN2DS-TR4F0-040DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	979	979	979
5°	983	969	975
10°	977	959	964
15°	965	947	946
20°	948	928	927
25°	931	905	905
30°	909	884	876
35°	889	859	846
40°	863	833	818
45°	838	808	788
50°	810	782	754
55°	782	752	724
60°	749	716	689
65°	715	680	649
70°	672	636	606
75°	611	586	571
80°	543	526	499
85°	442	422	378

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 838 cd/sqm

TEST NUMBER: P931451

CATALOG NUMBER: DFN2DS-TR4F0-040DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.0	3.7
10°-20°	326.4	10.4
20°-30°	479.7	15.3
30°-40°	557.2	17.8
40°-50°	556.5	17.7
50°-60°	485.2	15.5
60°-70°	358.7	11.4
70°-80°	202.9	6.5
80°-90°	53.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	922.2	29.4
0°-40°	1479.4	47.2
0°-60°	2521.1	80.4
0°-90°	3136.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3136.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1233	1233	1233	1233	1233	
5°	1233	1228	1215	1224	1222	117
15°	1173	1166	1151	1156	1150	330
25°	1062	1053	1032	1035	1032	489
35°	916	904	886	878	872	572
45°	746	737	720	706	702	575
55°	564	557	543	529	523	504
65°	381	373	362	351	345	376
75°	199	197	191	184	186	213
85°	48	47	46	43	42	57
90°	0	0	0	0	0	

TEST NUMBER: P931451

CATALOG NUMBER: DFN2DS-TR4F0-040DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1232.7	1232.7	1232.7	1232.7	1232.7
2.5°	1239.9	1233.9	1220.9	1232.7	1230.5
5°	1232.7	1228.0	1214.9	1224.4	1222.1
7.5°	1224.4	1217.3	1204.2	1213.8	1211.4
10°	1211.4	1203.1	1189.0	1198.4	1194.8
12.5°	1193.5	1186.5	1172.3	1178.3	1175.8
15°	1173.4	1166.4	1150.9	1155.7	1149.8
17.5°	1148.6	1141.5	1126.1	1131.9	1126.1
20°	1121.2	1114.2	1097.6	1101.1	1096.5
22.5°	1094.1	1083.4	1067.9	1067.9	1065.6
25°	1062.0	1052.6	1032.5	1034.7	1032.5
27.5°	1026.4	1018.1	1002.8	999.3	993.4
30°	991.0	981.4	963.7	960.1	955.4
32.5°	953.0	946.0	927.0	919.8	915.0
35°	916.3	904.5	885.5	878.3	872.4
37.5°	874.8	864.1	845.1	836.8	830.9
40°	832.2	822.6	803.6	793.0	788.3
42.5°	790.7	781.1	762.2	750.3	743.2
45°	745.6	737.4	719.5	706.5	701.7
47.5°	701.7	693.4	674.5	661.4	654.4
50°	655.5	649.5	633.0	616.3	610.4
52.5°	610.4	602.2	586.8	573.7	565.4
55°	564.3	557.1	542.9	528.7	522.8
57.5°	518.0	512.1	496.6	482.4	477.7
60°	471.7	467.0	450.5	437.4	433.9
62.5°	426.7	418.4	406.6	394.7	390.0
65°	380.6	373.3	361.5	350.9	345.0
67.5°	333.1	327.1	316.6	308.2	303.5
70°	289.2	284.5	273.8	265.5	260.8
72.5°	244.3	239.4	233.6	225.2	221.7
75°	199.1	196.8	190.8	183.7	186.1
77.5°	158.8	154.0	151.7	148.1	144.6
80°	118.6	117.3	114.9	111.4	109.1
82.5°	80.6	80.6	79.5	74.7	74.7
85°	48.5	47.4	46.3	42.6	41.5
87.5°	21.4	19.0	16.6	13.1	11.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931451

CATALOG NUMBER: DFN2DS-TR4F0-040DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.21	12.82	11.57	13.13	13.45	10.77	12.38	11.13	12.69	13.00
	3H	12.96	14.41	13.34	14.74	15.10	12.47	13.92	12.85	14.25	14.61
	4H	13.61	14.98	14.00	15.32	15.70	13.11	14.48	13.51	14.83	15.20
	6H	14.08	15.34	14.49	15.71	16.10	13.57	14.84	13.98	15.21	15.60
	8H	14.22	15.43	14.64	15.82	16.22	13.72	14.93	14.14	15.32	15.71
	12H	14.31	15.47	14.74	15.85	16.28	13.80	14.96	14.23	15.34	15.77
4H	2H	11.77	13.14	12.17	13.49	13.86	11.42	12.79	11.82	13.13	13.51
	3H	13.75	14.89	14.15	15.29	15.69	13.34	14.48	13.75	14.88	15.28
	4H	14.52	15.56	14.95	15.97	16.41	14.10	15.13	14.53	15.55	15.98
	6H	15.12	16.02	15.57	16.46	16.92	14.69	15.59	15.14	16.03	16.49
	8H	15.31	16.15	15.77	16.60	17.06	14.87	15.72	15.33	16.16	16.62
	12H	15.44	16.20	15.92	16.68	17.14	14.99	15.75	15.47	16.22	16.69
8H	4H	14.80	15.64	15.26	16.08	16.55	14.42	15.27	14.88	15.71	16.18
	6H	15.51	16.21	16.00	16.70	17.18	15.13	15.83	15.62	16.32	16.79
	8H	15.77	16.40	16.28	16.91	17.39	15.38	16.01	15.89	16.51	17.00
	12H	15.97	16.53	16.48	17.02	17.58	15.56	16.11	16.06	16.60	17.16
12H	4H	14.82	15.58	15.30	16.06	16.53	14.46	15.22	14.94	15.69	16.16
	6H	15.55	16.19	16.06	16.69	17.18	15.19	15.82	15.70	16.32	16.81
	8H	15.87	16.43	16.38	16.92	17.48	15.49	16.05	16.00	16.54	17.10