

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331373

Luminaire Tested: **S122DIP-S675D1080U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331373
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S675D1080U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6555.5 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331373

CATALOG NUMBER: S122DIP-S675D1080U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331373

CATALOG NUMBER: S122DIP-S675D1080U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41																				
1	96	92	88	84	87	84	80	77	69	66	64	55	54	52	42	41	41	35																				
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29																				
3	80	70	63	57	72	64	58	53	53	49	45	43	39	37	33	31	29	25																				
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	21																				
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18																				
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19	16																				
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14																				
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13																				
9	49	37	30	25	45	34	27	23	29	23	20	24	20	17	19	16	14	12																				
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17142	17142	17142
5°	17208	16960	17058
10°	17105	16787	16870
15°	16893	16568	16552
20°	16593	16242	16225
25°	16295	15841	15841
30°	15910	15474	15340
35°	15554	15031	14808
40°	15104	14587	14309
45°	14661	14150	13798
50°	14179	13692	13205
55°	13678	13163	12673
60°	13120	12526	12064
65°	12520	11897	11351
70°	11759	11131	10603
75°	10699	10256	10000
80°	9493	9205	8731
85°	7762	7373	6614



TEST NUMBER: P331373

CATALOG NUMBER: S122DIP-S675D1080U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.8	1.5
10°-20°	280.9	4.3
20°-30°	412.9	6.3
30°-40°	479.6	7.3
40°-50°	479.1	7.3
50°-60°	417.8	6.4
60°-70°	308.9	4.7
70°-80°	175.0	2.7
80°-90°	52.5	0.8
90°-100°	87.2	1.3
100°-110°	270.9	4.1
110°-120°	463.1	7.1
120°-130°	608.9	9.3
130°-140°	683.5	10.4
140°-150°	670.1	10.2
150°-160°	562.1	8.6
160°-170°	372.8	5.7
170°-180°	130.3	2.0
0°-30°	793.6	12.1
0°-40°	1273.2	19.4
0°-60°	2170.1	33.1
0°-90°	2706.6	41.3
90°-120°	821.2	12.5
90°-150°	2783.7	42.5
90°-180°	3849.0	58.7
0°-180°	6555.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1062	1062	1062	1062	1062	
5°	1062	1057	1046	1054	1052	101
15°	1011	1004	991	995	990	284
25°	915	906	889	891	889	421
35°	789	779	763	756	751	492
45°	642	635	620	609	604	495
55°	486	479	468	456	450	434
65°	328	321	311	302	297	324
75°	172	169	164	159	160	183
85°	42	41	40	37	36	48
90°	1	16	41	39	40	5
95°	60	72	74	74	72	69
105°	250	253	256	258	258	264
115°	465	471	469	468	465	459
125°	676	686	683	680	678	604
135°	875	887	890	888	885	675
145°	1062	1070	1077	1078	1073	663
155°	1214	1217	1221	1226	1223	558
165°	1321	1320	1320	1327	1322	372
175°	1374	1371	1368	1376	1370	130
180°	1376	1376	1376	1376	1376	



TEST NUMBER: P331373

CATALOG NUMBER: S122DIP-S675D1080U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7
2.5°	1066.6	1065.7	1064.8	1063.9	1063.0	1061.5	1059.5	1057.5	1055.5	1053.5	1055.3
5°	1061.7	1060.8	1059.9	1059.0	1058.1	1056.4	1053.9	1051.4	1048.9	1046.4	1048.2
7.5°	1052.3	1050.9	1049.5	1048.1	1046.7	1044.7	1042.2	1039.6	1037.1	1034.5	1036.3
10°	1043.3	1041.7	1040.1	1038.5	1037.0	1034.8	1032.1	1029.4	1026.6	1023.9	1025.7
12.5°	1031.1	1029.7	1028.2	1026.8	1025.4	1023.4	1020.6	1017.9	1015.2	1012.5	1013.8
15°	1010.6	1009.3	1007.9	1006.6	1005.2	1003.0	1000.1	997.1	994.2	991.2	992.2
17.5°	984.5	983.1	981.8	980.4	979.1	976.9	973.9	970.9	967.9	964.9	966.0
20°	965.7	964.4	963.0	961.6	960.3	958.0	954.8	951.7	948.5	945.3	946.0
22.5°	946.9	945.0	943.1	941.2	939.3	936.9	933.9	930.9	927.9	924.9	925.0
25°	914.7	912.9	911.1	909.2	907.4	904.6	900.7	896.9	893.0	889.2	889.6
27.5°	877.9	876.3	874.7	873.0	871.4	869.1	866.0	863.0	859.9	856.9	856.2
30°	853.4	851.6	849.8	848.0	846.2	843.6	840.2	836.8	833.4	830.0	829.3
32.5°	827.3	825.8	824.4	822.9	821.5	819.0	815.4	811.8	808.2	804.6	803.4
35°	789.1	786.9	784.6	782.3	780.0	777.1	773.5	769.8	766.2	762.6	761.2
37.5°	746.0	744.0	742.0	740.0	738.1	735.2	731.6	728.0	724.4	720.7	719.0
40°	716.6	714.8	713.0	711.2	709.4	706.7	703.0	699.4	695.8	692.1	690.1
42.5°	688.1	686.2	684.4	682.6	680.8	678.1	674.4	670.8	667.2	663.6	661.3
45°	642.1	640.5	638.9	637.4	635.8	633.3	629.9	626.5	623.1	619.7	617.2
47.5°	596.4	594.9	593.4	591.9	590.4	587.9	584.3	580.8	577.3	573.7	571.1
50°	564.5	563.4	562.3	561.1	560.0	557.8	554.7	551.5	548.3	545.1	542.0
52.5°	533.5	532.0	530.5	529.0	527.5	525.3	522.3	519.3	516.3	513.3	510.7
55°	485.9	484.6	483.2	481.8	480.5	478.4	475.7	473.0	470.3	467.6	464.8
57.5°	438.1	437.1	436.0	434.9	433.8	431.8	428.8	425.8	422.8	419.8	417.1
60°	406.3	405.4	404.5	403.6	402.7	400.6	397.5	394.3	391.1	387.9	385.4
62.5°	375.3	373.8	372.4	370.9	369.5	367.5	365.1	362.6	360.2	357.7	355.4
65°	327.7	326.3	325.0	323.6	322.2	320.4	318.2	315.9	313.6	311.4	309.3
67.5°	279.3	278.2	277.1	276.0	274.9	273.4	271.3	269.3	267.3	265.2	263.6
70°	249.1	248.2	247.3	246.4	245.5	244.0	241.9	239.9	237.9	235.8	234.2
72.5°	218.1	217.1	216.2	215.3	214.4	213.3	212.0	210.7	209.4	208.0	206.5
75°	171.5	171.0	170.6	170.1	169.7	168.9	167.8	166.6	165.5	164.4	163.0
77.5°	129.9	129.1	128.3	127.5	126.8	126.2	125.7	125.2	124.8	124.3	123.7
80°	102.1	101.9	101.6	101.4	101.2	100.8	100.4	99.9	99.5	99.0	98.3
82.5°	76.0	75.9	75.9	75.8	75.8	75.6	75.3	75.1	74.8	74.5	73.7
85°	41.9	41.6	41.4	41.2	40.9	40.7	40.5	40.3	40.0	39.8	39.1
87.5°	14.9	15.2	15.4	15.7	16.0	16.5	17.2	18.0	18.8	19.6	18.9
90°	1.2	4.3	7.4	10.5	13.6	17.9	23.6	29.3	35.0	40.7	40.1
92.5°	20.7	22.9	25.2	27.5	29.8	31.6	32.9	34.3	35.6	36.9	37.0
95°	60.4	63.0	65.6	68.1	70.7	72.3	72.8	73.3	73.8	74.3	74.3
97.5°	110.4	112.6	114.9	117.2	119.4	121.1	122.0	123.0	124.0	125.0	125.0
100°	147.5	149.6	151.7	153.7	155.8	157.2	158.0	158.7	159.5	160.3	160.3
102.5°	186.6	188.2	189.9	191.5	193.2	194.5	195.5	196.4	197.4	198.4	198.6
105°	249.7	250.5	251.3	252.1	252.8	253.5	254.0	254.5	255.0	255.5	256.1
107.5°	313.4	314.5	315.7	316.8	317.9	318.5	318.5	318.5	318.5	318.5	318.7
110°	354.3	355.8	357.4	358.9	360.5	361.3	361.3	361.3	361.3	361.3	361.3



TEST NUMBER: P331373

CATALOG NUMBER: S122DIP-S675D1080U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	398.9	400.4	402.0	403.5	405.1	405.8	405.5	405.3	405.1	404.9	404.3
115°	464.6	466.2	467.7	469.3	470.8	471.3	470.8	470.3	469.8	469.3	469.0
117.5°	530.1	532.2	534.3	536.3	538.4	538.7	537.3	535.8	534.4	532.9	532.3
120°	573.8	575.9	578.0	580.0	582.1	582.1	580.0	578.0	575.9	573.8	573.8
122.5°	613.8	616.3	618.7	621.2	623.7	624.2	622.8	621.3	619.9	618.4	617.8
125°	676.0	678.4	680.7	683.0	685.3	686.1	685.3	684.6	683.8	683.0	682.2
127.5°	736.7	739.6	742.6	745.5	748.4	749.5	748.5	747.6	746.7	745.7	744.8
130°	774.8	778.1	781.5	784.8	788.2	789.6	789.1	788.6	788.1	787.6	787.0
132.5°	817.5	820.3	823.0	825.7	828.5	829.9	830.0	830.1	830.2	830.3	829.2
135°	874.7	877.5	880.4	883.2	886.0	887.7	888.2	888.7	889.3	889.8	889.5
137.5°	934.8	937.2	939.5	941.8	944.1	945.6	946.3	947.0	947.6	948.3	948.1
140°	971.1	973.4	975.7	978.1	980.4	982.2	983.5	984.8	986.1	987.3	987.3
142.5°	1008.3	1010.6	1012.9	1015.2	1017.5	1019.1	1020.0	1020.9	1021.8	1022.7	1022.9
145°	1061.7	1063.5	1065.3	1067.1	1068.9	1070.6	1072.1	1073.7	1075.2	1076.8	1077.0
147.5°	1109.3	1111.5	1113.6	1115.8	1118.0	1119.6	1120.6	1121.7	1122.7	1123.7	1124.3
150°	1141.8	1143.4	1144.9	1146.5	1148.0	1149.3	1150.4	1151.4	1152.4	1153.5	1154.2
152.5°	1170.6	1172.2	1173.7	1175.3	1176.8	1178.2	1179.5	1180.7	1182.0	1183.2	1184.2
155°	1213.9	1214.6	1215.4	1216.2	1217.0	1217.7	1218.5	1219.3	1220.1	1220.8	1222.1
157.5°	1250.8	1251.3	1251.8	1252.3	1252.9	1253.3	1253.8	1254.3	1254.7	1255.2	1257.0
160°	1273.1	1273.6	1274.1	1274.6	1275.2	1275.5	1275.8	1276.1	1276.3	1276.6	1278.1
162.5°	1293.5	1293.6	1293.7	1293.8	1294.0	1294.1	1294.4	1294.6	1294.9	1295.2	1296.9
165°	1320.7	1320.5	1320.2	1319.9	1319.7	1319.6	1319.6	1319.6	1319.6	1319.6	1321.4
167.5°	1343.5	1342.7	1341.9	1341.2	1340.4	1340.0	1339.9	1339.9	1339.8	1339.8	1341.6
170°	1355.6	1354.8	1354.0	1353.2	1352.5	1352.0	1351.7	1351.4	1351.2	1350.9	1352.7
172.5°	1363.9	1363.2	1362.4	1361.6	1360.8	1360.3	1360.1	1359.8	1359.5	1359.3	1361.1
175°	1374.2	1373.4	1372.6	1371.8	1371.1	1370.4	1369.9	1369.4	1368.9	1368.3	1370.2
177.5°	1378.3	1377.7	1377.1	1376.5	1375.9	1375.3	1374.9	1374.5	1374.1	1373.7	1374.9
180°	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5



TEST NUMBER: P331373

CATALOG NUMBER: S122DIP-S675D1080U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7
2.5°	1057.1	1059.0	1060.8	1061.5	1061.1	1060.8	1060.4	1060.1
5°	1050.0	1051.8	1053.6	1054.3	1053.9	1053.4	1053.0	1052.5
7.5°	1038.2	1040.0	1041.8	1042.4	1041.9	1041.5	1041.0	1040.5
10°	1027.5	1029.4	1031.2	1031.7	1031.1	1030.4	1029.7	1029.0
12.5°	1015.0	1016.3	1017.6	1017.9	1017.4	1017.0	1016.5	1016.0
15°	993.1	994.0	994.9	994.8	993.6	992.5	991.4	990.2
17.5°	967.0	968.0	969.1	969.1	968.0	966.9	965.8	964.7
20°	946.7	947.4	948.0	947.9	947.0	946.1	945.2	944.3
22.5°	925.2	925.3	925.4	925.2	924.7	924.1	923.6	923.1
25°	890.1	890.5	891.0	891.0	890.5	890.1	889.6	889.2
27.5°	855.5	854.9	854.2	853.3	852.2	851.1	850.0	848.9
30°	828.6	827.9	827.2	826.4	825.5	824.6	823.7	822.8
32.5°	802.2	801.0	799.7	798.7	797.8	796.9	795.9	795.0
35°	759.9	758.5	757.1	755.9	754.8	753.6	752.5	751.3
37.5°	717.4	715.7	714.0	712.6	711.5	710.4	709.4	708.3
40°	688.1	686.0	684.0	682.5	681.6	680.7	679.8	678.9
42.5°	659.1	656.9	654.7	652.9	651.6	650.4	649.1	647.8
45°	614.7	612.2	609.7	608.0	607.1	606.2	605.3	604.3
47.5°	568.5	565.8	563.2	561.2	559.9	558.6	557.3	556.0
50°	538.8	535.6	532.4	530.3	529.1	528.0	526.9	525.7
52.5°	508.0	505.4	502.8	500.7	499.2	497.7	496.2	494.7
55°	462.1	459.4	456.7	454.7	453.6	452.5	451.3	450.2
57.5°	414.4	411.7	409.1	407.3	406.4	405.6	404.7	403.8
60°	382.9	380.4	377.9	376.4	375.7	375.0	374.3	373.6
62.5°	353.1	350.8	348.5	346.9	346.0	345.1	344.3	343.4
65°	307.3	305.2	303.2	301.6	300.5	299.3	298.2	297.1
67.5°	262.0	260.5	258.9	257.6	256.7	255.8	254.9	254.0
70°	232.6	231.1	229.5	228.2	227.3	226.4	225.5	224.6
72.5°	204.9	203.3	201.7	200.5	199.8	199.1	198.4	197.6
75°	161.6	160.3	158.9	158.5	158.9	159.4	159.8	160.3
77.5°	123.0	122.3	121.6	121.0	120.3	119.7	119.1	118.4
80°	97.7	97.0	96.3	95.7	95.3	94.8	94.4	93.9
82.5°	72.8	71.9	71.1	70.6	70.5	70.4	70.3	70.2
85°	38.5	37.8	37.1	36.6	36.4	36.2	36.0	35.7
87.5°	18.3	17.6	17.0	16.6	16.5	16.3	16.2	16.1
90°	39.6	39.1	38.6	38.5	38.7	39.0	39.2	39.5
92.5°	37.1	37.2	37.4	37.4	37.5	37.5	37.6	37.6
95°	74.3	74.3	74.3	74.1	73.6	73.1	72.5	72.0
97.5°	125.0	125.0	125.0	125.0	124.9	124.9	124.8	124.8
100°	160.3	160.3	160.3	160.2	159.9	159.7	159.4	159.1
102.5°	198.8	199.0	199.2	199.2	198.9	198.7	198.4	198.2
105°	256.6	257.1	257.6	257.9	257.9	257.9	257.9	257.9
107.5°	318.9	319.1	319.3	318.8	317.7	316.5	315.3	314.1
110°	361.3	361.3	361.3	360.9	360.1	359.3	358.5	357.8



TEST NUMBER: P331373

CATALOG NUMBER: S122DIP-S675D1080U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	403.7	403.1	402.5	401.9	401.3	400.7	400.2	399.6
115°	468.8	468.5	468.2	467.7	467.0	466.2	465.4	464.6
117.5°	531.7	531.1	530.5	529.8	529.0	528.2	527.4	526.7
120°	573.8	573.8	573.8	573.4	572.7	571.9	571.1	570.3
122.5°	617.2	616.6	615.9	615.4	614.8	614.2	613.7	613.1
125°	681.5	680.7	679.9	679.4	679.1	678.9	678.6	678.4
127.5°	743.9	742.9	742.0	741.1	740.3	739.5	738.7	737.8
130°	786.5	786.0	785.5	784.7	783.7	782.6	781.6	780.6
132.5°	828.0	826.9	825.8	824.8	824.0	823.1	822.3	821.5
135°	889.3	889.0	888.7	888.2	887.4	886.7	885.9	885.1
137.5°	947.9	947.7	947.5	946.9	945.8	944.8	943.8	942.7
140°	987.3	987.3	987.3	986.8	985.8	984.8	983.7	982.7
142.5°	1023.1	1023.3	1023.5	1023.1	1022.0	1021.0	1020.0	1018.9
145°	1077.3	1077.6	1077.8	1077.4	1076.4	1075.4	1074.3	1073.3
147.5°	1124.9	1125.4	1126.0	1125.8	1124.8	1123.8	1122.8	1121.9
150°	1155.0	1155.8	1156.6	1156.6	1155.8	1155.0	1154.2	1153.5
152.5°	1185.2	1186.1	1187.1	1187.1	1186.1	1185.2	1184.2	1183.2
155°	1223.4	1224.7	1226.0	1226.2	1225.5	1224.7	1223.9	1223.1
157.5°	1258.7	1260.5	1262.2	1262.5	1261.2	1260.0	1258.8	1257.5
160°	1279.7	1281.2	1282.8	1283.0	1282.0	1281.0	1279.9	1278.9
162.5°	1298.7	1300.4	1302.2	1302.4	1301.2	1300.0	1298.7	1297.5
165°	1323.2	1325.0	1326.8	1327.0	1325.8	1324.5	1323.2	1321.9
167.5°	1343.4	1345.2	1347.0	1347.2	1345.9	1344.5	1343.2	1341.9
170°	1354.5	1356.3	1358.1	1358.3	1356.7	1355.2	1353.6	1352.1
172.5°	1362.9	1364.7	1366.5	1366.6	1365.1	1363.5	1362.0	1360.4
175°	1372.0	1373.8	1375.6	1375.7	1374.2	1372.6	1371.1	1369.5
177.5°	1376.2	1377.4	1378.6	1378.6	1377.4	1376.2	1374.9	1373.7
180°	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5

(END OF REPORT)